

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P246974

Luminaire Tested: **213-8LED3025-12-BK-DIFF**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246974  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-28)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 213-8LED3025-12-BK-DIFF  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD BLACK, DIFFUSED LENS  
Light Source: (1) SORAA 3000K 95 CRI 25°NFL LED SM16-07-25D-930-03  
Ballast/Driver: CHROMA POWER SUPPLY IN0004

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4000.0 lumens  
Efficiency: N/A  
Efficacy: 506.3 lumens/watt  
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.54  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246974  
CATALOG NUMBER: 213-8LED3025-12-BK-DIFF

### Luminous Intensity Polar Plot





TEST NUMBER: P246974  
 CATALOG NUMBER: 213-8LED3025-12-BK-DIFF

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82
5	97	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	79	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69
9	84	76	71	68	83	76	71	68	75	70	67	74	70	67	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	64	63

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	5373495
5°	4964231
10°	3973909
15°	2892111
20°	1921764
25°	1211853
30°	706606
35°	360299
40°	173639
45°	72914
50°	34924
55°	13075
60°	14999
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246974  
 CATALOG NUMBER: 213-8LED3025-12-BK-DIFF

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	889.4	22.2
10°-20°	1557.8	38.9
20°-30°	1035.9	25.9
30°-40°	400.1	10.0
40°-50°	94.8	2.4
50°-60°	20.2	0.5
60°-70°	1.8	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3483.0	87.1
0°-40°	3883.2	97.1
0°-60°	3998.2	100.0
0°-90°	4000.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4000.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10891	
5°	10023	889
15°	5662	1558
25°	2226	1036
35°	598	400
45°	104	95
55°	15	20
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246974  
CATALOG NUMBER: 213-8LED3025-12-BK-DIFF

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10891.2
1°	10815.4
2°	10680.6
3°	10517.1
4°	10293.0
5°	10023.4
6°	9694.7
7°	9322.3
8°	8889.2
9°	8425.8
10°	7932.1
12.5°	6782.8
15°	5662.1
17.5°	4615.7
20°	3660.2
22.5°	2868.1
25°	2226.1
27.5°	1688.5
30°	1240.3
32.5°	866.2
35°	598.2
37.5°	402.8
40°	269.6
42.5°	165.1
45°	104.5
47.5°	74.1
50°	45.5
52.5°	30.3
55°	15.2
57.5°	15.2
60°	15.2
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)