

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P246991

Luminaire Tested: **213-8LED3036-12-CS-LVR**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246991
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-46)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 213-8LED3036-12-CS-LVR
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD SILVER, HEX CELL LOUVER
Light Source: (1) SORAA 3000K 90 CRI LED
SM16-07-36D-930-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4000.0 lumens
Efficiency: N/A
Efficacy: 526.3 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.48
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246991
CATALOG NUMBER: 213-8LED3036-12-CS-LVR

Luminous Intensity Polar Plot





TEST NUMBER: P246991
 CATALOG NUMBER: 213-8LED3036-12-CS-LVR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96
2	111	107	104	102	109	106	103	101	103	100	99	100	98	96	97	96	95	93
3	107	103	99	96	106	101	98	95	99	96	94	97	94	93	95	93	91	90
4	104	99	95	92	102	98	94	91	96	92	90	94	91	89	92	90	88	87
5	101	95	91	88	99	94	90	87	92	89	87	91	88	86	90	87	85	84
6	98	92	87	84	97	91	87	84	89	86	83	88	85	83	87	84	82	81
7	95	88	84	81	94	88	84	81	87	83	81	86	83	80	85	82	80	79
8	92	86	81	78	91	85	81	78	84	81	78	83	80	78	82	80	77	76
9	90	83	79	76	89	83	79	76	82	78	76	81	78	75	80	77	75	74
10	87	81	76	74	87	80	76	74	80	76	73	79	76	73	78	75	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7577422
5°	6930232
10°	5530186
15°	3764070
20°	1884224
25°	648634
30°	199055
35°	96068
40°	50752
45°	33771
50°	12358
55°	13849
60°	15887
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246991
 CATALOG NUMBER: 213-8LED3036-12-CS-LVR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1242.4	31.1
10°-20°	1962.1	49.1
20°-30°	627.0	15.7
30°-40°	107.9	2.7
40°-50°	36.3	0.9
50°-60°	14.4	0.4
60°-70°	9.9	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3831.4	95.8
0°-40°	3939.3	98.5
0°-60°	3990.1	99.8
0°-90°	4000.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4000.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15358	
5°	13993	###
15°	7369	1962
25°	1192	627
35°	160	108
45°	48	36
55°	16	14
65°	0	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246991
CATALOG NUMBER: 213-8LED3036-12-CS-LVR

CANDELA DISTRIBUTION (FULL):

	0°
0°	15358.2
1°	15184.4
2°	14897.8
3°	14629.0
4°	14342.3
5°	13993.0
6°	13564.8
7°	13055.9
8°	12436.0
9°	11769.5
10°	11038.5
11°	10277.1
12°	9546.1
13°	8815.1
14°	8084.1
15°	7369.2
16°	6623.8
17°	5828.3
18°	5066.8
19°	4303.6
20°	3588.7
21°	2954.4
22°	2382.9
23°	1906.3
24°	1508.6
25°	1191.5
26°	904.8
27°	714.9
28°	555.4
29°	428.2
30°	349.4
32.5°	222.2
35°	159.5
37.5°	111.1
40°	78.8
42.5°	62.7
45°	48.4
47.5°	32.2
50°	16.1
52.5°	16.1
55°	16.1
57.5°	16.1
60°	16.1
62.5°	16.1
65°	0.0



TEST NUMBER: P246991
CATALOG NUMBER: 213-8LED3036-12-CS-LVR

CANDELA DISTRIBUTION (continued):

	0°
67.5°	16.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)