

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED2710-12-BK-LSL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-25)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED2710-12-BK-LSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD BLACK, LINEAR SPREAD LENS
Light Source: (1) SORAA 2700K 95 CRI 10°NSP LED
SM16-07-10D-927-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004


Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 2V
Luminaire Lumens:	230.8 lumens	Max Intensity:	1185.8 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	28.8 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	50.8°H x 11.9°V	Field Angle (10%):	61.2°H x 22.1°V
Beam Lumens:	112.7 lumens	Field Lumens:	188.9 lumens
Beam Efficiency:	48.9%	Field Efficiency:	81.8%

Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

Iso-Candela Plot




REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

Lumen Table




REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

Luminous Intensity Polar Plot



REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

Luminous Intensity Plot



Beam:
H Angle: 50.8°
V Angle: 11.9°
Lumens: 112.7
Efficiency: 48.9%

Field:
H Angle: 61.2°
V Angle: 22.1°
Lumens: 188.9
Efficiency: 81.8%

Spill:
Lumens: 41.9
Efficiency: 18.2%

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

FIELD
BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	1
40°	0	0	0	0	0	0	0	0	0	0	1
38.75°	0	0	0	0	0	0	0	0	0	1	1
37.5°	0	0	0	0	0	0	0	0	0	1	1
36.25°	0	0	0	0	0	0	0	0	1	1	1
35°	0	0	0	0	0	0	0	1	1	1	2

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	0	0	0	0	0	0	0	1	1	1	2
32.5°	0	0	0	0	0	0	1	1	1	2	2
31.25°	0	0	0	0	0	0	1	1	1	2	2
30°	0	0	0	0	0	1	1	1	2	2	3
28.75°	0	0	0	0	0	1	1	1	2	2	3
27.5°	0	0	0	0	0	1	1	1	2	3	4
26.25°	0	0	0	0	1	1	1	2	2	3	4
25°	0	0	0	0	1	1	1	2	3	3	4
23.75°	0	0	0	1	1	1	2	2	3	4	4
22.5°	0	0	0	1	1	1	2	2	3	4	4
21.25°	0	0	0	1	1	1	2	3	4	4	5
20°	0	0	1	1	1	1	2	3	4	4	5
18.75°	0	0	1	1	1	2	2	3	4	5	5
17.5°	0	0	1	1	1	2	2	3	4	5	5
16.25°	0	1	1	1	1	2	3	4	4	5	5
15°	0	1	1	1	1	2	3	4	5	5	6
13.75°	0	1	1	1	1	2	3	4	5	5	6
12.5°	0	1	1	1	1	2	3	4	5	5	6
11.25°	1	1	1	1	2	2	4	4	5	5	6
10°	1	1	1	1	2	2	4	5	5	6	6
8.75°	1	1	1	1	2	3	4	5	5	6	7
7.5°	1	1	1	1	2	3	4	5	5	6	7
6.25°	1	1	1	1	2	3	4	5	5	6	7
5°	1	1	1	1	2	3	4	5	5	6	7
3.75°	1	1	1	1	2	3	4	5	5	6	7
2.5°	1	1	1	1	2	3	4	5	5	6	7
1.25°	1	1	1	1	2	3	5	5	5	6	7
0°	1	1	1	1	2	3	5	5	5	6	7
-1.25°	1	1	1	1	2	3	5	5	5	6	7
-2.5°	1	1	1	1	2	3	4	5	5	6	7
-3.75°	1	1	1	1	2	3	4	5	5	6	7
-5°	1	1	1	1	2	3	4	5	5	6	7
-6.25°	1	1	1	1	2	3	4	5	5	6	7
-7.5°	1	1	1	1	2	3	4	5	5	6	7
-8.75°	1	1	1	1	2	3	4	5	5	6	7
-10°	1	1	1	1	2	2	4	5	5	6	6
-11.25°	1	1	1	1	2	2	4	4	5	5	6
-12.5°	1	1	1	1	1	2	3	4	5	5	6
-13.75°	1	1	1	1	1	2	3	4	5	5	6
-15°	1	1	1	1	1	2	3	4	5	5	6
-16.25°	0	1	1	1	1	2	3	4	4	5	5
-17.5°	0	1	1	1	1	2	2	3	4	5	5
-18.75°	0	1	1	1	1	2	2	3	4	5	5
-20°	0	1	1	1	1	1	2	3	4	4	5
-21.25°	0	1	1	1	1	1	2	3	4	4	5

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	0	0	1	1	1	1	2	2	3	4	4
-23.75°	0	0	1	1	1	1	2	2	3	4	4
-25°	0	0	1	1	1	1	1	2	3	3	4
-26.25°	0	0	1	1	1	1	1	2	2	3	4
-27.5°	0	0	0	1	1	1	1	1	2	3	4
-28.75°	0	0	0	1	1	1	1	1	2	2	3
-30°	0	0	0	1	1	1	1	1	2	2	3
-31.25°	0	0	0	0	1	1	1	1	1	2	2
-32.5°	0	0	0	0	1	1	1	1	1	2	2
-33.75°	0	0	0	0	1	1	1	1	1	1	2
-35°	0	0	0	0	0	1	1	1	1	1	2
-36.25°	0	0	0	0	0	1	1	1	1	1	1
-37.5°	0	0	0	0	0	0	1	1	1	1	1
-38.75°	0	0	0	0	0	0	1	1	1	1	1
-40°	0	0	0	0	0	0	0	1	1	1	1
-41.25°	0	0	0	0	0	0	0	1	1	1	1
-42.5°	0	0	0	0	0	0	0	0	1	1	1
-43.75°	0	0	0	0	0	0	0	0	0	1	1
-45°	0	0	0	0	0	0	0	0	0	0	1
-46.25°	0	0	0	0	0	0	0	0	0	0	1
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	1
51.25°	0	0	0	0	0	0	0	0	1	1	1
50°	0	0	0	0	0	0	1	1	1	1	1
48.75°	0	0	0	0	0	1	1	1	1	1	2
47.5°	0	0	0	0	1	1	1	1	2	2	2
46.25°	0	0	0	1	1	1	1	2	2	2	2
45°	0	0	1	1	1	1	2	2	2	2	3
43.75°	0	1	1	1	1	2	2	2	3	3	3
42.5°	1	1	1	1	2	2	2	3	3	3	4
41.25°	1	1	1	2	2	2	3	3	4	4	4
40°	1	1	2	2	2	3	3	4	4	5	5
38.75°	1	2	2	2	3	3	4	4	5	5	5
37.5°	1	2	2	3	3	4	4	5	5	5	6
36.25°	2	2	3	3	4	4	5	5	5	6	6
35°	2	3	3	4	4	4	5	5	6	6	6

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	2	3	4	4	4	5	5	6	6	6	7
32.5°	3	3	4	4	5	5	6	6	6	7	7
31.25°	3	4	4	4	5	6	6	6	7	7	7
30°	4	4	4	5	5	6	6	7	7	7	8
28.75°	4	4	5	5	6	6	7	7	7	8	8
27.5°	4	4	5	6	6	7	7	7	8	8	9
26.25°	4	5	5	6	6	7	7	8	8	9	9
25°	4	5	6	6	7	7	7	8	9	9	9
23.75°	5	5	6	7	7	7	8	9	9	9	10
22.5°	5	6	6	7	7	8	8	9	9	10	10
21.25°	5	6	7	7	7	8	9	9	10	10	11
20°	5	6	7	7	8	8	9	10	10	11	12
18.75°	6	6	7	7	8	9	9	10	10	11	12
17.5°	6	7	7	8	8	9	10	10	11	12	13
16.25°	6	7	7	8	9	10	10	10	12	13	14
15°	6	7	8	8	9	10	10	11	12	13	14
13.75°	7	7	8	9	9	10	11	11	13	14	15
12.5°	7	8	8	9	10	10	11	12	13	14	15
11.25°	7	8	8	9	10	11	11	13	14	15	16
10°	7	8	9	10	10	11	12	13	14	15	17
8.75°	7	8	9	10	11	11	12	13	15	16	18
7.5°	8	8	9	10	11	11	13	14	15	16	19
6.25°	8	8	9	10	11	12	13	14	16	17	20
5°	8	9	10	10	11	12	13	15	16	18	21
3.75°	8	9	10	11	11	12	13	15	16	18	21
2.5°	8	9	10	11	12	12	14	15	17	18	22
1.25°	8	9	10	11	12	13	14	15	17	19	23
0°	8	9	10	11	12	13	14	15	17	19	23
-1.25°	8	9	10	11	12	13	14	15	17	19	23
-2.5°	8	9	10	11	12	12	14	15	17	18	22
-3.75°	8	9	10	11	11	12	13	15	16	18	21
-5°	8	9	10	10	11	12	13	15	16	18	20
-6.25°	8	8	9	10	11	12	13	14	16	17	20
-7.5°	8	8	9	10	11	11	13	14	15	16	19
-8.75°	7	8	9	10	11	11	12	13	15	16	18
-10°	7	8	9	10	10	11	12	13	14	15	17
-11.25°	7	8	8	9	10	11	11	13	14	15	16
-12.5°	7	8	8	9	10	10	11	12	13	14	15
-13.75°	7	7	8	9	9	10	11	11	13	14	15
-15°	6	7	8	8	9	10	10	11	12	13	14
-16.25°	6	7	7	8	9	10	10	10	12	13	14
-17.5°	6	7	7	8	8	9	10	10	11	12	13
-18.75°	6	6	7	7	8	9	9	10	10	11	12
-20°	5	6	7	7	8	8	9	10	10	11	12
-21.25°	5	6	7	7	7	8	9	9	10	10	11

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	5	6	6	7	7	8	8	9	9	10	10
-23.75°	5	5	6	7	7	7	8	9	9	9	10
-25°	4	5	6	6	7	7	7	8	9	9	9
-26.25°	4	5	5	6	6	7	7	8	8	9	9
-27.5°	4	4	5	6	6	7	7	7	8	8	9
-28.75°	4	4	5	5	6	6	7	7	7	8	8
-30°	4	4	4	5	5	6	6	7	7	7	8
-31.25°	3	4	4	4	5	6	6	6	7	7	7
-32.5°	3	4	4	4	5	5	6	6	6	7	7
-33.75°	2	3	4	4	4	5	5	6	6	6	7
-35°	2	3	3	4	4	4	5	5	6	6	6
-36.25°	2	2	3	4	4	4	5	5	5	6	6
-37.5°	2	2	3	3	4	4	4	5	5	5	6
-38.75°	1	2	2	3	3	4	4	4	5	5	5
-40°	1	2	2	2	3	3	4	4	4	5	5
-41.25°	1	1	2	2	3	3	3	4	4	4	5
-42.5°	1	1	2	2	2	3	3	3	4	4	4
-43.75°	1	1	1	2	2	2	3	3	3	4	4
-45°	1	1	1	1	2	2	2	3	3	3	4
-46.25°	1	1	1	1	1	2	2	2	3	3	3
-47.5°	1	1	1	1	1	2	2	2	2	3	3
-48.75°	0	1	1	1	1	1	2	2	2	2	3
-50°	0	0	1	1	1	1	1	2	2	2	2
-51.25°	0	0	0	0	1	1	1	1	1	2	2
-52.5°	0	0	0	0	0	1	1	1	1	1	2
-53.75°	0	0	0	0	0	0	1	1	1	1	1
-55°	0	0	0	0	0	0	0	0	1	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	1	1	1
56.25°	0	0	0	0	0	1	1	1	1	1	1
55°	0	0	1	1	1	1	1	1	1	2	2
53.75°	1	1	1	1	1	1	1	2	2	2	2
52.5°	1	1	1	1	2	2	2	2	2	2	2
51.25°	1	1	2	2	2	2	2	2	3	3	3
50°	2	2	2	2	2	2	3	3	3	3	3
48.75°	2	2	2	2	3	3	3	3	4	4	4
47.5°	2	2	3	3	3	4	4	4	4	4	4
46.25°	3	3	3	4	4	4	4	4	5	5	5
45°	3	3	4	4	4	5	5	5	5	5	5
43.75°	4	4	5	5	5	5	5	5	5	5	6
42.5°	4	5	5	5	5	5	6	6	6	6	6
41.25°	5	5	5	5	6	6	6	6	6	6	6
40°	5	5	6	6	6	6	6	6	7	7	7
38.75°	6	6	6	6	6	6	7	7	7	7	7
37.5°	6	6	6	6	7	7	7	7	8	8	8
36.25°	6	6	7	7	7	7	8	8	8	8	9
35°	6	7	7	7	7	8	8	9	9	9	9

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	7	7	7	8	8	9	9	9	9	9	9
32.5°	7	8	8	8	9	9	9	9	10	10	10
31.25°	8	8	8	9	9	10	10	10	10	11	11
30°	8	9	9	9	10	10	10	11	11	12	12
28.75°	9	9	10	10	10	11	11	11	12	12	13
27.5°	9	10	10	11	11	11	12	12	13	13	13
26.25°	9	10	11	11	12	12	13	13	14	14	14
25°	10	11	11	12	12	13	14	14	15	15	16
23.75°	11	11	12	13	13	14	15	15	16	17	17
22.5°	11	12	13	13	14	15	16	17	18	19	20
21.25°	12	13	13	14	15	16	18	19	20	22	23
20°	13	13	14	15	16	18	20	21	24	25	27
18.75°	13	14	15	16	18	20	22	25	28	30	34
17.5°	14	14	16	18	20	22	25	29	32	38	43
16.25°	14	15	17	19	22	24	29	33	40	48	54
15°	15	17	19	21	24	28	33	39	50	59	74
13.75°	16	18	20	23	26	32	38	49	61	76	97
12.5°	17	19	22	27	31	39	44	60	74	99	124
11.25°	18	21	25	30	39	49	62	78	92	125	154
10°	19	22	28	34	48	61	85	107	137	166	195
8.75°	21	24	32	40	58	75	112	142	192	232	277
7.5°	22	27	35	49	70	98	142	188	252	308	369
6.25°	23	30	39	57	82	122	175	239	316	391	466
5°	24	33	43	66	94	147	209	292	384	476	566
3.75°	25	35	46	75	106	172	243	346	452	561	667
2.5°	26	38	50	83	118	196	277	398	520	645	767
1.25°	27	40	53	91	129	219	309	447	585	725	864
0°	27	42	56	97	139	238	338	491	644	800	955
-1.25°	27	40	53	91	129	218	307	443	578	715	850
-2.5°	26	37	50	83	117	194	273	390	507	625	739
-3.75°	25	35	46	74	105	169	238	335	434	533	627
-5°	24	32	42	65	92	144	203	279	361	441	515
-6.25°	23	30	39	56	80	118	168	225	290	351	407
-7.5°	21	27	35	48	68	94	135	175	224	265	304
-8.75°	20	24	31	40	56	72	104	130	164	188	210
-10°	19	21	28	34	46	58	78	95	112	122	130
-11.25°	18	20	25	29	37	46	56	66	72	90	105
-12.5°	17	19	22	26	30	36	39	50	60	75	88
-13.75°	16	18	19	23	25	30	35	43	52	61	73
-15°	15	16	18	20	23	26	31	35	43	50	59
-16.25°	14	15	17	18	21	23	27	31	36	42	46
-17.5°	14	14	16	17	19	21	24	27	30	35	39
-18.75°	13	14	15	16	17	19	21	24	26	29	32
-20°	13	13	14	15	16	17	19	20	23	25	27
-21.25°	12	13	13	14	15	16	17	19	20	22	23

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	11	12	13	13	14	15	16	17	18	19	20
-23.75°	11	11	12	13	13	14	14	15	16	17	17
-25°	10	11	11	12	12	13	14	14	15	15	16
-26.25°	9	10	11	11	12	12	13	13	14	14	15
-27.5°	9	10	10	11	11	11	12	12	13	13	13
-28.75°	9	9	10	10	10	11	11	11	12	12	13
-30°	8	9	9	9	10	10	10	11	11	12	12
-31.25°	8	8	8	9	9	10	10	10	10	11	11
-32.5°	7	8	8	8	9	9	9	10	10	10	11
-33.75°	7	7	7	8	8	9	9	9	9	10	10
-35°	6	7	7	7	7	8	8	9	9	9	9
-36.25°	6	6	7	7	7	7	8	8	9	9	9
-37.5°	6	6	6	6	7	7	7	8	8	8	8
-38.75°	6	6	6	6	6	7	7	7	7	8	8
-40°	5	5	6	6	6	6	6	7	7	7	7
-41.25°	5	5	5	5	6	6	6	6	6	6	7
-42.5°	4	5	5	5	5	5	6	6	6	6	6
-43.75°	4	4	5	5	5	5	5	5	5	5	6
-45°	4	4	4	4	4	5	5	5	5	5	5
-46.25°	3	4	4	4	4	4	4	4	5	5	5
-47.5°	3	3	3	4	4	4	4	4	4	4	4
-48.75°	3	3	3	3	3	3	4	4	4	4	4
-50°	2	3	3	3	3	3	3	3	3	3	4
-51.25°	2	2	2	3	3	3	3	3	3	3	3
-52.5°	2	2	2	2	2	3	3	3	3	3	3
-53.75°	1	2	2	2	2	2	2	3	3	3	3
-55°	1	1	1	2	2	2	2	2	2	2	3
-56.25°	1	1	1	1	1	1	2	2	2	2	2
-57.5°	0	1	1	1	1	1	1	1	1	2	2
-58.75°	0	0	0	0	1	1	1	1	1	1	1
-60°	0	0	0	0	0	0	0	1	1	1	1
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	2	2	2
56.25°	1	1	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	3
53.75°	2	2	2	2	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	5	5	5	5	5	5	5	5	5	5
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	5	5	5	6	6	6	6	6	6	6	6
43.75°	6	6	6	6	6	6	6	6	6	6	6
42.5°	6	6	6	6	6	7	7	7	7	7	7
41.25°	7	7	7	7	7	7	7	7	7	7	7
40°	7	7	7	7	7	7	7	7	8	8	8
38.75°	8	8	8	8	8	8	8	8	8	8	8
37.5°	8	8	8	8	8	8	8	9	9	9	9
36.25°	9	9	9	9	9	9	9	9	10	10	10
35°	9	9	9	10	10	10	10	10	10	10	10

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	10	10	10	11	11	11	11	11	11	11	11
32.5°	11	11	11	11	11	11	11	11	11	12	12
31.25°	11	12	12	12	12	12	12	12	12	12	12
30°	12	12	12	13	13	13	13	13	13	13	13
28.75°	13	13	14	14	14	14	14	14	14	14	14
27.5°	14	14	15	15	15	15	15	15	15	16	16
26.25°	15	15	16	16	17	17	17	17	17	18	18
25°	16	17	17	18	18	19	19	20	20	19	20
23.75°	18	18	19	20	21	21	22	22	22	22	21
22.5°	20	20	21	22	23	24	25	25	25	25	24
21.25°	23	23	24	25	27	28	28	29	29	29	28
20°	29	29	27	29	30	32	33	34	34	33	33
18.75°	37	38	37	33	35	37	38	39	40	40	40
17.5°	48	53	52	46	41	43	45	46	47	47	48
16.25°	66	72	74	71	58	50	52	54	55	57	58
15°	88	97	106	105	93	70	60	63	65	67	68
13.75°	114	134	145	146	136	114	82	73	76	79	81
12.5°	150	176	192	195	188	166	134	94	89	93	94
11.25°	194	225	244	252	246	223	193	155	112	107	119
10°	242	279	303	317	306	287	258	221	179	144	150
8.75°	314	336	367	379	371	355	326	292	262	229	196
7.5°	419	444	461	444	441	424	398	372	348	319	315
6.25°	524	558	575	556	535	499	475	457	437	430	429
5°	630	675	686	669	639	597	564	543	532	536	539
3.75°	737	793	796	781	740	691	650	617	610	625	653
2.5°	843	910	907	893	840	783	729	681	673	678	712
1.25°	946	1026	1017	1006	940	874	807	742	730	723	760
0°	1046	1137	1128	1118	1043	969	886	804	784	763	798
-1.25°	929	1004	995	982	916	850	782	717	704	696	730
-2.5°	808	868	862	846	792	734	680	631	622	626	655
-3.75°	686	731	729	711	668	618	575	541	533	546	570
-5°	565	596	597	576	543	499	464	442	437	448	449
-6.25°	446	464	466	441	413	375	364	362	354	350	342
-7.5°	331	336	332	306	315	314	305	294	280	258	244
-8.75°	220	221	246	260	265	262	250	232	212	187	154
-10°	159	184	204	217	218	213	199	178	151	123	125
-11.25°	130	151	166	175	176	168	152	130	101	99	105
-12.5°	104	121	132	138	137	128	111	87	84	87	89
-13.75°	82	95	104	107	103	93	75	71	73	76	78
-15°	67	73	80	80	75	64	60	63	65	67	67
-16.25°	53	57	60	60	53	50	53	55	57	59	59
-17.5°	42	45	46	44	42	44	46	48	50	52	52
-18.75°	34	35	36	35	37	39	40	42	43	45	45
-20°	28	28	28	30	32	34	35	36	37	38	39
-21.25°	24	24	25	26	28	29	30	31	32	33	33

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	20	21	22	23	24	25	26	27	27	28	28
-23.75°	18	19	20	21	22	22	23	23	24	24	24
-25°	16	17	18	19	20	20	20	21	21	21	21
-26.25°	15	16	17	17	18	18	19	19	19	19	19
-27.5°	14	15	15	16	16	17	17	17	17	17	18
-28.75°	13	14	14	14	15	15	15	16	16	16	16
-30°	12	13	13	13	14	14	14	14	14	15	15
-31.25°	12	12	12	12	13	13	13	13	13	13	14
-32.5°	11	11	12	12	12	12	12	12	12	13	13
-33.75°	10	11	11	11	11	12	12	12	12	12	12
-35°	9	10	10	10	11	11	11	11	11	11	11
-36.25°	9	9	9	10	10	10	10	10	11	11	11
-37.5°	9	9	9	9	9	9	9	10	10	10	10
-38.75°	8	8	8	9	9	9	9	9	9	9	9
-40°	8	8	8	8	8	8	8	8	8	8	8
-41.25°	7	7	7	8	8	8	8	8	8	8	8
-42.5°	6	7	7	7	7	7	7	8	8	8	8
-43.75°	6	6	6	6	7	7	7	7	7	7	7
-45°	5	5	5	6	6	6	6	6	6	6	7
-46.25°	5	5	5	5	5	5	5	5	6	6	6
-47.5°	4	5	5	5	5	5	5	5	5	5	5
-48.75°	4	4	4	4	4	4	5	5	5	5	5
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	3	3	3	3	3	4	4	4	4	4	4
-52.5°	3	3	3	3	3	3	3	3	3	4	4
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	2	2	3	3	3	3	3	3	3	3
-57.5°	2	2	2	2	2	2	2	2	2	3	3
-58.75°	1	2	2	2	2	2	2	2	2	2	2
-60°	1	1	1	1	1	1	1	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	0	0	0	0	0	1	1	1	1	1	1
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	6	6	6	6	6	6	6	6	6	6	6
43.75°	6	6	6	6	6	6	6	6	6	6	6
42.5°	7	7	7	7	7	6	6	6	7	7	7
41.25°	7	7	7	7	7	7	7	7	7	7	7
40°	8	8	8	7	7	7	7	7	7	7	8
38.75°	8	8	8	8	8	8	8	8	8	8	8
37.5°	9	9	9	9	8	8	8	8	8	9	9
36.25°	10	9	9	9	9	9	9	9	9	9	9
35°	10	10	10	10	10	10	10	10	10	10	10

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	11	11	11	11	11	11	11	11	11	11	11
32.5°	12	12	12	11	11	11	11	11	11	11	12
31.25°	13	13	13	13	13	12	12	12	13	13	13
30°	14	14	14	14	14	14	14	14	14	14	14
28.75°	15	15	15	15	15	15	15	15	15	15	15
27.5°	16	17	17	17	17	17	16	17	17	17	17
26.25°	18	18	19	19	19	18	18	18	19	19	19
25°	20	20	20	20	20	20	20	20	20	20	20
23.75°	22	22	23	23	23	23	22	23	23	23	23
22.5°	25	25	26	26	25	25	25	25	25	26	26
21.25°	28	29	30	30	30	29	29	29	30	30	30
20°	33	34	35	35	34	34	33	34	34	35	35
18.75°	39	40	41	42	42	42	41	42	42	42	41
17.5°	48	49	50	51	51	50	49	50	51	51	50
16.25°	57	57	59	59	59	59	58	59	59	59	59
15°	68	67	68	68	68	67	66	67	68	68	68
13.75°	80	78	78	81	81	81	79	81	81	81	78
12.5°	98	98	93	95	96	95	92	95	96	95	93
11.25°	124	122	117	122	126	126	121	126	126	122	117
10°	155	171	169	160	163	159	150	159	163	160	169
8.75°	225	239	233	233	247	253	239	253	247	233	233
7.5°	307	328	351	382	406	420	400	420	406	382	351
6.25°	431	451	510	570	610	628	608	628	610	570	510
5°	560	610	678	753	804	829	815	829	804	753	678
3.75°	692	759	835	905	961	995	982	995	961	905	835
2.5°	781	875	954	1020	1069	1107	1099	1107	1069	1020	954
1.25°	830	920	1012	1089	1136	1164	1171	1164	1136	1089	1012
0°	861	943	1029	1099	1144	1172	1186	1172	1144	1099	1029
-1.25°	795	880	971	1046	1094	1119	1124	1119	1094	1046	971
-2.5°	714	797	872	938	987	1018	1038	1018	987	938	872
-3.75°	601	652	718	781	833	863	862	863	833	781	718
-5°	459	485	530	593	632	677	695	677	632	593	530
-6.25°	327	326	365	400	416	463	472	463	416	400	365
-7.5°	217	230	243	252	261	289	292	289	261	252	243
-8.75°	168	175	170	164	172	181	182	181	172	164	170
-10°	129	136	134	128	131	132	130	132	131	128	134
-11.25°	109	108	105	108	111	112	110	112	111	108	105
-12.5°	91	91	89	91	92	92	91	92	92	91	89
-13.75°	78	77	78	80	81	81	80	81	81	80	78
-15°	68	67	69	70	70	70	69	70	70	70	69
-16.25°	59	59	61	62	62	62	62	62	62	62	61
-17.5°	52	53	54	54	55	55	54	55	55	54	54
-18.75°	46	47	48	48	48	48	48	48	48	48	48
-20°	40	41	42	42	42	42	41	42	42	42	42
-21.25°	33	34	35	35	35	35	34	35	35	35	35

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	29	29	29	29	29	28	27	28	29	29	29
-23.75°	24	25	25	25	25	25	24	25	25	25	25
-25°	22	22	22	22	22	21	21	21	22	22	22
-26.25°	19	20	20	20	20	20	20	20	20	20	20
-27.5°	18	18	18	18	18	18	18	18	18	18	18
-28.75°	17	17	17	17	17	17	17	17	17	17	17
-30°	15	15	15	16	16	16	16	16	16	16	15
-31.25°	14	14	14	14	14	14	14	14	14	14	14
-32.5°	13	13	13	13	13	13	13	13	13	13	13
-33.75°	12	12	12	12	12	12	12	12	12	12	12
-35°	11	11	11	11	11	11	11	11	11	11	11
-36.25°	11	11	11	11	11	11	11	11	11	11	11
-37.5°	10	10	10	10	10	10	10	10	10	10	10
-38.75°	9	9	9	9	9	9	9	9	9	9	9
-40°	8	8	8	8	8	8	8	8	8	8	8
-41.25°	8	8	8	8	8	8	8	8	8	8	8
-42.5°	8	8	8	7	7	7	7	7	7	7	8
-43.75°	7	7	7	7	7	7	7	7	7	7	7
-45°	7	7	7	7	7	6	6	6	7	7	7
-46.25°	6	6	6	6	6	6	6	6	6	6	6
-47.5°	5	5	5	5	5	5	6	5	5	5	5
-48.75°	5	5	5	5	5	5	5	5	5	5	5
-50°	4	4	5	5	5	5	5	5	5	5	5
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	3	3	4	4	4	4	4	4	4	4	4
-55°	3	3	3	3	4	4	4	4	4	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	1	1	1	1	1	1	1	0	0	0	0
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	2	2	2	2	1	1	1	1	1	1
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	2	2	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	3	3	3	2	2
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	6	6	6	6	6	6	6	6	6	6	5
43.75°	6	6	6	6	6	6	6	6	6	6	6
42.5°	7	7	7	7	7	7	7	7	6	6	6
41.25°	7	7	7	7	7	7	7	7	7	7	7
40°	8	8	8	8	8	7	7	7	7	7	7
38.75°	8	8	8	8	8	8	8	8	8	8	8
37.5°	9	9	9	9	9	9	8	8	8	8	8
36.25°	9	10	10	10	10	9	9	9	9	9	9
35°	10	10	10	10	10	10	10	10	10	10	9

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	11	11	11	11	11	11	11	11	11	11	10
32.5°	12	12	12	12	11	11	11	11	11	11	11
31.25°	13	13	12	12	12	12	12	12	12	12	12
30°	14	14	13	13	13	13	13	13	13	13	12
28.75°	15	15	14	14	14	14	14	14	14	14	14
27.5°	17	16	16	16	15	15	15	15	15	15	15
26.25°	18	18	18	18	17	17	17	17	17	16	16
25°	20	20	20	19	20	20	19	19	18	18	17
23.75°	22	22	21	22	22	22	22	21	21	20	19
22.5°	25	25	24	25	25	25	25	24	23	22	21
21.25°	29	28	28	29	29	29	28	28	27	25	24
20°	34	33	33	33	34	34	33	32	30	29	27
18.75°	40	39	40	40	40	39	38	37	35	33	37
17.5°	49	48	48	47	47	46	45	43	41	46	52
16.25°	57	57	58	57	55	54	52	50	58	71	74
15°	67	68	68	67	65	63	60	70	93	105	106
13.75°	78	80	81	79	76	73	82	114	136	146	145
12.5°	98	98	94	93	89	94	134	166	188	195	192
11.25°	122	124	119	107	112	155	193	223	246	252	244
10°	171	155	150	144	179	221	258	287	306	317	303
8.75°	239	225	196	229	262	292	326	355	371	379	367
7.5°	328	307	315	319	348	372	398	424	441	444	461
6.25°	451	431	429	430	437	457	475	499	535	556	575
5°	610	560	539	536	532	543	564	597	639	669	686
3.75°	759	692	653	625	610	617	650	691	740	781	796
2.5°	875	781	712	678	673	681	729	783	840	893	907
1.25°	920	830	760	723	730	742	807	874	940	1006	1017
0°	943	861	798	763	784	804	886	969	1043	1118	1128
-1.25°	880	795	730	696	704	717	782	850	916	982	995
-2.5°	797	714	655	626	622	631	680	734	792	846	862
-3.75°	652	601	570	546	533	541	575	618	668	711	729
-5°	485	459	449	448	437	442	464	499	543	576	597
-6.25°	326	327	342	350	354	362	364	375	413	441	466
-7.5°	230	217	244	258	280	294	305	314	315	306	332
-8.75°	175	168	154	187	212	232	250	262	265	260	246
-10°	136	129	125	123	151	178	199	213	218	217	204
-11.25°	108	109	105	99	101	130	152	168	176	175	166
-12.5°	91	91	89	87	84	87	111	128	137	138	132
-13.75°	77	78	78	76	73	71	75	93	103	107	104
-15°	67	68	67	67	65	63	60	64	75	80	80
-16.25°	59	59	59	59	57	55	53	50	53	60	60
-17.5°	53	52	52	52	50	48	46	44	42	44	46
-18.75°	47	46	45	45	43	42	40	39	37	35	36
-20°	41	40	39	38	37	36	35	34	32	30	28
-21.25°	34	33	33	33	32	31	30	29	28	26	25

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	29	29	28	28	27	27	26	25	24	23	22
-23.75°	25	24	24	24	24	23	23	22	22	21	20
-25°	22	22	21	21	21	21	20	20	20	19	18
-26.25°	20	19	19	19	19	19	19	18	18	17	17
-27.5°	18	18	18	17	17	17	17	17	16	16	15
-28.75°	17	17	16	16	16	16	15	15	15	14	14
-30°	15	15	15	15	14	14	14	14	14	13	13
-31.25°	14	14	14	13	13	13	13	13	13	12	12
-32.5°	13	13	13	13	12	12	12	12	12	12	12
-33.75°	12	12	12	12	12	12	12	12	11	11	11
-35°	11	11	11	11	11	11	11	11	11	10	10
-36.25°	11	11	11	11	11	10	10	10	10	10	9
-37.5°	10	10	10	10	10	10	9	9	9	9	9
-38.75°	9	9	9	9	9	9	9	9	9	9	8
-40°	8	8	8	8	8	8	8	8	8	8	8
-41.25°	8	8	8	8	8	8	8	8	8	8	7
-42.5°	8	8	8	8	8	8	7	7	7	7	7
-43.75°	7	7	7	7	7	7	7	7	7	6	6
-45°	7	7	7	6	6	6	6	6	6	6	5
-46.25°	6	6	6	6	6	5	5	5	5	5	5
-47.5°	5	5	5	5	5	5	5	5	5	5	5
-48.75°	5	5	5	5	5	5	5	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	3	3	3
-52.5°	4	4	4	4	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	2
-57.5°	3	3	3	3	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	1	1	0	0	0	0	0	0	0	0	0
57.5°	1	1	1	1	1	0	0	0	0	0	0
56.25°	1	1	1	1	1	1	1	1	0	0	0
55°	2	2	2	2	1	1	1	1	1	1	1
53.75°	2	2	2	2	2	2	1	1	1	1	1
52.5°	3	3	2	2	2	2	2	2	2	1	1
51.25°	3	3	3	3	3	2	2	2	2	2	2
50°	4	4	3	3	3	3	3	2	2	2	2
48.75°	4	4	4	4	4	3	3	3	3	2	2
47.5°	5	4	4	4	4	4	4	4	3	3	3
46.25°	5	5	5	5	5	4	4	4	4	4	3
45°	5	5	5	5	5	5	5	5	4	4	4
43.75°	6	6	6	5	5	5	5	5	5	5	5
42.5°	6	6	6	6	6	6	6	5	5	5	5
41.25°	7	7	6	6	6	6	6	6	6	5	5
40°	7	7	7	7	7	6	6	6	6	6	6
38.75°	8	8	7	7	7	7	7	6	6	6	6
37.5°	8	8	8	8	8	7	7	7	7	6	6
36.25°	9	9	9	8	8	8	8	7	7	7	7
35°	9	9	9	9	9	9	8	8	7	7	7

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	10	10	9	9	9	9	9	9	8	8	7
32.5°	11	11	10	10	10	9	9	9	9	8	8
31.25°	12	11	11	11	10	10	10	10	9	9	8
30°	12	12	12	12	11	11	10	10	10	9	9
28.75°	13	13	13	12	12	11	11	11	10	10	10
27.5°	14	14	13	13	13	12	12	11	11	11	10
26.25°	15	15	14	14	14	13	13	12	12	11	11
25°	17	16	16	15	15	14	14	13	12	12	11
23.75°	18	18	17	17	16	15	15	14	13	13	12
22.5°	20	20	20	19	18	17	16	15	14	13	13
21.25°	23	23	23	22	20	19	18	16	15	14	13
20°	29	29	27	25	24	21	20	18	16	15	14
18.75°	38	37	34	30	28	25	22	20	18	16	15
17.5°	53	48	43	38	32	29	25	22	20	18	16
16.25°	72	66	54	48	40	33	29	24	22	19	17
15°	97	88	74	59	50	39	33	28	24	21	19
13.75°	134	114	97	76	61	49	38	32	26	23	20
12.5°	176	150	124	99	74	60	44	39	31	27	22
11.25°	225	194	154	125	92	78	62	49	39	30	25
10°	279	242	195	166	137	107	85	61	48	34	28
8.75°	336	314	277	232	192	142	112	75	58	40	32
7.5°	444	419	369	308	252	188	142	98	70	49	35
6.25°	558	524	466	391	316	239	175	122	82	57	39
5°	675	630	566	476	384	292	209	147	94	66	43
3.75°	793	737	667	561	452	346	243	172	106	75	46
2.5°	910	843	767	645	520	398	277	196	118	83	50
1.25°	1026	946	864	725	585	447	309	219	129	91	53
0°	1137	1046	955	800	644	491	338	238	139	97	56
-1.25°	1004	929	850	715	578	443	307	218	129	91	53
-2.5°	868	808	739	625	507	390	273	194	117	83	50
-3.75°	731	686	627	533	434	335	238	169	105	74	46
-5°	596	565	515	441	361	279	203	144	92	65	42
-6.25°	464	446	407	351	290	225	168	118	80	56	39
-7.5°	336	331	304	265	224	175	135	94	68	48	35
-8.75°	221	220	210	188	164	130	104	72	56	40	31
-10°	184	159	130	122	112	95	78	58	46	34	28
-11.25°	151	130	105	90	72	66	56	46	37	29	25
-12.5°	121	104	88	75	60	50	39	36	30	26	22
-13.75°	95	82	73	61	52	43	35	30	25	23	19
-15°	73	67	59	50	43	35	31	26	23	20	18
-16.25°	57	53	46	42	36	31	27	23	21	18	17
-17.5°	45	42	39	35	30	27	24	21	19	17	16
-18.75°	35	34	32	29	26	24	21	19	17	16	15
-20°	28	28	27	25	23	20	19	17	16	15	14
-21.25°	24	24	23	22	20	19	17	16	15	14	13

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	21	20	20	19	18	17	16	15	14	13	13
-23.75°	19	18	17	17	16	15	14	14	13	13	12
-25°	17	16	16	15	15	14	14	13	12	12	11
-26.25°	16	15	15	14	14	13	13	12	12	11	11
-27.5°	15	14	13	13	13	12	12	11	11	11	10
-28.75°	14	13	13	12	12	11	11	11	10	10	10
-30°	13	12	12	12	11	11	10	10	10	9	9
-31.25°	12	12	11	11	10	10	10	10	9	9	8
-32.5°	11	11	11	10	10	10	9	9	9	8	8
-33.75°	11	10	10	10	9	9	9	9	8	8	7
-35°	10	9	9	9	9	9	8	8	7	7	7
-36.25°	9	9	9	9	9	8	8	7	7	7	7
-37.5°	9	9	8	8	8	8	7	7	7	6	6
-38.75°	8	8	8	8	7	7	7	7	6	6	6
-40°	8	8	7	7	7	7	6	6	6	6	6
-41.25°	7	7	7	6	6	6	6	6	6	5	5
-42.5°	7	6	6	6	6	6	6	5	5	5	5
-43.75°	6	6	6	5	5	5	5	5	5	5	5
-45°	5	5	5	5	5	5	5	5	4	4	4
-46.25°	5	5	5	5	5	4	4	4	4	4	4
-47.5°	5	4	4	4	4	4	4	4	4	4	3
-48.75°	4	4	4	4	4	4	4	3	3	3	3
-50°	4	4	4	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	2
-52.5°	3	3	3	3	3	3	3	3	2	2	2
-53.75°	3	3	3	3	3	3	2	2	2	2	2
-55°	3	3	3	2	2	2	2	2	2	2	1
-56.25°	2	2	2	2	2	2	2	1	1	1	1
-57.5°	2	2	2	2	1	1	1	1	1	1	1
-58.75°	2	1	1	1	1	1	1	1	1	0	0
-60°	1	1	1	1	1	1	0	0	0	0	0
-61.25°	1	1	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	1	1	0	0	0	0	0	0	0	0	0
52.5°	1	1	1	0	0	0	0	0	0	0	0
51.25°	1	1	1	1	1	0	0	0	0	0	0
50°	2	2	1	1	1	1	1	0	0	0	0
48.75°	2	2	2	1	1	1	1	1	0	0	0
47.5°	2	2	2	2	2	1	1	1	1	0	0
46.25°	3	3	2	2	2	2	1	1	1	1	0
45°	3	3	3	2	2	2	2	1	1	1	1
43.75°	4	4	3	3	3	2	2	2	1	1	1
42.5°	5	4	4	3	3	3	2	2	2	1	1
41.25°	5	5	4	4	4	3	3	2	2	2	1
40°	5	5	5	5	4	4	3	3	2	2	2
38.75°	6	6	5	5	5	4	4	3	3	2	2
37.5°	6	6	6	5	5	5	4	4	3	3	2
36.25°	6	6	6	6	5	5	5	4	4	3	3
35°	7	6	6	6	6	5	5	4	4	4	3

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	7	7	7	6	6	6	5	5	4	4	4
32.5°	8	7	7	7	6	6	6	5	5	4	4
31.25°	8	8	7	7	7	6	6	6	5	4	4
30°	9	8	8	7	7	7	6	6	5	5	4
28.75°	9	9	8	8	7	7	7	6	6	5	5
27.5°	10	9	9	8	8	7	7	7	6	6	5
26.25°	10	9	9	9	8	8	7	7	6	6	5
25°	11	10	9	9	9	8	7	7	7	6	6
23.75°	11	11	10	9	9	9	8	7	7	7	6
22.5°	12	11	10	10	9	9	8	8	7	7	6
21.25°	13	12	11	10	10	9	9	8	7	7	7
20°	13	13	12	11	10	10	9	8	8	7	7
18.75°	14	13	12	11	10	10	9	9	8	7	7
17.5°	14	14	13	12	11	10	10	9	8	8	7
16.25°	15	14	14	13	12	10	10	10	9	8	7
15°	17	15	14	13	12	11	10	10	9	8	8
13.75°	18	16	15	14	13	11	11	10	9	9	8
12.5°	19	17	15	14	13	12	11	10	10	9	8
11.25°	21	18	16	15	14	13	11	11	10	9	8
10°	22	19	17	15	14	13	12	11	10	10	9
8.75°	24	21	18	16	15	13	12	11	11	10	9
7.5°	27	22	19	16	15	14	13	11	11	10	9
6.25°	30	23	20	17	16	14	13	12	11	10	9
5°	33	24	21	18	16	15	13	12	11	10	10
3.75°	35	25	21	18	16	15	13	12	11	11	10
2.5°	38	26	22	18	17	15	14	12	12	11	10
1.25°	40	27	23	19	17	15	14	13	12	11	10
0°	42	27	23	19	17	15	14	13	12	11	10
-1.25°	40	27	23	19	17	15	14	13	12	11	10
-2.5°	37	26	22	18	17	15	14	12	12	11	10
-3.75°	35	25	21	18	16	15	13	12	11	11	10
-5°	32	24	20	18	16	15	13	12	11	10	10
-6.25°	30	23	20	17	16	14	13	12	11	10	9
-7.5°	27	21	19	16	15	14	13	11	11	10	9
-8.75°	24	20	18	16	15	13	12	11	11	10	9
-10°	21	19	17	15	14	13	12	11	10	10	9
-11.25°	20	18	16	15	14	13	11	11	10	9	8
-12.5°	19	17	15	14	13	12	11	10	10	9	8
-13.75°	18	16	15	14	13	11	11	10	9	9	8
-15°	16	15	14	13	12	11	10	10	9	8	8
-16.25°	15	14	14	13	12	10	10	10	9	8	7
-17.5°	14	14	13	12	11	10	10	9	8	8	7
-18.75°	14	13	12	11	10	10	9	9	8	7	7
-20°	13	13	12	11	10	10	9	8	8	7	7
-21.25°	13	12	11	10	10	9	9	8	7	7	7

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	12	11	10	10	9	9	8	8	7	7	6
-23.75°	11	11	10	9	9	9	8	7	7	7	6
-25°	11	10	9	9	9	8	7	7	7	6	6
-26.25°	10	9	9	9	8	8	7	7	6	6	5
-27.5°	10	9	9	8	8	7	7	7	6	6	5
-28.75°	9	9	8	8	7	7	7	6	6	5	5
-30°	9	8	8	7	7	7	6	6	5	5	4
-31.25°	8	8	7	7	7	6	6	6	5	4	4
-32.5°	8	7	7	7	6	6	6	5	5	4	4
-33.75°	7	7	7	6	6	6	5	5	4	4	4
-35°	7	6	6	6	6	5	5	4	4	4	3
-36.25°	6	6	6	6	5	5	5	4	4	4	3
-37.5°	6	6	6	5	5	5	4	4	4	3	3
-38.75°	6	6	5	5	5	4	4	4	3	3	2
-40°	5	5	5	5	4	4	4	3	3	2	2
-41.25°	5	5	5	4	4	4	3	3	3	2	2
-42.5°	5	4	4	4	4	3	3	3	2	2	2
-43.75°	4	4	4	4	3	3	3	2	2	2	1
-45°	4	4	4	3	3	3	2	2	2	1	1
-46.25°	4	3	3	3	3	2	2	2	1	1	1
-47.5°	3	3	3	3	2	2	2	2	1	1	1
-48.75°	3	3	3	2	2	2	2	1	1	1	1
-50°	3	2	2	2	2	2	1	1	1	1	1
-51.25°	2	2	2	2	1	1	1	1	1	0	0
-52.5°	2	2	2	1	1	1	1	1	0	0	0
-53.75°	2	1	1	1	1	1	1	0	0	0	0
-55°	1	1	1	1	1	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	1	0	0	0	0	0	0	0	0	0	0
42.5°	1	1	0	0	0	0	0	0	0	0	0
41.25°	1	1	1	0	0	0	0	0	0	0	0
40°	1	1	1	0	0	0	0	0	0	0	0
38.75°	2	1	1	1	0	0	0	0	0	0	0
37.5°	2	1	1	1	0	0	0	0	0	0	0
36.25°	2	2	1	1	1	0	0	0	0	0	0
35°	3	2	2	1	1	1	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	3	2	2	1	1	1	0	0	0	0	0
32.5°	3	3	2	2	1	1	1	0	0	0	0
31.25°	4	3	2	2	1	1	1	0	0	0	0
30°	4	4	3	2	2	1	1	1	0	0	0
28.75°	4	4	3	2	2	1	1	1	0	0	0
27.5°	4	4	4	3	2	1	1	1	0	0	0
26.25°	5	4	4	3	2	2	1	1	1	0	0
25°	5	4	4	3	3	2	1	1	1	0	0
23.75°	5	5	4	4	3	2	2	1	1	1	0
22.5°	6	5	4	4	3	2	2	1	1	1	0
21.25°	6	5	5	4	4	3	2	1	1	1	0
20°	6	5	5	4	4	3	2	1	1	1	1
18.75°	6	6	5	5	4	3	2	2	1	1	1
17.5°	7	6	5	5	4	3	2	2	1	1	1
16.25°	7	6	5	5	4	4	3	2	1	1	1
15°	7	6	6	5	5	4	3	2	1	1	1
13.75°	7	7	6	5	5	4	3	2	1	1	1
12.5°	8	7	6	5	5	4	3	2	1	1	1
11.25°	8	7	6	5	5	4	4	2	2	1	1
10°	8	7	6	6	5	5	4	2	2	1	1
8.75°	8	7	7	6	5	5	4	3	2	1	1
7.5°	8	8	7	6	5	5	4	3	2	1	1
6.25°	8	8	7	6	5	5	4	3	2	1	1
5°	9	8	7	6	5	5	4	3	2	1	1
3.75°	9	8	7	6	5	5	4	3	2	1	1
2.5°	9	8	7	6	5	5	4	3	2	1	1
1.25°	9	8	7	6	5	5	5	3	2	1	1
0°	9	8	7	6	5	5	5	3	2	1	1
-1.25°	9	8	7	6	5	5	5	3	2	1	1
-2.5°	9	8	7	6	5	5	4	3	2	1	1
-3.75°	9	8	7	6	5	5	4	3	2	1	1
-5°	9	8	7	6	5	5	4	3	2	1	1
-6.25°	8	8	7	6	5	5	4	3	2	1	1
-7.5°	8	8	7	6	5	5	4	3	2	1	1
-8.75°	8	7	7	6	5	5	4	3	2	1	1
-10°	8	7	6	6	5	5	4	2	2	1	1
-11.25°	8	7	6	5	5	4	4	2	2	1	1
-12.5°	8	7	6	5	5	4	3	2	1	1	1
-13.75°	7	7	6	5	5	4	3	2	1	1	1
-15°	7	6	6	5	5	4	3	2	1	1	1
-16.25°	7	6	5	5	4	4	3	2	1	1	1
-17.5°	7	6	5	5	4	3	2	2	1	1	1
-18.75°	6	6	5	5	4	3	2	2	1	1	1
-20°	6	5	5	4	4	3	2	1	1	1	1
-21.25°	6	5	5	4	4	3	2	1	1	1	1

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	6	5	4	4	3	2	2	1	1	1	1
-23.75°	5	5	4	4	3	2	2	1	1	1	1
-25°	5	4	4	3	3	2	1	1	1	1	1
-26.25°	5	4	4	3	2	2	1	1	1	1	1
-27.5°	4	4	4	3	2	1	1	1	1	1	0
-28.75°	4	4	3	2	2	1	1	1	1	1	0
-30°	4	4	3	2	2	1	1	1	1	1	0
-31.25°	4	3	2	2	1	1	1	1	1	0	0
-32.5°	4	3	2	2	1	1	1	1	1	0	0
-33.75°	3	2	2	1	1	1	1	1	1	0	0
-35°	3	2	2	1	1	1	1	1	0	0	0
-36.25°	2	2	1	1	1	1	1	1	0	0	0
-37.5°	2	2	1	1	1	1	1	0	0	0	0
-38.75°	2	1	1	1	1	1	1	0	0	0	0
-40°	2	1	1	1	1	1	0	0	0	0	0
-41.25°	1	1	1	1	1	1	0	0	0	0	0
-42.5°	1	1	1	1	1	0	0	0	0	0	0
-43.75°	1	1	1	1	0	0	0	0	0	0	0
-45°	1	1	1	0	0	0	0	0	0	0	0
-46.25°	1	1	1	0	0	0	0	0	0	0	0
-47.5°	1	1	0	0	0	0	0	0	0	0	0
-48.75°	1	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	1	0	0	0	0	0	0	0	0	0	0
15°	1	0	0	0	0	0	0	0	0	0	0
13.75°	1	0	0	0	0	0	0	0	0	0	0
12.5°	1	0	0	0	0	0	0	0	0	0	0
11.25°	1	1	0	0	0	0	0	0	0	0	0
10°	1	1	0	0	0	0	0	0	0	0	0
8.75°	1	1	0	0	0	0	0	0	0	0	0
7.5°	1	1	0	0	0	0	0	0	0	0	0
6.25°	1	1	0	0	0	0	0	0	0	0	0
5°	1	1	0	0	0	0	0	0	0	0	0
3.75°	1	1	0	0	0	0	0	0	0	0	0
2.5°	1	1	0	0	0	0	0	0	0	0	0
1.25°	1	1	0	0	0	0	0	0	0	0	0
0°	1	1	0	0	0	0	0	0	0	0	0
-1.25°	1	1	0	0	0	0	0	0	0	0	0
-2.5°	1	1	0	0	0	0	0	0	0	0	0
-3.75°	1	1	0	0	0	0	0	0	0	0	0
-5°	1	1	0	0	0	0	0	0	0	0	0
-6.25°	1	1	0	0	0	0	0	0	0	0	0
-7.5°	1	1	0	0	0	0	0	0	0	0	0
-8.75°	1	1	0	0	0	0	0	0	0	0	0
-10°	1	1	0	0	0	0	0	0	0	0	0
-11.25°	1	1	0	0	0	0	0	0	0	0	0
-12.5°	1	1	0	0	0	0	0	0	0	0	0
-13.75°	1	1	0	0	0	0	0	0	0	0	0
-15°	1	1	0	0	0	0	0	0	0	0	0
-16.25°	1	0	0	0	0	0	0	0	0	0	0
-17.5°	1	0	0	0	0	0	0	0	0	0	0
-18.75°	1	0	0	0	0	0	0	0	0	0	0
-20°	1	0	0	0	0	0	0	0	0	0	0
-21.25°	1	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0

REPORT NUMBER: P247009 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)