

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED2736-12-CS**

Issue Date: 3/3/2020

Test Information


Test Method: LM-79-08
Report Number: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-9)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED2736-12-CS
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD SILVER
Light Source: (1) SORAA 2700K 90 CRI LED
SM16-07-36D-927-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	339.1 lumens	Max Intensity:	985.9 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	44.6 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	35.1°H x 35.1°V	Field Angle (10%):	52.2°H x 52.2°V
Beam Lumens:	218 lumens	Field Lumens:	308.7 lumens
Beam Efficiency:	64.3%	Field Efficiency:	91.0%
Input Watts (W):	7.6		
Input Voltage (V):	NR		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2736-12-CS

Iso-Candela Plot




REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2736-12-CS

Lumen Table

90																
80	0.0	0.0		0.0		0.0		0.0		0.0		0.0		0.0		0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	
50	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.1	0.1	0.1	0.0	0.0	0.0	0.0
40		0.0	0.0	0.1	0.1	0.2	0.3	0.5	0.5	0.3	0.2	0.1	0.1	0.0	0.0	
30	0.0	0.0	0.0	0.1	0.2	0.5	1.7	4.0	4.0	1.7	0.5	0.2	0.1	0.0	0.0	0.0
20		0.0	0.1	0.1	0.3	1.7	8.7	17.1	17.1	8.7	1.7	0.3	0.1	0.1	0.0	
10	0.0	0.0	0.1	0.1	0.4	3.7	16.7	27.2	27.2	16.7	3.7	0.4	0.1	0.1	0.0	0.0
0		0.0	0.1	0.1	0.4	3.7	16.7	27.2	27.2	16.7	3.7	0.4	0.1	0.1	0.0	
-10	0.0	0.0	0.1	0.1	0.3	1.7	8.7	17.1	17.1	8.7	1.7	0.3	0.1	0.1	0.0	0.0
-20		0.0	0.0	0.1	0.2	0.5	1.7	4.0	4.0	1.7	0.5	0.2	0.1	0.0	0.0	
-30	0.0	0.0	0.0	0.1	0.1	0.2	0.3	0.5	0.5	0.3	0.2	0.1	0.1	0.0	0.0	0.0
-40		0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.1	0.1	0.1	0.0	0.0	0.0	
-50	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
-70																
-80	0.0	0.0		0.0		0.0		0.0		0.0		0.0		0.0		0.0
-90																

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2736-12-CS


Luminous Intensity Polar Plot





REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2736-12-CS

Luminous Intensity Plot



Beam:
H Angle: 35.1°
V Angle: 35.1°
Lumens: 218
Efficiency: 64.3%

Field:
H Angle: 52.2°
V Angle: 52.2°
Lumens: 308.7
Efficiency: 91.0%

Spill:
Lumens: 30.4
Efficiency: 9.0%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 0-Deg

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

FIELD
BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	1
55°	0	0	0	0	0	0	0	0	0	1	1
53.75°	0	0	0	0	0	0	0	0	0	1	1
52.5°	0	0	0	0	0	0	0	0	1	1	1
51.25°	0	0	0	0	0	0	0	0	1	1	1
50°	0	0	0	0	0	0	0	1	1	1	1
48.75°	0	0	0	0	0	0	0	1	1	1	1
47.5°	0	0	0	0	0	0	1	1	1	1	1
46.25°	0	0	0	0	0	0	1	1	1	1	1
45°	0	0	0	0	0	1	1	1	1	1	1
43.75°	0	0	0	0	0	1	1	1	1	1	1
42.5°	0	0	0	0	0	1	1	1	1	1	1
41.25°	0	0	0	0	1	1	1	1	1	1	1
40°	0	0	0	0	1	1	1	1	1	1	1
38.75°	0	0	0	0	1	1	1	1	1	1	1
37.5°	0	0	0	0	1	1	1	1	1	1	1
36.25°	0	0	0	1	1	1	1	1	1	1	1
35°	0	0	0	1	1	1	1	1	1	1	1

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	1	1	1	1	1	1	1	1
32.5°	0	0	0	1	1	1	1	1	1	1	1
31.25°	0	0	0	1	1	1	1	1	1	1	1
30°	0	0	1	1	1	1	1	1	1	1	1
28.75°	0	0	1	1	1	1	1	1	1	1	1
27.5°	0	0	1	1	1	1	1	1	1	1	1
26.25°	0	0	1	1	1	1	1	1	1	1	1
25°	0	0	1	1	1	1	1	1	1	1	1
23.75°	0	0	1	1	1	1	1	1	1	1	1
22.5°	0	0	1	1	1	1	1	1	1	1	1
21.25°	0	1	1	1	1	1	1	1	1	1	1
20°	0	1	1	1	1	1	1	1	1	1	1
18.75°	0	1	1	1	1	1	1	1	1	1	1
17.5°	0	1	1	1	1	1	1	1	1	1	1
16.25°	0	1	1	1	1	1	1	1	1	1	1
15°	0	1	1	1	1	1	1	1	1	1	1
13.75°	0	1	1	1	1	1	1	1	1	1	1
12.5°	0	1	1	1	1	1	1	1	1	1	1
11.25°	0	1	1	1	1	1	1	1	1	1	1
10°	0	1	1	1	1	1	1	1	1	1	1
8.75°	0	1	1	1	1	1	1	1	1	1	1
7.5°	0	1	1	1	1	1	1	1	1	1	1
6.25°	0	1	1	1	1	1	1	1	1	1	1
5°	0	1	1	1	1	1	1	1	1	1	1
3.75°	0	1	1	1	1	1	1	1	1	1	1
2.5°	0	1	1	1	1	1	1	1	1	1	1
1.25°	0	1	1	1	1	1	1	1	1	1	1
0°	0	1	1	1	1	1	1	1	1	1	1
-1.25°	0	1	1	1	1	1	1	1	1	1	1
-2.5°	0	1	1	1	1	1	1	1	1	1	1
-3.75°	0	1	1	1	1	1	1	1	1	1	1
-5°	0	1	1	1	1	1	1	1	1	1	1
-6.25°	0	1	1	1	1	1	1	1	1	1	1
-7.5°	0	1	1	1	1	1	1	1	1	1	1
-8.75°	0	1	1	1	1	1	1	1	1	1	1
-10°	0	1	1	1	1	1	1	1	1	1	1
-11.25°	0	1	1	1	1	1	1	1	1	1	1
-12.5°	0	1	1	1	1	1	1	1	1	1	1
-13.75°	0	1	1	1	1	1	1	1	1	1	1
-15°	0	1	1	1	1	1	1	1	1	1	1
-16.25°	0	1	1	1	1	1	1	1	1	1	1
-17.5°	0	1	1	1	1	1	1	1	1	1	1
-18.75°	0	1	1	1	1	1	1	1	1	1	1
-20°	0	1	1	1	1	1	1	1	1	1	1
-21.25°	0	1	1	1	1	1	1	1	1	1	1

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	1	1	1	1	1	1	1	1	1
-23.75°	0	0	1	1	1	1	1	1	1	1	1
-25°	0	0	1	1	1	1	1	1	1	1	1
-26.25°	0	0	1	1	1	1	1	1	1	1	1
-27.5°	0	0	1	1	1	1	1	1	1	1	1
-28.75°	0	0	1	1	1	1	1	1	1	1	1
-30°	0	0	1	1	1	1	1	1	1	1	1
-31.25°	0	0	0	1	1	1	1	1	1	1	1
-32.5°	0	0	0	1	1	1	1	1	1	1	1
-33.75°	0	0	0	1	1	1	1	1	1	1	1
-35°	0	0	0	1	1	1	1	1	1	1	1
-36.25°	0	0	0	1	1	1	1	1	1	1	1
-37.5°	0	0	0	0	1	1	1	1	1	1	1
-38.75°	0	0	0	0	1	1	1	1	1	1	1
-40°	0	0	0	0	1	1	1	1	1	1	1
-41.25°	0	0	0	0	1	1	1	1	1	1	1
-42.5°	0	0	0	0	0	1	1	1	1	1	1
-43.75°	0	0	0	0	0	1	1	1	1	1	1
-45°	0	0	0	0	0	1	1	1	1	1	1
-46.25°	0	0	0	0	0	0	1	1	1	1	1
-47.5°	0	0	0	0	0	0	1	1	1	1	1
-48.75°	0	0	0	0	0	0	0	1	1	1	1
-50°	0	0	0	0	0	0	0	1	1	1	1
-51.25°	0	0	0	0	0	0	0	0	1	1	1
-52.5°	0	0	0	0	0	0	0	0	1	1	1
-53.75°	0	0	0	0	0	0	0	0	0	1	1
-55°	0	0	0	0	0	0	0	0	0	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	1
66.25°	0	0	0	0	0	0	0	0	1	1	1
65°	0	0	0	0	0	0	1	1	1	1	1
63.75°	0	0	0	0	0	1	1	1	1	1	1
62.5°	0	0	0	0	1	1	1	1	1	1	1
61.25°	0	0	1	1	1	1	1	1	1	1	1
60°	0	1	1	1	1	1	1	1	1	1	1
58.75°	0	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	2
43.75°	1	1	1	1	1	1	1	1	1	2	2
42.5°	1	1	1	1	1	1	1	1	2	2	2
41.25°	1	1	1	1	1	1	1	1	2	2	2
40°	1	1	1	1	1	1	1	2	2	2	2
38.75°	1	1	1	1	1	1	1	2	2	2	2
37.5°	1	1	1	1	1	1	2	2	2	2	2
36.25°	1	1	1	1	1	1	2	2	2	2	2
35°	1	1	1	1	1	2	2	2	2	2	2

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	1	1	1	2	2	2	2	2	3
32.5°	1	1	1	1	2	2	2	2	2	2	3
31.25°	1	1	1	1	2	2	2	2	2	3	3
30°	1	1	1	2	2	2	2	2	2	3	3
28.75°	1	1	1	2	2	2	2	2	3	3	3
27.5°	1	1	1	2	2	2	2	2	3	3	4
26.25°	1	1	1	2	2	2	2	3	3	3	4
25°	1	1	2	2	2	2	2	3	3	4	4
23.75°	1	1	2	2	2	2	2	3	3	4	4
22.5°	1	1	2	2	2	2	3	3	3	4	4
21.25°	1	1	2	2	2	2	3	3	4	4	4
20°	1	2	2	2	2	2	3	3	4	4	4
18.75°	1	2	2	2	2	2	3	3	4	4	4
17.5°	1	2	2	2	2	3	3	3	4	4	4
16.25°	1	2	2	2	2	3	3	4	4	4	4
15°	1	2	2	2	2	3	3	4	4	4	4
13.75°	1	2	2	2	2	3	3	4	4	4	4
12.5°	2	2	2	2	2	3	3	4	4	4	4
11.25°	2	2	2	2	2	3	3	4	4	4	4
10°	2	2	2	2	3	3	3	4	4	4	4
8.75°	2	2	2	2	3	3	4	4	4	4	4
7.5°	2	2	2	2	3	3	4	4	4	4	4
6.25°	2	2	2	2	3	3	4	4	4	4	4
5°	2	2	2	2	3	3	4	4	4	4	4
3.75°	2	2	2	2	3	3	4	4	4	4	4
2.5°	2	2	2	2	3	3	4	4	4	4	4
1.25°	2	2	2	2	3	3	4	4	4	4	4
0°	2	2	2	2	3	3	4	4	4	4	4
-1.25°	2	2	2	2	3	3	4	4	4	4	4
-2.5°	2	2	2	2	3	3	4	4	4	4	4
-3.75°	2	2	2	2	3	3	4	4	4	4	4
-5°	2	2	2	2	3	3	4	4	4	4	4
-6.25°	2	2	2	2	3	3	4	4	4	4	4
-7.5°	2	2	2	2	3	3	4	4	4	4	4
-8.75°	2	2	2	2	3	3	4	4	4	4	4
-10°	2	2	2	2	3	3	3	4	4	4	4
-11.25°	2	2	2	2	2	3	3	4	4	4	4
-12.5°	2	2	2	2	2	3	3	4	4	4	4
-13.75°	1	2	2	2	2	3	3	4	4	4	4
-15°	1	2	2	2	2	3	3	4	4	4	4
-16.25°	1	2	2	2	2	3	3	4	4	4	4
-17.5°	1	2	2	2	2	3	3	3	4	4	4
-18.75°	1	2	2	2	2	2	3	3	4	4	4
-20°	1	2	2	2	2	2	3	3	4	4	4
-21.25°	1	1	2	2	2	2	3	3	4	4	4

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	1	1	2	2	2	2	3	3	3	4	4
-23.75°	1	1	2	2	2	2	2	3	3	4	4
-25°	1	1	2	2	2	2	2	3	3	4	4
-26.25°	1	1	1	2	2	2	2	3	3	3	4
-27.5°	1	1	1	2	2	2	2	2	3	3	4
-28.75°	1	1	1	2	2	2	2	2	3	3	3
-30°	1	1	1	2	2	2	2	2	2	3	3
-31.25°	1	1	1	1	2	2	2	2	2	3	3
-32.5°	1	1	1	1	2	2	2	2	2	2	3
-33.75°	1	1	1	1	1	2	2	2	2	2	3
-35°	1	1	1	1	1	2	2	2	2	2	2
-36.25°	1	1	1	1	1	1	2	2	2	2	2
-37.5°	1	1	1	1	1	1	2	2	2	2	2
-38.75°	1	1	1	1	1	1	1	2	2	2	2
-40°	1	1	1	1	1	1	1	2	2	2	2
-41.25°	1	1	1	1	1	1	1	1	2	2	2
-42.5°	1	1	1	1	1	1	1	1	2	2	2
-43.75°	1	1	1	1	1	1	1	1	1	2	2
-45°	1	1	1	1	1	1	1	1	1	1	2
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	0	1	1	1	1	1	1	1	1	1	1
-60°	0	1	1	1	1	1	1	1	1	1	1
-61.25°	0	0	1	1	1	1	1	1	1	1	1
-62.5°	0	0	0	0	1	1	1	1	1	1	1
-63.75°	0	0	0	0	0	1	1	1	1	1	1
-65°	0	0	0	0	0	0	1	1	1	1	1
-66.25°	0	0	0	0	0	0	0	0	1	1	1
-67.5°	0	0	0	0	0	0	0	0	0	0	1
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	1
71.25°	0	0	0	0	0	0	1	1	1	1	1
70°	0	0	0	1	1	1	1	1	1	1	1
68.75°	0	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	2	2
53.75°	1	1	1	1	1	1	1	2	2	2	2
52.5°	1	1	1	1	1	2	2	2	2	2	2
51.25°	1	1	1	1	2	2	2	2	2	2	2
50°	1	1	1	2	2	2	2	2	2	2	2
48.75°	1	1	2	2	2	2	2	2	2	2	3
47.5°	1	2	2	2	2	2	2	2	2	3	3
46.25°	2	2	2	2	2	2	2	3	3	3	3
45°	2	2	2	2	2	2	3	3	3	3	4
43.75°	2	2	2	2	2	3	3	3	3	4	4
42.5°	2	2	2	2	3	3	3	3	4	4	4
41.25°	2	2	2	3	3	3	3	4	4	4	4
40°	2	2	3	3	3	3	4	4	4	4	4
38.75°	2	2	3	3	3	4	4	4	4	4	4
37.5°	2	3	3	3	4	4	4	4	4	4	4
36.25°	3	3	3	4	4	4	4	4	4	4	4
35°	3	3	4	4	4	4	4	4	4	4	4

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	3	3	4	4	4	4	4	4	4	4	4
32.5°	3	4	4	4	4	4	4	4	4	4	5
31.25°	3	4	4	4	4	4	4	4	4	5	5
30°	4	4	4	4	4	4	4	4	5	5	5
28.75°	4	4	4	4	4	4	4	4	5	5	5
27.5°	4	4	4	4	4	4	4	5	5	5	5
26.25°	4	4	4	4	4	4	5	5	5	5	5
25°	4	4	4	4	4	4	5	5	5	5	5
23.75°	4	4	4	4	4	5	5	5	5	5	6
22.5°	4	4	4	4	4	5	5	5	5	5	6
21.25°	4	4	4	4	5	5	5	5	5	6	6
20°	4	4	4	4	5	5	5	5	5	6	7
18.75°	4	4	4	4	5	5	5	5	6	6	7
17.5°	4	4	4	5	5	5	5	5	6	7	8
16.25°	4	4	4	5	5	5	5	5	6	7	8
15°	4	4	4	5	5	5	5	6	6	7	9
13.75°	4	4	4	5	5	5	5	6	7	8	9
12.5°	4	4	5	5	5	5	5	6	7	8	9
11.25°	4	4	5	5	5	5	6	6	7	8	10
10°	4	4	5	5	5	5	6	7	7	9	10
8.75°	4	4	5	5	5	5	6	7	8	9	11
7.5°	4	4	5	5	5	5	6	7	8	9	11
6.25°	4	4	5	5	5	5	6	7	8	10	11
5°	4	5	5	5	5	5	6	7	8	10	11
3.75°	4	5	5	5	5	5	6	7	8	10	12
2.5°	4	5	5	5	5	5	6	7	9	10	12
1.25°	4	5	5	5	5	5	6	7	9	10	12
0°	4	5	5	5	5	6	6	7	9	10	12
-1.25°	4	5	5	5	5	5	6	7	9	10	12
-2.5°	4	5	5	5	5	5	6	7	9	10	12
-3.75°	4	5	5	5	5	5	6	7	8	10	12
-5°	4	5	5	5	5	5	6	7	8	10	11
-6.25°	4	4	5	5	5	5	6	7	8	10	11
-7.5°	4	4	5	5	5	5	6	7	8	9	11
-8.75°	4	4	5	5	5	5	6	7	8	9	11
-10°	4	4	5	5	5	5	6	7	7	9	10
-11.25°	4	4	5	5	5	5	6	6	7	8	10
-12.5°	4	4	5	5	5	5	5	6	7	8	9
-13.75°	4	4	4	5	5	5	5	6	7	8	9
-15°	4	4	4	5	5	5	5	6	6	7	9
-16.25°	4	4	4	5	5	5	5	5	6	7	8
-17.5°	4	4	4	5	5	5	5	5	6	7	8
-18.75°	4	4	4	4	5	5	5	5	6	6	7
-20°	4	4	4	4	5	5	5	5	5	6	7
-21.25°	4	4	4	4	5	5	5	5	5	6	6

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	4	4	4	4	4	5	5	5	5	5	6
-23.75°	4	4	4	4	4	5	5	5	5	5	6
-25°	4	4	4	4	4	4	5	5	5	5	5
-26.25°	4	4	4	4	4	4	5	5	5	5	5
-27.5°	4	4	4	4	4	4	4	5	5	5	5
-28.75°	4	4	4	4	4	4	4	4	5	5	5
-30°	4	4	4	4	4	4	4	4	5	5	5
-31.25°	3	4	4	4	4	4	4	4	4	5	5
-32.5°	3	4	4	4	4	4	4	4	4	4	5
-33.75°	3	3	4	4	4	4	4	4	4	4	4
-35°	3	3	4	4	4	4	4	4	4	4	4
-36.25°	3	3	3	4	4	4	4	4	4	4	4
-37.5°	2	3	3	3	4	4	4	4	4	4	4
-38.75°	2	2	3	3	3	4	4	4	4	4	4
-40°	2	2	3	3	3	3	4	4	4	4	4
-41.25°	2	2	2	3	3	3	3	4	4	4	4
-42.5°	2	2	2	2	3	3	3	3	4	4	4
-43.75°	2	2	2	2	2	3	3	3	3	4	4
-45°	2	2	2	2	2	2	3	3	3	3	4
-46.25°	2	2	2	2	2	2	2	3	3	3	3
-47.5°	1	2	2	2	2	2	2	2	2	3	3
-48.75°	1	1	2	2	2	2	2	2	2	2	3
-50°	1	1	1	2	2	2	2	2	2	2	2
-51.25°	1	1	1	1	2	2	2	2	2	2	2
-52.5°	1	1	1	1	1	2	2	2	2	2	2
-53.75°	1	1	1	1	1	1	1	2	2	2	2
-55°	1	1	1	1	1	1	1	1	1	2	2
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	0	1	1	1	1	1	1	1	1	1	1
-70°	0	0	0	1	1	1	1	1	1	1	1
-71.25°	0	0	0	0	0	0	1	1	1	1	1
-72.5°	0	0	0	0	0	0	0	0	0	0	1
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	2	2	2
58.75°	1	1	1	1	2	2	2	2	2	2	2
57.5°	1	1	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	3
53.75°	2	2	2	2	2	2	2	3	3	3	3
52.5°	2	2	2	2	2	3	3	3	3	3	3
51.25°	2	2	2	3	3	3	3	3	4	4	4
50°	2	3	3	3	3	3	4	4	4	4	4
48.75°	3	3	3	3	4	4	4	4	4	4	4
47.5°	3	3	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	4	4	4	4	4	4
42.5°	4	4	4	4	4	4	4	4	4	5	5
41.25°	4	4	4	4	4	4	4	5	5	5	5
40°	4	4	4	4	4	4	5	5	5	5	5
38.75°	4	4	4	4	5	5	5	5	5	5	5
37.5°	4	4	4	5	5	5	5	5	5	5	5
36.25°	4	4	5	5	5	5	5	5	5	6	6
35°	4	5	5	5	5	5	5	5	6	6	7

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	5	5	5	5	5	5	6	6	7	7	8
32.5°	5	5	5	5	5	6	6	7	7	8	9
31.25°	5	5	5	5	6	6	7	7	8	9	10
30°	5	5	5	6	6	7	8	8	9	10	11
28.75°	5	5	6	6	7	8	8	9	10	11	12
27.5°	5	6	6	7	8	8	9	10	11	13	14
26.25°	5	6	7	7	8	9	10	12	13	14	16
25°	6	7	7	8	9	10	11	13	14	17	19
23.75°	6	7	8	9	10	11	13	14	17	19	22
22.5°	7	8	9	10	11	12	14	16	19	22	27
21.25°	7	8	9	10	12	13	16	19	22	26	31
20°	8	9	10	11	13	15	18	21	26	30	36
18.75°	8	9	11	12	14	17	20	24	29	35	44
17.5°	9	10	12	13	16	19	22	28	33	42	54
16.25°	9	11	12	14	17	20	26	31	39	51	67
15°	10	11	13	16	19	23	28	34	45	60	80
13.75°	10	12	14	17	20	26	31	40	53	71	95
12.5°	11	13	15	18	22	28	34	45	62	84	113
11.25°	11	13	16	19	24	30	38	52	71	96	131
10°	12	14	17	21	26	32	43	58	80	110	147
8.75°	12	14	18	22	28	34	47	65	90	124	162
7.5°	13	15	19	23	30	37	52	72	99	137	176
6.25°	13	16	19	25	31	40	55	77	108	147	188
5°	13	16	20	26	32	42	59	83	117	156	198
3.75°	13	17	20	26	33	44	62	88	123	163	208
2.5°	14	17	21	27	33	46	65	91	128	168	215
1.25°	14	17	21	27	34	47	66	93	131	171	219
0°	14	17	21	27	34	47	67	94	132	172	221
-1.25°	14	17	21	27	34	47	66	93	131	171	219
-2.5°	14	17	21	27	33	46	65	91	128	168	215
-3.75°	13	17	20	26	33	44	62	88	123	163	208
-5°	13	16	20	26	32	42	59	83	117	156	198
-6.25°	13	16	19	25	31	40	55	77	108	147	188
-7.5°	13	15	19	23	30	37	52	72	99	137	176
-8.75°	12	14	18	22	28	34	47	65	90	124	162
-10°	12	14	17	21	26	32	43	58	80	110	147
-11.25°	11	13	16	19	24	30	38	52	71	96	131
-12.5°	11	13	15	18	22	28	34	45	62	84	113
-13.75°	10	12	14	17	20	26	31	40	53	71	95
-15°	10	11	13	16	19	23	28	34	45	60	80
-16.25°	9	11	12	14	17	20	26	31	39	51	67
-17.5°	9	10	12	13	16	19	22	28	33	42	54
-18.75°	8	9	11	12	14	17	20	24	29	35	44
-20°	8	9	10	11	13	15	18	21	26	30	36
-21.25°	7	8	9	10	12	13	16	19	22	26	31

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	7	8	9	10	11	12	14	16	19	22	27
-23.75°	6	7	8	9	10	11	13	14	17	19	22
-25°	6	7	7	8	9	10	11	13	14	17	19
-26.25°	5	6	7	7	8	9	10	12	13	14	16
-27.5°	5	6	6	7	8	8	9	10	11	13	14
-28.75°	5	5	6	6	7	8	8	9	10	11	12
-30°	5	5	5	6	6	7	8	8	9	10	11
-31.25°	5	5	5	5	6	6	7	7	8	9	10
-32.5°	5	5	5	5	5	6	6	7	7	8	9
-33.75°	5	5	5	5	5	5	6	6	7	7	8
-35°	4	5	5	5	5	5	5	5	6	6	7
-36.25°	4	4	5	5	5	5	5	5	5	6	6
-37.5°	4	4	4	5	5	5	5	5	5	5	5
-38.75°	4	4	4	4	5	5	5	5	5	5	5
-40°	4	4	4	4	4	4	5	5	5	5	5
-41.25°	4	4	4	4	4	4	4	5	5	5	5
-42.5°	4	4	4	4	4	4	4	4	4	5	5
-43.75°	4	4	4	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	3	3	4	4	4	4	4	4	4	4	4
-48.75°	3	3	3	3	4	4	4	4	4	4	4
-50°	2	3	3	3	3	3	4	4	4	4	4
-51.25°	2	2	2	3	3	3	3	3	4	4	4
-52.5°	2	2	2	2	2	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	2	3	3	3	3
-55°	2	2	2	2	2	2	2	2	2	2	3
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	1	1	2	2	2	2	2	2	2	2	2
-58.75°	1	1	1	1	2	2	2	2	2	2	2
-60°	1	1	1	1	1	1	1	1	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	0	1	1	1	1	1	1	1
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	2	2	2	2
61.25°	1	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	3	3
56.25°	2	2	2	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	4
53.75°	3	3	3	3	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	5	5	5	5
45°	4	4	4	5	5	5	5	5	5	5	5
43.75°	5	5	5	5	5	5	5	5	5	5	5
42.5°	5	5	5	5	5	5	5	5	5	5	5
41.25°	5	5	5	5	5	5	5	5	6	6	6
40°	5	5	5	5	5	6	6	6	6	7	7
38.75°	5	5	6	6	6	6	7	7	7	7	8
37.5°	6	6	6	7	7	7	8	8	8	9	9
36.25°	6	7	7	8	8	9	9	9	10	10	11
35°	7	8	8	9	9	10	10	11	11	12	12

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	8	9	9	10	11	11	12	13	13	14	14
32.5°	9	10	11	12	12	13	14	15	16	17	18
31.25°	10	11	12	13	14	16	17	18	19	21	22
30°	12	13	14	16	17	19	20	22	24	26	28
28.75°	13	15	17	19	20	23	26	28	30	32	34
27.5°	16	18	20	22	26	28	31	34	38	43	47
26.25°	19	21	24	28	31	34	40	45	52	58	65
25°	22	26	29	33	39	45	53	62	71	80	90
23.75°	26	30	35	42	51	60	71	84	96	110	124
22.5°	31	36	44	54	67	80	95	113	131	147	162
21.25°	37	46	57	71	87	106	127	147	166	185	203
20°	46	58	73	92	114	137	160	183	206	231	255
18.75°	57	73	93	118	144	169	195	225	255	284	313
17.5°	71	92	118	146	174	204	237	273	308	343	377
16.25°	87	114	144	174	207	244	284	326	367	406	442
15°	106	137	169	204	244	288	334	381	426	469	508
13.75°	127	160	195	237	284	334	386	436	485	530	568
12.5°	147	183	225	273	326	381	436	490	540	585	622
11.25°	166	206	255	308	367	426	485	540	590	632	668
10°	185	231	284	343	406	469	530	585	632	673	711
8.75°	203	255	313	377	442	508	568	622	668	711	751
7.5°	222	277	340	407	475	542	601	653	701	745	785
6.25°	238	297	364	433	504	570	629	680	729	775	815
5°	252	315	384	456	528	593	650	703	753	799	841
3.75°	264	329	400	473	545	610	667	721	772	818	861
2.5°	273	339	412	486	558	622	680	734	785	832	876
1.25°	278	346	419	494	566	630	687	742	793	841	884
0°	280	348	421	497	568	633	689	744	795	844	887
-1.25°	278	346	419	494	566	630	687	742	793	841	884
-2.5°	273	339	412	486	558	622	680	734	785	832	876
-3.75°	264	329	400	473	545	610	667	721	772	818	861
-5°	252	315	384	456	528	593	650	703	753	799	841
-6.25°	238	297	364	433	504	570	629	680	729	775	815
-7.5°	222	277	340	407	475	542	601	653	701	745	785
-8.75°	203	255	313	377	442	508	568	622	668	711	751
-10°	185	231	284	343	406	469	530	585	632	673	711
-11.25°	166	206	255	308	367	426	485	540	590	632	668
-12.5°	147	183	225	273	326	381	436	490	540	585	622
-13.75°	127	160	195	237	284	334	386	436	485	530	568
-15°	106	137	169	204	244	288	334	381	426	469	508
-16.25°	87	114	144	174	207	244	284	326	367	406	442
-17.5°	71	92	118	146	174	204	237	273	308	343	377
-18.75°	57	73	93	118	144	169	195	225	255	284	313
-20°	46	58	73	92	114	137	160	183	206	231	255
-21.25°	37	46	57	71	87	106	127	147	166	185	203

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	31	36	44	54	67	80	95	113	131	147	162
-23.75°	26	30	35	42	51	60	71	84	96	110	124
-25°	22	26	29	33	39	45	53	62	71	80	90
-26.25°	19	21	24	28	31	34	40	45	52	58	65
-27.5°	16	18	20	22	26	28	31	34	38	43	47
-28.75°	13	15	17	19	20	23	26	28	30	32	34
-30°	12	13	14	16	17	19	20	22	24	26	28
-31.25°	10	11	12	13	14	16	17	18	19	21	22
-32.5°	9	10	11	12	12	13	14	15	16	17	18
-33.75°	8	9	9	10	11	11	12	13	13	14	14
-35°	7	8	8	9	9	10	10	11	11	12	12
-36.25°	6	7	7	8	8	9	9	9	10	10	11
-37.5°	6	6	6	7	7	7	8	8	8	9	9
-38.75°	5	5	6	6	6	6	7	7	7	7	8
-40°	5	5	5	5	5	6	6	6	6	7	7
-41.25°	5	5	5	5	5	5	5	5	6	6	6
-42.5°	5	5	5	5	5	5	5	5	5	5	5
-43.75°	5	5	5	5	5	5	5	5	5	5	5
-45°	4	4	4	5	5	5	5	5	5	5	5
-46.25°	4	4	4	4	4	4	4	5	5	5	5
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	3	3	3	3	4	4	4	4	4	4	4
-55°	3	3	3	3	3	3	3	3	3	3	4
-56.25°	2	2	2	3	3	3	3	3	3	3	3
-57.5°	2	2	2	2	2	2	2	2	2	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	2	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	1	1	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	4	4	4	4	4	4	4	4	4	4	4
53.75°	4	4	4	4	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	5	5	5	5	5	5	5	5	5
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	5	5	5	5	5	5	5	5	5	5	5
43.75°	5	5	5	5	5	5	5	5	5	5	5
42.5°	5	5	5	5	5	5	6	5	5	5	5
41.25°	6	6	6	6	6	6	6	6	6	6	6
40°	7	7	7	7	7	7	7	7	7	7	7
38.75°	8	8	8	8	9	9	9	9	9	8	8
37.5°	9	10	10	10	10	10	10	10	10	10	10
36.25°	11	11	11	12	12	12	12	12	12	12	11
35°	13	13	13	13	14	14	14	14	14	13	13

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	15	16	16	17	17	17	17	17	17	17	16
32.5°	19	19	20	20	21	21	21	21	21	20	20
31.25°	23	25	26	26	27	27	27	27	27	26	26
30°	30	31	32	33	33	34	34	34	33	33	32
28.75°	37	40	42	44	46	47	47	47	46	44	42
27.5°	52	55	59	62	65	66	67	66	65	62	59
26.25°	72	77	83	88	91	93	94	93	91	88	83
25°	99	108	117	123	128	131	132	131	128	123	117
23.75°	137	147	156	163	168	171	172	171	168	163	156
22.5°	176	188	198	208	215	219	221	219	215	208	198
21.25°	222	238	252	264	273	278	280	278	273	264	252
20°	277	297	315	329	339	346	348	346	339	329	315
18.75°	340	364	384	400	412	419	421	419	412	400	384
17.5°	407	433	456	473	486	494	497	494	486	473	456
16.25°	475	504	528	545	558	566	568	566	558	545	528
15°	542	570	593	610	622	630	633	630	622	610	593
13.75°	601	629	650	667	680	687	689	687	680	667	650
12.5°	653	680	703	721	734	742	744	742	734	721	703
11.25°	701	729	753	772	785	793	795	793	785	772	753
10°	745	775	799	818	832	841	844	841	832	818	799
8.75°	785	815	841	861	876	884	887	884	876	861	841
7.5°	821	852	879	898	912	919	922	919	912	898	879
6.25°	852	884	909	928	939	946	948	946	939	928	909
5°	879	909	933	948	957	961	963	961	957	948	933
3.75°	898	928	948	960	967	971	971	971	967	960	948
2.5°	912	939	957	967	972	975	975	975	972	967	957
1.25°	919	946	961	971	975	978	981	978	975	971	961
0°	922	948	963	971	975	981	986	981	975	971	963
-1.25°	919	946	961	971	975	978	981	978	975	971	961
-2.5°	912	939	957	967	972	975	975	975	972	967	957
-3.75°	898	928	948	960	967	971	971	971	967	960	948
-5°	879	909	933	948	957	961	963	961	957	948	933
-6.25°	852	884	909	928	939	946	948	946	939	928	909
-7.5°	821	852	879	898	912	919	922	919	912	898	879
-8.75°	785	815	841	861	876	884	887	884	876	861	841
-10°	745	775	799	818	832	841	844	841	832	818	799
-11.25°	701	729	753	772	785	793	795	793	785	772	753
-12.5°	653	680	703	721	734	742	744	742	734	721	703
-13.75°	601	629	650	667	680	687	689	687	680	667	650
-15°	542	570	593	610	622	630	633	630	622	610	593
-16.25°	475	504	528	545	558	566	568	566	558	545	528
-17.5°	407	433	456	473	486	494	497	494	486	473	456
-18.75°	340	364	384	400	412	419	421	419	412	400	384
-20°	277	297	315	329	339	346	348	346	339	329	315
-21.25°	222	238	252	264	273	278	280	278	273	264	252

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	176	188	198	208	215	219	221	219	215	208	198
-23.75°	137	147	156	163	168	171	172	171	168	163	156
-25°	99	108	117	123	128	131	132	131	128	123	117
-26.25°	72	77	83	88	91	93	94	93	91	88	83
-27.5°	52	55	59	62	65	66	67	66	65	62	59
-28.75°	37	40	42	44	46	47	47	47	46	44	42
-30°	30	31	32	33	33	34	34	34	33	33	32
-31.25°	23	25	26	26	27	27	27	27	27	26	26
-32.5°	19	19	20	20	21	21	21	21	21	20	20
-33.75°	15	16	16	17	17	17	17	17	17	17	16
-35°	13	13	13	13	14	14	14	14	14	13	13
-36.25°	11	11	11	12	12	12	12	12	12	12	11
-37.5°	9	10	10	10	10	10	10	10	10	10	10
-38.75°	8	8	8	8	9	9	9	9	9	8	8
-40°	7	7	7	7	7	7	7	7	7	7	7
-41.25°	6	6	6	6	6	6	6	6	6	6	6
-42.5°	5	5	5	5	5	5	6	5	5	5	5
-43.75°	5	5	5	5	5	5	5	5	5	5	5
-45°	5	5	5	5	5	5	5	5	5	5	5
-46.25°	5	5	5	5	5	5	5	5	5	5	5
-47.5°	4	4	5	5	5	5	5	5	5	5	5
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	4	4	4	4
-55°	4	4	4	4	4	4	4	4	4	4	4
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	1	1	1	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	2	2	2	2	2	2	2
56.25°	3	3	3	3	3	3	3	3	3	3	2
55°	4	4	4	3	3	3	3	3	3	3	3
53.75°	4	4	4	4	4	4	4	4	4	3	3
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	5	5	5	5	5	5	4	4	4	4	4
45°	5	5	5	5	5	5	5	5	5	5	4
43.75°	5	5	5	5	5	5	5	5	5	5	5
42.5°	5	5	5	5	5	5	5	5	5	5	5
41.25°	6	6	6	6	6	5	5	5	5	5	5
40°	7	7	7	7	6	6	6	6	5	5	5
38.75°	8	8	8	7	7	7	7	6	6	6	6
37.5°	10	9	9	9	8	8	8	7	7	7	6
36.25°	11	11	11	10	10	9	9	9	8	8	7
35°	13	13	12	12	11	11	10	10	9	9	8

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	16	15	14	14	13	13	12	11	11	10	9
32.5°	19	19	18	17	16	15	14	13	12	12	11
31.25°	25	23	22	21	19	18	17	16	14	13	12
30°	31	30	28	26	24	22	20	19	17	16	14
28.75°	40	37	34	32	30	28	26	23	20	19	17
27.5°	55	52	47	43	38	34	31	28	26	22	20
26.25°	77	72	65	58	52	45	40	34	31	28	24
25°	108	99	90	80	71	62	53	45	39	33	29
23.75°	147	137	124	110	96	84	71	60	51	42	35
22.5°	188	176	162	147	131	113	95	80	67	54	44
21.25°	238	222	203	185	166	147	127	106	87	71	57
20°	297	277	255	231	206	183	160	137	114	92	73
18.75°	364	340	313	284	255	225	195	169	144	118	93
17.5°	433	407	377	343	308	273	237	204	174	146	118
16.25°	504	475	442	406	367	326	284	244	207	174	144
15°	570	542	508	469	426	381	334	288	244	204	169
13.75°	629	601	568	530	485	436	386	334	284	237	195
12.5°	680	653	622	585	540	490	436	381	326	273	225
11.25°	729	701	668	632	590	540	485	426	367	308	255
10°	775	745	711	673	632	585	530	469	406	343	284
8.75°	815	785	751	711	668	622	568	508	442	377	313
7.5°	852	821	785	745	701	653	601	542	475	407	340
6.25°	884	852	815	775	729	680	629	570	504	433	364
5°	909	879	841	799	753	703	650	593	528	456	384
3.75°	928	898	861	818	772	721	667	610	545	473	400
2.5°	939	912	876	832	785	734	680	622	558	486	412
1.25°	946	919	884	841	793	742	687	630	566	494	419
0°	948	922	887	844	795	744	689	633	568	497	421
-1.25°	946	919	884	841	793	742	687	630	566	494	419
-2.5°	939	912	876	832	785	734	680	622	558	486	412
-3.75°	928	898	861	818	772	721	667	610	545	473	400
-5°	909	879	841	799	753	703	650	593	528	456	384
-6.25°	884	852	815	775	729	680	629	570	504	433	364
-7.5°	852	821	785	745	701	653	601	542	475	407	340
-8.75°	815	785	751	711	668	622	568	508	442	377	313
-10°	775	745	711	673	632	585	530	469	406	343	284
-11.25°	729	701	668	632	590	540	485	426	367	308	255
-12.5°	680	653	622	585	540	490	436	381	326	273	225
-13.75°	629	601	568	530	485	436	386	334	284	237	195
-15°	570	542	508	469	426	381	334	288	244	204	169
-16.25°	504	475	442	406	367	326	284	244	207	174	144
-17.5°	433	407	377	343	308	273	237	204	174	146	118
-18.75°	364	340	313	284	255	225	195	169	144	118	93
-20°	297	277	255	231	206	183	160	137	114	92	73
-21.25°	238	222	203	185	166	147	127	106	87	71	57

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	188	176	162	147	131	113	95	80	67	54	44
-23.75°	147	137	124	110	96	84	71	60	51	42	35
-25°	108	99	90	80	71	62	53	45	39	33	29
-26.25°	77	72	65	58	52	45	40	34	31	28	24
-27.5°	55	52	47	43	38	34	31	28	26	22	20
-28.75°	40	37	34	32	30	28	26	23	20	19	17
-30°	31	30	28	26	24	22	20	19	17	16	14
-31.25°	25	23	22	21	19	18	17	16	14	13	12
-32.5°	19	19	18	17	16	15	14	13	12	12	11
-33.75°	16	15	14	14	13	13	12	11	11	10	9
-35°	13	13	12	12	11	11	10	10	9	9	8
-36.25°	11	11	11	10	10	9	9	9	8	8	7
-37.5°	10	9	9	9	8	8	8	7	7	7	6
-38.75°	8	8	8	7	7	7	7	6	6	6	6
-40°	7	7	7	7	6	6	6	6	5	5	5
-41.25°	6	6	6	6	6	5	5	5	5	5	5
-42.5°	5	5	5	5	5	5	5	5	5	5	5
-43.75°	5	5	5	5	5	5	5	5	5	5	5
-45°	5	5	5	5	5	5	5	5	5	5	4
-46.25°	5	5	5	5	5	5	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	4	4	3	3
-55°	4	4	4	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	2
-57.5°	3	3	3	3	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	1	1	0	0	0	0	0	0	0	0	0
73.75°	1	1	1	1	1	1	1	1	1	0	0
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	1	1	1	1	1	1	1	1	1	1
60°	2	2	2	2	2	1	1	1	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	1	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	2	2	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	2	2	2	2	2
52.5°	4	4	3	3	3	3	3	3	2	2	2
51.25°	4	4	4	4	4	3	3	3	3	3	2
50°	4	4	4	4	4	4	4	3	3	3	3
48.75°	4	4	4	4	4	4	4	4	4	3	3
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	5	5	4	4	4	4	4	4	4	4	4
42.5°	5	5	5	5	4	4	4	4	4	4	4
41.25°	5	5	5	5	5	5	4	4	4	4	4
40°	5	5	5	5	5	5	5	4	4	4	4
38.75°	5	5	5	5	5	5	5	5	5	4	4
37.5°	6	6	5	5	5	5	5	5	5	5	4
36.25°	7	6	6	6	5	5	5	5	5	5	5
35°	8	7	7	6	6	5	5	5	5	5	5

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	9	8	8	7	7	6	6	5	5	5	5
32.5°	10	9	9	8	7	7	6	6	5	5	5
31.25°	11	10	10	9	8	7	7	6	6	5	5
30°	13	12	11	10	9	8	8	7	6	6	5
28.75°	15	13	12	11	10	9	8	8	7	6	6
27.5°	18	16	14	13	11	10	9	8	8	7	6
26.25°	21	19	16	14	13	12	10	9	8	7	7
25°	26	22	19	17	14	13	11	10	9	8	7
23.75°	30	26	22	19	17	14	13	11	10	9	8
22.5°	36	31	27	22	19	16	14	12	11	10	9
21.25°	46	37	31	26	22	19	16	13	12	10	9
20°	58	46	36	30	26	21	18	15	13	11	10
18.75°	73	57	44	35	29	24	20	17	14	12	11
17.5°	92	71	54	42	33	28	22	19	16	13	12
16.25°	114	87	67	51	39	31	26	20	17	14	12
15°	137	106	80	60	45	34	28	23	19	16	13
13.75°	160	127	95	71	53	40	31	26	20	17	14
12.5°	183	147	113	84	62	45	34	28	22	18	15
11.25°	206	166	131	96	71	52	38	30	24	19	16
10°	231	185	147	110	80	58	43	32	26	21	17
8.75°	255	203	162	124	90	65	47	34	28	22	18
7.5°	277	222	176	137	99	72	52	37	30	23	19
6.25°	297	238	188	147	108	77	55	40	31	25	19
5°	315	252	198	156	117	83	59	42	32	26	20
3.75°	329	264	208	163	123	88	62	44	33	26	20
2.5°	339	273	215	168	128	91	65	46	33	27	21
1.25°	346	278	219	171	131	93	66	47	34	27	21
0°	348	280	221	172	132	94	67	47	34	27	21
-1.25°	346	278	219	171	131	93	66	47	34	27	21
-2.5°	339	273	215	168	128	91	65	46	33	27	21
-3.75°	329	264	208	163	123	88	62	44	33	26	20
-5°	315	252	198	156	117	83	59	42	32	26	20
-6.25°	297	238	188	147	108	77	55	40	31	25	19
-7.5°	277	222	176	137	99	72	52	37	30	23	19
-8.75°	255	203	162	124	90	65	47	34	28	22	18
-10°	231	185	147	110	80	58	43	32	26	21	17
-11.25°	206	166	131	96	71	52	38	30	24	19	16
-12.5°	183	147	113	84	62	45	34	28	22	18	15
-13.75°	160	127	95	71	53	40	31	26	20	17	14
-15°	137	106	80	60	45	34	28	23	19	16	13
-16.25°	114	87	67	51	39	31	26	20	17	14	12
-17.5°	92	71	54	42	33	28	22	19	16	13	12
-18.75°	73	57	44	35	29	24	20	17	14	12	11
-20°	58	46	36	30	26	21	18	15	13	11	10
-21.25°	46	37	31	26	22	19	16	13	12	10	9

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	36	31	27	22	19	16	14	12	11	10	9
-23.75°	30	26	22	19	17	14	13	11	10	9	8
-25°	26	22	19	17	14	13	11	10	9	8	7
-26.25°	21	19	16	14	13	12	10	9	8	7	7
-27.5°	18	16	14	13	11	10	9	8	8	7	6
-28.75°	15	13	12	11	10	9	8	8	7	6	6
-30°	13	12	11	10	9	8	8	7	6	6	5
-31.25°	11	10	10	9	8	7	7	6	6	5	5
-32.5°	10	9	9	8	7	7	6	6	5	5	5
-33.75°	9	8	8	7	7	6	6	5	5	5	5
-35°	8	7	7	6	6	5	5	5	5	5	5
-36.25°	7	6	6	6	5	5	5	5	5	5	5
-37.5°	6	6	5	5	5	5	5	5	5	5	4
-38.75°	5	5	5	5	5	5	5	5	5	4	4
-40°	5	5	5	5	5	5	5	4	4	4	4
-41.25°	5	5	5	5	5	5	4	4	4	4	4
-42.5°	5	5	5	5	4	4	4	4	4	4	4
-43.75°	5	5	4	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	3	3
-50°	4	4	4	4	4	4	4	3	3	3	3
-51.25°	4	4	4	4	4	3	3	3	3	3	2
-52.5°	4	4	3	3	3	3	3	3	2	2	2
-53.75°	3	3	3	3	3	3	2	2	2	2	2
-55°	3	3	3	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	1	1
-60°	2	2	2	2	2	1	1	1	1	1	1
-61.25°	2	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	0	0
-75°	1	1	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	1	0	0	0	0	0	0	0	0
71.25°	1	1	1	1	1	1	1	0	0	0	0
70°	1	1	1	1	1	1	1	1	1	1	0
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	1	1	1	1	1	1	1	1	1
55°	2	2	2	2	1	1	1	1	1	1	1
53.75°	2	2	2	2	2	2	1	1	1	1	1
52.5°	2	2	2	2	2	2	2	2	1	1	1
51.25°	2	2	2	2	2	2	2	2	2	1	1
50°	3	2	2	2	2	2	2	2	2	2	1
48.75°	3	3	3	2	2	2	2	2	2	2	2
47.5°	3	3	3	3	2	2	2	2	2	2	2
46.25°	4	4	3	3	3	3	2	2	2	2	2
45°	4	4	4	3	3	3	3	2	2	2	2
43.75°	4	4	4	4	3	3	3	3	2	2	2
42.5°	4	4	4	4	4	3	3	3	3	2	2
41.25°	4	4	4	4	4	4	3	3	3	3	2
40°	4	4	4	4	4	4	4	3	3	3	3
38.75°	4	4	4	4	4	4	4	4	3	3	3
37.5°	4	4	4	4	4	4	4	4	4	3	3
36.25°	4	4	4	4	4	4	4	4	4	4	3
35°	5	4	4	4	4	4	4	4	4	4	4

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	5	5	4	4	4	4	4	4	4	4	4
32.5°	5	5	5	4	4	4	4	4	4	4	4
31.25°	5	5	5	5	4	4	4	4	4	4	4
30°	5	5	5	5	5	4	4	4	4	4	4
28.75°	5	5	5	5	5	4	4	4	4	4	4
27.5°	6	5	5	5	5	5	4	4	4	4	4
26.25°	6	5	5	5	5	5	5	4	4	4	4
25°	7	6	5	5	5	5	5	4	4	4	4
23.75°	7	6	6	5	5	5	5	5	4	4	4
22.5°	8	7	6	5	5	5	5	5	4	4	4
21.25°	8	7	6	6	5	5	5	5	5	4	4
20°	9	8	7	6	5	5	5	5	5	4	4
18.75°	9	8	7	6	6	5	5	5	5	4	4
17.5°	10	9	8	7	6	5	5	5	5	5	4
16.25°	11	9	8	7	6	5	5	5	5	5	4
15°	11	10	9	7	6	6	5	5	5	5	4
13.75°	12	10	9	8	7	6	5	5	5	5	4
12.5°	13	11	9	8	7	6	5	5	5	5	5
11.25°	13	11	10	8	7	6	6	5	5	5	5
10°	14	12	10	9	7	7	6	5	5	5	5
8.75°	14	12	11	9	8	7	6	5	5	5	5
7.5°	15	13	11	9	8	7	6	5	5	5	5
6.25°	16	13	11	10	8	7	6	5	5	5	5
5°	16	13	11	10	8	7	6	5	5	5	5
3.75°	17	13	12	10	8	7	6	5	5	5	5
2.5°	17	14	12	10	9	7	6	5	5	5	5
1.25°	17	14	12	10	9	7	6	5	5	5	5
0°	17	14	12	10	9	7	6	6	5	5	5
-1.25°	17	14	12	10	9	7	6	5	5	5	5
-2.5°	17	14	12	10	9	7	6	5	5	5	5
-3.75°	17	13	12	10	8	7	6	5	5	5	5
-5°	16	13	11	10	8	7	6	5	5	5	5
-6.25°	16	13	11	10	8	7	6	5	5	5	5
-7.5°	15	13	11	9	8	7	6	5	5	5	5
-8.75°	14	12	11	9	8	7	6	5	5	5	5
-10°	14	12	10	9	7	7	6	5	5	5	5
-11.25°	13	11	10	8	7	6	6	5	5	5	5
-12.5°	13	11	9	8	7	6	5	5	5	5	5
-13.75°	12	10	9	8	7	6	5	5	5	5	4
-15°	11	10	9	7	6	6	5	5	5	5	4
-16.25°	11	9	8	7	6	5	5	5	5	5	4
-17.5°	10	9	8	7	6	5	5	5	5	5	4
-18.75°	9	8	7	6	6	5	5	5	5	4	4
-20°	9	8	7	6	5	5	5	5	5	4	4
-21.25°	8	7	6	6	5	5	5	5	5	4	4

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	8	7	6	5	5	5	5	5	4	4	4
-23.75°	7	6	6	5	5	5	5	5	4	4	4
-25°	7	6	5	5	5	5	5	4	4	4	4
-26.25°	6	5	5	5	5	5	5	4	4	4	4
-27.5°	6	5	5	5	5	5	4	4	4	4	4
-28.75°	5	5	5	5	5	4	4	4	4	4	4
-30°	5	5	5	5	5	4	4	4	4	4	4
-31.25°	5	5	5	5	4	4	4	4	4	4	4
-32.5°	5	5	5	4	4	4	4	4	4	4	4
-33.75°	5	5	4	4	4	4	4	4	4	4	4
-35°	5	4	4	4	4	4	4	4	4	4	4
-36.25°	4	4	4	4	4	4	4	4	4	4	3
-37.5°	4	4	4	4	4	4	4	4	4	3	3
-38.75°	4	4	4	4	4	4	4	4	3	3	3
-40°	4	4	4	4	4	4	4	3	3	3	3
-41.25°	4	4	4	4	4	4	3	3	3	3	2
-42.5°	4	4	4	4	4	3	3	3	3	2	2
-43.75°	4	4	4	4	3	3	3	3	2	2	2
-45°	4	4	4	3	3	3	3	2	2	2	2
-46.25°	4	4	3	3	3	3	2	2	2	2	2
-47.5°	3	3	3	3	2	2	2	2	2	2	2
-48.75°	3	3	3	2	2	2	2	2	2	2	2
-50°	3	2	2	2	2	2	2	2	2	2	1
-51.25°	2	2	2	2	2	2	2	2	2	1	1
-52.5°	2	2	2	2	2	2	2	2	1	1	1
-53.75°	2	2	2	2	2	2	1	1	1	1	1
-55°	2	2	2	2	1	1	1	1	1	1	1
-56.25°	2	2	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	0
-71.25°	1	1	1	1	1	1	1	0	0	0	0
-72.5°	1	1	1	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	1	0	0	0	0	0	0	0	0	0	0
67.5°	1	1	1	0	0	0	0	0	0	0	0
66.25°	1	1	1	1	1	0	0	0	0	0	0
65°	1	1	1	1	1	1	1	0	0	0	0
63.75°	1	1	1	1	1	1	1	1	0	0	0
62.5°	1	1	1	1	1	1	1	1	1	0	0
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	2	1	1	1	1	1	1	1	1	1	1
46.25°	2	2	1	1	1	1	1	1	1	1	1
45°	2	2	2	1	1	1	1	1	1	1	1
43.75°	2	2	2	2	1	1	1	1	1	1	1
42.5°	2	2	2	2	2	1	1	1	1	1	1
41.25°	2	2	2	2	2	1	1	1	1	1	1
40°	2	2	2	2	2	2	1	1	1	1	1
38.75°	2	2	2	2	2	2	1	1	1	1	1
37.5°	3	2	2	2	2	2	2	1	1	1	1
36.25°	3	3	2	2	2	2	2	1	1	1	1
35°	3	3	2	2	2	2	2	2	1	1	1

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	3	3	3	2	2	2	2	2	1	1	1
32.5°	4	3	3	2	2	2	2	2	2	1	1
31.25°	4	3	3	3	2	2	2	2	2	1	1
30°	4	4	3	3	2	2	2	2	2	2	1
28.75°	4	4	3	3	3	2	2	2	2	2	1
27.5°	4	4	4	3	3	2	2	2	2	2	1
26.25°	4	4	4	3	3	3	2	2	2	2	1
25°	4	4	4	4	3	3	2	2	2	2	2
23.75°	4	4	4	4	3	3	2	2	2	2	2
22.5°	4	4	4	4	3	3	3	2	2	2	2
21.25°	4	4	4	4	4	3	3	2	2	2	2
20°	4	4	4	4	4	3	3	2	2	2	2
18.75°	4	4	4	4	4	3	3	2	2	2	2
17.5°	4	4	4	4	4	3	3	3	2	2	2
16.25°	4	4	4	4	4	4	3	3	2	2	2
15°	4	4	4	4	4	4	3	3	2	2	2
13.75°	4	4	4	4	4	4	3	3	2	2	2
12.5°	4	4	4	4	4	4	3	3	2	2	2
11.25°	4	4	4	4	4	4	3	3	2	2	2
10°	4	4	4	4	4	4	3	3	3	2	2
8.75°	4	4	4	4	4	4	4	3	3	2	2
7.5°	4	4	4	4	4	4	4	3	3	2	2
6.25°	4	4	4	4	4	4	4	3	3	2	2
5°	5	4	4	4	4	4	4	3	3	2	2
3.75°	5	4	4	4	4	4	4	3	3	2	2
2.5°	5	4	4	4	4	4	4	3	3	2	2
1.25°	5	4	4	4	4	4	4	3	3	2	2
0°	5	4	4	4	4	4	4	3	3	2	2
-1.25°	5	4	4	4	4	4	4	3	3	2	2
-2.5°	5	4	4	4	4	4	4	3	3	2	2
-3.75°	5	4	4	4	4	4	4	3	3	2	2
-5°	5	4	4	4	4	4	4	3	3	2	2
-6.25°	4	4	4	4	4	4	4	3	3	2	2
-7.5°	4	4	4	4	4	4	4	3	3	2	2
-8.75°	4	4	4	4	4	4	4	3	3	2	2
-10°	4	4	4	4	4	4	3	3	3	2	2
-11.25°	4	4	4	4	4	4	3	3	2	2	2
-12.5°	4	4	4	4	4	4	3	3	2	2	2
-13.75°	4	4	4	4	4	4	3	3	2	2	2
-15°	4	4	4	4	4	4	3	3	2	2	2
-16.25°	4	4	4	4	4	4	3	3	2	2	2
-17.5°	4	4	4	4	4	3	3	3	2	2	2
-18.75°	4	4	4	4	4	3	3	2	2	2	2
-20°	4	4	4	4	4	3	3	2	2	2	2
-21.25°	4	4	4	4	4	3	3	2	2	2	2

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	4	4	4	4	3	3	3	2	2	2	2
-23.75°	4	4	4	4	3	3	2	2	2	2	2
-25°	4	4	4	4	3	3	2	2	2	2	2
-26.25°	4	4	4	3	3	3	2	2	2	2	1
-27.5°	4	4	4	3	3	2	2	2	2	2	1
-28.75°	4	4	3	3	3	2	2	2	2	2	1
-30°	4	4	3	3	2	2	2	2	2	2	1
-31.25°	4	3	3	3	2	2	2	2	2	1	1
-32.5°	4	3	3	2	2	2	2	2	2	1	1
-33.75°	3	3	3	2	2	2	2	2	1	1	1
-35°	3	3	2	2	2	2	2	2	1	1	1
-36.25°	3	3	2	2	2	2	2	1	1	1	1
-37.5°	3	2	2	2	2	2	2	1	1	1	1
-38.75°	2	2	2	2	2	2	1	1	1	1	1
-40°	2	2	2	2	2	2	1	1	1	1	1
-41.25°	2	2	2	2	2	1	1	1	1	1	1
-42.5°	2	2	2	2	2	1	1	1	1	1	1
-43.75°	2	2	2	2	1	1	1	1	1	1	1
-45°	2	2	2	1	1	1	1	1	1	1	1
-46.25°	2	2	1	1	1	1	1	1	1	1	1
-47.5°	2	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	0	0
-63.75°	1	1	1	1	1	1	1	1	0	0	0
-65°	1	1	1	1	1	1	1	0	0	0	0
-66.25°	1	1	1	1	1	0	0	0	0	0	0
-67.5°	1	1	1	0	0	0	0	0	0	0	0
-68.75°	1	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	1	0	0	0	0	0	0	0	0	0	0
58.75°	1	0	0	0	0	0	0	0	0	0	0
57.5°	1	1	0	0	0	0	0	0	0	0	0
56.25°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	1	0	0	0	0	0	0	0
53.75°	1	1	1	1	0	0	0	0	0	0	0
52.5°	1	1	1	1	1	0	0	0	0	0	0
51.25°	1	1	1	1	1	0	0	0	0	0	0
50°	1	1	1	1	1	1	0	0	0	0	0
48.75°	1	1	1	1	1	1	0	0	0	0	0
47.5°	1	1	1	1	1	1	1	0	0	0	0
46.25°	1	1	1	1	1	1	1	0	0	0	0
45°	1	1	1	1	1	1	1	1	0	0	0
43.75°	1	1	1	1	1	1	1	1	0	0	0
42.5°	1	1	1	1	1	1	1	1	0	0	0
41.25°	1	1	1	1	1	1	1	1	1	0	0
40°	1	1	1	1	1	1	1	1	1	0	0
38.75°	1	1	1	1	1	1	1	1	1	0	0
37.5°	1	1	1	1	1	1	1	1	1	0	0
36.25°	1	1	1	1	1	1	1	1	1	1	0
35°	1	1	1	1	1	1	1	1	1	1	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	1	1	1	1	1	1	1	0
32.5°	1	1	1	1	1	1	1	1	1	1	0
31.25°	1	1	1	1	1	1	1	1	1	1	0
30°	1	1	1	1	1	1	1	1	1	1	1
28.75°	1	1	1	1	1	1	1	1	1	1	1
27.5°	1	1	1	1	1	1	1	1	1	1	1
26.25°	1	1	1	1	1	1	1	1	1	1	1
25°	1	1	1	1	1	1	1	1	1	1	1
23.75°	1	1	1	1	1	1	1	1	1	1	1
22.5°	1	1	1	1	1	1	1	1	1	1	1
21.25°	1	1	1	1	1	1	1	1	1	1	1
20°	2	1	1	1	1	1	1	1	1	1	1
18.75°	2	1	1	1	1	1	1	1	1	1	1
17.5°	2	1	1	1	1	1	1	1	1	1	1
16.25°	2	1	1	1	1	1	1	1	1	1	1
15°	2	1	1	1	1	1	1	1	1	1	1
13.75°	2	1	1	1	1	1	1	1	1	1	1
12.5°	2	2	1	1	1	1	1	1	1	1	1
11.25°	2	2	1	1	1	1	1	1	1	1	1
10°	2	2	1	1	1	1	1	1	1	1	1
8.75°	2	2	1	1	1	1	1	1	1	1	1
7.5°	2	2	1	1	1	1	1	1	1	1	1
6.25°	2	2	1	1	1	1	1	1	1	1	1
5°	2	2	1	1	1	1	1	1	1	1	1
3.75°	2	2	1	1	1	1	1	1	1	1	1
2.5°	2	2	1	1	1	1	1	1	1	1	1
1.25°	2	2	1	1	1	1	1	1	1	1	1
0°	2	2	1	1	1	1	1	1	1	1	1
-1.25°	2	2	1	1	1	1	1	1	1	1	1
-2.5°	2	2	1	1	1	1	1	1	1	1	1
-3.75°	2	2	1	1	1	1	1	1	1	1	1
-5°	2	2	1	1	1	1	1	1	1	1	1
-6.25°	2	2	1	1	1	1	1	1	1	1	1
-7.5°	2	2	1	1	1	1	1	1	1	1	1
-8.75°	2	2	1	1	1	1	1	1	1	1	1
-10°	2	2	1	1	1	1	1	1	1	1	1
-11.25°	2	2	1	1	1	1	1	1	1	1	1
-12.5°	2	2	1	1	1	1	1	1	1	1	1
-13.75°	2	1	1	1	1	1	1	1	1	1	1
-15°	2	1	1	1	1	1	1	1	1	1	1
-16.25°	2	1	1	1	1	1	1	1	1	1	1
-17.5°	2	1	1	1	1	1	1	1	1	1	1
-18.75°	2	1	1	1	1	1	1	1	1	1	1
-20°	2	1	1	1	1	1	1	1	1	1	1
-21.25°	1	1	1	1	1	1	1	1	1	1	1

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	1	1	1	1	1	1	1	1	1	1	1
-23.75°	1	1	1	1	1	1	1	1	1	1	1
-25°	1	1	1	1	1	1	1	1	1	1	1
-26.25°	1	1	1	1	1	1	1	1	1	1	1
-27.5°	1	1	1	1	1	1	1	1	1	1	1
-28.75°	1	1	1	1	1	1	1	1	1	1	1
-30°	1	1	1	1	1	1	1	1	1	1	1
-31.25°	1	1	1	1	1	1	1	1	1	1	0
-32.5°	1	1	1	1	1	1	1	1	1	1	0
-33.75°	1	1	1	1	1	1	1	1	1	1	0
-35°	1	1	1	1	1	1	1	1	1	1	0
-36.25°	1	1	1	1	1	1	1	1	1	1	0
-37.5°	1	1	1	1	1	1	1	1	1	0	0
-38.75°	1	1	1	1	1	1	1	1	1	0	0
-40°	1	1	1	1	1	1	1	1	1	0	0
-41.25°	1	1	1	1	1	1	1	1	1	0	0
-42.5°	1	1	1	1	1	1	1	1	0	0	0
-43.75°	1	1	1	1	1	1	1	1	0	0	0
-45°	1	1	1	1	1	1	1	1	0	0	0
-46.25°	1	1	1	1	1	1	1	0	0	0	0
-47.5°	1	1	1	1	1	1	1	0	0	0	0
-48.75°	1	1	1	1	1	1	0	0	0	0	0
-50°	1	1	1	1	1	1	0	0	0	0	0
-51.25°	1	1	1	1	1	0	0	0	0	0	0
-52.5°	1	1	1	1	1	0	0	0	0	0	0
-53.75°	1	1	1	1	0	0	0	0	0	0	0
-55°	1	1	1	1	0	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	1	0	0	0	0	0	0	0	0	0
-58.75°	1	0	0	0	0	0	0	0	0	0	0
-60°	1	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	1	0	0	0	0	0	0	0	0	0	0
20°	1	0	0	0	0	0	0	0	0	0	0
18.75°	1	0	0	0	0	0	0	0	0	0	0
17.5°	1	0	0	0	0	0	0	0	0	0	0
16.25°	1	0	0	0	0	0	0	0	0	0	0
15°	1	0	0	0	0	0	0	0	0	0	0
13.75°	1	0	0	0	0	0	0	0	0	0	0
12.5°	1	0	0	0	0	0	0	0	0	0	0
11.25°	1	0	0	0	0	0	0	0	0	0	0
10°	1	0	0	0	0	0	0	0	0	0	0
8.75°	1	0	0	0	0	0	0	0	0	0	0
7.5°	1	0	0	0	0	0	0	0	0	0	0
6.25°	1	0	0	0	0	0	0	0	0	0	0
5°	1	0	0	0	0	0	0	0	0	0	0
3.75°	1	0	0	0	0	0	0	0	0	0	0
2.5°	1	0	0	0	0	0	0	0	0	0	0
1.25°	1	0	0	0	0	0	0	0	0	0	0
0°	1	0	0	0	0	0	0	0	0	0	0
-1.25°	1	0	0	0	0	0	0	0	0	0	0
-2.5°	1	0	0	0	0	0	0	0	0	0	0
-3.75°	1	0	0	0	0	0	0	0	0	0	0
-5°	1	0	0	0	0	0	0	0	0	0	0
-6.25°	1	0	0	0	0	0	0	0	0	0	0
-7.5°	1	0	0	0	0	0	0	0	0	0	0
-8.75°	1	0	0	0	0	0	0	0	0	0	0
-10°	1	0	0	0	0	0	0	0	0	0	0
-11.25°	1	0	0	0	0	0	0	0	0	0	0
-12.5°	1	0	0	0	0	0	0	0	0	0	0
-13.75°	1	0	0	0	0	0	0	0	0	0	0
-15°	1	0	0	0	0	0	0	0	0	0	0
-16.25°	1	0	0	0	0	0	0	0	0	0	0
-17.5°	1	0	0	0	0	0	0	0	0	0	0
-18.75°	1	0	0	0	0	0	0	0	0	0	0
-20°	1	0	0	0	0	0	0	0	0	0	0
-21.25°	1	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0

REPORT NUMBER: P247031 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2736-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)