

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220557

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED2797-W-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220557
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29475)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-W-BK-L1-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS, WIDE FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 2700K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 518.8 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.67
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220557

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-W-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220557

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-W-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102		102	101	99		98	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	90
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91	88	86	85
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75		81	77	74		80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71		77	73	70		76	73	70	69
8	85	77	71	68	84	76	71	68	75	71	67		74	70	67		73	69	67	66
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70	66	64	63
10	78	70	65	61	78	70	65	61	69	64	61		68	64	61		67	64	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	203054
5°	203896
10°	190733
15°	162952
20°	138472
25°	82287
30°	37449
35°	23744
40°	13454
45°	4931
50°	1569
55°	1147
60°	1009
65°	571
70°	256
75°	339
80°	0
85°	0



TEST NUMBER: P220557

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-W-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.3	16.6
10°-20°	200.6	38.7
20°-30°	155.7	30.0
30°-40°	56.8	10.9
40°-50°	15.0	2.9
50°-60°	2.8	0.5
60°-70°	1.2	0.2
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	442.6	85.3
0°-40°	499.4	96.3
0°-60°	517.2	99.7
0°-90°	518.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	518.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	926	
5°	926	86
15°	718	201
25°	340	156
35°	89	57
45°	16	15
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220557

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-W-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	926.0
1°	923.3
2°	923.3
3°	926.0
4°	927.5
5°	926.3
6°	921.8
7°	912.3
8°	897.5
9°	878.2
10°	856.6
11°	831.6
12°	803.9
13°	774.7
14°	744.7
15°	717.8
16°	693.5
17°	667.7
18°	643.1
19°	618.1
20°	593.4
21°	566.1
22°	522.9
23°	466.0
24°	404.2
25°	340.1
26°	279.8
27°	226.0
28°	185.4
29°	162.3
30°	147.9
32.5°	116.4
35°	88.7
37.5°	66.7
40°	47.0
42.5°	31.1
45°	15.9
47.5°	7.2
50°	4.6
52.5°	3.4
55°	3.0
57.5°	2.7
60°	2.3
62.5°	1.5
65°	1.1



TEST NUMBER: P220557

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-W-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.1
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)