

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED3036-12-CS-LSL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-45)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED3036-12-CS-LSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD SILVER, LINEAR SPREAD LENS
Light Source: (1) SORAA 3000K 90 CRI LED
SM16-07-36D-930-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp:	N/A	NEMA Type:	5H x 4V
Luminaire Lumens:	281.2 lumens	Max Intensity:	495.6 candela
Efficiency:	N/A	Max Intensity Angle:	-11.25°H x 0°V
Efficacy:	37.0 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		

Beam Angle (50%):	59.6°H x 32.6°V	Field Angle (10%):	78.4°H x 52.6°V
Beam Lumens:	184.6 lumens	Field Lumens:	257.3 lumens
Beam Efficiency:	65.7%	Field Efficiency:	91.5%

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT


REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

Iso-Candela Plot




REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

Lumen Table




REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

Luminous Intensity Polar Plot



REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

Luminous Intensity Plot



Beam:
H Angle: 59.6°
V Angle: 32.6°
Lumens: 184.6
Efficiency: 65.7%

Field:
H Angle: 78.4°
V Angle: 52.6°
Lumens: 257.3
Efficiency: 91.5%

Spill:
Lumens: 24
Efficiency: 8.5%

— Vertical Distribution through -11.25-Deg
- - Horizontal Distribution through 0-Deg

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

FIELD
BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	1
57.5°	0	0	0	0	0	0	0	0	0	0	1
56.25°	0	0	0	0	0	0	0	0	0	0	1
55°	0	0	0	0	0	0	0	0	0	1	1
53.75°	0	0	0	0	0	0	0	0	0	1	1
52.5°	0	0	0	0	0	0	0	0	0	1	1
51.25°	0	0	0	0	0	0	0	0	0	1	1
50°	0	0	0	0	0	0	0	0	1	1	1
48.75°	0	0	0	0	0	0	0	0	1	1	1
47.5°	0	0	0	0	0	0	0	0	1	1	1
46.25°	0	0	0	0	0	0	0	0	1	1	1
45°	0	0	0	0	0	0	0	0	1	1	1
43.75°	0	0	0	0	0	0	0	0	1	1	1
42.5°	0	0	0	0	0	0	0	1	1	1	1
41.25°	0	0	0	0	0	0	0	1	1	1	1
40°	0	0	0	0	0	0	0	1	1	1	1
38.75°	0	0	0	0	0	0	0	1	1	1	1
37.5°	0	0	0	0	0	0	0	1	1	1	1
36.25°	0	0	0	0	0	0	0	1	1	1	1
35°	0	0	0	0	0	0	0	1	1	1	1

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	1	1	1	1
32.5°	0	0	0	0	0	0	0	1	1	1	1
31.25°	0	0	0	0	0	0	1	1	1	1	1
30°	0	0	0	0	0	0	1	1	1	1	1
28.75°	0	0	0	0	0	0	1	1	1	1	1
27.5°	0	0	0	0	0	0	1	1	1	1	1
26.25°	0	0	0	0	0	0	1	1	1	1	1
25°	0	0	0	0	0	0	1	1	1	1	1
23.75°	0	0	0	0	0	0	1	1	1	1	1
22.5°	0	0	0	0	0	0	1	1	1	1	1
21.25°	0	0	0	0	0	0	1	1	1	1	1
20°	0	0	0	0	0	0	1	1	1	1	1
18.75°	0	0	0	0	0	0	1	1	1	1	1
17.5°	0	0	0	0	0	0	1	1	1	1	1
16.25°	0	0	0	0	0	0	1	1	1	1	1
15°	0	0	0	0	0	0	1	1	1	1	1
13.75°	0	0	0	0	0	0	1	1	1	1	1
12.5°	0	0	0	0	0	0	1	1	1	1	1
11.25°	0	0	0	0	0	0	1	1	1	1	1
10°	0	0	0	0	0	0	1	1	1	1	1
8.75°	0	0	0	0	0	0	1	1	1	1	1
7.5°	0	0	0	0	0	0	1	1	1	1	1
6.25°	0	0	0	0	0	0	1	1	1	1	1
5°	0	0	0	0	0	0	1	1	1	1	1
3.75°	0	0	0	0	0	0	1	1	1	1	1
2.5°	0	0	0	0	0	0	1	1	1	1	1
1.25°	0	0	0	0	0	0	1	1	1	1	1
0°	0	0	0	0	0	0	1	1	1	1	1
-1.25°	0	0	0	0	0	0	1	1	1	1	1
-2.5°	0	0	0	0	0	0	1	1	1	1	1
-3.75°	0	0	0	0	0	0	1	1	1	1	1
-5°	0	0	0	0	0	0	1	1	1	1	1
-6.25°	0	0	0	0	0	0	1	1	1	1	1
-7.5°	0	0	0	0	0	0	1	1	1	1	1
-8.75°	0	0	0	0	0	0	1	1	1	1	1
-10°	0	0	0	0	0	0	1	1	1	1	1
-11.25°	0	0	0	0	0	0	1	1	1	1	1
-12.5°	0	0	0	0	0	0	1	1	1	1	1
-13.75°	0	0	0	0	0	0	1	1	1	1	1
-15°	0	0	0	0	0	0	1	1	1	1	1
-16.25°	0	0	0	0	0	0	1	1	1	1	1
-17.5°	0	0	0	0	0	0	1	1	1	1	1
-18.75°	0	0	0	0	0	0	1	1	1	1	1
-20°	0	0	0	0	0	0	1	1	1	1	1
-21.25°	0	0	0	0	0	0	1	1	1	1	1

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	1	1	1	1	1
-23.75°	0	0	0	0	0	0	1	1	1	1	1
-25°	0	0	0	0	0	0	1	1	1	1	1
-26.25°	0	0	0	0	0	0	1	1	1	1	1
-27.5°	0	0	0	0	0	0	1	1	1	1	1
-28.75°	0	0	0	0	0	0	1	1	1	1	1
-30°	0	0	0	0	0	0	1	1	1	1	1
-31.25°	0	0	0	0	0	0	1	1	1	1	1
-32.5°	0	0	0	0	0	0	0	1	1	1	1
-33.75°	0	0	0	0	0	0	0	1	1	1	1
-35°	0	0	0	0	0	0	0	1	1	1	1
-36.25°	0	0	0	0	0	0	0	1	1	1	1
-37.5°	0	0	0	0	0	0	0	1	1	1	1
-38.75°	0	0	0	0	0	0	0	1	1	1	1
-40°	0	0	0	0	0	0	0	1	1	1	1
-41.25°	0	0	0	0	0	0	0	1	1	1	1
-42.5°	0	0	0	0	0	0	0	1	1	1	1
-43.75°	0	0	0	0	0	0	0	0	1	1	1
-45°	0	0	0	0	0	0	0	0	1	1	1
-46.25°	0	0	0	0	0	0	0	0	1	1	1
-47.5°	0	0	0	0	0	0	0	0	1	1	1
-48.75°	0	0	0	0	0	0	0	0	1	1	1
-50°	0	0	0	0	0	0	0	0	1	1	1
-51.25°	0	0	0	0	0	0	0	0	0	1	1
-52.5°	0	0	0	0	0	0	0	0	0	1	1
-53.75°	0	0	0	0	0	0	0	0	0	1	1
-55°	0	0	0	0	0	0	0	0	0	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	1
-58.75°	0	0	0	0	0	0	0	0	0	0	1
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	1	1	1
72.5°	0	0	0	0	0	0	0	1	1	1	1
71.25°	0	0	0	0	0	0	1	1	1	1	1
70°	0	0	0	0	0	1	1	1	1	1	1
68.75°	0	0	0	0	1	1	1	1	1	1	1
67.5°	0	0	0	1	1	1	1	1	1	1	1
66.25°	0	0	1	1	1	1	1	1	1	1	1
65°	0	0	1	1	1	1	1	1	1	1	1
63.75°	0	1	1	1	1	1	1	1	1	1	1
62.5°	0	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	2
40°	1	1	1	1	1	1	1	1	1	1	2
38.75°	1	1	1	1	1	1	1	1	1	2	2
37.5°	1	1	1	1	1	1	1	1	1	2	2
36.25°	1	1	1	1	1	1	1	1	1	2	2
35°	1	1	1	1	1	1	1	1	2	2	2

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	1	1	1	1	2	2	2
32.5°	1	1	1	1	1	1	1	1	2	2	2
31.25°	1	1	1	1	1	1	1	1	2	2	2
30°	1	1	1	1	1	1	1	2	2	2	2
28.75°	1	1	1	1	1	1	1	2	2	2	2
27.5°	1	1	1	1	1	1	1	2	2	2	2
26.25°	1	1	1	1	1	1	1	2	2	2	2
25°	1	1	1	1	1	1	2	2	2	2	2
23.75°	1	1	1	1	1	1	2	2	2	2	2
22.5°	1	1	1	1	1	1	2	2	2	2	2
21.25°	1	1	1	1	1	1	2	2	2	2	2
20°	1	1	1	1	1	1	2	2	2	2	2
18.75°	1	1	1	1	1	1	2	2	2	2	2
17.5°	1	1	1	1	1	1	2	2	2	2	2
16.25°	1	1	1	1	1	2	2	2	2	2	2
15°	1	1	1	1	1	2	2	2	2	2	2
13.75°	1	1	1	1	1	2	2	2	2	2	2
12.5°	1	1	1	1	1	2	2	2	2	2	2
11.25°	1	1	1	1	1	2	2	2	2	2	2
10°	1	1	1	1	1	2	2	2	2	2	2
8.75°	1	1	1	1	1	2	2	2	2	2	2
7.5°	1	1	1	1	1	2	2	2	2	2	2
6.25°	1	1	1	1	1	2	2	2	2	2	2
5°	1	1	1	1	1	2	2	2	2	2	2
3.75°	1	1	1	1	1	2	2	2	2	2	2
2.5°	1	1	1	1	1	2	2	2	2	2	2
1.25°	1	1	1	1	1	2	2	2	2	2	2
0°	1	1	1	1	1	2	2	2	2	2	2
-1.25°	1	1	1	1	1	2	2	2	2	2	2
-2.5°	1	1	1	1	1	2	2	2	2	2	2
-3.75°	1	1	1	1	1	2	2	2	2	2	2
-5°	1	1	1	1	1	2	2	2	2	2	2
-6.25°	1	1	1	1	1	2	2	2	2	2	2
-7.5°	1	1	1	1	1	2	2	2	2	2	2
-8.75°	1	1	1	1	1	2	2	2	2	2	2
-10°	1	1	1	1	1	2	2	2	2	2	2
-11.25°	1	1	1	1	1	2	2	2	2	2	2
-12.5°	1	1	1	1	1	2	2	2	2	2	2
-13.75°	1	1	1	1	1	2	2	2	2	2	2
-15°	1	1	1	1	1	2	2	2	2	2	2
-16.25°	1	1	1	1	1	2	2	2	2	2	2
-17.5°	1	1	1	1	1	1	2	2	2	2	2
-18.75°	1	1	1	1	1	1	2	2	2	2	2
-20°	1	1	1	1	1	1	2	2	2	2	2
-21.25°	1	1	1	1	1	1	2	2	2	2	2

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	1	1	1	1	2	2	2	2	2
-23.75°	1	1	1	1	1	1	2	2	2	2	2
-25°	1	1	1	1	1	1	2	2	2	2	2
-26.25°	1	1	1	1	1	1	1	2	2	2	2
-27.5°	1	1	1	1	1	1	1	2	2	2	2
-28.75°	1	1	1	1	1	1	1	2	2	2	2
-30°	1	1	1	1	1	1	1	2	2	2	2
-31.25°	1	1	1	1	1	1	1	1	2	2	2
-32.5°	1	1	1	1	1	1	1	1	2	2	2
-33.75°	1	1	1	1	1	1	1	1	2	2	2
-35°	1	1	1	1	1	1	1	1	2	2	2
-36.25°	1	1	1	1	1	1	1	1	1	2	2
-37.5°	1	1	1	1	1	1	1	1	1	2	2
-38.75°	1	1	1	1	1	1	1	1	1	2	2
-40°	1	1	1	1	1	1	1	1	1	1	2
-41.25°	1	1	1	1	1	1	1	1	1	1	2
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	0	1	1	1	1	1	1	1	1	1	1
-63.75°	0	1	1	1	1	1	1	1	1	1	1
-65°	0	0	1	1	1	1	1	1	1	1	1
-66.25°	0	0	1	1	1	1	1	1	1	1	1
-67.5°	0	0	0	1	1	1	1	1	1	1	1
-68.75°	0	0	0	0	1	1	1	1	1	1	1
-70°	0	0	0	0	0	1	1	1	1	1	1
-71.25°	0	0	0	0	0	0	1	1	1	1	1
-72.5°	0	0	0	0	0	0	0	1	1	1	1
-73.75°	0	0	0	0	0	0	0	0	1	1	1
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	2	2
53.75°	1	1	1	1	1	1	1	2	2	2	2
52.5°	1	1	1	1	1	2	2	2	2	2	2
51.25°	1	1	1	1	2	2	2	2	2	2	2
50°	1	1	1	2	2	2	2	2	2	2	2
48.75°	1	1	2	2	2	2	2	2	2	2	2
47.5°	1	1	2	2	2	2	2	2	2	2	2
46.25°	1	2	2	2	2	2	2	2	2	2	2
45°	1	2	2	2	2	2	2	2	2	2	3
43.75°	2	2	2	2	2	2	2	2	2	2	3
42.5°	2	2	2	2	2	2	2	2	2	3	3
41.25°	2	2	2	2	2	2	2	2	3	3	3
40°	2	2	2	2	2	2	2	2	3	3	3
38.75°	2	2	2	2	2	2	2	3	3	3	3
37.5°	2	2	2	2	2	2	3	3	3	3	3
36.25°	2	2	2	2	2	2	3	3	3	3	3
35°	2	2	2	2	2	3	3	3	3	3	3

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	2	2	2	2	2	3	3	3	3	3	3
32.5°	2	2	2	2	3	3	3	3	4	3	4
31.25°	2	2	2	2	3	3	3	4	4	3	4
30°	2	2	2	2	3	3	3	4	4	4	4
28.75°	2	2	2	3	3	3	4	4	4	4	4
27.5°	2	2	2	3	3	3	4	4	4	4	4
26.25°	2	2	2	3	3	3	4	4	4	4	4
25°	2	2	3	3	3	4	4	4	4	4	4
23.75°	2	2	3	3	3	4	4	4	4	4	4
22.5°	2	2	3	3	3	4	4	4	4	4	5
21.25°	2	2	3	3	4	4	4	4	4	4	5
20°	2	2	3	3	4	4	4	4	4	5	5
18.75°	2	3	3	3	4	4	4	4	4	5	5
17.5°	2	3	3	3	4	4	4	4	4	5	5
16.25°	2	3	3	3	4	4	4	4	5	5	5
15°	2	3	3	4	4	4	4	4	5	5	5
13.75°	2	3	3	4	4	4	4	4	5	5	5
12.5°	2	3	3	4	4	4	4	4	5	5	5
11.25°	2	3	3	4	4	4	4	5	5	5	5
10°	3	3	3	4	4	4	4	5	5	5	6
8.75°	3	3	3	4	4	4	4	5	5	5	6
7.5°	3	3	3	4	4	4	4	5	5	5	6
6.25°	3	3	3	4	4	4	4	5	5	5	6
5°	3	3	3	4	4	4	4	5	5	6	6
3.75°	3	3	3	4	4	4	4	5	5	6	6
2.5°	3	3	3	4	4	4	4	5	5	6	6
1.25°	3	3	3	4	4	4	4	5	5	6	6
0°	3	3	4	4	4	4	4	5	5	6	6
-1.25°	3	3	3	4	4	4	4	5	5	6	6
-2.5°	3	3	3	4	4	4	4	5	5	6	6
-3.75°	3	3	3	4	4	4	4	5	5	6	6
-5°	3	3	3	4	4	4	4	5	5	6	6
-6.25°	3	3	3	4	4	4	4	5	5	5	6
-7.5°	3	3	3	4	4	4	4	5	5	5	6
-8.75°	3	3	3	4	4	4	4	5	5	5	6
-10°	3	3	3	4	4	4	4	5	5	5	6
-11.25°	2	3	3	4	4	4	4	5	5	5	5
-12.5°	2	3	3	4	4	4	4	4	5	5	5
-13.75°	2	3	3	4	4	4	4	4	5	5	5
-15°	2	3	3	4	4	4	4	4	5	5	5
-16.25°	2	3	3	3	4	4	4	4	5	5	5
-17.5°	2	3	3	3	4	4	4	4	4	5	5
-18.75°	2	3	3	3	4	4	4	4	4	5	5
-20°	2	2	3	3	4	4	4	4	4	5	5
-21.25°	2	2	3	3	4	4	4	4	4	4	5

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	2	3	3	3	4	4	4	4	4	5
-23.75°	2	2	3	3	3	4	4	4	4	4	4
-25°	2	2	3	3	3	4	4	4	4	4	4
-26.25°	2	2	2	3	3	3	4	4	4	4	4
-27.5°	2	2	2	3	3	3	4	4	4	4	4
-28.75°	2	2	2	3	3	3	4	4	4	4	4
-30°	2	2	2	2	3	3	3	4	4	4	4
-31.25°	2	2	2	2	3	3	3	4	4	3	4
-32.5°	2	2	2	2	3	3	3	3	4	3	4
-33.75°	2	2	2	2	2	3	3	3	3	3	3
-35°	2	2	2	2	2	3	3	3	3	3	3
-36.25°	2	2	2	2	2	2	3	3	3	3	3
-37.5°	2	2	2	2	2	2	3	3	3	3	3
-38.75°	2	2	2	2	2	2	2	3	3	3	3
-40°	2	2	2	2	2	2	2	2	3	3	3
-41.25°	2	2	2	2	2	2	2	2	3	3	3
-42.5°	2	2	2	2	2	2	2	2	2	3	3
-43.75°	2	2	2	2	2	2	2	2	2	2	3
-45°	1	2	2	2	2	2	2	2	2	2	3
-46.25°	1	2	2	2	2	2	2	2	2	2	2
-47.5°	1	1	2	2	2	2	2	2	2	2	2
-48.75°	1	1	2	2	2	2	2	2	2	2	2
-50°	1	1	1	2	2	2	2	2	2	2	2
-51.25°	1	1	1	1	2	2	2	2	2	2	2
-52.5°	1	1	1	1	1	2	2	2	2	2	2
-53.75°	1	1	1	1	1	1	1	2	2	2	2
-55°	1	1	1	1	1	1	1	1	1	2	2
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	1	1	1	1
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	2
61.25°	1	1	1	1	1	1	1	1	2	2	2
60°	1	1	1	1	1	2	2	2	2	2	2
58.75°	1	1	1	2	2	2	2	2	2	2	2
57.5°	1	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	3
53.75°	2	2	2	2	2	2	2	2	3	3	3
52.5°	2	2	2	2	2	2	3	3	3	3	3
51.25°	2	2	2	2	2	3	3	3	3	3	3
50°	2	2	2	3	3	3	3	3	3	3	3
48.75°	2	2	3	3	3	3	3	3	3	3	3
47.5°	2	3	3	3	3	3	3	3	3	3	3
46.25°	3	3	3	3	3	3	3	3	4	4	4
45°	3	3	3	3	3	3	3	4	4	4	4
43.75°	3	3	3	3	3	3	4	4	4	4	4
42.5°	3	3	3	3	3	4	4	4	4	4	4
41.25°	3	3	3	3	4	4	4	4	4	4	4
40°	3	3	3	4	4	4	4	4	4	4	5
38.75°	3	3	4	4	4	4	4	4	4	5	5
37.5°	3	3	4	4	4	4	4	4	5	5	5
36.25°	3	4	4	4	4	4	4	5	5	5	6
35°	4	4	4	4	4	4	5	5	5	6	6

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	4	4	4	4	4	5	5	5	6	6	6
32.5°	4	4	4	4	4	5	5	5	6	6	7
31.25°	4	4	4	4	5	5	5	6	6	7	7
30°	4	4	4	4	5	5	6	6	7	7	8
28.75°	4	4	4	5	5	5	6	7	7	8	9
27.5°	4	4	5	5	5	6	6	7	8	9	10
26.25°	4	4	5	5	6	6	7	8	9	10	12
25°	4	5	5	5	6	7	8	9	10	11	13
23.75°	5	5	5	6	6	7	8	10	11	13	15
22.5°	5	5	5	6	7	8	9	10	12	14	17
21.25°	5	5	6	6	7	8	10	12	14	16	20
20°	5	5	6	7	8	9	11	13	15	19	23
18.75°	5	5	6	7	8	10	12	14	17	21	26
17.5°	5	6	6	7	9	11	13	15	19	24	31
16.25°	5	6	7	8	10	11	14	16	22	27	37
15°	6	6	7	8	10	12	15	18	24	30	42
13.75°	6	6	7	9	11	13	16	21	27	35	48
12.5°	6	7	8	10	12	14	17	23	29	40	53
11.25°	6	7	8	10	12	15	18	25	32	44	58
10°	6	7	8	11	13	16	20	27	35	49	63
8.75°	6	7	9	11	14	17	22	29	39	53	69
7.5°	7	7	9	11	14	17	23	31	42	56	75
6.25°	7	8	10	12	15	18	25	33	45	59	80
5°	7	8	10	12	15	19	26	35	48	62	85
3.75°	7	8	10	13	16	19	28	36	50	65	89
2.5°	7	8	10	13	16	20	29	38	52	67	93
1.25°	7	8	11	13	17	20	29	39	54	69	95
0°	7	8	11	13	17	20	30	40	55	70	97
-1.25°	7	8	11	13	17	20	29	39	54	69	95
-2.5°	7	8	10	13	16	20	29	38	52	67	93
-3.75°	7	8	10	13	16	19	28	36	50	65	89
-5°	7	8	10	12	15	19	26	35	48	62	85
-6.25°	7	8	10	12	15	18	25	33	45	59	80
-7.5°	7	7	9	11	14	17	23	31	42	56	75
-8.75°	6	7	9	11	14	17	22	29	39	53	69
-10°	6	7	8	11	13	16	20	27	35	49	63
-11.25°	6	7	8	10	12	15	18	25	32	44	58
-12.5°	6	7	8	10	12	14	17	23	29	40	53
-13.75°	6	6	7	9	11	13	16	21	27	35	48
-15°	6	6	7	8	10	12	15	18	24	30	42
-16.25°	5	6	7	8	10	11	14	16	22	27	37
-17.5°	5	6	6	7	9	11	13	15	19	24	31
-18.75°	5	5	6	7	8	10	12	14	17	21	26
-20°	5	5	6	7	8	9	11	13	15	19	23
-21.25°	5	5	6	6	7	8	10	12	14	16	20

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	5	5	5	6	7	8	9	10	12	14	17
-23.75°	5	5	5	6	6	7	8	10	11	13	15
-25°	4	5	5	5	6	7	8	9	10	11	13
-26.25°	4	4	5	5	6	6	7	8	9	10	12
-27.5°	4	4	5	5	5	6	6	7	8	9	10
-28.75°	4	4	4	5	5	5	6	7	7	8	9
-30°	4	4	4	4	5	5	6	6	7	7	8
-31.25°	4	4	4	4	5	5	5	6	6	7	7
-32.5°	4	4	4	4	4	5	5	5	6	6	7
-33.75°	4	4	4	4	4	5	5	5	6	6	6
-35°	4	4	4	4	4	4	5	5	5	6	6
-36.25°	3	4	4	4	4	4	4	5	5	5	6
-37.5°	3	3	4	4	4	4	4	4	5	5	5
-38.75°	3	3	4	4	4	4	4	4	4	5	5
-40°	3	3	3	4	4	4	4	4	4	4	5
-41.25°	3	3	3	3	4	4	4	4	4	4	4
-42.5°	3	3	3	3	3	4	4	4	4	4	4
-43.75°	3	3	3	3	3	3	4	4	4	4	4
-45°	3	3	3	3	3	3	3	4	4	4	4
-46.25°	3	3	3	3	3	3	3	3	4	4	4
-47.5°	2	3	3	3	3	3	3	3	3	3	3
-48.75°	2	2	3	3	3	3	3	3	3	3	3
-50°	2	2	2	3	3	3	3	3	3	3	3
-51.25°	2	2	2	2	2	3	3	3	3	3	3
-52.5°	2	2	2	2	2	2	3	3	3	3	3
-53.75°	2	2	2	2	2	2	2	2	3	3	3
-55°	2	2	2	2	2	2	2	2	2	2	3
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	1	2	2	2	2	2	2	2	2	2	2
-58.75°	1	1	1	2	2	2	2	2	2	2	2
-60°	1	1	1	1	1	2	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	2	2	2
-62.5°	1	1	1	1	1	1	1	1	1	1	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	1	1	1	1	1	1	1

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	2
65°	1	1	1	1	1	2	2	2	2	2	2
63.75°	1	1	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	3	3
56.25°	2	2	2	2	2	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	4
50°	3	3	3	3	3	3	3	4	4	4	4
48.75°	3	3	3	3	3	4	4	4	4	4	4
47.5°	3	3	3	4	4	4	4	4	4	4	5
46.25°	3	4	4	4	4	4	4	5	5	5	5
45°	4	4	4	4	4	5	5	5	5	5	5
43.75°	4	4	4	5	5	5	5	5	5	5	5
42.5°	4	5	5	5	5	5	5	5	6	6	6
41.25°	5	5	5	5	5	6	6	6	6	6	6
40°	5	5	5	6	6	6	6	6	6	7	7
38.75°	5	5	6	6	6	6	6	7	7	7	7
37.5°	6	6	6	6	6	7	7	7	8	8	8
36.25°	6	6	6	7	7	7	8	8	9	9	9
35°	6	7	7	7	7	8	9	9	10	10	11

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	7	7	7	8	8	9	10	10	11	11	12
32.5°	7	8	8	9	10	10	11	12	12	13	15
31.25°	8	9	10	10	11	12	12	13	15	16	17
30°	9	10	11	12	13	14	15	16	17	19	21
28.75°	10	11	12	14	15	17	19	19	21	24	26
27.5°	12	13	15	16	18	21	23	25	27	30	32
26.25°	13	15	17	19	23	26	29	33	35	36	42
25°	15	18	20	25	29	33	38	42	45	49	53
23.75°	18	21	25	31	36	42	48	53	59	64	67
22.5°	21	24	32	38	45	53	59	68	74	80	87
21.25°	24	31	38	46	56	64	74	83	91	100	107
20°	28	37	45	57	67	78	90	100	111	120	128
18.75°	35	45	56	68	80	94	107	119	130	140	149
17.5°	42	52	67	80	96	111	125	139	151	161	172
16.25°	48	62	78	94	112	128	144	158	171	183	195
15°	54	72	90	109	128	146	163	178	191	205	218
13.75°	61	81	99	122	145	164	182	197	212	227	241
12.5°	69	89	110	134	157	179	201	216	233	249	264
11.25°	77	98	121	145	169	192	213	234	254	270	287
10°	85	106	131	156	180	204	225	247	268	288	310
8.75°	92	115	140	165	191	216	237	260	280	302	324
7.5°	98	123	149	175	201	226	249	271	292	314	337
6.25°	104	130	156	183	210	236	259	281	302	325	349
5°	110	136	163	191	219	245	268	290	312	335	359
3.75°	115	142	169	198	227	253	276	299	321	344	368
2.5°	119	147	174	204	233	260	283	306	328	351	376
1.25°	122	150	178	209	239	266	290	312	334	358	381
0°	125	153	182	213	244	271	295	317	339	363	386
-1.25°	122	150	178	209	239	266	290	312	334	358	381
-2.5°	119	147	174	204	233	260	283	306	328	351	376
-3.75°	115	142	169	198	227	253	276	299	321	344	368
-5°	110	136	163	191	219	245	268	290	312	335	359
-6.25°	104	130	156	183	210	236	259	281	302	325	349
-7.5°	98	123	149	175	201	226	249	271	292	314	337
-8.75°	92	115	140	165	191	216	237	260	280	302	324
-10°	85	106	131	156	180	204	225	247	268	288	310
-11.25°	77	98	121	145	169	192	213	234	254	270	287
-12.5°	69	89	110	134	157	179	201	216	233	249	264
-13.75°	61	81	99	122	145	164	182	197	212	227	241
-15°	54	72	90	109	128	146	163	178	191	205	218
-16.25°	48	62	78	94	112	128	144	158	171	183	195
-17.5°	42	52	67	80	96	111	125	139	151	161	172
-18.75°	35	45	56	68	80	94	107	119	130	140	149
-20°	28	37	45	57	67	78	90	100	111	120	128
-21.25°	24	31	38	46	56	64	74	83	91	100	107

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	21	24	32	38	45	53	59	68	74	80	87
-23.75°	18	21	25	31	36	42	48	53	59	64	67
-25°	15	18	20	25	29	33	38	42	45	49	53
-26.25°	13	15	17	19	23	26	29	33	35	36	42
-27.5°	12	13	15	16	18	21	23	25	27	30	32
-28.75°	10	11	12	14	15	17	19	19	21	24	26
-30°	9	10	11	12	13	14	15	16	17	19	21
-31.25°	8	9	10	10	11	12	12	13	15	16	17
-32.5°	7	8	8	9	10	10	11	12	12	13	15
-33.75°	7	7	7	8	8	9	10	10	11	11	12
-35°	6	7	7	7	7	8	9	9	10	10	11
-36.25°	6	6	6	7	7	7	8	8	9	9	9
-37.5°	6	6	6	6	6	7	7	7	8	8	8
-38.75°	5	5	6	6	6	6	6	7	7	7	7
-40°	5	5	5	6	6	6	6	6	6	7	7
-41.25°	5	5	5	5	5	6	6	6	6	6	6
-42.5°	4	5	5	5	5	5	5	5	6	6	6
-43.75°	4	4	4	5	5	5	5	5	5	5	5
-45°	4	4	4	4	4	5	5	5	5	5	5
-46.25°	3	4	4	4	4	4	4	5	5	5	5
-47.5°	3	3	3	4	4	4	4	4	4	4	5
-48.75°	3	3	3	3	3	4	4	4	4	4	4
-50°	3	3	3	3	3	3	3	4	4	4	4
-51.25°	3	3	3	3	3	3	3	3	3	3	4
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	2	2	2	2	3	3	3	3	3	3
-57.5°	2	2	2	2	2	2	2	2	2	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	1	2	2	2	2	2	2	2	2	2
-65°	1	1	1	1	1	2	2	2	2	2	2
-66.25°	1	1	1	1	1	1	1	1	1	1	2
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	3	3
58.75°	2	2	2	3	3	3	3	3	3	3	3
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	4	4	4	4	4
52.5°	3	3	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	5	5
47.5°	5	5	4	4	5	5	5	5	5	5	5
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	5	5	5	5	5	5	5	6	6	6	6
43.75°	6	6	6	6	6	6	6	6	6	6	6
42.5°	6	6	6	6	6	6	6	6	7	7	7
41.25°	6	6	7	7	7	7	7	7	7	7	7
40°	7	7	7	7	7	7	8	8	8	8	8
38.75°	8	8	8	8	8	8	8	9	9	9	9
37.5°	8	9	9	9	9	9	9	10	10	10	10
36.25°	10	10	10	10	11	11	11	11	11	11	11
35°	11	11	12	12	12	12	12	12	13	13	13

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	13	14	14	14	15	15	14	14	14	15	15
32.5°	15	16	17	18	18	18	17	16	17	17	18
31.25°	19	20	21	22	22	22	21	20	20	20	21
30°	23	25	26	28	28	28	27	25	24	25	26
28.75°	28	31	34	35	35	36	35	32	29	30	31
27.5°	37	40	43	45	46	46	44	41	38	37	39
26.25°	47	50	55	58	59	58	57	54	50	47	49
25°	58	65	69	72	74	74	72	70	65	60	62
23.75°	74	81	85	89	91	92	91	88	85	79	78
22.5°	92	98	105	109	112	113	112	110	106	100	95
21.25°	113	119	125	131	135	136	136	134	130	125	118
20°	135	142	149	155	159	161	161	159	156	152	146
18.75°	158	167	174	180	185	187	188	187	186	182	177
17.5°	182	191	200	206	211	215	217	218	217	215	211
16.25°	206	216	225	233	239	244	248	249	250	248	245
15°	230	242	251	260	268	275	279	281	282	281	278
13.75°	254	267	278	290	299	305	310	312	312	311	309
12.5°	279	293	307	319	328	334	337	339	340	340	336
11.25°	303	319	335	347	355	360	363	366	368	366	360
10°	328	346	363	373	380	384	388	391	391	387	382
8.75°	348	373	388	397	403	407	411	413	411	407	403
7.5°	362	387	406	419	424	429	432	433	430	427	424
6.25°	374	399	417	430	440	449	452	452	450	446	442
5°	385	408	427	439	449	458	464	468	468	462	456
3.75°	393	417	436	448	458	467	472	476	477	472	468
2.5°	400	425	444	456	466	475	479	483	482	478	474
1.25°	406	432	451	463	473	482	486	489	489	484	480
0°	410	437	457	469	479	488	492	495	496	490	485
-1.25°	406	432	451	463	473	482	486	489	489	484	480
-2.5°	400	425	444	456	466	475	479	483	482	478	474
-3.75°	393	417	436	448	458	467	472	476	477	472	468
-5°	385	408	427	439	449	458	464	468	468	462	456
-6.25°	374	399	417	430	440	449	452	452	450	446	442
-7.5°	362	387	406	419	424	429	432	433	430	427	424
-8.75°	348	373	388	397	403	407	411	413	411	407	403
-10°	328	346	363	373	380	384	388	391	391	387	382
-11.25°	303	319	335	347	355	360	363	366	368	366	360
-12.5°	279	293	307	319	328	334	337	339	340	340	336
-13.75°	254	267	278	290	299	305	310	312	312	311	309
-15°	230	242	251	260	268	275	279	281	282	281	278
-16.25°	206	216	225	233	239	244	248	249	250	248	245
-17.5°	182	191	200	206	211	215	217	218	217	215	211
-18.75°	158	167	174	180	185	187	188	187	186	182	177
-20°	135	142	149	155	159	161	161	159	156	152	146
-21.25°	113	119	125	131	135	136	136	134	130	125	118

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	92	98	105	109	112	113	112	110	106	100	95
-23.75°	74	81	85	89	91	92	91	88	85	79	78
-25°	58	65	69	72	74	74	72	70	65	60	62
-26.25°	47	50	55	58	59	58	57	54	50	47	49
-27.5°	37	40	43	45	46	46	44	41	38	37	39
-28.75°	28	31	34	35	35	36	35	32	29	30	31
-30°	23	25	26	28	28	28	27	25	24	25	26
-31.25°	19	20	21	22	22	22	21	20	20	20	21
-32.5°	15	16	17	18	18	18	17	16	17	17	18
-33.75°	13	14	14	14	15	15	14	14	14	15	15
-35°	11	11	12	12	12	12	12	12	13	13	13
-36.25°	10	10	10	10	11	11	11	11	11	11	11
-37.5°	8	9	9	9	9	9	9	10	10	10	10
-38.75°	8	8	8	8	8	8	8	9	9	9	9
-40°	7	7	7	7	7	7	8	8	8	8	8
-41.25°	6	6	7	7	7	7	7	7	7	7	7
-42.5°	6	6	6	6	6	6	6	6	7	7	7
-43.75°	6	6	6	6	6	6	6	6	6	6	6
-45°	5	5	5	5	5	5	5	6	6	6	6
-46.25°	5	5	5	5	5	5	5	5	5	5	5
-47.5°	5	5	4	4	5	5	5	5	5	5	5
-48.75°	4	4	4	4	4	4	4	4	4	5	5
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	3	3	4	4	4	4	4	4	4	4	4
-53.75°	3	3	3	3	3	3	4	4	4	4	4
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	3	3	3	3	3	3	3	3
-60°	2	2	2	2	2	2	2	2	2	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	1	1	1	1	1	2	2	2	2	2	2
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	3	3	3	3	3
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	4	3	3	3	3
53.75°	4	4	4	4	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	5	5	5	4	4	4	4	4	4	4	5
47.5°	5	5	5	5	5	4	4	4	5	5	5
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	6	6	6	5	5	5	5	5	5	5	6
43.75°	6	6	6	6	6	6	6	6	6	6	6
42.5°	7	7	7	7	7	7	7	7	7	7	7
41.25°	7	8	8	8	8	8	8	8	8	8	8
40°	8	8	8	8	8	8	8	8	8	8	8
38.75°	9	9	9	9	9	9	9	9	9	9	9
37.5°	10	10	10	10	10	10	10	10	10	10	10
36.25°	12	12	12	12	12	12	12	12	12	12	12
35°	13	13	14	14	14	13	13	13	14	14	14

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	15	16	16	16	16	15	15	15	16	16	16
32.5°	18	18	18	18	18	17	17	17	18	18	18
31.25°	21	22	22	22	21	21	20	21	21	22	22
30°	26	26	26	26	25	25	24	25	25	26	26
28.75°	32	32	32	32	31	30	29	30	31	32	32
27.5°	40	40	40	40	39	38	36	38	39	40	40
26.25°	50	51	52	52	51	49	47	49	51	52	52
25°	64	66	66	66	65	63	60	63	65	66	66
23.75°	80	82	82	82	80	78	75	78	80	82	82
22.5°	98	100	101	101	99	97	93	97	99	101	101
21.25°	120	122	123	123	122	119	114	119	122	123	123
20°	144	147	149	149	147	143	137	143	147	149	149
18.75°	172	176	178	178	175	171	164	171	175	178	178
17.5°	205	206	208	207	204	198	191	198	204	207	208
16.25°	241	238	239	237	233	227	219	227	233	237	239
15°	274	267	267	265	261	255	247	255	261	265	267
13.75°	304	297	292	290	285	278	270	278	285	290	292
12.5°	331	324	316	314	310	304	296	304	310	314	316
11.25°	354	348	341	337	333	327	319	327	333	337	341
10°	377	372	365	359	355	350	341	350	355	359	365
8.75°	400	396	389	379	375	370	363	370	375	379	389
7.5°	422	417	408	399	393	388	381	388	393	399	408
6.25°	438	434	426	416	407	402	395	402	407	416	426
5°	452	447	441	430	419	413	408	413	419	430	441
3.75°	465	459	449	438	428	420	415	420	428	438	449
2.5°	474	468	457	445	433	425	421	425	433	445	457
1.25°	478	471	460	449	437	429	425	429	437	449	460
0°	482	475	464	451	438	431	429	431	438	451	464
-1.25°	478	471	460	449	437	429	425	429	437	449	460
-2.5°	474	468	457	445	433	425	421	425	433	445	457
-3.75°	465	459	449	438	428	420	415	420	428	438	449
-5°	452	447	441	430	419	413	408	413	419	430	441
-6.25°	438	434	426	416	407	402	395	402	407	416	426
-7.5°	422	417	408	399	393	388	381	388	393	399	408
-8.75°	400	396	389	379	375	370	363	370	375	379	389
-10°	377	372	365	359	355	350	341	350	355	359	365
-11.25°	354	348	341	337	333	327	319	327	333	337	341
-12.5°	331	324	316	314	310	304	296	304	310	314	316
-13.75°	304	297	292	290	285	278	270	278	285	290	292
-15°	274	267	267	265	261	255	247	255	261	265	267
-16.25°	241	238	239	237	233	227	219	227	233	237	239
-17.5°	205	206	208	207	204	198	191	198	204	207	208
-18.75°	172	176	178	178	175	171	164	171	175	178	178
-20°	144	147	149	149	147	143	137	143	147	149	149
-21.25°	120	122	123	123	122	119	114	119	122	123	123

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	98	100	101	101	99	97	93	97	99	101	101
-23.75°	80	82	82	82	80	78	75	78	80	82	82
-25°	64	66	66	66	65	63	60	63	65	66	66
-26.25°	50	51	52	52	51	49	47	49	51	52	52
-27.5°	40	40	40	40	39	38	36	38	39	40	40
-28.75°	32	32	32	32	31	30	29	30	31	32	32
-30°	26	26	26	26	25	25	24	25	25	26	26
-31.25°	21	22	22	22	21	21	20	21	21	22	22
-32.5°	18	18	18	18	18	17	17	17	18	18	18
-33.75°	15	16	16	16	16	15	15	15	16	16	16
-35°	13	13	14	14	14	13	13	13	14	14	14
-36.25°	12	12	12	12	12	12	12	12	12	12	12
-37.5°	10	10	10	10	10	10	10	10	10	10	10
-38.75°	9	9	9	9	9	9	9	9	9	9	9
-40°	8	8	8	8	8	8	8	8	8	8	8
-41.25°	7	8	8	8	8	8	8	8	8	8	8
-42.5°	7	7	7	7	7	7	7	7	7	7	7
-43.75°	6	6	6	6	6	6	6	6	6	6	6
-45°	6	6	6	5	5	5	5	5	5	5	6
-46.25°	5	5	5	5	5	5	5	5	5	5	5
-47.5°	5	5	5	5	5	4	4	4	5	5	5
-48.75°	5	5	5	4	4	4	4	4	4	4	5
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	4	4	4	4
-55°	3	3	3	3	3	3	4	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	2	2	2	2	2	2	2	2	1	1	1
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	3	3	3	3	2	2	2	2	2	2	2
58.75°	3	3	3	3	3	3	3	3	3	3	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	4	4	4	4	4	4	4	3	3	3	3
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	5	5	5	5	4	4	4	4	4	4	4
47.5°	5	5	5	5	5	5	5	5	5	4	4
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	6	6	6	6	6	6	5	5	5	5	5
43.75°	6	6	6	6	6	6	6	6	6	6	6
42.5°	7	7	7	7	7	6	6	6	6	6	6
41.25°	8	7	7	7	7	7	7	7	7	7	7
40°	8	8	8	8	8	8	8	7	7	7	7
38.75°	9	9	9	9	9	9	8	8	8	8	8
37.5°	10	10	10	10	10	10	9	9	9	9	9
36.25°	12	12	11	11	11	11	11	11	11	10	10
35°	13	13	13	13	13	12	12	12	12	12	12

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	16	15	15	15	14	14	14	15	15	14	14
32.5°	18	18	18	17	17	16	17	18	18	18	17
31.25°	22	21	21	20	20	20	21	22	22	22	21
30°	26	26	26	25	24	25	27	28	28	28	26
28.75°	32	32	31	30	29	32	35	36	35	35	34
27.5°	40	40	39	37	38	41	44	46	46	45	43
26.25°	51	50	49	47	50	54	57	58	59	58	55
25°	66	64	62	60	65	70	72	74	74	72	69
23.75°	82	80	78	79	85	88	91	92	91	89	85
22.5°	100	98	95	100	106	110	112	113	112	109	105
21.25°	122	120	118	125	130	134	136	136	135	131	125
20°	147	144	146	152	156	159	161	161	159	155	149
18.75°	176	172	177	182	186	187	188	187	185	180	174
17.5°	206	205	211	215	217	218	217	215	211	206	200
16.25°	238	241	245	248	250	249	248	244	239	233	225
15°	267	274	278	281	282	281	279	275	268	260	251
13.75°	297	304	309	311	312	312	310	305	299	290	278
12.5°	324	331	336	340	340	339	337	334	328	319	307
11.25°	348	354	360	366	368	366	363	360	355	347	335
10°	372	377	382	387	391	391	388	384	380	373	363
8.75°	396	400	403	407	411	413	411	407	403	397	388
7.5°	417	422	424	427	430	433	432	429	424	419	406
6.25°	434	438	442	446	450	452	452	449	440	430	417
5°	447	452	456	462	468	468	464	458	449	439	427
3.75°	459	465	468	472	477	476	472	467	458	448	436
2.5°	468	474	474	478	482	483	479	475	466	456	444
1.25°	471	478	480	484	489	489	486	482	473	463	451
0°	475	482	485	490	496	495	492	488	479	469	457
-1.25°	471	478	480	484	489	489	486	482	473	463	451
-2.5°	468	474	474	478	482	483	479	475	466	456	444
-3.75°	459	465	468	472	477	476	472	467	458	448	436
-5°	447	452	456	462	468	468	464	458	449	439	427
-6.25°	434	438	442	446	450	452	452	449	440	430	417
-7.5°	417	422	424	427	430	433	432	429	424	419	406
-8.75°	396	400	403	407	411	413	411	407	403	397	388
-10°	372	377	382	387	391	391	388	384	380	373	363
-11.25°	348	354	360	366	368	366	363	360	355	347	335
-12.5°	324	331	336	340	340	339	337	334	328	319	307
-13.75°	297	304	309	311	312	312	310	305	299	290	278
-15°	267	274	278	281	282	281	279	275	268	260	251
-16.25°	238	241	245	248	250	249	248	244	239	233	225
-17.5°	206	205	211	215	217	218	217	215	211	206	200
-18.75°	176	172	177	182	186	187	188	187	185	180	174
-20°	147	144	146	152	156	159	161	161	159	155	149
-21.25°	122	120	118	125	130	134	136	136	135	131	125

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	100	98	95	100	106	110	112	113	112	109	105
-23.75°	82	80	78	79	85	88	91	92	91	89	85
-25°	66	64	62	60	65	70	72	74	74	72	69
-26.25°	51	50	49	47	50	54	57	58	59	58	55
-27.5°	40	40	39	37	38	41	44	46	46	45	43
-28.75°	32	32	31	30	29	32	35	36	35	35	34
-30°	26	26	26	25	24	25	27	28	28	28	26
-31.25°	22	21	21	20	20	20	21	22	22	22	21
-32.5°	18	18	18	17	17	16	17	18	18	18	17
-33.75°	16	15	15	15	14	14	14	15	15	14	14
-35°	13	13	13	13	13	12	12	12	12	12	12
-36.25°	12	12	11	11	11	11	11	11	11	10	10
-37.5°	10	10	10	10	10	10	9	9	9	9	9
-38.75°	9	9	9	9	9	9	8	8	8	8	8
-40°	8	8	8	8	8	8	8	7	7	7	7
-41.25°	8	7	7	7	7	7	7	7	7	7	7
-42.5°	7	7	7	7	7	6	6	6	6	6	6
-43.75°	6	6	6	6	6	6	6	6	6	6	6
-45°	6	6	6	6	6	6	5	5	5	5	5
-46.25°	5	5	5	5	5	5	5	5	5	5	5
-47.5°	5	5	5	5	5	5	5	5	5	4	4
-48.75°	5	5	5	5	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	2
-60°	3	3	3	3	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	2	2	2	1	1	1	1	1	1	1	1
65°	2	2	2	2	2	2	2	2	1	1	1
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	2	2	2	2	2	2	2
56.25°	3	3	3	3	3	3	3	3	2	2	2
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	4	4	4	3	3	3	3	3	3	3	3
50°	4	4	4	4	4	4	3	3	3	3	3
48.75°	4	4	4	4	4	4	4	4	3	3	3
47.5°	5	5	5	4	4	4	4	4	4	4	3
46.25°	5	5	5	5	5	5	4	4	4	4	4
45°	5	5	5	5	5	5	5	5	4	4	4
43.75°	6	6	5	5	5	5	5	5	5	5	4
42.5°	6	6	6	6	6	5	5	5	5	5	5
41.25°	6	6	6	6	6	6	6	6	5	5	5
40°	7	7	7	7	6	6	6	6	6	6	5
38.75°	8	8	7	7	7	7	6	6	6	6	6
37.5°	9	8	8	8	8	7	7	7	6	6	6
36.25°	10	10	9	9	9	8	8	7	7	7	6
35°	11	11	11	10	10	9	9	8	7	7	7

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	14	13	12	11	11	10	10	9	8	8	7
32.5°	16	15	15	13	12	12	11	10	10	9	8
31.25°	20	19	17	16	15	13	12	12	11	10	10
30°	25	23	21	19	17	16	15	14	13	12	11
28.75°	31	28	26	24	21	19	19	17	15	14	12
27.5°	40	37	32	30	27	25	23	21	18	16	15
26.25°	50	47	42	36	35	33	29	26	23	19	17
25°	65	58	53	49	45	42	38	33	29	25	20
23.75°	81	74	67	64	59	53	48	42	36	31	25
22.5°	98	92	87	80	74	68	59	53	45	38	32
21.25°	119	113	107	100	91	83	74	64	56	46	38
20°	142	135	128	120	111	100	90	78	67	57	45
18.75°	167	158	149	140	130	119	107	94	80	68	56
17.5°	191	182	172	161	151	139	125	111	96	80	67
16.25°	216	206	195	183	171	158	144	128	112	94	78
15°	242	230	218	205	191	178	163	146	128	109	90
13.75°	267	254	241	227	212	197	182	164	145	122	99
12.5°	293	279	264	249	233	216	201	179	157	134	110
11.25°	319	303	287	270	254	234	213	192	169	145	121
10°	346	328	310	288	268	247	225	204	180	156	131
8.75°	373	348	324	302	280	260	237	216	191	165	140
7.5°	387	362	337	314	292	271	249	226	201	175	149
6.25°	399	374	349	325	302	281	259	236	210	183	156
5°	408	385	359	335	312	290	268	245	219	191	163
3.75°	417	393	368	344	321	299	276	253	227	198	169
2.5°	425	400	376	351	328	306	283	260	233	204	174
1.25°	432	406	381	358	334	312	290	266	239	209	178
0°	437	410	386	363	339	317	295	271	244	213	182
-1.25°	432	406	381	358	334	312	290	266	239	209	178
-2.5°	425	400	376	351	328	306	283	260	233	204	174
-3.75°	417	393	368	344	321	299	276	253	227	198	169
-5°	408	385	359	335	312	290	268	245	219	191	163
-6.25°	399	374	349	325	302	281	259	236	210	183	156
-7.5°	387	362	337	314	292	271	249	226	201	175	149
-8.75°	373	348	324	302	280	260	237	216	191	165	140
-10°	346	328	310	288	268	247	225	204	180	156	131
-11.25°	319	303	287	270	254	234	213	192	169	145	121
-12.5°	293	279	264	249	233	216	201	179	157	134	110
-13.75°	267	254	241	227	212	197	182	164	145	122	99
-15°	242	230	218	205	191	178	163	146	128	109	90
-16.25°	216	206	195	183	171	158	144	128	112	94	78
-17.5°	191	182	172	161	151	139	125	111	96	80	67
-18.75°	167	158	149	140	130	119	107	94	80	68	56
-20°	142	135	128	120	111	100	90	78	67	57	45
-21.25°	119	113	107	100	91	83	74	64	56	46	38

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	98	92	87	80	74	68	59	53	45	38	32
-23.75°	81	74	67	64	59	53	48	42	36	31	25
-25°	65	58	53	49	45	42	38	33	29	25	20
-26.25°	50	47	42	36	35	33	29	26	23	19	17
-27.5°	40	37	32	30	27	25	23	21	18	16	15
-28.75°	31	28	26	24	21	19	19	17	15	14	12
-30°	25	23	21	19	17	16	15	14	13	12	11
-31.25°	20	19	17	16	15	13	12	12	11	10	10
-32.5°	16	15	15	13	12	12	11	10	10	9	8
-33.75°	14	13	12	11	11	10	10	9	8	8	7
-35°	11	11	11	10	10	9	9	8	7	7	7
-36.25°	10	10	9	9	9	8	8	7	7	7	6
-37.5°	9	8	8	8	8	7	7	7	6	6	6
-38.75°	8	8	7	7	7	7	6	6	6	6	6
-40°	7	7	7	7	6	6	6	6	6	6	5
-41.25°	6	6	6	6	6	6	6	6	5	5	5
-42.5°	6	6	6	6	6	5	5	5	5	5	5
-43.75°	6	6	5	5	5	5	5	5	5	5	4
-45°	5	5	5	5	5	5	5	5	4	4	4
-46.25°	5	5	5	5	5	5	4	4	4	4	4
-47.5°	5	5	5	4	4	4	4	4	4	4	3
-48.75°	4	4	4	4	4	4	4	4	3	3	3
-50°	4	4	4	4	4	4	3	3	3	3	3
-51.25°	4	4	4	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	2	2	2
-57.5°	3	3	3	3	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	1	1	1
-66.25°	2	2	2	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	1	1	1	1	1	1	1	1
61.25°	2	2	2	2	2	1	1	1	1	1	1
60°	2	2	2	2	2	2	2	2	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	2	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	2	2	2	2	2	2	2	2
53.75°	3	3	3	3	3	2	2	2	2	2	2
52.5°	3	3	3	3	3	3	3	2	2	2	2
51.25°	3	3	3	3	3	3	3	3	2	2	2
50°	3	3	3	3	3	3	3	3	3	3	2
48.75°	3	3	3	3	3	3	3	3	3	3	3
47.5°	3	3	3	3	3	3	3	3	3	3	3
46.25°	4	3	4	4	4	3	3	3	3	3	3
45°	4	4	4	4	4	4	3	3	3	3	3
43.75°	4	4	4	4	4	4	4	3	3	3	3
42.5°	5	4	4	4	4	4	4	4	3	3	3
41.25°	5	5	4	4	4	4	4	4	4	3	3
40°	5	5	5	4	4	4	4	4	4	4	3
38.75°	5	5	5	5	4	4	4	4	4	4	4
37.5°	6	6	5	5	5	4	4	4	4	4	4
36.25°	6	6	6	5	5	5	4	4	4	4	4
35°	7	6	6	6	5	5	5	4	4	4	4

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	7	7	6	6	6	5	5	5	4	4	4
32.5°	8	7	7	6	6	5	5	5	4	4	4
31.25°	9	8	7	7	6	6	5	5	5	4	4
30°	10	9	8	7	7	6	6	5	5	4	4
28.75°	11	10	9	8	7	7	6	5	5	5	4
27.5°	13	12	10	9	8	7	6	6	5	5	5
26.25°	15	13	12	10	9	8	7	6	6	5	5
25°	18	15	13	11	10	9	8	7	6	5	5
23.75°	21	18	15	13	11	10	8	7	6	6	5
22.5°	24	21	17	14	12	10	9	8	7	6	5
21.25°	31	24	20	16	14	12	10	8	7	6	6
20°	37	28	23	19	15	13	11	9	8	7	6
18.75°	45	35	26	21	17	14	12	10	8	7	6
17.5°	52	42	31	24	19	15	13	11	9	7	6
16.25°	62	48	37	27	22	16	14	11	10	8	7
15°	72	54	42	30	24	18	15	12	10	8	7
13.75°	81	61	48	35	27	21	16	13	11	9	7
12.5°	89	69	53	40	29	23	17	14	12	10	8
11.25°	98	77	58	44	32	25	18	15	12	10	8
10°	106	85	63	49	35	27	20	16	13	11	8
8.75°	115	92	69	53	39	29	22	17	14	11	9
7.5°	123	98	75	56	42	31	23	17	14	11	9
6.25°	130	104	80	59	45	33	25	18	15	12	10
5°	136	110	85	62	48	35	26	19	15	12	10
3.75°	142	115	89	65	50	36	28	19	16	13	10
2.5°	147	119	93	67	52	38	29	20	16	13	10
1.25°	150	122	95	69	54	39	29	20	17	13	11
0°	153	125	97	70	55	40	30	20	17	13	11
-1.25°	150	122	95	69	54	39	29	20	17	13	11
-2.5°	147	119	93	67	52	38	29	20	16	13	10
-3.75°	142	115	89	65	50	36	28	19	16	13	10
-5°	136	110	85	62	48	35	26	19	15	12	10
-6.25°	130	104	80	59	45	33	25	18	15	12	10
-7.5°	123	98	75	56	42	31	23	17	14	11	9
-8.75°	115	92	69	53	39	29	22	17	14	11	9
-10°	106	85	63	49	35	27	20	16	13	11	8
-11.25°	98	77	58	44	32	25	18	15	12	10	8
-12.5°	89	69	53	40	29	23	17	14	12	10	8
-13.75°	81	61	48	35	27	21	16	13	11	9	7
-15°	72	54	42	30	24	18	15	12	10	8	7
-16.25°	62	48	37	27	22	16	14	11	10	8	7
-17.5°	52	42	31	24	19	15	13	11	9	7	6
-18.75°	45	35	26	21	17	14	12	10	8	7	6
-20°	37	28	23	19	15	13	11	9	8	7	6
-21.25°	31	24	20	16	14	12	10	8	7	6	6

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	24	21	17	14	12	10	9	8	7	6	5
-23.75°	21	18	15	13	11	10	8	7	6	6	5
-25°	18	15	13	11	10	9	8	7	6	5	5
-26.25°	15	13	12	10	9	8	7	6	6	5	5
-27.5°	13	12	10	9	8	7	6	6	5	5	5
-28.75°	11	10	9	8	7	7	6	5	5	5	4
-30°	10	9	8	7	7	6	6	5	5	4	4
-31.25°	9	8	7	7	6	6	5	5	5	4	4
-32.5°	8	7	7	6	6	5	5	5	4	4	4
-33.75°	7	7	6	6	6	5	5	5	4	4	4
-35°	7	6	6	6	5	5	5	4	4	4	4
-36.25°	6	6	6	5	5	5	4	4	4	4	4
-37.5°	6	6	5	5	5	4	4	4	4	4	4
-38.75°	5	5	5	5	4	4	4	4	4	4	4
-40°	5	5	5	4	4	4	4	4	4	4	3
-41.25°	5	5	4	4	4	4	4	4	4	3	3
-42.5°	5	4	4	4	4	4	4	4	3	3	3
-43.75°	4	4	4	4	4	4	4	3	3	3	3
-45°	4	4	4	4	4	4	3	3	3	3	3
-46.25°	4	3	4	4	4	3	3	3	3	3	3
-47.5°	3	3	3	3	3	3	3	3	3	3	3
-48.75°	3	3	3	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	2
-51.25°	3	3	3	3	3	3	3	3	2	2	2
-52.5°	3	3	3	3	3	3	3	2	2	2	2
-53.75°	3	3	3	3	3	2	2	2	2	2	2
-55°	3	3	3	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	1
-60°	2	2	2	2	2	2	2	2	1	1	1
-61.25°	2	2	2	2	2	1	1	1	1	1	1
-62.5°	2	2	2	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	0	0



REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	1	1	1	1	1	0	0	0	0	0
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	1	1	1	1	1	1	1	1	1
55°	2	2	2	2	1	1	1	1	1	1	1
53.75°	2	2	2	2	2	2	1	1	1	1	1
52.5°	2	2	2	2	2	2	2	2	1	1	1
51.25°	2	2	2	2	2	2	2	2	2	1	1
50°	2	2	2	2	2	2	2	2	2	2	1
48.75°	2	2	2	2	2	2	2	2	2	2	2
47.5°	3	2	2	2	2	2	2	2	2	2	2
46.25°	3	3	2	2	2	2	2	2	2	2	2
45°	3	3	3	2	2	2	2	2	2	2	2
43.75°	3	3	3	2	2	2	2	2	2	2	2
42.5°	3	3	3	3	2	2	2	2	2	2	2
41.25°	3	3	3	3	3	2	2	2	2	2	2
40°	3	3	3	3	3	2	2	2	2	2	2
38.75°	3	3	3	3	3	3	2	2	2	2	2
37.5°	3	3	3	3	3	3	3	2	2	2	2
36.25°	4	3	3	3	3	3	3	2	2	2	2
35°	4	4	3	3	3	3	3	3	2	2	2

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	4	4	3	3	3	3	3	3	2	2	2
32.5°	4	4	4	3	4	3	3	3	3	2	2
31.25°	4	4	4	3	4	4	3	3	3	2	2
30°	4	4	4	4	4	4	3	3	3	2	2
28.75°	4	4	4	4	4	4	4	3	3	3	2
27.5°	4	4	4	4	4	4	4	3	3	3	2
26.25°	4	4	4	4	4	4	4	3	3	3	2
25°	5	4	4	4	4	4	4	4	3	3	3
23.75°	5	5	4	4	4	4	4	4	3	3	3
22.5°	5	5	5	4	4	4	4	4	3	3	3
21.25°	5	5	5	4	4	4	4	4	4	3	3
20°	5	5	5	5	4	4	4	4	4	3	3
18.75°	5	5	5	5	4	4	4	4	4	3	3
17.5°	6	5	5	5	4	4	4	4	4	3	3
16.25°	6	5	5	5	5	4	4	4	4	3	3
15°	6	6	5	5	5	4	4	4	4	4	3
13.75°	6	6	5	5	5	4	4	4	4	4	3
12.5°	7	6	5	5	5	4	4	4	4	4	3
11.25°	7	6	5	5	5	5	4	4	4	4	3
10°	7	6	6	5	5	5	4	4	4	4	3
8.75°	7	6	6	5	5	5	4	4	4	4	3
7.5°	7	7	6	5	5	5	4	4	4	4	3
6.25°	8	7	6	5	5	5	4	4	4	4	3
5°	8	7	6	6	5	5	4	4	4	4	3
3.75°	8	7	6	6	5	5	4	4	4	4	3
2.5°	8	7	6	6	5	5	4	4	4	4	3
1.25°	8	7	6	6	5	5	4	4	4	4	3
0°	8	7	6	6	5	5	4	4	4	4	4
-1.25°	8	7	6	6	5	5	4	4	4	4	3
-2.5°	8	7	6	6	5	5	4	4	4	4	3
-3.75°	8	7	6	6	5	5	4	4	4	4	3
-5°	8	7	6	6	5	5	4	4	4	4	3
-6.25°	8	7	6	5	5	5	4	4	4	4	3
-7.5°	7	7	6	5	5	5	4	4	4	4	3
-8.75°	7	6	6	5	5	5	4	4	4	4	3
-10°	7	6	6	5	5	5	4	4	4	4	3
-11.25°	7	6	5	5	5	5	4	4	4	4	3
-12.5°	7	6	5	5	5	4	4	4	4	4	3
-13.75°	6	6	5	5	5	4	4	4	4	4	3
-15°	6	6	5	5	5	4	4	4	4	4	3
-16.25°	6	5	5	5	5	4	4	4	4	3	3
-17.5°	6	5	5	5	4	4	4	4	4	3	3
-18.75°	5	5	5	5	4	4	4	4	4	3	3
-20°	5	5	5	5	4	4	4	4	4	3	3
-21.25°	5	5	5	4	4	4	4	4	4	3	3

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	5	5	5	4	4	4	4	4	3	3	3
-23.75°	5	5	4	4	4	4	4	4	3	3	3
-25°	5	4	4	4	4	4	4	4	3	3	3
-26.25°	4	4	4	4	4	4	4	3	3	3	2
-27.5°	4	4	4	4	4	4	4	3	3	3	2
-28.75°	4	4	4	4	4	4	4	3	3	3	2
-30°	4	4	4	4	4	4	3	3	3	2	2
-31.25°	4	4	4	3	4	4	3	3	3	2	2
-32.5°	4	4	4	3	4	3	3	3	3	2	2
-33.75°	4	4	3	3	3	3	3	3	2	2	2
-35°	4	4	3	3	3	3	3	3	2	2	2
-36.25°	4	3	3	3	3	3	3	2	2	2	2
-37.5°	3	3	3	3	3	3	3	2	2	2	2
-38.75°	3	3	3	3	3	3	2	2	2	2	2
-40°	3	3	3	3	3	2	2	2	2	2	2
-41.25°	3	3	3	3	3	2	2	2	2	2	2
-42.5°	3	3	3	3	2	2	2	2	2	2	2
-43.75°	3	3	3	2	2	2	2	2	2	2	2
-45°	3	3	3	2	2	2	2	2	2	2	2
-46.25°	3	3	2	2	2	2	2	2	2	2	2
-47.5°	3	2	2	2	2	2	2	2	2	2	2
-48.75°	2	2	2	2	2	2	2	2	2	2	2
-50°	2	2	2	2	2	2	2	2	2	2	1
-51.25°	2	2	2	2	2	2	2	2	2	1	1
-52.5°	2	2	2	2	2	2	2	2	1	1	1
-53.75°	2	2	2	2	2	2	1	1	1	1	1
-55°	2	2	2	2	1	1	1	1	1	1	1
-56.25°	2	2	1	1	1	1	1	1	1	1	1
-57.5°	2	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	1	1	0	0	0	0	0	0	0	0	0
73.75°	1	1	1	1	1	0	0	0	0	0	0
72.5°	1	1	1	1	1	1	0	0	0	0	0
71.25°	1	1	1	1	1	1	1	0	0	0	0
70°	1	1	1	1	1	1	1	1	0	0	0
68.75°	1	1	1	1	1	1	1	1	1	0	0
67.5°	1	1	1	1	1	1	1	1	1	1	0
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	2	1	1	1	1	1	1	1	1	1	1
45°	2	1	1	1	1	1	1	1	1	1	1
43.75°	2	2	1	1	1	1	1	1	1	1	1
42.5°	2	2	1	1	1	1	1	1	1	1	1
41.25°	2	2	2	1	1	1	1	1	1	1	1
40°	2	2	2	1	1	1	1	1	1	1	1
38.75°	2	2	2	2	1	1	1	1	1	1	1
37.5°	2	2	2	2	1	1	1	1	1	1	1
36.25°	2	2	2	2	1	1	1	1	1	1	1
35°	2	2	2	2	2	1	1	1	1	1	1

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	2	2	2	2	2	1	1	1	1	1	1
32.5°	2	2	2	2	2	1	1	1	1	1	1
31.25°	2	2	2	2	2	1	1	1	1	1	1
30°	2	2	2	2	2	2	1	1	1	1	1
28.75°	2	2	2	2	2	2	1	1	1	1	1
27.5°	2	2	2	2	2	2	1	1	1	1	1
26.25°	2	2	2	2	2	2	1	1	1	1	1
25°	2	2	2	2	2	2	2	1	1	1	1
23.75°	2	2	2	2	2	2	2	1	1	1	1
22.5°	2	2	2	2	2	2	2	1	1	1	1
21.25°	2	2	2	2	2	2	2	1	1	1	1
20°	2	2	2	2	2	2	2	1	1	1	1
18.75°	3	2	2	2	2	2	2	1	1	1	1
17.5°	3	2	2	2	2	2	2	1	1	1	1
16.25°	3	2	2	2	2	2	2	2	1	1	1
15°	3	2	2	2	2	2	2	2	1	1	1
13.75°	3	2	2	2	2	2	2	2	1	1	1
12.5°	3	2	2	2	2	2	2	2	1	1	1
11.25°	3	2	2	2	2	2	2	2	1	1	1
10°	3	3	2	2	2	2	2	2	1	1	1
8.75°	3	3	2	2	2	2	2	2	1	1	1
7.5°	3	3	2	2	2	2	2	2	1	1	1
6.25°	3	3	2	2	2	2	2	2	1	1	1
5°	3	3	2	2	2	2	2	2	1	1	1
3.75°	3	3	2	2	2	2	2	2	1	1	1
2.5°	3	3	2	2	2	2	2	2	1	1	1
1.25°	3	3	2	2	2	2	2	2	1	1	1
0°	3	3	2	2	2	2	2	2	1	1	1
-1.25°	3	3	2	2	2	2	2	2	1	1	1
-2.5°	3	3	2	2	2	2	2	2	1	1	1
-3.75°	3	3	2	2	2	2	2	2	1	1	1
-5°	3	3	2	2	2	2	2	2	1	1	1
-6.25°	3	3	2	2	2	2	2	2	1	1	1
-7.5°	3	3	2	2	2	2	2	2	1	1	1
-8.75°	3	3	2	2	2	2	2	2	1	1	1
-10°	3	3	2	2	2	2	2	2	1	1	1
-11.25°	3	2	2	2	2	2	2	2	1	1	1
-12.5°	3	2	2	2	2	2	2	2	1	1	1
-13.75°	3	2	2	2	2	2	2	2	1	1	1
-15°	3	2	2	2	2	2	2	2	1	1	1
-16.25°	3	2	2	2	2	2	2	2	1	1	1
-17.5°	3	2	2	2	2	2	2	1	1	1	1
-18.75°	3	2	2	2	2	2	2	1	1	1	1
-20°	2	2	2	2	2	2	2	1	1	1	1
-21.25°	2	2	2	2	2	2	2	1	1	1	1

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	2	2	2	2	2	2	1	1	1	1
-23.75°	2	2	2	2	2	2	2	1	1	1	1
-25°	2	2	2	2	2	2	2	1	1	1	1
-26.25°	2	2	2	2	2	2	1	1	1	1	1
-27.5°	2	2	2	2	2	2	1	1	1	1	1
-28.75°	2	2	2	2	2	2	1	1	1	1	1
-30°	2	2	2	2	2	2	1	1	1	1	1
-31.25°	2	2	2	2	2	1	1	1	1	1	1
-32.5°	2	2	2	2	2	1	1	1	1	1	1
-33.75°	2	2	2	2	2	1	1	1	1	1	1
-35°	2	2	2	2	2	1	1	1	1	1	1
-36.25°	2	2	2	2	1	1	1	1	1	1	1
-37.5°	2	2	2	2	1	1	1	1	1	1	1
-38.75°	2	2	2	2	1	1	1	1	1	1	1
-40°	2	2	2	1	1	1	1	1	1	1	1
-41.25°	2	2	2	1	1	1	1	1	1	1	1
-42.5°	2	2	1	1	1	1	1	1	1	1	1
-43.75°	2	2	1	1	1	1	1	1	1	1	1
-45°	2	1	1	1	1	1	1	1	1	1	1
-46.25°	2	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	0
-68.75°	1	1	1	1	1	1	1	1	1	0	0
-70°	1	1	1	1	1	1	1	1	0	0	0
-71.25°	1	1	1	1	1	1	1	0	0	0	0
-72.5°	1	1	1	1	1	1	0	0	0	0	0
-73.75°	1	1	1	1	1	0	0	0	0	0	0
-75°	1	1	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	1	0	0	0	0	0	0	0	0	0	0
62.5°	1	0	0	0	0	0	0	0	0	0	0
61.25°	1	1	0	0	0	0	0	0	0	0	0
60°	1	1	0	0	0	0	0	0	0	0	0
58.75°	1	1	1	0	0	0	0	0	0	0	0
57.5°	1	1	1	0	0	0	0	0	0	0	0
56.25°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	1	0	0	0	0	0	0	0
53.75°	1	1	1	1	0	0	0	0	0	0	0
52.5°	1	1	1	1	0	0	0	0	0	0	0
51.25°	1	1	1	1	0	0	0	0	0	0	0
50°	1	1	1	1	1	0	0	0	0	0	0
48.75°	1	1	1	1	1	0	0	0	0	0	0
47.5°	1	1	1	1	1	0	0	0	0	0	0
46.25°	1	1	1	1	1	0	0	0	0	0	0
45°	1	1	1	1	1	0	0	0	0	0	0
43.75°	1	1	1	1	1	0	0	0	0	0	0
42.5°	1	1	1	1	1	1	0	0	0	0	0
41.25°	1	1	1	1	1	1	0	0	0	0	0
40°	1	1	1	1	1	1	0	0	0	0	0
38.75°	1	1	1	1	1	1	0	0	0	0	0
37.5°	1	1	1	1	1	1	0	0	0	0	0
36.25°	1	1	1	1	1	1	0	0	0	0	0
35°	1	1	1	1	1	1	0	0	0	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	1	1	1	1	0	0	0	0	0
32.5°	1	1	1	1	1	1	0	0	0	0	0
31.25°	1	1	1	1	1	1	1	0	0	0	0
30°	1	1	1	1	1	1	1	0	0	0	0
28.75°	1	1	1	1	1	1	1	0	0	0	0
27.5°	1	1	1	1	1	1	1	0	0	0	0
26.25°	1	1	1	1	1	1	1	0	0	0	0
25°	1	1	1	1	1	1	1	0	0	0	0
23.75°	1	1	1	1	1	1	1	0	0	0	0
22.5°	1	1	1	1	1	1	1	0	0	0	0
21.25°	1	1	1	1	1	1	1	0	0	0	0
20°	1	1	1	1	1	1	1	0	0	0	0
18.75°	1	1	1	1	1	1	1	0	0	0	0
17.5°	1	1	1	1	1	1	1	0	0	0	0
16.25°	1	1	1	1	1	1	1	0	0	0	0
15°	1	1	1	1	1	1	1	0	0	0	0
13.75°	1	1	1	1	1	1	1	0	0	0	0
12.5°	1	1	1	1	1	1	1	0	0	0	0
11.25°	1	1	1	1	1	1	1	0	0	0	0
10°	1	1	1	1	1	1	1	0	0	0	0
8.75°	1	1	1	1	1	1	1	0	0	0	0
7.5°	1	1	1	1	1	1	1	0	0	0	0
6.25°	1	1	1	1	1	1	1	0	0	0	0
5°	1	1	1	1	1	1	1	0	0	0	0
3.75°	1	1	1	1	1	1	1	0	0	0	0
2.5°	1	1	1	1	1	1	1	0	0	0	0
1.25°	1	1	1	1	1	1	1	0	0	0	0
0°	1	1	1	1	1	1	1	0	0	0	0
-1.25°	1	1	1	1	1	1	1	0	0	0	0
-2.5°	1	1	1	1	1	1	1	0	0	0	0
-3.75°	1	1	1	1	1	1	1	0	0	0	0
-5°	1	1	1	1	1	1	1	0	0	0	0
-6.25°	1	1	1	1	1	1	1	0	0	0	0
-7.5°	1	1	1	1	1	1	1	0	0	0	0
-8.75°	1	1	1	1	1	1	1	0	0	0	0
-10°	1	1	1	1	1	1	1	0	0	0	0
-11.25°	1	1	1	1	1	1	1	0	0	0	0
-12.5°	1	1	1	1	1	1	1	0	0	0	0
-13.75°	1	1	1	1	1	1	1	0	0	0	0
-15°	1	1	1	1	1	1	1	0	0	0	0
-16.25°	1	1	1	1	1	1	1	0	0	0	0
-17.5°	1	1	1	1	1	1	1	0	0	0	0
-18.75°	1	1	1	1	1	1	1	0	0	0	0
-20°	1	1	1	1	1	1	1	0	0	0	0
-21.25°	1	1	1	1	1	1	1	0	0	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	1	1	1	1	0	0	0	0
-23.75°	1	1	1	1	1	1	1	0	0	0	0
-25°	1	1	1	1	1	1	1	0	0	0	0
-26.25°	1	1	1	1	1	1	1	0	0	0	0
-27.5°	1	1	1	1	1	1	1	0	0	0	0
-28.75°	1	1	1	1	1	1	1	0	0	0	0
-30°	1	1	1	1	1	1	1	0	0	0	0
-31.25°	1	1	1	1	1	1	1	0	0	0	0
-32.5°	1	1	1	1	1	1	0	0	0	0	0
-33.75°	1	1	1	1	1	1	0	0	0	0	0
-35°	1	1	1	1	1	1	0	0	0	0	0
-36.25°	1	1	1	1	1	1	0	0	0	0	0
-37.5°	1	1	1	1	1	1	0	0	0	0	0
-38.75°	1	1	1	1	1	1	0	0	0	0	0
-40°	1	1	1	1	1	1	0	0	0	0	0
-41.25°	1	1	1	1	1	1	0	0	0	0	0
-42.5°	1	1	1	1	1	1	0	0	0	0	0
-43.75°	1	1	1	1	1	0	0	0	0	0	0
-45°	1	1	1	1	1	0	0	0	0	0	0
-46.25°	1	1	1	1	1	0	0	0	0	0	0
-47.5°	1	1	1	1	1	0	0	0	0	0	0
-48.75°	1	1	1	1	1	0	0	0	0	0	0
-50°	1	1	1	1	1	0	0	0	0	0	0
-51.25°	1	1	1	1	0	0	0	0	0	0	0
-52.5°	1	1	1	1	0	0	0	0	0	0	0
-53.75°	1	1	1	1	0	0	0	0	0	0	0
-55°	1	1	1	1	0	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	1	1	0	0	0	0	0	0	0	0
-58.75°	1	1	1	0	0	0	0	0	0	0	0
-60°	1	1	0	0	0	0	0	0	0	0	0
-61.25°	1	1	0	0	0	0	0	0	0	0	0
-62.5°	1	0	0	0	0	0	0	0	0	0	0
-63.75°	1	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0

REPORT NUMBER: P246990 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)