

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220507

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220507
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29472)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-BK-L1-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS, SPOT OPTIC, BLACK HOUSING.
Light Source: (1) 3000K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 581.1 lumens
Efficiency: N/A
Efficacy: 59.3 lumens/watt
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220507

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220507

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105		104	103	102		100	100	99	97
2	112	109	106	104	110	107	105	102	104	102	100		101	100	98		99	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96		99	97	95		97	95	94	92
4	106	101	98	95	105	100	97	94	98	95	93		96	94	92		95	93	91	90
5	103	98	94	92	102	97	94	91	96	93	91		94	92	90		93	91	89	88
6	101	95	92	89	100	95	91	89	93	90	88		92	90	88		91	89	87	86
7	99	93	89	87	98	92	89	86	91	88	86		90	88	86		89	87	85	84
8	96	91	87	84	95	90	87	84	89	86	84		88	86	84		88	85	83	82
9	94	88	85	82	94	88	85	82	87	84	82		87	84	82		86	84	82	81
10	92	87	83	81	92	86	83	81	86	83	80		85	82	80		84	82	80	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1092281
5°	836802
10°	351051
15°	148151
20°	96375
25°	42220
30°	5722
35°	2142
40°	1546
45°	1178
50°	1058
55°	1032
60°	833
65°	571
70°	256
75°	0
80°	0
85°	0



TEST NUMBER: P220507

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.2	49.2
10°-20°	199.6	34.3
20°-30°	82.3	14.2
30°-40°	6.5	1.1
40°-50°	3.1	0.5
50°-60°	2.3	0.4
60°-70°	1.1	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	568.0	97.7
0°-40°	574.5	98.9
0°-60°	579.8	99.8
0°-90°	581.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	581.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4981	
5°	3802	286
15°	653	200
25°	174	82
35°	8	6
45°	4	3
55°	3	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220507

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	4981.2
1°	4917.7
2°	4768.8
3°	4526.5
4°	4203.1
5°	3801.6
6°	3354.9
7°	2886.8
8°	2405.3
9°	1963.9
10°	1576.6
11°	1270.0
12°	1043.0
13°	875.8
14°	753.7
15°	652.6
16°	571.1
17°	517.9
18°	476.9
19°	440.9
20°	413.0
21°	387.4
22°	348.3
23°	295.1
24°	234.6
25°	174.5
26°	121.3
27°	72.7
28°	40.6
29°	27.2
30°	22.6
32.5°	14.5
35°	8.0
37.5°	6.1
40°	5.4
42.5°	4.6
45°	3.8
47.5°	3.4
50°	3.1
52.5°	2.7
55°	2.7
57.5°	2.3
60°	1.9
62.5°	1.5
65°	1.1



TEST NUMBER: P220507

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.8
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)