

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED3036-12-CS-OSL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-47)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED3036-12-CS-OSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD SILVER, OVERALL SPREAD LENS
Light Source: (1) SORAA 3000K 90 CRI LED
SM16-07-36D-930-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004


Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	308.9 lumens	Max Intensity:	806.7 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	40.6 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	35.4°H x 35.4°V	Field Angle (10%):	57.9°H x 57.9°V
Beam Lumens:	176.5 lumens	Field Lumens:	279.6 lumens
Beam Efficiency:	57.1%	Field Efficiency:	90.5%
Input Watts (W):	7.6		
Input Voltage (V):	NR		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

Iso-Candela Plot



REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

Lumen Table


90																
80	0.0	0.0		0.0		0.0		0.0		0.0		0.0		0.0		0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.1	0.1	0.1	0.0	0.0	0.0	0.0
40		0.0	0.0	0.1	0.1	0.2	0.5	0.7	0.7	0.5	0.2	0.1	0.1	0.0	0.0	
30	0.0	0.0	0.0	0.1	0.2	0.7	2.6	4.8	4.8	2.6	0.7	0.2	0.1	0.0	0.0	0.0
20		0.0	0.0	0.1	0.4	2.5	8.3	13.9	13.9	8.3	2.5	0.4	0.1	0.0	0.0	
10	0.0	0.0	0.1	0.1	0.6	4.5	13.5	21.7	21.7	13.5	4.5	0.6	0.1	0.1	0.0	0.0
0		0.0	0.1	0.1	0.6	4.5	13.5	21.7	21.7	13.5	4.5	0.6	0.1	0.1	0.0	
-10	0.0	0.0	0.0	0.1	0.4	2.5	8.3	13.9	13.9	8.3	2.5	0.4	0.1	0.0	0.0	0.0
-20		0.0	0.0	0.1	0.2	0.7	2.6	4.8	4.8	2.6	0.7	0.2	0.1	0.0	0.0	
-30	0.0	0.0	0.0	0.1	0.1	0.2	0.5	0.7	0.7	0.5	0.2	0.1	0.1	0.0	0.0	0.0
-40		0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.1	0.1	0.1	0.0	0.0	0.0	
-50	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
-70																
-80	0.0	0.0		0.0		0.0		0.0		0.0		0.0		0.0		0.0
-90																

Horizontal Angle (degrees)

Vertical Angle (degrees)


REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

Luminous Intensity Polar Plot



REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

Luminous Intensity Plot



Beam:
H Angle: 35.4°
V Angle: 35.4°
Lumens: 176.5
Efficiency: 57.1%

Field:
H Angle: 57.9°
V Angle: 57.9°
Lumens: 279.6
Efficiency: 90.5%

Spill:
Lumens: 29.3
Efficiency: 9.5%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 0-Deg

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

FIELD
BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	1
22.5°	0	0	0	0	0	0	0	0	0	0	1
21.25°	0	0	0	0	0	0	0	0	0	0	1
20°	0	0	0	0	0	0	0	0	0	0	1
18.75°	0	0	0	0	0	0	0	0	0	0	1
17.5°	0	0	0	0	0	0	0	0	0	0	1
16.25°	0	0	0	0	0	0	0	0	0	0	1
15°	0	0	0	0	0	0	0	0	0	0	1
13.75°	0	0	0	0	0	0	0	0	0	0	1
12.5°	0	0	0	0	0	0	0	0	0	0	1
11.25°	0	0	0	0	0	0	0	0	0	0	1
10°	0	0	0	0	0	0	0	0	0	0	1
8.75°	0	0	0	0	0	0	0	0	0	0	1
7.5°	0	0	0	0	0	0	0	0	0	0	1
6.25°	0	0	0	0	0	0	0	0	0	0	1
5°	0	0	0	0	0	0	0	0	0	0	1
3.75°	0	0	0	0	0	0	0	0	0	0	1
2.5°	0	0	0	0	0	0	0	0	0	0	1
1.25°	0	0	0	0	0	0	0	0	0	0	1
0°	0	0	0	0	0	0	0	0	0	0	1
-1.25°	0	0	0	0	0	0	0	0	0	0	1
-2.5°	0	0	0	0	0	0	0	0	0	0	1
-3.75°	0	0	0	0	0	0	0	0	0	0	1
-5°	0	0	0	0	0	0	0	0	0	0	1
-6.25°	0	0	0	0	0	0	0	0	0	0	1
-7.5°	0	0	0	0	0	0	0	0	0	0	1
-8.75°	0	0	0	0	0	0	0	0	0	0	1
-10°	0	0	0	0	0	0	0	0	0	0	1
-11.25°	0	0	0	0	0	0	0	0	0	0	1
-12.5°	0	0	0	0	0	0	0	0	0	0	1
-13.75°	0	0	0	0	0	0	0	0	0	0	1
-15°	0	0	0	0	0	0	0	0	0	0	1
-16.25°	0	0	0	0	0	0	0	0	0	0	1
-17.5°	0	0	0	0	0	0	0	0	0	0	1
-18.75°	0	0	0	0	0	0	0	0	0	0	1
-20°	0	0	0	0	0	0	0	0	0	0	1
-21.25°	0	0	0	0	0	0	0	0	0	0	1

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	1
-23.75°	0	0	0	0	0	0	0	0	0	0	1
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	1
61.25°	0	0	0	0	0	0	0	0	0	1	1
60°	0	0	0	0	0	0	0	0	1	1	1
58.75°	0	0	0	0	0	0	0	1	1	1	1
57.5°	0	0	0	0	0	0	0	1	1	1	1
56.25°	0	0	0	0	0	0	1	1	1	1	1
55°	0	0	0	0	0	0	1	1	1	1	1
53.75°	0	0	0	0	0	1	1	1	1	1	1
52.5°	0	0	0	0	0	1	1	1	1	1	1
51.25°	0	0	0	0	1	1	1	1	1	1	1
50°	0	0	0	0	1	1	1	1	1	1	1
48.75°	0	0	0	1	1	1	1	1	1	1	1
47.5°	0	0	0	1	1	1	1	1	1	1	1
46.25°	0	0	0	1	1	1	1	1	1	1	1
45°	0	0	1	1	1	1	1	1	1	1	1
43.75°	0	0	1	1	1	1	1	1	1	1	1
42.5°	0	0	1	1	1	1	1	1	1	1	1
41.25°	0	0	1	1	1	1	1	1	1	1	1
40°	0	1	1	1	1	1	1	1	1	1	1
38.75°	0	1	1	1	1	1	1	1	1	1	1
37.5°	0	1	1	1	1	1	1	1	1	1	1
36.25°	0	1	1	1	1	1	1	1	1	1	1
35°	0	1	1	1	1	1	1	1	1	1	1

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	1	1	1	1	1	1	1
32.5°	1	1	1	1	1	1	1	1	1	1	1
31.25°	1	1	1	1	1	1	1	1	1	1	1
30°	1	1	1	1	1	1	1	1	1	1	1
28.75°	1	1	1	1	1	1	1	1	1	1	1
27.5°	1	1	1	1	1	1	1	1	1	1	1
26.25°	1	1	1	1	1	1	1	1	1	1	1
25°	1	1	1	1	1	1	1	1	1	1	1
23.75°	1	1	1	1	1	1	1	1	1	1	1
22.5°	1	1	1	1	1	1	1	1	1	1	1
21.25°	1	1	1	1	1	1	1	1	1	1	2
20°	1	1	1	1	1	1	1	1	1	1	2
18.75°	1	1	1	1	1	1	1	1	1	1	2
17.5°	1	1	1	1	1	1	1	1	1	1	2
16.25°	1	1	1	1	1	1	1	1	1	1	2
15°	1	1	1	1	1	1	1	1	1	1	2
13.75°	1	1	1	1	1	1	1	1	1	2	2
12.5°	1	1	1	1	1	1	1	1	1	2	2
11.25°	1	1	1	1	1	1	1	1	1	2	2
10°	1	1	1	1	1	1	1	1	1	2	2
8.75°	1	1	1	1	1	1	1	1	1	2	2
7.5°	1	1	1	1	1	1	1	1	1	2	2
6.25°	1	1	1	1	1	1	1	1	1	2	2
5°	1	1	1	1	1	1	1	1	1	2	2
3.75°	1	1	1	1	1	1	1	1	1	2	2
2.5°	1	1	1	1	1	1	1	1	1	2	2
1.25°	1	1	1	1	1	1	1	1	1	2	2
0°	1	1	1	1	1	1	1	1	1	2	2
-1.25°	1	1	1	1	1	1	1	1	1	2	2
-2.5°	1	1	1	1	1	1	1	1	1	2	2
-3.75°	1	1	1	1	1	1	1	1	1	2	2
-5°	1	1	1	1	1	1	1	1	1	2	2
-6.25°	1	1	1	1	1	1	1	1	1	2	2
-7.5°	1	1	1	1	1	1	1	1	1	2	2
-8.75°	1	1	1	1	1	1	1	1	1	2	2
-10°	1	1	1	1	1	1	1	1	1	2	2
-11.25°	1	1	1	1	1	1	1	1	1	2	2
-12.5°	1	1	1	1	1	1	1	1	1	2	2
-13.75°	1	1	1	1	1	1	1	1	1	2	2
-15°	1	1	1	1	1	1	1	1	1	1	2
-16.25°	1	1	1	1	1	1	1	1	1	1	2
-17.5°	1	1	1	1	1	1	1	1	1	1	2
-18.75°	1	1	1	1	1	1	1	1	1	1	2
-20°	1	1	1	1	1	1	1	1	1	1	2
-21.25°	1	1	1	1	1	1	1	1	1	1	2

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	1	1	1	1	1	1	1	1	1
-23.75°	1	1	1	1	1	1	1	1	1	1	1
-25°	1	1	1	1	1	1	1	1	1	1	1
-26.25°	1	1	1	1	1	1	1	1	1	1	1
-27.5°	1	1	1	1	1	1	1	1	1	1	1
-28.75°	1	1	1	1	1	1	1	1	1	1	1
-30°	1	1	1	1	1	1	1	1	1	1	1
-31.25°	1	1	1	1	1	1	1	1	1	1	1
-32.5°	1	1	1	1	1	1	1	1	1	1	1
-33.75°	1	1	1	1	1	1	1	1	1	1	1
-35°	0	1	1	1	1	1	1	1	1	1	1
-36.25°	0	1	1	1	1	1	1	1	1	1	1
-37.5°	0	1	1	1	1	1	1	1	1	1	1
-38.75°	0	1	1	1	1	1	1	1	1	1	1
-40°	0	1	1	1	1	1	1	1	1	1	1
-41.25°	0	0	1	1	1	1	1	1	1	1	1
-42.5°	0	0	1	1	1	1	1	1	1	1	1
-43.75°	0	0	1	1	1	1	1	1	1	1	1
-45°	0	0	1	1	1	1	1	1	1	1	1
-46.25°	0	0	0	1	1	1	1	1	1	1	1
-47.5°	0	0	0	1	1	1	1	1	1	1	1
-48.75°	0	0	0	1	1	1	1	1	1	1	1
-50°	0	0	0	0	1	1	1	1	1	1	1
-51.25°	0	0	0	0	1	1	1	1	1	1	1
-52.5°	0	0	0	0	0	1	1	1	1	1	1
-53.75°	0	0	0	0	0	1	1	1	1	1	1
-55°	0	0	0	0	0	0	1	1	1	1	1
-56.25°	0	0	0	0	0	0	1	1	1	1	1
-57.5°	0	0	0	0	0	0	0	1	1	1	1
-58.75°	0	0	0	0	0	0	0	1	1	1	1
-60°	0	0	0	0	0	0	0	0	1	1	1
-61.25°	0	0	0	0	0	0	0	0	0	1	1
-62.5°	0	0	0	0	0	0	0	0	0	0	1
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	1	1
70°	0	0	0	0	0	0	0	1	1	1	1
68.75°	0	0	0	0	0	1	1	1	1	1	1
67.5°	0	0	0	1	1	1	1	1	1	1	1
66.25°	0	0	1	1	1	1	1	1	1	1	1
65°	0	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	2
48.75°	1	1	1	1	1	1	1	1	1	2	2
47.5°	1	1	1	1	1	1	1	1	2	2	2
46.25°	1	1	1	1	1	1	1	1	2	2	2
45°	1	1	1	1	1	1	1	2	2	2	2
43.75°	1	1	1	1	1	1	2	2	2	2	2
42.5°	1	1	1	1	1	2	2	2	2	2	2
41.25°	1	1	1	1	1	2	2	2	2	2	2
40°	1	1	1	1	2	2	2	2	2	2	2
38.75°	1	1	1	1	2	2	2	2	2	2	2
37.5°	1	1	1	2	2	2	2	2	2	2	2
36.25°	1	1	1	2	2	2	2	2	2	2	2
35°	1	1	2	2	2	2	2	2	2	2	2

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	2	2	2	2	2	2	2	2	3
32.5°	1	1	2	2	2	2	2	2	2	2	3
31.25°	1	2	2	2	2	2	2	2	2	3	3
30°	1	2	2	2	2	2	2	2	2	3	3
28.75°	1	2	2	2	2	2	2	2	3	3	3
27.5°	2	2	2	2	2	2	2	2	3	3	3
26.25°	2	2	2	2	2	2	2	3	3	3	3
25°	2	2	2	2	2	2	2	3	3	3	3
23.75°	2	2	2	2	2	2	2	3	3	3	3
22.5°	2	2	2	2	2	2	3	3	3	3	3
21.25°	2	2	2	2	2	2	3	3	3	3	3
20°	2	2	2	2	2	2	3	3	3	3	3
18.75°	2	2	2	2	2	2	3	3	3	3	3
17.5°	2	2	2	2	2	3	3	3	3	3	4
16.25°	2	2	2	2	2	3	3	3	3	3	4
15°	2	2	2	2	2	3	3	3	3	3	4
13.75°	2	2	2	2	2	3	3	3	3	3	4
12.5°	2	2	2	2	2	3	3	3	3	4	4
11.25°	2	2	2	2	2	3	3	3	3	4	4
10°	2	2	2	2	3	3	3	3	3	4	4
8.75°	2	2	2	2	3	3	3	3	3	4	4
7.5°	2	2	2	2	3	3	3	3	3	4	4
6.25°	2	2	2	2	3	3	3	3	3	4	4
5°	2	2	2	2	3	3	3	3	3	4	4
3.75°	2	2	2	2	3	3	3	3	3	4	4
2.5°	2	2	2	2	3	3	3	3	3	4	4
1.25°	2	2	2	2	3	3	3	3	3	4	4
0°	2	2	2	2	3	3	3	3	4	4	4
-1.25°	2	2	2	2	3	3	3	3	3	4	4
-2.5°	2	2	2	2	3	3	3	3	3	4	4
-3.75°	2	2	2	2	3	3	3	3	3	4	4
-5°	2	2	2	2	3	3	3	3	3	4	4
-6.25°	2	2	2	2	3	3	3	3	3	4	4
-7.5°	2	2	2	2	3	3	3	3	3	4	4
-8.75°	2	2	2	2	3	3	3	3	3	4	4
-10°	2	2	2	2	3	3	3	3	3	4	4
-11.25°	2	2	2	2	2	3	3	3	3	4	4
-12.5°	2	2	2	2	2	3	3	3	3	4	4
-13.75°	2	2	2	2	2	3	3	3	3	3	4
-15°	2	2	2	2	2	3	3	3	3	3	4
-16.25°	2	2	2	2	2	3	3	3	3	3	4
-17.5°	2	2	2	2	2	3	3	3	3	3	4
-18.75°	2	2	2	2	2	2	3	3	3	3	3
-20°	2	2	2	2	2	2	3	3	3	3	3
-21.25°	2	2	2	2	2	2	3	3	3	3	3

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	2	2	2	2	2	3	3	3	3	3
-23.75°	2	2	2	2	2	2	2	3	3	3	3
-25°	2	2	2	2	2	2	2	3	3	3	3
-26.25°	2	2	2	2	2	2	2	3	3	3	3
-27.5°	2	2	2	2	2	2	2	2	3	3	3
-28.75°	1	2	2	2	2	2	2	2	3	3	3
-30°	1	2	2	2	2	2	2	2	2	3	3
-31.25°	1	2	2	2	2	2	2	2	2	3	3
-32.5°	1	1	2	2	2	2	2	2	2	2	3
-33.75°	1	1	2	2	2	2	2	2	2	2	3
-35°	1	1	2	2	2	2	2	2	2	2	2
-36.25°	1	1	1	2	2	2	2	2	2	2	2
-37.5°	1	1	1	2	2	2	2	2	2	2	2
-38.75°	1	1	1	1	2	2	2	2	2	2	2
-40°	1	1	1	1	2	2	2	2	2	2	2
-41.25°	1	1	1	1	1	2	2	2	2	2	2
-42.5°	1	1	1	1	1	2	2	2	2	2	2
-43.75°	1	1	1	1	1	1	2	2	2	2	2
-45°	1	1	1	1	1	1	1	2	2	2	2
-46.25°	1	1	1	1	1	1	1	1	2	2	2
-47.5°	1	1	1	1	1	1	1	1	2	2	2
-48.75°	1	1	1	1	1	1	1	1	1	2	2
-50°	1	1	1	1	1	1	1	1	1	1	2
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	0	1	1	1	1	1	1	1	1	1	1
-66.25°	0	0	1	1	1	1	1	1	1	1	1
-67.5°	0	0	0	1	1	1	1	1	1	1	1
-68.75°	0	0	0	0	0	1	1	1	1	1	1
-70°	0	0	0	0	0	0	0	1	1	1	1
-71.25°	0	0	0	0	0	0	0	0	0	1	1
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	1	1	1	1
73.75°	0	0	0	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	2	2
57.5°	1	1	1	1	1	1	1	2	2	2	2
56.25°	1	1	1	1	1	2	2	2	2	2	2
55°	1	1	1	1	2	2	2	2	2	2	2
53.75°	1	1	1	2	2	2	2	2	2	2	2
52.5°	1	2	2	2	2	2	2	2	2	2	2
51.25°	2	2	2	2	2	2	2	2	2	2	2
50°	2	2	2	2	2	2	2	2	2	2	2
48.75°	2	2	2	2	2	2	2	2	2	2	3
47.5°	2	2	2	2	2	2	2	2	2	3	3
46.25°	2	2	2	2	2	2	2	3	3	3	3
45°	2	2	2	2	2	2	3	3	3	3	3
43.75°	2	2	2	2	2	3	3	3	3	3	3
42.5°	2	2	2	2	3	3	3	3	3	3	3
41.25°	2	2	2	3	3	3	3	3	3	3	3
40°	2	2	3	3	3	3	3	3	3	3	4
38.75°	2	2	3	3	3	3	3	3	3	4	4
37.5°	2	3	3	3	3	3	3	3	4	4	4
36.25°	3	3	3	3	3	3	3	4	4	4	4
35°	3	3	3	3	3	3	4	4	4	4	4

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	3	3	3	3	3	4	4	4	4	4	4
32.5°	3	3	3	3	4	4	4	4	4	4	5
31.25°	3	3	3	3	4	4	4	4	4	4	5
30°	3	3	3	4	4	4	4	4	4	5	5
28.75°	3	3	3	4	4	4	4	4	5	5	5
27.5°	3	3	4	4	4	4	4	5	5	5	6
26.25°	3	3	4	4	4	4	4	5	5	6	6
25°	3	4	4	4	4	4	5	5	5	6	7
23.75°	3	4	4	4	4	4	5	5	6	6	7
22.5°	4	4	4	4	4	5	5	5	6	7	8
21.25°	4	4	4	4	4	5	5	6	6	7	8
20°	4	4	4	4	4	5	5	6	7	8	9
18.75°	4	4	4	4	5	5	6	6	7	8	10
17.5°	4	4	4	4	5	5	6	7	8	9	10
16.25°	4	4	4	4	5	5	6	7	8	9	11
15°	4	4	4	5	5	6	6	7	9	10	11
13.75°	4	4	4	5	5	6	7	8	9	10	12
12.5°	4	4	4	5	5	6	7	8	9	11	13
11.25°	4	4	4	5	5	6	7	8	10	11	13
10°	4	4	5	5	6	6	7	9	10	12	14
8.75°	4	4	5	5	6	7	8	9	10	12	14
7.5°	4	4	5	5	6	7	8	9	11	12	15
6.25°	4	4	5	5	6	7	8	9	11	13	16
5°	4	4	5	5	6	7	8	10	11	13	16
3.75°	4	4	5	5	6	7	8	10	11	13	17
2.5°	4	4	5	5	6	7	8	10	11	13	17
1.25°	4	4	5	5	6	7	8	10	12	13	17
0°	4	4	5	5	6	7	8	10	12	13	17
-1.25°	4	4	5	5	6	7	8	10	12	13	17
-2.5°	4	4	5	5	6	7	8	10	11	13	17
-3.75°	4	4	5	5	6	7	8	10	11	13	17
-5°	4	4	5	5	6	7	8	10	11	13	16
-6.25°	4	4	5	5	6	7	8	9	11	13	16
-7.5°	4	4	5	5	6	7	8	9	11	12	15
-8.75°	4	4	5	5	6	7	8	9	10	12	14
-10°	4	4	5	5	6	6	7	9	10	12	14
-11.25°	4	4	4	5	5	6	7	8	10	11	13
-12.5°	4	4	4	5	5	6	7	8	9	11	13
-13.75°	4	4	4	5	5	6	7	8	9	10	12
-15°	4	4	4	5	5	6	6	7	9	10	11
-16.25°	4	4	4	4	5	5	6	7	8	9	11
-17.5°	4	4	4	4	5	5	6	7	8	9	10
-18.75°	4	4	4	4	5	5	6	6	7	8	10
-20°	4	4	4	4	4	5	5	6	7	8	9
-21.25°	4	4	4	4	4	5	5	6	6	7	8

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	4	4	4	4	4	5	5	5	6	7	8
-23.75°	3	4	4	4	4	4	5	5	6	6	7
-25°	3	4	4	4	4	4	5	5	5	6	7
-26.25°	3	3	4	4	4	4	4	5	5	6	6
-27.5°	3	3	4	4	4	4	4	5	5	5	6
-28.75°	3	3	3	4	4	4	4	4	5	5	5
-30°	3	3	3	4	4	4	4	4	4	5	5
-31.25°	3	3	3	3	4	4	4	4	4	4	5
-32.5°	3	3	3	3	4	4	4	4	4	4	5
-33.75°	3	3	3	3	3	4	4	4	4	4	4
-35°	3	3	3	3	3	3	4	4	4	4	4
-36.25°	3	3	3	3	3	3	3	4	4	4	4
-37.5°	2	3	3	3	3	3	3	3	4	4	4
-38.75°	2	2	3	3	3	3	3	3	3	4	4
-40°	2	2	3	3	3	3	3	3	3	3	4
-41.25°	2	2	2	3	3	3	3	3	3	3	3
-42.5°	2	2	2	2	3	3	3	3	3	3	3
-43.75°	2	2	2	2	2	3	3	3	3	3	3
-45°	2	2	2	2	2	2	3	3	3	3	3
-46.25°	2	2	2	2	2	2	2	3	3	3	3
-47.5°	2	2	2	2	2	2	2	2	2	3	3
-48.75°	2	2	2	2	2	2	2	2	2	2	3
-50°	2	2	2	2	2	2	2	2	2	2	2
-51.25°	2	2	2	2	2	2	2	2	2	2	2
-52.5°	1	2	2	2	2	2	2	2	2	2	2
-53.75°	1	1	1	2	2	2	2	2	2	2	2
-55°	1	1	1	1	2	2	2	2	2	2	2
-56.25°	1	1	1	1	1	2	2	2	2	2	2
-57.5°	1	1	1	1	1	1	1	2	2	2	2
-58.75°	1	1	1	1	1	1	1	1	1	2	2
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	1	1	1	1	1	1	1	1
-75°	0	0	0	0	0	0	0	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	1	1
76.25°	0	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	2	2	2	2	2
61.25°	1	1	1	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	3
53.75°	2	2	2	2	2	2	2	3	3	3	3
52.5°	2	2	2	2	2	3	3	3	3	3	3
51.25°	2	2	2	3	3	3	3	3	3	3	3
50°	2	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	4
47.5°	3	3	3	3	3	3	3	3	4	4	4
46.25°	3	3	3	3	3	3	4	4	4	4	4
45°	3	3	3	3	4	4	4	4	4	4	4
43.75°	3	3	4	4	4	4	4	4	4	4	4
42.5°	3	4	4	4	4	4	4	4	4	4	5
41.25°	4	4	4	4	4	4	4	4	5	5	5
40°	4	4	4	4	4	4	5	5	5	5	5
38.75°	4	4	4	4	4	5	5	5	5	6	6
37.5°	4	4	4	4	5	5	5	6	6	6	7
36.25°	4	4	5	5	5	5	6	6	7	7	8
35°	4	5	5	5	5	6	6	7	8	8	9

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	5	5	5	6	6	7	7	8	9	9	10
32.5°	5	5	6	6	7	7	8	9	10	11	11
31.25°	5	6	6	7	7	8	9	10	11	12	13
30°	5	6	7	7	8	9	10	11	12	13	15
28.75°	6	7	7	8	9	10	11	12	14	16	18
27.5°	6	7	8	9	10	11	12	14	17	19	21
26.25°	7	8	9	10	11	12	14	17	19	22	26
25°	8	9	10	11	12	14	17	19	22	27	31
23.75°	8	9	11	12	13	16	19	22	27	31	37
22.5°	9	10	11	13	15	18	21	26	31	37	47
21.25°	10	11	12	14	18	21	25	30	36	46	57
20°	10	12	13	16	20	24	29	34	45	55	67
18.75°	11	13	15	18	22	27	33	42	53	64	79
17.5°	12	13	17	20	25	31	38	49	61	76	94
16.25°	12	15	18	22	28	34	45	56	70	88	109
15°	13	16	20	25	31	39	51	63	81	101	124
13.75°	14	18	21	27	33	45	57	72	92	115	139
12.5°	15	19	24	30	37	50	63	81	103	127	153
11.25°	16	20	26	32	42	55	70	91	114	139	166
10°	17	21	27	34	46	60	77	99	124	151	180
8.75°	18	23	29	37	50	64	84	108	134	161	192
7.5°	19	24	31	40	53	69	90	115	142	171	203
6.25°	20	25	32	42	56	73	96	121	149	180	213
5°	20	26	33	45	59	77	100	127	156	187	222
3.75°	21	27	34	46	61	79	104	131	160	193	229
2.5°	21	28	34	48	62	82	107	134	164	197	234
1.25°	21	28	34	48	63	83	108	136	166	200	237
0°	21	28	35	49	63	84	109	137	167	201	238
-1.25°	21	28	34	48	63	83	108	136	166	200	237
-2.5°	21	28	34	48	62	82	107	134	164	197	234
-3.75°	21	27	34	46	61	79	104	131	160	193	229
-5°	20	26	33	45	59	77	100	127	156	187	222
-6.25°	20	25	32	42	56	73	96	121	149	180	213
-7.5°	19	24	31	40	53	69	90	115	142	171	203
-8.75°	18	23	29	37	50	64	84	108	134	161	192
-10°	17	21	27	34	46	60	77	99	124	151	180
-11.25°	16	20	26	32	42	55	70	91	114	139	166
-12.5°	15	19	24	30	37	50	63	81	103	127	153
-13.75°	14	18	21	27	33	45	57	72	92	115	139
-15°	13	16	20	25	31	39	51	63	81	101	124
-16.25°	12	15	18	22	28	34	45	56	70	88	109
-17.5°	12	13	17	20	25	31	38	49	61	76	94
-18.75°	11	13	15	18	22	27	33	42	53	64	79
-20°	10	12	13	16	20	24	29	34	45	55	67
-21.25°	10	11	12	14	18	21	25	30	36	46	57

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	9	10	11	13	15	18	21	26	31	37	47
-23.75°	8	9	11	12	13	16	19	22	27	31	37
-25°	8	9	10	11	12	14	17	19	22	27	31
-26.25°	7	8	9	10	11	12	14	17	19	22	26
-27.5°	6	7	8	9	10	11	12	14	17	19	21
-28.75°	6	7	7	8	9	10	11	12	14	16	18
-30°	5	6	7	7	8	9	10	11	12	13	15
-31.25°	5	6	6	7	7	8	9	10	11	12	13
-32.5°	5	5	6	6	7	7	8	9	10	11	11
-33.75°	5	5	5	6	6	7	7	8	9	9	10
-35°	4	5	5	5	5	6	6	7	8	8	9
-36.25°	4	4	5	5	5	5	6	6	7	7	8
-37.5°	4	4	4	4	5	5	5	6	6	6	7
-38.75°	4	4	4	4	4	5	5	5	5	6	6
-40°	4	4	4	4	4	4	5	5	5	5	5
-41.25°	4	4	4	4	4	4	4	4	5	5	5
-42.5°	3	4	4	4	4	4	4	4	4	4	5
-43.75°	3	3	4	4	4	4	4	4	4	4	4
-45°	3	3	3	3	4	4	4	4	4	4	4
-46.25°	3	3	3	3	3	3	4	4	4	4	4
-47.5°	3	3	3	3	3	3	3	3	4	4	4
-48.75°	3	3	3	3	3	3	3	3	3	3	4
-50°	2	3	3	3	3	3	3	3	3	3	3
-51.25°	2	2	2	3	3	3	3	3	3	3	3
-52.5°	2	2	2	2	2	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	2	3	3	3	3
-55°	2	2	2	2	2	2	2	2	2	2	3
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	1	1	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	1	2	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	0	0	0	0	0	1	1

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	3	3
56.25°	2	2	2	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	4	4	4	4
50°	3	3	3	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	5	5
45°	4	4	4	4	4	5	5	5	5	5	5
43.75°	4	4	5	5	5	5	5	5	5	6	6
42.5°	5	5	5	5	5	6	6	6	6	6	7
41.25°	5	5	6	6	6	6	7	7	7	7	8
40°	6	6	6	7	7	7	8	8	8	9	9
38.75°	6	7	7	8	8	9	9	9	10	10	10
37.5°	7	8	8	9	9	10	10	11	11	12	12
36.25°	8	9	10	10	11	11	12	13	13	14	14
35°	10	10	11	12	12	13	14	15	16	17	18

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	11	12	13	13	15	16	18	19	20	21	23
32.5°	12	13	15	17	18	20	21	24	26	27	29
31.25°	14	16	18	20	22	25	27	30	32	34	37
30°	18	20	22	25	28	31	33	37	42	46	50
28.75°	21	24	27	31	34	39	45	50	55	60	64
27.5°	25	29	33	38	45	51	57	63	70	77	84
26.25°	30	34	42	49	56	63	72	81	91	99	108
25°	36	45	53	61	70	81	92	103	114	124	134
23.75°	46	55	64	76	88	101	115	127	139	151	161
22.5°	57	67	79	94	109	124	139	153	166	180	192
21.25°	68	82	97	114	131	147	163	180	196	211	226
20°	82	99	117	135	153	172	190	209	228	246	262
18.75°	97	117	136	156	177	198	219	241	262	281	299
17.5°	114	135	156	179	202	226	251	274	296	317	338
16.25°	131	153	177	202	228	255	281	307	332	356	378
15°	147	172	198	226	255	283	312	341	368	394	416
13.75°	163	190	219	251	281	312	344	375	403	429	454
12.5°	180	209	241	274	307	341	375	406	436	464	490
11.25°	196	228	262	296	332	368	403	436	468	497	524
10°	211	246	281	317	356	394	429	464	497	528	558
8.75°	226	262	299	338	378	416	454	490	524	558	588
7.5°	239	277	315	357	398	437	476	513	549	584	617
6.25°	251	289	330	373	414	455	495	534	572	608	643
5°	261	300	342	386	428	470	511	551	590	628	665
3.75°	268	309	352	397	439	482	524	565	605	645	683
2.5°	274	315	360	404	447	490	533	575	616	657	696
1.25°	277	319	364	409	452	496	539	581	623	665	703
0°	278	320	365	410	454	497	541	583	625	668	705
-1.25°	277	319	364	409	452	496	539	581	623	665	703
-2.5°	274	315	360	404	447	490	533	575	616	657	696
-3.75°	268	309	352	397	439	482	524	565	605	645	683
-5°	261	300	342	386	428	470	511	551	590	628	665
-6.25°	251	289	330	373	414	455	495	534	572	608	643
-7.5°	239	277	315	357	398	437	476	513	549	584	617
-8.75°	226	262	299	338	378	416	454	490	524	558	588
-10°	211	246	281	317	356	394	429	464	497	528	558
-11.25°	196	228	262	296	332	368	403	436	468	497	524
-12.5°	180	209	241	274	307	341	375	406	436	464	490
-13.75°	163	190	219	251	281	312	344	375	403	429	454
-15°	147	172	198	226	255	283	312	341	368	394	416
-16.25°	131	153	177	202	228	255	281	307	332	356	378
-17.5°	114	135	156	179	202	226	251	274	296	317	338
-18.75°	97	117	136	156	177	198	219	241	262	281	299
-20°	82	99	117	135	153	172	190	209	228	246	262
-21.25°	68	82	97	114	131	147	163	180	196	211	226

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	57	67	79	94	109	124	139	153	166	180	192
-23.75°	46	55	64	76	88	101	115	127	139	151	161
-25°	36	45	53	61	70	81	92	103	114	124	134
-26.25°	30	34	42	49	56	63	72	81	91	99	108
-27.5°	25	29	33	38	45	51	57	63	70	77	84
-28.75°	21	24	27	31	34	39	45	50	55	60	64
-30°	18	20	22	25	28	31	33	37	42	46	50
-31.25°	14	16	18	20	22	25	27	30	32	34	37
-32.5°	12	13	15	17	18	20	21	24	26	27	29
-33.75°	11	12	13	13	15	16	18	19	20	21	23
-35°	10	10	11	12	12	13	14	15	16	17	18
-36.25°	8	9	10	10	11	11	12	13	13	14	14
-37.5°	7	8	8	9	9	10	10	11	11	12	12
-38.75°	6	7	7	8	8	9	9	9	10	10	10
-40°	6	6	6	7	7	7	8	8	8	9	9
-41.25°	5	5	6	6	6	6	7	7	7	7	8
-42.5°	5	5	5	5	5	6	6	6	6	6	7
-43.75°	4	4	5	5	5	5	5	5	5	6	6
-45°	4	4	4	4	4	5	5	5	5	5	5
-46.25°	4	4	4	4	4	4	4	4	4	5	5
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	3	3	3	4	4	4	4	4	4	4	4
-51.25°	3	3	3	3	3	3	3	4	4	4	4
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	2	2	3	3	3	3	3	3	3	3
-57.5°	2	2	2	2	2	2	2	2	2	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	1	1	1	1	1	1	2	2	2	2	2
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	4	3	3	3	3
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	5	5	5	5	5	5	5	5	5	5	5
43.75°	6	6	6	6	6	6	6	6	6	6	6
42.5°	7	7	7	7	7	7	7	7	7	7	7
41.25°	8	8	8	8	8	8	8	8	8	8	8
40°	9	9	10	10	10	10	10	10	10	10	10
38.75°	11	11	11	11	11	12	12	12	11	11	11
37.5°	12	13	13	13	13	13	13	13	13	13	13
36.25°	15	16	16	17	17	17	17	17	17	17	16
35°	19	20	20	21	21	21	21	21	21	21	20

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	24	25	26	27	28	28	28	28	28	27	26
32.5°	31	32	33	34	34	34	35	34	34	34	33
31.25°	40	42	45	46	48	48	49	48	48	46	45
30°	53	56	59	61	62	63	63	63	62	61	59
28.75°	69	73	77	79	82	83	84	83	82	79	77
27.5°	90	96	100	104	107	108	109	108	107	104	100
26.25°	115	121	127	131	134	136	137	136	134	131	127
25°	142	149	156	160	164	166	167	166	164	160	156
23.75°	171	180	187	193	197	200	201	200	197	193	187
22.5°	203	213	222	229	234	237	238	237	234	229	222
21.25°	239	251	261	268	274	277	278	277	274	268	261
20°	277	289	300	309	315	319	320	319	315	309	300
18.75°	315	330	342	352	360	364	365	364	360	352	342
17.5°	357	373	386	397	404	409	410	409	404	397	386
16.25°	398	414	428	439	447	452	454	452	447	439	428
15°	437	455	470	482	490	496	497	496	490	482	470
13.75°	476	495	511	524	533	539	541	539	533	524	511
12.5°	513	534	551	565	575	581	583	581	575	565	551
11.25°	549	572	590	605	616	623	625	623	616	605	590
10°	584	608	628	645	657	665	668	665	657	645	628
8.75°	617	643	665	683	696	703	705	703	696	683	665
7.5°	648	675	698	716	728	735	738	735	728	716	698
6.25°	675	703	726	743	753	759	761	759	753	743	726
5°	698	726	748	761	770	776	778	776	770	761	748
3.75°	716	743	761	774	782	787	788	787	782	774	761
2.5°	728	753	770	782	790	796	797	796	790	782	770
1.25°	735	759	776	787	796	801	803	801	796	787	776
0°	738	761	778	788	797	803	807	803	797	788	778
-1.25°	735	759	776	787	796	801	803	801	796	787	776
-2.5°	728	753	770	782	790	796	797	796	790	782	770
-3.75°	716	743	761	774	782	787	788	787	782	774	761
-5°	698	726	748	761	770	776	778	776	770	761	748
-6.25°	675	703	726	743	753	759	761	759	753	743	726
-7.5°	648	675	698	716	728	735	738	735	728	716	698
-8.75°	617	643	665	683	696	703	705	703	696	683	665
-10°	584	608	628	645	657	665	668	665	657	645	628
-11.25°	549	572	590	605	616	623	625	623	616	605	590
-12.5°	513	534	551	565	575	581	583	581	575	565	551
-13.75°	476	495	511	524	533	539	541	539	533	524	511
-15°	437	455	470	482	490	496	497	496	490	482	470
-16.25°	398	414	428	439	447	452	454	452	447	439	428
-17.5°	357	373	386	397	404	409	410	409	404	397	386
-18.75°	315	330	342	352	360	364	365	364	360	352	342
-20°	277	289	300	309	315	319	320	319	315	309	300
-21.25°	239	251	261	268	274	277	278	277	274	268	261

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	203	213	222	229	234	237	238	237	234	229	222
-23.75°	171	180	187	193	197	200	201	200	197	193	187
-25°	142	149	156	160	164	166	167	166	164	160	156
-26.25°	115	121	127	131	134	136	137	136	134	131	127
-27.5°	90	96	100	104	107	108	109	108	107	104	100
-28.75°	69	73	77	79	82	83	84	83	82	79	77
-30°	53	56	59	61	62	63	63	63	62	61	59
-31.25°	40	42	45	46	48	48	49	48	48	46	45
-32.5°	31	32	33	34	34	34	35	34	34	34	33
-33.75°	24	25	26	27	28	28	28	28	28	27	26
-35°	19	20	20	21	21	21	21	21	21	21	20
-36.25°	15	16	16	17	17	17	17	17	17	17	16
-37.5°	12	13	13	13	13	13	13	13	13	13	13
-38.75°	11	11	11	11	11	12	12	12	11	11	11
-40°	9	9	10	10	10	10	10	10	10	10	10
-41.25°	8	8	8	8	8	8	8	8	8	8	8
-42.5°	7	7	7	7	7	7	7	7	7	7	7
-43.75°	6	6	6	6	6	6	6	6	6	6	6
-45°	5	5	5	5	5	5	5	5	5	5	5
-46.25°	5	5	5	5	5	5	5	5	5	5	5
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	3	3	3	3	3	3	4	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	2	2	2	2	2	2	2	1	1	1	1
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	2	2	2	2	2	2	2
56.25°	3	3	3	3	3	3	3	3	3	3	2
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	4	4	4	4	4	4	3	3	3	3	3
50°	4	4	4	4	4	4	4	4	4	4	3
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	5	5	5	5	4	4	4	4	4	4	4
45°	5	5	5	5	5	5	5	5	4	4	4
43.75°	6	6	6	6	5	5	5	5	5	5	5
42.5°	7	7	7	6	6	6	6	6	5	5	5
41.25°	8	8	8	7	7	7	7	6	6	6	6
40°	9	9	9	9	8	8	8	7	7	7	6
38.75°	11	11	10	10	10	9	9	9	8	8	7
37.5°	13	12	12	12	11	11	10	10	9	9	8
36.25°	16	15	14	14	13	13	12	11	11	10	10
35°	20	19	18	17	16	15	14	13	12	12	11

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	25	24	23	21	20	19	18	16	15	13	13
32.5°	32	31	29	27	26	24	21	20	18	17	15
31.25°	42	40	37	34	32	30	27	25	22	20	18
30°	56	53	50	46	42	37	33	31	28	25	22
28.75°	73	69	64	60	55	50	45	39	34	31	27
27.5°	96	90	84	77	70	63	57	51	45	38	33
26.25°	121	115	108	99	91	81	72	63	56	49	42
25°	149	142	134	124	114	103	92	81	70	61	53
23.75°	180	171	161	151	139	127	115	101	88	76	64
22.5°	213	203	192	180	166	153	139	124	109	94	79
21.25°	251	239	226	211	196	180	163	147	131	114	97
20°	289	277	262	246	228	209	190	172	153	135	117
18.75°	330	315	299	281	262	241	219	198	177	156	136
17.5°	373	357	338	317	296	274	251	226	202	179	156
16.25°	414	398	378	356	332	307	281	255	228	202	177
15°	455	437	416	394	368	341	312	283	255	226	198
13.75°	495	476	454	429	403	375	344	312	281	251	219
12.5°	534	513	490	464	436	406	375	341	307	274	241
11.25°	572	549	524	497	468	436	403	368	332	296	262
10°	608	584	558	528	497	464	429	394	356	317	281
8.75°	643	617	588	558	524	490	454	416	378	338	299
7.5°	675	648	617	584	549	513	476	437	398	357	315
6.25°	703	675	643	608	572	534	495	455	414	373	330
5°	726	698	665	628	590	551	511	470	428	386	342
3.75°	743	716	683	645	605	565	524	482	439	397	352
2.5°	753	728	696	657	616	575	533	490	447	404	360
1.25°	759	735	703	665	623	581	539	496	452	409	364
0°	761	738	705	668	625	583	541	497	454	410	365
-1.25°	759	735	703	665	623	581	539	496	452	409	364
-2.5°	753	728	696	657	616	575	533	490	447	404	360
-3.75°	743	716	683	645	605	565	524	482	439	397	352
-5°	726	698	665	628	590	551	511	470	428	386	342
-6.25°	703	675	643	608	572	534	495	455	414	373	330
-7.5°	675	648	617	584	549	513	476	437	398	357	315
-8.75°	643	617	588	558	524	490	454	416	378	338	299
-10°	608	584	558	528	497	464	429	394	356	317	281
-11.25°	572	549	524	497	468	436	403	368	332	296	262
-12.5°	534	513	490	464	436	406	375	341	307	274	241
-13.75°	495	476	454	429	403	375	344	312	281	251	219
-15°	455	437	416	394	368	341	312	283	255	226	198
-16.25°	414	398	378	356	332	307	281	255	228	202	177
-17.5°	373	357	338	317	296	274	251	226	202	179	156
-18.75°	330	315	299	281	262	241	219	198	177	156	136
-20°	289	277	262	246	228	209	190	172	153	135	117
-21.25°	251	239	226	211	196	180	163	147	131	114	97

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	213	203	192	180	166	153	139	124	109	94	79
-23.75°	180	171	161	151	139	127	115	101	88	76	64
-25°	149	142	134	124	114	103	92	81	70	61	53
-26.25°	121	115	108	99	91	81	72	63	56	49	42
-27.5°	96	90	84	77	70	63	57	51	45	38	33
-28.75°	73	69	64	60	55	50	45	39	34	31	27
-30°	56	53	50	46	42	37	33	31	28	25	22
-31.25°	42	40	37	34	32	30	27	25	22	20	18
-32.5°	32	31	29	27	26	24	21	20	18	17	15
-33.75°	25	24	23	21	20	19	18	16	15	13	13
-35°	20	19	18	17	16	15	14	13	12	12	11
-36.25°	16	15	14	14	13	13	12	11	11	10	10
-37.5°	13	12	12	12	11	11	10	10	9	9	8
-38.75°	11	11	10	10	10	9	9	9	8	8	7
-40°	9	9	9	9	8	8	8	7	7	7	6
-41.25°	8	8	8	7	7	7	7	6	6	6	6
-42.5°	7	7	7	6	6	6	6	6	5	5	5
-43.75°	6	6	6	6	5	5	5	5	5	5	5
-45°	5	5	5	5	5	5	5	5	4	4	4
-46.25°	5	5	5	5	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	3
-51.25°	4	4	4	4	4	4	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	2
-57.5°	3	3	3	3	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	0	0	0	0	0	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	2	2	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	2	1	1	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	1
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	2	2	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	2	2	2	2	2
52.5°	3	3	3	3	3	3	3	3	2	2	2
51.25°	3	3	3	3	3	3	3	3	3	3	2
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	4	4	4	3	3	3	3	3	3	3	3
47.5°	4	4	4	4	4	3	3	3	3	3	3
46.25°	4	4	4	4	4	4	4	3	3	3	3
45°	4	4	4	4	4	4	4	4	4	3	3
43.75°	4	4	4	4	4	4	4	4	4	4	4
42.5°	5	5	5	4	4	4	4	4	4	4	4
41.25°	5	5	5	5	5	4	4	4	4	4	4
40°	6	6	5	5	5	5	5	4	4	4	4
38.75°	7	6	6	6	5	5	5	5	4	4	4
37.5°	8	7	7	6	6	6	5	5	5	4	4
36.25°	9	8	8	7	7	6	6	5	5	5	5
35°	10	10	9	8	8	7	6	6	5	5	5

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	12	11	10	9	9	8	7	7	6	6	5
32.5°	13	12	11	11	10	9	8	7	7	6	6
31.25°	16	14	13	12	11	10	9	8	7	7	6
30°	20	18	15	13	12	11	10	9	8	7	7
28.75°	24	21	18	16	14	12	11	10	9	8	7
27.5°	29	25	21	19	17	14	12	11	10	9	8
26.25°	34	30	26	22	19	17	14	12	11	10	9
25°	45	36	31	27	22	19	17	14	12	11	10
23.75°	55	46	37	31	27	22	19	16	13	12	11
22.5°	67	57	47	37	31	26	21	18	15	13	11
21.25°	82	68	57	46	36	30	25	21	18	14	12
20°	99	82	67	55	45	34	29	24	20	16	13
18.75°	117	97	79	64	53	42	33	27	22	18	15
17.5°	135	114	94	76	61	49	38	31	25	20	17
16.25°	153	131	109	88	70	56	45	34	28	22	18
15°	172	147	124	101	81	63	51	39	31	25	20
13.75°	190	163	139	115	92	72	57	45	33	27	21
12.5°	209	180	153	127	103	81	63	50	37	30	24
11.25°	228	196	166	139	114	91	70	55	42	32	26
10°	246	211	180	151	124	99	77	60	46	34	27
8.75°	262	226	192	161	134	108	84	64	50	37	29
7.5°	277	239	203	171	142	115	90	69	53	40	31
6.25°	289	251	213	180	149	121	96	73	56	42	32
5°	300	261	222	187	156	127	100	77	59	45	33
3.75°	309	268	229	193	160	131	104	79	61	46	34
2.5°	315	274	234	197	164	134	107	82	62	48	34
1.25°	319	277	237	200	166	136	108	83	63	48	34
0°	320	278	238	201	167	137	109	84	63	49	35
-1.25°	319	277	237	200	166	136	108	83	63	48	34
-2.5°	315	274	234	197	164	134	107	82	62	48	34
-3.75°	309	268	229	193	160	131	104	79	61	46	34
-5°	300	261	222	187	156	127	100	77	59	45	33
-6.25°	289	251	213	180	149	121	96	73	56	42	32
-7.5°	277	239	203	171	142	115	90	69	53	40	31
-8.75°	262	226	192	161	134	108	84	64	50	37	29
-10°	246	211	180	151	124	99	77	60	46	34	27
-11.25°	228	196	166	139	114	91	70	55	42	32	26
-12.5°	209	180	153	127	103	81	63	50	37	30	24
-13.75°	190	163	139	115	92	72	57	45	33	27	21
-15°	172	147	124	101	81	63	51	39	31	25	20
-16.25°	153	131	109	88	70	56	45	34	28	22	18
-17.5°	135	114	94	76	61	49	38	31	25	20	17
-18.75°	117	97	79	64	53	42	33	27	22	18	15
-20°	99	82	67	55	45	34	29	24	20	16	13
-21.25°	82	68	57	46	36	30	25	21	18	14	12

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	67	57	47	37	31	26	21	18	15	13	11
-23.75°	55	46	37	31	27	22	19	16	13	12	11
-25°	45	36	31	27	22	19	17	14	12	11	10
-26.25°	34	30	26	22	19	17	14	12	11	10	9
-27.5°	29	25	21	19	17	14	12	11	10	9	8
-28.75°	24	21	18	16	14	12	11	10	9	8	7
-30°	20	18	15	13	12	11	10	9	8	7	7
-31.25°	16	14	13	12	11	10	9	8	7	7	6
-32.5°	13	12	11	11	10	9	8	7	7	6	6
-33.75°	12	11	10	9	9	8	7	7	6	6	5
-35°	10	10	9	8	8	7	6	6	5	5	5
-36.25°	9	8	8	7	7	6	6	5	5	5	5
-37.5°	8	7	7	6	6	6	5	5	5	4	4
-38.75°	7	6	6	6	5	5	5	5	4	4	4
-40°	6	6	5	5	5	5	5	4	4	4	4
-41.25°	5	5	5	5	5	4	4	4	4	4	4
-42.5°	5	5	5	4	4	4	4	4	4	4	4
-43.75°	4	4	4	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	3	3
-46.25°	4	4	4	4	4	4	4	3	3	3	3
-47.5°	4	4	4	4	4	3	3	3	3	3	3
-48.75°	4	4	4	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	2
-52.5°	3	3	3	3	3	3	3	3	2	2	2
-53.75°	3	3	3	3	3	3	2	2	2	2	2
-55°	3	3	3	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	1
-62.5°	2	2	2	2	2	2	2	1	1	1	1
-63.75°	2	2	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	0	0	0	0	0	0	0



REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	0	0	0	0	0
73.75°	1	1	1	1	1	1	1	1	1	1	0
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	2	2	1	1	1	1	1	1	1	1	1
58.75°	2	2	2	2	1	1	1	1	1	1	1
57.5°	2	2	2	2	2	2	1	1	1	1	1
56.25°	2	2	2	2	2	2	2	2	1	1	1
55°	2	2	2	2	2	2	2	2	2	1	1
53.75°	2	2	2	2	2	2	2	2	2	2	1
52.5°	2	2	2	2	2	2	2	2	2	2	2
51.25°	2	2	2	2	2	2	2	2	2	2	2
50°	3	2	2	2	2	2	2	2	2	2	2
48.75°	3	3	3	2	2	2	2	2	2	2	2
47.5°	3	3	3	3	2	2	2	2	2	2	2
46.25°	3	3	3	3	3	3	2	2	2	2	2
45°	3	3	3	3	3	3	3	2	2	2	2
43.75°	3	3	3	3	3	3	3	3	2	2	2
42.5°	4	3	3	3	3	3	3	3	3	2	2
41.25°	4	4	3	3	3	3	3	3	3	3	2
40°	4	4	4	3	3	3	3	3	3	3	3
38.75°	4	4	4	4	3	3	3	3	3	3	3
37.5°	4	4	4	4	4	3	3	3	3	3	3
36.25°	4	4	4	4	4	4	3	3	3	3	3
35°	5	4	4	4	4	4	4	3	3	3	3

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	5	5	4	4	4	4	4	4	3	3	3
32.5°	5	5	5	4	4	4	4	4	4	3	3
31.25°	6	5	5	4	4	4	4	4	4	3	3
30°	6	5	5	5	4	4	4	4	4	4	3
28.75°	7	6	5	5	5	4	4	4	4	4	3
27.5°	7	6	6	5	5	5	4	4	4	4	4
26.25°	8	7	6	6	5	5	4	4	4	4	4
25°	9	8	7	6	5	5	5	4	4	4	4
23.75°	9	8	7	6	6	5	5	4	4	4	4
22.5°	10	9	8	7	6	5	5	5	4	4	4
21.25°	11	10	8	7	6	6	5	5	4	4	4
20°	12	10	9	8	7	6	5	5	4	4	4
18.75°	13	11	10	8	7	6	6	5	5	4	4
17.5°	13	12	10	9	8	7	6	5	5	4	4
16.25°	15	12	11	9	8	7	6	5	5	4	4
15°	16	13	11	10	9	7	6	6	5	5	4
13.75°	18	14	12	10	9	8	7	6	5	5	4
12.5°	19	15	13	11	9	8	7	6	5	5	4
11.25°	20	16	13	11	10	8	7	6	5	5	4
10°	21	17	14	12	10	9	7	6	6	5	5
8.75°	23	18	14	12	10	9	8	7	6	5	5
7.5°	24	19	15	12	11	9	8	7	6	5	5
6.25°	25	20	16	13	11	9	8	7	6	5	5
5°	26	20	16	13	11	10	8	7	6	5	5
3.75°	27	21	17	13	11	10	8	7	6	5	5
2.5°	28	21	17	13	11	10	8	7	6	5	5
1.25°	28	21	17	13	12	10	8	7	6	5	5
0°	28	21	17	13	12	10	8	7	6	5	5
-1.25°	28	21	17	13	12	10	8	7	6	5	5
-2.5°	28	21	17	13	11	10	8	7	6	5	5
-3.75°	27	21	17	13	11	10	8	7	6	5	5
-5°	26	20	16	13	11	10	8	7	6	5	5
-6.25°	25	20	16	13	11	9	8	7	6	5	5
-7.5°	24	19	15	12	11	9	8	7	6	5	5
-8.75°	23	18	14	12	10	9	8	7	6	5	5
-10°	21	17	14	12	10	9	7	6	6	5	5
-11.25°	20	16	13	11	10	8	7	6	5	5	4
-12.5°	19	15	13	11	9	8	7	6	5	5	4
-13.75°	18	14	12	10	9	8	7	6	5	5	4
-15°	16	13	11	10	9	7	6	6	5	5	4
-16.25°	15	12	11	9	8	7	6	5	5	4	4
-17.5°	13	12	10	9	8	7	6	5	5	4	4
-18.75°	13	11	10	8	7	6	6	5	5	4	4
-20°	12	10	9	8	7	6	5	5	4	4	4
-21.25°	11	10	8	7	6	6	5	5	4	4	4

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	10	9	8	7	6	5	5	5	4	4	4
-23.75°	9	8	7	6	6	5	5	4	4	4	4
-25°	9	8	7	6	5	5	5	4	4	4	4
-26.25°	8	7	6	6	5	5	4	4	4	4	4
-27.5°	7	6	6	5	5	5	4	4	4	4	4
-28.75°	7	6	5	5	5	4	4	4	4	4	3
-30°	6	5	5	5	4	4	4	4	4	4	3
-31.25°	6	5	5	4	4	4	4	4	4	3	3
-32.5°	5	5	5	4	4	4	4	4	4	3	3
-33.75°	5	5	4	4	4	4	4	4	3	3	3
-35°	5	4	4	4	4	4	4	3	3	3	3
-36.25°	4	4	4	4	4	4	3	3	3	3	3
-37.5°	4	4	4	4	4	3	3	3	3	3	3
-38.75°	4	4	4	4	3	3	3	3	3	3	3
-40°	4	4	4	3	3	3	3	3	3	3	3
-41.25°	4	4	3	3	3	3	3	3	3	3	2
-42.5°	4	3	3	3	3	3	3	3	3	2	2
-43.75°	3	3	3	3	3	3	3	3	2	2	2
-45°	3	3	3	3	3	3	3	2	2	2	2
-46.25°	3	3	3	3	3	3	2	2	2	2	2
-47.5°	3	3	3	3	2	2	2	2	2	2	2
-48.75°	3	3	3	2	2	2	2	2	2	2	2
-50°	3	2	2	2	2	2	2	2	2	2	2
-51.25°	2	2	2	2	2	2	2	2	2	2	2
-52.5°	2	2	2	2	2	2	2	2	2	2	2
-53.75°	2	2	2	2	2	2	2	2	2	2	1
-55°	2	2	2	2	2	2	2	2	2	1	1
-56.25°	2	2	2	2	2	2	2	2	1	1	1
-57.5°	2	2	2	2	2	2	1	1	1	1	1
-58.75°	2	2	2	2	1	1	1	1	1	1	1
-60°	2	2	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	0
-75°	1	1	1	1	1	1	0	0	0	0	0
-76.25°	1	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	0	0	0	0	0	0	0	0	0
71.25°	1	1	1	1	0	0	0	0	0	0	0
70°	1	1	1	1	1	1	0	0	0	0	0
68.75°	1	1	1	1	1	1	1	1	0	0	0
67.5°	1	1	1	1	1	1	1	1	1	1	0
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	2	1	1	1	1	1	1	1	1	1	1
51.25°	2	2	1	1	1	1	1	1	1	1	1
50°	2	2	2	1	1	1	1	1	1	1	1
48.75°	2	2	2	2	1	1	1	1	1	1	1
47.5°	2	2	2	2	2	1	1	1	1	1	1
46.25°	2	2	2	2	2	1	1	1	1	1	1
45°	2	2	2	2	2	2	1	1	1	1	1
43.75°	2	2	2	2	2	2	2	1	1	1	1
42.5°	2	2	2	2	2	2	2	2	1	1	1
41.25°	2	2	2	2	2	2	2	2	1	1	1
40°	2	2	2	2	2	2	2	2	2	1	1
38.75°	2	2	2	2	2	2	2	2	2	1	1
37.5°	3	2	2	2	2	2	2	2	2	2	1
36.25°	3	3	2	2	2	2	2	2	2	2	1
35°	3	3	2	2	2	2	2	2	2	2	2

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	3	3	3	2	2	2	2	2	2	2	2
32.5°	3	3	3	2	2	2	2	2	2	2	2
31.25°	3	3	3	3	2	2	2	2	2	2	2
30°	3	3	3	3	2	2	2	2	2	2	2
28.75°	3	3	3	3	3	2	2	2	2	2	2
27.5°	3	3	3	3	3	2	2	2	2	2	2
26.25°	3	3	3	3	3	3	2	2	2	2	2
25°	4	3	3	3	3	3	2	2	2	2	2
23.75°	4	3	3	3	3	3	2	2	2	2	2
22.5°	4	4	3	3	3	3	3	2	2	2	2
21.25°	4	4	3	3	3	3	3	2	2	2	2
20°	4	4	3	3	3	3	3	2	2	2	2
18.75°	4	4	3	3	3	3	3	2	2	2	2
17.5°	4	4	4	3	3	3	3	3	2	2	2
16.25°	4	4	4	3	3	3	3	3	2	2	2
15°	4	4	4	3	3	3	3	3	2	2	2
13.75°	4	4	4	3	3	3	3	3	2	2	2
12.5°	4	4	4	4	3	3	3	3	2	2	2
11.25°	4	4	4	4	3	3	3	3	2	2	2
10°	4	4	4	4	3	3	3	3	3	2	2
8.75°	4	4	4	4	3	3	3	3	3	2	2
7.5°	4	4	4	4	3	3	3	3	3	2	2
6.25°	4	4	4	4	3	3	3	3	3	2	2
5°	4	4	4	4	3	3	3	3	3	2	2
3.75°	4	4	4	4	3	3	3	3	3	2	2
2.5°	4	4	4	4	3	3	3	3	3	2	2
1.25°	4	4	4	4	3	3	3	3	3	2	2
0°	4	4	4	4	4	3	3	3	3	2	2
-1.25°	4	4	4	4	3	3	3	3	3	2	2
-2.5°	4	4	4	4	3	3	3	3	3	2	2
-3.75°	4	4	4	4	3	3	3	3	3	2	2
-5°	4	4	4	4	3	3	3	3	3	2	2
-6.25°	4	4	4	4	3	3	3	3	3	2	2
-7.5°	4	4	4	4	3	3	3	3	3	2	2
-8.75°	4	4	4	4	3	3	3	3	3	2	2
-10°	4	4	4	4	3	3	3	3	3	2	2
-11.25°	4	4	4	4	3	3	3	3	2	2	2
-12.5°	4	4	4	4	3	3	3	3	2	2	2
-13.75°	4	4	4	3	3	3	3	3	2	2	2
-15°	4	4	4	3	3	3	3	3	2	2	2
-16.25°	4	4	4	3	3	3	3	3	2	2	2
-17.5°	4	4	4	3	3	3	3	3	2	2	2
-18.75°	4	4	3	3	3	3	3	2	2	2	2
-20°	4	4	3	3	3	3	3	2	2	2	2
-21.25°	4	4	3	3	3	3	3	2	2	2	2

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	4	4	3	3	3	3	3	2	2	2	2
-23.75°	4	3	3	3	3	3	2	2	2	2	2
-25°	4	3	3	3	3	3	2	2	2	2	2
-26.25°	3	3	3	3	3	3	2	2	2	2	2
-27.5°	3	3	3	3	3	2	2	2	2	2	2
-28.75°	3	3	3	3	3	2	2	2	2	2	2
-30°	3	3	3	3	2	2	2	2	2	2	2
-31.25°	3	3	3	3	2	2	2	2	2	2	2
-32.5°	3	3	3	2	2	2	2	2	2	2	2
-33.75°	3	3	3	2	2	2	2	2	2	2	2
-35°	3	3	2	2	2	2	2	2	2	2	2
-36.25°	3	3	2	2	2	2	2	2	2	2	1
-37.5°	3	2	2	2	2	2	2	2	2	2	1
-38.75°	2	2	2	2	2	2	2	2	2	1	1
-40°	2	2	2	2	2	2	2	2	2	1	1
-41.25°	2	2	2	2	2	2	2	2	1	1	1
-42.5°	2	2	2	2	2	2	2	2	1	1	1
-43.75°	2	2	2	2	2	2	2	1	1	1	1
-45°	2	2	2	2	2	2	1	1	1	1	1
-46.25°	2	2	2	2	2	1	1	1	1	1	1
-47.5°	2	2	2	2	2	1	1	1	1	1	1
-48.75°	2	2	2	2	1	1	1	1	1	1	1
-50°	2	2	2	1	1	1	1	1	1	1	1
-51.25°	2	2	1	1	1	1	1	1	1	1	1
-52.5°	2	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	0
-68.75°	1	1	1	1	1	1	1	1	0	0	0
-70°	1	1	1	1	1	1	0	0	0	0	0
-71.25°	1	1	1	1	0	0	0	0	0	0	0
-72.5°	1	1	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	1	0	0	0	0	0	0	0	0	0	0
63.75°	1	1	0	0	0	0	0	0	0	0	0
62.5°	1	1	1	0	0	0	0	0	0	0	0
61.25°	1	1	1	1	0	0	0	0	0	0	0
60°	1	1	1	1	1	0	0	0	0	0	0
58.75°	1	1	1	1	1	1	0	0	0	0	0
57.5°	1	1	1	1	1	1	0	0	0	0	0
56.25°	1	1	1	1	1	1	1	0	0	0	0
55°	1	1	1	1	1	1	1	0	0	0	0
53.75°	1	1	1	1	1	1	1	1	0	0	0
52.5°	1	1	1	1	1	1	1	1	0	0	0
51.25°	1	1	1	1	1	1	1	1	1	0	0
50°	1	1	1	1	1	1	1	1	1	0	0
48.75°	1	1	1	1	1	1	1	1	1	1	0
47.5°	1	1	1	1	1	1	1	1	1	1	0
46.25°	1	1	1	1	1	1	1	1	1	1	0
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	1
40°	1	1	1	1	1	1	1	1	1	1	1
38.75°	1	1	1	1	1	1	1	1	1	1	1
37.5°	1	1	1	1	1	1	1	1	1	1	1
36.25°	1	1	1	1	1	1	1	1	1	1	1
35°	1	1	1	1	1	1	1	1	1	1	1

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	1	1	1	1	1	1	1	1
32.5°	1	1	1	1	1	1	1	1	1	1	1
31.25°	2	1	1	1	1	1	1	1	1	1	1
30°	2	1	1	1	1	1	1	1	1	1	1
28.75°	2	1	1	1	1	1	1	1	1	1	1
27.5°	2	2	1	1	1	1	1	1	1	1	1
26.25°	2	2	1	1	1	1	1	1	1	1	1
25°	2	2	1	1	1	1	1	1	1	1	1
23.75°	2	2	1	1	1	1	1	1	1	1	1
22.5°	2	2	1	1	1	1	1	1	1	1	1
21.25°	2	2	2	1	1	1	1	1	1	1	1
20°	2	2	2	1	1	1	1	1	1	1	1
18.75°	2	2	2	1	1	1	1	1	1	1	1
17.5°	2	2	2	1	1	1	1	1	1	1	1
16.25°	2	2	2	1	1	1	1	1	1	1	1
15°	2	2	2	1	1	1	1	1	1	1	1
13.75°	2	2	2	2	1	1	1	1	1	1	1
12.5°	2	2	2	2	1	1	1	1	1	1	1
11.25°	2	2	2	2	1	1	1	1	1	1	1
10°	2	2	2	2	1	1	1	1	1	1	1
8.75°	2	2	2	2	1	1	1	1	1	1	1
7.5°	2	2	2	2	1	1	1	1	1	1	1
6.25°	2	2	2	2	1	1	1	1	1	1	1
5°	2	2	2	2	1	1	1	1	1	1	1
3.75°	2	2	2	2	1	1	1	1	1	1	1
2.5°	2	2	2	2	1	1	1	1	1	1	1
1.25°	2	2	2	2	1	1	1	1	1	1	1
0°	2	2	2	2	1	1	1	1	1	1	1
-1.25°	2	2	2	2	1	1	1	1	1	1	1
-2.5°	2	2	2	2	1	1	1	1	1	1	1
-3.75°	2	2	2	2	1	1	1	1	1	1	1
-5°	2	2	2	2	1	1	1	1	1	1	1
-6.25°	2	2	2	2	1	1	1	1	1	1	1
-7.5°	2	2	2	2	1	1	1	1	1	1	1
-8.75°	2	2	2	2	1	1	1	1	1	1	1
-10°	2	2	2	2	1	1	1	1	1	1	1
-11.25°	2	2	2	2	1	1	1	1	1	1	1
-12.5°	2	2	2	2	1	1	1	1	1	1	1
-13.75°	2	2	2	2	1	1	1	1	1	1	1
-15°	2	2	2	1	1	1	1	1	1	1	1
-16.25°	2	2	2	1	1	1	1	1	1	1	1
-17.5°	2	2	2	1	1	1	1	1	1	1	1
-18.75°	2	2	2	1	1	1	1	1	1	1	1
-20°	2	2	2	1	1	1	1	1	1	1	1
-21.25°	2	2	2	1	1	1	1	1	1	1	1

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	2	1	1	1	1	1	1	1	1	1
-23.75°	2	2	1	1	1	1	1	1	1	1	1
-25°	2	2	1	1	1	1	1	1	1	1	1
-26.25°	2	2	1	1	1	1	1	1	1	1	1
-27.5°	2	2	1	1	1	1	1	1	1	1	1
-28.75°	2	1	1	1	1	1	1	1	1	1	1
-30°	2	1	1	1	1	1	1	1	1	1	1
-31.25°	2	1	1	1	1	1	1	1	1	1	1
-32.5°	1	1	1	1	1	1	1	1	1	1	1
-33.75°	1	1	1	1	1	1	1	1	1	1	1
-35°	1	1	1	1	1	1	1	1	1	1	1
-36.25°	1	1	1	1	1	1	1	1	1	1	1
-37.5°	1	1	1	1	1	1	1	1	1	1	1
-38.75°	1	1	1	1	1	1	1	1	1	1	1
-40°	1	1	1	1	1	1	1	1	1	1	1
-41.25°	1	1	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	0
-47.5°	1	1	1	1	1	1	1	1	1	1	0
-48.75°	1	1	1	1	1	1	1	1	1	1	0
-50°	1	1	1	1	1	1	1	1	1	0	0
-51.25°	1	1	1	1	1	1	1	1	1	0	0
-52.5°	1	1	1	1	1	1	1	1	0	0	0
-53.75°	1	1	1	1	1	1	1	1	0	0	0
-55°	1	1	1	1	1	1	1	0	0	0	0
-56.25°	1	1	1	1	1	1	1	0	0	0	0
-57.5°	1	1	1	1	1	1	0	0	0	0	0
-58.75°	1	1	1	1	1	1	0	0	0	0	0
-60°	1	1	1	1	1	0	0	0	0	0	0
-61.25°	1	1	1	1	0	0	0	0	0	0	0
-62.5°	1	1	1	0	0	0	0	0	0	0	0
-63.75°	1	1	0	0	0	0	0	0	0	0	0
-65°	1	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	1	0	0	0	0	0	0	0	0	0	0
38.75°	1	0	0	0	0	0	0	0	0	0	0
37.5°	1	0	0	0	0	0	0	0	0	0	0
36.25°	1	0	0	0	0	0	0	0	0	0	0
35°	1	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	0	0	0	0	0	0	0	0	0
32.5°	1	1	0	0	0	0	0	0	0	0	0
31.25°	1	1	0	0	0	0	0	0	0	0	0
30°	1	1	0	0	0	0	0	0	0	0	0
28.75°	1	1	0	0	0	0	0	0	0	0	0
27.5°	1	1	0	0	0	0	0	0	0	0	0
26.25°	1	1	0	0	0	0	0	0	0	0	0
25°	1	1	0	0	0	0	0	0	0	0	0
23.75°	1	1	1	0	0	0	0	0	0	0	0
22.5°	1	1	1	0	0	0	0	0	0	0	0
21.25°	1	1	1	0	0	0	0	0	0	0	0
20°	1	1	1	0	0	0	0	0	0	0	0
18.75°	1	1	1	0	0	0	0	0	0	0	0
17.5°	1	1	1	0	0	0	0	0	0	0	0
16.25°	1	1	1	0	0	0	0	0	0	0	0
15°	1	1	1	0	0	0	0	0	0	0	0
13.75°	1	1	1	0	0	0	0	0	0	0	0
12.5°	1	1	1	0	0	0	0	0	0	0	0
11.25°	1	1	1	0	0	0	0	0	0	0	0
10°	1	1	1	0	0	0	0	0	0	0	0
8.75°	1	1	1	0	0	0	0	0	0	0	0
7.5°	1	1	1	0	0	0	0	0	0	0	0
6.25°	1	1	1	0	0	0	0	0	0	0	0
5°	1	1	1	0	0	0	0	0	0	0	0
3.75°	1	1	1	0	0	0	0	0	0	0	0
2.5°	1	1	1	0	0	0	0	0	0	0	0
1.25°	1	1	1	0	0	0	0	0	0	0	0
0°	1	1	1	0	0	0	0	0	0	0	0
-1.25°	1	1	1	0	0	0	0	0	0	0	0
-2.5°	1	1	1	0	0	0	0	0	0	0	0
-3.75°	1	1	1	0	0	0	0	0	0	0	0
-5°	1	1	1	0	0	0	0	0	0	0	0
-6.25°	1	1	1	0	0	0	0	0	0	0	0
-7.5°	1	1	1	0	0	0	0	0	0	0	0
-8.75°	1	1	1	0	0	0	0	0	0	0	0
-10°	1	1	1	0	0	0	0	0	0	0	0
-11.25°	1	1	1	0	0	0	0	0	0	0	0
-12.5°	1	1	1	0	0	0	0	0	0	0	0
-13.75°	1	1	1	0	0	0	0	0	0	0	0
-15°	1	1	1	0	0	0	0	0	0	0	0
-16.25°	1	1	1	0	0	0	0	0	0	0	0
-17.5°	1	1	1	0	0	0	0	0	0	0	0
-18.75°	1	1	1	0	0	0	0	0	0	0	0
-20°	1	1	1	0	0	0	0	0	0	0	0
-21.25°	1	1	1	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	0	0	0	0	0	0	0	0
-23.75°	1	1	1	0	0	0	0	0	0	0	0
-25°	1	1	0	0	0	0	0	0	0	0	0
-26.25°	1	1	0	0	0	0	0	0	0	0	0
-27.5°	1	1	0	0	0	0	0	0	0	0	0
-28.75°	1	1	0	0	0	0	0	0	0	0	0
-30°	1	1	0	0	0	0	0	0	0	0	0
-31.25°	1	1	0	0	0	0	0	0	0	0	0
-32.5°	1	1	0	0	0	0	0	0	0	0	0
-33.75°	1	1	0	0	0	0	0	0	0	0	0
-35°	1	0	0	0	0	0	0	0	0	0	0
-36.25°	1	0	0	0	0	0	0	0	0	0	0
-37.5°	1	0	0	0	0	0	0	0	0	0	0
-38.75°	1	0	0	0	0	0	0	0	0	0	0
-40°	1	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0

REPORT NUMBER: P246992 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS-OSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)