

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220474

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED3597-F-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220474
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29470)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-F-WT-L1-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS, FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 3500K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 815.1 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.56
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220474

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-F-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220474

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-F-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	84
4	100	94	89	85	98	92	88	84	90	87	83	88	85	83	87	84	82	80
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77
6	93	85	80	76	91	84	80	76	83	79	76	82	78	75	80	77	75	73
7	89	82	77	73	88	81	76	73	80	76	72	79	75	72	78	74	72	71
8	86	78	73	70	85	78	73	70	77	73	70	76	72	69	75	72	69	68
9	84	76	71	67	83	75	70	67	74	70	67	73	70	67	73	69	67	65
10	81	73	68	65	80	72	68	65	72	67	65	71	67	64	70	67	64	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	458867
5°	448007
10°	395183
15°	307516
20°	192097
25°	75004
30°	20459
35°	11966
40°	9561
45°	9706
50°	10234
55°	10475
60°	10262
65°	9443
70°	8078
75°	7371
80°	8208
85°	7548



TEST NUMBER: P220474

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-F-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.0	22.8
10°-20°	363.1	44.5
20°-30°	155.7	19.1
30°-40°	30.7	3.8
40°-50°	24.3	3.0
50°-60°	24.3	3.0
60°-70°	18.0	2.2
70°-80°	9.6	1.2
80°-90°	3.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	704.8	86.5
0°-40°	735.5	90.2
0°-60°	784.1	96.2
0°-90°	815.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	815.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2093	
5°	2035	186
15°	1355	363
25°	310	156
35°	45	31
45°	31	24
55°	27	24
65°	18	18
75°	9	10
85°	3	3
90°	0	



TEST NUMBER: P220474

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-F-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2092.6
1°	2086.5
2°	2080.0
3°	2073.9
4°	2059.6
5°	2035.3
6°	2002.7
7°	1960.2
8°	1905.9
9°	1844.7
10°	1774.8
11°	1700.1
12°	1622.4
13°	1538.2
14°	1449.6
15°	1354.6
16°	1253.0
17°	1146.2
18°	1035.9
19°	927.8
20°	823.2
21°	723.7
22°	616.9
23°	507.5
24°	403.3
25°	310.0
26°	228.8
27°	161.9
28°	115.5
29°	91.6
30°	80.8
32.5°	61.2
35°	44.7
37.5°	36.5
40°	33.4
42.5°	32.1
45°	31.3
47.5°	30.8
50°	30.0
52.5°	28.7
55°	27.4
57.5°	25.6
60°	23.4
62.5°	21.3
65°	18.2



TEST NUMBER: P220474

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-F-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	15.2
70°	12.6
72.5°	10.4
75°	8.7
77.5°	7.8
80°	6.5
82.5°	4.8
85°	3.0
87.5°	1.3
90°	0.0

(END OF REPORT)