

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220574

Luminaire Tested: **1003-[A1, S1, SU1]-FL-LED2797-S-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29476)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-FL-LED2797-S-WT-L1-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, FLUSH LENS, SPOT OPTIC, WHITE HOUSING.
Light Source: (1) 2700K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 644.6 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220574

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2797-S-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220574

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2797-S-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	104	103	102	101	100	99	99	97
2	111	108	105	103	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	104	100	97	106	102	99	97	100	97	95	98	95	94	95	94	92	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	88	91	89	87	86
6	99	93	89	86	98	93	89	86	91	88	86	90	87	85	89	86	85	83
7	97	90	86	84	96	90	86	83	89	85	83	88	85	83	87	84	82	81
8	94	88	84	81	93	87	84	81	87	83	81	86	83	81	85	82	80	79
9	92	86	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	77
10	90	83	80	77	89	83	79	77	82	79	77	82	79	77	81	78	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1071690
5°	832069
10°	355460
15°	150307
20°	99642
25°	74690
30°	28612
35°	4363
40°	2376
45°	1054
50°	785
55°	726
60°	833
65°	778
70°	705
75°	678
80°	505
85°	1006



TEST NUMBER: P220574

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2797-S-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	285.7	44.3
10°-20°	202.4	31.4
20°-30°	130.5	20.2
30°-40°	18.8	2.9
40°-50°	3.0	0.5
50°-60°	1.8	0.3
60°-70°	1.4	0.2
70°-80°	0.7	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	618.6	96.0
0°-40°	637.4	98.9
0°-60°	642.2	99.6
0°-90°	644.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	644.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4887	
5°	3780	286
15°	662	202
25°	309	130
35°	16	19
45°	3	3
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220574

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2797-S-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	4887.3
1°	4826.2
2°	4691.3
3°	4469.4
4°	4160.8
5°	3780.1
6°	3342.5
7°	2885.6
8°	2433.6
9°	1986.9
10°	1596.4
11°	1277.5
12°	1047.7
13°	879.7
14°	755.0
15°	662.1
16°	585.5
17°	529.7
18°	489.9
19°	455.0
20°	427.0
21°	402.7
22°	381.5
23°	361.7
24°	339.0
25°	308.7
26°	273.0
27°	234.7
28°	193.0
29°	151.7
30°	113.0
32.5°	37.5
35°	16.3
37.5°	11.8
40°	8.3
42.5°	4.2
45°	3.4
47.5°	2.7
50°	2.3
52.5°	2.3
55°	1.9
57.5°	1.9
60°	1.9
62.5°	1.5
65°	1.5



TEST NUMBER: P220574

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED2797-S-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.1
70°	1.1
72.5°	0.8
75°	0.8
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)