

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220693

Luminaire Tested: **1003-[A1, S1, SU1]-FL-LED3090-W-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220693
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29479)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-FL-LED3090-W-BK-L1-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, FLUSH LENS, WIDE FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 705.2 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220693

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-W-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220693

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-W-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	92	90	88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83
4	99	92	87	83	97	91	86	82	88	84	81	87	83	80	85	82	79	78
5	94	86	81	77	93	86	80	77	84	79	76	82	78	75	81	77	75	73
6	90	82	76	72	89	81	76	72	79	75	71	78	74	71	77	73	70	69
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65
8	82	73	68	64	81	73	68	64	72	67	64	71	66	63	70	66	63	62
9	79	70	64	61	78	69	64	60	68	64	60	68	63	60	67	63	60	59
10	75	66	61	57	75	66	61	57	65	60	57	64	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	230596
5°	232335
10°	219502
15°	188832
20°	162087
25°	134137
30°	71555
35°	32551
40°	20810
45°	13676
50°	9586
55°	4817
60°	1140
65°	1141
70°	1090
75°	763
80°	505
85°	1006



TEST NUMBER: P220693

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-W-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.6	14.0
10°-20°	232.6	33.0
20°-30°	237.7	33.7
30°-40°	86.1	12.2
40°-50°	35.4	5.0
50°-60°	11.5	1.6
60°-70°	2.0	0.3
70°-80°	1.0	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	569.0	80.7
0°-40°	655.0	92.9
0°-60°	702.0	99.5
0°-90°	705.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	705.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1052	
5°	1056	99
15°	832	233
25°	554	238
35°	122	86
45°	44	35
55°	13	11
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220693

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-W-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	1051.6
1°	1048.6
2°	1049.0
3°	1052.9
4°	1056.4
5°	1055.5
6°	1052.5
7°	1043.0
8°	1027.8
9°	1007.9
10°	985.8
11°	959.5
12°	930.5
13°	898.0
14°	864.2
15°	831.8
16°	800.6
17°	773.4
18°	748.3
19°	720.6
20°	694.6
21°	669.9
22°	645.7
23°	622.3
24°	594.6
25°	554.4
26°	505.0
27°	451.4
28°	394.7
29°	337.6
30°	282.6
32.5°	169.6
35°	121.6
37.5°	93.9
40°	72.7
42.5°	55.4
45°	44.1
47.5°	35.5
50°	28.1
52.5°	20.8
55°	12.6
57.5°	3.5
60°	2.6
62.5°	2.2
65°	2.2



TEST NUMBER: P220693

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-W-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.7
70°	1.7
72.5°	1.3
75°	0.9
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)