

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information


Test Method: LM-79-08
Report Number: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29472)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS, SPOT OPTIC, BLACK HOUSING.
Light Source: (1) 2700K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A	NEMA Type:	3H x 3V
Luminaire Lumens:	574.9 lumens	Max Intensity:	4934.7 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	58.7 lumens/watt		
Luminous Opening:	Circular (Dia: 0.25' x H: 0')		
Beam Angle (50%):	15.7°H x 15.7°V	Field Angle (10%):	35°H x 35°V
Beam Lumens:	204.9 lumens	Field Lumens:	440.4 lumens
Beam Efficiency:	35.6%	Field Efficiency:	76.6%
Input Watts (W):	9.8		
Input Voltage (V):	120		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

Iso-Candela Plot






REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	
40		0.0	0.0	0.1	0.1	0.1	0.2	0.3	0.3	0.2	0.1	0.1	0.1	0.0	0.0		
30	0.0	0.0	0.0	0.1	0.1	0.3	1.8	5.0	5.0	1.8	0.3	0.1	0.1	0.0	0.0	0.0	
20		0.0	0.0	0.1	0.2	1.7	10.4	19.7	19.7	10.4	1.7	0.2	0.1	0.0	0.0		
10	0.0	0.0	0.0	0.1	0.3	4.7	19.1	78.5	78.5	19.1	4.7	0.3	0.1	0.0	0.0	0.0	
0		0.0	0.0	0.1	0.3	4.7	19.1	78.5	78.5	19.1	4.7	0.3	0.1	0.0	0.0		
-10	0.0	0.0	0.0	0.1	0.3	4.7	19.1	78.5	78.5	19.1	4.7	0.3	0.1	0.0	0.0	0.0	
-20		0.0	0.0	0.1	0.2	1.7	10.4	19.7	19.7	10.4	1.7	0.2	0.1	0.0	0.0		
-30	0.0	0.0	0.0	0.1	0.1	0.3	1.8	5.0	5.0	1.8	0.3	0.1	0.1	0.0	0.0	0.0	
-40		0.0	0.0	0.1	0.1	0.1	0.2	0.3	0.3	0.2	0.1	0.1	0.1	0.0	0.0		
-50	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	


REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

Luminous Intensity Polar Plot



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

Luminous Intensity Plot



Beam:
H Angle: 15.7°
V Angle: 15.7°
Lumens: 204.9
Efficiency: 35.6%

Field:
H Angle: 35°
V Angle: 35°
Lumens: 440.4
Efficiency: 76.6%

Spill:
Lumens: 134.5
Efficiency: 23.4%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 0-Deg



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	1
35°	0	0	0	0	0	0	0	0	0	0	1



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	0	0	0	0	0	0	0	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
31.25°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	0	1	1
28.75°	0	0	0	0	0	0	0	0	1	1	1
27.5°	0	0	0	0	0	0	0	0	1	1	1
26.25°	0	0	0	0	0	0	0	0	1	1	1
25°	0	0	0	0	0	0	0	0	1	1	1
23.75°	0	0	0	0	0	0	0	0	1	1	1
22.5°	0	0	0	0	0	0	0	1	1	1	1
21.25°	0	0	0	0	0	0	0	1	1	1	1
20°	0	0	0	0	0	0	0	1	1	1	1
18.75°	0	0	0	0	0	0	0	1	1	1	1
17.5°	0	0	0	0	0	0	0	1	1	1	1
16.25°	0	0	0	0	0	0	0	1	1	1	1
15°	0	0	0	0	0	0	0	1	1	1	1
13.75°	0	0	0	0	0	0	0	1	1	1	1
12.5°	0	0	0	0	0	0	1	1	1	1	1
11.25°	0	0	0	0	0	0	1	1	1	1	1
10°	0	0	0	0	0	0	1	1	1	1	1
8.75°	0	0	0	0	0	0	1	1	1	1	1
7.5°	0	0	0	0	0	0	1	1	1	1	1
6.25°	0	0	0	0	0	0	1	1	1	1	1
5°	0	0	0	0	0	0	1	1	1	1	1
3.75°	0	0	0	0	0	0	1	1	1	1	1
2.5°	0	0	0	0	0	0	1	1	1	1	1
1.25°	0	0	0	0	0	0	1	1	1	1	1
0°	0	0	0	0	0	0	1	1	1	1	1
-1.25°	0	0	0	0	0	0	1	1	1	1	1
-2.5°	0	0	0	0	0	0	1	1	1	1	1
-3.75°	0	0	0	0	0	0	1	1	1	1	1
-5°	0	0	0	0	0	0	1	1	1	1	1
-6.25°	0	0	0	0	0	0	1	1	1	1	1
-7.5°	0	0	0	0	0	0	1	1	1	1	1
-8.75°	0	0	0	0	0	0	1	1	1	1	1
-10°	0	0	0	0	0	0	1	1	1	1	1
-11.25°	0	0	0	0	0	0	1	1	1	1	1
-12.5°	0	0	0	0	0	0	1	1	1	1	1
-13.75°	0	0	0	0	0	0	0	1	1	1	1
-15°	0	0	0	0	0	0	0	1	1	1	1
-16.25°	0	0	0	0	0	0	0	1	1	1	1
-17.5°	0	0	0	0	0	0	0	1	1	1	1
-18.75°	0	0	0	0	0	0	0	1	1	1	1
-20°	0	0	0	0	0	0	0	1	1	1	1
-21.25°	0	0	0	0	0	0	0	1	1	1	1



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	0	0	0	0	0	1	1	1	1
-23.75°	0	0	0	0	0	0	0	0	1	1	1
-25°	0	0	0	0	0	0	0	0	1	1	1
-26.25°	0	0	0	0	0	0	0	0	1	1	1
-27.5°	0	0	0	0	0	0	0	0	1	1	1
-28.75°	0	0	0	0	0	0	0	0	1	1	1
-30°	0	0	0	0	0	0	0	0	0	1	1
-31.25°	0	0	0	0	0	0	0	0	0	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-33.75°	0	0	0	0	0	0	0	0	0	0	1
-35°	0	0	0	0	0	0	0	0	0	0	1
-36.25°	0	0	0	0	0	0	0	0	0	0	1
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	1
55°	0	0	0	0	0	0	0	0	0	1	1
53.75°	0	0	0	0	0	0	0	0	1	1	1
52.5°	0	0	0	0	0	0	0	1	1	1	1
51.25°	0	0	0	0	0	0	1	1	1	1	1
50°	0	0	0	0	0	1	1	1	1	1	1
48.75°	0	0	0	0	1	1	1	1	1	1	1
47.5°	0	0	0	0	1	1	1	1	1	1	1
46.25°	0	0	0	1	1	1	1	1	1	1	1
45°	0	0	1	1	1	1	1	1	1	1	1
43.75°	0	0	1	1	1	1	1	1	1	1	2
42.5°	0	1	1	1	1	1	1	1	1	1	2
41.25°	0	1	1	1	1	1	1	1	1	2	2
40°	1	1	1	1	1	1	1	1	2	2	2
38.75°	1	1	1	1	1	1	1	1	2	2	2
37.5°	1	1	1	1	1	1	1	2	2	2	2
36.25°	1	1	1	1	1	1	2	2	2	2	2
35°	1	1	1	1	1	1	2	2	2	2	2



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	1	1	1	2	2	2	2	2	2
32.5°	1	1	1	1	1	2	2	2	2	2	2
31.25°	1	1	1	1	1	2	2	2	2	2	2
30°	1	1	1	1	2	2	2	2	2	2	3
28.75°	1	1	1	1	2	2	2	2	2	2	3
27.5°	1	1	1	1	2	2	2	2	2	2	3
26.25°	1	1	1	2	2	2	2	2	2	3	3
25°	1	1	1	2	2	2	2	2	2	3	3
23.75°	1	1	1	2	2	2	2	2	3	3	3
22.5°	1	1	2	2	2	2	2	2	3	3	3
21.25°	1	1	2	2	2	2	2	2	3	3	3
20°	1	1	2	2	2	2	2	3	3	3	3
18.75°	1	1	2	2	2	2	2	3	3	3	3
17.5°	1	1	2	2	2	2	2	3	3	3	3
16.25°	1	2	2	2	2	2	2	3	3	3	3
15°	1	2	2	2	2	2	2	3	3	3	3
13.75°	1	2	2	2	2	2	3	3	3	3	3
12.5°	1	2	2	2	2	2	3	3	3	3	3
11.25°	1	2	2	2	2	2	3	3	3	3	3
10°	1	2	2	2	2	2	3	3	3	3	3
8.75°	1	2	2	2	2	2	3	3	3	3	3
7.5°	1	2	2	2	2	2	3	3	3	3	3
6.25°	1	2	2	2	2	2	3	3	3	3	3
5°	1	2	2	2	2	2	3	3	3	3	3
3.75°	1	2	2	2	2	2	3	3	3	3	3
2.5°	1	2	2	2	2	2	3	3	3	3	3
1.25°	1	2	2	2	2	2	3	3	3	3	3
0°	2	2	2	2	2	3	3	3	3	3	3
-1.25°	1	2	2	2	2	2	3	3	3	3	3
-2.5°	1	2	2	2	2	2	3	3	3	3	3
-3.75°	1	2	2	2	2	2	3	3	3	3	3
-5°	1	2	2	2	2	2	3	3	3	3	3
-6.25°	1	2	2	2	2	2	3	3	3	3	3
-7.5°	1	2	2	2	2	2	3	3	3	3	3
-8.75°	1	2	2	2	2	2	3	3	3	3	3
-10°	1	2	2	2	2	2	3	3	3	3	3
-11.25°	1	2	2	2	2	2	3	3	3	3	3
-12.5°	1	2	2	2	2	2	3	3	3	3	3
-13.75°	1	2	2	2	2	2	3	3	3	3	3
-15°	1	2	2	2	2	2	2	3	3	3	3
-16.25°	1	2	2	2	2	2	2	3	3	3	3
-17.5°	1	1	2	2	2	2	2	3	3	3	3
-18.75°	1	1	2	2	2	2	2	3	3	3	3
-20°	1	1	2	2	2	2	2	3	3	3	3
-21.25°	1	1	2	2	2	2	2	2	3	3	3



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	1	1	2	2	2	2	2	2	3	3	3
-23.75°	1	1	1	2	2	2	2	2	3	3	3
-25°	1	1	1	2	2	2	2	2	2	3	3
-26.25°	1	1	1	2	2	2	2	2	2	3	3
-27.5°	1	1	1	1	2	2	2	2	2	2	3
-28.75°	1	1	1	1	2	2	2	2	2	2	3
-30°	1	1	1	1	2	2	2	2	2	2	3
-31.25°	1	1	1	1	1	2	2	2	2	2	2
-32.5°	1	1	1	1	1	2	2	2	2	2	2
-33.75°	1	1	1	1	1	2	2	2	2	2	2
-35°	1	1	1	1	1	1	2	2	2	2	2
-36.25°	1	1	1	1	1	1	2	2	2	2	2
-37.5°	1	1	1	1	1	1	1	2	2	2	2
-38.75°	1	1	1	1	1	1	1	1	2	2	2
-40°	1	1	1	1	1	1	1	1	2	2	2
-41.25°	0	1	1	1	1	1	1	1	1	2	2
-42.5°	0	1	1	1	1	1	1	1	1	1	2
-43.75°	0	0	1	1	1	1	1	1	1	1	2
-45°	0	0	1	1	1	1	1	1	1	1	1
-46.25°	0	0	0	1	1	1	1	1	1	1	1
-47.5°	0	0	0	0	1	1	1	1	1	1	1
-48.75°	0	0	0	0	1	1	1	1	1	1	1
-50°	0	0	0	0	0	1	1	1	1	1	1
-51.25°	0	0	0	0	0	0	1	1	1	1	1
-52.5°	0	0	0	0	0	0	0	1	1	1	1
-53.75°	0	0	0	0	0	0	0	0	1	1	1
-55°	0	0	0	0	0	0	0	0	0	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	1
62.5°	0	0	0	0	0	0	0	1	1	1	1
61.25°	0	0	0	0	0	1	1	1	1	1	1
60°	0	0	0	1	1	1	1	1	1	1	1
58.75°	0	0	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	2
53.75°	1	1	1	1	1	1	1	1	1	2	2
52.5°	1	1	1	1	1	1	1	2	2	2	2
51.25°	1	1	1	1	1	1	2	2	2	2	2
50°	1	1	1	1	2	2	2	2	2	2	2
48.75°	1	1	1	2	2	2	2	2	2	2	2
47.5°	1	1	2	2	2	2	2	2	2	2	2
46.25°	1	2	2	2	2	2	2	2	2	2	3
45°	2	2	2	2	2	2	2	2	2	3	3
43.75°	2	2	2	2	2	2	2	2	3	3	3
42.5°	2	2	2	2	2	2	2	3	3	3	3
41.25°	2	2	2	2	2	2	3	3	3	3	3
40°	2	2	2	2	2	3	3	3	3	3	3
38.75°	2	2	2	2	3	3	3	3	3	3	3
37.5°	2	2	2	3	3	3	3	3	3	3	3
36.25°	2	2	3	3	3	3	3	3	3	3	3
35°	2	2	3	3	3	3	3	3	3	3	3



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	2	3	3	3	3	3	3	3	3	3	3
32.5°	3	3	3	3	3	3	3	3	3	3	3
31.25°	3	3	3	3	3	3	3	3	3	3	4
30°	3	3	3	3	3	3	3	3	3	4	4
28.75°	3	3	3	3	3	3	3	3	4	4	4
27.5°	3	3	3	3	3	3	3	3	4	4	4
26.25°	3	3	3	3	3	3	3	4	4	4	4
25°	3	3	3	3	3	3	3	4	4	4	4
23.75°	3	3	3	3	3	3	4	4	4	4	5
22.5°	3	3	3	3	3	3	4	4	4	4	5
21.25°	3	3	3	3	3	4	4	4	4	5	5
20°	3	3	3	3	3	4	4	4	4	5	5
18.75°	3	3	3	3	4	4	4	4	5	5	5
17.5°	3	3	3	3	4	4	4	4	5	5	5
16.25°	3	3	3	3	4	4	4	4	5	5	6
15°	3	3	3	3	4	4	4	4	5	5	6
13.75°	3	3	3	4	4	4	4	4	5	5	6
12.5°	3	3	3	4	4	4	4	5	5	6	6
11.25°	3	3	3	4	4	4	4	5	5	6	6
10°	3	3	3	4	4	4	4	5	5	6	6
8.75°	3	3	3	4	4	4	4	5	5	6	6
7.5°	3	3	4	4	4	4	4	5	5	6	7
6.25°	3	3	4	4	4	4	4	5	5	6	7
5°	3	3	4	4	4	4	5	5	5	6	7
3.75°	3	3	4	4	4	4	5	5	5	6	7
2.5°	3	3	4	4	4	4	5	5	5	6	7
1.25°	3	3	4	4	4	4	5	5	5	6	7
0°	3	3	4	4	4	5	5	5	6	6	7
-1.25°	3	3	4	4	4	5	5	5	6	6	7
-2.5°	3	3	4	4	4	5	5	5	6	6	7
-3.75°	3	3	4	4	4	5	5	5	6	6	7
-5°	3	3	4	4	4	5	5	5	6	6	7
-6.25°	3	3	4	4	4	4	5	5	6	6	7
-7.5°	3	3	4	4	4	4	5	5	6	6	7
-8.75°	3	3	3	4	4	4	4	5	5	6	6
-10°	3	3	3	4	4	4	4	5	5	6	6
-11.25°	3	3	3	4	4	4	4	5	5	6	6
-12.5°	3	3	3	4	4	4	4	5	5	6	6
-13.75°	3	3	3	4	4	4	4	4	5	5	6
-15°	3	3	3	3	4	4	4	4	5	5	6
-16.25°	3	3	3	3	4	4	4	4	5	5	6
-17.5°	3	3	3	3	4	4	4	4	4	5	5
-18.75°	3	3	3	3	4	4	4	4	4	5	5
-20°	3	3	3	3	3	4	4	4	4	5	5
-21.25°	3	3	3	3	3	4	4	4	4	5	5



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	3	3	3	3	3	3	4	4	4	4	5
-23.75°	3	3	3	3	3	3	4	4	4	4	5
-25°	3	3	3	3	3	3	3	4	4	4	4
-26.25°	3	3	3	3	3	3	3	4	4	4	4
-27.5°	3	3	3	3	3	3	3	3	4	4	4
-28.75°	3	3	3	3	3	3	3	3	4	4	4
-30°	3	3	3	3	3	3	3	3	3	4	4
-31.25°	3	3	3	3	3	3	3	3	3	3	4
-32.5°	3	3	3	3	3	3	3	3	3	3	3
-33.75°	2	3	3	3	3	3	3	3	3	3	3
-35°	2	2	3	3	3	3	3	3	3	3	3
-36.25°	2	2	3	3	3	3	3	3	3	3	3
-37.5°	2	2	2	3	3	3	3	3	3	3	3
-38.75°	2	2	2	2	3	3	3	3	3	3	3
-40°	2	2	2	2	2	3	3	3	3	3	3
-41.25°	2	2	2	2	2	2	3	3	3	3	3
-42.5°	2	2	2	2	2	2	2	3	3	3	3
-43.75°	2	2	2	2	2	2	2	2	3	3	3
-45°	2	2	2	2	2	2	2	2	2	3	3
-46.25°	1	2	2	2	2	2	2	2	2	2	3
-47.5°	1	1	2	2	2	2	2	2	2	2	2
-48.75°	1	1	1	2	2	2	2	2	2	2	2
-50°	1	1	1	1	2	2	2	2	2	2	2
-51.25°	1	1	1	1	1	1	2	2	2	2	2
-52.5°	1	1	1	1	1	1	1	2	2	2	2
-53.75°	1	1	1	1	1	1	1	1	1	2	2
-55°	1	1	1	1	1	1	1	1	1	1	2
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	0	0	1	1	1	1	1	1	1	1	1
-60°	0	0	0	1	1	1	1	1	1	1	1
-61.25°	0	0	0	0	0	1	1	1	1	1	1
-62.5°	0	0	0	0	0	0	0	1	1	1	1
-63.75°	0	0	0	0	0	0	0	0	0	0	1
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	1
66.25°	0	0	0	0	0	1	1	1	1	1	1
65°	0	0	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	2
58.75°	1	1	1	1	1	1	1	2	2	2	2
57.5°	1	1	1	1	2	2	2	2	2	2	2
56.25°	1	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	2
53.75°	2	2	2	2	2	2	2	2	2	2	2
52.5°	2	2	2	2	2	2	2	2	2	3	3
51.25°	2	2	2	2	2	2	2	3	3	3	3
50°	2	2	2	2	3	3	3	3	3	3	3
48.75°	2	2	3	3	3	3	3	3	3	3	3
47.5°	2	3	3	3	3	3	3	3	3	3	3
46.25°	3	3	3	3	3	3	3	3	3	3	3
45°	3	3	3	3	3	3	3	3	3	3	3
43.75°	3	3	3	3	3	3	3	3	3	3	3
42.5°	3	3	3	3	3	3	3	3	3	3	3
41.25°	3	3	3	3	3	3	3	3	3	4	4
40°	3	3	3	3	3	3	3	4	4	4	4
38.75°	3	3	3	3	3	4	4	4	4	4	4
37.5°	3	3	3	3	4	4	4	4	4	4	4
36.25°	3	3	3	4	4	4	4	4	4	5	5
35°	3	3	4	4	4	4	4	5	5	5	5



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	3	4	4	4	4	4	5	5	5	5	5
32.5°	4	4	4	4	4	5	5	5	5	5	6
31.25°	4	4	4	4	5	5	5	5	6	6	6
30°	4	4	4	5	5	5	5	6	6	6	7
28.75°	4	4	5	5	5	5	6	6	6	7	7
27.5°	4	5	5	5	5	6	6	6	7	7	8
26.25°	5	5	5	5	6	6	6	7	8	8	10
25°	5	5	5	6	6	6	7	8	9	11	13
23.75°	5	5	5	6	6	7	7	8	11	13	15
22.5°	5	5	6	6	7	7	8	10	13	15	18
21.25°	5	6	6	6	7	8	10	12	15	18	21
20°	5	6	6	7	8	9	12	14	17	20	24
18.75°	6	6	6	7	8	11	13	16	20	23	27
17.5°	6	6	7	8	10	12	15	19	22	26	37
16.25°	6	6	7	8	11	14	17	21	25	33	56
15°	6	7	8	10	13	16	19	23	28	45	80
13.75°	6	7	8	11	14	17	21	25	36	64	111
12.5°	7	7	9	12	15	19	22	28	48	88	142
11.25°	7	8	10	13	16	20	24	35	64	113	172
10°	7	8	11	14	18	21	26	41	81	138	202
8.75°	7	9	12	15	19	23	30	54	101	161	229
7.5°	7	9	12	16	20	24	35	65	119	182	253
6.25°	8	10	13	17	21	25	38	75	135	202	274
5°	8	10	14	17	21	26	43	87	148	218	291
3.75°	8	11	14	18	22	27	49	96	159	231	303
2.5°	8	11	14	18	22	29	53	103	167	240	312
1.25°	8	11	14	18	22	30	55	107	171	246	317
0°	8	11	14	18	22	30	56	108	173	247	319
-1.25°	8	11	14	18	22	30	55	107	171	246	317
-2.5°	8	11	14	18	22	29	53	103	167	240	312
-3.75°	8	11	14	18	22	27	49	96	159	231	303
-5°	8	10	14	17	21	26	43	87	148	218	291
-6.25°	8	10	13	17	21	25	38	75	135	202	274
-7.5°	7	9	12	16	20	24	35	65	119	182	253
-8.75°	7	9	12	15	19	23	30	54	101	161	229
-10°	7	8	11	14	18	21	26	41	81	138	202
-11.25°	7	8	10	13	16	20	24	35	64	113	172
-12.5°	7	7	9	12	15	19	22	28	48	88	142
-13.75°	6	7	8	11	14	17	21	25	36	64	111
-15°	6	7	8	10	13	16	19	23	28	45	80
-16.25°	6	6	7	8	11	14	17	21	25	33	56
-17.5°	6	6	7	8	10	12	15	19	22	26	37
-18.75°	6	6	6	7	8	11	13	16	20	23	27
-20°	5	6	6	7	8	9	12	14	17	20	24
-21.25°	5	6	6	6	7	8	10	12	15	18	21



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	5	5	6	6	7	7	8	10	13	15	18
-23.75°	5	5	5	6	6	7	7	8	11	13	15
-25°	5	5	5	6	6	6	7	8	9	11	13
-26.25°	5	5	5	5	6	6	6	7	8	8	10
-27.5°	4	5	5	5	5	6	6	6	7	7	8
-28.75°	4	4	5	5	5	5	6	6	6	7	7
-30°	4	4	4	5	5	5	5	6	6	6	7
-31.25°	4	4	4	4	5	5	5	5	6	6	6
-32.5°	4	4	4	4	4	5	5	5	5	5	6
-33.75°	3	4	4	4	4	4	5	5	5	5	5
-35°	3	3	4	4	4	4	4	5	5	5	5
-36.25°	3	3	3	4	4	4	4	4	4	5	5
-37.5°	3	3	3	3	4	4	4	4	4	4	4
-38.75°	3	3	3	3	3	4	4	4	4	4	4
-40°	3	3	3	3	3	3	3	4	4	4	4
-41.25°	3	3	3	3	3	3	3	3	3	4	4
-42.5°	3	3	3	3	3	3	3	3	3	3	3
-43.75°	3	3	3	3	3	3	3	3	3	3	3
-45°	3	3	3	3	3	3	3	3	3	3	3
-46.25°	3	3	3	3	3	3	3	3	3	3	3
-47.5°	2	3	3	3	3	3	3	3	3	3	3
-48.75°	2	2	3	3	3	3	3	3	3	3	3
-50°	2	2	2	2	3	3	3	3	3	3	3
-51.25°	2	2	2	2	2	2	2	3	3	3	3
-52.5°	2	2	2	2	2	2	2	2	2	3	3
-53.75°	2	2	2	2	2	2	2	2	2	2	2
-55°	2	2	2	2	2	2	2	2	2	2	2
-56.25°	1	2	2	2	2	2	2	2	2	2	2
-57.5°	1	1	1	1	2	2	2	2	2	2	2
-58.75°	1	1	1	1	1	1	1	2	2	2	2
-60°	1	1	1	1	1	1	1	1	1	1	2
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	0	0	1	1	1	1	1	1	1	1	1
-66.25°	0	0	0	0	0	1	1	1	1	1	1
-67.5°	0	0	0	0	0	0	0	0	0	0	1
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	3	3	3	3	3
53.75°	2	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	3
47.5°	3	3	3	3	3	3	3	3	3	3	3
46.25°	3	3	3	3	3	3	3	3	3	3	3
45°	3	3	3	3	3	3	4	4	4	4	4
43.75°	3	3	4	4	4	4	4	4	4	4	4
42.5°	4	4	4	4	4	4	4	4	4	4	4
41.25°	4	4	4	4	4	4	4	5	5	5	5
40°	4	4	4	4	5	5	5	5	5	5	5
38.75°	4	4	5	5	5	5	5	5	5	5	5
37.5°	5	5	5	5	5	5	5	6	6	6	6
36.25°	5	5	5	5	6	6	6	6	6	6	6
35°	5	5	6	6	6	6	6	7	7	7	7



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	6	6	6	6	6	7	7	7	8	8	9
32.5°	6	6	6	7	7	8	8	9	10	11	12
31.25°	6	7	7	8	8	10	11	12	13	14	15
30°	7	8	8	10	11	13	14	15	16	18	19
28.75°	8	9	11	12	14	16	17	19	20	21	23
27.5°	10	12	13	15	17	19	21	22	24	26	30
26.25°	12	14	16	19	21	23	25	28	35	41	54
25°	15	17	20	22	25	28	36	48	64	81	101
23.75°	18	20	23	26	33	45	64	88	113	138	161
22.5°	21	24	27	37	56	80	111	142	172	202	229
21.25°	24	29	40	63	95	130	166	202	237	269	297
20°	29	40	67	104	144	184	226	265	301	331	354
18.75°	40	67	107	150	196	242	286	324	354	377	393
17.5°	63	104	150	199	250	298	339	369	391	407	423
16.25°	95	144	196	250	302	346	377	399	418	437	458
15°	130	184	242	298	346	380	403	425	449	474	500
13.75°	166	226	286	339	377	403	427	455	485	516	552
12.5°	202	265	324	369	399	425	455	488	526	569	629
11.25°	237	301	354	391	418	449	485	526	577	646	725
10°	269	331	377	407	437	474	516	569	646	736	836
8.75°	297	354	393	423	458	500	552	629	725	836	975
7.5°	320	372	405	437	478	527	596	692	808	954	1144
6.25°	339	386	417	453	498	554	640	752	892	1084	1337
5°	353	394	426	466	514	582	685	813	984	1220	1541
3.75°	362	401	434	477	531	610	722	863	1067	1357	1748
2.5°	369	405	440	486	543	630	750	910	1141	1469	1908
1.25°	373	408	444	491	550	642	770	940	1187	1538	2016
0°	374	409	446	493	553	647	777	950	1202	1562	2055
-1.25°	373	408	444	491	550	642	770	940	1187	1538	2016
-2.5°	369	405	440	486	543	630	750	910	1141	1469	1908
-3.75°	362	401	434	477	531	610	722	863	1067	1357	1748
-5°	353	394	426	466	514	582	685	813	984	1220	1541
-6.25°	339	386	417	453	498	554	640	752	892	1084	1337
-7.5°	320	372	405	437	478	527	596	692	808	954	1144
-8.75°	297	354	393	423	458	500	552	629	725	836	975
-10°	269	331	377	407	437	474	516	569	646	736	836
-11.25°	237	301	354	391	418	449	485	526	577	646	725
-12.5°	202	265	324	369	399	425	455	488	526	569	629
-13.75°	166	226	286	339	377	403	427	455	485	516	552
-15°	130	184	242	298	346	380	403	425	449	474	500
-16.25°	95	144	196	250	302	346	377	399	418	437	458
-17.5°	63	104	150	199	250	298	339	369	391	407	423
-18.75°	40	67	107	150	196	242	286	324	354	377	393
-20°	29	40	67	104	144	184	226	265	301	331	354
-21.25°	24	29	40	63	95	130	166	202	237	269	297



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	21	24	27	37	56	80	111	142	172	202	229
-23.75°	18	20	23	26	33	45	64	88	113	138	161
-25°	15	17	20	22	25	28	36	48	64	81	101
-26.25°	12	14	16	19	21	23	25	28	35	41	54
-27.5°	10	12	13	15	17	19	21	22	24	26	30
-28.75°	8	9	11	12	14	16	17	19	20	21	23
-30°	7	8	8	10	11	13	14	15	16	18	19
-31.25°	6	7	7	8	8	10	11	12	13	14	15
-32.5°	6	6	6	7	7	8	8	9	10	11	12
-33.75°	6	6	6	6	6	7	7	7	8	8	9
-35°	5	5	6	6	6	6	6	7	7	7	7
-36.25°	5	5	5	5	6	6	6	6	6	6	6
-37.5°	5	5	5	5	5	5	5	6	6	6	6
-38.75°	4	4	5	5	5	5	5	5	5	5	5
-40°	4	4	4	4	5	5	5	5	5	5	5
-41.25°	4	4	4	4	4	4	4	5	5	5	5
-42.5°	4	4	4	4	4	4	4	4	4	4	4
-43.75°	3	3	4	4	4	4	4	4	4	4	4
-45°	3	3	3	3	3	3	4	4	4	4	4
-46.25°	3	3	3	3	3	3	3	3	3	3	3
-47.5°	3	3	3	3	3	3	3	3	3	3	3
-48.75°	3	3	3	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	2	3	3	3	3	3	3	3	3	3	3
-55°	2	2	2	2	2	2	3	3	3	3	3
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	1	1	1	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	0	0	0	0	0	0	0	1	1	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	2	1	1	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	3	2	2	2	2
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	3
47.5°	3	3	3	3	3	3	3	3	3	3	3
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	4	4	4	4	4	4
42.5°	4	4	5	5	5	5	5	5	5	5	5
41.25°	5	5	5	5	5	5	5	5	5	5	5
40°	5	5	5	5	5	5	5	5	5	5	5
38.75°	6	6	6	6	6	6	6	6	6	6	6
37.5°	6	6	6	6	6	6	6	6	6	6	6
36.25°	7	7	7	7	7	7	7	7	7	7	7
35°	7	8	8	8	8	8	8	8	8	8	8



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	9	10	10	11	11	11	11	11	11	11	10
32.5°	12	13	14	14	14	14	14	14	14	14	14
31.25°	16	17	17	18	18	18	18	18	18	18	17
30°	20	21	21	22	22	22	22	22	22	22	21
28.75°	24	25	26	27	29	30	30	30	29	27	26
27.5°	35	38	43	49	53	55	56	55	53	49	43
26.25°	65	75	87	96	103	107	108	107	103	96	87
25°	119	135	148	159	167	171	173	171	167	159	148
23.75°	182	202	218	231	240	246	247	246	240	231	218
22.5°	253	274	291	303	312	317	319	317	312	303	291
21.25°	320	339	353	362	369	373	374	373	369	362	353
20°	372	386	394	401	405	408	409	408	405	401	394
18.75°	405	417	426	434	440	444	446	444	440	434	426
17.5°	437	453	466	477	486	491	493	491	486	477	466
16.25°	478	498	514	531	543	550	553	550	543	531	514
15°	527	554	582	610	630	642	647	642	630	610	582
13.75°	596	640	685	722	750	770	777	770	750	722	685
12.5°	692	752	813	863	910	940	950	940	910	863	813
11.25°	808	892	984	1067	1141	1187	1202	1187	1141	1067	984
10°	954	1084	1220	1357	1469	1538	1562	1538	1469	1357	1220
8.75°	1144	1337	1541	1748	1908	2016	2055	2016	1908	1748	1541
7.5°	1382	1657	1943	2216	2429	2572	2621	2572	2429	2216	1943
6.25°	1657	2020	2384	2724	2985	3150	3208	3150	2985	2724	2384
5°	1943	2384	2828	3209	3506	3698	3766	3698	3506	3209	2828
3.75°	2216	2724	3209	3633	3963	4179	4244	4179	3963	3633	3209
2.5°	2429	2985	3506	3963	4313	4533	4604	4533	4313	3963	3506
1.25°	2572	3150	3698	4179	4533	4759	4835	4759	4533	4179	3698
0°	2621	3208	3766	4244	4604	4835	4935	4835	4604	4244	3766
-1.25°	2572	3150	3698	4179	4533	4759	4835	4759	4533	4179	3698
-2.5°	2429	2985	3506	3963	4313	4533	4604	4533	4313	3963	3506
-3.75°	2216	2724	3209	3633	3963	4179	4244	4179	3963	3633	3209
-5°	1943	2384	2828	3209	3506	3698	3766	3698	3506	3209	2828
-6.25°	1657	2020	2384	2724	2985	3150	3208	3150	2985	2724	2384
-7.5°	1382	1657	1943	2216	2429	2572	2621	2572	2429	2216	1943
-8.75°	1144	1337	1541	1748	1908	2016	2055	2016	1908	1748	1541
-10°	954	1084	1220	1357	1469	1538	1562	1538	1469	1357	1220
-11.25°	808	892	984	1067	1141	1187	1202	1187	1141	1067	984
-12.5°	692	752	813	863	910	940	950	940	910	863	813
-13.75°	596	640	685	722	750	770	777	770	750	722	685
-15°	527	554	582	610	630	642	647	642	630	610	582
-16.25°	478	498	514	531	543	550	553	550	543	531	514
-17.5°	437	453	466	477	486	491	493	491	486	477	466
-18.75°	405	417	426	434	440	444	446	444	440	434	426
-20°	372	386	394	401	405	408	409	408	405	401	394
-21.25°	320	339	353	362	369	373	374	373	369	362	353



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	253	274	291	303	312	317	319	317	312	303	291
-23.75°	182	202	218	231	240	246	247	246	240	231	218
-25°	119	135	148	159	167	171	173	171	167	159	148
-26.25°	65	75	87	96	103	107	108	107	103	96	87
-27.5°	35	38	43	49	53	55	56	55	53	49	43
-28.75°	24	25	26	27	29	30	30	30	29	27	26
-30°	20	21	21	22	22	22	22	22	22	22	21
-31.25°	16	17	17	18	18	18	18	18	18	18	17
-32.5°	12	13	14	14	14	14	14	14	14	14	14
-33.75°	9	10	10	11	11	11	11	11	11	11	10
-35°	7	8	8	8	8	8	8	8	8	8	8
-36.25°	7	7	7	7	7	7	7	7	7	7	7
-37.5°	6	6	6	6	6	6	6	6	6	6	6
-38.75°	6	6	6	6	6	6	6	6	6	6	6
-40°	5	5	5	5	5	5	5	5	5	5	5
-41.25°	5	5	5	5	5	5	5	5	5	5	5
-42.5°	4	4	5	5	5	5	5	5	5	5	5
-43.75°	4	4	4	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	3	3	3	3	3	3	3	3	3	3	3
-48.75°	3	3	3	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	2	2	2	2	2	3	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	1	2	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	1	1	0	0	0	0	0
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	2	2	2	2	2	2	2	2	1	1
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	3	3	3	3	2	2	2	2
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	3
47.5°	3	3	3	3	3	3	3	3	3	3	3
46.25°	4	4	3	3	3	3	3	3	3	3	3
45°	4	4	4	4	4	4	4	3	3	3	3
43.75°	4	4	4	4	4	4	4	4	4	4	4
42.5°	4	4	4	4	4	4	4	4	4	4	4
41.25°	5	5	5	5	5	5	4	4	4	4	4
40°	5	5	5	5	5	5	5	5	5	4	4
38.75°	6	6	5	5	5	5	5	5	5	5	5
37.5°	6	6	6	6	6	6	5	5	5	5	5
36.25°	7	7	6	6	6	6	6	6	6	5	5
35°	8	7	7	7	7	7	6	6	6	6	6



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	10	9	9	8	8	7	7	7	6	6	6
32.5°	13	12	12	11	10	9	8	8	7	7	6
31.25°	17	16	15	14	13	12	11	10	8	8	7
30°	21	20	19	18	16	15	14	13	11	10	8
28.75°	25	24	23	21	20	19	17	16	14	12	11
27.5°	38	35	30	26	24	22	21	19	17	15	13
26.25°	75	65	54	41	35	28	25	23	21	19	16
25°	135	119	101	81	64	48	36	28	25	22	20
23.75°	202	182	161	138	113	88	64	45	33	26	23
22.5°	274	253	229	202	172	142	111	80	56	37	27
21.25°	339	320	297	269	237	202	166	130	95	63	40
20°	386	372	354	331	301	265	226	184	144	104	67
18.75°	417	405	393	377	354	324	286	242	196	150	107
17.5°	453	437	423	407	391	369	339	298	250	199	150
16.25°	498	478	458	437	418	399	377	346	302	250	196
15°	554	527	500	474	449	425	403	380	346	298	242
13.75°	640	596	552	516	485	455	427	403	377	339	286
12.5°	752	692	629	569	526	488	455	425	399	369	324
11.25°	892	808	725	646	577	526	485	449	418	391	354
10°	1084	954	836	736	646	569	516	474	437	407	377
8.75°	1337	1144	975	836	725	629	552	500	458	423	393
7.5°	1657	1382	1144	954	808	692	596	527	478	437	405
6.25°	2020	1657	1337	1084	892	752	640	554	498	453	417
5°	2384	1943	1541	1220	984	813	685	582	514	466	426
3.75°	2724	2216	1748	1357	1067	863	722	610	531	477	434
2.5°	2985	2429	1908	1469	1141	910	750	630	543	486	440
1.25°	3150	2572	2016	1538	1187	940	770	642	550	491	444
0°	3208	2621	2055	1562	1202	950	777	647	553	493	446
-1.25°	3150	2572	2016	1538	1187	940	770	642	550	491	444
-2.5°	2985	2429	1908	1469	1141	910	750	630	543	486	440
-3.75°	2724	2216	1748	1357	1067	863	722	610	531	477	434
-5°	2384	1943	1541	1220	984	813	685	582	514	466	426
-6.25°	2020	1657	1337	1084	892	752	640	554	498	453	417
-7.5°	1657	1382	1144	954	808	692	596	527	478	437	405
-8.75°	1337	1144	975	836	725	629	552	500	458	423	393
-10°	1084	954	836	736	646	569	516	474	437	407	377
-11.25°	892	808	725	646	577	526	485	449	418	391	354
-12.5°	752	692	629	569	526	488	455	425	399	369	324
-13.75°	640	596	552	516	485	455	427	403	377	339	286
-15°	554	527	500	474	449	425	403	380	346	298	242
-16.25°	498	478	458	437	418	399	377	346	302	250	196
-17.5°	453	437	423	407	391	369	339	298	250	199	150
-18.75°	417	405	393	377	354	324	286	242	196	150	107
-20°	386	372	354	331	301	265	226	184	144	104	67
-21.25°	339	320	297	269	237	202	166	130	95	63	40



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	274	253	229	202	172	142	111	80	56	37	27
-23.75°	202	182	161	138	113	88	64	45	33	26	23
-25°	135	119	101	81	64	48	36	28	25	22	20
-26.25°	75	65	54	41	35	28	25	23	21	19	16
-27.5°	38	35	30	26	24	22	21	19	17	15	13
-28.75°	25	24	23	21	20	19	17	16	14	12	11
-30°	21	20	19	18	16	15	14	13	11	10	8
-31.25°	17	16	15	14	13	12	11	10	8	8	7
-32.5°	13	12	12	11	10	9	8	8	7	7	6
-33.75°	10	9	9	8	8	7	7	7	6	6	6
-35°	8	7	7	7	7	7	6	6	6	6	6
-36.25°	7	7	6	6	6	6	6	6	6	5	5
-37.5°	6	6	6	6	6	6	5	5	5	5	5
-38.75°	6	6	5	5	5	5	5	5	5	5	5
-40°	5	5	5	5	5	5	5	5	5	4	4
-41.25°	5	5	5	5	5	5	4	4	4	4	4
-42.5°	4	4	4	4	4	4	4	4	4	4	4
-43.75°	4	4	4	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	3	3	3	3
-46.25°	4	4	3	3	3	3	3	3	3	3	3
-47.5°	3	3	3	3	3	3	3	3	3	3	3
-48.75°	3	3	3	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	1	1	1	0	0	0	0	0	0	0	0
66.25°	1	1	1	1	1	1	1	1	0	0	0
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	2	2	2	1	1	1	1	1	1	1	1
58.75°	2	2	2	2	2	2	1	1	1	1	1
57.5°	2	2	2	2	2	2	2	2	2	1	1
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	2
53.75°	3	2	2	2	2	2	2	2	2	2	2
52.5°	3	3	3	3	2	2	2	2	2	2	2
51.25°	3	3	3	3	3	3	2	2	2	2	2
50°	3	3	3	3	3	3	3	3	3	2	2
48.75°	3	3	3	3	3	3	3	3	3	3	3
47.5°	3	3	3	3	3	3	3	3	3	3	3
46.25°	3	3	3	3	3	3	3	3	3	3	3
45°	3	3	3	3	3	3	3	3	3	3	3
43.75°	3	3	3	3	3	3	3	3	3	3	3
42.5°	4	4	3	3	3	3	3	3	3	3	3
41.25°	4	4	4	4	3	3	3	3	3	3	3
40°	4	4	4	4	4	4	3	3	3	3	3
38.75°	4	4	4	4	4	4	4	4	3	3	3
37.5°	5	5	4	4	4	4	4	4	4	3	3
36.25°	5	5	5	5	4	4	4	4	4	4	3
35°	5	5	5	5	5	5	4	4	4	4	4



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	6	6	5	5	5	5	5	4	4	4	4
32.5°	6	6	6	5	5	5	5	5	4	4	4
31.25°	7	6	6	6	6	5	5	5	5	4	4
30°	8	7	7	6	6	6	5	5	5	5	4
28.75°	9	8	7	7	6	6	6	5	5	5	5
27.5°	12	10	8	7	7	6	6	6	5	5	5
26.25°	14	12	10	8	8	7	6	6	6	5	5
25°	17	15	13	11	9	8	7	6	6	6	5
23.75°	20	18	15	13	11	8	7	7	6	6	5
22.5°	24	21	18	15	13	10	8	7	7	6	6
21.25°	29	24	21	18	15	12	10	8	7	6	6
20°	40	29	24	20	17	14	12	9	8	7	6
18.75°	67	40	27	23	20	16	13	11	8	7	6
17.5°	104	63	37	26	22	19	15	12	10	8	7
16.25°	144	95	56	33	25	21	17	14	11	8	7
15°	184	130	80	45	28	23	19	16	13	10	8
13.75°	226	166	111	64	36	25	21	17	14	11	8
12.5°	265	202	142	88	48	28	22	19	15	12	9
11.25°	301	237	172	113	64	35	24	20	16	13	10
10°	331	269	202	138	81	41	26	21	18	14	11
8.75°	354	297	229	161	101	54	30	23	19	15	12
7.5°	372	320	253	182	119	65	35	24	20	16	12
6.25°	386	339	274	202	135	75	38	25	21	17	13
5°	394	353	291	218	148	87	43	26	21	17	14
3.75°	401	362	303	231	159	96	49	27	22	18	14
2.5°	405	369	312	240	167	103	53	29	22	18	14
1.25°	408	373	317	246	171	107	55	30	22	18	14
0°	409	374	319	247	173	108	56	30	22	18	14
-1.25°	408	373	317	246	171	107	55	30	22	18	14
-2.5°	405	369	312	240	167	103	53	29	22	18	14
-3.75°	401	362	303	231	159	96	49	27	22	18	14
-5°	394	353	291	218	148	87	43	26	21	17	14
-6.25°	386	339	274	202	135	75	38	25	21	17	13
-7.5°	372	320	253	182	119	65	35	24	20	16	12
-8.75°	354	297	229	161	101	54	30	23	19	15	12
-10°	331	269	202	138	81	41	26	21	18	14	11
-11.25°	301	237	172	113	64	35	24	20	16	13	10
-12.5°	265	202	142	88	48	28	22	19	15	12	9
-13.75°	226	166	111	64	36	25	21	17	14	11	8
-15°	184	130	80	45	28	23	19	16	13	10	8
-16.25°	144	95	56	33	25	21	17	14	11	8	7
-17.5°	104	63	37	26	22	19	15	12	10	8	7
-18.75°	67	40	27	23	20	16	13	11	8	7	6
-20°	40	29	24	20	17	14	12	9	8	7	6
-21.25°	29	24	21	18	15	12	10	8	7	6	6



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	24	21	18	15	13	10	8	7	7	6	6
-23.75°	20	18	15	13	11	8	7	7	6	6	5
-25°	17	15	13	11	9	8	7	6	6	6	5
-26.25°	14	12	10	8	8	7	6	6	6	5	5
-27.5°	12	10	8	7	7	6	6	6	5	5	5
-28.75°	9	8	7	7	6	6	6	5	5	5	5
-30°	8	7	7	6	6	6	5	5	5	5	4
-31.25°	7	6	6	6	6	5	5	5	5	4	4
-32.5°	6	6	6	5	5	5	5	5	4	4	4
-33.75°	6	6	5	5	5	5	5	4	4	4	4
-35°	5	5	5	5	5	5	4	4	4	4	4
-36.25°	5	5	5	5	4	4	4	4	4	4	3
-37.5°	5	5	4	4	4	4	4	4	4	3	3
-38.75°	4	4	4	4	4	4	4	4	3	3	3
-40°	4	4	4	4	4	4	3	3	3	3	3
-41.25°	4	4	4	4	3	3	3	3	3	3	3
-42.5°	4	4	3	3	3	3	3	3	3	3	3
-43.75°	3	3	3	3	3	3	3	3	3	3	3
-45°	3	3	3	3	3	3	3	3	3	3	3
-46.25°	3	3	3	3	3	3	3	3	3	3	3
-47.5°	3	3	3	3	3	3	3	3	3	3	3
-48.75°	3	3	3	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	2	2
-51.25°	3	3	3	3	3	3	2	2	2	2	2
-52.5°	3	3	3	3	2	2	2	2	2	2	2
-53.75°	3	2	2	2	2	2	2	2	2	2	2
-55°	2	2	2	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	1	1
-58.75°	2	2	2	2	2	2	1	1	1	1	1
-60°	2	2	2	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	0	0	0
-67.5°	1	1	1	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	1	1	1	0	0	0	0	0	0	0	0
62.5°	1	1	1	1	1	1	0	0	0	0	0
61.25°	1	1	1	1	1	1	1	1	0	0	0
60°	1	1	1	1	1	1	1	1	1	1	0
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	2	1	1	1	1	1	1	1	1	1	1
55°	2	2	2	1	1	1	1	1	1	1	1
53.75°	2	2	2	2	1	1	1	1	1	1	1
52.5°	2	2	2	2	2	2	1	1	1	1	1
51.25°	2	2	2	2	2	2	2	1	1	1	1
50°	2	2	2	2	2	2	2	2	2	1	1
48.75°	2	2	2	2	2	2	2	2	2	2	1
47.5°	3	2	2	2	2	2	2	2	2	2	2
46.25°	3	3	3	2	2	2	2	2	2	2	2
45°	3	3	3	3	2	2	2	2	2	2	2
43.75°	3	3	3	3	3	2	2	2	2	2	2
42.5°	3	3	3	3	3	3	2	2	2	2	2
41.25°	3	3	3	3	3	3	3	2	2	2	2
40°	3	3	3	3	3	3	3	3	2	2	2
38.75°	3	3	3	3	3	3	3	3	3	2	2
37.5°	3	3	3	3	3	3	3	3	3	3	2
36.25°	3	3	3	3	3	3	3	3	3	3	3
35°	3	3	3	3	3	3	3	3	3	3	3



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	4	3	3	3	3	3	3	3	3	3	3
32.5°	4	4	3	3	3	3	3	3	3	3	3
31.25°	4	4	4	3	3	3	3	3	3	3	3
30°	4	4	4	4	3	3	3	3	3	3	3
28.75°	4	4	4	4	4	3	3	3	3	3	3
27.5°	5	4	4	4	4	3	3	3	3	3	3
26.25°	5	5	4	4	4	4	3	3	3	3	3
25°	5	5	4	4	4	4	3	3	3	3	3
23.75°	5	5	5	4	4	4	4	3	3	3	3
22.5°	5	5	5	4	4	4	4	3	3	3	3
21.25°	6	5	5	5	4	4	4	4	3	3	3
20°	6	5	5	5	4	4	4	4	3	3	3
18.75°	6	6	5	5	5	4	4	4	4	3	3
17.5°	6	6	5	5	5	4	4	4	4	3	3
16.25°	6	6	6	5	5	5	4	4	4	3	3
15°	7	6	6	5	5	5	4	4	4	3	3
13.75°	7	6	6	5	5	5	4	4	4	4	3
12.5°	7	7	6	6	5	5	5	4	4	4	3
11.25°	8	7	6	6	5	5	5	4	4	4	3
10°	8	7	6	6	5	5	5	4	4	4	3
8.75°	9	7	6	6	5	5	5	4	4	4	3
7.5°	9	7	7	6	6	5	5	4	4	4	4
6.25°	10	8	7	6	6	5	5	4	4	4	4
5°	10	8	7	6	6	5	5	5	4	4	4
3.75°	11	8	7	6	6	5	5	5	4	4	4
2.5°	11	8	7	6	6	5	5	5	4	4	4
1.25°	11	8	7	6	6	5	5	5	4	4	4
0°	11	8	7	6	6	5	5	5	4	4	4
-1.25°	11	8	7	6	6	5	5	5	4	4	4
-2.5°	11	8	7	6	6	5	5	5	4	4	4
-3.75°	11	8	7	6	6	5	5	5	4	4	4
-5°	10	8	7	6	6	5	5	5	4	4	4
-6.25°	10	8	7	6	6	5	5	4	4	4	4
-7.5°	9	7	7	6	6	5	5	4	4	4	4
-8.75°	9	7	6	6	5	5	5	4	4	4	3
-10°	8	7	6	6	5	5	5	4	4	4	3
-11.25°	8	7	6	6	5	5	5	4	4	4	3
-12.5°	7	7	6	6	5	5	5	4	4	4	3
-13.75°	7	6	6	5	5	5	4	4	4	4	3
-15°	7	6	6	5	5	5	4	4	4	3	3
-16.25°	6	6	6	5	5	5	4	4	4	3	3
-17.5°	6	6	5	5	5	4	4	4	4	3	3
-18.75°	6	6	5	5	5	4	4	4	4	3	3
-20°	6	5	5	5	4	4	4	4	3	3	3
-21.25°	6	5	5	5	4	4	4	4	3	3	3



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	5	5	5	4	4	4	4	3	3	3	3
-23.75°	5	5	5	4	4	4	4	3	3	3	3
-25°	5	5	4	4	4	4	3	3	3	3	3
-26.25°	5	5	4	4	4	4	3	3	3	3	3
-27.5°	5	4	4	4	4	3	3	3	3	3	3
-28.75°	4	4	4	4	4	3	3	3	3	3	3
-30°	4	4	4	4	3	3	3	3	3	3	3
-31.25°	4	4	4	3	3	3	3	3	3	3	3
-32.5°	4	4	3	3	3	3	3	3	3	3	3
-33.75°	4	3	3	3	3	3	3	3	3	3	3
-35°	3	3	3	3	3	3	3	3	3	3	3
-36.25°	3	3	3	3	3	3	3	3	3	3	3
-37.5°	3	3	3	3	3	3	3	3	3	3	2
-38.75°	3	3	3	3	3	3	3	3	3	2	2
-40°	3	3	3	3	3	3	3	3	2	2	2
-41.25°	3	3	3	3	3	3	3	2	2	2	2
-42.5°	3	3	3	3	3	3	2	2	2	2	2
-43.75°	3	3	3	3	3	2	2	2	2	2	2
-45°	3	3	3	3	2	2	2	2	2	2	2
-46.25°	3	3	3	2	2	2	2	2	2	2	2
-47.5°	3	2	2	2	2	2	2	2	2	2	2
-48.75°	2	2	2	2	2	2	2	2	2	2	1
-50°	2	2	2	2	2	2	2	2	2	1	1
-51.25°	2	2	2	2	2	2	2	1	1	1	1
-52.5°	2	2	2	2	2	2	1	1	1	1	1
-53.75°	2	2	2	2	1	1	1	1	1	1	1
-55°	2	2	2	1	1	1	1	1	1	1	1
-56.25°	2	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	0
-61.25°	1	1	1	1	1	1	1	1	0	0	0
-62.5°	1	1	1	1	1	1	0	0	0	0	0
-63.75°	1	1	1	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	1	1	0	0	0	0	0	0	0	0	0
56.25°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	1	0	0	0	0	0	0	0
53.75°	1	1	1	1	1	0	0	0	0	0	0
52.5°	1	1	1	1	1	1	0	0	0	0	0
51.25°	1	1	1	1	1	1	1	0	0	0	0
50°	1	1	1	1	1	1	1	1	0	0	0
48.75°	1	1	1	1	1	1	1	1	1	0	0
47.5°	1	1	1	1	1	1	1	1	1	0	0
46.25°	2	1	1	1	1	1	1	1	1	1	0
45°	2	2	1	1	1	1	1	1	1	1	1
43.75°	2	2	2	1	1	1	1	1	1	1	1
42.5°	2	2	2	1	1	1	1	1	1	1	1
41.25°	2	2	2	2	1	1	1	1	1	1	1
40°	2	2	2	2	2	1	1	1	1	1	1
38.75°	2	2	2	2	2	1	1	1	1	1	1
37.5°	2	2	2	2	2	2	1	1	1	1	1
36.25°	2	2	2	2	2	2	2	1	1	1	1
35°	2	2	2	2	2	2	2	1	1	1	1



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	3	2	2	2	2	2	2	2	1	1	1
32.5°	3	3	2	2	2	2	2	2	1	1	1
31.25°	3	3	2	2	2	2	2	2	1	1	1
30°	3	3	3	2	2	2	2	2	2	1	1
28.75°	3	3	3	2	2	2	2	2	2	1	1
27.5°	3	3	3	2	2	2	2	2	2	1	1
26.25°	3	3	3	3	2	2	2	2	2	2	1
25°	3	3	3	3	2	2	2	2	2	2	1
23.75°	3	3	3	3	3	2	2	2	2	2	1
22.5°	3	3	3	3	3	2	2	2	2	2	2
21.25°	3	3	3	3	3	2	2	2	2	2	2
20°	3	3	3	3	3	3	2	2	2	2	2
18.75°	3	3	3	3	3	3	2	2	2	2	2
17.5°	3	3	3	3	3	3	2	2	2	2	2
16.25°	3	3	3	3	3	3	2	2	2	2	2
15°	3	3	3	3	3	3	2	2	2	2	2
13.75°	3	3	3	3	3	3	3	2	2	2	2
12.5°	3	3	3	3	3	3	3	2	2	2	2
11.25°	3	3	3	3	3	3	3	2	2	2	2
10°	3	3	3	3	3	3	3	2	2	2	2
8.75°	3	3	3	3	3	3	3	2	2	2	2
7.5°	3	3	3	3	3	3	3	2	2	2	2
6.25°	3	3	3	3	3	3	3	2	2	2	2
5°	3	3	3	3	3	3	3	2	2	2	2
3.75°	3	3	3	3	3	3	3	2	2	2	2
2.5°	3	3	3	3	3	3	3	2	2	2	2
1.25°	3	3	3	3	3	3	3	2	2	2	2
0°	3	3	3	3	3	3	3	3	2	2	2
-1.25°	3	3	3	3	3	3	3	2	2	2	2
-2.5°	3	3	3	3	3	3	3	2	2	2	2
-3.75°	3	3	3	3	3	3	3	2	2	2	2
-5°	3	3	3	3	3	3	3	2	2	2	2
-6.25°	3	3	3	3	3	3	3	2	2	2	2
-7.5°	3	3	3	3	3	3	3	2	2	2	2
-8.75°	3	3	3	3	3	3	3	2	2	2	2
-10°	3	3	3	3	3	3	3	2	2	2	2
-11.25°	3	3	3	3	3	3	3	2	2	2	2
-12.5°	3	3	3	3	3	3	3	2	2	2	2
-13.75°	3	3	3	3	3	3	3	2	2	2	2
-15°	3	3	3	3	3	3	2	2	2	2	2
-16.25°	3	3	3	3	3	3	2	2	2	2	2
-17.5°	3	3	3	3	3	3	2	2	2	2	2
-18.75°	3	3	3	3	3	3	2	2	2	2	2
-20°	3	3	3	3	3	3	2	2	2	2	2
-21.25°	3	3	3	3	3	2	2	2	2	2	2



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	3	3	3	3	3	2	2	2	2	2	2
-23.75°	3	3	3	3	3	2	2	2	2	2	1
-25°	3	3	3	3	2	2	2	2	2	2	1
-26.25°	3	3	3	3	2	2	2	2	2	2	1
-27.5°	3	3	3	2	2	2	2	2	2	1	1
-28.75°	3	3	3	2	2	2	2	2	2	1	1
-30°	3	3	3	2	2	2	2	2	2	1	1
-31.25°	3	3	2	2	2	2	2	2	1	1	1
-32.5°	3	3	2	2	2	2	2	2	1	1	1
-33.75°	3	2	2	2	2	2	2	2	1	1	1
-35°	2	2	2	2	2	2	2	1	1	1	1
-36.25°	2	2	2	2	2	2	2	1	1	1	1
-37.5°	2	2	2	2	2	2	1	1	1	1	1
-38.75°	2	2	2	2	2	1	1	1	1	1	1
-40°	2	2	2	2	2	1	1	1	1	1	1
-41.25°	2	2	2	2	1	1	1	1	1	1	1
-42.5°	2	2	2	1	1	1	1	1	1	1	1
-43.75°	2	2	2	1	1	1	1	1	1	1	1
-45°	2	2	1	1	1	1	1	1	1	1	1
-46.25°	2	1	1	1	1	1	1	1	1	1	0
-47.5°	1	1	1	1	1	1	1	1	1	0	0
-48.75°	1	1	1	1	1	1	1	1	1	0	0
-50°	1	1	1	1	1	1	1	1	0	0	0
-51.25°	1	1	1	1	1	1	1	0	0	0	0
-52.5°	1	1	1	1	1	1	0	0	0	0	0
-53.75°	1	1	1	1	1	0	0	0	0	0	0
-55°	1	1	1	1	0	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	1	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	1	0	0	0	0	0	0	0	0	0	0
41.25°	1	0	0	0	0	0	0	0	0	0	0
40°	1	1	0	0	0	0	0	0	0	0	0
38.75°	1	1	0	0	0	0	0	0	0	0	0
37.5°	1	1	0	0	0	0	0	0	0	0	0
36.25°	1	1	1	0	0	0	0	0	0	0	0
35°	1	1	1	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	0	0	0	0	0	0	0	0
32.5°	1	1	1	1	0	0	0	0	0	0	0
31.25°	1	1	1	1	0	0	0	0	0	0	0
30°	1	1	1	1	0	0	0	0	0	0	0
28.75°	1	1	1	1	1	0	0	0	0	0	0
27.5°	1	1	1	1	1	0	0	0	0	0	0
26.25°	1	1	1	1	1	0	0	0	0	0	0
25°	1	1	1	1	1	0	0	0	0	0	0
23.75°	1	1	1	1	1	0	0	0	0	0	0
22.5°	1	1	1	1	1	1	0	0	0	0	0
21.25°	1	1	1	1	1	1	0	0	0	0	0
20°	1	1	1	1	1	1	0	0	0	0	0
18.75°	1	1	1	1	1	1	0	0	0	0	0
17.5°	1	1	1	1	1	1	0	0	0	0	0
16.25°	2	1	1	1	1	1	0	0	0	0	0
15°	2	1	1	1	1	1	0	0	0	0	0
13.75°	2	1	1	1	1	1	0	0	0	0	0
12.5°	2	1	1	1	1	1	1	0	0	0	0
11.25°	2	1	1	1	1	1	1	0	0	0	0
10°	2	1	1	1	1	1	1	0	0	0	0
8.75°	2	1	1	1	1	1	1	0	0	0	0
7.5°	2	1	1	1	1	1	1	0	0	0	0
6.25°	2	1	1	1	1	1	1	0	0	0	0
5°	2	1	1	1	1	1	1	0	0	0	0
3.75°	2	1	1	1	1	1	1	0	0	0	0
2.5°	2	1	1	1	1	1	1	0	0	0	0
1.25°	2	1	1	1	1	1	1	0	0	0	0
0°	2	2	1	1	1	1	1	0	0	0	0
-1.25°	2	1	1	1	1	1	1	0	0	0	0
-2.5°	2	1	1	1	1	1	1	0	0	0	0
-3.75°	2	1	1	1	1	1	1	0	0	0	0
-5°	2	1	1	1	1	1	1	0	0	0	0
-6.25°	2	1	1	1	1	1	1	0	0	0	0
-7.5°	2	1	1	1	1	1	1	0	0	0	0
-8.75°	2	1	1	1	1	1	1	0	0	0	0
-10°	2	1	1	1	1	1	1	0	0	0	0
-11.25°	2	1	1	1	1	1	1	0	0	0	0
-12.5°	2	1	1	1	1	1	1	0	0	0	0
-13.75°	2	1	1	1	1	1	0	0	0	0	0
-15°	2	1	1	1	1	1	0	0	0	0	0
-16.25°	2	1	1	1	1	1	0	0	0	0	0
-17.5°	1	1	1	1	1	1	0	0	0	0	0
-18.75°	1	1	1	1	1	1	0	0	0	0	0
-20°	1	1	1	1	1	1	0	0	0	0	0
-21.25°	1	1	1	1	1	1	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	1	1	1	1	1	1	0	0	0	0	0
-23.75°	1	1	1	1	1	0	0	0	0	0	0
-25°	1	1	1	1	1	0	0	0	0	0	0
-26.25°	1	1	1	1	1	0	0	0	0	0	0
-27.5°	1	1	1	1	1	0	0	0	0	0	0
-28.75°	1	1	1	1	1	0	0	0	0	0	0
-30°	1	1	1	1	0	0	0	0	0	0	0
-31.25°	1	1	1	1	0	0	0	0	0	0	0
-32.5°	1	1	1	1	0	0	0	0	0	0	0
-33.75°	1	1	1	0	0	0	0	0	0	0	0
-35°	1	1	1	0	0	0	0	0	0	0	0
-36.25°	1	1	1	0	0	0	0	0	0	0	0
-37.5°	1	1	0	0	0	0	0	0	0	0	0
-38.75°	1	1	0	0	0	0	0	0	0	0	0
-40°	1	1	0	0	0	0	0	0	0	0	0
-41.25°	1	0	0	0	0	0	0	0	0	0	0
-42.5°	1	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: P220506 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)