

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information


Test Method: LM-79-08
Report Number: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29473)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS,
MEDIUM FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 3500K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	625.7 lumens	Max Intensity:	3002.6 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	63.8 lumens/watt		
Luminous Opening:	Circular (Dia: 0.25' x H: 0')		
Beam Angle (50%):	23.8°H x 23.8°V	Field Angle (10%):	47.3°H x 47.3°V
Beam Lumens:	293.7 lumens	Field Lumens:	564 lumens
Beam Efficiency:	46.9%	Field Efficiency:	90.1%
Input Watts (W):	9.8		
Input Voltage (V):	120		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

Iso-Candela Plot






REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.1	0.1	0.1	0.0	0.0	0.0	0.0	
40		0.0	0.0	0.1	0.1	0.2	0.3	0.5	0.5	0.3	0.2	0.1	0.1	0.0	0.0		
30	0.0	0.0	0.0	0.1	0.2	0.5	2.5	6.2	6.2	2.5	0.5	0.2	0.1	0.0	0.0	0.0	
20		0.0	0.0	0.1	0.3	2.3	13.2	27.7	27.7	13.2	2.3	0.3	0.1	0.0	0.0		
10	0.0	0.0	0.1	0.1	0.4	5.8	26.9	67.6	67.6	26.9	5.8	0.4	0.1	0.1	0.0	0.0	
0		0.0	0.1	0.1	0.4	5.8	26.9	67.6	67.6	26.9	5.8	0.4	0.1	0.1	0.0		
-10	0.0	0.0	0.1	0.1	0.4	5.8	26.9	67.6	67.6	26.9	5.8	0.4	0.1	0.1	0.0	0.0	
-20		0.0	0.0	0.1	0.3	2.3	13.2	27.7	27.7	13.2	2.3	0.3	0.1	0.0	0.0		
-30	0.0	0.0	0.0	0.1	0.2	0.5	2.5	6.2	6.2	2.5	0.5	0.2	0.1	0.0	0.0	0.0	
-40		0.0	0.0	0.1	0.1	0.2	0.3	0.5	0.5	0.3	0.2	0.1	0.1	0.0	0.0		
-50	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.1	0.1	0.1	0.0	0.0	0.0	0.0	
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0			
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	


REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

Luminous Intensity Polar Plot



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

Luminous Intensity Plot



Beam:
 H Angle: 23.8°
 V Angle: 23.8°
 Lumens: 293.7
 Efficiency: 46.9%

Field:
 H Angle: 47.3°
 V Angle: 47.3°
 Lumens: 564
 Efficiency: 90.1%

Spill:
 Lumens: 61.7
 Efficiency: 9.9%

- Vertical Distribution through 0-Deg
- - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	1
36.25°	0	0	0	0	0	0	0	0	0	0	1
35°	0	0	0	0	0	0	0	0	0	0	1



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	0	0	0	0	0	0	1	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
31.25°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	0	1	1
28.75°	0	0	0	0	0	0	0	0	1	1	1
27.5°	0	0	0	0	0	0	0	0	1	1	1
26.25°	0	0	0	0	0	0	0	0	1	1	1
25°	0	0	0	0	0	0	0	0	1	1	1
23.75°	0	0	0	0	0	0	0	1	1	1	1
22.5°	0	0	0	0	0	0	0	1	1	1	1
21.25°	0	0	0	0	0	0	0	1	1	1	1
20°	0	0	0	0	0	0	0	1	1	1	1
18.75°	0	0	0	0	0	0	0	1	1	1	1
17.5°	0	0	0	0	0	0	0	1	1	1	1
16.25°	0	0	0	0	0	0	0	1	1	1	1
15°	0	0	0	0	0	0	0	1	1	1	1
13.75°	0	0	0	0	0	0	1	1	1	1	1
12.5°	0	0	0	0	0	0	1	1	1	1	1
11.25°	0	0	0	0	0	0	1	1	1	1	1
10°	0	0	0	0	0	0	1	1	1	1	1
8.75°	0	0	0	0	0	0	1	1	1	1	1
7.5°	0	0	0	0	0	0	1	1	1	1	1
6.25°	0	0	0	0	0	0	1	1	1	1	1
5°	0	0	0	0	0	0	1	1	1	1	1
3.75°	0	0	0	0	0	0	1	1	1	1	1
2.5°	0	0	0	0	0	0	1	1	1	1	1
1.25°	0	0	0	0	0	0	1	1	1	1	1
0°	0	0	0	0	0	0	1	1	1	1	2
-1.25°	0	0	0	0	0	0	1	1	1	1	1
-2.5°	0	0	0	0	0	0	1	1	1	1	1
-3.75°	0	0	0	0	0	0	1	1	1	1	1
-5°	0	0	0	0	0	0	1	1	1	1	1
-6.25°	0	0	0	0	0	0	1	1	1	1	1
-7.5°	0	0	0	0	0	0	1	1	1	1	1
-8.75°	0	0	0	0	0	0	1	1	1	1	1
-10°	0	0	0	0	0	0	1	1	1	1	1
-11.25°	0	0	0	0	0	0	1	1	1	1	1
-12.5°	0	0	0	0	0	0	1	1	1	1	1
-13.75°	0	0	0	0	0	0	1	1	1	1	1
-15°	0	0	0	0	0	0	0	1	1	1	1
-16.25°	0	0	0	0	0	0	0	1	1	1	1
-17.5°	0	0	0	0	0	0	0	1	1	1	1
-18.75°	0	0	0	0	0	0	0	1	1	1	1
-20°	0	0	0	0	0	0	0	1	1	1	1
-21.25°	0	0	0	0	0	0	0	1	1	1	1



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	0	0	0	0	0	1	1	1	1
-23.75°	0	0	0	0	0	0	0	1	1	1	1
-25°	0	0	0	0	0	0	0	0	1	1	1
-26.25°	0	0	0	0	0	0	0	0	1	1	1
-27.5°	0	0	0	0	0	0	0	0	1	1	1
-28.75°	0	0	0	0	0	0	0	0	1	1	1
-30°	0	0	0	0	0	0	0	0	0	1	1
-31.25°	0	0	0	0	0	0	0	0	0	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-33.75°	0	0	0	0	0	0	0	0	0	1	1
-35°	0	0	0	0	0	0	0	0	0	0	1
-36.25°	0	0	0	0	0	0	0	0	0	0	1
-37.5°	0	0	0	0	0	0	0	0	0	0	1
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	1
55°	0	0	0	0	0	0	0	0	0	1	1
53.75°	0	0	0	0	0	0	0	0	1	1	1
52.5°	0	0	0	0	0	0	0	1	1	1	1
51.25°	0	0	0	0	0	0	1	1	1	1	1
50°	0	0	0	0	0	1	1	1	1	1	1
48.75°	0	0	0	0	1	1	1	1	1	1	1
47.5°	0	0	0	1	1	1	1	1	1	1	1
46.25°	0	0	0	1	1	1	1	1	1	1	2
45°	0	0	1	1	1	1	1	1	1	2	2
43.75°	0	0	1	1	1	1	1	1	1	2	2
42.5°	0	1	1	1	1	1	1	1	2	2	2
41.25°	0	1	1	1	1	1	1	2	2	2	2
40°	1	1	1	1	1	1	1	2	2	2	2
38.75°	1	1	1	1	1	1	2	2	2	2	2
37.5°	1	1	1	1	1	1	2	2	2	2	2
36.25°	1	1	1	1	1	2	2	2	2	2	2
35°	1	1	1	1	1	2	2	2	2	2	2



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	1	1	2	2	2	2	2	2	3
32.5°	1	1	1	1	2	2	2	2	2	2	3
31.25°	1	1	1	2	2	2	2	2	2	3	3
30°	1	1	1	2	2	2	2	2	2	3	3
28.75°	1	1	1	2	2	2	2	2	3	3	3
27.5°	1	1	2	2	2	2	2	2	3	3	3
26.25°	1	1	2	2	2	2	2	3	3	3	3
25°	1	1	2	2	2	2	2	3	3	3	3
23.75°	1	1	2	2	2	2	2	3	3	3	3
22.5°	1	2	2	2	2	2	3	3	3	3	3
21.25°	1	2	2	2	2	2	3	3	3	3	3
20°	1	2	2	2	2	2	3	3	3	3	3
18.75°	1	2	2	2	2	2	3	3	3	3	3
17.5°	1	2	2	2	2	3	3	3	3	3	4
16.25°	2	2	2	2	2	3	3	3	3	3	4
15°	2	2	2	2	2	3	3	3	3	3	4
13.75°	2	2	2	2	2	3	3	3	3	3	4
12.5°	2	2	2	2	2	3	3	3	3	4	4
11.25°	2	2	2	2	2	3	3	3	3	4	4
10°	2	2	2	2	3	3	3	3	3	4	4
8.75°	2	2	2	2	3	3	3	3	3	4	4
7.5°	2	2	2	2	3	3	3	3	3	4	4
6.25°	2	2	2	2	3	3	3	3	3	4	4
5°	2	2	2	2	3	3	3	3	3	4	4
3.75°	2	2	2	2	3	3	3	3	3	4	4
2.5°	2	2	2	2	3	3	3	3	3	4	4
1.25°	2	2	2	2	3	3	3	3	3	4	4
0°	2	2	2	2	3	3	3	3	4	4	4
-1.25°	2	2	2	2	3	3	3	3	3	4	4
-2.5°	2	2	2	2	3	3	3	3	3	4	4
-3.75°	2	2	2	2	3	3	3	3	3	4	4
-5°	2	2	2	2	3	3	3	3	3	4	4
-6.25°	2	2	2	2	3	3	3	3	3	4	4
-7.5°	2	2	2	2	3	3	3	3	3	4	4
-8.75°	2	2	2	2	3	3	3	3	3	4	4
-10°	2	2	2	2	3	3	3	3	3	4	4
-11.25°	2	2	2	2	2	3	3	3	3	4	4
-12.5°	2	2	2	2	2	3	3	3	3	4	4
-13.75°	2	2	2	2	2	3	3	3	3	3	4
-15°	2	2	2	2	2	3	3	3	3	3	4
-16.25°	2	2	2	2	2	3	3	3	3	3	4
-17.5°	1	2	2	2	2	3	3	3	3	3	4
-18.75°	1	2	2	2	2	2	3	3	3	3	3
-20°	1	2	2	2	2	2	3	3	3	3	3
-21.25°	1	2	2	2	2	2	3	3	3	3	3



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	1	2	2	2	2	2	3	3	3	3	3
-23.75°	1	1	2	2	2	2	2	3	3	3	3
-25°	1	1	2	2	2	2	2	3	3	3	3
-26.25°	1	1	2	2	2	2	2	3	3	3	3
-27.5°	1	1	2	2	2	2	2	2	3	3	3
-28.75°	1	1	1	2	2	2	2	2	3	3	3
-30°	1	1	1	2	2	2	2	2	2	3	3
-31.25°	1	1	1	2	2	2	2	2	2	3	3
-32.5°	1	1	1	1	2	2	2	2	2	2	3
-33.75°	1	1	1	1	2	2	2	2	2	2	3
-35°	1	1	1	1	1	2	2	2	2	2	2
-36.25°	1	1	1	1	1	2	2	2	2	2	2
-37.5°	1	1	1	1	1	1	2	2	2	2	2
-38.75°	1	1	1	1	1	1	2	2	2	2	2
-40°	1	1	1	1	1	1	1	2	2	2	2
-41.25°	0	1	1	1	1	1	1	2	2	2	2
-42.5°	0	1	1	1	1	1	1	1	2	2	2
-43.75°	0	0	1	1	1	1	1	1	1	2	2
-45°	0	0	1	1	1	1	1	1	1	2	2
-46.25°	0	0	0	1	1	1	1	1	1	1	2
-47.5°	0	0	0	1	1	1	1	1	1	1	1
-48.75°	0	0	0	0	1	1	1	1	1	1	1
-50°	0	0	0	0	0	1	1	1	1	1	1
-51.25°	0	0	0	0	0	0	1	1	1	1	1
-52.5°	0	0	0	0	0	0	0	1	1	1	1
-53.75°	0	0	0	0	0	0	0	0	1	1	1
-55°	0	0	0	0	0	0	0	0	0	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	1	1
62.5°	0	0	0	0	0	0	0	1	1	1	1
61.25°	0	0	0	0	0	1	1	1	1	1	1
60°	0	0	0	1	1	1	1	1	1	1	1
58.75°	0	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	2
55°	1	1	1	1	1	1	1	1	2	2	2
53.75°	1	1	1	1	1	1	2	2	2	2	2
52.5°	1	1	1	1	1	2	2	2	2	2	2
51.25°	1	1	1	2	2	2	2	2	2	2	2
50°	1	1	2	2	2	2	2	2	2	2	2
48.75°	1	2	2	2	2	2	2	2	2	2	3
47.5°	2	2	2	2	2	2	2	2	2	3	3
46.25°	2	2	2	2	2	2	2	3	3	3	3
45°	2	2	2	2	2	2	3	3	3	3	3
43.75°	2	2	2	2	2	3	3	3	3	3	3
42.5°	2	2	2	2	3	3	3	3	3	3	3
41.25°	2	2	2	3	3	3	3	3	3	3	3
40°	2	2	3	3	3	3	3	3	3	3	4
38.75°	2	2	3	3	3	3	3	3	3	4	4
37.5°	2	3	3	3	3	3	3	3	4	4	4
36.25°	3	3	3	3	3	3	3	4	4	4	4
35°	3	3	3	3	3	3	4	4	4	4	5



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	3	3	3	3	3	4	4	4	4	5	5
32.5°	3	3	3	3	4	4	4	4	5	5	5
31.25°	3	3	3	3	4	4	4	4	5	5	5
30°	3	3	3	4	4	4	4	5	5	5	5
28.75°	3	3	3	4	4	4	5	5	5	5	6
27.5°	3	3	4	4	4	4	5	5	5	6	6
26.25°	3	3	4	4	4	5	5	5	5	6	6
25°	3	4	4	4	4	5	5	5	6	6	6
23.75°	3	4	4	4	5	5	5	5	6	6	7
22.5°	4	4	4	4	5	5	5	6	6	6	7
21.25°	4	4	4	5	5	5	5	6	6	7	7
20°	4	4	4	5	5	5	6	6	6	7	7
18.75°	4	4	4	5	5	5	6	6	7	7	7
17.5°	4	4	5	5	5	5	6	6	7	7	8
16.25°	4	4	5	5	5	6	6	6	7	7	8
15°	4	4	5	5	5	6	6	7	7	7	8
13.75°	4	5	5	5	5	6	6	7	7	8	8
12.5°	4	5	5	5	6	6	6	7	7	8	9
11.25°	4	5	5	5	6	6	7	7	7	8	9
10°	4	5	5	5	6	6	7	7	8	8	9
8.75°	4	5	5	5	6	6	7	7	8	9	10
7.5°	4	5	5	5	6	6	7	7	8	9	10
6.25°	4	5	5	5	6	6	7	7	8	9	11
5°	5	5	5	6	6	6	7	7	8	9	11
3.75°	5	5	5	6	6	6	7	7	8	9	11
2.5°	5	5	5	6	6	6	7	7	8	9	11
1.25°	5	5	5	6	6	6	7	7	8	9	11
0°	5	5	5	6	6	7	7	7	8	9	12
-1.25°	5	5	5	6	6	6	7	7	8	9	11
-2.5°	5	5	5	6	6	6	7	7	8	9	11
-3.75°	5	5	5	6	6	6	7	7	8	9	11
-5°	5	5	5	6	6	6	7	7	8	9	11
-6.25°	4	5	5	5	6	6	7	7	8	9	11
-7.5°	4	5	5	5	6	6	7	7	8	9	10
-8.75°	4	5	5	5	6	6	7	7	8	9	10
-10°	4	5	5	5	6	6	7	7	8	8	9
-11.25°	4	5	5	5	6	6	7	7	7	8	9
-12.5°	4	5	5	5	6	6	6	7	7	8	9
-13.75°	4	5	5	5	5	6	6	7	7	8	8
-15°	4	4	5	5	5	6	6	7	7	7	8
-16.25°	4	4	5	5	5	6	6	6	7	7	8
-17.5°	4	4	5	5	5	5	6	6	7	7	8
-18.75°	4	4	4	5	5	5	6	6	7	7	7
-20°	4	4	4	5	5	5	6	6	6	7	7
-21.25°	4	4	4	5	5	5	5	6	6	7	7



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	4	4	4	4	5	5	5	6	6	6	7
-23.75°	3	4	4	4	5	5	5	5	6	6	7
-25°	3	4	4	4	4	5	5	5	6	6	6
-26.25°	3	3	4	4	4	5	5	5	5	6	6
-27.5°	3	3	4	4	4	4	5	5	5	6	6
-28.75°	3	3	3	4	4	4	5	5	5	5	6
-30°	3	3	3	4	4	4	4	5	5	5	5
-31.25°	3	3	3	3	4	4	4	4	5	5	5
-32.5°	3	3	3	3	4	4	4	4	5	5	5
-33.75°	3	3	3	3	3	4	4	4	4	5	5
-35°	3	3	3	3	3	3	4	4	4	4	5
-36.25°	3	3	3	3	3	3	3	4	4	4	4
-37.5°	2	3	3	3	3	3	3	3	4	4	4
-38.75°	2	2	3	3	3	3	3	3	3	4	4
-40°	2	2	3	3	3	3	3	3	3	3	4
-41.25°	2	2	2	3	3	3	3	3	3	3	3
-42.5°	2	2	2	2	3	3	3	3	3	3	3
-43.75°	2	2	2	2	2	3	3	3	3	3	3
-45°	2	2	2	2	2	2	3	3	3	3	3
-46.25°	2	2	2	2	2	2	2	3	3	3	3
-47.5°	2	2	2	2	2	2	2	2	2	3	3
-48.75°	1	2	2	2	2	2	2	2	2	2	3
-50°	1	1	2	2	2	2	2	2	2	2	2
-51.25°	1	1	1	2	2	2	2	2	2	2	2
-52.5°	1	1	1	1	1	2	2	2	2	2	2
-53.75°	1	1	1	1	1	1	2	2	2	2	2
-55°	1	1	1	1	1	1	1	1	2	2	2
-56.25°	1	1	1	1	1	1	1	1	1	1	2
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	0	1	1	1	1	1	1	1	1	1	1
-60°	0	0	0	1	1	1	1	1	1	1	1
-61.25°	0	0	0	0	0	1	1	1	1	1	1
-62.5°	0	0	0	0	0	0	0	1	1	1	1
-63.75°	0	0	0	0	0	0	0	0	0	1	1
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	1	1
66.25°	0	0	0	0	0	1	1	1	1	1	1
65°	0	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	2
60°	1	1	1	1	1	1	2	2	2	2	2
58.75°	1	1	1	2	2	2	2	2	2	2	2
57.5°	1	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	3
53.75°	2	2	2	2	2	2	2	3	3	3	3
52.5°	2	2	2	2	2	3	3	3	3	3	3
51.25°	2	2	2	3	3	3	3	3	3	3	3
50°	2	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	4
47.5°	3	3	3	3	3	3	3	3	4	4	4
46.25°	3	3	3	3	3	3	4	4	4	4	4
45°	3	3	3	3	4	4	4	4	4	4	4
43.75°	3	3	4	4	4	4	4	4	4	5	5
42.5°	3	4	4	4	4	4	4	5	5	5	5
41.25°	4	4	4	4	4	5	5	5	5	5	5
40°	4	4	4	4	5	5	5	5	5	5	6
38.75°	4	4	5	5	5	5	5	5	6	6	6
37.5°	4	5	5	5	5	5	6	6	6	6	6
36.25°	5	5	5	5	5	6	6	6	6	7	7
35°	5	5	5	5	6	6	6	6	7	7	7



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	5	5	5	6	6	6	7	7	7	7	8
32.5°	5	5	6	6	6	7	7	7	7	8	8
31.25°	5	6	6	6	7	7	7	7	8	8	9
30°	6	6	6	7	7	7	8	8	9	9	10
28.75°	6	6	7	7	7	8	8	9	9	11	12
27.5°	6	7	7	7	8	8	9	9	11	13	14
26.25°	6	7	7	7	8	9	9	11	13	15	19
25°	7	7	7	8	9	9	11	13	15	19	24
23.75°	7	7	8	8	9	11	13	15	19	24	28
22.5°	7	8	8	9	10	12	14	19	24	28	33
21.25°	7	8	9	10	12	14	18	23	28	32	37
20°	8	8	9	11	13	16	22	27	32	36	42
18.75°	8	9	10	12	14	20	25	30	35	40	47
17.5°	8	9	11	13	17	23	28	34	39	46	60
16.25°	9	10	12	15	20	26	31	37	43	55	83
15°	9	11	13	17	23	29	34	40	49	70	112
13.75°	10	12	14	20	26	32	37	44	59	93	146
12.5°	10	12	16	22	28	34	40	49	73	120	181
11.25°	11	13	18	24	30	36	43	57	92	148	215
10°	12	14	20	26	32	38	46	66	112	177	247
8.75°	12	15	22	28	34	40	51	80	135	203	276
7.5°	13	17	23	29	36	42	57	93	154	226	302
6.25°	13	18	24	31	37	44	62	106	173	247	324
5°	13	19	25	32	38	46	67	119	188	264	342
3.75°	14	19	26	32	39	47	74	129	200	278	356
2.5°	14	20	26	33	39	50	79	136	209	288	366
1.25°	14	20	27	33	40	51	82	141	214	294	372
0°	14	20	27	33	40	51	83	142	216	296	374
-1.25°	14	20	27	33	40	51	82	141	214	294	372
-2.5°	14	20	26	33	39	50	79	136	209	288	366
-3.75°	14	19	26	32	39	47	74	129	200	278	356
-5°	13	19	25	32	38	46	67	119	188	264	342
-6.25°	13	18	24	31	37	44	62	106	173	247	324
-7.5°	13	17	23	29	36	42	57	93	154	226	302
-8.75°	12	15	22	28	34	40	51	80	135	203	276
-10°	12	14	20	26	32	38	46	66	112	177	247
-11.25°	11	13	18	24	30	36	43	57	92	148	215
-12.5°	10	12	16	22	28	34	40	49	73	120	181
-13.75°	10	12	14	20	26	32	37	44	59	93	146
-15°	9	11	13	17	23	29	34	40	49	70	112
-16.25°	9	10	12	15	20	26	31	37	43	55	83
-17.5°	8	9	11	13	17	23	28	34	39	46	60
-18.75°	8	9	10	12	14	20	25	30	35	40	47
-20°	8	8	9	11	13	16	22	27	32	36	42
-21.25°	7	8	9	10	12	14	18	23	28	32	37



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	7	8	8	9	10	12	14	19	24	28	33
-23.75°	7	7	8	8	9	11	13	15	19	24	28
-25°	7	7	7	8	9	9	11	13	15	19	24
-26.25°	6	7	7	7	8	9	9	11	13	15	19
-27.5°	6	7	7	7	8	8	9	9	11	13	14
-28.75°	6	6	7	7	7	8	8	9	9	11	12
-30°	6	6	6	7	7	7	8	8	9	9	10
-31.25°	5	6	6	6	7	7	7	7	8	8	9
-32.5°	5	5	6	6	6	7	7	7	7	8	8
-33.75°	5	5	5	6	6	6	7	7	7	7	8
-35°	5	5	5	5	6	6	6	6	7	7	7
-36.25°	5	5	5	5	5	6	6	6	6	7	7
-37.5°	4	5	5	5	5	5	6	6	6	6	6
-38.75°	4	4	5	5	5	5	5	5	6	6	6
-40°	4	4	4	4	5	5	5	5	5	5	6
-41.25°	4	4	4	4	4	5	5	5	5	5	5
-42.5°	3	4	4	4	4	4	4	5	5	5	5
-43.75°	3	3	4	4	4	4	4	4	4	5	5
-45°	3	3	3	3	4	4	4	4	4	4	4
-46.25°	3	3	3	3	3	3	4	4	4	4	4
-47.5°	3	3	3	3	3	3	3	3	4	4	4
-48.75°	3	3	3	3	3	3	3	3	3	3	4
-50°	2	3	3	3	3	3	3	3	3	3	3
-51.25°	2	2	2	3	3	3	3	3	3	3	3
-52.5°	2	2	2	2	2	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	2	3	3	3	3
-55°	2	2	2	2	2	2	2	2	2	2	3
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	1	2	2	2	2	2	2	2	2	2	2
-58.75°	1	1	1	2	2	2	2	2	2	2	2
-60°	1	1	1	1	1	1	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	2
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	0	1	1	1	1	1	1	1	1	1	1
-66.25°	0	0	0	0	0	1	1	1	1	1	1
-67.5°	0	0	0	0	0	0	0	0	0	1	1
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	3	3
56.25°	2	2	2	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	4	4	4	4
50°	3	3	3	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	5	5	5	5	5
46.25°	4	4	4	5	5	5	5	5	5	5	5
45°	5	5	5	5	5	5	5	5	5	5	5
43.75°	5	5	5	5	5	5	5	6	6	6	6
42.5°	5	5	5	5	6	6	6	6	6	6	6
41.25°	5	6	6	6	6	6	6	6	7	7	7
40°	6	6	6	6	6	7	7	7	7	7	7
38.75°	6	6	7	7	7	7	7	7	7	8	8
37.5°	7	7	7	7	7	7	8	8	8	8	9
36.25°	7	7	7	8	8	8	8	9	9	9	10
35°	7	8	8	8	9	9	10	10	11	12	12



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	8	8	9	9	10	11	12	12	13	14	15
32.5°	9	9	10	11	12	13	14	16	18	20	22
31.25°	10	11	12	13	15	17	20	22	24	26	28
30°	12	13	14	17	20	23	26	28	30	32	34
28.75°	14	16	20	23	26	29	32	34	36	38	40
27.5°	18	22	25	28	31	34	37	40	43	46	51
26.25°	23	27	30	34	37	40	44	49	57	66	80
25°	28	32	35	39	43	49	59	73	92	112	135
23.75°	32	36	40	46	55	70	93	120	148	177	203
22.5°	37	42	47	60	83	112	146	181	215	247	276
21.25°	42	49	63	92	128	167	208	247	285	319	349
20°	49	65	96	138	183	228	273	315	354	388	417
18.75°	63	96	141	190	240	290	337	380	417	448	473
17.5°	92	138	190	245	298	350	397	436	469	498	529
16.25°	128	183	240	298	354	406	448	483	519	556	601
15°	167	228	290	350	406	452	491	533	581	634	694
13.75°	208	273	337	397	448	491	537	593	659	730	810
12.5°	247	315	380	436	483	533	593	667	752	845	949
11.25°	285	354	417	469	519	581	659	752	859	979	1100
10°	319	388	448	498	556	634	730	845	979	1117	1260
8.75°	349	417	473	529	601	694	810	949	1100	1260	1420
7.5°	375	440	495	557	644	755	891	1050	1220	1397	1576
6.25°	398	460	516	590	688	813	969	1142	1331	1525	1721
5°	415	475	536	617	726	868	1039	1228	1429	1639	1849
3.75°	427	486	551	641	762	916	1096	1297	1510	1733	1954
2.5°	436	495	563	661	789	951	1139	1350	1573	1804	2032
1.25°	442	500	572	673	805	973	1167	1382	1611	1847	2081
0°	443	501	575	677	810	980	1176	1393	1624	1862	2097
-1.25°	442	500	572	673	805	973	1167	1382	1611	1847	2081
-2.5°	436	495	563	661	789	951	1139	1350	1573	1804	2032
-3.75°	427	486	551	641	762	916	1096	1297	1510	1733	1954
-5°	415	475	536	617	726	868	1039	1228	1429	1639	1849
-6.25°	398	460	516	590	688	813	969	1142	1331	1525	1721
-7.5°	375	440	495	557	644	755	891	1050	1220	1397	1576
-8.75°	349	417	473	529	601	694	810	949	1100	1260	1420
-10°	319	388	448	498	556	634	730	845	979	1117	1260
-11.25°	285	354	417	469	519	581	659	752	859	979	1100
-12.5°	247	315	380	436	483	533	593	667	752	845	949
-13.75°	208	273	337	397	448	491	537	593	659	730	810
-15°	167	228	290	350	406	452	491	533	581	634	694
-16.25°	128	183	240	298	354	406	448	483	519	556	601
-17.5°	92	138	190	245	298	350	397	436	469	498	529
-18.75°	63	96	141	190	240	290	337	380	417	448	473
-20°	49	65	96	138	183	228	273	315	354	388	417
-21.25°	42	49	63	92	128	167	208	247	285	319	349



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	37	42	47	60	83	112	146	181	215	247	276
-23.75°	32	36	40	46	55	70	93	120	148	177	203
-25°	28	32	35	39	43	49	59	73	92	112	135
-26.25°	23	27	30	34	37	40	44	49	57	66	80
-27.5°	18	22	25	28	31	34	37	40	43	46	51
-28.75°	14	16	20	23	26	29	32	34	36	38	40
-30°	12	13	14	17	20	23	26	28	30	32	34
-31.25°	10	11	12	13	15	17	20	22	24	26	28
-32.5°	9	9	10	11	12	13	14	16	18	20	22
-33.75°	8	8	9	9	10	11	12	12	13	14	15
-35°	7	8	8	8	9	9	10	10	11	12	12
-36.25°	7	7	7	8	8	8	8	9	9	9	10
-37.5°	7	7	7	7	7	7	8	8	8	8	9
-38.75°	6	6	7	7	7	7	7	7	7	8	8
-40°	6	6	6	6	6	7	7	7	7	7	7
-41.25°	5	6	6	6	6	6	6	6	7	7	7
-42.5°	5	5	5	5	6	6	6	6	6	6	6
-43.75°	5	5	5	5	5	5	5	6	6	6	6
-45°	5	5	5	5	5	5	5	5	5	5	5
-46.25°	4	4	4	5	5	5	5	5	5	5	5
-47.5°	4	4	4	4	4	4	5	5	5	5	5
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	3	3	3	4	4	4	4	4	4	4	4
-51.25°	3	3	3	3	3	3	3	4	4	4	4
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	2	2	3	3	3	3	3	3	3	3
-57.5°	2	2	2	2	2	2	2	2	2	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	0	0	0	0	0	0	1	1	1	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	2	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	4	3	3	3	3
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	5	5	5	5	5	5	5	5	5
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	5	5	6	6	6	6	6	6	6	6	6
43.75°	6	6	6	6	6	6	6	6	6	6	6
42.5°	6	6	6	6	6	6	7	6	6	6	6
41.25°	7	7	7	7	7	7	7	7	7	7	7
40°	7	7	7	7	7	7	7	7	7	7	7
38.75°	8	8	8	8	8	8	8	8	8	8	8
37.5°	9	9	9	9	9	9	9	9	9	9	9
36.25°	10	11	11	11	11	11	12	11	11	11	11
35°	13	13	13	14	14	14	14	14	14	14	13



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	17	18	19	19	20	20	20	20	20	19	19
32.5°	23	24	25	26	26	27	27	27	26	26	25
31.25°	29	31	32	32	33	33	33	33	33	32	32
30°	36	37	38	39	39	40	40	40	39	39	38
28.75°	42	44	46	47	50	51	51	51	50	47	46
27.5°	57	62	67	74	79	82	83	82	79	74	67
26.25°	93	106	119	129	136	141	142	141	136	129	119
25°	154	173	188	200	209	214	216	214	209	200	188
23.75°	226	247	264	278	288	294	296	294	288	278	264
22.5°	302	324	342	356	366	372	374	372	366	356	342
21.25°	375	398	415	427	436	442	443	442	436	427	415
20°	440	460	475	486	495	500	501	500	495	486	475
18.75°	495	516	536	551	563	572	575	572	563	551	536
17.5°	557	590	617	641	661	673	677	673	661	641	617
16.25°	644	688	726	762	789	805	810	805	789	762	726
15°	755	813	868	916	951	973	980	973	951	916	868
13.75°	891	969	1039	1096	1139	1167	1176	1167	1139	1096	1039
12.5°	1050	1142	1228	1297	1350	1382	1393	1382	1350	1297	1228
11.25°	1220	1331	1429	1510	1573	1611	1624	1611	1573	1510	1429
10°	1397	1525	1639	1733	1804	1847	1862	1847	1804	1733	1639
8.75°	1576	1721	1849	1954	2032	2081	2097	2081	2032	1954	1849
7.5°	1749	1909	2050	2165	2251	2302	2319	2302	2251	2165	2050
6.25°	1909	2082	2235	2356	2444	2498	2516	2498	2444	2356	2235
5°	2050	2235	2393	2516	2606	2661	2681	2661	2606	2516	2393
3.75°	2165	2356	2516	2642	2733	2791	2808	2791	2733	2642	2516
2.5°	2251	2444	2606	2733	2827	2886	2904	2886	2827	2733	2606
1.25°	2302	2498	2661	2791	2886	2946	2968	2946	2886	2791	2661
0°	2319	2516	2681	2808	2904	2968	3003	2968	2904	2808	2681
-1.25°	2302	2498	2661	2791	2886	2946	2968	2946	2886	2791	2661
-2.5°	2251	2444	2606	2733	2827	2886	2904	2886	2827	2733	2606
-3.75°	2165	2356	2516	2642	2733	2791	2808	2791	2733	2642	2516
-5°	2050	2235	2393	2516	2606	2661	2681	2661	2606	2516	2393
-6.25°	1909	2082	2235	2356	2444	2498	2516	2498	2444	2356	2235
-7.5°	1749	1909	2050	2165	2251	2302	2319	2302	2251	2165	2050
-8.75°	1576	1721	1849	1954	2032	2081	2097	2081	2032	1954	1849
-10°	1397	1525	1639	1733	1804	1847	1862	1847	1804	1733	1639
-11.25°	1220	1331	1429	1510	1573	1611	1624	1611	1573	1510	1429
-12.5°	1050	1142	1228	1297	1350	1382	1393	1382	1350	1297	1228
-13.75°	891	969	1039	1096	1139	1167	1176	1167	1139	1096	1039
-15°	755	813	868	916	951	973	980	973	951	916	868
-16.25°	644	688	726	762	789	805	810	805	789	762	726
-17.5°	557	590	617	641	661	673	677	673	661	641	617
-18.75°	495	516	536	551	563	572	575	572	563	551	536
-20°	440	460	475	486	495	500	501	500	495	486	475
-21.25°	375	398	415	427	436	442	443	442	436	427	415



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	302	324	342	356	366	372	374	372	366	356	342
-23.75°	226	247	264	278	288	294	296	294	288	278	264
-25°	154	173	188	200	209	214	216	214	209	200	188
-26.25°	93	106	119	129	136	141	142	141	136	129	119
-27.5°	57	62	67	74	79	82	83	82	79	74	67
-28.75°	42	44	46	47	50	51	51	51	50	47	46
-30°	36	37	38	39	39	40	40	40	39	39	38
-31.25°	29	31	32	32	33	33	33	33	33	32	32
-32.5°	23	24	25	26	26	27	27	27	26	26	25
-33.75°	17	18	19	19	20	20	20	20	20	19	19
-35°	13	13	13	14	14	14	14	14	14	14	13
-36.25°	10	11	11	11	11	11	12	11	11	11	11
-37.5°	9	9	9	9	9	9	9	9	9	9	9
-38.75°	8	8	8	8	8	8	8	8	8	8	8
-40°	7	7	7	7	7	7	7	7	7	7	7
-41.25°	7	7	7	7	7	7	7	7	7	7	7
-42.5°	6	6	6	6	6	6	7	6	6	6	6
-43.75°	6	6	6	6	6	6	6	6	6	6	6
-45°	5	5	6	6	6	6	6	6	6	6	6
-46.25°	5	5	5	5	5	5	5	5	5	5	5
-47.5°	5	5	5	5	5	5	5	5	5	5	5
-48.75°	4	4	5	5	5	5	5	5	5	5	5
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	3	3	3	3	3	3	4	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	2	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	1	1	1	0	0	0	0
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	2	2	2	2	2	2	2
56.25°	3	3	3	3	3	3	3	3	3	3	2
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	4	4	4	4	4	4	3	3	3	3	3
50°	4	4	4	4	4	4	4	4	4	4	3
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	5	5	5	5	5	5	5	4	4	4	4
46.25°	5	5	5	5	5	5	5	5	5	5	4
45°	5	5	5	5	5	5	5	5	5	5	5
43.75°	6	6	6	6	6	6	5	5	5	5	5
42.5°	6	6	6	6	6	6	6	6	6	5	5
41.25°	7	7	7	7	7	6	6	6	6	6	6
40°	7	7	7	7	7	7	7	7	6	6	6
38.75°	8	8	8	8	7	7	7	7	7	7	7
37.5°	9	9	9	8	8	8	8	7	7	7	7
36.25°	11	10	10	9	9	9	8	8	8	8	7
35°	13	13	12	12	11	10	10	9	9	8	8



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	18	17	15	14	13	12	12	11	10	9	9
32.5°	24	23	22	20	18	16	14	13	12	11	10
31.25°	31	29	28	26	24	22	20	17	15	13	12
30°	37	36	34	32	30	28	26	23	20	17	14
28.75°	44	42	40	38	36	34	32	29	26	23	20
27.5°	62	57	51	46	43	40	37	34	31	28	25
26.25°	106	93	80	66	57	49	44	40	37	34	30
25°	173	154	135	112	92	73	59	49	43	39	35
23.75°	247	226	203	177	148	120	93	70	55	46	40
22.5°	324	302	276	247	215	181	146	112	83	60	47
21.25°	398	375	349	319	285	247	208	167	128	92	63
20°	460	440	417	388	354	315	273	228	183	138	96
18.75°	516	495	473	448	417	380	337	290	240	190	141
17.5°	590	557	529	498	469	436	397	350	298	245	190
16.25°	688	644	601	556	519	483	448	406	354	298	240
15°	813	755	694	634	581	533	491	452	406	350	290
13.75°	969	891	810	730	659	593	537	491	448	397	337
12.5°	1142	1050	949	845	752	667	593	533	483	436	380
11.25°	1331	1220	1100	979	859	752	659	581	519	469	417
10°	1525	1397	1260	1117	979	845	730	634	556	498	448
8.75°	1721	1576	1420	1260	1100	949	810	694	601	529	473
7.5°	1909	1749	1576	1397	1220	1050	891	755	644	557	495
6.25°	2082	1909	1721	1525	1331	1142	969	813	688	590	516
5°	2235	2050	1849	1639	1429	1228	1039	868	726	617	536
3.75°	2356	2165	1954	1733	1510	1297	1096	916	762	641	551
2.5°	2444	2251	2032	1804	1573	1350	1139	951	789	661	563
1.25°	2498	2302	2081	1847	1611	1382	1167	973	805	673	572
0°	2516	2319	2097	1862	1624	1393	1176	980	810	677	575
-1.25°	2498	2302	2081	1847	1611	1382	1167	973	805	673	572
-2.5°	2444	2251	2032	1804	1573	1350	1139	951	789	661	563
-3.75°	2356	2165	1954	1733	1510	1297	1096	916	762	641	551
-5°	2235	2050	1849	1639	1429	1228	1039	868	726	617	536
-6.25°	2082	1909	1721	1525	1331	1142	969	813	688	590	516
-7.5°	1909	1749	1576	1397	1220	1050	891	755	644	557	495
-8.75°	1721	1576	1420	1260	1100	949	810	694	601	529	473
-10°	1525	1397	1260	1117	979	845	730	634	556	498	448
-11.25°	1331	1220	1100	979	859	752	659	581	519	469	417
-12.5°	1142	1050	949	845	752	667	593	533	483	436	380
-13.75°	969	891	810	730	659	593	537	491	448	397	337
-15°	813	755	694	634	581	533	491	452	406	350	290
-16.25°	688	644	601	556	519	483	448	406	354	298	240
-17.5°	590	557	529	498	469	436	397	350	298	245	190
-18.75°	516	495	473	448	417	380	337	290	240	190	141
-20°	460	440	417	388	354	315	273	228	183	138	96
-21.25°	398	375	349	319	285	247	208	167	128	92	63



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	324	302	276	247	215	181	146	112	83	60	47
-23.75°	247	226	203	177	148	120	93	70	55	46	40
-25°	173	154	135	112	92	73	59	49	43	39	35
-26.25°	106	93	80	66	57	49	44	40	37	34	30
-27.5°	62	57	51	46	43	40	37	34	31	28	25
-28.75°	44	42	40	38	36	34	32	29	26	23	20
-30°	37	36	34	32	30	28	26	23	20	17	14
-31.25°	31	29	28	26	24	22	20	17	15	13	12
-32.5°	24	23	22	20	18	16	14	13	12	11	10
-33.75°	18	17	15	14	13	12	12	11	10	9	9
-35°	13	13	12	12	11	10	10	9	9	8	8
-36.25°	11	10	10	9	9	9	8	8	8	8	7
-37.5°	9	9	9	8	8	8	8	7	7	7	7
-38.75°	8	8	8	8	7	7	7	7	7	7	7
-40°	7	7	7	7	7	7	7	7	6	6	6
-41.25°	7	7	7	7	7	6	6	6	6	6	6
-42.5°	6	6	6	6	6	6	6	6	6	5	5
-43.75°	6	6	6	6	6	6	5	5	5	5	5
-45°	5	5	5	5	5	5	5	5	5	5	5
-46.25°	5	5	5	5	5	5	5	5	5	5	4
-47.5°	5	5	5	5	5	5	5	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	3
-51.25°	4	4	4	4	4	4	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	2
-57.5°	3	3	3	3	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	1	1	1	1	0	0	0	0	0	0	0
66.25°	1	1	1	1	1	1	1	1	0	0	0
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	2	2	1	1	1	1	1	1	1	1
60°	2	2	2	2	2	2	2	1	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	2	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	2	2	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	2	2	2	2	2
52.5°	3	3	3	3	3	3	3	3	2	2	2
51.25°	3	3	3	3	3	3	3	3	3	3	2
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	4	4	4	3	3	3	3	3	3	3	3
47.5°	4	4	4	4	4	3	3	3	3	3	3
46.25°	4	4	4	4	4	4	4	3	3	3	3
45°	5	5	4	4	4	4	4	4	4	3	3
43.75°	5	5	5	5	4	4	4	4	4	4	4
42.5°	5	5	5	5	5	5	4	4	4	4	4
41.25°	6	5	5	5	5	5	5	5	4	4	4
40°	6	6	6	5	5	5	5	5	5	4	4
38.75°	6	6	6	6	6	5	5	5	5	5	5
37.5°	7	7	6	6	6	6	6	5	5	5	5
36.25°	7	7	7	7	6	6	6	6	5	5	5
35°	8	7	7	7	7	6	6	6	6	5	5



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	8	8	8	7	7	7	7	6	6	6	5
32.5°	9	9	8	8	7	7	7	7	6	6	6
31.25°	11	10	9	8	8	7	7	7	7	6	6
30°	13	12	10	9	9	8	8	7	7	7	6
28.75°	16	14	12	11	9	9	8	8	7	7	7
27.5°	22	18	14	13	11	9	9	8	8	7	7
26.25°	27	23	19	15	13	11	9	9	8	7	7
25°	32	28	24	19	15	13	11	9	9	8	7
23.75°	36	32	28	24	19	15	13	11	9	8	8
22.5°	42	37	33	28	24	19	14	12	10	9	8
21.25°	49	42	37	32	28	23	18	14	12	10	9
20°	65	49	42	36	32	27	22	16	13	11	9
18.75°	96	63	47	40	35	30	25	20	14	12	10
17.5°	138	92	60	46	39	34	28	23	17	13	11
16.25°	183	128	83	55	43	37	31	26	20	15	12
15°	228	167	112	70	49	40	34	29	23	17	13
13.75°	273	208	146	93	59	44	37	32	26	20	14
12.5°	315	247	181	120	73	49	40	34	28	22	16
11.25°	354	285	215	148	92	57	43	36	30	24	18
10°	388	319	247	177	112	66	46	38	32	26	20
8.75°	417	349	276	203	135	80	51	40	34	28	22
7.5°	440	375	302	226	154	93	57	42	36	29	23
6.25°	460	398	324	247	173	106	62	44	37	31	24
5°	475	415	342	264	188	119	67	46	38	32	25
3.75°	486	427	356	278	200	129	74	47	39	32	26
2.5°	495	436	366	288	209	136	79	50	39	33	26
1.25°	500	442	372	294	214	141	82	51	40	33	27
0°	501	443	374	296	216	142	83	51	40	33	27
-1.25°	500	442	372	294	214	141	82	51	40	33	27
-2.5°	495	436	366	288	209	136	79	50	39	33	26
-3.75°	486	427	356	278	200	129	74	47	39	32	26
-5°	475	415	342	264	188	119	67	46	38	32	25
-6.25°	460	398	324	247	173	106	62	44	37	31	24
-7.5°	440	375	302	226	154	93	57	42	36	29	23
-8.75°	417	349	276	203	135	80	51	40	34	28	22
-10°	388	319	247	177	112	66	46	38	32	26	20
-11.25°	354	285	215	148	92	57	43	36	30	24	18
-12.5°	315	247	181	120	73	49	40	34	28	22	16
-13.75°	273	208	146	93	59	44	37	32	26	20	14
-15°	228	167	112	70	49	40	34	29	23	17	13
-16.25°	183	128	83	55	43	37	31	26	20	15	12
-17.5°	138	92	60	46	39	34	28	23	17	13	11
-18.75°	96	63	47	40	35	30	25	20	14	12	10
-20°	65	49	42	36	32	27	22	16	13	11	9
-21.25°	49	42	37	32	28	23	18	14	12	10	9



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	42	37	33	28	24	19	14	12	10	9	8
-23.75°	36	32	28	24	19	15	13	11	9	8	8
-25°	32	28	24	19	15	13	11	9	9	8	7
-26.25°	27	23	19	15	13	11	9	9	8	7	7
-27.5°	22	18	14	13	11	9	9	8	8	7	7
-28.75°	16	14	12	11	9	9	8	8	7	7	7
-30°	13	12	10	9	9	8	8	7	7	7	6
-31.25°	11	10	9	8	8	7	7	7	7	6	6
-32.5°	9	9	8	8	7	7	7	7	6	6	6
-33.75°	8	8	8	7	7	7	7	6	6	6	5
-35°	8	7	7	7	7	6	6	6	6	5	5
-36.25°	7	7	7	7	6	6	6	6	5	5	5
-37.5°	7	7	6	6	6	6	6	5	5	5	5
-38.75°	6	6	6	6	6	5	5	5	5	5	5
-40°	6	6	6	5	5	5	5	5	5	4	4
-41.25°	6	5	5	5	5	5	5	5	4	4	4
-42.5°	5	5	5	5	5	5	4	4	4	4	4
-43.75°	5	5	5	5	4	4	4	4	4	4	4
-45°	5	5	4	4	4	4	4	4	4	3	3
-46.25°	4	4	4	4	4	4	4	3	3	3	3
-47.5°	4	4	4	4	4	3	3	3	3	3	3
-48.75°	4	4	4	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	2
-52.5°	3	3	3	3	3	3	3	3	2	2	2
-53.75°	3	3	3	3	3	3	2	2	2	2	2
-55°	3	3	3	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	1
-60°	2	2	2	2	2	2	2	1	1	1	1
-61.25°	2	2	2	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	0	0	0
-67.5°	1	1	1	1	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	1	0	0	0	0	0	0	0	0	0	0
63.75°	1	1	1	1	0	0	0	0	0	0	0
62.5°	1	1	1	1	1	1	0	0	0	0	0
61.25°	1	1	1	1	1	1	1	1	0	0	0
60°	1	1	1	1	1	1	1	1	1	1	0
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	2	1	1	1	1	1	1	1	1
55°	2	2	2	2	2	1	1	1	1	1	1
53.75°	2	2	2	2	2	2	2	1	1	1	1
52.5°	2	2	2	2	2	2	2	2	1	1	1
51.25°	2	2	2	2	2	2	2	2	2	2	1
50°	3	2	2	2	2	2	2	2	2	2	2
48.75°	3	3	3	2	2	2	2	2	2	2	2
47.5°	3	3	3	3	2	2	2	2	2	2	2
46.25°	3	3	3	3	3	3	2	2	2	2	2
45°	3	3	3	3	3	3	3	2	2	2	2
43.75°	3	3	3	3	3	3	3	3	2	2	2
42.5°	4	3	3	3	3	3	3	3	3	2	2
41.25°	4	4	3	3	3	3	3	3	3	3	2
40°	4	4	4	3	3	3	3	3	3	3	3
38.75°	4	4	4	4	3	3	3	3	3	3	3
37.5°	5	4	4	4	4	3	3	3	3	3	3
36.25°	5	5	4	4	4	4	3	3	3	3	3
35°	5	5	5	4	4	4	4	3	3	3	3



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	5	5	5	5	4	4	4	4	3	3	3
32.5°	5	5	5	5	5	4	4	4	4	3	3
31.25°	6	5	5	5	5	4	4	4	4	3	3
30°	6	6	5	5	5	5	4	4	4	4	3
28.75°	6	6	6	5	5	5	5	4	4	4	3
27.5°	7	6	6	6	5	5	5	4	4	4	4
26.25°	7	6	6	6	5	5	5	5	4	4	4
25°	7	7	6	6	6	5	5	5	4	4	4
23.75°	7	7	7	6	6	5	5	5	5	4	4
22.5°	8	7	7	6	6	6	5	5	5	4	4
21.25°	8	7	7	7	6	6	5	5	5	5	4
20°	8	8	7	7	6	6	6	5	5	5	4
18.75°	9	8	7	7	7	6	6	5	5	5	4
17.5°	9	8	8	7	7	6	6	5	5	5	5
16.25°	10	9	8	7	7	6	6	6	5	5	5
15°	11	9	8	7	7	7	6	6	5	5	5
13.75°	12	10	8	8	7	7	6	6	5	5	5
12.5°	12	10	9	8	7	7	6	6	6	5	5
11.25°	13	11	9	8	7	7	7	6	6	5	5
10°	14	12	9	8	8	7	7	6	6	5	5
8.75°	15	12	10	9	8	7	7	6	6	5	5
7.5°	17	13	10	9	8	7	7	6	6	5	5
6.25°	18	13	11	9	8	7	7	6	6	5	5
5°	19	13	11	9	8	7	7	6	6	6	5
3.75°	19	14	11	9	8	7	7	6	6	6	5
2.5°	20	14	11	9	8	7	7	6	6	6	5
1.25°	20	14	11	9	8	7	7	6	6	6	5
0°	20	14	12	9	8	7	7	7	6	6	5
-1.25°	20	14	11	9	8	7	7	6	6	6	5
-2.5°	20	14	11	9	8	7	7	6	6	6	5
-3.75°	19	14	11	9	8	7	7	6	6	6	5
-5°	19	13	11	9	8	7	7	6	6	6	5
-6.25°	18	13	11	9	8	7	7	6	6	5	5
-7.5°	17	13	10	9	8	7	7	6	6	5	5
-8.75°	15	12	10	9	8	7	7	6	6	5	5
-10°	14	12	9	8	8	7	7	6	6	5	5
-11.25°	13	11	9	8	7	7	7	6	6	5	5
-12.5°	12	10	9	8	7	7	6	6	6	5	5
-13.75°	12	10	8	8	7	7	6	6	5	5	5
-15°	11	9	8	7	7	7	6	6	5	5	5
-16.25°	10	9	8	7	7	6	6	6	5	5	5
-17.5°	9	8	8	7	7	6	6	5	5	5	5
-18.75°	9	8	7	7	7	6	6	5	5	5	4
-20°	8	8	7	7	6	6	6	5	5	5	4
-21.25°	8	7	7	7	6	6	5	5	5	5	4



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	8	7	7	6	6	6	5	5	5	4	4
-23.75°	7	7	7	6	6	5	5	5	5	4	4
-25°	7	7	6	6	6	5	5	5	4	4	4
-26.25°	7	6	6	6	5	5	5	5	4	4	4
-27.5°	7	6	6	6	5	5	5	4	4	4	4
-28.75°	6	6	6	5	5	5	5	4	4	4	3
-30°	6	6	5	5	5	5	4	4	4	4	3
-31.25°	6	5	5	5	5	4	4	4	4	3	3
-32.5°	5	5	5	5	5	4	4	4	4	3	3
-33.75°	5	5	5	5	4	4	4	4	3	3	3
-35°	5	5	5	4	4	4	4	3	3	3	3
-36.25°	5	5	4	4	4	4	3	3	3	3	3
-37.5°	5	4	4	4	4	3	3	3	3	3	3
-38.75°	4	4	4	4	3	3	3	3	3	3	3
-40°	4	4	4	3	3	3	3	3	3	3	3
-41.25°	4	4	3	3	3	3	3	3	3	3	2
-42.5°	4	3	3	3	3	3	3	3	3	2	2
-43.75°	3	3	3	3	3	3	3	3	2	2	2
-45°	3	3	3	3	3	3	3	2	2	2	2
-46.25°	3	3	3	3	3	3	2	2	2	2	2
-47.5°	3	3	3	3	2	2	2	2	2	2	2
-48.75°	3	3	3	2	2	2	2	2	2	2	2
-50°	3	2	2	2	2	2	2	2	2	2	2
-51.25°	2	2	2	2	2	2	2	2	2	2	1
-52.5°	2	2	2	2	2	2	2	2	1	1	1
-53.75°	2	2	2	2	2	2	2	1	1	1	1
-55°	2	2	2	2	2	1	1	1	1	1	1
-56.25°	2	2	2	1	1	1	1	1	1	1	1
-57.5°	2	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	0
-61.25°	1	1	1	1	1	1	1	1	0	0	0
-62.5°	1	1	1	1	1	1	0	0	0	0	0
-63.75°	1	1	1	1	0	0	0	0	0	0	0
-65°	1	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	1	0	0	0	0	0	0	0	0	0	0
57.5°	1	1	0	0	0	0	0	0	0	0	0
56.25°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	1	0	0	0	0	0	0	0
53.75°	1	1	1	1	1	0	0	0	0	0	0
52.5°	1	1	1	1	1	1	0	0	0	0	0
51.25°	1	1	1	1	1	1	1	0	0	0	0
50°	1	1	1	1	1	1	1	1	0	0	0
48.75°	2	1	1	1	1	1	1	1	1	0	0
47.5°	2	2	1	1	1	1	1	1	1	1	0
46.25°	2	2	2	1	1	1	1	1	1	1	0
45°	2	2	2	2	1	1	1	1	1	1	1
43.75°	2	2	2	2	1	1	1	1	1	1	1
42.5°	2	2	2	2	2	1	1	1	1	1	1
41.25°	2	2	2	2	2	2	1	1	1	1	1
40°	2	2	2	2	2	2	1	1	1	1	1
38.75°	2	2	2	2	2	2	2	1	1	1	1
37.5°	3	2	2	2	2	2	2	1	1	1	1
36.25°	3	3	2	2	2	2	2	2	1	1	1
35°	3	3	2	2	2	2	2	2	1	1	1



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	3	3	3	2	2	2	2	2	2	1	1
32.5°	3	3	3	2	2	2	2	2	2	1	1
31.25°	3	3	3	3	2	2	2	2	2	2	1
30°	3	3	3	3	2	2	2	2	2	2	1
28.75°	3	3	3	3	3	2	2	2	2	2	1
27.5°	3	3	3	3	3	2	2	2	2	2	2
26.25°	3	3	3	3	3	3	2	2	2	2	2
25°	4	3	3	3	3	3	2	2	2	2	2
23.75°	4	3	3	3	3	3	2	2	2	2	2
22.5°	4	4	3	3	3	3	3	2	2	2	2
21.25°	4	4	3	3	3	3	3	2	2	2	2
20°	4	4	3	3	3	3	3	2	2	2	2
18.75°	4	4	3	3	3	3	3	2	2	2	2
17.5°	4	4	4	3	3	3	3	3	2	2	2
16.25°	4	4	4	3	3	3	3	3	2	2	2
15°	4	4	4	3	3	3	3	3	2	2	2
13.75°	5	4	4	3	3	3	3	3	2	2	2
12.5°	5	4	4	4	3	3	3	3	2	2	2
11.25°	5	4	4	4	3	3	3	3	2	2	2
10°	5	4	4	4	3	3	3	3	3	2	2
8.75°	5	4	4	4	3	3	3	3	3	2	2
7.5°	5	4	4	4	3	3	3	3	3	2	2
6.25°	5	4	4	4	3	3	3	3	3	2	2
5°	5	5	4	4	3	3	3	3	3	2	2
3.75°	5	5	4	4	3	3	3	3	3	2	2
2.5°	5	5	4	4	3	3	3	3	3	2	2
1.25°	5	5	4	4	3	3	3	3	3	2	2
0°	5	5	4	4	4	3	3	3	3	2	2
-1.25°	5	5	4	4	3	3	3	3	3	2	2
-2.5°	5	5	4	4	3	3	3	3	3	2	2
-3.75°	5	5	4	4	3	3	3	3	3	2	2
-5°	5	5	4	4	3	3	3	3	3	2	2
-6.25°	5	4	4	4	3	3	3	3	3	2	2
-7.5°	5	4	4	4	3	3	3	3	3	2	2
-8.75°	5	4	4	4	3	3	3	3	3	2	2
-10°	5	4	4	4	3	3	3	3	3	2	2
-11.25°	5	4	4	4	3	3	3	3	2	2	2
-12.5°	5	4	4	4	3	3	3	3	2	2	2
-13.75°	5	4	4	3	3	3	3	3	2	2	2
-15°	4	4	4	3	3	3	3	3	2	2	2
-16.25°	4	4	4	3	3	3	3	3	2	2	2
-17.5°	4	4	4	3	3	3	3	3	2	2	2
-18.75°	4	4	3	3	3	3	3	2	2	2	2
-20°	4	4	3	3	3	3	3	2	2	2	2
-21.25°	4	4	3	3	3	3	3	2	2	2	2



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	4	4	3	3	3	3	3	2	2	2	2
-23.75°	4	3	3	3	3	3	2	2	2	2	2
-25°	4	3	3	3	3	3	2	2	2	2	2
-26.25°	3	3	3	3	3	3	2	2	2	2	2
-27.5°	3	3	3	3	3	2	2	2	2	2	2
-28.75°	3	3	3	3	3	2	2	2	2	2	1
-30°	3	3	3	3	2	2	2	2	2	2	1
-31.25°	3	3	3	3	2	2	2	2	2	2	1
-32.5°	3	3	3	2	2	2	2	2	2	1	1
-33.75°	3	3	3	2	2	2	2	2	2	1	1
-35°	3	3	2	2	2	2	2	2	1	1	1
-36.25°	3	3	2	2	2	2	2	2	1	1	1
-37.5°	3	2	2	2	2	2	2	1	1	1	1
-38.75°	2	2	2	2	2	2	2	1	1	1	1
-40°	2	2	2	2	2	2	1	1	1	1	1
-41.25°	2	2	2	2	2	2	1	1	1	1	1
-42.5°	2	2	2	2	2	1	1	1	1	1	1
-43.75°	2	2	2	2	1	1	1	1	1	1	1
-45°	2	2	2	2	1	1	1	1	1	1	1
-46.25°	2	2	2	1	1	1	1	1	1	1	0
-47.5°	2	2	1	1	1	1	1	1	1	1	0
-48.75°	2	1	1	1	1	1	1	1	1	0	0
-50°	1	1	1	1	1	1	1	1	0	0	0
-51.25°	1	1	1	1	1	1	1	0	0	0	0
-52.5°	1	1	1	1	1	1	0	0	0	0	0
-53.75°	1	1	1	1	1	0	0	0	0	0	0
-55°	1	1	1	1	0	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	1	0	0	0	0	0	0	0	0	0
-58.75°	1	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	1	0	0	0	0	0	0	0	0	0	0
41.25°	1	0	0	0	0	0	0	0	0	0	0
40°	1	1	0	0	0	0	0	0	0	0	0
38.75°	1	1	0	0	0	0	0	0	0	0	0
37.5°	1	1	1	0	0	0	0	0	0	0	0
36.25°	1	1	1	0	0	0	0	0	0	0	0
35°	1	1	1	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	1	0	0	0	0	0	0	0
32.5°	1	1	1	1	0	0	0	0	0	0	0
31.25°	1	1	1	1	0	0	0	0	0	0	0
30°	1	1	1	1	0	0	0	0	0	0	0
28.75°	1	1	1	1	1	0	0	0	0	0	0
27.5°	1	1	1	1	1	0	0	0	0	0	0
26.25°	1	1	1	1	1	0	0	0	0	0	0
25°	1	1	1	1	1	0	0	0	0	0	0
23.75°	1	1	1	1	1	1	0	0	0	0	0
22.5°	2	1	1	1	1	1	0	0	0	0	0
21.25°	2	1	1	1	1	1	0	0	0	0	0
20°	2	1	1	1	1	1	0	0	0	0	0
18.75°	2	1	1	1	1	1	0	0	0	0	0
17.5°	2	1	1	1	1	1	0	0	0	0	0
16.25°	2	2	1	1	1	1	0	0	0	0	0
15°	2	2	1	1	1	1	0	0	0	0	0
13.75°	2	2	1	1	1	1	1	0	0	0	0
12.5°	2	2	1	1	1	1	1	0	0	0	0
11.25°	2	2	1	1	1	1	1	0	0	0	0
10°	2	2	1	1	1	1	1	0	0	0	0
8.75°	2	2	1	1	1	1	1	0	0	0	0
7.5°	2	2	1	1	1	1	1	0	0	0	0
6.25°	2	2	1	1	1	1	1	0	0	0	0
5°	2	2	1	1	1	1	1	0	0	0	0
3.75°	2	2	1	1	1	1	1	0	0	0	0
2.5°	2	2	1	1	1	1	1	0	0	0	0
1.25°	2	2	1	1	1	1	1	0	0	0	0
0°	2	2	2	1	1	1	1	0	0	0	0
-1.25°	2	2	1	1	1	1	1	0	0	0	0
-2.5°	2	2	1	1	1	1	1	0	0	0	0
-3.75°	2	2	1	1	1	1	1	0	0	0	0
-5°	2	2	1	1	1	1	1	0	0	0	0
-6.25°	2	2	1	1	1	1	1	0	0	0	0
-7.5°	2	2	1	1	1	1	1	0	0	0	0
-8.75°	2	2	1	1	1	1	1	0	0	0	0
-10°	2	2	1	1	1	1	1	0	0	0	0
-11.25°	2	2	1	1	1	1	1	0	0	0	0
-12.5°	2	2	1	1	1	1	1	0	0	0	0
-13.75°	2	2	1	1	1	1	1	0	0	0	0
-15°	2	2	1	1	1	1	0	0	0	0	0
-16.25°	2	2	1	1	1	1	0	0	0	0	0
-17.5°	2	1	1	1	1	1	0	0	0	0	0
-18.75°	2	1	1	1	1	1	0	0	0	0	0
-20°	2	1	1	1	1	1	0	0	0	0	0
-21.25°	2	1	1	1	1	1	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	1	1	1	1	1	0	0	0	0	0
-23.75°	1	1	1	1	1	1	0	0	0	0	0
-25°	1	1	1	1	1	0	0	0	0	0	0
-26.25°	1	1	1	1	1	0	0	0	0	0	0
-27.5°	1	1	1	1	1	0	0	0	0	0	0
-28.75°	1	1	1	1	1	0	0	0	0	0	0
-30°	1	1	1	1	0	0	0	0	0	0	0
-31.25°	1	1	1	1	0	0	0	0	0	0	0
-32.5°	1	1	1	1	0	0	0	0	0	0	0
-33.75°	1	1	1	1	0	0	0	0	0	0	0
-35°	1	1	1	0	0	0	0	0	0	0	0
-36.25°	1	1	1	0	0	0	0	0	0	0	0
-37.5°	1	1	1	0	0	0	0	0	0	0	0
-38.75°	1	1	0	0	0	0	0	0	0	0	0
-40°	1	1	0	0	0	0	0	0	0	0	0
-41.25°	1	0	0	0	0	0	0	0	0	0	0
-42.5°	1	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: P220525 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)