

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29472)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS, SPOT
OPTIC, BLACK HOUSING.
Light Source: (1) 4000K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp:	N/A	NEMA Type:	3H x 3V
Luminaire Lumens:	651.8 lumens	Max Intensity:	5595.6 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	66.5 lumens/watt		
Luminous Opening:	Circular (Dia: 0.25' x H: 0')		
Beam Angle (50%):	15.7°H x 15.7°V	Field Angle (10%):	35°H x 35°V
Beam Lumens:	232.4 lumens	Field Lumens:	499.3 lumens
Beam Efficiency:	35.7%	Field Efficiency:	76.6%

Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

Iso-Candela Plot




REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	
40		0.0	0.0	0.1	0.1	0.1	0.2	0.3	0.3	0.2	0.1	0.1	0.1	0.0	0.0		
30	0.0	0.0	0.0	0.1	0.1	0.3	2.0	5.7	5.7	2.0	0.3	0.1	0.1	0.0	0.0	0.0	
20		0.0	0.0	0.1	0.2	1.9	11.8	22.3	22.3	11.8	1.9	0.2	0.1	0.0	0.0		
10	0.0	0.0	0.0	0.1	0.3	5.3	21.7	89.0	89.0	21.7	5.3	0.3	0.1	0.0	0.0	0.0	
0		0.0	0.0	0.1	0.3	5.3	21.7	89.0	89.0	21.7	5.3	0.3	0.1	0.0	0.0		
-10	0.0	0.0	0.0	0.1	0.2	1.9	11.8	22.3	22.3	11.8	1.9	0.2	0.1	0.0	0.0	0.0	
-20		0.0	0.0	0.1	0.1	0.3	2.0	5.7	5.7	2.0	0.3	0.1	0.1	0.0	0.0		
-30	0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.3	0.3	0.2	0.1	0.1	0.1	0.0	0.0	0.0	
-40		0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0		
-50	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	


REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

Luminous Intensity Polar Plot



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

Luminous Intensity Plot



Beam:
 H Angle: 15.7°
 V Angle: 15.7°
 Lumens: 232.4
 Efficiency: 35.7%

Field:
 H Angle: 35°
 V Angle: 35°
 Lumens: 499.3
 Efficiency: 76.6%

Spill:
 Lumens: 152.5
 Efficiency: 23.4%

- Vertical Distribution through 0-Deg
- - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	1
36.25°	0	0	0	0	0	0	0	0	0	0	1
35°	0	0	0	0	0	0	0	0	0	0	1



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	0	0	0	0	0	0	1	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
31.25°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	0	1	1
28.75°	0	0	0	0	0	0	0	0	1	1	1
27.5°	0	0	0	0	0	0	0	0	1	1	1
26.25°	0	0	0	0	0	0	0	0	1	1	1
25°	0	0	0	0	0	0	0	0	1	1	1
23.75°	0	0	0	0	0	0	0	1	1	1	1
22.5°	0	0	0	0	0	0	0	1	1	1	1
21.25°	0	0	0	0	0	0	0	1	1	1	1
20°	0	0	0	0	0	0	0	1	1	1	1
18.75°	0	0	0	0	0	0	0	1	1	1	1
17.5°	0	0	0	0	0	0	0	1	1	1	1
16.25°	0	0	0	0	0	0	0	1	1	1	1
15°	0	0	0	0	0	0	0	1	1	1	1
13.75°	0	0	0	0	0	0	1	1	1	1	1
12.5°	0	0	0	0	0	0	1	1	1	1	1
11.25°	0	0	0	0	0	0	1	1	1	1	1
10°	0	0	0	0	0	0	1	1	1	1	1
8.75°	0	0	0	0	0	0	1	1	1	1	1
7.5°	0	0	0	0	0	0	1	1	1	1	1
6.25°	0	0	0	0	0	0	1	1	1	1	1
5°	0	0	0	0	0	0	1	1	1	1	1
3.75°	0	0	0	0	0	0	1	1	1	1	1
2.5°	0	0	0	0	0	0	1	1	1	1	1
1.25°	0	0	0	0	0	0	1	1	1	1	1
0°	0	0	0	0	0	0	1	1	1	1	2
-1.25°	0	0	0	0	0	0	1	1	1	1	1
-2.5°	0	0	0	0	0	0	1	1	1	1	1
-3.75°	0	0	0	0	0	0	1	1	1	1	1
-5°	0	0	0	0	0	0	1	1	1	1	1
-6.25°	0	0	0	0	0	0	1	1	1	1	1
-7.5°	0	0	0	0	0	0	1	1	1	1	1
-8.75°	0	0	0	0	0	0	1	1	1	1	1
-10°	0	0	0	0	0	0	1	1	1	1	1
-11.25°	0	0	0	0	0	0	1	1	1	1	1
-12.5°	0	0	0	0	0	0	1	1	1	1	1
-13.75°	0	0	0	0	0	0	1	1	1	1	1
-15°	0	0	0	0	0	0	0	1	1	1	1
-16.25°	0	0	0	0	0	0	0	1	1	1	1
-17.5°	0	0	0	0	0	0	0	1	1	1	1
-18.75°	0	0	0	0	0	0	0	1	1	1	1
-20°	0	0	0	0	0	0	0	1	1	1	1
-21.25°	0	0	0	0	0	0	0	1	1	1	1



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	0	0	0	0	0	1	1	1	1
-23.75°	0	0	0	0	0	0	0	1	1	1	1
-25°	0	0	0	0	0	0	0	0	1	1	1
-26.25°	0	0	0	0	0	0	0	0	1	1	1
-27.5°	0	0	0	0	0	0	0	0	1	1	1
-28.75°	0	0	0	0	0	0	0	0	1	1	1
-30°	0	0	0	0	0	0	0	0	0	1	1
-31.25°	0	0	0	0	0	0	0	0	0	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-33.75°	0	0	0	0	0	0	0	0	0	1	1
-35°	0	0	0	0	0	0	0	0	0	0	1
-36.25°	0	0	0	0	0	0	0	0	0	0	1
-37.5°	0	0	0	0	0	0	0	0	0	0	1
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	1
55°	0	0	0	0	0	0	0	0	1	1	1
53.75°	0	0	0	0	0	0	0	1	1	1	1
52.5°	0	0	0	0	0	0	1	1	1	1	1
51.25°	0	0	0	0	0	1	1	1	1	1	1
50°	0	0	0	0	1	1	1	1	1	1	1
48.75°	0	0	0	1	1	1	1	1	1	1	1
47.5°	0	0	1	1	1	1	1	1	1	1	1
46.25°	0	0	1	1	1	1	1	1	1	2	2
45°	0	0	1	1	1	1	1	1	2	2	2
43.75°	0	0	1	1	1	1	1	1	2	2	2
42.5°	0	1	1	1	1	1	1	2	2	2	2
41.25°	0	1	1	1	1	1	2	2	2	2	2
40°	1	1	1	1	1	1	2	2	2	2	2
38.75°	1	1	1	1	1	2	2	2	2	2	2
37.5°	1	1	1	1	1	2	2	2	2	2	2
36.25°	1	1	1	1	2	2	2	2	2	2	2
35°	1	1	1	1	2	2	2	2	2	2	2



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	1	1	2	2	2	2	2	2	3
32.5°	1	1	1	1	2	2	2	2	2	2	3
31.25°	1	1	1	2	2	2	2	2	2	3	3
30°	1	1	1	2	2	2	2	2	2	3	3
28.75°	1	1	1	2	2	2	2	2	3	3	3
27.5°	1	1	2	2	2	2	2	2	3	3	3
26.25°	1	1	2	2	2	2	2	3	3	3	3
25°	1	1	2	2	2	2	2	3	3	3	3
23.75°	1	1	2	2	2	2	2	3	3	3	3
22.5°	1	2	2	2	2	2	2	3	3	3	3
21.25°	1	2	2	2	2	2	3	3	3	3	3
20°	1	2	2	2	2	2	3	3	3	3	3
18.75°	1	2	2	2	2	2	3	3	3	3	3
17.5°	1	2	2	2	2	2	3	3	3	3	3
16.25°	2	2	2	2	2	3	3	3	3	3	3
15°	2	2	2	2	2	3	3	3	3	3	3
13.75°	2	2	2	2	2	3	3	3	3	3	3
12.5°	2	2	2	2	2	3	3	3	3	3	3
11.25°	2	2	2	2	2	3	3	3	3	3	3
10°	2	2	2	2	2	3	3	3	3	3	3
8.75°	2	2	2	2	3	3	3	3	3	3	3
7.5°	2	2	2	2	3	3	3	3	3	3	3
6.25°	2	2	2	2	3	3	3	3	3	3	3
5°	2	2	2	2	3	3	3	3	3	3	3
3.75°	2	2	2	2	3	3	3	3	3	3	3
2.5°	2	2	2	2	3	3	3	3	3	3	3
1.25°	2	2	2	2	3	3	3	3	3	3	3
0°	2	2	2	2	3	3	3	3	3	3	3
-1.25°	2	2	2	2	3	3	3	3	3	3	3
-2.5°	2	2	2	2	3	3	3	3	3	3	3
-3.75°	2	2	2	2	3	3	3	3	3	3	3
-5°	2	2	2	2	3	3	3	3	3	3	3
-6.25°	2	2	2	2	3	3	3	3	3	3	3
-7.5°	2	2	2	2	3	3	3	3	3	3	3
-8.75°	2	2	2	2	3	3	3	3	3	3	3
-10°	2	2	2	2	2	3	3	3	3	3	3
-11.25°	2	2	2	2	2	3	3	3	3	3	3
-12.5°	2	2	2	2	2	3	3	3	3	3	3
-13.75°	2	2	2	2	2	3	3	3	3	3	3
-15°	2	2	2	2	2	3	3	3	3	3	3
-16.25°	2	2	2	2	2	3	3	3	3	3	3
-17.5°	1	2	2	2	2	2	3	3	3	3	3
-18.75°	1	2	2	2	2	2	3	3	3	3	3
-20°	1	2	2	2	2	2	3	3	3	3	3
-21.25°	1	2	2	2	2	2	3	3	3	3	3



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	1	2	2	2	2	2	2	3	3	3	3
-23.75°	1	1	2	2	2	2	2	3	3	3	3
-25°	1	1	2	2	2	2	2	3	3	3	3
-26.25°	1	1	2	2	2	2	2	3	3	3	3
-27.5°	1	1	2	2	2	2	2	2	3	3	3
-28.75°	1	1	1	2	2	2	2	2	3	3	3
-30°	1	1	1	2	2	2	2	2	2	3	3
-31.25°	1	1	1	2	2	2	2	2	2	3	3
-32.5°	1	1	1	1	2	2	2	2	2	2	3
-33.75°	1	1	1	1	2	2	2	2	2	2	3
-35°	1	1	1	1	1	2	2	2	2	2	2
-36.25°	1	1	1	1	1	2	2	2	2	2	2
-37.5°	1	1	1	1	1	1	2	2	2	2	2
-38.75°	1	1	1	1	1	1	2	2	2	2	2
-40°	1	1	1	1	1	1	1	2	2	2	2
-41.25°	0	1	1	1	1	1	1	2	2	2	2
-42.5°	0	1	1	1	1	1	1	1	2	2	2
-43.75°	0	0	1	1	1	1	1	1	1	2	2
-45°	0	0	1	1	1	1	1	1	1	2	2
-46.25°	0	0	0	1	1	1	1	1	1	1	2
-47.5°	0	0	0	1	1	1	1	1	1	1	1
-48.75°	0	0	0	0	1	1	1	1	1	1	1
-50°	0	0	0	0	0	1	1	1	1	1	1
-51.25°	0	0	0	0	0	0	1	1	1	1	1
-52.5°	0	0	0	0	0	0	0	1	1	1	1
-53.75°	0	0	0	0	0	0	0	0	1	1	1
-55°	0	0	0	0	0	0	0	0	0	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	1	1
62.5°	0	0	0	0	0	0	0	1	1	1	1
61.25°	0	0	0	0	0	1	1	1	1	1	1
60°	0	0	0	1	1	1	1	1	1	1	1
58.75°	0	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	2
55°	1	1	1	1	1	1	1	1	2	2	2
53.75°	1	1	1	1	1	1	2	2	2	2	2
52.5°	1	1	1	1	1	2	2	2	2	2	2
51.25°	1	1	1	2	2	2	2	2	2	2	2
50°	1	1	2	2	2	2	2	2	2	2	2
48.75°	1	2	2	2	2	2	2	2	2	2	3
47.5°	2	2	2	2	2	2	2	2	2	3	3
46.25°	2	2	2	2	2	2	2	2	3	3	3
45°	2	2	2	2	2	2	3	3	3	3	3
43.75°	2	2	2	2	2	3	3	3	3	3	3
42.5°	2	2	2	2	3	3	3	3	3	3	3
41.25°	2	2	2	3	3	3	3	3	3	3	3
40°	2	2	2	3	3	3	3	3	3	3	3
38.75°	2	2	3	3	3	3	3	3	3	3	3
37.5°	2	3	3	3	3	3	3	3	3	3	3
36.25°	3	3	3	3	3	3	3	3	3	3	4
35°	3	3	3	3	3	3	3	3	3	4	4



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	3	3	3	3	3	3	3	3	3	4	4
32.5°	3	3	3	3	3	3	3	3	4	4	4
31.25°	3	3	3	3	3	3	3	4	4	4	4
30°	3	3	3	3	3	3	4	4	4	4	4
28.75°	3	3	3	3	3	3	4	4	4	4	4
27.5°	3	3	3	3	3	4	4	4	4	4	5
26.25°	3	3	3	3	3	4	4	4	4	4	5
25°	3	3	3	3	4	4	4	4	4	5	5
23.75°	3	3	3	3	4	4	4	4	4	5	5
22.5°	3	3	3	4	4	4	4	4	5	5	5
21.25°	3	3	3	4	4	4	4	5	5	5	6
20°	3	3	4	4	4	4	4	5	5	5	6
18.75°	3	3	4	4	4	4	4	5	5	6	6
17.5°	3	3	4	4	4	4	5	5	5	6	6
16.25°	3	3	4	4	4	4	5	5	6	6	6
15°	3	4	4	4	4	4	5	5	6	6	6
13.75°	3	4	4	4	4	5	5	5	6	6	7
12.5°	3	4	4	4	4	5	5	5	6	6	7
11.25°	3	4	4	4	4	5	5	6	6	6	7
10°	3	4	4	4	4	5	5	6	6	6	7
8.75°	4	4	4	4	5	5	5	6	6	7	7
7.5°	4	4	4	4	5	5	5	6	6	7	7
6.25°	4	4	4	4	5	5	5	6	6	7	8
5°	4	4	4	4	5	5	6	6	6	7	8
3.75°	4	4	4	4	5	5	6	6	6	7	8
2.5°	4	4	4	4	5	5	6	6	6	7	8
1.25°	4	4	4	4	5	5	6	6	6	7	8
0°	4	4	4	4	5	5	6	6	6	7	8
-1.25°	4	4	4	4	5	5	6	6	6	7	8
-2.5°	4	4	4	4	5	5	6	6	6	7	8
-3.75°	4	4	4	4	5	5	6	6	6	7	8
-5°	4	4	4	4	5	5	6	6	6	7	8
-6.25°	4	4	4	4	5	5	5	6	6	7	8
-7.5°	4	4	4	4	5	5	5	6	6	7	7
-8.75°	4	4	4	4	5	5	5	6	6	7	7
-10°	3	4	4	4	4	5	5	6	6	6	7
-11.25°	3	4	4	4	4	5	5	6	6	6	7
-12.5°	3	4	4	4	4	5	5	5	6	6	7
-13.75°	3	4	4	4	4	5	5	5	6	6	7
-15°	3	4	4	4	4	4	5	5	6	6	6
-16.25°	3	3	4	4	4	4	5	5	6	6	6
-17.5°	3	3	4	4	4	4	5	5	5	6	6
-18.75°	3	3	4	4	4	4	4	5	5	6	6
-20°	3	3	4	4	4	4	4	5	5	5	6
-21.25°	3	3	3	4	4	4	4	5	5	5	6



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	3	3	3	4	4	4	4	4	5	5	5
-23.75°	3	3	3	3	4	4	4	4	4	5	5
-25°	3	3	3	3	4	4	4	4	4	5	5
-26.25°	3	3	3	3	3	4	4	4	4	4	5
-27.5°	3	3	3	3	3	4	4	4	4	4	5
-28.75°	3	3	3	3	3	3	4	4	4	4	4
-30°	3	3	3	3	3	3	4	4	4	4	4
-31.25°	3	3	3	3	3	3	3	4	4	4	4
-32.5°	3	3	3	3	3	3	3	3	4	4	4
-33.75°	3	3	3	3	3	3	3	3	3	4	4
-35°	3	3	3	3	3	3	3	3	3	4	4
-36.25°	3	3	3	3	3	3	3	3	3	3	4
-37.5°	2	3	3	3	3	3	3	3	3	3	3
-38.75°	2	2	3	3	3	3	3	3	3	3	3
-40°	2	2	2	3	3	3	3	3	3	3	3
-41.25°	2	2	2	2	3	3	3	3	3	3	3
-42.5°	2	2	2	2	2	3	3	3	3	3	3
-43.75°	2	2	2	2	2	2	3	3	3	3	3
-45°	2	2	2	2	2	2	2	3	3	3	3
-46.25°	2	2	2	2	2	2	2	2	2	3	3
-47.5°	2	2	2	2	2	2	2	2	2	2	3
-48.75°	1	2	2	2	2	2	2	2	2	2	3
-50°	1	1	2	2	2	2	2	2	2	2	2
-51.25°	1	1	1	2	2	2	2	2	2	2	2
-52.5°	1	1	1	1	1	2	2	2	2	2	2
-53.75°	1	1	1	1	1	1	2	2	2	2	2
-55°	1	1	1	1	1	1	1	1	2	2	2
-56.25°	1	1	1	1	1	1	1	1	1	1	2
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	0	1	1	1	1	1	1	1	1	1	1
-60°	0	0	0	1	1	1	1	1	1	1	1
-61.25°	0	0	0	0	0	1	1	1	1	1	1
-62.5°	0	0	0	0	0	0	0	1	1	1	1
-63.75°	0	0	0	0	0	0	0	0	0	1	1
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	1	1
66.25°	0	0	0	0	0	1	1	1	1	1	1
65°	0	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	2
60°	1	1	1	1	1	1	2	2	2	2	2
58.75°	1	1	1	2	2	2	2	2	2	2	2
57.5°	1	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	2
53.75°	2	2	2	2	2	2	2	3	3	3	3
52.5°	2	2	2	2	2	3	3	3	3	3	3
51.25°	2	2	2	3	3	3	3	3	3	3	3
50°	2	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	3
47.5°	3	3	3	3	3	3	3	3	3	3	3
46.25°	3	3	3	3	3	3	3	3	3	3	3
45°	3	3	3	3	3	3	3	3	3	3	4
43.75°	3	3	3	3	3	3	3	3	4	4	4
42.5°	3	3	3	3	3	3	4	4	4	4	4
41.25°	3	3	3	3	4	4	4	4	4	4	4
40°	3	3	3	4	4	4	4	4	4	4	4
38.75°	3	3	4	4	4	4	4	4	4	4	5
37.5°	4	4	4	4	4	4	4	4	5	5	5
36.25°	4	4	4	4	4	4	5	5	5	5	5
35°	4	4	4	4	4	5	5	5	5	6	6



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	4	4	4	4	5	5	5	5	6	6	6
32.5°	4	4	4	5	5	5	5	6	6	6	6
31.25°	4	4	5	5	5	6	6	6	6	7	7
30°	4	5	5	5	6	6	6	6	7	7	7
28.75°	5	5	5	6	6	6	6	7	7	8	8
27.5°	5	5	5	6	6	6	7	7	8	8	9
26.25°	5	5	6	6	6	7	7	8	8	10	12
25°	5	6	6	6	7	7	8	8	10	12	14
23.75°	6	6	6	7	7	8	8	10	12	15	17
22.5°	6	6	6	7	7	8	9	12	14	17	20
21.25°	6	6	7	7	8	9	11	14	17	20	23
20°	6	6	7	8	9	10	13	16	20	23	27
18.75°	6	7	7	8	9	12	15	19	22	26	31
17.5°	6	7	8	9	11	14	17	21	25	29	42
16.25°	7	7	8	9	13	16	20	23	28	38	63
15°	7	8	9	11	14	18	22	26	32	51	91
13.75°	7	8	9	12	16	20	24	28	41	73	126
12.5°	7	8	10	14	17	21	25	32	54	100	161
11.25°	8	9	11	15	19	23	28	40	72	129	195
10°	8	9	12	16	20	24	30	47	92	157	229
8.75°	8	10	13	17	21	26	34	61	115	183	260
7.5°	8	11	14	18	22	27	39	74	135	207	287
6.25°	9	11	15	19	23	29	43	85	153	229	311
5°	9	12	15	20	24	30	49	99	168	247	330
3.75°	9	12	16	20	25	31	55	109	180	262	344
2.5°	9	12	16	21	25	33	60	117	189	272	354
1.25°	9	13	16	21	25	34	63	121	194	278	359
0°	9	13	16	21	25	34	64	123	196	281	361
-1.25°	9	13	16	21	25	34	63	121	194	278	359
-2.5°	9	12	16	21	25	33	60	117	189	272	354
-3.75°	9	12	16	20	25	31	55	109	180	262	344
-5°	9	12	15	20	24	30	49	99	168	247	330
-6.25°	9	11	15	19	23	29	43	85	153	229	311
-7.5°	8	11	14	18	22	27	39	74	135	207	287
-8.75°	8	10	13	17	21	26	34	61	115	183	260
-10°	8	9	12	16	20	24	30	47	92	157	229
-11.25°	8	9	11	15	19	23	28	40	72	129	195
-12.5°	7	8	10	14	17	21	25	32	54	100	161
-13.75°	7	8	9	12	16	20	24	28	41	73	126
-15°	7	8	9	11	14	18	22	26	32	51	91
-16.25°	7	7	8	9	13	16	20	23	28	38	63
-17.5°	6	7	8	9	11	14	17	21	25	29	42
-18.75°	6	7	7	8	9	12	15	19	22	26	31
-20°	6	6	7	8	9	10	13	16	20	23	27
-21.25°	6	6	7	7	8	9	11	14	17	20	23



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	6	6	6	7	7	8	9	12	14	17	20
-23.75°	6	6	6	7	7	8	8	10	12	15	17
-25°	5	6	6	6	7	7	8	8	10	12	14
-26.25°	5	5	6	6	6	7	7	8	8	10	12
-27.5°	5	5	5	6	6	6	7	7	8	8	9
-28.75°	5	5	5	6	6	6	6	7	7	8	8
-30°	4	5	5	5	6	6	6	6	7	7	7
-31.25°	4	4	5	5	5	6	6	6	6	7	7
-32.5°	4	4	4	5	5	5	5	6	6	6	6
-33.75°	4	4	4	4	5	5	5	5	6	6	6
-35°	4	4	4	4	4	5	5	5	5	6	6
-36.25°	4	4	4	4	4	4	5	5	5	5	5
-37.5°	4	4	4	4	4	4	4	4	5	5	5
-38.75°	3	3	4	4	4	4	4	4	4	4	5
-40°	3	3	3	4	4	4	4	4	4	4	4
-41.25°	3	3	3	3	4	4	4	4	4	4	4
-42.5°	3	3	3	3	3	3	4	4	4	4	4
-43.75°	3	3	3	3	3	3	3	3	4	4	4
-45°	3	3	3	3	3	3	3	3	3	3	4
-46.25°	3	3	3	3	3	3	3	3	3	3	3
-47.5°	3	3	3	3	3	3	3	3	3	3	3
-48.75°	3	3	3	3	3	3	3	3	3	3	3
-50°	2	3	3	3	3	3	3	3	3	3	3
-51.25°	2	2	2	3	3	3	3	3	3	3	3
-52.5°	2	2	2	2	2	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	2	3	3	3	3
-55°	2	2	2	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	1	2	2	2	2	2	2	2	2	2	2
-58.75°	1	1	1	2	2	2	2	2	2	2	2
-60°	1	1	1	1	1	1	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	2
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	0	1	1	1	1	1	1	1	1	1	1
-66.25°	0	0	0	0	0	1	1	1	1	1	1
-67.5°	0	0	0	0	0	0	0	0	0	1	1
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	3
56.25°	2	2	2	2	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	4
47.5°	3	3	3	3	3	4	4	4	4	4	4
46.25°	3	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	4	4	4	4	4	5
42.5°	4	4	4	4	4	4	5	5	5	5	5
41.25°	4	4	4	5	5	5	5	5	5	5	5
40°	5	5	5	5	5	5	5	5	6	6	6
38.75°	5	5	5	5	6	6	6	6	6	6	6
37.5°	5	5	6	6	6	6	6	6	6	6	7
36.25°	6	6	6	6	6	6	7	7	7	7	7
35°	6	6	6	6	7	7	7	7	8	8	8



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	6	6	7	7	7	8	8	8	9	9	10
32.5°	7	7	7	8	8	9	9	10	11	12	13
31.25°	7	8	8	9	9	11	12	14	15	16	17
30°	8	9	9	11	13	14	16	17	19	20	21
28.75°	9	10	12	14	16	18	20	21	23	24	26
27.5°	11	13	15	17	20	22	24	25	28	30	34
26.25°	14	16	19	21	23	26	28	32	40	47	61
25°	17	20	22	25	28	32	41	54	72	92	115
23.75°	20	23	26	29	38	51	73	100	129	157	183
22.5°	23	27	31	42	63	91	126	161	195	229	260
21.25°	27	33	45	72	108	148	188	229	269	305	337
20°	33	46	76	118	163	209	256	301	341	375	402
18.75°	45	76	121	170	222	274	324	367	402	428	446
17.5°	72	118	170	226	284	338	384	418	443	462	479
16.25°	108	163	222	284	342	392	428	452	474	495	520
15°	148	209	274	338	392	431	457	482	509	537	567
13.75°	188	256	324	384	428	457	484	515	550	585	626
12.5°	229	301	367	418	452	482	515	554	596	645	713
11.25°	269	341	402	443	474	509	550	596	654	732	822
10°	305	375	428	462	495	537	585	645	732	835	948
8.75°	337	402	446	479	520	567	626	713	822	948	1106
7.5°	363	422	460	496	542	598	676	785	916	1082	1298
6.25°	385	438	472	513	564	628	726	853	1012	1229	1517
5°	400	447	483	528	583	660	777	922	1116	1384	1748
3.75°	410	454	492	541	602	692	819	978	1210	1539	1983
2.5°	418	460	499	551	615	715	851	1032	1294	1666	2164
1.25°	423	463	504	557	624	728	873	1066	1345	1745	2286
0°	424	464	505	559	627	733	881	1078	1363	1771	2330
-1.25°	423	463	504	557	624	728	873	1066	1345	1745	2286
-2.5°	418	460	499	551	615	715	851	1032	1294	1666	2164
-3.75°	410	454	492	541	602	692	819	978	1210	1539	1983
-5°	400	447	483	528	583	660	777	922	1116	1384	1748
-6.25°	385	438	472	513	564	628	726	853	1012	1229	1517
-7.5°	363	422	460	496	542	598	676	785	916	1082	1298
-8.75°	337	402	446	479	520	567	626	713	822	948	1106
-10°	305	375	428	462	495	537	585	645	732	835	948
-11.25°	269	341	402	443	474	509	550	596	654	732	822
-12.5°	229	301	367	418	452	482	515	554	596	645	713
-13.75°	188	256	324	384	428	457	484	515	550	585	626
-15°	148	209	274	338	392	431	457	482	509	537	567
-16.25°	108	163	222	284	342	392	428	452	474	495	520
-17.5°	72	118	170	226	284	338	384	418	443	462	479
-18.75°	45	76	121	170	222	274	324	367	402	428	446
-20°	33	46	76	118	163	209	256	301	341	375	402
-21.25°	27	33	45	72	108	148	188	229	269	305	337



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	23	27	31	42	63	91	126	161	195	229	260
-23.75°	20	23	26	29	38	51	73	100	129	157	183
-25°	17	20	22	25	28	32	41	54	72	92	115
-26.25°	14	16	19	21	23	26	28	32	40	47	61
-27.5°	11	13	15	17	20	22	24	25	28	30	34
-28.75°	9	10	12	14	16	18	20	21	23	24	26
-30°	8	9	9	11	13	14	16	17	19	20	21
-31.25°	7	8	8	9	9	11	12	14	15	16	17
-32.5°	7	7	7	8	8	9	9	10	11	12	13
-33.75°	6	6	7	7	7	8	8	8	9	9	10
-35°	6	6	6	6	7	7	7	7	8	8	8
-36.25°	6	6	6	6	6	6	7	7	7	7	7
-37.5°	5	5	6	6	6	6	6	6	6	6	7
-38.75°	5	5	5	5	6	6	6	6	6	6	6
-40°	5	5	5	5	5	5	5	5	6	6	6
-41.25°	4	4	4	5	5	5	5	5	5	5	5
-42.5°	4	4	4	4	4	4	5	5	5	5	5
-43.75°	4	4	4	4	4	4	4	4	4	4	5
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	3	4	4	4	4	4	4	4	4	4	4
-47.5°	3	3	3	3	3	4	4	4	4	4	4
-48.75°	3	3	3	3	3	3	3	3	3	3	4
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	2	2	2	3	3	3	3	3	3	3
-57.5°	2	2	2	2	2	2	2	2	2	2	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	0	0	0	0	0	0	1	1	1	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	2	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	5	5	5	5	5	5	5	5	5	5	5
42.5°	5	5	5	5	5	5	5	5	5	5	5
41.25°	5	5	6	6	6	6	6	6	6	6	6
40°	6	6	6	6	6	6	6	6	6	6	6
38.75°	6	6	6	6	6	6	6	6	6	6	6
37.5°	7	7	7	7	7	7	7	7	7	7	7
36.25°	7	8	8	8	8	8	8	8	8	8	8
35°	8	9	9	9	9	9	9	9	9	9	9



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	11	11	12	12	12	13	13	13	12	12	12
32.5°	14	15	15	16	16	16	16	16	16	16	15
31.25°	18	19	20	20	21	21	21	21	21	20	20
30°	22	23	24	25	25	25	25	25	25	25	24
28.75°	27	29	30	31	33	34	34	34	33	31	30
27.5°	39	43	49	55	60	63	64	63	60	55	49
26.25°	74	85	99	109	117	121	123	121	117	109	99
25°	135	153	168	180	189	194	196	194	189	180	168
23.75°	207	229	247	262	272	278	281	278	272	262	247
22.5°	287	311	330	344	354	359	361	359	354	344	330
21.25°	363	385	400	410	418	423	424	423	418	410	400
20°	422	438	447	454	460	463	464	463	460	454	447
18.75°	460	472	483	492	499	504	505	504	499	492	483
17.5°	496	513	528	541	551	557	559	557	551	541	528
16.25°	542	564	583	602	615	624	627	624	615	602	583
15°	598	628	660	692	715	728	733	728	715	692	660
13.75°	676	726	777	819	851	873	881	873	851	819	777
12.5°	785	853	922	978	1032	1066	1078	1066	1032	978	922
11.25°	916	1012	1116	1210	1294	1345	1363	1345	1294	1210	1116
10°	1082	1229	1384	1539	1666	1745	1771	1745	1666	1539	1384
8.75°	1298	1517	1748	1983	2164	2286	2330	2286	2164	1983	1748
7.5°	1567	1879	2204	2513	2754	2917	2972	2917	2754	2513	2204
6.25°	1879	2290	2703	3089	3385	3572	3637	3572	3385	3089	2703
5°	2204	2703	3207	3639	3975	4193	4271	4193	3975	3639	3207
3.75°	2513	3089	3639	4119	4493	4739	4812	4739	4493	4119	3639
2.5°	2754	3385	3975	4493	4890	5141	5221	5141	4890	4493	3975
1.25°	2917	3572	4193	4739	5141	5396	5482	5396	5141	4739	4193
0°	2972	3637	4271	4812	5221	5482	5596	5482	5221	4812	4271
-1.25°	2917	3572	4193	4739	5141	5396	5482	5396	5141	4739	4193
-2.5°	2754	3385	3975	4493	4890	5141	5221	5141	4890	4493	3975
-3.75°	2513	3089	3639	4119	4493	4739	4812	4739	4493	4119	3639
-5°	2204	2703	3207	3639	3975	4193	4271	4193	3975	3639	3207
-6.25°	1879	2290	2703	3089	3385	3572	3637	3572	3385	3089	2703
-7.5°	1567	1879	2204	2513	2754	2917	2972	2917	2754	2513	2204
-8.75°	1298	1517	1748	1983	2164	2286	2330	2286	2164	1983	1748
-10°	1082	1229	1384	1539	1666	1745	1771	1745	1666	1539	1384
-11.25°	916	1012	1116	1210	1294	1345	1363	1345	1294	1210	1116
-12.5°	785	853	922	978	1032	1066	1078	1066	1032	978	922
-13.75°	676	726	777	819	851	873	881	873	851	819	777
-15°	598	628	660	692	715	728	733	728	715	692	660
-16.25°	542	564	583	602	615	624	627	624	615	602	583
-17.5°	496	513	528	541	551	557	559	557	551	541	528
-18.75°	460	472	483	492	499	504	505	504	499	492	483
-20°	422	438	447	454	460	463	464	463	460	454	447
-21.25°	363	385	400	410	418	423	424	423	418	410	400



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	287	311	330	344	354	359	361	359	354	344	330
-23.75°	207	229	247	262	272	278	281	278	272	262	247
-25°	135	153	168	180	189	194	196	194	189	180	168
-26.25°	74	85	99	109	117	121	123	121	117	109	99
-27.5°	39	43	49	55	60	63	64	63	60	55	49
-28.75°	27	29	30	31	33	34	34	34	33	31	30
-30°	22	23	24	25	25	25	25	25	25	25	24
-31.25°	18	19	20	20	21	21	21	21	21	20	20
-32.5°	14	15	15	16	16	16	16	16	16	16	15
-33.75°	11	11	12	12	12	13	13	13	12	12	12
-35°	8	9	9	9	9	9	9	9	9	9	9
-36.25°	7	8	8	8	8	8	8	8	8	8	8
-37.5°	7	7	7	7	7	7	7	7	7	7	7
-38.75°	6	6	6	6	6	6	6	6	6	6	6
-40°	6	6	6	6	6	6	6	6	6	6	6
-41.25°	5	5	6	6	6	6	6	6	6	6	6
-42.5°	5	5	5	5	5	5	5	5	5	5	5
-43.75°	5	5	5	5	5	5	5	5	5	5	5
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	2	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	1	1	1	0	0	0	0
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	2	2	2	2	2	2	2	2
56.25°	3	3	3	3	3	3	3	3	3	2	2
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	4	4	4	3	3	3	3	3	3	3	3
47.5°	4	4	4	4	4	4	4	4	3	3	3
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	5	5	5	4	4	4	4	4	4	4	4
42.5°	5	5	5	5	5	5	5	4	4	4	4
41.25°	5	5	5	5	5	5	5	5	5	5	4
40°	6	6	6	6	6	5	5	5	5	5	5
38.75°	6	6	6	6	6	6	6	6	6	5	5
37.5°	7	7	7	6	6	6	6	6	6	6	6
36.25°	8	7	7	7	7	7	7	6	6	6	6
35°	9	8	8	8	8	7	7	7	7	6	6



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	11	11	10	9	9	8	8	8	7	7	7
32.5°	15	14	13	12	11	10	9	9	8	8	7
31.25°	19	18	17	16	15	14	12	11	9	9	8
30°	23	22	21	20	19	17	16	14	13	11	9
28.75°	29	27	26	24	23	21	20	18	16	14	12
27.5°	43	39	34	30	28	25	24	22	20	17	15
26.25°	85	74	61	47	40	32	28	26	23	21	19
25°	153	135	115	92	72	54	41	32	28	25	22
23.75°	229	207	183	157	129	100	73	51	38	29	26
22.5°	311	287	260	229	195	161	126	91	63	42	31
21.25°	385	363	337	305	269	229	188	148	108	72	45
20°	438	422	402	375	341	301	256	209	163	118	76
18.75°	472	460	446	428	402	367	324	274	222	170	121
17.5°	513	496	479	462	443	418	384	338	284	226	170
16.25°	564	542	520	495	474	452	428	392	342	284	222
15°	628	598	567	537	509	482	457	431	392	338	274
13.75°	726	676	626	585	550	515	484	457	428	384	324
12.5°	853	785	713	645	596	554	515	482	452	418	367
11.25°	1012	916	822	732	654	596	550	509	474	443	402
10°	1229	1082	948	835	732	645	585	537	495	462	428
8.75°	1517	1298	1106	948	822	713	626	567	520	479	446
7.5°	1879	1567	1298	1082	916	785	676	598	542	496	460
6.25°	2290	1879	1517	1229	1012	853	726	628	564	513	472
5°	2703	2204	1748	1384	1116	922	777	660	583	528	483
3.75°	3089	2513	1983	1539	1210	978	819	692	602	541	492
2.5°	3385	2754	2164	1666	1294	1032	851	715	615	551	499
1.25°	3572	2917	2286	1745	1345	1066	873	728	624	557	504
0°	3637	2972	2330	1771	1363	1078	881	733	627	559	505
-1.25°	3572	2917	2286	1745	1345	1066	873	728	624	557	504
-2.5°	3385	2754	2164	1666	1294	1032	851	715	615	551	499
-3.75°	3089	2513	1983	1539	1210	978	819	692	602	541	492
-5°	2703	2204	1748	1384	1116	922	777	660	583	528	483
-6.25°	2290	1879	1517	1229	1012	853	726	628	564	513	472
-7.5°	1879	1567	1298	1082	916	785	676	598	542	496	460
-8.75°	1517	1298	1106	948	822	713	626	567	520	479	446
-10°	1229	1082	948	835	732	645	585	537	495	462	428
-11.25°	1012	916	822	732	654	596	550	509	474	443	402
-12.5°	853	785	713	645	596	554	515	482	452	418	367
-13.75°	726	676	626	585	550	515	484	457	428	384	324
-15°	628	598	567	537	509	482	457	431	392	338	274
-16.25°	564	542	520	495	474	452	428	392	342	284	222
-17.5°	513	496	479	462	443	418	384	338	284	226	170
-18.75°	472	460	446	428	402	367	324	274	222	170	121
-20°	438	422	402	375	341	301	256	209	163	118	76
-21.25°	385	363	337	305	269	229	188	148	108	72	45



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	311	287	260	229	195	161	126	91	63	42	31
-23.75°	229	207	183	157	129	100	73	51	38	29	26
-25°	153	135	115	92	72	54	41	32	28	25	22
-26.25°	85	74	61	47	40	32	28	26	23	21	19
-27.5°	43	39	34	30	28	25	24	22	20	17	15
-28.75°	29	27	26	24	23	21	20	18	16	14	12
-30°	23	22	21	20	19	17	16	14	13	11	9
-31.25°	19	18	17	16	15	14	12	11	9	9	8
-32.5°	15	14	13	12	11	10	9	9	8	8	7
-33.75°	11	11	10	9	9	8	8	8	7	7	7
-35°	9	8	8	8	8	7	7	7	7	6	6
-36.25°	8	7	7	7	7	7	7	6	6	6	6
-37.5°	7	7	7	6	6	6	6	6	6	6	6
-38.75°	6	6	6	6	6	6	6	6	6	5	5
-40°	6	6	6	6	6	5	5	5	5	5	5
-41.25°	5	5	5	5	5	5	5	5	5	5	4
-42.5°	5	5	5	5	5	5	5	4	4	4	4
-43.75°	5	5	5	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	3	3	3
-48.75°	4	4	4	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	2	2
-57.5°	3	3	3	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	1	1	1	1	0	0	0	0	0	0	0
66.25°	1	1	1	1	1	1	1	1	0	0	0
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	2	2	1	1	1	1	1	1	1	1
60°	2	2	2	2	2	2	2	1	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	2	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	2	2	2	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	2	2	2	2	2
52.5°	3	3	3	3	3	3	3	3	2	2	2
51.25°	3	3	3	3	3	3	3	3	3	3	2
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	3
47.5°	3	3	3	3	3	3	3	3	3	3	3
46.25°	4	3	3	3	3	3	3	3	3	3	3
45°	4	4	4	3	3	3	3	3	3	3	3
43.75°	4	4	4	4	4	3	3	3	3	3	3
42.5°	4	4	4	4	4	4	4	3	3	3	3
41.25°	4	4	4	4	4	4	4	4	4	3	3
40°	5	5	4	4	4	4	4	4	4	4	3
38.75°	5	5	5	4	4	4	4	4	4	4	4
37.5°	5	5	5	5	5	4	4	4	4	4	4
36.25°	6	6	5	5	5	5	5	4	4	4	4
35°	6	6	6	6	5	5	5	5	4	4	4



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	6	6	6	6	6	5	5	5	5	4	4
32.5°	7	7	6	6	6	6	5	5	5	5	4
31.25°	8	7	7	7	6	6	6	6	5	5	5
30°	9	8	7	7	7	6	6	6	6	5	5
28.75°	10	9	8	8	7	7	6	6	6	6	5
27.5°	13	11	9	8	8	7	7	6	6	6	5
26.25°	16	14	12	10	8	8	7	7	6	6	6
25°	20	17	14	12	10	8	8	7	7	6	6
23.75°	23	20	17	15	12	10	8	8	7	7	6
22.5°	27	23	20	17	14	12	9	8	7	7	6
21.25°	33	27	23	20	17	14	11	9	8	7	7
20°	46	33	27	23	20	16	13	10	9	8	7
18.75°	76	45	31	26	22	19	15	12	9	8	7
17.5°	118	72	42	29	25	21	17	14	11	9	8
16.25°	163	108	63	38	28	23	20	16	13	9	8
15°	209	148	91	51	32	26	22	18	14	11	9
13.75°	256	188	126	73	41	28	24	20	16	12	9
12.5°	301	229	161	100	54	32	25	21	17	14	10
11.25°	341	269	195	129	72	40	28	23	19	15	11
10°	375	305	229	157	92	47	30	24	20	16	12
8.75°	402	337	260	183	115	61	34	26	21	17	13
7.5°	422	363	287	207	135	74	39	27	22	18	14
6.25°	438	385	311	229	153	85	43	29	23	19	15
5°	447	400	330	247	168	99	49	30	24	20	15
3.75°	454	410	344	262	180	109	55	31	25	20	16
2.5°	460	418	354	272	189	117	60	33	25	21	16
1.25°	463	423	359	278	194	121	63	34	25	21	16
0°	464	424	361	281	196	123	64	34	25	21	16
-1.25°	463	423	359	278	194	121	63	34	25	21	16
-2.5°	460	418	354	272	189	117	60	33	25	21	16
-3.75°	454	410	344	262	180	109	55	31	25	20	16
-5°	447	400	330	247	168	99	49	30	24	20	15
-6.25°	438	385	311	229	153	85	43	29	23	19	15
-7.5°	422	363	287	207	135	74	39	27	22	18	14
-8.75°	402	337	260	183	115	61	34	26	21	17	13
-10°	375	305	229	157	92	47	30	24	20	16	12
-11.25°	341	269	195	129	72	40	28	23	19	15	11
-12.5°	301	229	161	100	54	32	25	21	17	14	10
-13.75°	256	188	126	73	41	28	24	20	16	12	9
-15°	209	148	91	51	32	26	22	18	14	11	9
-16.25°	163	108	63	38	28	23	20	16	13	9	8
-17.5°	118	72	42	29	25	21	17	14	11	9	8
-18.75°	76	45	31	26	22	19	15	12	9	8	7
-20°	46	33	27	23	20	16	13	10	9	8	7
-21.25°	33	27	23	20	17	14	11	9	8	7	7



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	27	23	20	17	14	12	9	8	7	7	6
-23.75°	23	20	17	15	12	10	8	8	7	7	6
-25°	20	17	14	12	10	8	8	7	7	6	6
-26.25°	16	14	12	10	8	8	7	7	6	6	6
-27.5°	13	11	9	8	8	7	7	6	6	6	5
-28.75°	10	9	8	8	7	7	6	6	6	6	5
-30°	9	8	7	7	7	6	6	6	6	5	5
-31.25°	8	7	7	7	6	6	6	6	5	5	5
-32.5°	7	7	6	6	6	6	5	5	5	5	4
-33.75°	6	6	6	6	6	5	5	5	5	4	4
-35°	6	6	6	6	5	5	5	5	4	4	4
-36.25°	6	6	5	5	5	5	5	4	4	4	4
-37.5°	5	5	5	5	5	4	4	4	4	4	4
-38.75°	5	5	5	4	4	4	4	4	4	4	4
-40°	5	5	4	4	4	4	4	4	4	4	3
-41.25°	4	4	4	4	4	4	4	4	4	3	3
-42.5°	4	4	4	4	4	4	4	3	3	3	3
-43.75°	4	4	4	4	4	3	3	3	3	3	3
-45°	4	4	4	3	3	3	3	3	3	3	3
-46.25°	4	3	3	3	3	3	3	3	3	3	3
-47.5°	3	3	3	3	3	3	3	3	3	3	3
-48.75°	3	3	3	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	2
-52.5°	3	3	3	3	3	3	3	3	2	2	2
-53.75°	3	3	3	3	3	3	2	2	2	2	2
-55°	3	3	2	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	1
-60°	2	2	2	2	2	2	2	1	1	1	1
-61.25°	2	2	2	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	0	0	0
-67.5°	1	1	1	1	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	1	0	0	0	0	0	0	0	0	0	0
63.75°	1	1	1	1	0	0	0	0	0	0	0
62.5°	1	1	1	1	1	1	0	0	0	0	0
61.25°	1	1	1	1	1	1	1	1	0	0	0
60°	1	1	1	1	1	1	1	1	1	1	0
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	2	1	1	1	1	1	1	1	1
55°	2	2	2	2	2	1	1	1	1	1	1
53.75°	2	2	2	2	2	2	2	1	1	1	1
52.5°	2	2	2	2	2	2	2	2	1	1	1
51.25°	2	2	2	2	2	2	2	2	2	2	1
50°	3	2	2	2	2	2	2	2	2	2	2
48.75°	3	3	3	2	2	2	2	2	2	2	2
47.5°	3	3	3	3	2	2	2	2	2	2	2
46.25°	3	3	3	3	3	2	2	2	2	2	2
45°	3	3	3	3	3	3	3	2	2	2	2
43.75°	3	3	3	3	3	3	3	3	2	2	2
42.5°	3	3	3	3	3	3	3	3	3	2	2
41.25°	3	3	3	3	3	3	3	3	3	3	2
40°	3	3	3	3	3	3	3	3	3	3	2
38.75°	3	3	3	3	3	3	3	3	3	3	3
37.5°	4	4	3	3	3	3	3	3	3	3	3
36.25°	4	4	4	3	3	3	3	3	3	3	3
35°	4	4	4	4	3	3	3	3	3	3	3



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	4	4	4	4	3	3	3	3	3	3	3
32.5°	4	4	4	4	4	3	3	3	3	3	3
31.25°	4	4	4	4	4	4	3	3	3	3	3
30°	5	4	4	4	4	4	4	3	3	3	3
28.75°	5	5	4	4	4	4	4	3	3	3	3
27.5°	5	5	5	4	4	4	4	4	3	3	3
26.25°	5	5	5	4	4	4	4	4	3	3	3
25°	6	5	5	5	4	4	4	4	4	3	3
23.75°	6	6	5	5	4	4	4	4	4	3	3
22.5°	6	6	5	5	5	4	4	4	4	4	3
21.25°	6	6	6	5	5	5	4	4	4	4	3
20°	6	6	6	5	5	5	4	4	4	4	4
18.75°	7	6	6	6	5	5	4	4	4	4	4
17.5°	7	6	6	6	5	5	5	4	4	4	4
16.25°	7	7	6	6	6	5	5	4	4	4	4
15°	8	7	6	6	6	5	5	4	4	4	4
13.75°	8	7	7	6	6	5	5	5	4	4	4
12.5°	8	7	7	6	6	5	5	5	4	4	4
11.25°	9	8	7	6	6	6	5	5	4	4	4
10°	9	8	7	6	6	6	5	5	4	4	4
8.75°	10	8	7	7	6	6	5	5	5	4	4
7.5°	11	8	7	7	6	6	5	5	5	4	4
6.25°	11	9	8	7	6	6	5	5	5	4	4
5°	12	9	8	7	6	6	6	5	5	4	4
3.75°	12	9	8	7	6	6	6	5	5	4	4
2.5°	12	9	8	7	6	6	6	5	5	4	4
1.25°	13	9	8	7	6	6	6	5	5	4	4
0°	13	9	8	7	6	6	6	5	5	4	4
-1.25°	13	9	8	7	6	6	6	5	5	4	4
-2.5°	12	9	8	7	6	6	6	5	5	4	4
-3.75°	12	9	8	7	6	6	6	5	5	4	4
-5°	12	9	8	7	6	6	6	5	5	4	4
-6.25°	11	9	8	7	6	6	5	5	5	4	4
-7.5°	11	8	7	7	6	6	5	5	5	4	4
-8.75°	10	8	7	7	6	6	5	5	5	4	4
-10°	9	8	7	6	6	6	5	5	4	4	4
-11.25°	9	8	7	6	6	6	5	5	4	4	4
-12.5°	8	7	7	6	6	5	5	5	4	4	4
-13.75°	8	7	7	6	6	5	5	5	4	4	4
-15°	8	7	6	6	6	5	5	4	4	4	4
-16.25°	7	7	6	6	6	5	5	4	4	4	4
-17.5°	7	6	6	6	5	5	5	4	4	4	4
-18.75°	7	6	6	6	5	5	4	4	4	4	4
-20°	6	6	6	5	5	5	4	4	4	4	4
-21.25°	6	6	6	5	5	5	4	4	4	4	3



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	6	6	5	5	5	4	4	4	4	4	3
-23.75°	6	6	5	5	4	4	4	4	4	3	3
-25°	6	5	5	5	4	4	4	4	4	3	3
-26.25°	5	5	5	4	4	4	4	4	3	3	3
-27.5°	5	5	5	4	4	4	4	4	3	3	3
-28.75°	5	5	4	4	4	4	4	3	3	3	3
-30°	5	4	4	4	4	4	4	3	3	3	3
-31.25°	4	4	4	4	4	4	3	3	3	3	3
-32.5°	4	4	4	4	4	3	3	3	3	3	3
-33.75°	4	4	4	4	3	3	3	3	3	3	3
-35°	4	4	4	4	3	3	3	3	3	3	3
-36.25°	4	4	4	3	3	3	3	3	3	3	3
-37.5°	4	4	3	3	3	3	3	3	3	3	3
-38.75°	3	3	3	3	3	3	3	3	3	3	3
-40°	3	3	3	3	3	3	3	3	3	3	2
-41.25°	3	3	3	3	3	3	3	3	3	3	2
-42.5°	3	3	3	3	3	3	3	3	3	2	2
-43.75°	3	3	3	3	3	3	3	3	2	2	2
-45°	3	3	3	3	3	3	3	2	2	2	2
-46.25°	3	3	3	3	3	2	2	2	2	2	2
-47.5°	3	3	3	3	2	2	2	2	2	2	2
-48.75°	3	3	3	2	2	2	2	2	2	2	2
-50°	3	2	2	2	2	2	2	2	2	2	2
-51.25°	2	2	2	2	2	2	2	2	2	2	1
-52.5°	2	2	2	2	2	2	2	2	1	1	1
-53.75°	2	2	2	2	2	2	2	1	1	1	1
-55°	2	2	2	2	2	1	1	1	1	1	1
-56.25°	2	2	2	1	1	1	1	1	1	1	1
-57.5°	2	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	0
-61.25°	1	1	1	1	1	1	1	1	0	0	0
-62.5°	1	1	1	1	1	1	0	0	0	0	0
-63.75°	1	1	1	1	0	0	0	0	0	0	0
-65°	1	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	1	0	0	0	0	0	0	0	0	0	0
57.5°	1	1	0	0	0	0	0	0	0	0	0
56.25°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	1	0	0	0	0	0	0	0
53.75°	1	1	1	1	1	0	0	0	0	0	0
52.5°	1	1	1	1	1	1	0	0	0	0	0
51.25°	1	1	1	1	1	1	1	0	0	0	0
50°	1	1	1	1	1	1	1	1	0	0	0
48.75°	2	1	1	1	1	1	1	1	1	0	0
47.5°	2	2	1	1	1	1	1	1	1	1	0
46.25°	2	2	2	1	1	1	1	1	1	1	0
45°	2	2	2	2	1	1	1	1	1	1	1
43.75°	2	2	2	2	1	1	1	1	1	1	1
42.5°	2	2	2	2	2	1	1	1	1	1	1
41.25°	2	2	2	2	2	2	1	1	1	1	1
40°	2	2	2	2	2	2	1	1	1	1	1
38.75°	2	2	2	2	2	2	2	1	1	1	1
37.5°	3	2	2	2	2	2	2	1	1	1	1
36.25°	3	3	2	2	2	2	2	2	1	1	1
35°	3	3	2	2	2	2	2	2	1	1	1



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	3	3	3	2	2	2	2	2	2	1	1
32.5°	3	3	3	2	2	2	2	2	2	1	1
31.25°	3	3	3	3	2	2	2	2	2	2	1
30°	3	3	3	3	2	2	2	2	2	2	1
28.75°	3	3	3	3	3	2	2	2	2	2	1
27.5°	3	3	3	3	3	2	2	2	2	2	2
26.25°	3	3	3	3	3	3	2	2	2	2	2
25°	3	3	3	3	3	3	2	2	2	2	2
23.75°	3	3	3	3	3	3	2	2	2	2	2
22.5°	3	3	3	3	3	3	2	2	2	2	2
21.25°	3	3	3	3	3	3	3	2	2	2	2
20°	3	3	3	3	3	3	3	2	2	2	2
18.75°	3	3	3	3	3	3	3	2	2	2	2
17.5°	3	3	3	3	3	3	3	2	2	2	2
16.25°	3	3	3	3	3	3	3	3	2	2	2
15°	4	3	3	3	3	3	3	3	2	2	2
13.75°	4	3	3	3	3	3	3	3	2	2	2
12.5°	4	3	3	3	3	3	3	3	2	2	2
11.25°	4	3	3	3	3	3	3	3	2	2	2
10°	4	3	3	3	3	3	3	3	2	2	2
8.75°	4	4	3	3	3	3	3	3	3	2	2
7.5°	4	4	3	3	3	3	3	3	3	2	2
6.25°	4	4	3	3	3	3	3	3	3	2	2
5°	4	4	3	3	3	3	3	3	3	2	2
3.75°	4	4	3	3	3	3	3	3	3	2	2
2.5°	4	4	3	3	3	3	3	3	3	2	2
1.25°	4	4	3	3	3	3	3	3	3	2	2
0°	4	4	3	3	3	3	3	3	3	2	2
-1.25°	4	4	3	3	3	3	3	3	3	2	2
-2.5°	4	4	3	3	3	3	3	3	3	2	2
-3.75°	4	4	3	3	3	3	3	3	3	2	2
-5°	4	4	3	3	3	3	3	3	3	2	2
-6.25°	4	4	3	3	3	3	3	3	3	2	2
-7.5°	4	4	3	3	3	3	3	3	3	2	2
-8.75°	4	4	3	3	3	3	3	3	3	2	2
-10°	4	3	3	3	3	3	3	3	2	2	2
-11.25°	4	3	3	3	3	3	3	3	2	2	2
-12.5°	4	3	3	3	3	3	3	3	2	2	2
-13.75°	4	3	3	3	3	3	3	3	2	2	2
-15°	4	3	3	3	3	3	3	3	2	2	2
-16.25°	3	3	3	3	3	3	3	3	2	2	2
-17.5°	3	3	3	3	3	3	3	2	2	2	2
-18.75°	3	3	3	3	3	3	3	2	2	2	2
-20°	3	3	3	3	3	3	3	2	2	2	2
-21.25°	3	3	3	3	3	3	3	2	2	2	2



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	3	3	3	3	3	3	2	2	2	2	2
-23.75°	3	3	3	3	3	3	2	2	2	2	2
-25°	3	3	3	3	3	3	2	2	2	2	2
-26.25°	3	3	3	3	3	3	2	2	2	2	2
-27.5°	3	3	3	3	3	2	2	2	2	2	2
-28.75°	3	3	3	3	3	2	2	2	2	2	1
-30°	3	3	3	3	2	2	2	2	2	2	1
-31.25°	3	3	3	3	2	2	2	2	2	2	1
-32.5°	3	3	3	2	2	2	2	2	2	1	1
-33.75°	3	3	3	2	2	2	2	2	2	1	1
-35°	3	3	2	2	2	2	2	2	1	1	1
-36.25°	3	3	2	2	2	2	2	2	1	1	1
-37.5°	3	2	2	2	2	2	2	1	1	1	1
-38.75°	2	2	2	2	2	2	2	1	1	1	1
-40°	2	2	2	2	2	2	1	1	1	1	1
-41.25°	2	2	2	2	2	2	1	1	1	1	1
-42.5°	2	2	2	2	2	1	1	1	1	1	1
-43.75°	2	2	2	2	1	1	1	1	1	1	1
-45°	2	2	2	2	1	1	1	1	1	1	1
-46.25°	2	2	2	1	1	1	1	1	1	1	0
-47.5°	2	2	1	1	1	1	1	1	1	1	0
-48.75°	2	1	1	1	1	1	1	1	1	0	0
-50°	1	1	1	1	1	1	1	1	0	0	0
-51.25°	1	1	1	1	1	1	1	0	0	0	0
-52.5°	1	1	1	1	1	1	0	0	0	0	0
-53.75°	1	1	1	1	1	0	0	0	0	0	0
-55°	1	1	1	1	0	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	1	0	0	0	0	0	0	0	0	0
-58.75°	1	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	1	0	0	0	0	0	0	0	0	0	0
41.25°	1	0	0	0	0	0	0	0	0	0	0
40°	1	1	0	0	0	0	0	0	0	0	0
38.75°	1	1	0	0	0	0	0	0	0	0	0
37.5°	1	1	1	0	0	0	0	0	0	0	0
36.25°	1	1	1	0	0	0	0	0	0	0	0
35°	1	1	1	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	1	0	0	0	0	0	0	0
32.5°	1	1	1	1	0	0	0	0	0	0	0
31.25°	1	1	1	1	0	0	0	0	0	0	0
30°	1	1	1	1	0	0	0	0	0	0	0
28.75°	1	1	1	1	1	0	0	0	0	0	0
27.5°	1	1	1	1	1	0	0	0	0	0	0
26.25°	1	1	1	1	1	0	0	0	0	0	0
25°	1	1	1	1	1	0	0	0	0	0	0
23.75°	1	1	1	1	1	1	0	0	0	0	0
22.5°	2	1	1	1	1	1	0	0	0	0	0
21.25°	2	1	1	1	1	1	0	0	0	0	0
20°	2	1	1	1	1	1	0	0	0	0	0
18.75°	2	1	1	1	1	1	0	0	0	0	0
17.5°	2	1	1	1	1	1	0	0	0	0	0
16.25°	2	2	1	1	1	1	0	0	0	0	0
15°	2	2	1	1	1	1	0	0	0	0	0
13.75°	2	2	1	1	1	1	1	0	0	0	0
12.5°	2	2	1	1	1	1	1	0	0	0	0
11.25°	2	2	1	1	1	1	1	0	0	0	0
10°	2	2	1	1	1	1	1	0	0	0	0
8.75°	2	2	1	1	1	1	1	0	0	0	0
7.5°	2	2	1	1	1	1	1	0	0	0	0
6.25°	2	2	1	1	1	1	1	0	0	0	0
5°	2	2	1	1	1	1	1	0	0	0	0
3.75°	2	2	1	1	1	1	1	0	0	0	0
2.5°	2	2	1	1	1	1	1	0	0	0	0
1.25°	2	2	1	1	1	1	1	0	0	0	0
0°	2	2	2	1	1	1	1	0	0	0	0
-1.25°	2	2	1	1	1	1	1	0	0	0	0
-2.5°	2	2	1	1	1	1	1	0	0	0	0
-3.75°	2	2	1	1	1	1	1	0	0	0	0
-5°	2	2	1	1	1	1	1	0	0	0	0
-6.25°	2	2	1	1	1	1	1	0	0	0	0
-7.5°	2	2	1	1	1	1	1	0	0	0	0
-8.75°	2	2	1	1	1	1	1	0	0	0	0
-10°	2	2	1	1	1	1	1	0	0	0	0
-11.25°	2	2	1	1	1	1	1	0	0	0	0
-12.5°	2	2	1	1	1	1	1	0	0	0	0
-13.75°	2	2	1	1	1	1	1	0	0	0	0
-15°	2	2	1	1	1	1	0	0	0	0	0
-16.25°	2	2	1	1	1	1	0	0	0	0	0
-17.5°	2	1	1	1	1	1	0	0	0	0	0
-18.75°	2	1	1	1	1	1	0	0	0	0	0
-20°	2	1	1	1	1	1	0	0	0	0	0
-21.25°	2	1	1	1	1	1	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	1	1	1	1	1	0	0	0	0	0
-23.75°	1	1	1	1	1	1	0	0	0	0	0
-25°	1	1	1	1	1	0	0	0	0	0	0
-26.25°	1	1	1	1	1	0	0	0	0	0	0
-27.5°	1	1	1	1	1	0	0	0	0	0	0
-28.75°	1	1	1	1	1	0	0	0	0	0	0
-30°	1	1	1	1	0	0	0	0	0	0	0
-31.25°	1	1	1	1	0	0	0	0	0	0	0
-32.5°	1	1	1	1	0	0	0	0	0	0	0
-33.75°	1	1	1	1	0	0	0	0	0	0	0
-35°	1	1	1	0	0	0	0	0	0	0	0
-36.25°	1	1	1	0	0	0	0	0	0	0	0
-37.5°	1	1	1	0	0	0	0	0	0	0	0
-38.75°	1	1	0	0	0	0	0	0	0	0	0
-40°	1	1	0	0	0	0	0	0	0	0	0
-41.25°	1	0	0	0	0	0	0	0	0	0	0
-42.5°	1	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: P220509 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED4097-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)