

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29477)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV  
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, FLUSH LENS, MEDIUM  
FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 3000K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	701.9 lumens	Max Intensity:	2971.8 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	71.6 lumens/watt		
Luminous Opening:	Circular (Dia: 0.25' x H: 0')		
Beam Angle (50%):	24.2°H x 24.2°V	Field Angle (10%):	53.3°H x 53.3°V
Beam Lumens:	306.8 lumens	Field Lumens:	626.9 lumens
Beam Efficiency:	43.7%	Field Efficiency:	89.3%
Input Watts (W):	9.8		
Input Voltage (V):	120		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

### Iso-Candela Plot






REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

### Lumen Table

90	0.0	0.0	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2	0.1	0.1	0.1	0.1	0.0	0.0	0.0
40		0.0	0.0	0.1	0.1	0.3	0.6	1.2	1.2	0.6	0.3	0.1	0.1	0.0		
30	0.0	0.0	0.0	0.1	0.2	1.2	5.7	9.8	9.8	5.7	1.2	0.2	0.1	0.0	0.0	0.0
20		0.0	0.0	0.1	0.5	5.4	14.8	28.2	28.2	14.8	5.4	0.5	0.1	0.0		
10	0.0	0.0	0.1	0.1	1.0	9.0	27.5	68.0	68.0	27.5	9.0	1.0	0.1	0.1	0.0	0.0
0		0.0	0.1	0.1	1.0	9.0	27.5	68.0	68.0	27.5	9.0	1.0	0.1	0.1		
-10	0.0	0.0	0.1	0.1	1.0	9.0	27.5	68.0	68.0	27.5	9.0	1.0	0.1	0.1	0.0	0.0
-20		0.0	0.0	0.1	0.5	5.4	14.8	28.2	28.2	14.8	5.4	0.5	0.1	0.0		
-30	0.0	0.0	0.0	0.1	0.2	1.2	5.7	9.8	9.8	5.7	1.2	0.2	0.1	0.0	0.0	0.0
-40		0.0	0.0	0.1	0.1	0.3	0.6	1.2	1.2	0.6	0.3	0.1	0.1	0.0		
-50	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2	0.1	0.1	0.1	0.1	0.0	0.0	0.0
-60		0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0		
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0		
-90	0.0	0.0	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0


REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

### Luminous Intensity Polar Plot



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

### Luminous Intensity Plot



**Beam:**  
 H Angle: 24.2°  
 V Angle: 24.2°  
 Lumens: 306.8  
 Efficiency: 43.7%

**Field:**  
 H Angle: 53.3°  
 V Angle: 53.3°  
 Lumens: 626.9  
 Efficiency: 89.3%

**Spill:**  
 Lumens: 74.9  
 Efficiency: 10.7%

— Vertical Distribution through 0-Deg  
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	1
31.25°	0	0	0	0	0	0	0	0	0	0	1
30°	0	0	0	0	0	0	0	0	0	0	1
28.75°	0	0	0	0	0	0	0	0	0	0	1
27.5°	0	0	0	0	0	0	0	0	0	0	1
26.25°	0	0	0	0	0	0	0	0	0	0	1
25°	0	0	0	0	0	0	0	0	0	0	1
23.75°	0	0	0	0	0	0	0	0	0	0	1
22.5°	0	0	0	0	0	0	0	0	0	0	1
21.25°	0	0	0	0	0	0	0	0	0	0	1
20°	0	0	0	0	0	0	0	0	0	1	1
18.75°	0	0	0	0	0	0	0	0	0	1	1
17.5°	0	0	0	0	0	0	0	0	0	1	1
16.25°	0	0	0	0	0	0	0	0	0	1	1
15°	0	0	0	0	0	0	0	0	0	1	1
13.75°	0	0	0	0	0	0	0	0	0	1	1
12.5°	0	0	0	0	0	0	0	0	0	1	1
11.25°	0	0	0	0	0	0	0	0	0	1	1
10°	0	0	0	0	0	0	0	0	0	1	1
8.75°	0	0	0	0	0	0	0	0	0	1	1
7.5°	0	0	0	0	0	0	0	0	0	1	1
6.25°	0	0	0	0	0	0	0	0	0	1	1
5°	0	0	0	0	0	0	0	0	0	1	1
3.75°	0	0	0	0	0	0	0	0	0	1	1
2.5°	0	0	0	0	0	0	0	0	0	1	1
1.25°	0	0	0	0	0	0	0	0	0	1	1
0°	0	0	0	0	0	0	0	0	0	1	1
-1.25°	0	0	0	0	0	0	0	0	0	1	1
-2.5°	0	0	0	0	0	0	0	0	0	1	1
-3.75°	0	0	0	0	0	0	0	0	0	1	1
-5°	0	0	0	0	0	0	0	0	0	1	1
-6.25°	0	0	0	0	0	0	0	0	0	1	1
-7.5°	0	0	0	0	0	0	0	0	0	1	1
-8.75°	0	0	0	0	0	0	0	0	0	1	1
-10°	0	0	0	0	0	0	0	0	0	1	1
-11.25°	0	0	0	0	0	0	0	0	0	1	1
-12.5°	0	0	0	0	0	0	0	0	0	1	1
-13.75°	0	0	0	0	0	0	0	0	0	1	1
-15°	0	0	0	0	0	0	0	0	0	1	1
-16.25°	0	0	0	0	0	0	0	0	0	1	1
-17.5°	0	0	0	0	0	0	0	0	0	1	1
-18.75°	0	0	0	0	0	0	0	0	0	1	1
-20°	0	0	0	0	0	0	0	0	0	1	1
-21.25°	0	0	0	0	0	0	0	0	0	0	1





REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	1
-23.75°	0	0	0	0	0	0	0	0	0	0	1
-25°	0	0	0	0	0	0	0	0	0	0	1
-26.25°	0	0	0	0	0	0	0	0	0	0	1
-27.5°	0	0	0	0	0	0	0	0	0	0	1
-28.75°	0	0	0	0	0	0	0	0	0	0	1
-30°	0	0	0	0	0	0	0	0	0	0	1
-31.25°	0	0	0	0	0	0	0	0	0	0	1
-32.5°	0	0	0	0	0	0	0	0	0	0	1
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	1
63.75°	0	0	0	0	0	0	0	0	0	1	1
62.5°	0	0	0	0	0	0	0	0	1	1	1
61.25°	0	0	0	0	0	0	0	1	1	1	1
60°	0	0	0	0	0	0	0	1	1	1	1
58.75°	0	0	0	0	0	0	1	1	1	1	1
57.5°	0	0	0	0	0	1	1	1	1	1	1
56.25°	0	0	0	0	0	1	1	1	1	1	1
55°	0	0	0	0	1	1	1	1	1	1	1
53.75°	0	0	0	0	1	1	1	1	1	1	1
52.5°	0	0	0	1	1	1	1	1	1	1	1
51.25°	0	0	0	1	1	1	1	1	1	1	1
50°	0	0	0	1	1	1	1	1	1	1	1
48.75°	0	0	1	1	1	1	1	1	1	1	1
47.5°	0	0	1	1	1	1	1	1	1	1	1
46.25°	0	0	1	1	1	1	1	1	1	1	1
45°	0	1	1	1	1	1	1	1	1	1	1
43.75°	0	1	1	1	1	1	1	1	1	1	1
42.5°	0	1	1	1	1	1	1	1	1	1	1
41.25°	0	1	1	1	1	1	1	1	1	1	1
40°	0	1	1	1	1	1	1	1	1	1	1
38.75°	1	1	1	1	1	1	1	1	1	1	1
37.5°	1	1	1	1	1	1	1	1	1	1	1
36.25°	1	1	1	1	1	1	1	1	1	1	1
35°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	1	1	1	1	1	1	1
32.5°	1	1	1	1	1	1	1	1	1	1	1
31.25°	1	1	1	1	1	1	1	1	1	1	1
30°	1	1	1	1	1	1	1	1	1	1	1
28.75°	1	1	1	1	1	1	1	1	1	1	1
27.5°	1	1	1	1	1	1	1	1	1	1	1
26.25°	1	1	1	1	1	1	1	1	1	1	1
25°	1	1	1	1	1	1	1	1	1	1	1
23.75°	1	1	1	1	1	1	1	1	1	1	2
22.5°	1	1	1	1	1	1	1	1	1	1	2
21.25°	1	1	1	1	1	1	1	1	1	1	2
20°	1	1	1	1	1	1	1	1	1	1	2
18.75°	1	1	1	1	1	1	1	1	1	1	2
17.5°	1	1	1	1	1	1	1	1	1	2	2
16.25°	1	1	1	1	1	1	1	1	1	2	2
15°	1	1	1	1	1	1	1	1	1	2	2
13.75°	1	1	1	1	1	1	1	1	1	2	2
12.5°	1	1	1	1	1	1	1	1	1	2	2
11.25°	1	1	1	1	1	1	1	1	1	2	2
10°	1	1	1	1	1	1	1	1	1	2	2
8.75°	1	1	1	1	1	1	1	1	1	2	2
7.5°	1	1	1	1	1	1	1	1	1	2	2
6.25°	1	1	1	1	1	1	1	1	1	2	2
5°	1	1	1	1	1	1	1	1	1	2	2
3.75°	1	1	1	1	1	1	1	1	1	2	2
2.5°	1	1	1	1	1	1	1	1	1	2	2
1.25°	1	1	1	1	1	1	1	1	1	2	2
0°	1	1	1	1	1	1	1	1	2	2	2
-1.25°	1	1	1	1	1	1	1	1	1	2	2
-2.5°	1	1	1	1	1	1	1	1	1	2	2
-3.75°	1	1	1	1	1	1	1	1	1	2	2
-5°	1	1	1	1	1	1	1	1	1	2	2
-6.25°	1	1	1	1	1	1	1	1	1	2	2
-7.5°	1	1	1	1	1	1	1	1	1	2	2
-8.75°	1	1	1	1	1	1	1	1	1	2	2
-10°	1	1	1	1	1	1	1	1	1	2	2
-11.25°	1	1	1	1	1	1	1	1	1	2	2
-12.5°	1	1	1	1	1	1	1	1	1	2	2
-13.75°	1	1	1	1	1	1	1	1	1	2	2
-15°	1	1	1	1	1	1	1	1	1	2	2
-16.25°	1	1	1	1	1	1	1	1	1	2	2
-17.5°	1	1	1	1	1	1	1	1	1	2	2
-18.75°	1	1	1	1	1	1	1	1	1	1	2
-20°	1	1	1	1	1	1	1	1	1	1	2
-21.25°	1	1	1	1	1	1	1	1	1	1	2



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	1	1	1	1	1	1	1	1	2
-23.75°	1	1	1	1	1	1	1	1	1	1	2
-25°	1	1	1	1	1	1	1	1	1	1	1
-26.25°	1	1	1	1	1	1	1	1	1	1	1
-27.5°	1	1	1	1	1	1	1	1	1	1	1
-28.75°	1	1	1	1	1	1	1	1	1	1	1
-30°	1	1	1	1	1	1	1	1	1	1	1
-31.25°	1	1	1	1	1	1	1	1	1	1	1
-32.5°	1	1	1	1	1	1	1	1	1	1	1
-33.75°	1	1	1	1	1	1	1	1	1	1	1
-35°	1	1	1	1	1	1	1	1	1	1	1
-36.25°	1	1	1	1	1	1	1	1	1	1	1
-37.5°	1	1	1	1	1	1	1	1	1	1	1
-38.75°	1	1	1	1	1	1	1	1	1	1	1
-40°	0	1	1	1	1	1	1	1	1	1	1
-41.25°	0	1	1	1	1	1	1	1	1	1	1
-42.5°	0	1	1	1	1	1	1	1	1	1	1
-43.75°	0	1	1	1	1	1	1	1	1	1	1
-45°	0	1	1	1	1	1	1	1	1	1	1
-46.25°	0	0	1	1	1	1	1	1	1	1	1
-47.5°	0	0	1	1	1	1	1	1	1	1	1
-48.75°	0	0	1	1	1	1	1	1	1	1	1
-50°	0	0	0	1	1	1	1	1	1	1	1
-51.25°	0	0	0	1	1	1	1	1	1	1	1
-52.5°	0	0	0	1	1	1	1	1	1	1	1
-53.75°	0	0	0	0	1	1	1	1	1	1	1
-55°	0	0	0	0	1	1	1	1	1	1	1
-56.25°	0	0	0	0	0	1	1	1	1	1	1
-57.5°	0	0	0	0	0	1	1	1	1	1	1
-58.75°	0	0	0	0	0	0	1	1	1	1	1
-60°	0	0	0	0	0	0	0	1	1	1	1
-61.25°	0	0	0	0	0	0	0	1	1	1	1
-62.5°	0	0	0	0	0	0	0	0	1	1	1
-63.75°	0	0	0	0	0	0	0	0	0	1	1
-65°	0	0	0	0	0	0	0	0	0	0	1
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	1	1	1
71.25°	0	0	0	0	0	0	1	1	1	1	1
70°	0	0	0	0	1	1	1	1	1	1	1
68.75°	0	0	0	1	1	1	1	1	1	1	1
67.5°	0	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	2
48.75°	1	1	1	1	1	1	1	1	1	2	2
47.5°	1	1	1	1	1	1	1	1	2	2	2
46.25°	1	1	1	1	1	1	1	2	2	2	2
45°	1	1	1	1	1	1	2	2	2	2	2
43.75°	1	1	1	1	1	1	2	2	2	2	2
42.5°	1	1	1	1	1	2	2	2	2	2	2
41.25°	1	1	1	1	2	2	2	2	2	2	2
40°	1	1	1	1	2	2	2	2	2	2	2
38.75°	1	1	1	2	2	2	2	2	2	2	2
37.5°	1	1	1	2	2	2	2	2	2	2	2
36.25°	1	1	2	2	2	2	2	2	2	2	2
35°	1	1	2	2	2	2	2	2	2	2	2



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	2	2	2	2	2	2	2	2	3
32.5°	1	2	2	2	2	2	2	2	2	2	3
31.25°	1	2	2	2	2	2	2	2	2	3	3
30°	1	2	2	2	2	2	2	2	2	3	3
28.75°	2	2	2	2	2	2	2	2	3	3	3
27.5°	2	2	2	2	2	2	2	2	3	3	3
26.25°	2	2	2	2	2	2	2	3	3	3	3
25°	2	2	2	2	2	2	2	3	3	3	3
23.75°	2	2	2	2	2	2	2	3	3	3	3
22.5°	2	2	2	2	2	2	3	3	3	3	3
21.25°	2	2	2	2	2	2	3	3	3	3	3
20°	2	2	2	2	2	2	3	3	3	3	3
18.75°	2	2	2	2	2	2	3	3	3	3	3
17.5°	2	2	2	2	2	3	3	3	3	3	4
16.25°	2	2	2	2	2	3	3	3	3	3	4
15°	2	2	2	2	2	3	3	3	3	3	4
13.75°	2	2	2	2	2	3	3	3	3	3	4
12.5°	2	2	2	2	2	3	3	3	3	4	4
11.25°	2	2	2	2	2	3	3	3	3	4	4
10°	2	2	2	2	3	3	3	3	3	4	4
8.75°	2	2	2	2	3	3	3	3	3	4	4
7.5°	2	2	2	2	3	3	3	3	3	4	4
6.25°	2	2	2	2	3	3	3	3	3	4	4
5°	2	2	2	2	3	3	3	3	3	4	4
3.75°	2	2	2	2	3	3	3	3	3	4	4
2.5°	2	2	2	2	3	3	3	3	3	4	4
1.25°	2	2	2	2	3	3	3	3	3	4	4
0°	2	2	2	2	3	3	3	3	4	4	4
-1.25°	2	2	2	2	3	3	3	3	3	4	4
-2.5°	2	2	2	2	3	3	3	3	3	4	4
-3.75°	2	2	2	2	3	3	3	3	3	4	4
-5°	2	2	2	2	3	3	3	3	3	4	4
-6.25°	2	2	2	2	3	3	3	3	3	4	4
-7.5°	2	2	2	2	3	3	3	3	3	4	4
-8.75°	2	2	2	2	3	3	3	3	3	4	4
-10°	2	2	2	2	3	3	3	3	3	4	4
-11.25°	2	2	2	2	2	3	3	3	3	4	4
-12.5°	2	2	2	2	2	3	3	3	3	4	4
-13.75°	2	2	2	2	2	3	3	3	3	3	4
-15°	2	2	2	2	2	3	3	3	3	3	4
-16.25°	2	2	2	2	2	3	3	3	3	3	4
-17.5°	2	2	2	2	2	3	3	3	3	3	4
-18.75°	2	2	2	2	2	2	3	3	3	3	3
-20°	2	2	2	2	2	2	3	3	3	3	3
-21.25°	2	2	2	2	2	2	3	3	3	3	3





REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	2	2	2	2	2	3	3	3	3	3
-23.75°	2	2	2	2	2	2	2	3	3	3	3
-25°	2	2	2	2	2	2	2	3	3	3	3
-26.25°	2	2	2	2	2	2	2	3	3	3	3
-27.5°	2	2	2	2	2	2	2	2	3	3	3
-28.75°	2	2	2	2	2	2	2	2	3	3	3
-30°	1	2	2	2	2	2	2	2	2	3	3
-31.25°	1	2	2	2	2	2	2	2	2	3	3
-32.5°	1	2	2	2	2	2	2	2	2	2	3
-33.75°	1	1	2	2	2	2	2	2	2	2	3
-35°	1	1	2	2	2	2	2	2	2	2	2
-36.25°	1	1	2	2	2	2	2	2	2	2	2
-37.5°	1	1	1	2	2	2	2	2	2	2	2
-38.75°	1	1	1	2	2	2	2	2	2	2	2
-40°	1	1	1	1	2	2	2	2	2	2	2
-41.25°	1	1	1	1	2	2	2	2	2	2	2
-42.5°	1	1	1	1	1	2	2	2	2	2	2
-43.75°	1	1	1	1	1	1	2	2	2	2	2
-45°	1	1	1	1	1	1	2	2	2	2	2
-46.25°	1	1	1	1	1	1	1	2	2	2	2
-47.5°	1	1	1	1	1	1	1	1	2	2	2
-48.75°	1	1	1	1	1	1	1	1	1	2	2
-50°	1	1	1	1	1	1	1	1	1	1	2
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	0	1	1	1	1	1	1	1	1	1	1
-68.75°	0	0	0	1	1	1	1	1	1	1	1
-70°	0	0	0	0	1	1	1	1	1	1	1
-71.25°	0	0	0	0	0	0	1	1	1	1	1
-72.5°	0	0	0	0	0	0	0	0	1	1	1
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	1	1	1
75°	0	0	0	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	2
58.75°	1	1	1	1	1	1	1	1	2	2	2
57.5°	1	1	1	1	1	1	2	2	2	2	2
56.25°	1	1	1	1	1	2	2	2	2	2	2
55°	1	1	1	2	2	2	2	2	2	2	2
53.75°	1	1	2	2	2	2	2	2	2	2	2
52.5°	1	2	2	2	2	2	2	2	2	2	2
51.25°	2	2	2	2	2	2	2	2	2	2	2
50°	2	2	2	2	2	2	2	2	2	2	2
48.75°	2	2	2	2	2	2	2	2	2	2	3
47.5°	2	2	2	2	2	2	2	2	2	3	3
46.25°	2	2	2	2	2	2	2	3	3	3	3
45°	2	2	2	2	2	2	3	3	3	3	3
43.75°	2	2	2	2	2	3	3	3	3	3	3
42.5°	2	2	2	2	3	3	3	3	3	3	3
41.25°	2	2	2	3	3	3	3	3	3	3	3
40°	2	2	3	3	3	3	3	3	3	3	4
38.75°	2	2	3	3	3	3	3	3	3	4	4
37.5°	2	3	3	3	3	3	3	3	4	4	4
36.25°	3	3	3	3	3	3	3	4	4	4	4
35°	3	3	3	3	3	3	4	4	4	4	4



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	3	3	3	3	3	4	4	4	4	4	5
32.5°	3	3	3	3	4	4	4	4	4	5	5
31.25°	3	3	3	3	4	4	4	4	5	5	5
30°	3	3	3	4	4	4	4	4	5	5	5
28.75°	3	3	3	4	4	4	4	5	5	5	5
27.5°	3	3	4	4	4	4	5	5	5	5	6
26.25°	3	3	4	4	4	4	5	5	5	5	6
25°	3	4	4	4	4	5	5	5	5	6	6
23.75°	3	4	4	4	4	5	5	5	5	6	7
22.5°	4	4	4	4	5	5	5	5	6	6	8
21.25°	4	4	4	4	5	5	5	5	6	7	10
20°	4	4	4	4	5	5	5	6	6	8	11
18.75°	4	4	4	5	5	5	5	6	7	9	12
17.5°	4	4	4	5	5	5	6	6	8	11	13
16.25°	4	4	4	5	5	5	6	6	9	12	14
15°	4	4	5	5	5	5	6	7	10	13	15
13.75°	4	4	5	5	5	6	6	8	11	14	16
12.5°	4	4	5	5	5	6	6	9	12	14	17
11.25°	4	4	5	5	5	6	7	9	12	15	18
10°	4	5	5	5	5	6	7	10	13	16	18
8.75°	4	5	5	5	5	6	8	11	14	16	19
7.5°	4	5	5	5	6	6	8	11	14	17	20
6.25°	4	5	5	5	6	6	9	12	14	17	21
5°	4	5	5	5	6	6	9	12	15	18	21
3.75°	4	5	5	5	6	6	9	12	15	18	21
2.5°	4	5	5	5	6	6	9	12	15	18	22
1.25°	4	5	5	5	6	6	10	13	15	18	22
0°	4	5	5	5	6	7	10	13	15	18	22
-1.25°	4	5	5	5	6	6	10	13	15	18	22
-2.5°	4	5	5	5	6	6	9	12	15	18	22
-3.75°	4	5	5	5	6	6	9	12	15	18	21
-5°	4	5	5	5	6	6	9	12	15	18	21
-6.25°	4	5	5	5	6	6	9	12	14	17	21
-7.5°	4	5	5	5	6	6	8	11	14	17	20
-8.75°	4	5	5	5	5	6	8	11	14	16	19
-10°	4	5	5	5	5	6	7	10	13	16	18
-11.25°	4	4	5	5	5	6	7	9	12	15	18
-12.5°	4	4	5	5	5	6	6	9	12	14	17
-13.75°	4	4	5	5	5	6	6	8	11	14	16
-15°	4	4	5	5	5	5	6	7	10	13	15
-16.25°	4	4	4	5	5	5	6	6	9	12	14
-17.5°	4	4	4	5	5	5	6	6	8	11	13
-18.75°	4	4	4	5	5	5	5	6	7	9	12
-20°	4	4	4	4	5	5	5	6	6	8	11
-21.25°	4	4	4	4	5	5	5	5	6	7	10



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	4	4	4	4	5	5	5	5	6	6	8
-23.75°	3	4	4	4	4	5	5	5	5	6	7
-25°	3	4	4	4	4	5	5	5	5	6	6
-26.25°	3	3	4	4	4	4	5	5	5	5	6
-27.5°	3	3	4	4	4	4	5	5	5	5	6
-28.75°	3	3	3	4	4	4	4	5	5	5	5
-30°	3	3	3	4	4	4	4	4	5	5	5
-31.25°	3	3	3	3	4	4	4	4	5	5	5
-32.5°	3	3	3	3	4	4	4	4	4	5	5
-33.75°	3	3	3	3	3	4	4	4	4	4	5
-35°	3	3	3	3	3	3	4	4	4	4	4
-36.25°	3	3	3	3	3	3	3	4	4	4	4
-37.5°	2	3	3	3	3	3	3	3	4	4	4
-38.75°	2	2	3	3	3	3	3	3	3	4	4
-40°	2	2	3	3	3	3	3	3	3	3	4
-41.25°	2	2	2	3	3	3	3	3	3	3	3
-42.5°	2	2	2	2	3	3	3	3	3	3	3
-43.75°	2	2	2	2	2	3	3	3	3	3	3
-45°	2	2	2	2	2	2	3	3	3	3	3
-46.25°	2	2	2	2	2	2	2	3	3	3	3
-47.5°	2	2	2	2	2	2	2	2	2	3	3
-48.75°	2	2	2	2	2	2	2	2	2	2	3
-50°	2	2	2	2	2	2	2	2	2	2	2
-51.25°	2	2	2	2	2	2	2	2	2	2	2
-52.5°	1	2	2	2	2	2	2	2	2	2	2
-53.75°	1	1	2	2	2	2	2	2	2	2	2
-55°	1	1	1	2	2	2	2	2	2	2	2
-56.25°	1	1	1	1	1	2	2	2	2	2	2
-57.5°	1	1	1	1	1	1	2	2	2	2	2
-58.75°	1	1	1	1	1	1	1	1	2	2	2
-60°	1	1	1	1	1	1	1	1	1	1	2
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	0	0	0	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	1	1	1
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	2	2
62.5°	1	1	1	1	1	2	2	2	2	2	2
61.25°	1	1	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	3
53.75°	2	2	2	2	2	2	2	3	3	3	3
52.5°	2	2	2	2	2	3	3	3	3	3	3
51.25°	2	2	2	3	3	3	3	3	3	3	3
50°	2	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	4
47.5°	3	3	3	3	3	3	3	3	4	4	4
46.25°	3	3	3	3	3	3	4	4	4	4	4
45°	3	3	3	3	4	4	4	4	4	4	4
43.75°	3	3	4	4	4	4	4	4	4	4	5
42.5°	3	4	4	4	4	4	4	4	5	5	5
41.25°	4	4	4	4	4	4	5	5	5	5	5
40°	4	4	4	4	4	5	5	5	5	5	5
38.75°	4	4	4	5	5	5	5	5	5	5	6
37.5°	4	4	5	5	5	5	5	5	6	6	6
36.25°	4	5	5	5	5	5	6	6	6	7	8
35°	5	5	5	5	5	6	6	6	8	9	11



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	5	5	5	5	6	6	7	8	10	12	13
32.5°	5	5	5	6	6	7	9	11	12	14	15
31.25°	5	5	6	6	7	9	11	13	14	16	17
30°	5	6	6	7	9	11	13	15	16	18	20
28.75°	6	6	7	9	11	13	15	17	19	21	23
27.5°	6	7	9	11	13	15	17	19	21	23	26
26.25°	6	8	11	13	15	17	19	21	24	27	35
25°	8	10	12	14	16	19	21	24	28	36	45
23.75°	9	12	14	16	18	21	23	27	36	45	60
22.5°	11	13	15	17	20	23	26	35	45	60	91
21.25°	12	14	17	19	22	25	33	43	56	89	121
20°	13	16	18	21	24	30	40	50	83	117	152
18.75°	15	17	20	23	26	37	47	74	109	145	188
17.5°	16	18	21	24	33	43	61	98	134	178	224
16.25°	17	20	23	27	38	49	83	121	163	210	258
15°	18	21	24	32	44	64	104	143	191	241	290
13.75°	19	22	26	37	49	83	123	168	219	271	318
12.5°	20	23	30	42	59	100	141	193	245	297	343
11.25°	21	24	34	46	74	116	162	215	269	320	365
10°	22	25	37	50	88	130	181	236	291	340	381
8.75°	23	28	41	57	100	144	199	255	309	357	395
7.5°	23	31	43	67	111	158	214	271	325	371	405
6.25°	24	33	46	76	120	170	227	285	337	381	413
5°	25	35	48	83	128	180	238	296	347	390	419
3.75°	25	36	49	89	133	188	247	304	355	396	424
2.5°	25	37	50	93	138	194	253	310	361	400	428
1.25°	25	38	51	95	140	198	257	314	365	402	430
0°	26	38	51	96	141	199	258	315	366	403	430
-1.25°	25	38	51	95	140	198	257	314	365	402	430
-2.5°	25	37	50	93	138	194	253	310	361	400	428
-3.75°	25	36	49	89	133	188	247	304	355	396	424
-5°	25	35	48	83	128	180	238	296	347	390	419
-6.25°	24	33	46	76	120	170	227	285	337	381	413
-7.5°	23	31	43	67	111	158	214	271	325	371	405
-8.75°	23	28	41	57	100	144	199	255	309	357	395
-10°	22	25	37	50	88	130	181	236	291	340	381
-11.25°	21	24	34	46	74	116	162	215	269	320	365
-12.5°	20	23	30	42	59	100	141	193	245	297	343
-13.75°	19	22	26	37	49	83	123	168	219	271	318
-15°	18	21	24	32	44	64	104	143	191	241	290
-16.25°	17	20	23	27	38	49	83	121	163	210	258
-17.5°	16	18	21	24	33	43	61	98	134	178	224
-18.75°	15	17	20	23	26	37	47	74	109	145	188
-20°	13	16	18	21	24	30	40	50	83	117	152
-21.25°	12	14	17	19	22	25	33	43	56	89	121





REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	11	13	15	17	20	23	26	35	45	60	91
-23.75°	9	12	14	16	18	21	23	27	36	45	60
-25°	8	10	12	14	16	19	21	24	28	36	45
-26.25°	6	8	11	13	15	17	19	21	24	27	35
-27.5°	6	7	9	11	13	15	17	19	21	23	26
-28.75°	6	6	7	9	11	13	15	17	19	21	23
-30°	5	6	6	7	9	11	13	15	16	18	20
-31.25°	5	5	6	6	7	9	11	13	14	16	17
-32.5°	5	5	5	6	6	7	9	11	12	14	15
-33.75°	5	5	5	5	6	6	7	8	10	12	13
-35°	5	5	5	5	5	6	6	6	8	9	11
-36.25°	4	5	5	5	5	5	6	6	6	7	8
-37.5°	4	4	5	5	5	5	5	5	6	6	6
-38.75°	4	4	4	5	5	5	5	5	5	5	6
-40°	4	4	4	4	4	5	5	5	5	5	5
-41.25°	4	4	4	4	4	4	5	5	5	5	5
-42.5°	3	4	4	4	4	4	4	4	5	5	5
-43.75°	3	3	4	4	4	4	4	4	4	4	5
-45°	3	3	3	3	4	4	4	4	4	4	4
-46.25°	3	3	3	3	3	3	4	4	4	4	4
-47.5°	3	3	3	3	3	3	3	3	4	4	4
-48.75°	3	3	3	3	3	3	3	3	3	3	4
-50°	2	3	3	3	3	3	3	3	3	3	3
-51.25°	2	2	2	3	3	3	3	3	3	3	3
-52.5°	2	2	2	2	2	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	2	3	3	3	3
-55°	2	2	2	2	2	2	2	2	2	2	3
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	1	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	2	2
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	3	3
56.25°	2	2	2	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	4	4	4	4
50°	3	3	3	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	5	5
46.25°	4	4	4	4	4	5	5	5	5	5	5
45°	4	4	5	5	5	5	5	5	5	5	5
43.75°	5	5	5	5	5	5	5	5	5	5	5
42.5°	5	5	5	5	5	5	6	6	6	6	6
41.25°	5	5	5	6	6	6	6	6	7	7	8
40°	5	6	6	6	6	7	8	9	9	10	11
38.75°	6	6	7	8	9	10	11	12	12	13	14
37.5°	7	8	9	11	12	13	14	14	15	16	16
36.25°	10	11	12	13	14	15	16	17	18	18	19
35°	12	13	15	16	17	18	19	20	21	22	23



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	14	16	17	18	20	21	22	23	24	25	28
32.5°	17	18	20	21	23	24	26	30	34	37	41
31.25°	19	21	23	24	27	32	37	42	46	50	57
30°	22	24	26	33	38	44	49	59	74	88	100
28.75°	25	30	37	43	49	64	83	100	116	130	144
27.5°	33	40	47	61	83	104	123	141	162	181	199
26.25°	43	50	74	98	121	143	168	193	215	236	255
25°	56	83	109	134	163	191	219	245	269	291	309
23.75°	89	117	145	178	210	241	271	297	320	340	357
22.5°	121	152	188	224	258	290	318	343	365	381	395
21.25°	155	194	232	269	303	334	360	381	399	411	422
20°	194	235	275	311	344	372	394	409	423	435	449
18.75°	232	275	314	349	378	401	417	432	449	467	489
17.5°	269	311	349	380	404	422	439	460	485	512	543
16.25°	303	344	378	404	423	442	467	498	534	571	617
15°	334	372	401	422	442	470	505	547	596	650	712
13.75°	360	394	417	439	467	505	552	609	676	748	832
12.5°	381	409	432	460	498	547	609	684	771	868	967
11.25°	399	423	449	485	534	596	676	771	881	995	1118
10°	411	435	467	512	571	650	748	868	995	1135	1275
8.75°	422	449	489	543	617	712	832	967	1118	1275	1435
7.5°	431	463	509	572	661	774	912	1067	1236	1413	1592
6.25°	439	476	531	606	705	835	986	1159	1345	1541	1738
5°	448	490	550	634	743	890	1056	1244	1445	1656	1866
3.75°	455	501	566	658	782	936	1114	1311	1527	1750	1972
2.5°	460	509	578	678	809	969	1156	1364	1589	1821	2051
1.25°	464	514	588	690	826	989	1184	1397	1627	1865	2100
0°	465	515	591	694	832	996	1193	1408	1640	1880	2116
-1.25°	464	514	588	690	826	989	1184	1397	1627	1865	2100
-2.5°	460	509	578	678	809	969	1156	1364	1589	1821	2051
-3.75°	455	501	566	658	782	936	1114	1311	1527	1750	1972
-5°	448	490	550	634	743	890	1056	1244	1445	1656	1866
-6.25°	439	476	531	606	705	835	986	1159	1345	1541	1738
-7.5°	431	463	509	572	661	774	912	1067	1236	1413	1592
-8.75°	422	449	489	543	617	712	832	967	1118	1275	1435
-10°	411	435	467	512	571	650	748	868	995	1135	1275
-11.25°	399	423	449	485	534	596	676	771	881	995	1118
-12.5°	381	409	432	460	498	547	609	684	771	868	967
-13.75°	360	394	417	439	467	505	552	609	676	748	832
-15°	334	372	401	422	442	470	505	547	596	650	712
-16.25°	303	344	378	404	423	442	467	498	534	571	617
-17.5°	269	311	349	380	404	422	439	460	485	512	543
-18.75°	232	275	314	349	378	401	417	432	449	467	489
-20°	194	235	275	311	344	372	394	409	423	435	449
-21.25°	155	194	232	269	303	334	360	381	399	411	422



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	121	152	188	224	258	290	318	343	365	381	395
-23.75°	89	117	145	178	210	241	271	297	320	340	357
-25°	56	83	109	134	163	191	219	245	269	291	309
-26.25°	43	50	74	98	121	143	168	193	215	236	255
-27.5°	33	40	47	61	83	104	123	141	162	181	199
-28.75°	25	30	37	43	49	64	83	100	116	130	144
-30°	22	24	26	33	38	44	49	59	74	88	100
-31.25°	19	21	23	24	27	32	37	42	46	50	57
-32.5°	17	18	20	21	23	24	26	30	34	37	41
-33.75°	14	16	17	18	20	21	22	23	24	25	28
-35°	12	13	15	16	17	18	19	20	21	22	23
-36.25°	10	11	12	13	14	15	16	17	18	18	19
-37.5°	7	8	9	11	12	13	14	14	15	16	16
-38.75°	6	6	7	8	9	10	11	12	12	13	14
-40°	5	6	6	6	6	7	8	9	9	10	11
-41.25°	5	5	5	6	6	6	6	6	7	7	8
-42.5°	5	5	5	5	5	5	6	6	6	6	6
-43.75°	5	5	5	5	5	5	5	5	5	5	5
-45°	4	4	5	5	5	5	5	5	5	5	5
-46.25°	4	4	4	4	4	5	5	5	5	5	5
-47.5°	4	4	4	4	4	4	4	4	4	5	5
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	3	3	3	4	4	4	4	4	4	4	4
-51.25°	3	3	3	3	3	3	3	4	4	4	4
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	2	2	3	3	3	3	3	3	3	3
-57.5°	2	2	2	2	2	2	2	2	2	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	1	1	1	2	2	2	2	2	2	2	2
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	1	1	1	1	1	1	1	1	1	1
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	2	1	1	1	1
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	4	3	3	3	3
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	5	5	5	5	5	5	5	5	5	5	5
43.75°	6	6	6	6	6	6	6	6	6	6	6
42.5°	6	6	6	6	6	6	7	6	6	6	6
41.25°	8	9	9	9	9	10	10	10	9	9	9
40°	11	12	12	12	12	13	13	13	12	12	12
38.75°	14	14	15	15	15	15	15	15	15	15	15
37.5°	17	17	18	18	18	18	18	18	18	18	18
36.25°	20	21	21	21	22	22	22	22	22	21	21
35°	23	24	25	25	25	25	26	25	25	25	25



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	31	33	35	36	37	38	38	38	37	36	35
32.5°	43	46	48	49	50	51	51	51	50	49	48
31.25°	67	76	83	89	93	95	96	95	93	89	83
30°	111	120	128	133	138	140	141	140	138	133	128
28.75°	158	170	180	188	194	198	199	198	194	188	180
27.5°	214	227	238	247	253	257	258	257	253	247	238
26.25°	271	285	296	304	310	314	315	314	310	304	296
25°	325	337	347	355	361	365	366	365	361	355	347
23.75°	371	381	390	396	400	402	403	402	400	396	390
22.5°	405	413	419	424	428	430	430	430	428	424	419
21.25°	431	439	448	455	460	464	465	464	460	455	448
20°	463	476	490	501	509	514	515	514	509	501	490
18.75°	509	531	550	566	578	588	591	588	578	566	550
17.5°	572	606	634	658	678	690	694	690	678	658	634
16.25°	661	705	743	782	809	826	832	826	809	782	743
15°	774	835	890	936	969	989	996	989	969	936	890
13.75°	912	986	1056	1114	1156	1184	1193	1184	1156	1114	1056
12.5°	1067	1159	1244	1311	1364	1397	1408	1397	1364	1311	1244
11.25°	1236	1345	1445	1527	1589	1627	1640	1627	1589	1527	1445
10°	1413	1541	1656	1750	1821	1865	1880	1865	1821	1750	1656
8.75°	1592	1738	1866	1972	2051	2100	2116	2100	2051	1972	1866
7.5°	1766	1927	2069	2183	2269	2319	2337	2319	2269	2183	2069
6.25°	1927	2101	2253	2372	2460	2512	2530	2512	2460	2372	2253
5°	2069	2253	2409	2531	2618	2671	2690	2671	2618	2531	2409
3.75°	2183	2372	2531	2653	2741	2796	2813	2796	2741	2653	2531
2.5°	2269	2460	2618	2741	2830	2884	2899	2884	2830	2741	2618
1.25°	2319	2512	2671	2796	2884	2930	2946	2930	2884	2796	2671
0°	2337	2530	2690	2813	2899	2946	2972	2946	2899	2813	2690
-1.25°	2319	2512	2671	2796	2884	2930	2946	2930	2884	2796	2671
-2.5°	2269	2460	2618	2741	2830	2884	2899	2884	2830	2741	2618
-3.75°	2183	2372	2531	2653	2741	2796	2813	2796	2741	2653	2531
-5°	2069	2253	2409	2531	2618	2671	2690	2671	2618	2531	2409
-6.25°	1927	2101	2253	2372	2460	2512	2530	2512	2460	2372	2253
-7.5°	1766	1927	2069	2183	2269	2319	2337	2319	2269	2183	2069
-8.75°	1592	1738	1866	1972	2051	2100	2116	2100	2051	1972	1866
-10°	1413	1541	1656	1750	1821	1865	1880	1865	1821	1750	1656
-11.25°	1236	1345	1445	1527	1589	1627	1640	1627	1589	1527	1445
-12.5°	1067	1159	1244	1311	1364	1397	1408	1397	1364	1311	1244
-13.75°	912	986	1056	1114	1156	1184	1193	1184	1156	1114	1056
-15°	774	835	890	936	969	989	996	989	969	936	890
-16.25°	661	705	743	782	809	826	832	826	809	782	743
-17.5°	572	606	634	658	678	690	694	690	678	658	634
-18.75°	509	531	550	566	578	588	591	588	578	566	550
-20°	463	476	490	501	509	514	515	514	509	501	490
-21.25°	431	439	448	455	460	464	465	464	460	455	448





REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	405	413	419	424	428	430	430	430	428	424	419
-23.75°	371	381	390	396	400	402	403	402	400	396	390
-25°	325	337	347	355	361	365	366	365	361	355	347
-26.25°	271	285	296	304	310	314	315	314	310	304	296
-27.5°	214	227	238	247	253	257	258	257	253	247	238
-28.75°	158	170	180	188	194	198	199	198	194	188	180
-30°	111	120	128	133	138	140	141	140	138	133	128
-31.25°	67	76	83	89	93	95	96	95	93	89	83
-32.5°	43	46	48	49	50	51	51	51	50	49	48
-33.75°	31	33	35	36	37	38	38	38	37	36	35
-35°	23	24	25	25	25	25	26	25	25	25	25
-36.25°	20	21	21	21	22	22	22	22	22	21	21
-37.5°	17	17	18	18	18	18	18	18	18	18	18
-38.75°	14	14	15	15	15	15	15	15	15	15	15
-40°	11	12	12	12	12	13	13	13	12	12	12
-41.25°	8	9	9	9	9	10	10	10	9	9	9
-42.5°	6	6	6	6	6	6	7	6	6	6	6
-43.75°	6	6	6	6	6	6	6	6	6	6	6
-45°	5	5	5	5	5	5	5	5	5	5	5
-46.25°	5	5	5	5	5	5	5	5	5	5	5
-47.5°	5	5	5	5	5	5	5	5	5	5	5
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	3	3	3	3	3	3	4	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	1	1	1	1	1	1	2	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	2	2	2	2	2	2	2	2	2	2	1
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	2	2	2	2	2	2	2
56.25°	3	3	3	3	3	3	3	3	3	3	2
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	4	4	4	4	4	4	3	3	3	3	3
50°	4	4	4	4	4	4	4	4	4	4	3
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	5	5	5	5	4	4	4	4	4	4	4
46.25°	5	5	5	5	5	5	5	5	4	4	4
45°	5	5	5	5	5	5	5	5	5	5	5
43.75°	6	6	5	5	5	5	5	5	5	5	5
42.5°	6	6	6	6	6	6	6	5	5	5	5
41.25°	9	8	8	7	7	6	6	6	6	6	5
40°	12	11	11	10	9	9	8	7	6	6	6
38.75°	14	14	14	13	12	12	11	10	9	8	7
37.5°	17	17	16	16	15	14	14	13	12	11	9
36.25°	21	20	19	18	18	17	16	15	14	13	12
35°	24	23	23	22	21	20	19	18	17	16	15



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	33	31	28	25	24	23	22	21	20	18	17
32.5°	46	43	41	37	34	30	26	24	23	21	20
31.25°	76	67	57	50	46	42	37	32	27	24	23
30°	120	111	100	88	74	59	49	44	38	33	26
28.75°	170	158	144	130	116	100	83	64	49	43	37
27.5°	227	214	199	181	162	141	123	104	83	61	47
26.25°	285	271	255	236	215	193	168	143	121	98	74
25°	337	325	309	291	269	245	219	191	163	134	109
23.75°	381	371	357	340	320	297	271	241	210	178	145
22.5°	413	405	395	381	365	343	318	290	258	224	188
21.25°	439	431	422	411	399	381	360	334	303	269	232
20°	476	463	449	435	423	409	394	372	344	311	275
18.75°	531	509	489	467	449	432	417	401	378	349	314
17.5°	606	572	543	512	485	460	439	422	404	380	349
16.25°	705	661	617	571	534	498	467	442	423	404	378
15°	835	774	712	650	596	547	505	470	442	422	401
13.75°	986	912	832	748	676	609	552	505	467	439	417
12.5°	1159	1067	967	868	771	684	609	547	498	460	432
11.25°	1345	1236	1118	995	881	771	676	596	534	485	449
10°	1541	1413	1275	1135	995	868	748	650	571	512	467
8.75°	1738	1592	1435	1275	1118	967	832	712	617	543	489
7.5°	1927	1766	1592	1413	1236	1067	912	774	661	572	509
6.25°	2101	1927	1738	1541	1345	1159	986	835	705	606	531
5°	2253	2069	1866	1656	1445	1244	1056	890	743	634	550
3.75°	2372	2183	1972	1750	1527	1311	1114	936	782	658	566
2.5°	2460	2269	2051	1821	1589	1364	1156	969	809	678	578
1.25°	2512	2319	2100	1865	1627	1397	1184	989	826	690	588
0°	2530	2337	2116	1880	1640	1408	1193	996	832	694	591
-1.25°	2512	2319	2100	1865	1627	1397	1184	989	826	690	588
-2.5°	2460	2269	2051	1821	1589	1364	1156	969	809	678	578
-3.75°	2372	2183	1972	1750	1527	1311	1114	936	782	658	566
-5°	2253	2069	1866	1656	1445	1244	1056	890	743	634	550
-6.25°	2101	1927	1738	1541	1345	1159	986	835	705	606	531
-7.5°	1927	1766	1592	1413	1236	1067	912	774	661	572	509
-8.75°	1738	1592	1435	1275	1118	967	832	712	617	543	489
-10°	1541	1413	1275	1135	995	868	748	650	571	512	467
-11.25°	1345	1236	1118	995	881	771	676	596	534	485	449
-12.5°	1159	1067	967	868	771	684	609	547	498	460	432
-13.75°	986	912	832	748	676	609	552	505	467	439	417
-15°	835	774	712	650	596	547	505	470	442	422	401
-16.25°	705	661	617	571	534	498	467	442	423	404	378
-17.5°	606	572	543	512	485	460	439	422	404	380	349
-18.75°	531	509	489	467	449	432	417	401	378	349	314
-20°	476	463	449	435	423	409	394	372	344	311	275
-21.25°	439	431	422	411	399	381	360	334	303	269	232



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	413	405	395	381	365	343	318	290	258	224	188
-23.75°	381	371	357	340	320	297	271	241	210	178	145
-25°	337	325	309	291	269	245	219	191	163	134	109
-26.25°	285	271	255	236	215	193	168	143	121	98	74
-27.5°	227	214	199	181	162	141	123	104	83	61	47
-28.75°	170	158	144	130	116	100	83	64	49	43	37
-30°	120	111	100	88	74	59	49	44	38	33	26
-31.25°	76	67	57	50	46	42	37	32	27	24	23
-32.5°	46	43	41	37	34	30	26	24	23	21	20
-33.75°	33	31	28	25	24	23	22	21	20	18	17
-35°	24	23	23	22	21	20	19	18	17	16	15
-36.25°	21	20	19	18	18	17	16	15	14	13	12
-37.5°	17	17	16	16	15	14	14	13	12	11	9
-38.75°	14	14	14	13	12	12	11	10	9	8	7
-40°	12	11	11	10	9	9	8	7	6	6	6
-41.25°	9	8	8	7	7	6	6	6	6	6	5
-42.5°	6	6	6	6	6	6	6	5	5	5	5
-43.75°	6	6	5	5	5	5	5	5	5	5	5
-45°	5	5	5	5	5	5	5	5	5	5	5
-46.25°	5	5	5	5	5	5	5	5	4	4	4
-47.5°	5	5	5	5	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	3
-51.25°	4	4	4	4	4	4	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	2
-57.5°	3	3	3	3	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	1	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	2	2	2	2	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	1	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	2	2	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	2	2	2	2	2
52.5°	3	3	3	3	3	3	3	3	2	2	2
51.25°	3	3	3	3	3	3	3	3	3	3	2
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	4	4	4	3	3	3	3	3	3	3	3
47.5°	4	4	4	4	4	3	3	3	3	3	3
46.25°	4	4	4	4	4	4	4	3	3	3	3
45°	4	4	4	4	4	4	4	4	4	3	3
43.75°	5	5	5	4	4	4	4	4	4	4	4
42.5°	5	5	5	5	5	4	4	4	4	4	4
41.25°	5	5	5	5	5	5	5	4	4	4	4
40°	6	5	5	5	5	5	5	5	4	4	4
38.75°	6	6	6	5	5	5	5	5	5	5	4
37.5°	8	7	6	6	6	5	5	5	5	5	5
36.25°	11	10	8	7	6	6	6	5	5	5	5
35°	13	12	11	9	8	6	6	6	5	5	5



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	16	14	13	12	10	8	7	6	6	5	5
32.5°	18	17	15	14	12	11	9	7	6	6	5
31.25°	21	19	17	16	14	13	11	9	7	6	6
30°	24	22	20	18	16	15	13	11	9	7	6
28.75°	30	25	23	21	19	17	15	13	11	9	7
27.5°	40	33	26	23	21	19	17	15	13	11	9
26.25°	50	43	35	27	24	21	19	17	15	13	11
25°	83	56	45	36	28	24	21	19	16	14	12
23.75°	117	89	60	45	36	27	23	21	18	16	14
22.5°	152	121	91	60	45	35	26	23	20	17	15
21.25°	194	155	121	89	56	43	33	25	22	19	17
20°	235	194	152	117	83	50	40	30	24	21	18
18.75°	275	232	188	145	109	74	47	37	26	23	20
17.5°	311	269	224	178	134	98	61	43	33	24	21
16.25°	344	303	258	210	163	121	83	49	38	27	23
15°	372	334	290	241	191	143	104	64	44	32	24
13.75°	394	360	318	271	219	168	123	83	49	37	26
12.5°	409	381	343	297	245	193	141	100	59	42	30
11.25°	423	399	365	320	269	215	162	116	74	46	34
10°	435	411	381	340	291	236	181	130	88	50	37
8.75°	449	422	395	357	309	255	199	144	100	57	41
7.5°	463	431	405	371	325	271	214	158	111	67	43
6.25°	476	439	413	381	337	285	227	170	120	76	46
5°	490	448	419	390	347	296	238	180	128	83	48
3.75°	501	455	424	396	355	304	247	188	133	89	49
2.5°	509	460	428	400	361	310	253	194	138	93	50
1.25°	514	464	430	402	365	314	257	198	140	95	51
0°	515	465	430	403	366	315	258	199	141	96	51
-1.25°	514	464	430	402	365	314	257	198	140	95	51
-2.5°	509	460	428	400	361	310	253	194	138	93	50
-3.75°	501	455	424	396	355	304	247	188	133	89	49
-5°	490	448	419	390	347	296	238	180	128	83	48
-6.25°	476	439	413	381	337	285	227	170	120	76	46
-7.5°	463	431	405	371	325	271	214	158	111	67	43
-8.75°	449	422	395	357	309	255	199	144	100	57	41
-10°	435	411	381	340	291	236	181	130	88	50	37
-11.25°	423	399	365	320	269	215	162	116	74	46	34
-12.5°	409	381	343	297	245	193	141	100	59	42	30
-13.75°	394	360	318	271	219	168	123	83	49	37	26
-15°	372	334	290	241	191	143	104	64	44	32	24
-16.25°	344	303	258	210	163	121	83	49	38	27	23
-17.5°	311	269	224	178	134	98	61	43	33	24	21
-18.75°	275	232	188	145	109	74	47	37	26	23	20
-20°	235	194	152	117	83	50	40	30	24	21	18
-21.25°	194	155	121	89	56	43	33	25	22	19	17





REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	152	121	91	60	45	35	26	23	20	17	15
-23.75°	117	89	60	45	36	27	23	21	18	16	14
-25°	83	56	45	36	28	24	21	19	16	14	12
-26.25°	50	43	35	27	24	21	19	17	15	13	11
-27.5°	40	33	26	23	21	19	17	15	13	11	9
-28.75°	30	25	23	21	19	17	15	13	11	9	7
-30°	24	22	20	18	16	15	13	11	9	7	6
-31.25°	21	19	17	16	14	13	11	9	7	6	6
-32.5°	18	17	15	14	12	11	9	7	6	6	5
-33.75°	16	14	13	12	10	8	7	6	6	5	5
-35°	13	12	11	9	8	6	6	6	5	5	5
-36.25°	11	10	8	7	6	6	6	5	5	5	5
-37.5°	8	7	6	6	6	5	5	5	5	5	5
-38.75°	6	6	6	5	5	5	5	5	5	5	4
-40°	6	5	5	5	5	5	5	5	4	4	4
-41.25°	5	5	5	5	5	5	5	4	4	4	4
-42.5°	5	5	5	5	5	4	4	4	4	4	4
-43.75°	5	5	5	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	3	3
-46.25°	4	4	4	4	4	4	4	3	3	3	3
-47.5°	4	4	4	4	4	3	3	3	3	3	3
-48.75°	4	4	4	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	2
-52.5°	3	3	3	3	3	3	3	3	2	2	2
-53.75°	3	3	3	3	3	3	2	2	2	2	2
-55°	3	3	3	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	1	1	1
-63.75°	2	2	2	2	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	1	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	1	1	1	1	0	0	0	0	0	0
75°	1	1	1	1	1	1	1	1	1	1	0
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	2	2	2	1	1	1	1	1	1	1	1
58.75°	2	2	2	2	2	1	1	1	1	1	1
57.5°	2	2	2	2	2	2	2	1	1	1	1
56.25°	2	2	2	2	2	2	2	2	1	1	1
55°	2	2	2	2	2	2	2	2	2	2	1
53.75°	2	2	2	2	2	2	2	2	2	2	2
52.5°	2	2	2	2	2	2	2	2	2	2	2
51.25°	2	2	2	2	2	2	2	2	2	2	2
50°	3	2	2	2	2	2	2	2	2	2	2
48.75°	3	3	3	2	2	2	2	2	2	2	2
47.5°	3	3	3	3	2	2	2	2	2	2	2
46.25°	3	3	3	3	3	3	2	2	2	2	2
45°	3	3	3	3	3	3	3	2	2	2	2
43.75°	3	3	3	3	3	3	3	3	2	2	2
42.5°	4	3	3	3	3	3	3	3	3	2	2
41.25°	4	4	3	3	3	3	3	3	3	3	2
40°	4	4	4	3	3	3	3	3	3	3	3
38.75°	4	4	4	4	3	3	3	3	3	3	3
37.5°	4	4	4	4	4	3	3	3	3	3	3
36.25°	5	4	4	4	4	4	3	3	3	3	3
35°	5	5	4	4	4	4	4	3	3	3	3



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	5	5	5	4	4	4	4	4	3	3	3
32.5°	5	5	5	5	4	4	4	4	4	3	3
31.25°	5	5	5	5	5	4	4	4	4	3	3
30°	6	5	5	5	5	4	4	4	4	4	3
28.75°	6	6	5	5	5	5	4	4	4	4	3
27.5°	7	6	6	5	5	5	5	4	4	4	4
26.25°	8	6	6	5	5	5	5	4	4	4	4
25°	10	8	6	6	5	5	5	5	4	4	4
23.75°	12	9	7	6	5	5	5	5	4	4	4
22.5°	13	11	8	6	6	5	5	5	5	4	4
21.25°	14	12	10	7	6	5	5	5	5	4	4
20°	16	13	11	8	6	6	5	5	5	4	4
18.75°	17	15	12	9	7	6	5	5	5	5	4
17.5°	18	16	13	11	8	6	6	5	5	5	4
16.25°	20	17	14	12	9	6	6	5	5	5	4
15°	21	18	15	13	10	7	6	5	5	5	5
13.75°	22	19	16	14	11	8	6	6	5	5	5
12.5°	23	20	17	14	12	9	6	6	5	5	5
11.25°	24	21	18	15	12	9	7	6	5	5	5
10°	25	22	18	16	13	10	7	6	5	5	5
8.75°	28	23	19	16	14	11	8	6	5	5	5
7.5°	31	23	20	17	14	11	8	6	6	5	5
6.25°	33	24	21	17	14	12	9	6	6	5	5
5°	35	25	21	18	15	12	9	6	6	5	5
3.75°	36	25	21	18	15	12	9	6	6	5	5
2.5°	37	25	22	18	15	12	9	6	6	5	5
1.25°	38	25	22	18	15	13	10	6	6	5	5
0°	38	26	22	18	15	13	10	7	6	5	5
-1.25°	38	25	22	18	15	13	10	6	6	5	5
-2.5°	37	25	22	18	15	12	9	6	6	5	5
-3.75°	36	25	21	18	15	12	9	6	6	5	5
-5°	35	25	21	18	15	12	9	6	6	5	5
-6.25°	33	24	21	17	14	12	9	6	6	5	5
-7.5°	31	23	20	17	14	11	8	6	6	5	5
-8.75°	28	23	19	16	14	11	8	6	5	5	5
-10°	25	22	18	16	13	10	7	6	5	5	5
-11.25°	24	21	18	15	12	9	7	6	5	5	5
-12.5°	23	20	17	14	12	9	6	6	5	5	5
-13.75°	22	19	16	14	11	8	6	6	5	5	5
-15°	21	18	15	13	10	7	6	5	5	5	5
-16.25°	20	17	14	12	9	6	6	5	5	5	4
-17.5°	18	16	13	11	8	6	6	5	5	5	4
-18.75°	17	15	12	9	7	6	5	5	5	5	4
-20°	16	13	11	8	6	6	5	5	5	4	4
-21.25°	14	12	10	7	6	5	5	5	5	4	4



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	13	11	8	6	6	5	5	5	5	4	4
-23.75°	12	9	7	6	5	5	5	5	4	4	4
-25°	10	8	6	6	5	5	5	5	4	4	4
-26.25°	8	6	6	5	5	5	5	4	4	4	4
-27.5°	7	6	6	5	5	5	5	4	4	4	4
-28.75°	6	6	5	5	5	5	4	4	4	4	3
-30°	6	5	5	5	5	4	4	4	4	4	3
-31.25°	5	5	5	5	5	4	4	4	4	3	3
-32.5°	5	5	5	5	4	4	4	4	4	3	3
-33.75°	5	5	5	4	4	4	4	4	3	3	3
-35°	5	5	4	4	4	4	4	3	3	3	3
-36.25°	5	4	4	4	4	4	3	3	3	3	3
-37.5°	4	4	4	4	4	3	3	3	3	3	3
-38.75°	4	4	4	4	3	3	3	3	3	3	3
-40°	4	4	4	3	3	3	3	3	3	3	3
-41.25°	4	4	3	3	3	3	3	3	3	3	2
-42.5°	4	3	3	3	3	3	3	3	3	2	2
-43.75°	3	3	3	3	3	3	3	3	2	2	2
-45°	3	3	3	3	3	3	3	2	2	2	2
-46.25°	3	3	3	3	3	3	2	2	2	2	2
-47.5°	3	3	3	3	2	2	2	2	2	2	2
-48.75°	3	3	3	2	2	2	2	2	2	2	2
-50°	3	2	2	2	2	2	2	2	2	2	2
-51.25°	2	2	2	2	2	2	2	2	2	2	2
-52.5°	2	2	2	2	2	2	2	2	2	2	2
-53.75°	2	2	2	2	2	2	2	2	2	2	2
-55°	2	2	2	2	2	2	2	2	2	2	1
-56.25°	2	2	2	2	2	2	2	2	1	1	1
-57.5°	2	2	2	2	2	2	2	1	1	1	1
-58.75°	2	2	2	2	2	1	1	1	1	1	1
-60°	2	2	2	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	0
-76.25°	1	1	1	1	1	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	1	1	0	0	0	0	0	0	0	0	0
72.5°	1	1	1	1	1	0	0	0	0	0	0
71.25°	1	1	1	1	1	1	1	0	0	0	0
70°	1	1	1	1	1	1	1	1	1	0	0
68.75°	1	1	1	1	1	1	1	1	1	1	0
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	2	1	1	1	1	1	1	1	1	1	1
51.25°	2	2	1	1	1	1	1	1	1	1	1
50°	2	2	2	1	1	1	1	1	1	1	1
48.75°	2	2	2	2	1	1	1	1	1	1	1
47.5°	2	2	2	2	2	1	1	1	1	1	1
46.25°	2	2	2	2	2	2	1	1	1	1	1
45°	2	2	2	2	2	2	2	1	1	1	1
43.75°	2	2	2	2	2	2	2	1	1	1	1
42.5°	2	2	2	2	2	2	2	2	1	1	1
41.25°	2	2	2	2	2	2	2	2	2	1	1
40°	2	2	2	2	2	2	2	2	2	1	1
38.75°	2	2	2	2	2	2	2	2	2	2	1
37.5°	3	2	2	2	2	2	2	2	2	2	1
36.25°	3	3	2	2	2	2	2	2	2	2	2
35°	3	3	2	2	2	2	2	2	2	2	2



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	3	3	3	2	2	2	2	2	2	2	2
32.5°	3	3	3	2	2	2	2	2	2	2	2
31.25°	3	3	3	3	2	2	2	2	2	2	2
30°	3	3	3	3	2	2	2	2	2	2	2
28.75°	3	3	3	3	3	2	2	2	2	2	2
27.5°	3	3	3	3	3	2	2	2	2	2	2
26.25°	3	3	3	3	3	3	2	2	2	2	2
25°	4	3	3	3	3	3	2	2	2	2	2
23.75°	4	3	3	3	3	3	2	2	2	2	2
22.5°	4	4	3	3	3	3	3	2	2	2	2
21.25°	4	4	3	3	3	3	3	2	2	2	2
20°	4	4	3	3	3	3	3	2	2	2	2
18.75°	4	4	3	3	3	3	3	2	2	2	2
17.5°	4	4	4	3	3	3	3	3	2	2	2
16.25°	4	4	4	3	3	3	3	3	2	2	2
15°	4	4	4	3	3	3	3	3	2	2	2
13.75°	4	4	4	3	3	3	3	3	2	2	2
12.5°	4	4	4	4	3	3	3	3	2	2	2
11.25°	4	4	4	4	3	3	3	3	2	2	2
10°	5	4	4	4	3	3	3	3	3	2	2
8.75°	5	4	4	4	3	3	3	3	3	2	2
7.5°	5	4	4	4	3	3	3	3	3	2	2
6.25°	5	4	4	4	3	3	3	3	3	2	2
5°	5	4	4	4	3	3	3	3	3	2	2
3.75°	5	4	4	4	3	3	3	3	3	2	2
2.5°	5	4	4	4	3	3	3	3	3	2	2
1.25°	5	4	4	4	3	3	3	3	3	2	2
0°	5	4	4	4	4	3	3	3	3	2	2
-1.25°	5	4	4	4	3	3	3	3	3	2	2
-2.5°	5	4	4	4	3	3	3	3	3	2	2
-3.75°	5	4	4	4	3	3	3	3	3	2	2
-5°	5	4	4	4	3	3	3	3	3	2	2
-6.25°	5	4	4	4	3	3	3	3	3	2	2
-7.5°	5	4	4	4	3	3	3	3	3	2	2
-8.75°	5	4	4	4	3	3	3	3	3	2	2
-10°	5	4	4	4	3	3	3	3	3	2	2
-11.25°	4	4	4	4	3	3	3	3	2	2	2
-12.5°	4	4	4	4	3	3	3	3	2	2	2
-13.75°	4	4	4	3	3	3	3	3	2	2	2
-15°	4	4	4	3	3	3	3	3	2	2	2
-16.25°	4	4	4	3	3	3	3	3	2	2	2
-17.5°	4	4	4	3	3	3	3	3	2	2	2
-18.75°	4	4	3	3	3	3	3	2	2	2	2
-20°	4	4	3	3	3	3	3	2	2	2	2
-21.25°	4	4	3	3	3	3	3	2	2	2	2





REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	4	4	3	3	3	3	3	2	2	2	2
-23.75°	4	3	3	3	3	3	2	2	2	2	2
-25°	4	3	3	3	3	3	2	2	2	2	2
-26.25°	3	3	3	3	3	3	2	2	2	2	2
-27.5°	3	3	3	3	3	2	2	2	2	2	2
-28.75°	3	3	3	3	3	2	2	2	2	2	2
-30°	3	3	3	3	2	2	2	2	2	2	2
-31.25°	3	3	3	3	2	2	2	2	2	2	2
-32.5°	3	3	3	2	2	2	2	2	2	2	2
-33.75°	3	3	3	2	2	2	2	2	2	2	2
-35°	3	3	2	2	2	2	2	2	2	2	2
-36.25°	3	3	2	2	2	2	2	2	2	2	2
-37.5°	3	2	2	2	2	2	2	2	2	2	1
-38.75°	2	2	2	2	2	2	2	2	2	2	1
-40°	2	2	2	2	2	2	2	2	2	1	1
-41.25°	2	2	2	2	2	2	2	2	2	1	1
-42.5°	2	2	2	2	2	2	2	2	1	1	1
-43.75°	2	2	2	2	2	2	2	1	1	1	1
-45°	2	2	2	2	2	2	2	1	1	1	1
-46.25°	2	2	2	2	2	2	1	1	1	1	1
-47.5°	2	2	2	2	2	1	1	1	1	1	1
-48.75°	2	2	2	2	1	1	1	1	1	1	1
-50°	2	2	2	1	1	1	1	1	1	1	1
-51.25°	2	2	1	1	1	1	1	1	1	1	1
-52.5°	2	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	0
-70°	1	1	1	1	1	1	1	1	1	0	0
-71.25°	1	1	1	1	1	1	1	0	0	0	0
-72.5°	1	1	1	1	1	0	0	0	0	0	0
-73.75°	1	1	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	1	0	0	0	0	0	0	0	0	0	0
66.25°	1	1	0	0	0	0	0	0	0	0	0
65°	1	1	1	0	0	0	0	0	0	0	0
63.75°	1	1	1	1	0	0	0	0	0	0	0
62.5°	1	1	1	1	1	0	0	0	0	0	0
61.25°	1	1	1	1	1	1	0	0	0	0	0
60°	1	1	1	1	1	1	0	0	0	0	0
58.75°	1	1	1	1	1	1	1	0	0	0	0
57.5°	1	1	1	1	1	1	1	1	0	0	0
56.25°	1	1	1	1	1	1	1	1	0	0	0
55°	1	1	1	1	1	1	1	1	1	0	0
53.75°	1	1	1	1	1	1	1	1	1	0	0
52.5°	1	1	1	1	1	1	1	1	1	1	0
51.25°	1	1	1	1	1	1	1	1	1	1	0
50°	1	1	1	1	1	1	1	1	1	1	0
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	1
40°	1	1	1	1	1	1	1	1	1	1	1
38.75°	1	1	1	1	1	1	1	1	1	1	1
37.5°	1	1	1	1	1	1	1	1	1	1	1
36.25°	1	1	1	1	1	1	1	1	1	1	1
35°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	1	1	1	1	1	1	1	1
32.5°	2	1	1	1	1	1	1	1	1	1	1
31.25°	2	1	1	1	1	1	1	1	1	1	1
30°	2	1	1	1	1	1	1	1	1	1	1
28.75°	2	2	1	1	1	1	1	1	1	1	1
27.5°	2	2	1	1	1	1	1	1	1	1	1
26.25°	2	2	1	1	1	1	1	1	1	1	1
25°	2	2	1	1	1	1	1	1	1	1	1
23.75°	2	2	2	1	1	1	1	1	1	1	1
22.5°	2	2	2	1	1	1	1	1	1	1	1
21.25°	2	2	2	1	1	1	1	1	1	1	1
20°	2	2	2	1	1	1	1	1	1	1	1
18.75°	2	2	2	1	1	1	1	1	1	1	1
17.5°	2	2	2	2	1	1	1	1	1	1	1
16.25°	2	2	2	2	1	1	1	1	1	1	1
15°	2	2	2	2	1	1	1	1	1	1	1
13.75°	2	2	2	2	1	1	1	1	1	1	1
12.5°	2	2	2	2	1	1	1	1	1	1	1
11.25°	2	2	2	2	1	1	1	1	1	1	1
10°	2	2	2	2	1	1	1	1	1	1	1
8.75°	2	2	2	2	1	1	1	1	1	1	1
7.5°	2	2	2	2	1	1	1	1	1	1	1
6.25°	2	2	2	2	1	1	1	1	1	1	1
5°	2	2	2	2	1	1	1	1	1	1	1
3.75°	2	2	2	2	1	1	1	1	1	1	1
2.5°	2	2	2	2	1	1	1	1	1	1	1
1.25°	2	2	2	2	1	1	1	1	1	1	1
0°	2	2	2	2	2	1	1	1	1	1	1
-1.25°	2	2	2	2	1	1	1	1	1	1	1
-2.5°	2	2	2	2	1	1	1	1	1	1	1
-3.75°	2	2	2	2	1	1	1	1	1	1	1
-5°	2	2	2	2	1	1	1	1	1	1	1
-6.25°	2	2	2	2	1	1	1	1	1	1	1
-7.5°	2	2	2	2	1	1	1	1	1	1	1
-8.75°	2	2	2	2	1	1	1	1	1	1	1
-10°	2	2	2	2	1	1	1	1	1	1	1
-11.25°	2	2	2	2	1	1	1	1	1	1	1
-12.5°	2	2	2	2	1	1	1	1	1	1	1
-13.75°	2	2	2	2	1	1	1	1	1	1	1
-15°	2	2	2	2	1	1	1	1	1	1	1
-16.25°	2	2	2	2	1	1	1	1	1	1	1
-17.5°	2	2	2	2	1	1	1	1	1	1	1
-18.75°	2	2	2	1	1	1	1	1	1	1	1
-20°	2	2	2	1	1	1	1	1	1	1	1
-21.25°	2	2	2	1	1	1	1	1	1	1	1



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	2	2	1	1	1	1	1	1	1	1
-23.75°	2	2	2	1	1	1	1	1	1	1	1
-25°	2	2	1	1	1	1	1	1	1	1	1
-26.25°	2	2	1	1	1	1	1	1	1	1	1
-27.5°	2	2	1	1	1	1	1	1	1	1	1
-28.75°	2	2	1	1	1	1	1	1	1	1	1
-30°	2	1	1	1	1	1	1	1	1	1	1
-31.25°	2	1	1	1	1	1	1	1	1	1	1
-32.5°	2	1	1	1	1	1	1	1	1	1	1
-33.75°	1	1	1	1	1	1	1	1	1	1	1
-35°	1	1	1	1	1	1	1	1	1	1	1
-36.25°	1	1	1	1	1	1	1	1	1	1	1
-37.5°	1	1	1	1	1	1	1	1	1	1	1
-38.75°	1	1	1	1	1	1	1	1	1	1	1
-40°	1	1	1	1	1	1	1	1	1	1	1
-41.25°	1	1	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	0
-51.25°	1	1	1	1	1	1	1	1	1	1	0
-52.5°	1	1	1	1	1	1	1	1	1	1	0
-53.75°	1	1	1	1	1	1	1	1	1	0	0
-55°	1	1	1	1	1	1	1	1	1	0	0
-56.25°	1	1	1	1	1	1	1	1	0	0	0
-57.5°	1	1	1	1	1	1	1	1	0	0	0
-58.75°	1	1	1	1	1	1	1	0	0	0	0
-60°	1	1	1	1	1	1	0	0	0	0	0
-61.25°	1	1	1	1	1	1	0	0	0	0	0
-62.5°	1	1	1	1	1	0	0	0	0	0	0
-63.75°	1	1	1	1	0	0	0	0	0	0	0
-65°	1	1	1	0	0	0	0	0	0	0	0
-66.25°	1	1	0	0	0	0	0	0	0	0	0
-67.5°	1	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	1	0	0	0	0	0	0	0	0	0	0
43.75°	1	0	0	0	0	0	0	0	0	0	0
42.5°	1	0	0	0	0	0	0	0	0	0	0
41.25°	1	0	0	0	0	0	0	0	0	0	0
40°	1	0	0	0	0	0	0	0	0	0	0
38.75°	1	1	0	0	0	0	0	0	0	0	0
37.5°	1	1	0	0	0	0	0	0	0	0	0
36.25°	1	1	0	0	0	0	0	0	0	0	0
35°	1	1	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	0	0	0	0	0	0	0	0	0
32.5°	1	1	1	0	0	0	0	0	0	0	0
31.25°	1	1	1	0	0	0	0	0	0	0	0
30°	1	1	1	0	0	0	0	0	0	0	0
28.75°	1	1	1	0	0	0	0	0	0	0	0
27.5°	1	1	1	0	0	0	0	0	0	0	0
26.25°	1	1	1	0	0	0	0	0	0	0	0
25°	1	1	1	0	0	0	0	0	0	0	0
23.75°	1	1	1	0	0	0	0	0	0	0	0
22.5°	1	1	1	0	0	0	0	0	0	0	0
21.25°	1	1	1	0	0	0	0	0	0	0	0
20°	1	1	1	1	0	0	0	0	0	0	0
18.75°	1	1	1	1	0	0	0	0	0	0	0
17.5°	1	1	1	1	0	0	0	0	0	0	0
16.25°	1	1	1	1	0	0	0	0	0	0	0
15°	1	1	1	1	0	0	0	0	0	0	0
13.75°	1	1	1	1	0	0	0	0	0	0	0
12.5°	1	1	1	1	0	0	0	0	0	0	0
11.25°	1	1	1	1	0	0	0	0	0	0	0
10°	1	1	1	1	0	0	0	0	0	0	0
8.75°	1	1	1	1	0	0	0	0	0	0	0
7.5°	1	1	1	1	0	0	0	0	0	0	0
6.25°	1	1	1	1	0	0	0	0	0	0	0
5°	1	1	1	1	0	0	0	0	0	0	0
3.75°	1	1	1	1	0	0	0	0	0	0	0
2.5°	1	1	1	1	0	0	0	0	0	0	0
1.25°	1	1	1	1	0	0	0	0	0	0	0
0°	1	1	1	1	0	0	0	0	0	0	0
-1.25°	1	1	1	1	0	0	0	0	0	0	0
-2.5°	1	1	1	1	0	0	0	0	0	0	0
-3.75°	1	1	1	1	0	0	0	0	0	0	0
-5°	1	1	1	1	0	0	0	0	0	0	0
-6.25°	1	1	1	1	0	0	0	0	0	0	0
-7.5°	1	1	1	1	0	0	0	0	0	0	0
-8.75°	1	1	1	1	0	0	0	0	0	0	0
-10°	1	1	1	1	0	0	0	0	0	0	0
-11.25°	1	1	1	1	0	0	0	0	0	0	0
-12.5°	1	1	1	1	0	0	0	0	0	0	0
-13.75°	1	1	1	1	0	0	0	0	0	0	0
-15°	1	1	1	1	0	0	0	0	0	0	0
-16.25°	1	1	1	1	0	0	0	0	0	0	0
-17.5°	1	1	1	1	0	0	0	0	0	0	0
-18.75°	1	1	1	1	0	0	0	0	0	0	0
-20°	1	1	1	1	0	0	0	0	0	0	0
-21.25°	1	1	1	0	0	0	0	0	0	0	0





REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	0	0	0	0	0	0	0	0
-23.75°	1	1	1	0	0	0	0	0	0	0	0
-25°	1	1	1	0	0	0	0	0	0	0	0
-26.25°	1	1	1	0	0	0	0	0	0	0	0
-27.5°	1	1	1	0	0	0	0	0	0	0	0
-28.75°	1	1	1	0	0	0	0	0	0	0	0
-30°	1	1	1	0	0	0	0	0	0	0	0
-31.25°	1	1	1	0	0	0	0	0	0	0	0
-32.5°	1	1	1	0	0	0	0	0	0	0	0
-33.75°	1	1	0	0	0	0	0	0	0	0	0
-35°	1	1	0	0	0	0	0	0	0	0	0
-36.25°	1	1	0	0	0	0	0	0	0	0	0
-37.5°	1	1	0	0	0	0	0	0	0	0	0
-38.75°	1	1	0	0	0	0	0	0	0	0	0
-40°	1	0	0	0	0	0	0	0	0	0	0
-41.25°	1	0	0	0	0	0	0	0	0	0	0
-42.5°	1	0	0	0	0	0	0	0	0	0	0
-43.75°	1	0	0	0	0	0	0	0	0	0	0
-45°	1	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: P220659 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)