

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220515

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-BK-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220515  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29472)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-BK-L2-UNV  
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS, SPOT OPTIC, BLACK HOUSING.  
Light Source: (1) 3000K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1071.6 lumens  
Efficiency: N/A  
Efficacy: 53.3 lumens/watt  
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220515

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-BK-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220515

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-BK-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	105	102	104	102	100	101	100	98	99	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	97	95	94	92
4	106	101	98	95	105	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	92	102	97	94	91	96	93	91	94	92	90	93	91	89	88
6	101	95	92	89	100	95	91	89	93	90	88	92	90	88	91	89	87	86
7	99	93	89	87	98	92	89	86	91	88	86	90	88	86	89	87	85	84
8	96	91	87	84	95	90	87	84	89	86	84	88	86	84	88	85	83	82
9	94	88	85	82	94	88	85	82	87	84	82	87	84	82	86	84	82	81
10	92	87	83	81	92	86	83	81	86	83	80	85	82	80	84	82	80	79

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2014268
5°	1543117
10°	647349
15°	273214
20°	177722
25°	77884
30°	10533
35°	3962
40°	2834
45°	2202
50°	1910
55°	1873
60°	1535
65°	1090
70°	449
75°	0
80°	0
85°	0



TEST NUMBER: P220515

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-BK-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	527.8	49.3
10°-20°	368.0	34.3
20°-30°	151.7	14.2
30°-40°	12.0	1.1
40°-50°	5.7	0.5
50°-60°	4.1	0.4
60°-70°	2.1	0.2
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1047.5	97.7
0°-40°	1059.4	98.9
0°-60°	1069.3	99.8
0°-90°	1071.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1071.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9186	
5°	7010	528
15°	1204	368
25°	322	152
35°	15	12
45°	7	6
55°	5	4
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220515

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-BK-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	9185.8
1°	9068.6
2°	8794.0
3°	8347.2
4°	7750.8
5°	7010.4
6°	6186.7
7°	5323.4
8°	4435.5
9°	3621.7
10°	2907.3
11°	2342.0
12°	1923.4
13°	1615.0
14°	1389.8
15°	1203.5
16°	1053.1
17°	955.0
18°	879.5
19°	813.1
20°	761.6
21°	714.3
22°	642.3
23°	544.2
24°	432.7
25°	321.9
26°	223.8
27°	134.1
28°	74.8
29°	50.1
30°	41.6
32.5°	26.8
35°	14.8
37.5°	11.3
40°	9.9
42.5°	8.5
45°	7.1
47.5°	6.4
50°	5.6
52.5°	4.9
55°	4.9
57.5°	4.2
60°	3.5
62.5°	2.8
65°	2.1



TEST NUMBER: P220515

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3097-S-BK-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.4
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)