

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220546

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED3590-F-BK-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220546  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29474)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED3590-F-BK-L2-UNV  
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS, FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 3500K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1316.7 lumens  
Efficiency: N/A  
Efficacy: 65.5 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220546

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3590-F-BK-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220546

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3590-F-BK-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	107	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89
4	103	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86
5	100	94	90	86	99	93	89	86	91	88	85	90	87	85	89	86	84	83
6	97	90	86	83	96	90	86	83	88	85	82	87	84	82	86	83	81	80
7	94	87	83	80	93	87	82	79	85	82	79	84	81	79	83	80	78	77
8	91	84	80	77	90	84	79	77	83	79	76	82	78	76	81	78	76	75
9	88	81	77	74	87	81	77	74	80	76	74	79	76	73	79	76	73	72
10	86	79	74	72	85	78	74	71	78	74	71	77	74	71	76	73	71	70

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	841950
5°	823815
10°	726061
15°	560979
20°	348397
25°	129080
30°	27017
35°	10172
40°	3693
45°	2512
50°	2217
55°	1835
60°	1403
65°	830
70°	513
75°	0
80°	0
85°	0



TEST NUMBER: P220546

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3590-F-BK-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	341.8	26.0
10°-20°	663.1	50.4
20°-30°	270.1	20.5
30°-40°	28.5	2.2
40°-50°	6.7	0.5
50°-60°	4.3	0.3
60°-70°	1.9	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1275.0	96.8
0°-40°	1303.5	99.0
0°-60°	1314.5	99.8
0°-90°	1316.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1316.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3840	
5°	3743	342
15°	2471	663
25°	534	270
35°	38	29
45°	8	7
55°	5	4
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220546

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3590-F-BK-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3839.6
1°	3829.9
2°	3818.5
3°	3808.0
4°	3787.0
5°	3742.6
6°	3681.9
7°	3602.7
8°	3501.7
9°	3386.9
10°	3260.8
11°	3122.6
12°	2975.5
13°	2821.9
14°	2653.7
15°	2471.1
16°	2285.1
17°	2079.0
18°	1886.6
19°	1686.2
20°	1493.0
21°	1304.6
22°	1105.0
23°	901.3
24°	708.1
25°	533.5
26°	382.3
27°	260.3
28°	172.2
29°	127.7
30°	106.7
32.5°	70.3
35°	38.0
37.5°	21.0
40°	12.9
42.5°	9.7
45°	8.1
47.5°	7.3
50°	6.5
52.5°	5.7
55°	4.8
57.5°	4.0
60°	3.2
62.5°	2.4
65°	1.6



TEST NUMBER: P220546

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3590-F-BK-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.6
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)