

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220685

Luminaire Tested: **1003-[A1, S1, SU1]-FL-LED3090-F-BK-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220685
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29478)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-FL-LED3090-F-BK-L2-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, FLUSH LENS, FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1426.2 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 20.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220685

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-F-BK-L2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220685

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-F-BK-L2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	104	103	101	100	99	98	98	96
2	110	107	103	101	108	105	102	100	102	99	97	99	97	95	96	95	93	92
3	107	101	98	94	105	100	97	94	98	95	92	95	93	91	93	91	89	88
4	103	97	93	89	101	96	92	89	94	90	88	92	89	87	90	88	86	85
5	99	93	88	85	98	92	88	85	90	87	84	89	86	83	87	85	82	81
6	96	89	84	81	95	88	84	81	87	83	80	86	82	80	84	82	79	78
7	93	85	81	78	91	85	81	77	84	80	77	83	79	77	82	79	76	75
8	90	82	78	75	89	82	77	74	81	77	74	80	76	74	79	76	74	72
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70
10	84	77	72	69	83	76	72	69	75	72	69	75	71	69	74	71	69	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	840174
5°	815274
10°	720762
15°	553488
20°	344523
25°	194261
30°	73758
35°	15821
40°	6154
45°	1985
50°	1637
55°	1223
60°	1053
65°	1245
70°	1026
75°	1356
80°	1010
85°	0



TEST NUMBER: P220685

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-F-BK-L2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	339.0	23.8
10°-20°	654.2	45.9
20°-30°	364.8	25.6
30°-40°	55.1	3.9
40°-50°	6.1	0.4
50°-60°	3.1	0.2
60°-70°	2.1	0.1
70°-80°	1.4	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1358.1	95.2
0°-40°	1413.2	99.1
0°-60°	1422.5	99.7
0°-90°	1426.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1426.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3832	
5°	3704	339
15°	2438	654
25°	803	365
35°	59	55
45°	6	6
55°	3	3
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P220685

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-F-BK-L2-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	3831.5
1°	3817.9
2°	3795.6
3°	3772.5
4°	3742.9
5°	3703.8
6°	3651.1
7°	3575.3
8°	3478.0
9°	3363.0
10°	3237.0
11°	3095.7
12°	2942.5
13°	2783.7
14°	2613.7
15°	2438.1
16°	2248.1
17°	2051.8
18°	1852.3
19°	1661.6
20°	1476.4
21°	1304.8
22°	1153.2
23°	1025.5
24°	914.6
25°	802.9
26°	693.5
27°	587.4
28°	484.4
29°	385.5
30°	291.3
32.5°	116.5
35°	59.1
37.5°	36.7
40°	21.5
42.5°	8.0
45°	6.4
47.5°	4.8
50°	4.8
52.5°	4.0
55°	3.2
57.5°	3.2
60°	2.4
62.5°	2.4
65°	2.4



TEST NUMBER: P220685

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3090-F-BK-L2-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)