

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P29555

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED CB-M-BK-LC2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P29555
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LEDCEB-M-BK-LC2-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS,
MEDIUM FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) COLOR CHAGING MODULE, SET TO 3500K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 570.1 lumens
Efficiency: N/A
Efficacy: 23.6 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.49
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 24.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P29555

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LEDCB-M-BK-LC2-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P29555

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LEDCB-M-BK-LC2-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	90	89	88
5	101	96	92	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85
6	98	92	88	85	97	92	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	81	79	77	76
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	79	77	75	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	491189
5°	460928
10°	359601
15°	243815
20°	129045
25°	34115
30°	6583
35°	3212
40°	1718
45°	1240
50°	1023
55°	765
60°	877
65°	519
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P29555

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LEDCEB-M-BK-LC2-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.9	32.3
10°-20°	288.9	50.7
20°-30°	82.7	14.5
30°-40°	8.4	1.5
40°-50°	3.2	0.6
50°-60°	2.1	0.4
60°-70°	1.0	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	555.5	97.4
0°-40°	563.9	98.9
0°-60°	569.1	99.8
0°-90°	570.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	570.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2240	
5°	2094	184
15°	1074	289
25°	141	83
35°	12	8
45°	4	3
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P29555

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LEDCEB-M-BK-LC2-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2240
1°	2235
2°	2215
3°	2189
4°	2151
5°	2094
6°	2020
7°	1931
8°	1830
9°	1724
10°	1615
11°	1504
12°	1393
13°	1284
14°	1178
15°	1074
16°	968
17°	862
18°	758
19°	655
20°	553
21°	455
22°	364
23°	279
24°	205
25°	141
26°	92
27°	57
28°	39
29°	31
30°	26
32.5°	19
35°	12
37.5°	8
40°	6
42.5°	5
45°	4
47.5°	3
50°	3
52.5°	3
55°	2
57.5°	2
60°	2
62.5°	1
65°	1



TEST NUMBER: P29555

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED CB-M-BK-LC2-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1
70°	0
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)