

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P221181

Luminaire Tested: **1003-[A1, S1, SU1]-FL-LEDCW-W-BK-LC2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P221181  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29561)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 1003-[A1, S1, SU1]-FL-LEDCW-W-BK-LC2-UNV  
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, FLUSH LENS, WIDE FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) WARM DIMMING MODULE, SET TO 3500K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 658.0 lumens  
Efficiency: N/A  
Efficacy: 27.4 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 24  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P221181

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LEDCW-W-BK-LC2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P221181

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LEDCW-W-BK-LC2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84
4	100	93	88	84	98	92	87	83	90	86	83	88	84	82	86	83	81	79
5	95	88	82	79	94	87	82	78	85	81	78	83	80	77	82	79	76	75
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	216255
5°	214021
10°	204583
15°	191919
20°	167688
25°	125886
30°	76037
35°	33970
40°	7385
45°	1830
50°	1706
55°	1529
60°	1754
65°	2075
70°	1923
75°	847
80°	0
85°	0



TEST NUMBER: P221181

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LEDCW-W-BK-LC2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.0	13.8
10°-20°	233.8	35.5
20°-30°	232.8	35.4
30°-40°	85.4	13.0
40°-50°	6.8	1.0
50°-60°	3.7	0.6
60°-70°	3.6	0.5
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	557.6	84.7
0°-40°	643.0	97.7
0°-60°	653.5	99.3
0°-90°	658.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	658.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	986	
5°	972	91
15°	845	234
25°	520	233
35°	127	85
45°	6	7
55°	4	4
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P221181

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LEDCW-W-BK-LC2-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	986.2
1°	983.2
2°	980.2
3°	977.3
4°	976.3
5°	972.3
6°	967.3
7°	956.4
8°	944.5
9°	928.7
10°	918.8
11°	906.9
12°	893.0
13°	878.1
14°	863.3
15°	845.4
16°	825.6
17°	800.8
18°	775.1
19°	747.3
20°	718.6
21°	686.9
22°	651.2
23°	610.5
24°	566.9
25°	520.3
26°	472.8
27°	426.2
28°	380.6
29°	339.0
30°	300.3
32.5°	216.1
35°	126.9
37.5°	60.5
40°	25.8
42.5°	9.9
45°	5.9
47.5°	5.0
50°	5.0
52.5°	4.0
55°	4.0
57.5°	4.0
60°	4.0
62.5°	4.0
65°	4.0



TEST NUMBER: P221181

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LEDCW-W-BK-LC2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	3.0
70°	3.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)