

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P247016

Luminaire Tested: **203-SS-8LED2725-12-BK**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247016  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-5)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 203-SS-8LED2725-12-BK  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD BLACK  
Light Source: (1) SORAA 2700K 95 CRI 25°NFL LED SM16-07-25D-927-03  
Ballast/Driver: CHROMA POWER SUPPLY IN0004

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 341.6 lumens  
Efficiency: N/A  
Efficacy: 43.2 lumens/watt  
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.33  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247016

CATALOG NUMBER: 203-SS-8LED2725-12-BK

### Luminous Intensity Polar Plot





TEST NUMBER: P247016

CATALOG NUMBER: 203-SS-8LED2725-12-BK

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105		104	103	102		100	100	99	97
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		98	97	96	95
3	109	104	101	98	107	103	100	98	101	98	96		98	96	95		96	95	93	92
4	106	101	97	94	104	100	96	94	98	95	93		96	94	92		94	92	91	90
5	103	97	94	91	102	97	93	91	95	92	90		94	91	89		92	90	88	87
6	100	95	91	88	99	94	90	88	93	90	87		91	89	87		90	88	86	85
7	98	92	88	85	97	91	88	85	90	87	85		89	87	84		88	86	84	83
8	96	90	86	83	95	89	86	83	88	85	83		87	85	82		87	84	82	81
9	93	87	84	81	93	87	83	81	86	83	81		85	83	81		85	82	80	79
10	91	85	82	79	91	85	81	79	84	81	79		84	81	79		83	81	79	78

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1152584
5°	920052
10°	507654
15°	245279
20°	120287
25°	50682
30°	11451
35°	4397
40°	2383
45°	1256
50°	691
55°	774
60°	888
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P247016

CATALOG NUMBER: 203-SS-8LED2725-12-BK

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.2	43.7
10°-20°	139.7	40.9
20°-30°	44.9	13.1
30°-40°	5.4	1.6
40°-50°	1.5	0.4
50°-60°	0.8	0.2
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	333.8	97.7
0°-40°	339.2	99.3
0°-60°	341.5	100.0
0°-90°	341.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	341.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2336	
5°	1858	149
15°	480	140
25°	93	45
35°	7	5
45°	2	1
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P247016

CATALOG NUMBER: 203-SS-8LED2725-12-BK

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2336.1
1°	2304.1
2°	2236.6
3°	2138.9
4°	2009.3
5°	1857.7
6°	1693.4
7°	1523.6
8°	1349.2
9°	1177.6
10°	1013.3
12.5°	681.0
15°	480.2
17.5°	340.5
20°	229.1
22.5°	147.9
25°	93.1
27.5°	46.6
30°	20.1
32.5°	11.9
35°	7.3
37.5°	4.6
40°	3.7
42.5°	2.7
45°	1.8
47.5°	0.9
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)