

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P246986

Luminaire Tested: **203-SS-8LED3036-12-BK-LVR**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246986
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-34)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED3036-12-BK-LVR
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD BLACK, HEX CELL LOUVER
Light Source: (1) SORAA 3000K 95 CRI LED
SM16-07-36D-930-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 223.4 lumens
Efficiency: N/A
Efficacy: 28.6 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.48
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246986
CATALOG NUMBER: 203-SS-8LED3036-12-BK-LVR

Luminous Intensity Polar Plot





TEST NUMBER: P246986

CATALOG NUMBER: 203-SS-8LED3036-12-BK-LVR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94		97	95	93		95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91		94	92	90		92	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87		91	89	86		90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84		89	86	84		88	85	83	82
7	96	89	85	82	94	89	85	82	87	84	81		86	83	81		85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79		84	81	79		83	80	78	77
9	90	84	80	77	89	83	79	77	83	79	77		82	79	76		81	78	76	75
10	88	81	77	75	87	81	77	75	80	77	74		80	76	74		79	76	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	435605
5°	393834
10°	314873
15°	211005
20°	108001
25°	35712
30°	10084
35°	4276
40°	2254
45°	1256
50°	691
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246986

CATALOG NUMBER: 203-SS-8LED3036-12-BK-LVR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.7	31.6
10°-20°	111.0	49.7
20°-30°	35.2	15.8
30°-40°	5.0	2.2
40°-50°	1.4	0.6
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	216.9	97.1
0°-40°	221.9	99.3
0°-60°	223.4	100.0
0°-90°	223.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	223.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	883	
5°	795	71
15°	413	111
25°	66	35
35°	7	5
45°	2	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246986

CATALOG NUMBER: 203-SS-8LED3036-12-BK-LVR

CANDELA DISTRIBUTION (FULL):

	0°
0°	882.9
1°	873.2
2°	855.5
3°	836.0
4°	816.5
5°	795.2
6°	770.4
7°	742.0
8°	706.5
9°	668.4
10°	628.5
11°	585.1
12°	539.9
13°	496.4
14°	453.9
15°	413.1
16°	372.3
17°	330.7
18°	288.1
19°	246.4
20°	205.7
21°	168.4
22°	136.5
23°	109.0
24°	84.2
25°	65.6
26°	51.4
27°	38.1
28°	30.1
29°	22.2
30°	17.7
32.5°	10.6
35°	7.1
37.5°	4.4
40°	3.5
42.5°	2.7
45°	1.8
47.5°	0.9
50°	0.9
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0



TEST NUMBER: P246986

CATALOG NUMBER: 203-SS-8LED3036-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)