

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P246955

Luminaire Tested: **203-FL-8LED3025-12-BK**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246955
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-FL-8LED3025-12-BK
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 25 DEGREE NARROW OPTIC, FLUSH HOOD BLACK
Light Source: (1) SORAA 3000K 90 CRI 25° NFL LED
SM16-07-25D-930-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 369.8 lumens
Efficiency: N/A
Efficacy: 47.4 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.33
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246955
CATALOG NUMBER: 203-FL-8LED3025-12-BK

Luminous Intensity Polar Plot





TEST NUMBER: P246955

CATALOG NUMBER: 203-FL-8LED3025-12-BK

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	107	107	105	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		97	96	95	93
3	108	103	99	96	106	102	98	96	99	96	94		97	95	93		95	93	91	90
4	104	99	95	92	103	98	94	92	96	93	91		94	92	90		92	90	89	87
5	101	96	91	88	100	95	91	88	93	90	87		92	89	87		90	88	86	85
6	99	92	88	85	97	92	88	85	90	87	85		89	86	84		88	85	84	82
7	96	90	86	83	95	89	85	82	88	85	82		87	84	82		86	83	81	80
8	94	87	83	80	93	87	83	80	86	82	80		85	82	80		84	81	79	78
9	91	85	81	78	90	84	81	78	84	80	78		83	80	78		82	79	77	76
10	89	83	79	76	88	82	79	76	82	78	76		81	78	76		80	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1176562
5°	939120
10°	519628
15°	250846
20°	122388
25°	51172
30°	20680
35°	11203
40°	6827
45°	4954
50°	4068
55°	3785
60°	3454
65°	3152
70°	2597
75°	1716
80°	0
85°	0



TEST NUMBER: P246955

CATALOG NUMBER: 203-FL-8LED3025-12-BK

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	41.5
10°-20°	143.0	38.7
20°-30°	47.9	12.9
30°-40°	12.5	3.4
40°-50°	5.6	1.5
50°-60°	3.7	1.0
60°-70°	2.7	0.7
70°-80°	1.2	0.3
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	344.2	93.1
0°-40°	356.7	96.4
0°-60°	366.0	99.0
0°-90°	369.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	369.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2385	
5°	1896	153
15°	491	143
25°	94	48
35°	19	12
45°	7	6
55°	4	4
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P246955

CATALOG NUMBER: 203-FL-8LED3025-12-BK

CANDELA DISTRIBUTION (FULL):

	0°
0°	2384.7
2.5°	2238.4
5°	1896.2
7.5°	1468.9
10°	1037.2
12.5°	696.8
15°	491.1
17.5°	349.3
20°	233.1
22.5°	148.9
25°	94.0
27.5°	58.5
30°	36.3
32.5°	23.9
35°	18.6
37.5°	15.1
40°	10.6
42.5°	8.0
45°	7.1
47.5°	6.2
50°	5.3
52.5°	4.4
55°	4.4
57.5°	3.5
60°	3.5
62.5°	2.7
65°	2.7
67.5°	2.7
70°	1.8
72.5°	1.8
75°	0.9
77.5°	0.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)