

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P247032

Luminaire Tested: **213-8LED2736-12-CS-DIFF**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247032  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-44)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 213-8LED2736-12-CS-DIFF  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 36 DEGREE WIDE OPTIC,  
REGRESSED HOOD SILVER, DIFFUSED LENS  
Light Source: (1) SORAA 2700K 90 CRI LED  
SM16-07-36D-927-03  
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4000.0 lumens  
Efficiency: N/A  
Efficacy: 519.5 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.65  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247032  
CATALOG NUMBER: 213-8LED2736-12-CS-DIFF

### Luminous Intensity Polar Plot





TEST NUMBER: P247032  
 CATALOG NUMBER: 213-8LED2736-12-CS-DIFF

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20								20
RC	80					70					50								0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		0
RCR																			
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		100
1	114	111	109	107		111	109	107	105		105	103	102		101	100	99		94
2	109	104	100	97		107	102	99	96		99	96	94		96	94	92		89
3	104	98	93	90		102	97	92	89		94	90	87		92	89	86		83
4	99	92	87	83		97	91	86	83		89	85	82		87	84	81		79
5	95	87	82	78		93	86	81	78		85	80	77		83	79	76		74
6	91	83	77	73		89	82	77	73		80	76	73		79	75	72		70
7	87	79	73	69		86	78	73	69		77	72	69		76	71	68		67
8	83	75	69	66		82	74	69	66		73	69	65		72	68	65		63
9	80	71	66	62		79	71	66	62		70	65	62		69	65	62		60
10	77	68	63	59		76	68	63	59		67	62	59		66	62	59		58

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3688555
5°	3584673
10°	3230589
15°	2700464
20°	2017007
25°	1337388
30°	805735
35°	439201
40°	230059
45°	135432
50°	91417
55°	64514
60°	43417
65°	34323
70°	42411
75°	28022
80°	41767
85°	0



TEST NUMBER: P247032  
 CATALOG NUMBER: 213-8LED2736-12-CS-DIFF

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	665.8	16.6
10°-20°	1443.9	36.1
20°-30°	1127.1	28.2
30°-40°	482.1	12.1
40°-50°	159.0	4.0
50°-60°	68.2	1.7
60°-70°	34.5	0.9
70°-80°	17.5	0.4
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3236.8	80.9
0°-40°	3718.9	93.0
0°-60°	3946.1	98.7
0°-90°	4000.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4000.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7476	
5°	7238	666
15°	5287	1444
25°	2457	1127
35°	729	482
45°	194	159
55°	75	68
65°	29	34
75°	15	17
85°	0	2
90°	0	



TEST NUMBER: P247032  
CATALOG NUMBER: 213-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7476.1
1°	7430.4
2°	7401.0
3°	7357.0
4°	7311.3
5°	7237.9
6°	7133.5
7°	6999.7
8°	6849.7
9°	6657.2
10°	6448.4
11°	6224.9
12°	6016.1
13°	5777.9
14°	5539.8
15°	5286.9
16°	5017.8
17°	4735.5
18°	4437.0
19°	4154.8
20°	3841.6
21°	3530.0
22°	3231.5
23°	2964.0
24°	2694.8
25°	2456.7
26°	2218.5
27°	1995.0
28°	1786.2
29°	1593.7
30°	1414.3
32.5°	1013.0
35°	729.2
37.5°	522.0
40°	357.2
42.5°	252.8
45°	194.1
47.5°	148.4
50°	119.1
52.5°	89.7
55°	75.0
57.5°	60.4
60°	44.0
62.5°	44.0
65°	29.4



TEST NUMBER: P247032  
CATALOG NUMBER: 213-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	29.4
70°	29.4
72.5°	14.7
75°	14.7
77.5°	14.7
80°	14.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)