

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P246968

Luminaire Tested: **213-8LED3010-12-BK-OSL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246968
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-27)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 213-8LED3010-12-BK-OSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD BLACK, OVERALL SPREAD LENS
Light Source: (1) SORAA 3000K 95 CRI 10°NSP LED
SM16-07-10D-930-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4000.0 lumens
Efficiency: N/A
Efficacy: 500.0 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246968
CATALOG NUMBER: 213-8LED3010-12-BK-OSL

Luminous Intensity Polar Plot





TEST NUMBER: P246968
 CATALOG NUMBER: 213-8LED3010-12-BK-OSL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	95
3	109	104	101	98	107	103	100	98	101	98	96	98	96	95	96	95	93	92
4	106	101	97	94	104	100	96	94	98	95	93	96	94	92	94	92	91	90
5	103	98	94	91	102	97	93	91	95	92	90	94	91	89	92	90	89	88
6	101	95	91	88	99	94	91	88	93	90	88	92	89	87	91	88	87	86
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	86	83	81	80
10	92	86	83	80	91	86	82	80	85	82	80	85	82	80	84	82	80	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	11742483
5°	11718495
10°	7484100
15°	2403086
20°	602855
25°	274261
30°	175469
35°	135097
40°	99701
45°	78217
50°	53346
55°	36644
60°	14012
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246968
 CATALOG NUMBER: 213-8LED3010-12-BK-OSL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1959.6	49.0
10°-20°	1517.6	37.9
20°-30°	259.8	6.5
30°-40°	138.0	3.4
40°-50°	86.0	2.2
50°-60°	37.2	0.9
60°-70°	1.7	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3737.0	93.4
0°-40°	3875.0	96.9
0°-60°	3998.3	100.0
0°-90°	4000.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4000.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23800	
5°	23661	###
15°	4705	1518
25°	504	260
35°	224	138
45°	112	86
55°	43	37
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246968
CATALOG NUMBER: 213-8LED3010-12-BK-OSL

CANDELA DISTRIBUTION (FULL):

	0°
0°	23800.1
1°	23912.2
2°	24193.3
3°	24403.4
4°	24277.0
5°	23661.1
6°	22541.4
7°	20987.3
8°	19082.7
9°	17065.9
10°	14938.6
12.5°	9491.6
15°	4704.7
17.5°	2072.0
20°	1148.2
22.5°	728.1
25°	503.8
27.5°	377.5
30°	308.0
32.5°	252.7
35°	224.3
37.5°	181.6
40°	154.8
42.5°	126.3
45°	112.1
47.5°	97.9
50°	69.5
52.5°	55.3
55°	42.6
57.5°	28.4
60°	14.2
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)