Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1527712

Luminaire Tested: 14CGTX-42-B2750-W2A-4000K

Issue Date: 8/26/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1527712
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2510-581-3)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	8/26/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	14CGTX-42-B2750-W2A-4000K
Description:	1X4 4200 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 4000K CCT WITH FROSTED SMOOTH L
Light Source:	4000K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3961.0 lumens
Efficiency:	N/A
Efficacy:	96.4 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.26 / 1.38
Luminous Opening:	Rectangular (W 2' x L: 4' x H: 0')
CIE Type:	Direct

Input Watts (W):	41.1
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527712
CATALOG NUMBER: 14CGTX-42-B2750-W2A-4000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527712
CATALOG NUMBER: 14CGTX-42-B2750-W2A-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	44	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	34	32
8	60	46	37	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	26	37	30	25	36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1812	1812	1812
5°	1814	1806	1817
10°	1813	1807	1814
15°	1806	1803	1812
20°	1799	1796	1802
25°	1791	1787	1792
30°	1783	1777	1777
35°	1769	1763	1761
40°	1758	1749	1743
45°	1739	1732	1716
50°	1722	1711	1701
55°	1696	1688	1670
60°	1663	1653	1634
65°	1638	1612	1577
70°	1584	1560	1513
75°	1534	1491	1455
80°	1443	1404	1350
85°	1306	1243	1212

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
Vertical Angle: 45°
Luminance: 1741 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527712
CATALOG NUMBER: 14CGTX-42-B2750-W2A-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.6	3.2
10°-20°	366.2	9.2
20°-30°	556.0	14.0
30°-40°	672.4	17.0
40°-50°	702.1	17.7
50°-60°	642.1	16.2
60°-70°	500.6	12.6
70°-80°	302.9	7.6
80°-90°	91.2	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1049.8	26.5
0°-40°	1722.3	43.5
0°-60°	3066.4	77.4
0°-90°	3961.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3961.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1347	1347	1347	1347	1347	
5°	1343	1342	1337	1345	1345	128
15°	1297	1298	1295	1301	1301	366
25°	1206	1206	1204	1209	1207	556
35°	1077	1076	1073	1074	1072	674
45°	914	915	910	908	902	705
55°	723	724	720	714	712	646
65°	514	512	506	501	495	507
75°	295	293	287	281	280	311
85°	85	84	80	78	78	95
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527712
CATALOG NUMBER: 14CGTX-42-B2750-W2A-4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.0	1347.0	1347.0	1347.0	*1347.0*
2.5°	*1346.0*	*1345.0*	*1341.0*	*1346.0*	*1349.0*
5°	1343.0	1342.0	1336.9	1345.0	*1345.0*
7.5°	1335.9	1335.9	1332.9	1336.9	*1337.9*
10°	1326.9	1325.9	1322.8	1327.9	*1327.9*
12.5°	1311.8	1312.8	1309.7	1315.8	*1316.8*
15°	1296.7	1297.7	1294.6	1300.7	*1300.7*
17.5°	1278.5	1279.5	1275.5	1281.6	*1281.6*
20°	1256.4	1256.4	1254.4	1258.4	*1258.4*
22.5°	1233.2	1233.2	1231.2	1234.2	*1236.3*
25°	1206.1	1206.1	1204.0	1209.1	*1207.1*
27.5°	1177.9	1177.9	1174.8	1178.9	*1179.9*
30°	1147.7	1145.7	1143.6	1145.7	*1143.6*
32.5°	1114.4	1112.4	1109.4	1111.4	*1110.4*
35°	1077.2	1076.2	1073.2	1074.2	*1072.2*
37.5°	1038.9	1037.9	1035.9	1035.9	*1032.9*
40°	1000.7	999.7	995.6	994.6	*992.6*
42.5°	956.4	956.4	955.4	951.4	*949.3*
45°	914.1	915.1	910.1	908.1	*902.0*
47.5°	868.8	868.8	864.8	860.7	*858.7*
50°	822.5	821.5	817.5	813.4	*812.4*
52.5°	772.2	775.2	768.1	766.1	*761.1*
55°	722.8	723.8	719.8	713.8	*711.8*
57.5°	672.5	672.5	667.5	662.4	*658.4*
60°	618.1	621.1	614.1	609.1	*607.1*
62.5°	565.8	566.8	561.8	554.7	*549.7*
65°	514.4	512.4	506.4	501.3	*495.3*
67.5°	458.1	458.1	452.0	446.0	*442.0*
70°	402.7	401.7	396.6	388.6	*384.6*
72.5°	349.3	346.3	341.3	334.2	*333.2*
75°	295.0	293.0	286.9	280.9	*279.9*
77.5°	239.6	237.6	232.6	227.5	*225.5*
80°	186.2	186.2	181.2	176.2	*174.2*
82.5°	134.9	132.9	128.9	126.8	*123.8*
85°	84.6	83.6	80.5	77.5	*78.5*
87.5°	37.2	36.2	34.2	32.2	*32.2*
90°	0.0	0.0	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1527712
CATALOG NUMBER: 14CGTX-42-B2750-W2A-4000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.05	15.71	14.42	16.02	16.34	13.94	15.60	14.30	15.91	16.22
	3H	15.98	17.49	16.36	17.81	18.17	15.81	17.32	16.19	17.64	18.00
	4H	16.75	18.17	17.15	18.52	18.89	16.55	17.97	16.94	18.31	18.69
	6H	17.35	18.66	17.76	19.03	19.42	17.11	18.43	17.52	18.79	19.18
	8H	17.55	18.81	17.98	19.20	19.60	17.30	18.56	17.72	18.95	19.35
	12H	17.70	18.91	18.13	19.29	19.72	17.43	18.64	17.86	19.02	19.45
4H	2H	14.70	16.12	15.10	16.47	16.85	14.62	16.04	15.01	16.38	16.76
	3H	16.87	18.06	17.28	18.46	18.86	16.72	17.91	17.13	18.31	18.71
	4H	17.77	18.86	18.20	19.27	19.70	17.59	18.67	18.02	19.08	19.52
	6H	18.51	19.46	18.96	19.90	20.35	18.28	19.23	18.74	19.67	20.13
	8H	18.78	19.66	19.23	20.11	20.57	18.53	19.42	18.99	19.86	20.32
	12H	18.98	19.78	19.45	20.25	20.72	18.71	19.51	19.19	19.99	20.46
8H	4H	18.11	19.00	18.57	19.44	19.91	17.95	18.84	18.41	19.28	19.75
	6H	18.99	19.73	19.48	20.22	20.69	18.79	19.53	19.28	20.01	20.49
	8H	19.34	20.01	19.85	20.51	21.00	19.11	19.78	19.62	20.28	20.77
	12H	19.63	20.22	20.13	20.71	21.27	19.38	19.97	19.88	20.46	21.02
12H	4H	18.16	18.96	18.64	19.43	19.90	18.00	18.80	18.48	19.28	19.75
	6H	19.06	19.73	19.57	20.23	20.72	18.87	19.53	19.37	20.04	20.52
	8H	19.47	20.06	19.98	20.55	21.11	19.26	19.85	19.76	20.34	20.89

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2505-441-9-R2

Test Date: 06/12/2025

Luminaire Tested: 24CGTX-55-B2750-W2A-4000K

Data in this report applies to families of products including 24CGTX

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2505-441-9-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-55-B2750-W2A-4000K**
Description:	*THIS IS A REVISION OF REPORT SP1-2504-441-9-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 5500 LUMEN CGTX AT 4.0V

Spectral Parameters

CCT (K):	4011
CIE u':	0.2325
CIE v':	0.4849
Duv:	-0.0134
CIE x:	0.3712
CIE y:	0.3440
CIE z:	0.2848
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	593
Purity:	14.59231
Rf:	88.3
Rg:	97.6

CRI (Ra):	88.2
R1:	91.9
R2:	87.7
R3:	86.7
R4:	92.6
R5:	90.4
R6:	81.2
R7:	85.8
R8:	89.2
R9:	89.9
R10:	76.6
R11:	93.9
R12:	70.9
R13:	89.9
R14:	94.3
R15:	92.5




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2024	6/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2505-441-9-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4011K
CIE x = 0.3712
CIE y = 0.3440
Duv = -0.0134

Point lies outside the range

REPORT NUMBER: SP1-2505-441-9-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	244	NR	620	332	NR	750	7	NR	880	0	NR
365	0	NR	495	224	NR	625	331	NR	755	6	NR	885	0	NR
370	0	NR	500	212	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	213	NR	635	647	NR	765	5	NR	895	0	NR
380	0	NR	510	218	NR	640	217	NR	770	4	NR	900	0	NR
385	0	NR	515	221	NR	645	208	NR	775	3	NR	905	0	NR
390	1	NR	520	225	NR	650	180	NR	780	3	NR	910	0	NR
395	2	NR	525	228	NR	655	152	NR	785	2	NR	915	0	NR
400	3	NR	530	232	NR	660	130	NR	790	2	NR	920	0	NR
405	4	NR	535	237	NR	665	109	NR	795	2	NR	925	0	NR
410	6	NR	540	243	NR	670	100	NR	800	2	NR	930	0	NR
415	10	NR	545	251	NR	675	82	NR	805	1	NR	935	0	NR
420	19	NR	550	259	NR	680	70	NR	810	1	NR	940	0	NR
425	35	NR	555	269	NR	685	60	NR	815	1	NR	945	0	NR
430	62	NR	560	281	NR	690	51	NR	820	1	NR	950	0	NR
435	106	NR	565	293	NR	695	44	NR	825	1	NR	955	0	NR
440	177	NR	570	305	NR	700	37	NR	830	1	NR	960	0	NR
445	307	NR	575	316	NR	705	32	NR	835	1	NR	965	0	NR
450	406	NR	580	327	NR	710	27	NR	840	1	NR	970	0	NR
455	313	NR	585	335	NR	715	23	NR	845	0	NR	975	0	NR
460	252	NR	590	339	NR	720	20	NR	850	0	NR	980	0	NR
465	303	NR	595	338	NR	725	17	NR	855	0	NR	985	0	NR
470	387	NR	600	339	NR	730	14	NR	860	0	NR	990	0	NR
475	416	NR	605	338	NR	735	12	NR	865	0	NR	995	0	NR
480	350	NR	610	359	NR	740	10	NR	870	0	NR	1000	0	NR
485	279	NR	615	375	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-9-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 2.01**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	244	NR	620	332	NR	750	7	NR	880	0	NR
365	0	NR	495	224	NR	625	331	NR	755	6	NR	885	0	NR
370	0	NR	500	212	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	213	NR	635	647	NR	765	5	NR	895	0	NR
380	0	NR	510	218	NR	640	217	NR	770	4	NR	900	0	NR
385	0	NR	515	221	NR	645	208	NR	775	3	NR	905	0	NR
390	1	NR	520	225	NR	650	180	NR	780	3	NR	910	0	NR
395	2	NR	525	228	NR	655	152	NR	785	2	NR	915	0	NR
400	3	NR	530	232	NR	660	130	NR	790	2	NR	920	0	NR
405	4	NR	535	237	NR	665	109	NR	795	2	NR	925	0	NR
410	6	NR	540	243	NR	670	100	NR	800	2	NR	930	0	NR
415	10	NR	545	251	NR	675	82	NR	805	1	NR	935	0	NR
420	19	NR	550	259	NR	680	70	NR	810	1	NR	940	0	NR
425	35	NR	555	269	NR	685	60	NR	815	1	NR	945	0	NR
430	62	NR	560	281	NR	690	51	NR	820	1	NR	950	0	NR
435	106	NR	565	293	NR	695	44	NR	825	1	NR	955	0	NR
440	177	NR	570	305	NR	700	37	NR	830	1	NR	960	0	NR
445	307	NR	575	316	NR	705	32	NR	835	1	NR	965	0	NR
450	406	NR	580	327	NR	710	27	NR	840	1	NR	970	0	NR
455	313	NR	585	335	NR	715	23	NR	845	0	NR	975	0	NR
460	252	NR	590	339	NR	720	20	NR	850	0	NR	980	0	NR
465	303	NR	595	338	NR	725	17	NR	855	0	NR	985	0	NR
470	387	NR	600	339	NR	730	14	NR	860	0	NR	990	0	NR
475	416	NR	605	338	NR	735	12	NR	865	0	NR	995	0	NR
480	350	NR	610	359	NR	740	10	NR	870	0	NR	1000	0	NR
485	279	NR	615	375	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-9-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 4.55**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	244	NR	620	332	NR	750	7	NR	880	0	NR
365	0	NR	495	224	NR	625	331	NR	755	6	NR	885	0	NR
370	0	NR	500	212	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	213	NR	635	647	NR	765	5	NR	895	0	NR
380	0	NR	510	218	NR	640	217	NR	770	4	NR	900	0	NR
385	0	NR	515	221	NR	645	208	NR	775	3	NR	905	0	NR
390	1	NR	520	225	NR	650	180	NR	780	3	NR	910	0	NR
395	2	NR	525	228	NR	655	152	NR	785	2	NR	915	0	NR
400	3	NR	530	232	NR	660	130	NR	790	2	NR	920	0	NR
405	4	NR	535	237	NR	665	109	NR	795	2	NR	925	0	NR
410	6	NR	540	243	NR	670	100	NR	800	2	NR	930	0	NR
415	10	NR	545	251	NR	675	82	NR	805	1	NR	935	0	NR
420	19	NR	550	259	NR	680	70	NR	810	1	NR	940	0	NR
425	35	NR	555	269	NR	685	60	NR	815	1	NR	945	0	NR
430	62	NR	560	281	NR	690	51	NR	820	1	NR	950	0	NR
435	106	NR	565	293	NR	695	44	NR	825	1	NR	955	0	NR
440	177	NR	570	305	NR	700	37	NR	830	1	NR	960	0	NR
445	307	NR	575	316	NR	705	32	NR	835	1	NR	965	0	NR
450	406	NR	580	327	NR	710	27	NR	840	1	NR	970	0	NR
455	313	NR	585	335	NR	715	23	NR	845	0	NR	975	0	NR
460	252	NR	590	339	NR	720	20	NR	850	0	NR	980	0	NR
465	303	NR	595	338	NR	725	17	NR	855	0	NR	985	0	NR
470	387	NR	600	339	NR	730	14	NR	860	0	NR	990	0	NR
475	416	NR	605	338	NR	735	12	NR	865	0	NR	995	0	NR
480	350	NR	610	359	NR	740	10	NR	870	0	NR	1000	0	NR
485	279	NR	615	375	NR	745	9	NR	875	0	NR			


REPORT NUMBER: SP1-2505-441-9-R2

TM-30-18


Summary


R_f = 88.3
R_g = 97.6
CIE R_a = 88.2
R_9 = 89.9


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2505-441-9-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 93	CES51 = 89	CES76 = 88
CES02 = 62	CES27 = 84	CES52 = 92	CES77 = 80
CES03 = 32	CES28 = 95	CES53 = 86	CES78 = 88
CES04 = 70	CES29 = 86	CES54 = 85	CES79 = 83
CES05 = 49	CES30 = 80	CES55 = 83	CES80 = 83
CES06 = 51	CES31 = 86	CES56 = 83	CES81 = 66
CES07 = 43	CES32 = 95	CES57 = 81	CES82 = 93
CES08 = 41	CES33 = 86	CES58 = 81	CES83 = 88
CES09 = 29	CES34 = 93	CES59 = 93	CES84 = 96
CES10 = 75	CES35 = 95	CES60 = 89	CES85 = 78
CES11 = 58	CES36 = 76	CES61 = 88	CES86 = 77
CES12 = 64	CES37 = 95	CES62 = 79	CES87 = 92
CES13 = 43	CES38 = 75	CES63 = 92	CES88 = 91
CES14 = 74	CES39 = 95	CES64 = 85	CES89 = 85
CES15 = 72	CES40 = 91	CES65 = 90	CES90 = 87
CES16 = 47	CES41 = 90	CES66 = 86	CES91 = 71
CES17 = 49	CES42 = 91	CES67 = 87	CES92 = 79
CES18 = 56	CES43 = 89	CES68 = 89	CES93 = 87
CES19 = 71	CES44 = 99	CES69 = 89	CES94 = 80
CES20 = 66	CES45 = 92	CES70 = 90	CES95 = 87
CES21 = 85	CES46 = 91	CES71 = 85	CES96 = 95
CES22 = 78	CES47 = 84	CES72 = 94	CES97 = 89
CES23 = 91	CES48 = 80	CES73 = 88	CES98 = 88
CES24 = 90	CES49 = 92	CES74 = 87	CES99 = 88
CES25 = 71	CES50 = 89	CES75 = 86	





REPORT NUMBER: SP1-2505-441-9-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2505-441-9-R2

TM-30-18

Measure Comparisons





(END OF REPORT)