

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-43

Luminaire Tested: **213-8LED4025-12-CS-OSL**

Test Date: 04/05/18

**Test Information**

Test Method: LM-79-08  
Report Number: G2-1802-569-43  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-43)  
Test Lab: INNOVATION CENTER(G2)  
Test Date: 04/05/18  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 213-8LED4025-12-CS-OSL  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD SILVER, OVERALL SPREAD LENS  
Light Source: (1) SORAA 4000K 90 CRI LED  
SM16-07-25D-940-03  
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4000.0 lumens  
Efficiency: N/A  
Efficacy: 526.3 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.45  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.6  
Input Voltage (V): 12.0  
Input Current (Ain): 0.662  
Voltage Rise (V): NR  
Power Factor: 0.9909  
Total Harmonic Distortion (THDi): 27.1%  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): 25.2  
Test Distance: 25 FT



TEST NUMBER: G2-1802-569-43  
CATALOG NUMBER: 213-8LED4025-12-CS-OSL

### Luminous Intensity Polar Plot





TEST NUMBER: G2-1802-569-43  
 CATALOG NUMBER: 213-8LED4025-12-CS-OSL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	92
3	107	102	98	95	105	101	97	95	98	95	93	96	94	92	94	92	90	89
4	103	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86
5	100	94	90	86	99	93	89	86	91	88	85	90	87	85	89	86	84	83
6	97	90	86	83	96	90	86	83	88	85	82	87	84	82	86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	78	77
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75
9	89	82	77	75	88	81	77	74	80	77	74	80	76	74	79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	72	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	7681525
5°	7089608
10°	5356643
15°	3245675
20°	1717365
25°	880759
30°	347293
35°	120039
40°	60413
45°	40888
50°	35999
55°	30278
60°	23090
65°	13659
70°	16878
75°	0
80°	0
85°	0



TEST NUMBER: G2-1802-569-43  
 CATALOG NUMBER: 213-8LED4025-12-CS-OSL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1251.5	31.3
10°-20°	1748.1	43.7
20°-30°	756.0	18.9
30°-40°	150.9	3.8
40°-50°	47.2	1.2
50°-60°	28.7	0.7
60°-70°	13.0	0.3
70°-80°	4.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3755.7	93.9
0°-40°	3906.5	97.7
0°-60°	3982.4	99.6
0°-90°	4000.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4000.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	15569	
5°	14315	###
15°	6354	1748
25°	1618	756
35°	199	151
45°	59	47
55°	35	29
65°	12	13
75°	0	5
85°	0	0
90°	0	



TEST NUMBER: G2-1802-569-43  
CATALOG NUMBER: 213-8LED4025-12-CS-OSL

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	15569.2
1°	15463.7
2°	15276.1
3°	15018.2
4°	14701.6
5°	14314.8
6°	13810.6
7°	13200.9
8°	12450.6
9°	11606.5
10°	10692.1
11°	9742.4
12°	8828.0
13°	7960.5
14°	7128.1
15°	6354.3
16°	5615.7
17°	4947.5
18°	4349.5
19°	3775.0
20°	3270.9
21°	2825.4
22°	2450.2
23°	2133.7
24°	1864.1
25°	1617.9
26°	1383.4
27°	1172.4
28°	961.3
29°	773.8
30°	609.6
32.5°	316.5
35°	199.3
37.5°	129.0
40°	93.8
42.5°	70.3
45°	58.6
47.5°	46.9
50°	46.9
52.5°	35.2
55°	35.2
57.5°	23.4
60°	23.4
62.5°	11.7
65°	11.7



TEST NUMBER: G2-1802-569-43  
CATALOG NUMBER: 213-8LED4025-12-CS-OSL

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	11.7
70°	11.7
72.5°	11.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)