

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-34

Luminaire Tested: **213-8LED4036-12-BK-LVR**

Test Date: 04/06/18

Test Information

Test Method: LM-79-08
Report Number: G2-1802-569-34
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-34)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/06/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 213-8LED4036-12-BK-LVR
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD BLACK, HEX CELL LOUVER
Light Source: (1) SORAA 4000K 95 CRI LED
SM16-07-36D-940-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4000.0 lumens
Efficiency: N/A
Efficacy: 512.8 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.48
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.8
Input Voltage (V): 12.0
Input Current (Ain): 0.680
Voltage Rise (V): NR
Power Factor: 0.9908
Total Harmonic Distortion (THDi): 27.3%
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): 24.9
Test Distance: 25 FT



TEST NUMBER: G2-1802-569-34
CATALOG NUMBER: 213-8LED4036-12-BK-LVR

Luminous Intensity Polar Plot





TEST NUMBER: G2-1802-569-34
 CATALOG NUMBER: 213-8LED4036-12-BK-LVR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	92	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	91	89	86	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77
9	90	84	80	77	89	83	79	77	83	79	77	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	75	80	77	74	80	76	74	79	76	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7798406
5°	7050086
10°	5636897
15°	3777351
20°	1933053
25°	639270
30°	180825
35°	76493
40°	40898
45°	22118
50°	12204
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: G2-1802-569-34
 CATALOG NUMBER: 213-8LED4036-12-BK-LVR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1265.5	31.6
10°-20°	1987.5	49.7
20°-30°	630.5	15.8
30°-40°	89.2	2.2
40°-50°	25.5	0.6
50°-60°	1.7	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3883.5	97.1
0°-40°	3972.7	99.3
0°-60°	4000.0	100.0
0°-90°	4000.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4000.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15806	
5°	14235	###
15°	7395	1987
25°	1174	631
35°	127	89
45°	32	26
55°	0	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: G2-1802-569-34
CATALOG NUMBER: 213-8LED4036-12-BK-LVR

CANDELA DISTRIBUTION (FULL):

0°	
0°	15806.1
1°	15631.5
2°	15314.1
3°	14965.0
4°	14615.9
5°	14235.0
6°	13790.7
7°	13282.8
8°	12648.1
9°	11965.7
10°	11251.5
11°	10473.9
12°	9664.6
13°	8887.0
14°	8125.2
15°	7395.2
16°	6665.2
17°	5919.4
18°	5157.6
19°	4411.7
20°	3681.7
21°	3015.2
22°	2443.9
23°	1952.0
24°	1507.6
25°	1174.3
26°	920.4
27°	682.4
28°	539.6
29°	396.7
30°	317.4
32.5°	190.4
35°	127.0
37.5°	79.3
40°	63.5
42.5°	47.6
45°	31.7
47.5°	15.9
50°	15.9
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0



TEST NUMBER: G2-1802-569-34
CATALOG NUMBER: 213-8LED4036-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)