Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1527751

Luminaire Tested: 24CGTX-30-B2750-W2A-2700K

Issue Date: 8/26/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


Test Information

Test Method:	LM-79-2019
Report Number:	P1527751
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	8/26/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-30-B2750-W2A-2700K
Description:	2X4 3000 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 2700K CCT WITH FROSTED SMOOTH L
Light Source:	2700K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	2977.6 lumens
Efficiency:	N/A
Efficacy:	115.9 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 1.81' x L: 3.83' x H: 0')
CIE Type:	Direct

Input Watts (W):	25.7
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527751
CATALOG NUMBER: 24CGTX-30-B2750-W2A-2700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527751
CATALOG NUMBER: 24CGTX-30-B2750-W2A-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	68
3	89	79	70	63	87	77	69	63	74	67	62	71	65	61	69	64	60	57
4	82	69	60	54	79	68	60	53	66	58	52	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	39	51	44	39	50	44	39	37
7	64	50	42	35	62	50	41	35	48	40	35	47	40	35	45	39	34	32
8	60	46	37	31	58	45	37	31	44	36	31	43	36	31	41	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	25	37	30	25	36	30	25	36	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1554	1554	1554
5°	1558	1549	1558
10°	1561	1551	1561
15°	1557	1548	1556
20°	1551	1548	1555
25°	1545	1547	1542
30°	1538	1528	1533
35°	1521	1521	1521
40°	1517	1499	1503
45°	1499	1490	1499
50°	1487	1492	1470
55°	1464	1461	1461
60°	1441	1438	1425
65°	1426	1400	1382
70°	1377	1359	1332
75°	1329	1305	1281
80°	1240	1222	1187
85°	1155	1138	1084

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
Vertical Angle: 47.5°
Luminance: 1504 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527751
CATALOG NUMBER: 24CGTX-30-B2750-W2A-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.0	3.2
10°-20°	273.0	9.2
20°-30°	415.6	14.0
30°-40°	503.5	16.9
40°-50°	527.0	17.7
50°-60°	484.0	16.3
60°-70°	378.3	12.7
70°-80°	230.3	7.7
80°-90°	70.9	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	783.6	26.3
0°-40°	1287.2	43.2
0°-60°	2298.2	77.2
0°-90°	2977.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2977.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1003	1003	1003	1003	1003	
5°	1002	995	996	997	1002	95
15°	971	968	965	966	970	273
25°	904	901	905	898	902	417
35°	804	808	804	806	804	505
45°	684	683	680	685	684	529
55°	542	543	541	540	541	486
65°	389	384	382	381	377	384
75°	222	219	218	215	214	235
85°	65	64	64	61	61	73
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527751
CATALOG NUMBER: 24CGTX-30-B2750-W2A-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1003	*1003*	1003	1003	1003
2.5°	*1004*	*1006*	*1002*	*999*	*1002*
5°	1002	*995*	996	997	1002
7.5°	999	*992*	994	993	995
10°	992	*987*	986	984	992
12.5°	980	*979*	977	977	978
15°	971	*968*	965	966	970
17.5°	952	*956*	952	954	958
20°	941	*937*	939	937	943
22.5°	926	*918*	919	921	919
25°	904	*901*	905	898	902
27.5°	884	*881*	882	882	884
30°	860	*855*	854	853	857
32.5°	836	*839*	831	829	832
35°	804	*808*	804	806	804
37.5°	781	*776*	777	773	775
40°	750	*749*	741	745	743
42.5°	716	*717*	712	716	718
45°	684	*683*	680	685	684
47.5°	654	*652*	646	648	656
50°	617	*614*	619	615	610
52.5°	583	*581*	580	579	578
55°	542	*543*	541	540	541
57.5°	508	*503*	504	502	501
60°	465	*463*	464	460	460
62.5°	433	*426*	425	420	420
65°	389	*384*	382	381	377
67.5°	346	*344*	341	338	335
70°	304	*301*	300	297	294
72.5°	265	*262*	259	256	259
75°	222	*219*	218	215	214
77.5°	183	*181*	177	174	174
80°	139	*139*	137	136	133
82.5°	102	*101*	100	98	97
85°	65	*64*	64	61	61
87.5°	30	*29*	30	29	29
90°	0	*0*	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1527751
CATALOG NUMBER: 24CGTX-30-B2750-W2A-2700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.52	15.18	13.88	15.50	15.81	13.49	15.15	13.85	15.47	15.78
	3H	15.47	16.98	15.84	17.30	17.66	15.38	16.88	15.75	17.21	17.57
	4H	16.24	17.66	16.64	18.01	18.38	16.13	17.55	16.52	17.90	18.27
	6H	16.85	18.17	17.26	18.53	18.92	16.70	18.02	17.11	18.38	18.77
	8H	17.05	18.32	17.48	18.71	19.10	16.90	18.16	17.32	18.55	18.95
	12H	17.21	18.42	17.64	18.80	19.23	17.04	18.25	17.47	18.63	19.06
4H	2H	14.19	15.61	14.58	15.96	16.33	14.16	15.59	14.56	15.93	16.31
	3H	16.36	17.56	16.77	17.95	18.35	16.28	17.48	16.69	17.88	18.28
	4H	17.27	18.35	17.70	18.76	19.20	17.16	18.25	17.59	18.66	19.10
	6H	18.01	18.97	18.47	19.40	19.86	17.88	18.83	18.33	19.27	19.72
	8H	18.28	19.17	18.74	19.61	20.08	18.13	19.02	18.59	19.46	19.93
	12H	18.48	19.29	18.96	19.76	20.23	18.32	19.13	18.80	19.60	20.07
8H	4H	17.62	18.51	18.08	18.95	19.41	17.53	18.42	17.99	18.86	19.33
	6H	18.50	19.25	18.99	19.73	20.21	18.38	19.12	18.87	19.61	20.08
	8H	18.85	19.52	19.36	20.03	20.51	18.72	19.39	19.22	19.89	20.37
	12H	19.15	19.74	19.65	20.23	20.79	18.99	19.59	19.50	20.08	20.63
12H	4H	17.66	18.47	18.14	18.94	19.41	17.58	18.38	18.06	18.86	19.32
	6H	18.57	19.25	19.08	19.75	20.23	18.46	19.13	18.96	19.63	20.12
	8H	18.99	19.59	19.50	20.07	20.63	18.86	19.45	19.37	19.94	20.50

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2505-441-19-R2

Test Date: 06/13/2025

Luminaire Tested: 24CGTX-55-B2750-W2A-2700K

Data in this report applies to families of products including 24CGTX

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2505-441-19-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-55-B2750-W2A-2700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2504-441-19-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 5500 LUMEN CGTX AT 9.0V

Spectral Parameters

CCT (K):	2790
CIE u':	0.2594
CIE v':	0.5218
Duv:	-0.0026
CIE x:	0.4483
CIE y:	0.4008
CIE z:	0.1509
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	584
Purity:	54.87344
Rf:	93.8
Rg:	102.2

CRI (Ra):	95.1				
R1:	96.3	R9:	82.2		
R2:	97.2	R10:	95.9		
R3:	99.0	R11:	90.1		
R4:	95.3	R12:	90.6		
R5:	95.9	R13:	96.2		
R6:	91.0	R14:	97.9		
R7:	93.9	R15:	99.0		
R8:	92.1				




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2024	6/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2505-441-19-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2790K
CIE x = 0.4483
CIE y = 0.4008
Duv = -0.0026

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2505-441-19-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	81	NR	620	239	NR	750	5	NR	880	0	NR
365	0	NR	495	96	NR	625	249	NR	755	4	NR	885	0	NR
370	0	NR	500	109	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	120	NR	635	641	NR	765	3	NR	895	0	NR
380	0	NR	510	127	NR	640	153	NR	770	3	NR	900	0	NR
385	0	NR	515	131	NR	645	152	NR	775	2	NR	905	0	NR
390	0	NR	520	135	NR	650	132	NR	780	2	NR	910	0	NR
395	0	NR	525	137	NR	655	109	NR	785	2	NR	915	0	NR
400	1	NR	530	140	NR	660	92	NR	790	1	NR	920	0	NR
405	1	NR	535	144	NR	665	76	NR	795	1	NR	925	0	NR
410	2	NR	540	149	NR	670	72	NR	800	1	NR	930	0	NR
415	4	NR	545	154	NR	675	57	NR	805	1	NR	935	0	NR
420	7	NR	550	158	NR	680	49	NR	810	1	NR	940	0	NR
425	13	NR	555	164	NR	685	42	NR	815	1	NR	945	0	NR
430	22	NR	560	170	NR	690	36	NR	820	1	NR	950	0	NR
435	34	NR	565	175	NR	695	31	NR	825	1	NR	955	0	NR
440	55	NR	570	181	NR	700	26	NR	830	0	NR	960	0	NR
445	94	NR	575	186	NR	705	22	NR	835	0	NR	965	0	NR
450	129	NR	580	192	NR	710	19	NR	840	0	NR	970	0	NR
455	99	NR	585	198	NR	715	16	NR	845	0	NR	975	0	NR
460	71	NR	590	203	NR	720	14	NR	850	0	NR	980	0	NR
465	68	NR	595	204	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	210	NR	730	10	NR	860	0	NR	990	0	NR
475	62	NR	605	216	NR	735	8	NR	865	0	NR	995	0	NR
480	64	NR	610	250	NR	740	7	NR	870	0	NR	1000	0	NR
485	71	NR	615	281	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-19-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.41**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	81	NR	620	239	NR	750	5	NR	880	0	NR
365	0	NR	495	96	NR	625	249	NR	755	4	NR	885	0	NR
370	0	NR	500	109	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	120	NR	635	641	NR	765	3	NR	895	0	NR
380	0	NR	510	127	NR	640	153	NR	770	3	NR	900	0	NR
385	0	NR	515	131	NR	645	152	NR	775	2	NR	905	0	NR
390	0	NR	520	135	NR	650	132	NR	780	2	NR	910	0	NR
395	0	NR	525	137	NR	655	109	NR	785	2	NR	915	0	NR
400	1	NR	530	140	NR	660	92	NR	790	1	NR	920	0	NR
405	1	NR	535	144	NR	665	76	NR	795	1	NR	925	0	NR
410	2	NR	540	149	NR	670	72	NR	800	1	NR	930	0	NR
415	4	NR	545	154	NR	675	57	NR	805	1	NR	935	0	NR
420	7	NR	550	158	NR	680	49	NR	810	1	NR	940	0	NR
425	13	NR	555	164	NR	685	42	NR	815	1	NR	945	0	NR
430	22	NR	560	170	NR	690	36	NR	820	1	NR	950	0	NR
435	34	NR	565	175	NR	695	31	NR	825	1	NR	955	0	NR
440	55	NR	570	181	NR	700	26	NR	830	0	NR	960	0	NR
445	94	NR	575	186	NR	705	22	NR	835	0	NR	965	0	NR
450	129	NR	580	192	NR	710	19	NR	840	0	NR	970	0	NR
455	99	NR	585	198	NR	715	16	NR	845	0	NR	975	0	NR
460	71	NR	590	203	NR	720	14	NR	850	0	NR	980	0	NR
465	68	NR	595	204	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	210	NR	730	10	NR	860	0	NR	990	0	NR
475	62	NR	605	216	NR	735	8	NR	865	0	NR	995	0	NR
480	64	NR	610	250	NR	740	7	NR	870	0	NR	1000	0	NR
485	71	NR	615	281	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-19-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.77**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	81	NR	620	239	NR	750	5	NR	880	0	NR
365	0	NR	495	96	NR	625	249	NR	755	4	NR	885	0	NR
370	0	NR	500	109	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	120	NR	635	641	NR	765	3	NR	895	0	NR
380	0	NR	510	127	NR	640	153	NR	770	3	NR	900	0	NR
385	0	NR	515	131	NR	645	152	NR	775	2	NR	905	0	NR
390	0	NR	520	135	NR	650	132	NR	780	2	NR	910	0	NR
395	0	NR	525	137	NR	655	109	NR	785	2	NR	915	0	NR
400	1	NR	530	140	NR	660	92	NR	790	1	NR	920	0	NR
405	1	NR	535	144	NR	665	76	NR	795	1	NR	925	0	NR
410	2	NR	540	149	NR	670	72	NR	800	1	NR	930	0	NR
415	4	NR	545	154	NR	675	57	NR	805	1	NR	935	0	NR
420	7	NR	550	158	NR	680	49	NR	810	1	NR	940	0	NR
425	13	NR	555	164	NR	685	42	NR	815	1	NR	945	0	NR
430	22	NR	560	170	NR	690	36	NR	820	1	NR	950	0	NR
435	34	NR	565	175	NR	695	31	NR	825	1	NR	955	0	NR
440	55	NR	570	181	NR	700	26	NR	830	0	NR	960	0	NR
445	94	NR	575	186	NR	705	22	NR	835	0	NR	965	0	NR
450	129	NR	580	192	NR	710	19	NR	840	0	NR	970	0	NR
455	99	NR	585	198	NR	715	16	NR	845	0	NR	975	0	NR
460	71	NR	590	203	NR	720	14	NR	850	0	NR	980	0	NR
465	68	NR	595	204	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	210	NR	730	10	NR	860	0	NR	990	0	NR
475	62	NR	605	216	NR	735	8	NR	865	0	NR	995	0	NR
480	64	NR	610	250	NR	740	7	NR	870	0	NR	1000	0	NR
485	71	NR	615	281	NR	745	6	NR	875	0	NR			


REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18


Summary


R_f = 93.8
R_g = 102.2
CIE R_a = 95.1
R_9 = 82.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 98	CES51 = 94	CES76 = 95
CES02 = 64	CES27 = 94	CES52 = 94	CES77 = 80
CES03 = 32	CES28 = 99	CES53 = 94	CES78 = 92
CES04 = 70	CES29 = 97	CES54 = 95	CES79 = 84
CES05 = 51	CES30 = 99	CES55 = 95	CES80 = 89
CES06 = 51	CES31 = 97	CES56 = 96	CES81 = 66
CES07 = 45	CES32 = 90	CES57 = 97	CES82 = 95
CES08 = 43	CES33 = 97	CES58 = 95	CES83 = 91
CES09 = 29	CES34 = 97	CES59 = 98	CES84 = 98
CES10 = 77	CES35 = 99	CES60 = 96	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 96	CES86 = 79
CES12 = 66	CES37 = 96	CES62 = 91	CES87 = 95
CES13 = 45	CES38 = 95	CES63 = 97	CES88 = 99
CES14 = 74	CES39 = 98	CES64 = 96	CES89 = 85
CES15 = 72	CES40 = 95	CES65 = 98	CES90 = 98
CES16 = 48	CES41 = 94	CES66 = 97	CES91 = 85
CES17 = 50	CES42 = 94	CES67 = 97	CES92 = 83
CES18 = 57	CES43 = 94	CES68 = 96	CES93 = 89
CES19 = 72	CES44 = 99	CES69 = 96	CES94 = 77
CES20 = 68	CES45 = 95	CES70 = 96	CES95 = 90
CES21 = 86	CES46 = 96	CES71 = 95	CES96 = 96
CES22 = 79	CES47 = 83	CES72 = 98	CES97 = 94
CES23 = 92	CES48 = 98	CES73 = 93	CES98 = 97
CES24 = 90	CES49 = 94	CES74 = 86	CES99 = 96
CES25 = 72	CES50 = 94	CES75 = 95	





REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18

Measure Comparisons





(END OF REPORT)