

Scaled data based on original data using
LM-31-95 IESNA Approved Method for Photometric Testing of Roadway Luminaires
Using Incandescent Filament and High Intensity Discharge Lamps

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P189462

Luminaire Tested: **1900-OA-XX-50PAR20-120-BK**

Issue Date: 3/3/2020

Test Information

Test Method: LM-31-95
Report Number: P189462
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (ITL52171)
Test Lab:
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1900-OA-XX-50PAR20-120-BK
Description: CYLINDRICAL METAL HOUSING WITH ADJUSTABLE TOP PIECE, FABRICATED METAL SOCKET ASSEMBLY, TWO CLEAR FLAT GLASS INTERNAL PANELS BETWEEN LAMP AND UPPER OPTIC ASSEMBLY, CLEAR CYLINDRICAL PLASTIC LENS WITH CONVEX TOP AND WHITE PAINTED TOP SURFACE. TOP PIECE ADJUSTED SO BOTTOM ALIGNED WITH UPPER EDGE OF LENS FOR THIS TEST.
Light Source: (1) 50W PAR 20 INCANDESCENT LAMP
VERTICAL BASE-DOWN POSITION.
Ballast/Driver: -

Summary

Lumens per Lamp: 530 (1 lamp)
Luminaire Lumens: 38.8 lumens
Efficiency: 7.3%
Efficacy: 0.8 lumens/watt
Luminous Opening: (L: 0 ' x W: -0.29 ' x H: 0.08 '
IES Classification: Type V - Short - Cutoff
BUG Rating: B0 - U1 - G0


Input Watts (W): 50
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P189462
 CATALOG NUMBER: 1900-OA-XX-50PAR20-120-BK

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 2.4 foot mounting height. Maximum calculated value = 0.6 fc
 Type V - Short - Cutoff

REPORT NUMBER: P189462
CATALOG NUMBER: 1900-OA-XX-50PAR20-120-BK

Luminous Intensity Polar Plot



REPORT NUMBER: P189462

CATALOG NUMBER: 1900-OA-XX-50PAR20-120-BK


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	15.5	3.9	19.4
	% Lamp	2.9	0.7	3.7
Street Side	Lumens	15.5	3.9	19.4
	% Lamp	2.9	0.7	3.7
Total	Lumens	31.1	7.7	38.8
	% Lamp	5.9	1.5	7.3

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture	% Lamp
0°-10°	0.1	0.2	0.0
10°-20°	0.6	1.5	0.1
20°-30°	1.8	4.5	0.3
30°-40°	3.6	9.2	0.7
40°-50°	5.7	14.7	1.1
50°-60°	7.0	18.1	1.3
60°-70°	6.5	16.9	1.2
70°-80°	4.3	11.1	0.8
80°-90°	1.5	3.9	0.3
90°-100°	0.9	2.2	0.2
100°-110°	1.4	3.6	0.3
110°-120°	1.7	4.3	0.3
120°-130°	1.5	3.9	0.3
130°-140°	1.1	2.9	0.2
140°-150°	0.7	1.7	0.1
150°-160°	0.3	0.7	0.1
160°-170°	0.1	0.2	0.0
170°-180°	0.0	0.0	0.0
0°-90°	31.1	80.1	5.9
0°-180°	38.8	100.0	7.3



REPORT NUMBER: P189462


CATALOG NUMBER: 1900-OA-XX-50PAR20-120-BK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Lamp	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1.2	0.2			
FM (30°-60°)	8.2	1.5			
FH (60°-80°)	5.4	1.0			G0/660
FVH (80°-90°)	0.8	0.1			G0/10
BL (0°-30°)	1.2	0.2	B0/110		
BM (30°-60°)	8.2	1.5	B0/220		
BH (60°-80°)	5.4	1.0	B0/110		G0/660
BVH (80°-90°)	0.8	0.1			G0/10
UL (90°-100°)	0.9	0.2		U1/10	
UH (100°-180°)	3.9	0.7		U1/10	
Trapped Light	491.2	92.7			

BUG Rating: B0-U1-G0

Type V Short





REPORT NUMBER: P189462

CATALOG NUMBER: 1900-OA-XX-50PAR20-120-BK

CANDELA DISTRIBUTION (FULL):

	0°
0°	0.0
2.5°	0.3
5°	0.5
7.5°	0.8
10°	1.1
12.5°	1.3
15°	1.9
17.5°	2.4
20°	2.9
22.5°	3.2
25°	3.7
27.5°	4.2
30°	4.8
32.5°	5.3
35°	5.6
37.5°	6.1
40°	6.6
42.5°	6.9
45°	7.4
47.5°	7.7
50°	8.0
52.5°	8.0
55°	8.0
57.5°	7.7
60°	7.4
62.5°	7.2
65°	6.6
67.5°	6.1
70°	5.6
72.5°	4.8
75°	4.0
77.5°	3.4
80°	2.7
82.5°	1.9
85°	1.3
87.5°	0.8
90°	0.5
95°	0.8
105°	1.3
115°	1.9
125°	1.6
135°	1.6
145°	1.1
155°	0.5
165°	0.3



REPORT NUMBER: P189462

CATALOG NUMBER: 1900-OA-XX-50PAR20-120-BK

CANDELA DISTRIBUTION (continued):

	0°
175°	0.0
180°	0.0

(END OF REPORT)