Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1527781

Luminaire Tested: 24CGTX-65-B2750-W2A2-2700K

Issue Date: 8/26/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


Test Information

Test Method:	LM-79-2019
Report Number:	P1527781
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	8/26/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-65-B2750-W2A2-2700K
Description:	2X4 6500 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 2700K CCT WITH FROSTED SMOOTH L
Light Source:	2700K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	6076.5 lumens
Efficiency:	N/A
Efficacy:	108.5 lumens/watt
Spacing Criteria (0/90/45):	1.29 / 1.28 / 1.4
Luminous Opening:	Rectangular (W 1.81' x L: 3.83' x H: 0')
CIE Type:	Direct

Input Watts (W):	56
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527781
CATALOG NUMBER: 24CGTX-65-B2750-W2A2-2700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527781
CATALOG NUMBER: 24CGTX-65-B2750-W2A2-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	97	93	96	93	90	92	90	87	89	87	84	82
2	98	89	82	76	95	87	81	75	84	78	73	80	76	72	77	74	70	68
3	89	78	70	63	86	76	69	62	73	67	61	71	65	60	68	63	59	57
4	81	69	60	53	79	68	59	53	65	58	52	63	56	51	60	55	50	48
5	75	61	52	45	73	60	52	45	58	50	45	56	49	44	54	48	44	41
6	69	55	46	39	67	54	46	39	52	45	39	51	44	39	49	43	38	36
7	64	50	41	35	62	49	41	35	48	40	34	46	39	34	45	39	34	32
8	59	46	37	31	58	45	37	31	44	36	31	42	35	30	41	35	30	28
9	55	42	33	28	54	41	33	28	40	33	28	39	32	27	38	32	27	25
10	52	39	30	25	51	38	30	25	37	30	25	36	29	25	35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3075	3075	3075
5°	3092	3081	3087
10°	3094	3083	3093
15°	3097	3084	3091
20°	3095	3083	3090
25°	3091	3079	3091
30°	3080	3072	3075
35°	3070	3058	3066
40°	3050	3044	3040
45°	3050	3026	3028
50°	3030	3010	3001
55°	2998	2985	2979
60°	2965	2959	2934
65°	2940	2907	2892
70°	2876	2836	2808
75°	2843	2783	2753
80°	2766	2730	2668
85°	2755	2684	2702

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
Vertical Angle: 87.5°
Luminance: 3232 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527781
CATALOG NUMBER: 24CGTX-65-B2750-W2A2-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.6	3.1
10°-20°	543.5	8.9
20°-30°	830.9	13.7
30°-40°	1012.9	16.7
40°-50°	1067.9	17.6
50°-60°	988.4	16.3
60°-70°	784.1	12.9
70°-80°	491.9	8.1
80°-90°	168.1	2.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1563.1	25.7
0°-40°	2576.0	42.4
0°-60°	4632.4	76.2
0°-90°	6076.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6076.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1985	1985	1985	1985	1985	
5°	1988	1983	1981	1981	1985	189
15°	1931	1925	1923	1922	1927	545
25°	1808	1803	1801	1802	1808	833
35°	1623	1620	1617	1617	1621	1015
45°	1392	1386	1381	1382	1382	1072
55°	1110	1109	1105	1101	1103	993
65°	802	796	793	788	789	791
75°	475	472	465	462	460	499
85°	155	153	151	151	152	171
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527781
CATALOG NUMBER: 24CGTX-65-B2750-W2A2-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*1985*	1985	1985	1985	1985
2.5°	*1992*	*1986*	*1985*	*1982*	*1987*
5°	*1988*	1983	1981	1981	1985
7.5°	*1982*	1976	1973	1971	1980
10°	*1967*	1963	1960	1961	1966
12.5°	*1950*	1945	1944	1945	1946
15°	*1931*	1925	1923	1922	1927
17.5°	*1906*	1901	1899	1900	1905
20°	*1877*	1870	1870	1868	1874
22.5°	*1845*	1838	1836	1837	1840
25°	*1808*	1803	1801	1802	1808
27.5°	*1768*	1762	1763	1758	1765
30°	*1722*	1717	1717	1718	1719
32.5°	*1671*	1670	1670	1668	1670
35°	*1623*	1620	1617	1617	1621
37.5°	*1571*	1565	1563	1563	1566
40°	*1508*	1509	1505	1508	1503
42.5°	*1452*	1450	1447	1447	1445
45°	*1392*	1386	1381	1382	1382
47.5°	*1323*	1323	1317	1316	1318
50°	*1257*	1254	1249	1248	1245
52.5°	*1186*	1183	1179	1177	1179
55°	*1110*	1109	1105	1101	1103
57.5°	*1035*	1033	1033	1026	1027
60°	*957*	956	955	948	947
62.5°	*879*	878	874	870	870
65°	*802*	796	793	788	789
67.5°	*717*	714	710	707	706
70°	*635*	633	626	624	620
72.5°	*556*	553	546	541	536
75°	*475*	472	465	462	460
77.5°	*389*	390	386	381	380
80°	*310*	308	306	300	299
82.5°	*232*	228	227	226	223
85°	*155*	153	151	151	152
87.5°	*86*	82	85	89	91
90°	*0*	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1527781
CATALOG NUMBER: 24CGTX-65-B2750-W2A2-2700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.02	17.69	16.38	18.01	18.32	15.97	17.65	16.33	17.96	18.27
	3H	18.01	19.54	18.39	19.86	20.22	17.94	19.46	18.32	19.79	20.15
	4H	18.83	20.27	19.23	20.62	20.99	18.73	20.16	19.13	20.51	20.89
	6H	19.49	20.82	19.90	21.19	21.58	19.37	20.71	19.78	21.07	21.46
	8H	19.74	21.01	20.16	21.40	21.80	19.61	20.88	20.03	21.27	21.67
	12H	19.93	21.15	20.36	21.53	21.96	19.80	21.02	20.23	21.40	21.83
4H	2H	16.70	18.14	17.10	18.48	18.86	16.66	18.10	17.06	18.45	18.82
	3H	18.93	20.14	19.34	20.54	20.93	18.86	20.07	19.27	20.47	20.87
	4H	19.89	20.99	20.32	21.40	21.84	19.79	20.89	20.22	21.31	21.74
	6H	20.70	21.66	21.15	22.10	22.55	20.58	21.55	21.03	21.99	22.44
	8H	21.00	21.91	21.46	22.35	22.81	20.88	21.79	21.34	22.23	22.69
	12H	21.26	22.07	21.74	22.55	23.02	21.13	21.95	21.61	22.42	22.89
8H	4H	20.27	21.17	20.72	21.61	22.08	20.18	21.09	20.64	21.53	21.99
	6H	21.22	21.98	21.71	22.47	22.94	21.12	21.88	21.61	22.36	22.84
	8H	21.63	22.31	22.13	22.81	23.29	21.51	22.20	22.02	22.70	23.18
	12H	21.98	22.59	22.49	23.07	23.63	21.87	22.47	22.37	22.96	23.52
12H	4H	20.32	21.14	20.80	21.61	22.08	20.24	21.06	20.72	21.53	22.00
	6H	21.31	21.99	21.82	22.50	22.98	21.21	21.89	21.72	22.40	22.88
	8H	21.78	22.39	22.29	22.88	23.43	21.68	22.28	22.18	22.77	23.33

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2505-441-19-R2

Test Date: 06/13/2025

Luminaire Tested: 24CGTX-55-B2750-W2A-2700K

Data in this report applies to families of products including 24CGTX

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2505-441-19-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-55-B2750-W2A-2700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2504-441-19-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 5500 LUMEN CGTX AT 9.0V

Spectral Parameters

CCT (K):	2790
CIE u':	0.2594
CIE v':	0.5218
Duv:	-0.0026
CIE x:	0.4483
CIE y:	0.4008
CIE z:	0.1509
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	584
Purity:	54.87344
Rf:	93.8
Rg:	102.2

CRI (Ra):	95.1				
R1:	96.3	R9:	82.2		
R2:	97.2	R10:	95.9		
R3:	99.0	R11:	90.1		
R4:	95.3	R12:	90.6		
R5:	95.9	R13:	96.2		
R6:	91.0	R14:	97.9		
R7:	93.9	R15:	99.0		
R8:	92.1				




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2024	6/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2505-441-19-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2790K
CIE x = 0.4483
CIE y = 0.4008
Duv = -0.0026

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2505-441-19-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	81	NR	620	239	NR	750	5	NR	880	0	NR
365	0	NR	495	96	NR	625	249	NR	755	4	NR	885	0	NR
370	0	NR	500	109	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	120	NR	635	641	NR	765	3	NR	895	0	NR
380	0	NR	510	127	NR	640	153	NR	770	3	NR	900	0	NR
385	0	NR	515	131	NR	645	152	NR	775	2	NR	905	0	NR
390	0	NR	520	135	NR	650	132	NR	780	2	NR	910	0	NR
395	0	NR	525	137	NR	655	109	NR	785	2	NR	915	0	NR
400	1	NR	530	140	NR	660	92	NR	790	1	NR	920	0	NR
405	1	NR	535	144	NR	665	76	NR	795	1	NR	925	0	NR
410	2	NR	540	149	NR	670	72	NR	800	1	NR	930	0	NR
415	4	NR	545	154	NR	675	57	NR	805	1	NR	935	0	NR
420	7	NR	550	158	NR	680	49	NR	810	1	NR	940	0	NR
425	13	NR	555	164	NR	685	42	NR	815	1	NR	945	0	NR
430	22	NR	560	170	NR	690	36	NR	820	1	NR	950	0	NR
435	34	NR	565	175	NR	695	31	NR	825	1	NR	955	0	NR
440	55	NR	570	181	NR	700	26	NR	830	0	NR	960	0	NR
445	94	NR	575	186	NR	705	22	NR	835	0	NR	965	0	NR
450	129	NR	580	192	NR	710	19	NR	840	0	NR	970	0	NR
455	99	NR	585	198	NR	715	16	NR	845	0	NR	975	0	NR
460	71	NR	590	203	NR	720	14	NR	850	0	NR	980	0	NR
465	68	NR	595	204	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	210	NR	730	10	NR	860	0	NR	990	0	NR
475	62	NR	605	216	NR	735	8	NR	865	0	NR	995	0	NR
480	64	NR	610	250	NR	740	7	NR	870	0	NR	1000	0	NR
485	71	NR	615	281	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-19-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.41**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	81	NR	620	239	NR	750	5	NR	880	0	NR
365	0	NR	495	96	NR	625	249	NR	755	4	NR	885	0	NR
370	0	NR	500	109	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	120	NR	635	641	NR	765	3	NR	895	0	NR
380	0	NR	510	127	NR	640	153	NR	770	3	NR	900	0	NR
385	0	NR	515	131	NR	645	152	NR	775	2	NR	905	0	NR
390	0	NR	520	135	NR	650	132	NR	780	2	NR	910	0	NR
395	0	NR	525	137	NR	655	109	NR	785	2	NR	915	0	NR
400	1	NR	530	140	NR	660	92	NR	790	1	NR	920	0	NR
405	1	NR	535	144	NR	665	76	NR	795	1	NR	925	0	NR
410	2	NR	540	149	NR	670	72	NR	800	1	NR	930	0	NR
415	4	NR	545	154	NR	675	57	NR	805	1	NR	935	0	NR
420	7	NR	550	158	NR	680	49	NR	810	1	NR	940	0	NR
425	13	NR	555	164	NR	685	42	NR	815	1	NR	945	0	NR
430	22	NR	560	170	NR	690	36	NR	820	1	NR	950	0	NR
435	34	NR	565	175	NR	695	31	NR	825	1	NR	955	0	NR
440	55	NR	570	181	NR	700	26	NR	830	0	NR	960	0	NR
445	94	NR	575	186	NR	705	22	NR	835	0	NR	965	0	NR
450	129	NR	580	192	NR	710	19	NR	840	0	NR	970	0	NR
455	99	NR	585	198	NR	715	16	NR	845	0	NR	975	0	NR
460	71	NR	590	203	NR	720	14	NR	850	0	NR	980	0	NR
465	68	NR	595	204	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	210	NR	730	10	NR	860	0	NR	990	0	NR
475	62	NR	605	216	NR	735	8	NR	865	0	NR	995	0	NR
480	64	NR	610	250	NR	740	7	NR	870	0	NR	1000	0	NR
485	71	NR	615	281	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-19-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.77**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	81	NR	620	239	NR	750	5	NR	880	0	NR
365	0	NR	495	96	NR	625	249	NR	755	4	NR	885	0	NR
370	0	NR	500	109	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	120	NR	635	641	NR	765	3	NR	895	0	NR
380	0	NR	510	127	NR	640	153	NR	770	3	NR	900	0	NR
385	0	NR	515	131	NR	645	152	NR	775	2	NR	905	0	NR
390	0	NR	520	135	NR	650	132	NR	780	2	NR	910	0	NR
395	0	NR	525	137	NR	655	109	NR	785	2	NR	915	0	NR
400	1	NR	530	140	NR	660	92	NR	790	1	NR	920	0	NR
405	1	NR	535	144	NR	665	76	NR	795	1	NR	925	0	NR
410	2	NR	540	149	NR	670	72	NR	800	1	NR	930	0	NR
415	4	NR	545	154	NR	675	57	NR	805	1	NR	935	0	NR
420	7	NR	550	158	NR	680	49	NR	810	1	NR	940	0	NR
425	13	NR	555	164	NR	685	42	NR	815	1	NR	945	0	NR
430	22	NR	560	170	NR	690	36	NR	820	1	NR	950	0	NR
435	34	NR	565	175	NR	695	31	NR	825	1	NR	955	0	NR
440	55	NR	570	181	NR	700	26	NR	830	0	NR	960	0	NR
445	94	NR	575	186	NR	705	22	NR	835	0	NR	965	0	NR
450	129	NR	580	192	NR	710	19	NR	840	0	NR	970	0	NR
455	99	NR	585	198	NR	715	16	NR	845	0	NR	975	0	NR
460	71	NR	590	203	NR	720	14	NR	850	0	NR	980	0	NR
465	68	NR	595	204	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	210	NR	730	10	NR	860	0	NR	990	0	NR
475	62	NR	605	216	NR	735	8	NR	865	0	NR	995	0	NR
480	64	NR	610	250	NR	740	7	NR	870	0	NR	1000	0	NR
485	71	NR	615	281	NR	745	6	NR	875	0	NR			


REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18


Summary


R_f = 93.8
R_g = 102.2
CIE R_a = 95.1
R_9 = 82.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 98	CES51 = 94	CES76 = 95
CES02 = 64	CES27 = 94	CES52 = 94	CES77 = 80
CES03 = 32	CES28 = 99	CES53 = 94	CES78 = 92
CES04 = 70	CES29 = 97	CES54 = 95	CES79 = 84
CES05 = 51	CES30 = 99	CES55 = 95	CES80 = 89
CES06 = 51	CES31 = 97	CES56 = 96	CES81 = 66
CES07 = 45	CES32 = 90	CES57 = 97	CES82 = 95
CES08 = 43	CES33 = 97	CES58 = 95	CES83 = 91
CES09 = 29	CES34 = 97	CES59 = 98	CES84 = 98
CES10 = 77	CES35 = 99	CES60 = 96	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 96	CES86 = 79
CES12 = 66	CES37 = 96	CES62 = 91	CES87 = 95
CES13 = 45	CES38 = 95	CES63 = 97	CES88 = 99
CES14 = 74	CES39 = 98	CES64 = 96	CES89 = 85
CES15 = 72	CES40 = 95	CES65 = 98	CES90 = 98
CES16 = 48	CES41 = 94	CES66 = 97	CES91 = 85
CES17 = 50	CES42 = 94	CES67 = 97	CES92 = 83
CES18 = 57	CES43 = 94	CES68 = 96	CES93 = 89
CES19 = 72	CES44 = 99	CES69 = 96	CES94 = 77
CES20 = 68	CES45 = 95	CES70 = 96	CES95 = 90
CES21 = 86	CES46 = 96	CES71 = 95	CES96 = 96
CES22 = 79	CES47 = 83	CES72 = 98	CES97 = 94
CES23 = 92	CES48 = 98	CES73 = 93	CES98 = 97
CES24 = 90	CES49 = 94	CES74 = 86	CES99 = 96
CES25 = 72	CES50 = 94	CES75 = 95	





REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18

Measure Comparisons





(END OF REPORT)