

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **922-50MR16-12-NSP**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: (CONVERTED FROM TYPE C PHOTOMETRY)
Test Lab:
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 922-50MR16-12-NSP
Description:
Light Source: Q50MR16/C/NSP15°-EXT
BARE LAMP DATA FOR 922
Ballast/Driver: -

Summary


Lumens per Lamp:	1815 (1 lamp)	NEMA Type:	2H x 2V
Luminaire Lumens:	1804.9 lumens	Max Intensity:	10280 candela
Efficiency:	99.4%	Max Intensity Angle:	-1.25°H x 0°V
Efficacy:	NR		
Luminous Opening:	Point Source (0' x 0' x 0')		
Beam Angle (50%):	13°H x 12.7°V	Field Angle (10%):	24°H x 23.9°V
Beam Lumens:	322.1 lumens	Field Lumens:	537.6 lumens
Beam Efficiency:	17.8%	Field Efficiency:	29.8%

Input Watts (W): 0
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

Iso-Candela Plot




REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

Lumen Table

90																		
80	3.3		9.3		14.3		17.5		18.7		17.5		14.3		9.3		3.3	
70	3.2		2.0	2.7	3.3	3.9	4.3	4.5	4.7	4.7	4.5	4.3	3.9	3.3	2.7	2.0	3.2	
60			2.0	2.7	3.3	3.9	4.3	4.7	4.8	4.8	4.7	4.3	3.9	3.3	2.7	2.0		
50	3.2		2.0	2.7	3.4	4.0	5.1	6.5	7.2	7.2	6.5	5.1	4.0	3.4	2.7	2.0	3.2	
40			2.0	2.7	3.5	5.2	7.3	8.1	8.4	8.4	8.1	7.3	5.2	3.5	2.7	2.0		
30	3.2		2.0	2.7	4.0	6.6	7.7	8.6	9.4	9.4	8.6	7.7	6.6	4.0	2.7	2.0	3.2	
20			2.0	2.8	4.8	6.9	8.1	10.7	18.4	18.4	10.7	8.1	6.9	4.8	2.8	2.0		
10	3.2		2.0	2.8	5.2	6.9	8.6	17.9	128.8	128.8	17.9	8.6	6.9	5.2	2.8	2.0	3.2	
0			2.0	2.8	5.2	6.9	8.6	17.9	128.8	128.8	17.9	8.6	6.9	5.2	2.8	2.0		
-10	3.2		2.0	2.8	4.8	6.9	8.1	10.7	18.4	18.4	10.7	8.1	6.9	4.8	2.8	2.0	3.2	
-20			2.0	2.7	4.0	6.6	7.7	8.6	9.4	9.4	8.6	7.7	6.6	4.0	2.7	2.0		
-30	3.2		2.0	2.7	3.5	5.2	7.3	8.1	8.4	8.4	8.1	7.3	5.2	3.5	2.7	2.0	3.2	
-40			2.0	2.7	3.4	4.0	5.1	6.5	7.2	7.2	6.5	5.1	4.0	3.4	2.7	2.0		
-50	3.2		2.0	2.7	3.3	3.9	4.3	4.7	4.8	4.8	4.7	4.3	3.9	3.3	2.7	2.0	3.2	
-60			2.0	2.7	3.3	3.9	4.3	4.5	4.7	4.7	4.5	4.3	3.9	3.3	2.7	2.0		
-70																		
-80	3.3		9.3		14.3		17.5		18.7		17.5		14.3		9.3		3.3	
-90																		


REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

Luminous Intensity Polar Plot



REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

Luminous Intensity Plot



Beam:
H Angle: 13°
V Angle: 12.7°
Lumens: 322.1
Efficiency: 17.8%

Field:
H Angle: 24°
V Angle: 23.9°
Lumens: 537.6
Efficiency: 29.8%

Spill:
Lumens: 1267.3
Efficiency: 70.2%

— Vertical Distribution through -1.25-Deg
- - Horizontal Distribution through 0-Deg

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

FIELD
BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
88.75°	157.0	157.0	157.0	156.9	156.9	156.9	156.9	156.8	156.8	156.8	156.8
87.5°	157.0	157.0	156.9	156.9	156.8	156.8	156.7	156.7	156.7	156.6	156.6
86.25°	157.0	156.9	156.9	156.8	156.7	156.7	156.6	156.5	156.5	156.4	156.4
85°	157.0	156.9	156.8	156.7	156.7	156.6	156.5	156.4	156.3	156.2	156.1
83.75°	157.0	156.9	156.8	156.7	156.6	156.5	156.3	156.2	156.1	156.0	155.9
82.5°	157.0	156.9	156.7	156.6	156.5	156.3	156.2	156.1	156.0	155.8	155.7
81.25°	157.0	156.8	156.7	156.5	156.4	156.2	156.1	155.9	155.8	155.6	155.5
80°	157.0	156.8	156.7	156.5	156.3	156.1	156.0	155.8	155.6	155.4	155.3
78.75°	157.0	156.8	156.6	156.4	156.2	156.0	155.8	155.6	155.4	155.3	155.1
77.5°	157.0	156.8	156.6	156.4	156.1	155.9	155.7	155.5	155.3	155.1	154.9
76.25°	157.0	156.8	156.5	156.3	156.1	155.8	155.6	155.3	155.1	154.9	154.6
75°	157.0	156.7	156.5	156.2	156.0	155.7	155.5	155.2	154.9	154.7	154.4
73.75°	157.0	156.7	156.4	156.2	155.9	155.6	155.3	155.0	154.8	154.5	154.2
72.5°	157.0	156.7	156.4	156.1	155.8	155.5	155.2	154.9	154.6	154.3	154.0
71.25°	157.0	156.7	156.4	156.0	155.7	155.4	155.1	154.8	154.4	154.1	153.8
70°	157.0	156.7	156.3	156.0	155.6	155.3	155.0	154.6	154.3	153.9	153.6
68.75°	157.0	156.6	156.3	155.9	155.6	155.2	154.8	154.5	154.1	153.8	153.4
67.5°	157.0	156.6	156.2	155.9	155.5	155.1	154.7	154.3	154.0	153.6	153.2
66.25°	157.0	156.6	156.2	155.8	155.4	155.0	154.6	154.2	153.8	153.4	153.0
65°	157.0	156.6	156.2	155.7	155.3	154.9	154.5	154.1	153.6	153.2	153.0
63.75°	157.0	156.6	156.1	155.7	155.2	154.8	154.4	153.9	153.5	153.0	153.0
62.5°	157.0	156.5	156.1	155.6	155.2	154.7	154.2	153.8	153.3	153.0	153.0
61.25°	157.0	156.5	156.0	155.6	155.1	154.6	154.1	153.6	153.2	153.0	153.0
60°	157.0	156.5	156.0	155.5	155.0	154.5	154.0	153.5	153.0	153.0	153.0
58.75°	157.0	156.5	156.0	155.4	154.9	154.4	153.9	153.4	153.0	153.0	153.0
57.5°	157.0	156.5	155.9	155.4	154.9	154.3	153.8	153.2	153.0	153.0	153.0
56.25°	157.0	156.4	155.9	155.3	154.8	154.2	153.7	153.1	153.0	153.0	153.0
55°	157.0	156.4	155.9	155.3	154.7	154.1	153.6	153.0	153.0	153.0	153.0
53.75°	157.0	156.4	155.8	155.2	154.6	154.0	153.5	153.0	153.0	153.0	153.0
52.5°	157.0	156.4	155.8	155.2	154.6	154.0	153.4	153.0	153.0	153.0	153.0
51.25°	157.0	156.4	155.7	155.1	154.5	153.9	153.3	153.0	153.0	153.0	153.0
50°	157.0	156.4	155.7	155.1	154.4	153.8	153.1	153.0	153.0	153.0	153.0
48.75°	157.0	156.3	155.7	155.0	154.4	153.7	153.1	153.0	153.0	153.0	153.0
47.5°	157.0	156.3	155.6	155.0	154.3	153.6	153.0	153.0	153.0	153.0	153.0
46.25°	157.0	156.3	155.6	154.9	154.2	153.5	153.0	153.0	153.0	153.0	153.0
45°	157.0	156.3	155.6	154.9	154.2	153.5	153.0	153.0	153.0	153.0	153.0
43.75°	157.0	156.3	155.6	154.8	154.1	153.4	153.0	153.0	153.0	153.0	153.0
42.5°	157.0	156.3	155.5	154.8	154.1	153.3	153.0	153.0	153.0	153.0	153.0
41.25°	157.0	156.2	155.5	154.7	154.0	153.2	153.0	153.0	153.0	153.0	153.0
40°	157.0	156.2	155.5	154.7	153.9	153.2	153.0	153.0	153.0	153.0	153.0
38.75°	157.0	156.2	155.4	154.7	153.9	153.1	153.0	153.0	153.0	153.0	153.0
37.5°	157.0	156.2	155.4	154.6	153.8	153.0	153.0	153.0	153.0	153.0	153.0
36.25°	157.0	156.2	155.4	154.6	153.8	153.0	153.0	153.0	153.0	153.0	153.0
35°	157.0	156.2	155.4	154.5	153.7	153.0	153.0	153.0	153.0	153.0	153.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	157.0	156.2	155.3	154.5	153.7	153.0	153.0	153.0	153.0	153.0	153.1
32.5°	157.0	156.2	155.3	154.5	153.6	153.0	153.0	153.0	153.0	153.0	153.1
31.25°	157.0	156.1	155.3	154.4	153.6	153.0	153.0	153.0	153.0	153.0	153.1
30°	157.0	156.1	155.3	154.4	153.5	153.0	153.0	153.0	153.0	153.0	153.2
28.75°	157.0	156.1	155.2	154.4	153.5	153.0	153.0	153.0	153.0	153.0	153.2
27.5°	157.0	156.1	155.2	154.3	153.5	153.0	153.0	153.0	153.0	153.0	153.2
26.25°	157.0	156.1	155.2	154.3	153.4	153.0	153.0	153.0	153.0	153.0	153.2
25°	157.0	156.1	155.2	154.3	153.4	153.0	153.0	153.0	153.0	153.0	153.3
23.75°	157.0	156.1	155.2	154.3	153.3	153.0	153.0	153.0	153.0	153.1	153.3
22.5°	157.0	156.1	155.2	154.2	153.3	153.0	153.0	153.0	153.0	153.1	153.3
21.25°	157.0	156.1	155.1	154.2	153.3	153.0	153.0	153.0	153.0	153.1	153.3
20°	157.0	156.1	155.1	154.2	153.2	153.0	153.0	153.0	153.0	153.1	153.3
18.75°	157.0	156.1	155.1	154.2	153.2	153.0	153.0	153.0	153.0	153.1	153.4
17.5°	157.0	156.0	155.1	154.1	153.2	153.0	153.0	153.0	153.0	153.1	153.4
16.25°	157.0	156.0	155.1	154.1	153.2	153.0	153.0	153.0	153.0	153.2	153.4
15°	157.0	156.0	155.1	154.1	153.1	153.0	153.0	153.0	153.0	153.2	153.4
13.75°	157.0	156.0	155.1	154.1	153.1	153.0	153.0	153.0	153.0	153.2	153.4
12.5°	157.0	156.0	155.0	154.1	153.1	153.0	153.0	153.0	153.0	153.2	153.4
11.25°	157.0	156.0	155.0	154.1	153.1	153.0	153.0	153.0	153.0	153.2	153.5
10°	157.0	156.0	155.0	154.0	153.1	153.0	153.0	153.0	153.0	153.2	153.5
8.75°	157.0	156.0	155.0	154.0	153.0	153.0	153.0	153.0	153.0	153.2	153.5
7.5°	157.0	156.0	155.0	154.0	153.0	153.0	153.0	153.0	153.0	153.2	153.5
6.25°	157.0	156.0	155.0	154.0	153.0	153.0	153.0	153.0	153.0	153.2	153.5
5°	157.0	156.0	155.0	154.0	153.0	153.0	153.0	153.0	153.0	153.2	153.5
3.75°	157.0	156.0	155.0	154.0	153.0	153.0	153.0	153.0	153.0	153.2	153.5
2.5°	157.0	156.0	155.0	154.0	153.0	153.0	153.0	153.0	153.0	153.2	153.5
1.25°	157.0	156.0	155.0	154.0	153.0	153.0	153.0	153.0	153.0	153.2	153.5
0°	157.0	156.0	155.0	154.0	153.0	153.0	153.0	153.0	153.0	153.2	153.5
-1.25°	157.0	156.0	155.0	154.0	153.0	153.0	153.0	153.0	153.0	153.2	153.5
-2.5°	157.0	156.0	155.0	154.0	153.0	153.0	153.0	153.0	153.0	153.2	153.5
-3.75°	157.0	156.0	155.0	154.0	153.0	153.0	153.0	153.0	153.0	153.2	153.5
-5°	157.0	156.0	155.0	154.0	153.0	153.0	153.0	153.0	153.0	153.2	153.5
-6.25°	157.0	156.0	155.0	154.0	153.0	153.0	153.0	153.0	153.0	153.2	153.5
-7.5°	157.0	156.0	155.0	154.0	153.0	153.0	153.0	153.0	153.0	153.2	153.5
-8.75°	157.0	156.0	155.0	154.0	153.0	153.0	153.0	153.0	153.0	153.2	153.5
-10°	157.0	156.0	155.0	154.0	153.1	153.0	153.0	153.0	153.0	153.2	153.5
-11.25°	157.0	156.0	155.0	154.1	153.1	153.0	153.0	153.0	153.0	153.2	153.5
-12.5°	157.0	156.0	155.0	154.1	153.1	153.0	153.0	153.0	153.0	153.2	153.4
-13.75°	157.0	156.0	155.1	154.1	153.1	153.0	153.0	153.0	153.0	153.2	153.4
-15°	157.0	156.0	155.1	154.1	153.1	153.0	153.0	153.0	153.0	153.2	153.4
-16.25°	157.0	156.0	155.1	154.1	153.2	153.0	153.0	153.0	153.0	153.2	153.4
-17.5°	157.0	156.0	155.1	154.1	153.2	153.0	153.0	153.0	153.0	153.1	153.4
-18.75°	157.0	156.1	155.1	154.2	153.2	153.0	153.0	153.0	153.0	153.1	153.4
-20°	157.0	156.1	155.1	154.2	153.2	153.0	153.0	153.0	153.0	153.1	153.3
-21.25°	157.0	156.1	155.1	154.2	153.3	153.0	153.0	153.0	153.0	153.1	153.3

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	157.0	156.1	155.2	154.2	153.3	153.0	153.0	153.0	153.0	153.1	153.3
-23.75°	157.0	156.1	155.2	154.3	153.3	153.0	153.0	153.0	153.0	153.1	153.3
-25°	157.0	156.1	155.2	154.3	153.4	153.0	153.0	153.0	153.0	153.0	153.3
-26.25°	157.0	156.1	155.2	154.3	153.4	153.0	153.0	153.0	153.0	153.0	153.2
-27.5°	157.0	156.1	155.2	154.3	153.5	153.0	153.0	153.0	153.0	153.0	153.2
-28.75°	157.0	156.1	155.2	154.4	153.5	153.0	153.0	153.0	153.0	153.0	153.2
-30°	157.0	156.1	155.3	154.4	153.5	153.0	153.0	153.0	153.0	153.0	153.2
-31.25°	157.0	156.1	155.3	154.4	153.6	153.0	153.0	153.0	153.0	153.0	153.1
-32.5°	157.0	156.2	155.3	154.5	153.6	153.0	153.0	153.0	153.0	153.0	153.1
-33.75°	157.0	156.2	155.3	154.5	153.7	153.0	153.0	153.0	153.0	153.0	153.1
-35°	157.0	156.2	155.4	154.5	153.7	153.0	153.0	153.0	153.0	153.0	153.0
-36.25°	157.0	156.2	155.4	154.6	153.8	153.0	153.0	153.0	153.0	153.0	153.0
-37.5°	157.0	156.2	155.4	154.6	153.8	153.0	153.0	153.0	153.0	153.0	153.0
-38.75°	157.0	156.2	155.4	154.7	153.9	153.1	153.0	153.0	153.0	153.0	153.0
-40°	157.0	156.2	155.5	154.7	153.9	153.2	153.0	153.0	153.0	153.0	153.0
-41.25°	157.0	156.2	155.5	154.7	154.0	153.2	153.0	153.0	153.0	153.0	153.0
-42.5°	157.0	156.3	155.5	154.8	154.1	153.3	153.0	153.0	153.0	153.0	153.0
-43.75°	157.0	156.3	155.6	154.8	154.1	153.4	153.0	153.0	153.0	153.0	153.0
-45°	157.0	156.3	155.6	154.9	154.2	153.5	153.0	153.0	153.0	153.0	153.0
-46.25°	157.0	156.3	155.6	154.9	154.2	153.5	153.0	153.0	153.0	153.0	153.0
-47.5°	157.0	156.3	155.6	155.0	154.3	153.6	153.0	153.0	153.0	153.0	153.0
-48.75°	157.0	156.3	155.7	155.0	154.4	153.7	153.1	153.0	153.0	153.0	153.0
-50°	157.0	156.4	155.7	155.1	154.4	153.8	153.1	153.0	153.0	153.0	153.0
-51.25°	157.0	156.4	155.7	155.1	154.5	153.9	153.3	153.0	153.0	153.0	153.0
-52.5°	157.0	156.4	155.8	155.2	154.6	154.0	153.4	153.0	153.0	153.0	153.0
-53.75°	157.0	156.4	155.8	155.2	154.6	154.0	153.5	153.0	153.0	153.0	153.0
-55°	157.0	156.4	155.9	155.3	154.7	154.1	153.6	153.0	153.0	153.0	153.0
-56.25°	157.0	156.4	155.9	155.3	154.8	154.2	153.7	153.1	153.0	153.0	153.0
-57.5°	157.0	156.5	155.9	155.4	154.9	154.3	153.8	153.2	153.0	153.0	153.0
-58.75°	157.0	156.5	156.0	155.4	154.9	154.4	153.9	153.4	153.0	153.0	153.0
-60°	157.0	156.5	156.0	155.5	155.0	154.5	154.0	153.5	153.0	153.0	153.0
-61.25°	157.0	156.5	156.0	155.6	155.1	154.6	154.1	153.6	153.2	153.0	153.0
-62.5°	157.0	156.5	156.1	155.6	155.2	154.7	154.2	153.8	153.3	153.0	153.0
-63.75°	157.0	156.6	156.1	155.7	155.2	154.8	154.4	153.9	153.5	153.0	153.0
-65°	157.0	156.6	156.2	155.7	155.3	154.9	154.5	154.1	153.6	153.2	153.0
-66.25°	157.0	156.6	156.2	155.8	155.4	155.0	154.6	154.2	153.8	153.4	153.0
-67.5°	157.0	156.6	156.2	155.9	155.5	155.1	154.7	154.3	154.0	153.6	153.2
-68.75°	157.0	156.6	156.3	155.9	155.6	155.2	154.8	154.5	154.1	153.8	153.4
-70°	157.0	156.7	156.3	156.0	155.6	155.3	155.0	154.6	154.3	153.9	153.6
-71.25°	157.0	156.7	156.4	156.0	155.7	155.4	155.1	154.8	154.4	154.1	153.8
-72.5°	157.0	156.7	156.4	156.1	155.8	155.5	155.2	154.9	154.6	154.3	154.0
-73.75°	157.0	156.7	156.4	156.2	155.9	155.6	155.3	155.0	154.8	154.5	154.2
-75°	157.0	156.7	156.5	156.2	156.0	155.7	155.5	155.2	154.9	154.7	154.4
-76.25°	157.0	156.8	156.5	156.3	156.1	155.8	155.6	155.3	155.1	154.9	154.6
-77.5°	157.0	156.8	156.6	156.4	156.1	155.9	155.7	155.5	155.3	155.1	154.9



REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	157.0	156.8	156.6	156.4	156.2	156.0	155.8	155.6	155.4	155.3	155.1
-80°	157.0	156.8	156.7	156.5	156.3	156.1	156.0	155.8	155.6	155.4	155.3
-81.25°	157.0	156.8	156.7	156.5	156.4	156.2	156.1	155.9	155.8	155.6	155.5
-82.5°	157.0	156.9	156.7	156.6	156.5	156.3	156.2	156.1	156.0	155.8	155.7
-83.75°	157.0	156.9	156.8	156.7	156.6	156.5	156.3	156.2	156.1	156.0	155.9
-85°	157.0	156.9	156.8	156.7	156.7	156.6	156.5	156.4	156.3	156.2	156.1
-86.25°	157.0	156.9	156.9	156.8	156.7	156.7	156.6	156.5	156.5	156.4	156.4
-87.5°	157.0	157.0	156.9	156.9	156.8	156.8	156.7	156.7	156.7	156.6	156.6
-88.75°	157.0	157.0	157.0	156.9	156.9	156.9	156.9	156.8	156.8	156.8	156.8
-90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
88.75°	156.8	156.7	156.7	156.7	156.7	156.7	156.6	156.6	156.6	156.6	156.6
87.5°	156.5	156.5	156.4	156.4	156.4	156.3	156.3	156.2	156.2	156.2	156.1
86.25°	156.3	156.2	156.2	156.1	156.0	156.0	155.9	155.9	155.8	155.7	155.7
85°	156.1	156.0	155.9	155.8	155.7	155.6	155.6	155.5	155.4	155.3	155.2
83.75°	155.8	155.7	155.6	155.5	155.4	155.3	155.2	155.1	155.0	154.9	154.8
82.5°	155.6	155.5	155.3	155.2	155.1	155.0	154.8	154.7	154.6	154.5	154.4
81.25°	155.3	155.2	155.0	154.9	154.8	154.6	154.5	154.3	154.2	154.1	153.9
80°	155.1	154.9	154.8	154.6	154.4	154.3	154.1	154.0	153.8	153.6	153.5
78.75°	154.9	154.7	154.5	154.3	154.1	153.9	153.8	153.6	153.4	153.2	153.0
77.5°	154.6	154.4	154.2	154.0	153.8	153.6	153.4	153.2	153.0	153.0	153.0
76.25°	154.4	154.2	153.9	153.7	153.5	153.3	153.0	153.0	153.0	153.0	153.0
75°	154.2	153.9	153.7	153.4	153.2	153.0	153.0	153.0	153.0	153.0	153.0
73.75°	153.9	153.7	153.4	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0
72.5°	153.7	153.4	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
71.25°	153.5	153.2	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
70°	153.3	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
68.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
67.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
66.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1
65°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.2
63.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.2	153.3
62.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.3	153.4
61.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.2	153.3	153.5
60°	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.2	153.3	153.4	153.6
58.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.2	153.3	153.4	153.5	153.7
57.5°	153.0	153.0	153.0	153.0	153.0	153.1	153.2	153.4	153.5	153.6	153.7
56.25°	153.0	153.0	153.0	153.0	153.1	153.2	153.3	153.5	153.6	153.7	153.8
55°	153.0	153.0	153.0	153.0	153.1	153.3	153.4	153.5	153.7	153.8	153.9
53.75°	153.0	153.0	153.0	153.0	153.2	153.3	153.5	153.6	153.8	153.9	154.0
52.5°	153.0	153.0	153.0	153.1	153.3	153.4	153.5	153.7	153.8	154.0	154.1
51.25°	153.0	153.0	153.0	153.2	153.3	153.5	153.6	153.8	153.9	154.1	154.2
50°	153.0	153.0	153.1	153.2	153.4	153.5	153.7	153.8	154.0	154.2	154.3
48.75°	153.0	153.0	153.1	153.3	153.4	153.6	153.8	153.9	154.1	154.2	154.4
47.5°	153.0	153.0	153.2	153.3	153.5	153.7	153.8	154.0	154.2	154.3	154.5
46.25°	153.0	153.1	153.2	153.4	153.6	153.7	153.9	154.1	154.2	154.4	154.6
45°	153.0	153.1	153.3	153.5	153.6	153.8	154.0	154.1	154.3	154.5	154.6
43.75°	153.0	153.2	153.3	153.5	153.7	153.9	154.0	154.2	154.4	154.6	154.7
42.5°	153.0	153.2	153.4	153.6	153.7	153.9	154.1	154.3	154.5	154.6	154.8
41.25°	153.1	153.2	153.4	153.6	153.8	154.0	154.2	154.3	154.5	154.7	154.9
40°	153.1	153.3	153.5	153.7	153.9	154.0	154.2	154.4	154.6	154.8	155.0
38.75°	153.1	153.3	153.5	153.7	153.9	154.1	154.3	154.5	154.7	154.8	155.0
37.5°	153.2	153.4	153.6	153.8	154.0	154.1	154.3	154.5	154.7	154.9	154.9
36.25°	153.2	153.4	153.6	153.8	154.0	154.2	154.4	154.6	154.8	155.0	154.8
35°	153.2	153.4	153.7	153.9	154.1	154.3	154.5	154.7	154.9	154.9	154.8

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	153.3	153.5	153.7	153.9	154.1	154.3	154.5	154.7	154.9	154.9	154.7
32.5°	153.3	153.5	153.7	153.9	154.1	154.4	154.6	154.8	155.0	154.8	154.6
31.25°	153.3	153.6	153.8	154.0	154.2	154.4	154.6	154.8	155.0	154.8	154.6
30°	153.4	153.6	153.8	154.0	154.2	154.4	154.7	154.9	154.9	154.7	154.5
28.75°	153.4	153.6	153.8	154.1	154.3	154.5	154.7	154.9	154.9	154.7	154.4
27.5°	153.4	153.7	153.9	154.1	154.3	154.5	154.8	155.0	154.8	154.6	154.4
26.25°	153.5	153.7	153.9	154.1	154.4	154.6	154.8	155.0	154.8	154.5	154.3
25°	153.5	153.7	153.9	154.2	154.4	154.6	154.8	154.9	154.7	154.5	154.3
23.75°	153.5	153.7	154.0	154.2	154.4	154.6	154.9	154.9	154.7	154.4	154.2
22.5°	153.5	153.8	154.0	154.2	154.5	154.7	154.9	154.9	154.6	154.4	154.2
21.25°	153.6	153.8	154.0	154.3	154.5	154.7	154.9	154.8	154.6	154.4	154.1
20°	153.6	153.8	154.0	154.3	154.5	154.7	155.0	154.8	154.6	154.3	154.1
18.75°	153.6	153.8	154.1	154.3	154.5	154.8	155.0	154.8	154.5	154.3	154.0
17.5°	153.6	153.9	154.1	154.3	154.6	154.8	155.0	154.7	154.5	154.2	154.0
16.25°	153.6	153.9	154.1	154.4	154.6	154.8	154.9	154.7	154.5	154.2	154.1
15°	153.7	153.9	154.1	154.4	154.6	154.9	154.9	154.7	154.4	154.2	154.2
13.75°	153.7	153.9	154.2	154.4	154.6	154.9	154.9	154.6	154.4	154.2	154.3
12.5°	153.7	153.9	154.2	154.4	154.7	154.9	154.9	154.6	154.4	154.1	154.3
11.25°	153.7	153.9	154.2	154.4	154.7	154.9	154.8	154.6	154.3	154.1	154.4
10°	153.7	154.0	154.2	154.4	154.7	154.9	154.8	154.6	154.3	154.1	154.5
8.75°	153.7	154.0	154.2	154.5	154.7	155.0	154.8	154.6	154.3	154.1	154.6
7.5°	153.7	154.0	154.2	154.5	154.7	155.0	154.8	154.5	154.3	154.0	154.6
6.25°	153.7	154.0	154.2	154.5	154.7	155.0	154.8	154.5	154.3	154.0	154.6
5°	153.7	154.0	154.2	154.5	154.7	155.0	154.8	154.5	154.3	154.0	154.7
3.75°	153.7	154.0	154.2	154.5	154.7	155.0	154.8	154.5	154.3	154.0	154.7
2.5°	153.7	154.0	154.2	154.5	154.7	155.0	154.8	154.5	154.3	154.0	154.7
1.25°	153.7	154.0	154.2	154.5	154.7	155.0	154.8	154.5	154.3	154.0	154.7
0°	153.8	154.0	154.3	154.5	154.8	155.0	154.8	154.5	154.3	154.0	154.8
-1.25°	153.7	154.0	154.2	154.5	154.7	155.0	154.8	154.5	154.3	154.0	154.7
-2.5°	153.7	154.0	154.2	154.5	154.7	155.0	154.8	154.5	154.3	154.0	154.7
-3.75°	153.7	154.0	154.2	154.5	154.7	155.0	154.8	154.5	154.3	154.0	154.7
-5°	153.7	154.0	154.2	154.5	154.7	155.0	154.8	154.5	154.3	154.0	154.7
-6.25°	153.7	154.0	154.2	154.5	154.7	155.0	154.8	154.5	154.3	154.0	154.6
-7.5°	153.7	154.0	154.2	154.5	154.7	155.0	154.8	154.5	154.3	154.0	154.6
-8.75°	153.7	154.0	154.2	154.5	154.7	155.0	154.8	154.6	154.3	154.1	154.6
-10°	153.7	154.0	154.2	154.4	154.7	154.9	154.8	154.6	154.3	154.1	154.5
-11.25°	153.7	153.9	154.2	154.4	154.7	154.9	154.8	154.6	154.3	154.1	154.4
-12.5°	153.7	153.9	154.2	154.4	154.7	154.9	154.9	154.6	154.4	154.1	154.3
-13.75°	153.7	153.9	154.2	154.4	154.6	154.9	154.9	154.6	154.4	154.2	154.3
-15°	153.7	153.9	154.1	154.4	154.6	154.9	154.9	154.7	154.4	154.2	154.2
-16.25°	153.6	153.9	154.1	154.4	154.6	154.8	154.9	154.7	154.5	154.2	154.1
-17.5°	153.6	153.9	154.1	154.3	154.6	154.8	155.0	154.7	154.5	154.2	154.0
-18.75°	153.6	153.8	154.1	154.3	154.5	154.8	155.0	154.8	154.5	154.3	154.0
-20°	153.6	153.8	154.0	154.3	154.5	154.7	155.0	154.8	154.6	154.3	154.1
-21.25°	153.6	153.8	154.0	154.3	154.5	154.7	154.9	154.8	154.6	154.4	154.1

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	153.5	153.8	154.0	154.2	154.5	154.7	154.9	154.9	154.6	154.4	154.2
-23.75°	153.5	153.7	154.0	154.2	154.4	154.6	154.9	154.9	154.7	154.4	154.2
-25°	153.5	153.7	153.9	154.2	154.4	154.6	154.8	154.9	154.7	154.5	154.3
-26.25°	153.5	153.7	153.9	154.1	154.4	154.6	154.8	155.0	154.8	154.5	154.3
-27.5°	153.4	153.7	153.9	154.1	154.3	154.5	154.8	155.0	154.8	154.6	154.4
-28.75°	153.4	153.6	153.8	154.1	154.3	154.5	154.7	154.9	154.9	154.7	154.4
-30°	153.4	153.6	153.8	154.0	154.2	154.4	154.7	154.9	154.9	154.7	154.5
-31.25°	153.3	153.6	153.8	154.0	154.2	154.4	154.6	154.8	155.0	154.8	154.6
-32.5°	153.3	153.5	153.7	153.9	154.1	154.4	154.6	154.8	155.0	154.8	154.6
-33.75°	153.3	153.5	153.7	153.9	154.1	154.3	154.5	154.7	154.9	154.9	154.7
-35°	153.2	153.4	153.7	153.9	154.1	154.3	154.5	154.7	154.9	154.9	154.8
-36.25°	153.2	153.4	153.6	153.8	154.0	154.2	154.4	154.6	154.8	155.0	154.8
-37.5°	153.2	153.4	153.6	153.8	154.0	154.1	154.3	154.5	154.7	154.9	154.9
-38.75°	153.1	153.3	153.5	153.7	153.9	154.1	154.3	154.5	154.7	154.8	155.0
-40°	153.1	153.3	153.5	153.7	153.9	154.0	154.2	154.4	154.6	154.8	155.0
-41.25°	153.1	153.2	153.4	153.6	153.8	154.0	154.2	154.3	154.5	154.7	154.9
-42.5°	153.0	153.2	153.4	153.6	153.7	153.9	154.1	154.3	154.5	154.6	154.8
-43.75°	153.0	153.2	153.3	153.5	153.7	153.9	154.0	154.2	154.4	154.6	154.7
-45°	153.0	153.1	153.3	153.5	153.6	153.8	154.0	154.1	154.3	154.5	154.6
-46.25°	153.0	153.1	153.2	153.4	153.6	153.7	153.9	154.1	154.2	154.4	154.6
-47.5°	153.0	153.0	153.2	153.3	153.5	153.7	153.8	154.0	154.2	154.3	154.5
-48.75°	153.0	153.0	153.1	153.3	153.4	153.6	153.8	153.9	154.1	154.2	154.4
-50°	153.0	153.0	153.1	153.2	153.4	153.5	153.7	153.8	154.0	154.2	154.3
-51.25°	153.0	153.0	153.0	153.2	153.3	153.5	153.6	153.8	153.9	154.1	154.2
-52.5°	153.0	153.0	153.0	153.1	153.3	153.4	153.5	153.7	153.8	154.0	154.1
-53.75°	153.0	153.0	153.0	153.0	153.2	153.3	153.5	153.6	153.8	153.9	154.0
-55°	153.0	153.0	153.0	153.0	153.1	153.3	153.4	153.5	153.7	153.8	153.9
-56.25°	153.0	153.0	153.0	153.0	153.1	153.2	153.3	153.5	153.6	153.7	153.8
-57.5°	153.0	153.0	153.0	153.0	153.0	153.1	153.2	153.4	153.5	153.6	153.7
-58.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.2	153.3	153.4	153.5	153.7
-60°	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.2	153.3	153.4	153.6
-61.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.2	153.3	153.5
-62.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.3	153.4
-63.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.2	153.3
-65°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.2
-66.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1
-67.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-68.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-70°	153.3	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-71.25°	153.5	153.2	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-72.5°	153.7	153.4	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-73.75°	153.9	153.7	153.4	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-75°	154.2	153.9	153.7	153.4	153.2	153.0	153.0	153.0	153.0	153.0	153.0
-76.25°	154.4	154.2	153.9	153.7	153.5	153.3	153.0	153.0	153.0	153.0	153.0
-77.5°	154.6	154.4	154.2	154.0	153.8	153.6	153.4	153.2	153.0	153.0	153.0



REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	154.9	154.7	154.5	154.3	154.1	153.9	153.8	153.6	153.4	153.2	153.0
-80°	155.1	154.9	154.8	154.6	154.4	154.3	154.1	154.0	153.8	153.6	153.5
-81.25°	155.3	155.2	155.0	154.9	154.8	154.6	154.5	154.3	154.2	154.1	153.9
-82.5°	155.6	155.5	155.3	155.2	155.1	155.0	154.8	154.7	154.6	154.5	154.4
-83.75°	155.8	155.7	155.6	155.5	155.4	155.3	155.2	155.1	155.0	154.9	154.8
-85°	156.1	156.0	155.9	155.8	155.7	155.6	155.6	155.5	155.4	155.3	155.2
-86.25°	156.3	156.2	156.2	156.1	156.0	156.0	155.9	155.9	155.8	155.7	155.7
-87.5°	156.5	156.5	156.4	156.4	156.4	156.3	156.3	156.2	156.2	156.2	156.1
-88.75°	156.8	156.7	156.7	156.7	156.7	156.7	156.6	156.6	156.6	156.6	156.6
-90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
88.75°	156.5	156.5	156.5	156.5	156.5	156.4	156.4	156.4	156.4	156.4	156.4
87.5°	156.1	156.0	156.0	156.0	155.9	155.9	155.9	155.8	155.8	155.7	155.7
86.25°	155.6	155.6	155.5	155.4	155.4	155.3	155.3	155.2	155.2	155.1	155.1
85°	155.2	155.1	155.0	154.9	154.9	154.8	154.7	154.6	154.6	154.5	154.4
83.75°	154.7	154.6	154.5	154.4	154.3	154.2	154.1	154.0	154.0	153.9	153.8
82.5°	154.2	154.1	154.0	153.9	153.8	153.7	153.6	153.5	153.4	153.3	153.1
81.25°	153.8	153.6	153.5	153.4	153.2	153.1	153.0	153.0	153.0	153.0	153.0
80°	153.3	153.2	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
78.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
77.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
76.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
73.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1
72.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.2	153.2
71.25°	153.0	153.0	153.0	153.0	153.0	153.1	153.1	153.2	153.3	153.3	153.4
70°	153.0	153.0	153.0	153.0	153.1	153.2	153.3	153.3	153.4	153.5	153.5
68.75°	153.0	153.0	153.1	153.2	153.2	153.3	153.4	153.5	153.5	153.6	153.7
67.5°	153.0	153.1	153.2	153.3	153.4	153.5	153.5	153.6	153.7	153.8	153.8
66.25°	153.1	153.2	153.3	153.4	153.5	153.6	153.7	153.8	153.8	153.9	154.0
65°	153.3	153.3	153.4	153.5	153.6	153.7	153.8	153.9	154.0	154.1	154.2
63.75°	153.4	153.5	153.6	153.7	153.7	153.8	153.9	154.0	154.1	154.2	154.3
62.5°	153.5	153.6	153.7	153.8	153.9	154.0	154.1	154.2	154.3	154.4	154.5
61.25°	153.6	153.7	153.8	153.9	154.0	154.1	154.2	154.3	154.4	154.5	154.6
60°	153.7	153.8	153.9	154.0	154.1	154.2	154.3	154.4	154.5	154.6	154.7
58.75°	153.8	153.9	154.0	154.1	154.2	154.4	154.5	154.6	154.7	154.8	154.9
57.5°	153.9	154.0	154.1	154.2	154.4	154.5	154.6	154.7	154.8	154.9	155.0
56.25°	154.0	154.1	154.2	154.4	154.5	154.6	154.7	154.8	155.0	154.9	154.8
55°	154.1	154.2	154.3	154.5	154.6	154.7	154.8	155.0	154.9	154.8	154.7
53.75°	154.2	154.3	154.4	154.6	154.7	154.8	155.0	154.9	154.8	154.7	154.5
52.5°	154.3	154.4	154.5	154.7	154.8	155.0	154.9	154.8	154.6	154.5	154.4
51.25°	154.4	154.5	154.6	154.8	154.9	154.9	154.8	154.7	154.5	154.4	154.3
50°	154.5	154.6	154.7	154.9	155.0	154.8	154.7	154.5	154.4	154.3	154.1
48.75°	154.5	154.7	154.8	155.0	154.9	154.7	154.6	154.4	154.3	154.1	154.0
47.5°	154.6	154.8	154.9	154.9	154.7	154.6	154.4	154.3	154.1	154.0	154.4
46.25°	154.7	154.9	155.0	154.8	154.6	154.5	154.3	154.2	154.0	154.4	154.8
45°	154.8	155.0	154.9	154.7	154.5	154.4	154.2	154.1	154.3	154.8	155.2
43.75°	154.9	154.9	154.8	154.6	154.4	154.3	154.1	154.2	154.7	155.1	155.6
42.5°	155.0	154.8	154.7	154.5	154.3	154.2	154.0	154.5	155.0	155.5	156.0
41.25°	154.9	154.8	154.6	154.4	154.2	154.1	154.3	154.8	155.3	155.8	156.3
40°	154.9	154.7	154.5	154.3	154.1	154.1	154.6	155.2	155.7	156.2	156.7
38.75°	154.8	154.6	154.4	154.2	154.0	154.4	154.9	155.5	156.0	156.5	157.0
37.5°	154.7	154.5	154.3	154.1	154.1	154.7	155.2	155.8	156.3	156.9	157.0
36.25°	154.6	154.4	154.2	154.1	154.4	155.0	155.5	156.1	156.6	157.0	157.0
35°	154.6	154.4	154.2	154.1	154.7	155.2	155.8	156.4	156.9	157.0	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	154.5	154.3	154.1	154.3	154.9	155.5	156.1	156.7	157.0	157.0	157.0
32.5°	154.4	154.2	154.0	154.6	155.2	155.8	156.4	156.9	157.0	157.0	157.0
31.25°	154.3	154.1	154.2	154.8	155.4	156.0	156.6	157.0	157.0	157.0	157.0
30°	154.3	154.1	154.4	155.0	155.6	156.3	156.9	157.0	157.0	157.0	157.0
28.75°	154.2	154.0	154.6	155.2	155.9	156.5	157.0	157.0	157.0	157.0	157.0
27.5°	154.2	154.2	154.8	155.4	156.1	156.7	157.0	157.0	157.0	157.0	157.0
26.25°	154.1	154.3	155.0	155.6	156.3	156.9	157.0	157.0	157.0	157.0	157.5
25°	154.1	154.5	155.2	155.8	156.5	157.0	157.0	157.0	157.0	157.0	158.6
23.75°	154.0	154.7	155.3	156.0	156.7	157.0	157.0	157.0	157.0	157.0	159.7
22.5°	154.2	154.8	155.5	156.2	156.9	157.0	157.0	157.0	157.0	157.9	160.7
21.25°	154.3	155.0	155.7	156.3	157.0	157.0	157.0	157.0	157.0	158.8	161.7
20°	154.4	155.1	155.8	156.5	157.0	157.0	157.0	157.0	157.0	159.7	162.6
18.75°	154.6	155.3	156.0	156.7	157.0	157.0	157.0	157.0	157.5	160.5	163.5
17.5°	154.7	155.4	156.1	156.8	157.0	157.0	157.0	157.0	158.3	161.3	164.3
16.25°	154.8	155.5	156.2	156.9	157.0	157.0	157.0	157.0	159.0	162.0	165.1
15°	154.9	155.6	156.3	157.0	157.0	157.0	157.0	157.0	159.6	162.7	165.8
13.75°	155.0	155.7	156.4	157.0	157.0	157.0	157.0	157.1	160.3	163.4	166.5
12.5°	155.1	155.8	156.5	157.0	157.0	157.0	157.0	157.7	160.8	163.9	167.1
11.25°	155.2	155.9	156.6	157.0	157.0	157.0	157.0	158.2	161.3	164.5	167.6
10°	155.2	156.0	156.7	157.0	157.0	157.0	157.0	158.6	161.8	164.9	168.1
8.75°	155.3	156.0	156.8	157.0	157.0	157.0	157.0	159.0	162.2	165.4	168.6
7.5°	155.3	156.1	156.8	157.0	157.0	157.0	157.0	159.3	162.5	165.7	168.9
6.25°	155.4	156.1	156.9	157.0	157.0	157.0	157.0	159.6	162.8	166.0	169.3
5°	155.4	156.2	156.9	157.0	157.0	157.0	157.0	159.8	163.1	166.3	169.5
3.75°	155.5	156.2	157.0	157.0	157.0	157.0	157.0	160.0	163.3	166.5	169.7
2.5°	155.5	156.2	157.0	157.0	157.0	157.0	157.0	160.1	163.4	166.6	169.9
1.25°	155.5	156.2	157.0	157.0	157.0	157.0	157.0	160.2	163.5	166.7	170.0
0°	155.5	156.3	157.0	157.0	157.0	157.0	157.0	160.3	163.5	166.8	170.0
-1.25°	155.5	156.2	157.0	157.0	157.0	157.0	157.0	160.2	163.5	166.7	170.0
-2.5°	155.5	156.2	157.0	157.0	157.0	157.0	157.0	160.1	163.4	166.6	169.9
-3.75°	155.5	156.2	157.0	157.0	157.0	157.0	157.0	160.0	163.3	166.5	169.7
-5°	155.4	156.2	156.9	157.0	157.0	157.0	157.0	159.8	163.1	166.3	169.5
-6.25°	155.4	156.1	156.9	157.0	157.0	157.0	157.0	159.6	162.8	166.0	169.3
-7.5°	155.3	156.1	156.8	157.0	157.0	157.0	157.0	159.3	162.5	165.7	168.9
-8.75°	155.3	156.0	156.8	157.0	157.0	157.0	157.0	159.0	162.2	165.4	168.6
-10°	155.2	156.0	156.7	157.0	157.0	157.0	157.0	158.6	161.8	164.9	168.1
-11.25°	155.2	155.9	156.6	157.0	157.0	157.0	157.0	158.2	161.3	164.5	167.6
-12.5°	155.1	155.8	156.5	157.0	157.0	157.0	157.0	157.7	160.8	163.9	167.1
-13.75°	155.0	155.7	156.4	157.0	157.0	157.0	157.0	157.1	160.3	163.4	166.5
-15°	154.9	155.6	156.3	157.0	157.0	157.0	157.0	157.0	159.6	162.7	165.8
-16.25°	154.8	155.5	156.2	156.9	157.0	157.0	157.0	157.0	159.0	162.0	165.1
-17.5°	154.7	155.4	156.1	156.8	157.0	157.0	157.0	157.0	158.3	161.3	164.3
-18.75°	154.6	155.3	156.0	156.7	157.0	157.0	157.0	157.0	157.5	160.5	163.5
-20°	154.4	155.1	155.8	156.5	157.0	157.0	157.0	157.0	157.0	159.7	162.6
-21.25°	154.3	155.0	155.7	156.3	157.0	157.0	157.0	157.0	157.0	158.8	161.7

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	154.2	154.8	155.5	156.2	156.9	157.0	157.0	157.0	157.0	157.9	160.7
-23.75°	154.0	154.7	155.3	156.0	156.7	157.0	157.0	157.0	157.0	157.0	159.7
-25°	154.1	154.5	155.2	155.8	156.5	157.0	157.0	157.0	157.0	157.0	158.6
-26.25°	154.1	154.3	155.0	155.6	156.3	156.9	157.0	157.0	157.0	157.0	157.5
-27.5°	154.2	154.2	154.8	155.4	156.1	156.7	157.0	157.0	157.0	157.0	157.0
-28.75°	154.2	154.0	154.6	155.2	155.9	156.5	157.0	157.0	157.0	157.0	157.0
-30°	154.3	154.1	154.4	155.0	155.6	156.3	156.9	157.0	157.0	157.0	157.0
-31.25°	154.3	154.1	154.2	154.8	155.4	156.0	156.6	157.0	157.0	157.0	157.0
-32.5°	154.4	154.2	154.0	154.6	155.2	155.8	156.4	156.9	157.0	157.0	157.0
-33.75°	154.5	154.3	154.1	154.3	154.9	155.5	156.1	156.7	157.0	157.0	157.0
-35°	154.6	154.4	154.2	154.1	154.7	155.2	155.8	156.4	156.9	157.0	157.0
-36.25°	154.6	154.4	154.2	154.1	154.4	155.0	155.5	156.1	156.6	157.0	157.0
-37.5°	154.7	154.5	154.3	154.1	154.1	154.7	155.2	155.8	156.3	156.9	157.0
-38.75°	154.8	154.6	154.4	154.2	154.0	154.4	154.9	155.5	156.0	156.5	157.0
-40°	154.9	154.7	154.5	154.3	154.1	154.1	154.6	155.2	155.7	156.2	156.7
-41.25°	154.9	154.8	154.6	154.4	154.2	154.1	154.3	154.8	155.3	155.8	156.3
-42.5°	155.0	154.8	154.7	154.5	154.3	154.2	154.0	154.5	155.0	155.5	156.0
-43.75°	154.9	154.9	154.8	154.6	154.4	154.3	154.1	154.2	154.7	155.1	155.6
-45°	154.8	155.0	154.9	154.7	154.5	154.4	154.2	154.1	154.3	154.8	155.2
-46.25°	154.7	154.9	155.0	154.8	154.6	154.5	154.3	154.2	154.0	154.4	154.8
-47.5°	154.6	154.8	154.9	154.9	154.7	154.6	154.4	154.3	154.1	154.0	154.4
-48.75°	154.5	154.7	154.8	155.0	154.9	154.7	154.6	154.4	154.3	154.1	154.0
-50°	154.5	154.6	154.7	154.9	155.0	154.8	154.7	154.5	154.4	154.3	154.1
-51.25°	154.4	154.5	154.6	154.8	154.9	154.9	154.8	154.7	154.5	154.4	154.3
-52.5°	154.3	154.4	154.5	154.7	154.8	155.0	154.9	154.8	154.6	154.5	154.4
-53.75°	154.2	154.3	154.4	154.6	154.7	154.8	155.0	154.9	154.8	154.7	154.5
-55°	154.1	154.2	154.3	154.5	154.6	154.7	154.8	155.0	154.9	154.8	154.7
-56.25°	154.0	154.1	154.2	154.4	154.5	154.6	154.7	154.8	155.0	154.9	154.8
-57.5°	153.9	154.0	154.1	154.2	154.4	154.5	154.6	154.7	154.8	154.9	155.0
-58.75°	153.8	153.9	154.0	154.1	154.2	154.4	154.5	154.6	154.7	154.8	154.9
-60°	153.7	153.8	153.9	154.0	154.1	154.2	154.3	154.4	154.5	154.6	154.7
-61.25°	153.6	153.7	153.8	153.9	154.0	154.1	154.2	154.3	154.4	154.5	154.6
-62.5°	153.5	153.6	153.7	153.8	153.9	154.0	154.1	154.2	154.3	154.4	154.5
-63.75°	153.4	153.5	153.6	153.7	153.7	153.8	153.9	154.0	154.1	154.2	154.3
-65°	153.3	153.3	153.4	153.5	153.6	153.7	153.8	153.9	154.0	154.1	154.2
-66.25°	153.1	153.2	153.3	153.4	153.5	153.6	153.7	153.8	153.8	153.9	154.0
-67.5°	153.0	153.1	153.2	153.3	153.4	153.5	153.5	153.6	153.7	153.8	153.8
-68.75°	153.0	153.0	153.1	153.2	153.2	153.3	153.4	153.5	153.5	153.6	153.7
-70°	153.0	153.0	153.0	153.0	153.1	153.2	153.3	153.3	153.4	153.5	153.5
-71.25°	153.0	153.0	153.0	153.0	153.0	153.1	153.1	153.2	153.3	153.3	153.4
-72.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.2	153.2
-73.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1
-75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-76.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-77.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0



REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-80°	153.3	153.2	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-81.25°	153.8	153.6	153.5	153.4	153.2	153.1	153.0	153.0	153.0	153.0	153.0
-82.5°	154.2	154.1	154.0	153.9	153.8	153.7	153.6	153.5	153.4	153.3	153.1
-83.75°	154.7	154.6	154.5	154.4	154.3	154.2	154.1	154.0	154.0	153.9	153.8
-85°	155.2	155.1	155.0	154.9	154.9	154.8	154.7	154.6	154.6	154.5	154.4
-86.25°	155.6	155.6	155.5	155.4	155.4	155.3	155.3	155.2	155.2	155.1	155.1
-87.5°	156.1	156.0	156.0	156.0	155.9	155.9	155.9	155.8	155.8	155.7	155.7
-88.75°	156.5	156.5	156.5	156.5	156.5	156.4	156.4	156.4	156.4	156.4	156.4
-90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
88.75°	156.3	156.3	156.3	156.3	156.3	156.3	156.2	156.2	156.2	156.2	156.2
87.5°	155.7	155.6	155.6	155.6	155.6	155.5	155.5	155.5	155.4	155.4	155.4
86.25°	155.0	155.0	154.9	154.9	154.8	154.8	154.7	154.7	154.7	154.6	154.6
85°	154.4	154.3	154.2	154.2	154.1	154.1	154.0	153.9	153.9	153.8	153.8
83.75°	153.7	153.6	153.5	153.5	153.4	153.3	153.2	153.2	153.1	153.0	153.0
82.5°	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
78.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
77.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
76.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.1	153.1	153.2	153.2
75°	153.0	153.0	153.1	153.1	153.2	153.2	153.2	153.3	153.3	153.4	153.4
73.75°	153.1	153.2	153.2	153.3	153.3	153.4	153.4	153.5	153.5	153.6	153.6
72.5°	153.3	153.3	153.4	153.5	153.5	153.6	153.6	153.7	153.7	153.8	153.8
71.25°	153.4	153.5	153.6	153.6	153.7	153.7	153.8	153.9	153.9	154.0	154.0
70°	153.6	153.7	153.7	153.8	153.9	153.9	154.0	154.0	154.1	154.1	154.2
68.75°	153.8	153.8	153.9	154.0	154.0	154.1	154.2	154.2	154.3	154.3	154.4
67.5°	153.9	154.0	154.1	154.1	154.2	154.3	154.3	154.4	154.5	154.5	154.6
66.25°	154.1	154.2	154.2	154.3	154.4	154.5	154.5	154.6	154.7	154.7	154.8
65°	154.2	154.3	154.4	154.5	154.6	154.6	154.7	154.8	154.8	154.9	155.0
63.75°	154.4	154.5	154.6	154.6	154.7	154.8	154.9	155.0	155.0	154.9	154.8
62.5°	154.5	154.6	154.7	154.8	154.9	155.0	154.9	154.9	154.8	154.7	154.6
61.25°	154.7	154.8	154.9	155.0	154.9	154.8	154.8	154.7	154.6	154.5	154.4
60°	154.8	154.9	155.0	154.9	154.8	154.7	154.6	154.5	154.4	154.3	154.2
58.75°	155.0	154.9	154.8	154.7	154.6	154.5	154.4	154.3	154.2	154.1	154.1
57.5°	154.9	154.7	154.6	154.5	154.4	154.3	154.2	154.1	154.0	154.1	154.4
56.25°	154.7	154.6	154.5	154.4	154.3	154.2	154.1	154.1	154.4	154.7	155.0
55°	154.6	154.4	154.3	154.2	154.1	154.0	154.3	154.6	154.9	155.2	155.5
53.75°	154.4	154.3	154.2	154.1	154.2	154.5	154.8	155.2	155.5	155.8	156.1
52.5°	154.3	154.1	154.0	154.3	154.7	155.0	155.3	155.7	156.0	156.3	156.6
51.25°	154.1	154.0	154.4	154.8	155.1	155.5	155.8	156.2	156.5	156.9	157.0
50°	154.0	154.4	154.8	155.2	155.6	156.0	156.3	156.7	157.0	157.0	157.0
48.75°	154.5	154.9	155.3	155.7	156.1	156.5	156.8	157.0	157.0	157.0	157.0
47.5°	154.9	155.3	155.7	156.1	156.5	156.9	157.0	157.0	157.0	157.0	157.0
46.25°	155.3	155.7	156.1	156.6	157.0	157.0	157.0	157.0	157.0	157.0	157.0
45°	155.7	156.1	156.6	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
43.75°	156.1	156.5	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	158.6
42.5°	156.5	156.9	157.0	157.0	157.0	157.0	157.0	157.0	157.3	159.1	160.9
41.25°	156.8	157.0	157.0	157.0	157.0	157.0	157.0	157.4	159.3	161.2	163.0
40°	157.0	157.0	157.0	157.0	157.0	157.0	157.4	159.4	161.4	163.3	165.2
38.75°	157.0	157.0	157.0	157.0	157.0	157.3	159.3	161.4	163.4	165.4	167.3
37.5°	157.0	157.0	157.0	157.0	157.0	159.1	161.2	163.3	165.4	167.4	169.4
36.25°	157.0	157.0	157.0	157.0	158.6	160.9	163.0	165.2	167.3	169.4	180.2
35°	157.0	157.0	157.0	158.0	160.3	162.6	164.8	167.1	169.2	179.6	194.2

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	157.0	157.0	157.3	159.6	162.0	164.3	166.6	168.9	177.6	192.9	207.9
32.5°	157.0	157.0	158.8	161.2	163.6	166.0	168.3	174.4	190.3	206.0	221.4
31.25°	157.0	157.7	160.2	162.7	165.2	167.6	170.0	186.4	202.7	218.7	234.5
30°	157.0	159.1	161.7	164.2	166.7	169.2	181.3	198.1	214.7	231.2	247.4
28.75°	157.8	160.4	163.0	165.6	168.2	174.9	192.2	209.4	226.5	243.3	259.9
27.5°	159.1	161.7	164.4	167.0	169.6	185.2	202.9	220.5	237.9	255.1	262.4
26.25°	160.3	163.0	165.7	168.3	176.9	195.1	213.2	231.1	248.9	261.3	264.8
25°	161.4	164.2	166.9	169.6	186.1	204.7	223.2	241.4	259.6	263.5	267.1
23.75°	162.5	165.3	168.1	176.0	195.0	213.9	232.7	251.4	262.0	265.6	269.3
22.5°	163.6	166.4	169.2	184.2	203.6	222.8	241.9	260.2	264.0	267.7	271.4
21.25°	164.6	167.5	172.3	192.1	211.7	231.3	250.7	262.0	265.8	269.7	273.4
20°	165.5	168.5	179.5	199.5	219.5	239.4	259.1	263.8	267.7	271.5	275.4
18.75°	166.5	169.4	186.3	206.6	226.9	247.0	261.4	265.4	269.4	273.3	277.2
17.5°	167.3	172.1	192.7	213.3	233.8	254.3	262.9	267.0	271.0	275.0	277.9
16.25°	168.1	177.9	198.7	219.6	240.3	260.2	264.3	268.4	272.5	276.6	277.7
15°	168.9	183.2	204.4	225.4	246.4	261.5	265.7	269.8	274.0	278.0	277.5
13.75°	169.5	188.2	209.6	230.9	252.1	262.7	266.9	271.1	275.3	277.8	277.4
12.5°	171.3	192.8	214.3	235.8	257.3	263.7	268.0	272.3	276.5	277.7	277.2
11.25°	175.2	197.0	218.7	240.4	260.4	264.7	269.0	273.3	277.6	277.6	277.1
10°	178.8	200.7	222.6	244.4	261.3	265.6	270.0	274.3	277.9	277.4	277.0
8.75°	182.0	204.1	226.1	248.1	262.0	266.4	270.8	275.2	277.8	277.3	276.9
7.5°	184.8	206.9	229.1	251.2	262.7	267.1	271.5	275.9	277.7	277.3	276.8
6.25°	187.1	209.4	231.6	253.9	263.2	267.7	272.1	276.5	277.7	277.2	276.7
5°	189.1	211.4	233.7	256.1	263.7	268.1	272.6	277.1	277.6	277.1	276.6
3.75°	190.6	213.0	235.4	257.8	264.0	268.5	273.0	277.5	277.6	277.1	276.6
2.5°	191.6	214.1	236.6	259.0	264.3	268.8	273.3	277.8	277.5	277.0	276.5
1.25°	192.3	214.8	237.3	259.8	264.4	268.9	273.4	277.9	277.5	277.0	276.5
0°	192.5	215.0	237.5	260.0	264.5	269.0	273.5	278.0	277.5	277.0	276.5
-1.25°	192.3	214.8	237.3	259.8	264.4	268.9	273.4	277.9	277.5	277.0	276.5
-2.5°	191.6	214.1	236.6	259.0	264.3	268.8	273.3	277.8	277.5	277.0	276.5
-3.75°	190.6	213.0	235.4	257.8	264.0	268.5	273.0	277.5	277.6	277.1	276.6
-5°	189.1	211.4	233.7	256.1	263.7	268.1	272.6	277.1	277.6	277.1	276.6
-6.25°	187.1	209.4	231.6	253.9	263.2	267.7	272.1	276.5	277.7	277.2	276.7
-7.5°	184.8	206.9	229.1	251.2	262.7	267.1	271.5	275.9	277.7	277.3	276.8
-8.75°	182.0	204.1	226.1	248.1	262.0	266.4	270.8	275.2	277.8	277.3	276.9
-10°	178.8	200.7	222.6	244.4	261.3	265.6	270.0	274.3	277.9	277.4	277.0
-11.25°	175.2	197.0	218.7	240.4	260.4	264.7	269.0	273.3	277.6	277.6	277.1
-12.5°	171.3	192.8	214.3	235.8	257.3	263.7	268.0	272.3	276.5	277.7	277.2
-13.75°	169.5	188.2	209.6	230.9	252.1	262.7	266.9	271.1	275.3	277.8	277.4
-15°	168.9	183.2	204.4	225.4	246.4	261.5	265.7	269.8	274.0	278.0	277.5
-16.25°	168.1	177.9	198.7	219.6	240.3	260.2	264.3	268.4	272.5	276.6	277.7
-17.5°	167.3	172.1	192.7	213.3	233.8	254.3	262.9	267.0	271.0	275.0	277.9
-18.75°	166.5	169.4	186.3	206.6	226.9	247.0	261.4	265.4	269.4	273.3	277.2
-20°	165.5	168.5	179.5	199.5	219.5	239.4	259.1	263.8	267.7	271.5	275.4
-21.25°	164.6	167.5	172.3	192.1	211.7	231.3	250.7	262.0	265.8	269.7	273.4

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	163.6	166.4	169.2	184.2	203.6	222.8	241.9	260.2	264.0	267.7	271.4
-23.75°	162.5	165.3	168.1	176.0	195.0	213.9	232.7	251.4	262.0	265.6	269.3
-25°	161.4	164.2	166.9	169.6	186.1	204.7	223.2	241.4	259.6	263.5	267.1
-26.25°	160.3	163.0	165.7	168.3	176.9	195.1	213.2	231.1	248.9	261.3	264.8
-27.5°	159.1	161.7	164.4	167.0	169.6	185.2	202.9	220.5	237.9	255.1	262.4
-28.75°	157.8	160.4	163.0	165.6	168.2	174.9	192.2	209.4	226.5	243.3	259.9
-30°	157.0	159.1	161.7	164.2	166.7	169.2	181.3	198.1	214.7	231.2	247.4
-31.25°	157.0	157.7	160.2	162.7	165.2	167.6	170.0	186.4	202.7	218.7	234.5
-32.5°	157.0	157.0	158.8	161.2	163.6	166.0	168.3	174.4	190.3	206.0	221.4
-33.75°	157.0	157.0	157.3	159.6	162.0	164.3	166.6	168.9	177.6	192.9	207.9
-35°	157.0	157.0	157.0	158.0	160.3	162.6	164.8	167.1	169.2	179.6	194.2
-36.25°	157.0	157.0	157.0	157.0	158.6	160.9	163.0	165.2	167.3	169.4	180.2
-37.5°	157.0	157.0	157.0	157.0	157.0	159.1	161.2	163.3	165.4	167.4	169.4
-38.75°	157.0	157.0	157.0	157.0	157.0	157.3	159.3	161.4	163.4	165.4	167.3
-40°	157.0	157.0	157.0	157.0	157.0	157.0	157.4	159.4	161.4	163.3	165.2
-41.25°	156.8	157.0	157.0	157.0	157.0	157.0	157.0	157.4	159.3	161.2	163.0
-42.5°	156.5	156.9	157.0	157.0	157.0	157.0	157.0	157.0	157.3	159.1	160.9
-43.75°	156.1	156.5	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	158.6
-45°	155.7	156.1	156.6	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-46.25°	155.3	155.7	156.1	156.6	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-47.5°	154.9	155.3	155.7	156.1	156.5	156.9	157.0	157.0	157.0	157.0	157.0
-48.75°	154.5	154.9	155.3	155.7	156.1	156.5	156.8	157.0	157.0	157.0	157.0
-50°	154.0	154.4	154.8	155.2	155.6	156.0	156.3	156.7	157.0	157.0	157.0
-51.25°	154.1	154.0	154.4	154.8	155.1	155.5	155.8	156.2	156.5	156.9	157.0
-52.5°	154.3	154.1	154.0	154.3	154.7	155.0	155.3	155.7	156.0	156.3	156.6
-53.75°	154.4	154.3	154.2	154.1	154.2	154.5	154.8	155.2	155.5	155.8	156.1
-55°	154.6	154.4	154.3	154.2	154.1	154.0	154.3	154.6	154.9	155.2	155.5
-56.25°	154.7	154.6	154.5	154.4	154.3	154.2	154.1	154.1	154.4	154.7	155.0
-57.5°	154.9	154.7	154.6	154.5	154.4	154.3	154.2	154.1	154.0	154.1	154.4
-58.75°	155.0	154.9	154.8	154.7	154.6	154.5	154.4	154.3	154.2	154.1	154.1
-60°	154.8	154.9	155.0	154.9	154.8	154.7	154.6	154.5	154.4	154.3	154.2
-61.25°	154.7	154.8	154.9	155.0	154.9	154.8	154.8	154.7	154.6	154.5	154.4
-62.5°	154.5	154.6	154.7	154.8	154.9	155.0	154.9	154.9	154.8	154.7	154.6
-63.75°	154.4	154.5	154.6	154.6	154.7	154.8	154.9	155.0	155.0	154.9	154.8
-65°	154.2	154.3	154.4	154.5	154.6	154.6	154.7	154.8	154.8	154.9	155.0
-66.25°	154.1	154.2	154.2	154.3	154.4	154.5	154.5	154.6	154.7	154.7	154.8
-67.5°	153.9	154.0	154.1	154.1	154.2	154.3	154.3	154.4	154.5	154.5	154.6
-68.75°	153.8	153.8	153.9	154.0	154.0	154.1	154.2	154.2	154.3	154.3	154.4
-70°	153.6	153.7	153.7	153.8	153.9	153.9	154.0	154.0	154.1	154.1	154.2
-71.25°	153.4	153.5	153.6	153.6	153.7	153.7	153.8	153.9	153.9	154.0	154.0
-72.5°	153.3	153.3	153.4	153.5	153.5	153.6	153.6	153.7	153.7	153.8	153.8
-73.75°	153.1	153.2	153.2	153.3	153.3	153.4	153.4	153.5	153.5	153.6	153.6
-75°	153.0	153.0	153.1	153.1	153.2	153.2	153.2	153.3	153.3	153.4	153.4
-76.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.1	153.1	153.2	153.2
-77.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-82.5°	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-83.75°	153.7	153.6	153.5	153.5	153.4	153.3	153.2	153.2	153.1	153.0	153.0
-85°	154.4	154.3	154.2	154.2	154.1	154.1	154.0	153.9	153.9	153.8	153.8
-86.25°	155.0	155.0	154.9	154.9	154.8	154.8	154.7	154.7	154.7	154.6	154.6
-87.5°	155.7	155.6	155.6	155.6	155.6	155.5	155.5	155.5	155.4	155.4	155.4
-88.75°	156.3	156.3	156.3	156.3	156.3	156.3	156.2	156.2	156.2	156.2	156.2
-90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
88.75°	156.2	156.2	156.2	156.1	156.1	156.1	156.1	156.1	156.1	156.1	156.1
87.5°	155.4	155.3	155.3	155.3	155.3	155.2	155.2	155.2	155.2	155.2	155.2
86.25°	154.5	154.5	154.5	154.4	154.4	154.4	154.3	154.3	154.3	154.3	154.2
85°	153.7	153.7	153.6	153.6	153.5	153.5	153.5	153.4	153.4	153.3	153.3
83.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
82.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
78.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.1
77.5°	153.0	153.1	153.1	153.1	153.2	153.2	153.2	153.2	153.3	153.3	153.3
76.25°	153.2	153.3	153.3	153.3	153.4	153.4	153.4	153.5	153.5	153.5	153.5
75°	153.4	153.5	153.5	153.6	153.6	153.6	153.7	153.7	153.7	153.7	153.8
73.75°	153.7	153.7	153.7	153.8	153.8	153.8	153.9	153.9	153.9	154.0	154.0
72.5°	153.9	153.9	153.9	154.0	154.0	154.1	154.1	154.1	154.2	154.2	154.2
71.25°	154.1	154.1	154.1	154.2	154.2	154.3	154.3	154.4	154.4	154.4	154.5
70°	154.3	154.3	154.4	154.4	154.4	154.5	154.5	154.6	154.6	154.6	154.7
68.75°	154.5	154.5	154.6	154.6	154.7	154.7	154.8	154.8	154.8	154.9	154.9
67.5°	154.7	154.7	154.8	154.8	154.9	154.9	155.0	155.0	154.9	154.9	154.9
66.25°	154.9	154.9	155.0	155.0	154.9	154.9	154.8	154.8	154.7	154.7	154.6
65°	154.9	154.9	154.8	154.8	154.7	154.7	154.6	154.5	154.5	154.4	154.4
63.75°	154.8	154.7	154.6	154.6	154.5	154.4	154.4	154.3	154.3	154.2	154.2
62.5°	154.6	154.5	154.4	154.3	154.3	154.2	154.2	154.1	154.1	154.0	154.2
61.25°	154.4	154.3	154.2	154.1	154.1	154.0	154.2	154.3	154.5	154.7	154.8
60°	154.2	154.1	154.0	154.2	154.4	154.6	154.8	155.0	155.2	155.3	155.5
58.75°	154.1	154.3	154.6	154.8	155.0	155.2	155.4	155.6	155.8	156.0	156.2
57.5°	154.7	154.9	155.2	155.4	155.6	155.9	156.1	156.3	156.5	156.7	156.9
56.25°	155.2	155.5	155.8	156.0	156.3	156.5	156.7	156.9	157.0	157.0	157.0
55°	155.8	156.1	156.4	156.6	156.9	157.0	157.0	157.0	157.0	157.0	157.0
53.75°	156.4	156.7	156.9	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
52.5°	156.9	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
51.25°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.9
50°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.5	158.6	159.7	160.7
48.75°	157.0	157.0	157.0	157.0	157.0	157.8	159.1	160.3	161.4	162.5	163.6
47.5°	157.0	157.0	157.0	157.7	159.1	160.4	161.7	163.0	164.2	165.3	166.4
46.25°	157.0	157.3	158.8	160.2	161.7	163.0	164.4	165.7	166.9	168.1	169.2
45°	158.0	159.6	161.2	162.7	164.2	165.6	167.0	168.3	169.6	176.0	184.2
43.75°	160.3	162.0	163.6	165.2	166.7	168.2	169.6	176.9	186.1	195.0	203.6
42.5°	162.6	164.3	166.0	167.6	169.2	174.9	185.2	195.1	204.7	213.9	222.8
41.25°	164.8	166.6	168.3	170.0	181.3	192.2	202.9	213.2	223.2	232.7	241.9
40°	167.1	168.9	174.4	186.4	198.1	209.4	220.5	231.1	241.4	251.4	260.2
38.75°	169.2	177.6	190.3	202.7	214.7	226.5	237.9	248.9	259.6	262.0	264.0
37.5°	179.6	192.9	206.0	218.7	231.2	243.3	255.1	261.3	263.5	265.6	267.7
36.25°	194.2	207.9	221.4	234.5	247.4	259.9	262.4	264.8	267.1	269.3	271.4
35°	208.6	222.7	236.6	250.1	260.7	263.3	265.8	268.2	270.6	272.9	275.1

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	222.7	237.3	251.5	261.1	263.8	266.5	269.1	271.6	274.0	276.4	277.9
32.5°	236.6	251.5	261.2	264.1	266.9	269.7	272.3	274.9	277.5	277.8	277.5
31.25°	250.1	261.1	264.1	267.1	269.9	272.8	275.5	278.0	277.7	277.4	277.1
30°	260.7	263.8	266.9	269.9	272.9	275.8	277.9	277.6	277.3	277.0	276.7
28.75°	263.3	266.5	269.7	272.8	275.8	277.9	277.6	277.3	277.0	276.7	276.4
27.5°	265.8	269.1	272.3	275.5	277.9	277.6	277.2	276.9	276.6	276.3	276.1
26.25°	268.2	271.6	274.9	278.0	277.6	277.3	276.9	276.6	276.3	276.3	277.5
25°	270.6	274.0	277.5	277.7	277.3	277.0	276.6	276.3	276.4	277.7	279.0
23.75°	272.9	276.4	277.8	277.4	277.0	276.7	276.3	276.3	277.7	279.1	280.4
22.5°	275.1	277.9	277.5	277.1	276.7	276.4	276.1	277.5	279.0	280.4	281.8
21.25°	277.2	277.7	277.3	276.9	276.5	276.1	277.2	278.7	280.2	281.7	283.1
20°	277.9	277.4	277.0	276.6	276.2	276.8	278.3	279.9	281.4	282.9	285.1
18.75°	277.7	277.2	276.8	276.4	276.1	277.8	279.4	281.0	282.6	284.4	288.5
17.5°	277.5	277.0	276.6	276.2	277.1	278.8	280.4	282.1	283.7	287.5	291.8
16.25°	277.3	276.8	276.4	276.3	278.0	279.7	281.4	283.1	286.1	290.6	295.0
15°	277.1	276.6	276.2	277.1	278.8	280.6	282.3	284.1	288.8	293.4	299.9
13.75°	276.9	276.5	276.0	277.8	279.6	281.4	283.2	286.6	291.4	296.9	304.5
12.5°	276.8	276.3	276.7	278.5	280.4	282.2	284.0	288.9	293.8	301.0	308.8
11.25°	276.6	276.1	277.3	279.2	281.0	282.9	286.0	291.0	296.7	304.8	312.8
10°	276.5	276.0	277.9	279.8	281.6	283.5	287.8	293.0	300.0	308.3	316.5
8.75°	276.4	276.4	278.3	280.3	282.2	284.3	289.5	294.7	303.0	311.4	319.8
7.5°	276.3	276.8	278.8	280.7	282.7	285.6	290.9	297.0	305.6	314.1	322.7
6.25°	276.2	277.2	279.2	281.1	283.1	286.8	292.2	299.1	307.8	316.5	325.2
5°	276.1	277.5	279.5	281.4	283.4	287.8	293.2	300.8	309.7	318.5	327.3
3.75°	276.1	277.7	279.7	281.7	283.7	288.5	294.0	302.2	311.1	320.0	328.9
2.5°	276.0	277.9	279.9	281.9	283.8	289.1	294.5	303.2	312.2	321.1	330.1
1.25°	276.0	278.0	280.0	282.0	284.0	289.4	294.9	303.8	312.8	321.8	330.8
0°	276.0	278.0	280.0	282.0	284.0	289.5	295.0	304.0	313.0	322.0	331.0
-1.25°	276.0	278.0	280.0	282.0	284.0	289.4	294.9	303.8	312.8	321.8	330.8
-2.5°	276.0	277.9	279.9	281.9	283.8	289.1	294.5	303.2	312.2	321.1	330.1
-3.75°	276.1	277.7	279.7	281.7	283.7	288.5	294.0	302.2	311.1	320.0	328.9
-5°	276.1	277.5	279.5	281.4	283.4	287.8	293.2	300.8	309.7	318.5	327.3
-6.25°	276.2	277.2	279.2	281.1	283.1	286.8	292.2	299.1	307.8	316.5	325.2
-7.5°	276.3	276.8	278.8	280.7	282.7	285.6	290.9	297.0	305.6	314.1	322.7
-8.75°	276.4	276.4	278.3	280.3	282.2	284.3	289.5	294.7	303.0	311.4	319.8
-10°	276.5	276.0	277.9	279.8	281.6	283.5	287.8	293.0	300.0	308.3	316.5
-11.25°	276.6	276.1	277.3	279.2	281.0	282.9	286.0	291.0	296.7	304.8	312.8
-12.5°	276.8	276.3	276.7	278.5	280.4	282.2	284.0	288.9	293.8	301.0	308.8
-13.75°	276.9	276.5	276.0	277.8	279.6	281.4	283.2	286.6	291.4	296.9	304.5
-15°	277.1	276.6	276.2	277.1	278.8	280.6	282.3	284.1	288.8	293.4	299.9
-16.25°	277.3	276.8	276.4	276.3	278.0	279.7	281.4	283.1	286.1	290.6	295.0
-17.5°	277.5	277.0	276.6	276.2	277.1	278.8	280.4	282.1	283.7	287.5	291.8
-18.75°	277.7	277.2	276.8	276.4	276.1	277.8	279.4	281.0	282.6	284.4	288.5
-20°	277.9	277.4	277.0	276.6	276.2	276.8	278.3	279.9	281.4	282.9	285.1
-21.25°	277.2	277.7	277.3	276.9	276.5	276.1	277.2	278.7	280.2	281.7	283.1

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	275.1	277.9	277.5	277.1	276.7	276.4	276.1	277.5	279.0	280.4	281.8
-23.75°	272.9	276.4	277.8	277.4	277.0	276.7	276.3	276.3	277.7	279.1	280.4
-25°	270.6	274.0	277.5	277.7	277.3	277.0	276.6	276.3	276.4	277.7	279.0
-26.25°	268.2	271.6	274.9	278.0	277.6	277.3	276.9	276.6	276.3	276.3	277.5
-27.5°	265.8	269.1	272.3	275.5	277.9	277.6	277.2	276.9	276.6	276.3	276.1
-28.75°	263.3	266.5	269.7	272.8	275.8	277.9	277.6	277.3	277.0	276.7	276.4
-30°	260.7	263.8	266.9	269.9	272.9	275.8	277.9	277.6	277.3	277.0	276.7
-31.25°	250.1	261.1	264.1	267.1	269.9	272.8	275.5	278.0	277.7	277.4	277.1
-32.5°	236.6	251.5	261.2	264.1	266.9	269.7	272.3	274.9	277.5	277.8	277.5
-33.75°	222.7	237.3	251.5	261.1	263.8	266.5	269.1	271.6	274.0	276.4	277.9
-35°	208.6	222.7	236.6	250.1	260.7	263.3	265.8	268.2	270.6	272.9	275.1
-36.25°	194.2	207.9	221.4	234.5	247.4	259.9	262.4	264.8	267.1	269.3	271.4
-37.5°	179.6	192.9	206.0	218.7	231.2	243.3	255.1	261.3	263.5	265.6	267.7
-38.75°	169.2	177.6	190.3	202.7	214.7	226.5	237.9	248.9	259.6	262.0	264.0
-40°	167.1	168.9	174.4	186.4	198.1	209.4	220.5	231.1	241.4	251.4	260.2
-41.25°	164.8	166.6	168.3	170.0	181.3	192.2	202.9	213.2	223.2	232.7	241.9
-42.5°	162.6	164.3	166.0	167.6	169.2	174.9	185.2	195.1	204.7	213.9	222.8
-43.75°	160.3	162.0	163.6	165.2	166.7	168.2	169.6	176.9	186.1	195.0	203.6
-45°	158.0	159.6	161.2	162.7	164.2	165.6	167.0	168.3	169.6	176.0	184.2
-46.25°	157.0	157.3	158.8	160.2	161.7	163.0	164.4	165.7	166.9	168.1	169.2
-47.5°	157.0	157.0	157.0	157.7	159.1	160.4	161.7	163.0	164.2	165.3	166.4
-48.75°	157.0	157.0	157.0	157.0	157.0	157.8	159.1	160.3	161.4	162.5	163.6
-50°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.5	158.6	159.7	160.7
-51.25°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.9
-52.5°	156.9	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-53.75°	156.4	156.7	156.9	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-55°	155.8	156.1	156.4	156.6	156.9	157.0	157.0	157.0	157.0	157.0	157.0
-56.25°	155.2	155.5	155.8	156.0	156.3	156.5	156.7	156.9	157.0	157.0	157.0
-57.5°	154.7	154.9	155.2	155.4	155.6	155.9	156.1	156.3	156.5	156.7	156.9
-58.75°	154.1	154.3	154.6	154.8	155.0	155.2	155.4	155.6	155.8	156.0	156.2
-60°	154.2	154.1	154.0	154.2	154.4	154.6	154.8	155.0	155.2	155.3	155.5
-61.25°	154.4	154.3	154.2	154.1	154.1	154.0	154.2	154.3	154.5	154.7	154.8
-62.5°	154.6	154.5	154.4	154.3	154.3	154.2	154.2	154.1	154.1	154.0	154.2
-63.75°	154.8	154.7	154.6	154.6	154.5	154.4	154.4	154.3	154.3	154.2	154.2
-65°	154.9	154.9	154.8	154.8	154.7	154.7	154.6	154.5	154.5	154.4	154.4
-66.25°	154.9	154.9	155.0	155.0	154.9	154.9	154.8	154.8	154.7	154.7	154.6
-67.5°	154.7	154.7	154.8	154.8	154.9	154.9	155.0	155.0	154.9	154.9	154.9
-68.75°	154.5	154.5	154.6	154.6	154.7	154.7	154.8	154.8	154.8	154.9	154.9
-70°	154.3	154.3	154.4	154.4	154.4	154.5	154.5	154.6	154.6	154.6	154.7
-71.25°	154.1	154.1	154.1	154.2	154.2	154.3	154.3	154.4	154.4	154.4	154.5
-72.5°	153.9	153.9	153.9	154.0	154.0	154.1	154.1	154.1	154.2	154.2	154.2
-73.75°	153.7	153.7	153.7	153.8	153.8	153.8	153.9	153.9	153.9	154.0	154.0
-75°	153.4	153.5	153.5	153.6	153.6	153.6	153.7	153.7	153.7	153.7	153.8
-76.25°	153.2	153.3	153.3	153.3	153.4	153.4	153.4	153.5	153.5	153.5	153.5
-77.5°	153.0	153.1	153.1	153.1	153.2	153.2	153.2	153.2	153.3	153.3	153.3

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.1
-80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-82.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-83.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-85°	153.7	153.7	153.6	153.6	153.5	153.5	153.5	153.4	153.4	153.3	153.3
-86.25°	154.5	154.5	154.5	154.4	154.4	154.4	154.3	154.3	154.3	154.3	154.2
-87.5°	155.4	155.3	155.3	155.3	155.3	155.2	155.2	155.2	155.2	155.2	155.2
-88.75°	156.2	156.2	156.2	156.1	156.1	156.1	156.1	156.1	156.1	156.1	156.1
-90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
88.75°	156.1	156.1	156.1	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0
87.5°	155.1	155.1	155.1	155.1	155.1	155.1	155.1	155.0	155.0	155.0	155.0
86.25°	154.2	154.2	154.2	154.1	154.1	154.1	154.1	154.1	154.1	154.0	154.0
85°	153.3	153.2	153.2	153.2	153.2	153.1	153.1	153.1	153.1	153.1	153.0
83.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
82.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
78.75°	153.1	153.1	153.1	153.1	153.2	153.2	153.2	153.2	153.2	153.2	153.2
77.5°	153.3	153.3	153.4	153.4	153.4	153.4	153.4	153.4	153.5	153.5	153.5
76.25°	153.6	153.6	153.6	153.6	153.6	153.7	153.7	153.7	153.7	153.7	153.7
75°	153.8	153.8	153.8	153.9	153.9	153.9	153.9	153.9	153.9	154.0	154.0
73.75°	154.0	154.0	154.1	154.1	154.1	154.1	154.2	154.2	154.2	154.2	154.2
72.5°	154.3	154.3	154.3	154.3	154.4	154.4	154.4	154.4	154.4	154.4	154.5
71.25°	154.5	154.5	154.5	154.6	154.6	154.6	154.6	154.7	154.7	154.7	154.7
70°	154.7	154.7	154.8	154.8	154.8	154.9	154.9	154.9	154.9	154.9	155.0
68.75°	154.9	155.0	155.0	155.0	154.9	154.9	154.9	154.9	154.8	154.8	154.8
67.5°	154.8	154.8	154.8	154.7	154.7	154.7	154.6	154.6	154.6	154.6	154.6
66.25°	154.6	154.6	154.5	154.5	154.5	154.4	154.4	154.4	154.3	154.3	154.3
65°	154.4	154.3	154.3	154.2	154.2	154.2	154.2	154.1	154.1	154.1	154.1
63.75°	154.1	154.1	154.0	154.0	154.1	154.2	154.3	154.3	154.4	154.5	154.6
62.5°	154.3	154.4	154.6	154.7	154.8	154.9	155.0	155.1	155.2	155.2	155.3
61.25°	155.0	155.1	155.3	155.4	155.5	155.6	155.7	155.8	155.9	156.0	156.0
60°	155.7	155.8	156.0	156.1	156.2	156.3	156.4	156.5	156.6	156.7	156.8
58.75°	156.3	156.5	156.7	156.8	156.9	157.0	157.0	157.0	157.0	157.0	157.0
57.5°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
56.25°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
55°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
53.75°	157.0	157.0	157.0	157.0	157.0	157.0	157.1	157.7	158.2	158.6	159.0
52.5°	157.0	157.0	157.5	158.3	159.0	159.6	160.3	160.8	161.3	161.8	162.2
51.25°	158.8	159.7	160.5	161.3	162.0	162.7	163.4	163.9	164.5	164.9	165.4
50°	161.7	162.6	163.5	164.3	165.1	165.8	166.5	167.1	167.6	168.1	168.6
48.75°	164.6	165.5	166.5	167.3	168.1	168.9	169.5	171.3	175.2	178.8	182.0
47.5°	167.5	168.5	169.4	172.1	177.9	183.2	188.2	192.8	197.0	200.7	204.1
46.25°	172.3	179.5	186.3	192.7	198.7	204.4	209.6	214.3	218.7	222.6	226.1
45°	192.1	199.5	206.6	213.3	219.6	225.4	230.9	235.8	240.4	244.4	248.1
43.75°	211.7	219.5	226.9	233.8	240.3	246.4	252.1	257.3	260.4	261.3	262.0
42.5°	231.3	239.4	247.0	254.3	260.2	261.5	262.7	263.7	264.7	265.6	266.4
41.25°	250.7	259.1	261.4	262.9	264.3	265.7	266.9	268.0	269.0	270.0	270.8
40°	262.0	263.8	265.4	267.0	268.4	269.8	271.1	272.3	273.3	274.3	275.2
38.75°	265.8	267.7	269.4	271.0	272.5	274.0	275.3	276.5	277.6	277.9	277.8
37.5°	269.7	271.5	273.3	275.0	276.6	278.0	277.8	277.7	277.6	277.4	277.3
36.25°	273.4	275.4	277.2	277.9	277.7	277.5	277.4	277.2	277.1	277.0	276.9
35°	277.2	277.9	277.7	277.5	277.3	277.1	276.9	276.8	276.6	276.5	276.4

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	277.7	277.4	277.2	277.0	276.8	276.6	276.5	276.3	276.1	276.0	276.4
32.5°	277.3	277.0	276.8	276.6	276.4	276.2	276.0	276.7	277.3	277.9	278.3
31.25°	276.9	276.6	276.4	276.2	276.3	277.1	277.8	278.5	279.2	279.8	280.3
30°	276.5	276.2	276.1	277.1	278.0	278.8	279.6	280.4	281.0	281.6	282.2
28.75°	276.1	276.8	277.8	278.8	279.7	280.6	281.4	282.2	282.9	283.5	284.3
27.5°	277.2	278.3	279.4	280.4	281.4	282.3	283.2	284.0	286.0	287.8	289.5
26.25°	278.7	279.9	281.0	282.1	283.1	284.1	286.6	288.9	291.0	293.0	294.7
25°	280.2	281.4	282.6	283.7	286.1	288.8	291.4	293.8	296.7	300.0	303.0
23.75°	281.7	282.9	284.4	287.5	290.6	293.4	296.9	301.0	304.8	308.3	311.4
22.5°	283.1	285.1	288.5	291.8	295.0	299.9	304.5	308.8	312.8	316.5	319.8
21.25°	285.3	289.0	292.6	296.7	302.1	307.2	312.0	316.6	320.8	324.6	328.1
20°	289.0	292.8	297.5	303.4	309.0	314.3	319.4	324.2	328.6	334.1	341.1
18.75°	292.6	297.5	303.8	309.9	315.7	321.3	326.7	332.2	341.0	349.2	356.5
17.5°	296.7	303.4	309.9	316.2	322.3	328.2	336.1	346.1	355.4	363.9	377.9
16.25°	302.1	309.0	315.7	322.3	328.7	338.1	349.1	359.6	373.4	390.8	406.6
15°	307.2	314.3	321.3	328.2	338.1	350.2	361.7	379.7	399.5	417.9	441.5
13.75°	312.0	319.4	326.7	336.1	349.1	361.7	381.9	404.0	424.9	464.4	507.3
12.5°	316.6	324.2	332.2	346.1	359.6	379.7	404.0	427.2	476.1	525.6	571.5
11.25°	320.8	328.6	341.0	355.4	373.4	399.5	424.9	476.1	531.8	584.4	679.5
10°	324.6	334.1	349.2	363.9	390.8	417.9	464.4	525.6	584.4	693.0	795.4
8.75°	328.1	341.1	356.5	377.9	406.6	441.5	507.3	571.5	679.5	795.4	928.5
7.5°	331.3	347.2	363.0	391.2	420.8	477.6	546.1	639.8	766.9	893.3	1162.3
6.25°	336.3	352.5	372.1	402.7	437.4	509.2	580.1	711.5	844.7	1087.5	1374.5
5°	340.5	357.0	381.1	412.4	462.1	535.8	631.6	772.5	942.9	1255.4	1560.1
3.75°	343.7	360.5	388.2	420.0	481.7	557.0	676.5	821.6	1066.7	1392.6	1951.1
2.5°	346.1	363.0	393.3	425.5	496.0	572.5	709.3	857.6	1158.0	1494.7	2270.0
1.25°	347.5	364.5	396.5	428.9	504.6	581.9	729.3	879.6	1214.1	1557.7	2468.5
0°	348.0	365.0	397.5	430.0	507.5	585.0	736.0	887.0	1233.0	1579.0	2536.0
-1.25°	347.5	364.5	396.5	428.9	504.6	581.9	729.3	879.6	1214.1	1557.7	2468.5
-2.5°	346.1	363.0	393.3	425.5	496.0	572.5	709.3	857.6	1158.0	1494.7	2270.0
-3.75°	343.7	360.5	388.2	420.0	481.7	557.0	676.5	821.6	1066.7	1392.6	1951.1
-5°	340.5	357.0	381.1	412.4	462.1	535.8	631.6	772.5	942.9	1255.4	1560.1
-6.25°	336.3	352.5	372.1	402.7	437.4	509.2	580.1	711.5	844.7	1087.5	1374.5
-7.5°	331.3	347.2	363.0	391.2	420.8	477.6	546.1	639.8	766.9	893.3	1162.3
-8.75°	328.1	341.1	356.5	377.9	406.6	441.5	507.3	571.5	679.5	795.4	928.5
-10°	324.6	334.1	349.2	363.9	390.8	417.9	464.4	525.6	584.4	693.0	795.4
-11.25°	320.8	328.6	341.0	355.4	373.4	399.5	424.9	476.1	531.8	584.4	679.5
-12.5°	316.6	324.2	332.2	346.1	359.6	379.7	404.0	427.2	476.1	525.6	571.5
-13.75°	312.0	319.4	326.7	336.1	349.1	361.7	381.9	404.0	424.9	464.4	507.3
-15°	307.2	314.3	321.3	328.2	338.1	350.2	361.7	379.7	399.5	417.9	441.5
-16.25°	302.1	309.0	315.7	322.3	328.7	338.1	349.1	359.6	373.4	390.8	406.6
-17.5°	296.7	303.4	309.9	316.2	322.3	328.2	336.1	346.1	355.4	363.9	377.9
-18.75°	292.6	297.5	303.8	309.9	315.7	321.3	326.7	332.2	341.0	349.2	356.5
-20°	289.0	292.8	297.5	303.4	309.0	314.3	319.4	324.2	328.6	334.1	341.1
-21.25°	285.3	289.0	292.6	296.7	302.1	307.2	312.0	316.6	320.8	324.6	328.1

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	283.1	285.1	288.5	291.8	295.0	299.9	304.5	308.8	312.8	316.5	319.8
-23.75°	281.7	282.9	284.4	287.5	290.6	293.4	296.9	301.0	304.8	308.3	311.4
-25°	280.2	281.4	282.6	283.7	286.1	288.8	291.4	293.8	296.7	300.0	303.0
-26.25°	278.7	279.9	281.0	282.1	283.1	284.1	286.6	288.9	291.0	293.0	294.7
-27.5°	277.2	278.3	279.4	280.4	281.4	282.3	283.2	284.0	286.0	287.8	289.5
-28.75°	276.1	276.8	277.8	278.8	279.7	280.6	281.4	282.2	282.9	283.5	284.3
-30°	276.5	276.2	276.1	277.1	278.0	278.8	279.6	280.4	281.0	281.6	282.2
-31.25°	276.9	276.6	276.4	276.2	276.3	277.1	277.8	278.5	279.2	279.8	280.3
-32.5°	277.3	277.0	276.8	276.6	276.4	276.2	276.0	276.7	277.3	277.9	278.3
-33.75°	277.7	277.4	277.2	277.0	276.8	276.6	276.5	276.3	276.1	276.0	276.4
-35°	277.2	277.9	277.7	277.5	277.3	277.1	276.9	276.8	276.6	276.5	276.4
-36.25°	273.4	275.4	277.2	277.9	277.7	277.5	277.4	277.2	277.1	277.0	276.9
-37.5°	269.7	271.5	273.3	275.0	276.6	278.0	277.8	277.7	277.6	277.4	277.3
-38.75°	265.8	267.7	269.4	271.0	272.5	274.0	275.3	276.5	277.6	277.9	277.8
-40°	262.0	263.8	265.4	267.0	268.4	269.8	271.1	272.3	273.3	274.3	275.2
-41.25°	250.7	259.1	261.4	262.9	264.3	265.7	266.9	268.0	269.0	270.0	270.8
-42.5°	231.3	239.4	247.0	254.3	260.2	261.5	262.7	263.7	264.7	265.6	266.4
-43.75°	211.7	219.5	226.9	233.8	240.3	246.4	252.1	257.3	260.4	261.3	262.0
-45°	192.1	199.5	206.6	213.3	219.6	225.4	230.9	235.8	240.4	244.4	248.1
-46.25°	172.3	179.5	186.3	192.7	198.7	204.4	209.6	214.3	218.7	222.6	226.1
-47.5°	167.5	168.5	169.4	172.1	177.9	183.2	188.2	192.8	197.0	200.7	204.1
-48.75°	164.6	165.5	166.5	167.3	168.1	168.9	169.5	171.3	175.2	178.8	182.0
-50°	161.7	162.6	163.5	164.3	165.1	165.8	166.5	167.1	167.6	168.1	168.6
-51.25°	158.8	159.7	160.5	161.3	162.0	162.7	163.4	163.9	164.5	164.9	165.4
-52.5°	157.0	157.0	157.5	158.3	159.0	159.6	160.3	160.8	161.3	161.8	162.2
-53.75°	157.0	157.0	157.0	157.0	157.0	157.0	157.1	157.7	158.2	158.6	159.0
-55°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-56.25°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-57.5°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-58.75°	156.3	156.5	156.7	156.8	156.9	157.0	157.0	157.0	157.0	157.0	157.0
-60°	155.7	155.8	156.0	156.1	156.2	156.3	156.4	156.5	156.6	156.7	156.8
-61.25°	155.0	155.1	155.3	155.4	155.5	155.6	155.7	155.8	155.9	156.0	156.0
-62.5°	154.3	154.4	154.6	154.7	154.8	154.9	155.0	155.1	155.2	155.2	155.3
-63.75°	154.1	154.1	154.0	154.0	154.1	154.2	154.3	154.3	154.4	154.5	154.6
-65°	154.4	154.3	154.3	154.2	154.2	154.2	154.2	154.1	154.1	154.1	154.1
-66.25°	154.6	154.6	154.5	154.5	154.5	154.4	154.4	154.4	154.3	154.3	154.3
-67.5°	154.8	154.8	154.8	154.7	154.7	154.7	154.6	154.6	154.6	154.6	154.6
-68.75°	154.9	155.0	155.0	155.0	154.9	154.9	154.9	154.9	154.8	154.8	154.8
-70°	154.7	154.7	154.8	154.8	154.8	154.9	154.9	154.9	154.9	154.9	155.0
-71.25°	154.5	154.5	154.5	154.6	154.6	154.6	154.6	154.7	154.7	154.7	154.7
-72.5°	154.3	154.3	154.3	154.3	154.4	154.4	154.4	154.4	154.4	154.4	154.5
-73.75°	154.0	154.0	154.1	154.1	154.1	154.1	154.2	154.2	154.2	154.2	154.2
-75°	153.8	153.8	153.8	153.9	153.9	153.9	153.9	153.9	153.9	154.0	154.0
-76.25°	153.6	153.6	153.6	153.6	153.6	153.7	153.7	153.7	153.7	153.7	153.7
-77.5°	153.3	153.3	153.4	153.4	153.4	153.4	153.4	153.4	153.5	153.5	153.5

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	153.1	153.1	153.1	153.1	153.2	153.2	153.2	153.2	153.2	153.2	153.2
-80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-82.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-83.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-85°	153.3	153.2	153.2	153.2	153.2	153.1	153.1	153.1	153.1	153.1	153.0
-86.25°	154.2	154.2	154.2	154.1	154.1	154.1	154.1	154.1	154.1	154.0	154.0
-87.5°	155.1	155.1	155.1	155.1	155.1	155.1	155.1	155.0	155.0	155.0	155.0
-88.75°	156.1	156.1	156.1	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0
-90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
88.75°	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0
87.5°	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0
86.25°	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0
85°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
83.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
82.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
78.75°	153.2	153.2	153.2	153.2	153.2	153.2	153.3	153.2	153.2	153.2	153.2
77.5°	153.5	153.5	153.5	153.5	153.5	153.5	153.5	153.5	153.5	153.5	153.5
76.25°	153.7	153.7	153.7	153.7	153.7	153.7	153.8	153.7	153.7	153.7	153.7
75°	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0
73.75°	154.2	154.2	154.2	154.2	154.2	154.2	154.3	154.2	154.2	154.2	154.2
72.5°	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5
71.25°	154.7	154.7	154.7	154.7	154.7	154.7	154.8	154.7	154.7	154.7	154.7
70°	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0
68.75°	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8
67.5°	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5
66.25°	154.3	154.3	154.3	154.3	154.3	154.3	154.3	154.3	154.3	154.3	154.3
65°	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0
63.75°	154.6	154.6	154.7	154.7	154.7	154.7	154.8	154.7	154.7	154.7	154.7
62.5°	155.3	155.4	155.4	155.5	155.5	155.5	155.5	155.5	155.5	155.5	155.4
61.25°	156.1	156.1	156.2	156.2	156.2	156.2	156.3	156.2	156.2	156.2	156.2
60°	156.8	156.9	156.9	157.0	157.0	157.0	157.0	157.0	157.0	157.0	156.9
58.75°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
57.5°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
56.25°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
55°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
53.75°	159.3	159.6	159.8	160.0	160.1	160.2	160.3	160.2	160.1	160.0	159.8
52.5°	162.5	162.8	163.1	163.3	163.4	163.5	163.5	163.5	163.4	163.3	163.1
51.25°	165.7	166.0	166.3	166.5	166.6	166.7	166.8	166.7	166.6	166.5	166.3
50°	168.9	169.3	169.5	169.7	169.9	170.0	170.0	170.0	169.9	169.7	169.5
48.75°	184.8	187.1	189.1	190.6	191.6	192.3	192.5	192.3	191.6	190.6	189.1
47.5°	206.9	209.4	211.4	213.0	214.1	214.8	215.0	214.8	214.1	213.0	211.4
46.25°	229.1	231.6	233.7	235.4	236.6	237.3	237.5	237.3	236.6	235.4	233.7
45°	251.2	253.9	256.1	257.8	259.0	259.8	260.0	259.8	259.0	257.8	256.1
43.75°	262.7	263.2	263.7	264.0	264.3	264.4	264.5	264.4	264.3	264.0	263.7
42.5°	267.1	267.7	268.1	268.5	268.8	268.9	269.0	268.9	268.8	268.5	268.1
41.25°	271.5	272.1	272.6	273.0	273.3	273.4	273.5	273.4	273.3	273.0	272.6
40°	275.9	276.5	277.1	277.5	277.8	277.9	278.0	277.9	277.8	277.5	277.1
38.75°	277.7	277.7	277.6	277.6	277.5	277.5	277.5	277.5	277.5	277.6	277.6
37.5°	277.3	277.2	277.1	277.1	277.0	277.0	277.0	277.0	277.0	277.1	277.1
36.25°	276.8	276.7	276.6	276.6	276.5	276.5	276.5	276.5	276.5	276.6	276.6
35°	276.3	276.2	276.1	276.1	276.0	276.0	276.0	276.0	276.0	276.1	276.1

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	276.8	277.2	277.5	277.7	277.9	278.0	278.0	278.0	277.9	277.7	277.5
32.5°	278.8	279.2	279.5	279.7	279.9	280.0	280.0	280.0	279.9	279.7	279.5
31.25°	280.7	281.1	281.4	281.7	281.9	282.0	282.0	282.0	281.9	281.7	281.4
30°	282.7	283.1	283.4	283.7	283.8	284.0	284.0	284.0	283.8	283.7	283.4
28.75°	285.6	286.8	287.8	288.5	289.1	289.4	289.5	289.4	289.1	288.5	287.8
27.5°	290.9	292.2	293.2	294.0	294.5	294.9	295.0	294.9	294.5	294.0	293.2
26.25°	297.0	299.1	300.8	302.2	303.2	303.8	304.0	303.8	303.2	302.2	300.8
25°	305.6	307.8	309.7	311.1	312.2	312.8	313.0	312.8	312.2	311.1	309.7
23.75°	314.1	316.5	318.5	320.0	321.1	321.8	322.0	321.8	321.1	320.0	318.5
22.5°	322.7	325.2	327.3	328.9	330.1	330.8	331.0	330.8	330.1	328.9	327.3
21.25°	331.3	336.3	340.5	343.7	346.1	347.5	348.0	347.5	346.1	343.7	340.5
20°	347.2	352.5	357.0	360.5	363.0	364.5	365.0	364.5	363.0	360.5	357.0
18.75°	363.0	372.1	381.1	388.2	393.3	396.5	397.5	396.5	393.3	388.2	381.1
17.5°	391.2	402.7	412.4	420.0	425.5	428.9	430.0	428.9	425.5	420.0	412.4
16.25°	420.8	437.4	462.1	481.7	496.0	504.6	507.5	504.6	496.0	481.7	462.1
15°	477.6	509.2	535.8	557.0	572.5	581.9	585.0	581.9	572.5	557.0	535.8
13.75°	546.1	580.1	631.6	676.5	709.3	729.3	736.0	729.3	709.3	676.5	631.6
12.5°	639.8	711.5	772.5	821.6	857.6	879.6	887.0	879.6	857.6	821.6	772.5
11.25°	766.9	844.7	942.9	1066.7	1158.0	1214.1	1233.0	1214.1	1158.0	1066.7	942.9
10°	893.3	1087.5	1255.4	1392.6	1494.7	1557.7	1579.0	1557.7	1494.7	1392.6	1255.4
8.75°	1162.3	1374.5	1560.1	1951.1	2270.0	2468.5	2536.0	2468.5	2270.0	1951.1	1560.1
7.5°	1415.3	1769.4	2340.1	2913.8	3401.5	3708.8	3814.0	3708.8	3401.5	2913.8	2340.1
6.25°	1769.4	2474.7	3305.2	4094.4	4818.0	5282.3	5443.0	5282.3	4818.0	4094.4	3305.2
5°	2340.1	3305.2	4378.8	5447.3	6435.9	7089.5	7320.0	7089.5	6435.9	5447.3	4378.8
3.75°	2913.8	4094.4	5447.3	6867.4	7980.4	8720.2	8991.0	8720.2	7980.4	6867.4	5447.3
2.5°	3401.5	4818.0	6435.9	7980.4	9163.5	9757.4	9994.0	9757.4	9163.5	7980.4	6435.9
1.25°	3708.8	5282.3	7089.5	8720.2	9757.4	10161.6	10280.0	10161.6	9757.4	8720.2	7089.5
0°	3814.0	5443.0	7320.0	8991.0	9994.0	10280.0	10200.0	10280.0	9994.0	8991.0	7320.0
-1.25°	3708.8	5282.3	7089.5	8720.2	9757.4	10161.6	10280.0	10161.6	9757.4	8720.2	7089.5
-2.5°	3401.5	4818.0	6435.9	7980.4	9163.5	9757.4	9994.0	9757.4	9163.5	7980.4	6435.9
-3.75°	2913.8	4094.4	5447.3	6867.4	7980.4	8720.2	8991.0	8720.2	7980.4	6867.4	5447.3
-5°	2340.1	3305.2	4378.8	5447.3	6435.9	7089.5	7320.0	7089.5	6435.9	5447.3	4378.8
-6.25°	1769.4	2474.7	3305.2	4094.4	4818.0	5282.3	5443.0	5282.3	4818.0	4094.4	3305.2
-7.5°	1415.3	1769.4	2340.1	2913.8	3401.5	3708.8	3814.0	3708.8	3401.5	2913.8	2340.1
-8.75°	1162.3	1374.5	1560.1	1951.1	2270.0	2468.5	2536.0	2468.5	2270.0	1951.1	1560.1
-10°	893.3	1087.5	1255.4	1392.6	1494.7	1557.7	1579.0	1557.7	1494.7	1392.6	1255.4
-11.25°	766.9	844.7	942.9	1066.7	1158.0	1214.1	1233.0	1214.1	1158.0	1066.7	942.9
-12.5°	639.8	711.5	772.5	821.6	857.6	879.6	887.0	879.6	857.6	821.6	772.5
-13.75°	546.1	580.1	631.6	676.5	709.3	729.3	736.0	729.3	709.3	676.5	631.6
-15°	477.6	509.2	535.8	557.0	572.5	581.9	585.0	581.9	572.5	557.0	535.8
-16.25°	420.8	437.4	462.1	481.7	496.0	504.6	507.5	504.6	496.0	481.7	462.1
-17.5°	391.2	402.7	412.4	420.0	425.5	428.9	430.0	428.9	425.5	420.0	412.4
-18.75°	363.0	372.1	381.1	388.2	393.3	396.5	397.5	396.5	393.3	388.2	381.1
-20°	347.2	352.5	357.0	360.5	363.0	364.5	365.0	364.5	363.0	360.5	357.0
-21.25°	331.3	336.3	340.5	343.7	346.1	347.5	348.0	347.5	346.1	343.7	340.5

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	322.7	325.2	327.3	328.9	330.1	330.8	331.0	330.8	330.1	328.9	327.3
-23.75°	314.1	316.5	318.5	320.0	321.1	321.8	322.0	321.8	321.1	320.0	318.5
-25°	305.6	307.8	309.7	311.1	312.2	312.8	313.0	312.8	312.2	311.1	309.7
-26.25°	297.0	299.1	300.8	302.2	303.2	303.8	304.0	303.8	303.2	302.2	300.8
-27.5°	290.9	292.2	293.2	294.0	294.5	294.9	295.0	294.9	294.5	294.0	293.2
-28.75°	285.6	286.8	287.8	288.5	289.1	289.4	289.5	289.4	289.1	288.5	287.8
-30°	282.7	283.1	283.4	283.7	283.8	284.0	284.0	284.0	283.8	283.7	283.4
-31.25°	280.7	281.1	281.4	281.7	281.9	282.0	282.0	282.0	281.9	281.7	281.4
-32.5°	278.8	279.2	279.5	279.7	279.9	280.0	280.0	280.0	279.9	279.7	279.5
-33.75°	276.8	277.2	277.5	277.7	277.9	278.0	278.0	278.0	277.9	277.7	277.5
-35°	276.3	276.2	276.1	276.1	276.0	276.0	276.0	276.0	276.0	276.1	276.1
-36.25°	276.8	276.7	276.6	276.6	276.5	276.5	276.5	276.5	276.5	276.6	276.6
-37.5°	277.3	277.2	277.1	277.1	277.0	277.0	277.0	277.0	277.0	277.1	277.1
-38.75°	277.7	277.7	277.6	277.6	277.5	277.5	277.5	277.5	277.5	277.6	277.6
-40°	275.9	276.5	277.1	277.5	277.8	277.9	278.0	277.9	277.8	277.5	277.1
-41.25°	271.5	272.1	272.6	273.0	273.3	273.4	273.5	273.4	273.3	273.0	272.6
-42.5°	267.1	267.7	268.1	268.5	268.8	268.9	269.0	268.9	268.8	268.5	268.1
-43.75°	262.7	263.2	263.7	264.0	264.3	264.4	264.5	264.4	264.3	264.0	263.7
-45°	251.2	253.9	256.1	257.8	259.0	259.8	260.0	259.8	259.0	257.8	256.1
-46.25°	229.1	231.6	233.7	235.4	236.6	237.3	237.5	237.3	236.6	235.4	233.7
-47.5°	206.9	209.4	211.4	213.0	214.1	214.8	215.0	214.8	214.1	213.0	211.4
-48.75°	184.8	187.1	189.1	190.6	191.6	192.3	192.5	192.3	191.6	190.6	189.1
-50°	168.9	169.3	169.5	169.7	169.9	170.0	170.0	170.0	169.9	169.7	169.5
-51.25°	165.7	166.0	166.3	166.5	166.6	166.7	166.8	166.7	166.6	166.5	166.3
-52.5°	162.5	162.8	163.1	163.3	163.4	163.5	163.5	163.5	163.4	163.3	163.1
-53.75°	159.3	159.6	159.8	160.0	160.1	160.2	160.3	160.2	160.1	160.0	159.8
-55°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-56.25°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-57.5°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-58.75°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-60°	156.8	156.9	156.9	157.0	157.0	157.0	157.0	157.0	157.0	157.0	156.9
-61.25°	156.1	156.1	156.2	156.2	156.2	156.2	156.3	156.2	156.2	156.2	156.2
-62.5°	155.3	155.4	155.4	155.5	155.5	155.5	155.5	155.5	155.5	155.5	155.4
-63.75°	154.6	154.6	154.7	154.7	154.7	154.7	154.8	154.7	154.7	154.7	154.7
-65°	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0
-66.25°	154.3	154.3	154.3	154.3	154.3	154.3	154.3	154.3	154.3	154.3	154.3
-67.5°	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5
-68.75°	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8
-70°	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0
-71.25°	154.7	154.7	154.7	154.7	154.7	154.7	154.8	154.7	154.7	154.7	154.7
-72.5°	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5	154.5
-73.75°	154.2	154.2	154.2	154.2	154.2	154.2	154.3	154.2	154.2	154.2	154.2
-75°	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0
-76.25°	153.7	153.7	153.7	153.7	153.7	153.7	153.8	153.7	153.7	153.7	153.7
-77.5°	153.5	153.5	153.5	153.5	153.5	153.5	153.5	153.5	153.5	153.5	153.5

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	153.2	153.2	153.2	153.2	153.2	153.2	153.3	153.2	153.2	153.2	153.2
-80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-82.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-83.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-85°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-86.25°	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0	154.0
-87.5°	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0	155.0
-88.75°	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0
-90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
88.75°	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.1
87.5°	155.0	155.0	155.0	155.0	155.0	155.0	155.1	155.1	155.1	155.1	155.1
86.25°	154.0	154.0	154.0	154.0	154.1	154.1	154.1	154.1	154.1	154.1	154.2
85°	153.0	153.0	153.0	153.1	153.1	153.1	153.1	153.1	153.2	153.2	153.2
83.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
82.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
78.75°	153.2	153.2	153.2	153.2	153.2	153.2	153.2	153.2	153.2	153.1	153.1
77.5°	153.5	153.5	153.5	153.5	153.5	153.4	153.4	153.4	153.4	153.4	153.4
76.25°	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.6	153.6	153.6
75°	154.0	154.0	154.0	154.0	153.9	153.9	153.9	153.9	153.9	153.9	153.8
73.75°	154.2	154.2	154.2	154.2	154.2	154.2	154.2	154.1	154.1	154.1	154.1
72.5°	154.5	154.5	154.5	154.4	154.4	154.4	154.4	154.4	154.4	154.3	154.3
71.25°	154.7	154.7	154.7	154.7	154.7	154.7	154.6	154.6	154.6	154.6	154.5
70°	155.0	155.0	155.0	154.9	154.9	154.9	154.9	154.9	154.8	154.8	154.8
68.75°	154.8	154.8	154.8	154.8	154.8	154.9	154.9	154.9	154.9	155.0	155.0
67.5°	154.5	154.5	154.6	154.6	154.6	154.6	154.6	154.7	154.7	154.7	154.8
66.25°	154.3	154.3	154.3	154.3	154.3	154.4	154.4	154.4	154.5	154.5	154.5
65°	154.0	154.0	154.1	154.1	154.1	154.1	154.2	154.2	154.2	154.2	154.3
63.75°	154.6	154.6	154.6	154.5	154.4	154.3	154.3	154.2	154.1	154.0	154.0
62.5°	155.4	155.3	155.3	155.2	155.2	155.1	155.0	154.9	154.8	154.7	154.6
61.25°	156.1	156.1	156.0	156.0	155.9	155.8	155.7	155.6	155.5	155.4	155.3
60°	156.9	156.8	156.8	156.7	156.6	156.5	156.4	156.3	156.2	156.1	156.0
58.75°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	156.9	156.8	156.7
57.5°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
56.25°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
55°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
53.75°	159.6	159.3	159.0	158.6	158.2	157.7	157.1	157.0	157.0	157.0	157.0
52.5°	162.8	162.5	162.2	161.8	161.3	160.8	160.3	159.6	159.0	158.3	157.5
51.25°	166.0	165.7	165.4	164.9	164.5	163.9	163.4	162.7	162.0	161.3	160.5
50°	169.3	168.9	168.6	168.1	167.6	167.1	166.5	165.8	165.1	164.3	163.5
48.75°	187.1	184.8	182.0	178.8	175.2	171.3	169.5	168.9	168.1	167.3	166.5
47.5°	209.4	206.9	204.1	200.7	197.0	192.8	188.2	183.2	177.9	172.1	169.4
46.25°	231.6	229.1	226.1	222.6	218.7	214.3	209.6	204.4	198.7	192.7	186.3
45°	253.9	251.2	248.1	244.4	240.4	235.8	230.9	225.4	219.6	213.3	206.6
43.75°	263.2	262.7	262.0	261.3	260.4	257.3	252.1	246.4	240.3	233.8	226.9
42.5°	267.7	267.1	266.4	265.6	264.7	263.7	262.7	261.5	260.2	254.3	247.0
41.25°	272.1	271.5	270.8	270.0	269.0	268.0	266.9	265.7	264.3	262.9	261.4
40°	276.5	275.9	275.2	274.3	273.3	272.3	271.1	269.8	268.4	267.0	265.4
38.75°	277.7	277.7	277.8	277.9	277.6	276.5	275.3	274.0	272.5	271.0	269.4
37.5°	277.2	277.3	277.3	277.4	277.6	277.7	277.8	278.0	276.6	275.0	273.3
36.25°	276.7	276.8	276.9	277.0	277.1	277.2	277.4	277.5	277.7	277.9	277.2
35°	276.2	276.3	276.4	276.5	276.6	276.8	276.9	277.1	277.3	277.5	277.7

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	277.2	276.8	276.4	276.0	276.1	276.3	276.5	276.6	276.8	277.0	277.2
32.5°	279.2	278.8	278.3	277.9	277.3	276.7	276.0	276.2	276.4	276.6	276.8
31.25°	281.1	280.7	280.3	279.8	279.2	278.5	277.8	277.1	276.3	276.2	276.4
30°	283.1	282.7	282.2	281.6	281.0	280.4	279.6	278.8	278.0	277.1	276.1
28.75°	286.8	285.6	284.3	283.5	282.9	282.2	281.4	280.6	279.7	278.8	277.8
27.5°	292.2	290.9	289.5	287.8	286.0	284.0	283.2	282.3	281.4	280.4	279.4
26.25°	299.1	297.0	294.7	293.0	291.0	288.9	286.6	284.1	283.1	282.1	281.0
25°	307.8	305.6	303.0	300.0	296.7	293.8	291.4	288.8	286.1	283.7	282.6
23.75°	316.5	314.1	311.4	308.3	304.8	301.0	296.9	293.4	290.6	287.5	284.4
22.5°	325.2	322.7	319.8	316.5	312.8	308.8	304.5	299.9	295.0	291.8	288.5
21.25°	336.3	331.3	328.1	324.6	320.8	316.6	312.0	307.2	302.1	296.7	292.6
20°	352.5	347.2	341.1	334.1	328.6	324.2	319.4	314.3	309.0	303.4	297.5
18.75°	372.1	363.0	356.5	349.2	341.0	332.2	326.7	321.3	315.7	309.9	303.8
17.5°	402.7	391.2	377.9	363.9	355.4	346.1	336.1	328.2	322.3	316.2	309.9
16.25°	437.4	420.8	406.6	390.8	373.4	359.6	349.1	338.1	328.7	322.3	315.7
15°	509.2	477.6	441.5	417.9	399.5	379.7	361.7	350.2	338.1	328.2	321.3
13.75°	580.1	546.1	507.3	464.4	424.9	404.0	381.9	361.7	349.1	336.1	326.7
12.5°	711.5	639.8	571.5	525.6	476.1	427.2	404.0	379.7	359.6	346.1	332.2
11.25°	844.7	766.9	679.5	584.4	531.8	476.1	424.9	399.5	373.4	355.4	341.0
10°	1087.5	893.3	795.4	693.0	584.4	525.6	464.4	417.9	390.8	363.9	349.2
8.75°	1374.5	1162.3	928.5	795.4	679.5	571.5	507.3	441.5	406.6	377.9	356.5
7.5°	1769.4	1415.3	1162.3	893.3	766.9	639.8	546.1	477.6	420.8	391.2	363.0
6.25°	2474.7	1769.4	1374.5	1087.5	844.7	711.5	580.1	509.2	437.4	402.7	372.1
5°	3305.2	2340.1	1560.1	1255.4	942.9	772.5	631.6	535.8	462.1	412.4	381.1
3.75°	4094.4	2913.8	1951.1	1392.6	1066.7	821.6	676.5	557.0	481.7	420.0	388.2
2.5°	4818.0	3401.5	2270.0	1494.7	1158.0	857.6	709.3	572.5	496.0	425.5	393.3
1.25°	5282.3	3708.8	2468.5	1557.7	1214.1	879.6	729.3	581.9	504.6	428.9	396.5
0°	5443.0	3814.0	2536.0	1579.0	1233.0	887.0	736.0	585.0	507.5	430.0	397.5
-1.25°	5282.3	3708.8	2468.5	1557.7	1214.1	879.6	729.3	581.9	504.6	428.9	396.5
-2.5°	4818.0	3401.5	2270.0	1494.7	1158.0	857.6	709.3	572.5	496.0	425.5	393.3
-3.75°	4094.4	2913.8	1951.1	1392.6	1066.7	821.6	676.5	557.0	481.7	420.0	388.2
-5°	3305.2	2340.1	1560.1	1255.4	942.9	772.5	631.6	535.8	462.1	412.4	381.1
-6.25°	2474.7	1769.4	1374.5	1087.5	844.7	711.5	580.1	509.2	437.4	402.7	372.1
-7.5°	1769.4	1415.3	1162.3	893.3	766.9	639.8	546.1	477.6	420.8	391.2	363.0
-8.75°	1374.5	1162.3	928.5	795.4	679.5	571.5	507.3	441.5	406.6	377.9	356.5
-10°	1087.5	893.3	795.4	693.0	584.4	525.6	464.4	417.9	390.8	363.9	349.2
-11.25°	844.7	766.9	679.5	584.4	531.8	476.1	424.9	399.5	373.4	355.4	341.0
-12.5°	711.5	639.8	571.5	525.6	476.1	427.2	404.0	379.7	359.6	346.1	332.2
-13.75°	580.1	546.1	507.3	464.4	424.9	404.0	381.9	361.7	349.1	336.1	326.7
-15°	509.2	477.6	441.5	417.9	399.5	379.7	361.7	350.2	338.1	328.2	321.3
-16.25°	437.4	420.8	406.6	390.8	373.4	359.6	349.1	338.1	328.7	322.3	315.7
-17.5°	402.7	391.2	377.9	363.9	355.4	346.1	336.1	328.2	322.3	316.2	309.9
-18.75°	372.1	363.0	356.5	349.2	341.0	332.2	326.7	321.3	315.7	309.9	303.8
-20°	352.5	347.2	341.1	334.1	328.6	324.2	319.4	314.3	309.0	303.4	297.5
-21.25°	336.3	331.3	328.1	324.6	320.8	316.6	312.0	307.2	302.1	296.7	292.6

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	325.2	322.7	319.8	316.5	312.8	308.8	304.5	299.9	295.0	291.8	288.5
-23.75°	316.5	314.1	311.4	308.3	304.8	301.0	296.9	293.4	290.6	287.5	284.4
-25°	307.8	305.6	303.0	300.0	296.7	293.8	291.4	288.8	286.1	283.7	282.6
-26.25°	299.1	297.0	294.7	293.0	291.0	288.9	286.6	284.1	283.1	282.1	281.0
-27.5°	292.2	290.9	289.5	287.8	286.0	284.0	283.2	282.3	281.4	280.4	279.4
-28.75°	286.8	285.6	284.3	283.5	282.9	282.2	281.4	280.6	279.7	278.8	277.8
-30°	283.1	282.7	282.2	281.6	281.0	280.4	279.6	278.8	278.0	277.1	276.1
-31.25°	281.1	280.7	280.3	279.8	279.2	278.5	277.8	277.1	276.3	276.2	276.4
-32.5°	279.2	278.8	278.3	277.9	277.3	276.7	276.0	276.2	276.4	276.6	276.8
-33.75°	277.2	276.8	276.4	276.0	276.1	276.3	276.5	276.6	276.8	277.0	277.2
-35°	276.2	276.3	276.4	276.5	276.6	276.8	276.9	277.1	277.3	277.5	277.7
-36.25°	276.7	276.8	276.9	277.0	277.1	277.2	277.4	277.5	277.7	277.9	277.2
-37.5°	277.2	277.3	277.3	277.4	277.6	277.7	277.8	278.0	276.6	275.0	273.3
-38.75°	277.7	277.7	277.8	277.9	277.6	276.5	275.3	274.0	272.5	271.0	269.4
-40°	276.5	275.9	275.2	274.3	273.3	272.3	271.1	269.8	268.4	267.0	265.4
-41.25°	272.1	271.5	270.8	270.0	269.0	268.0	266.9	265.7	264.3	262.9	261.4
-42.5°	267.7	267.1	266.4	265.6	264.7	263.7	262.7	261.5	260.2	254.3	247.0
-43.75°	263.2	262.7	262.0	261.3	260.4	257.3	252.1	246.4	240.3	233.8	226.9
-45°	253.9	251.2	248.1	244.4	240.4	235.8	230.9	225.4	219.6	213.3	206.6
-46.25°	231.6	229.1	226.1	222.6	218.7	214.3	209.6	204.4	198.7	192.7	186.3
-47.5°	209.4	206.9	204.1	200.7	197.0	192.8	188.2	183.2	177.9	172.1	169.4
-48.75°	187.1	184.8	182.0	178.8	175.2	171.3	169.5	168.9	168.1	167.3	166.5
-50°	169.3	168.9	168.6	168.1	167.6	167.1	166.5	165.8	165.1	164.3	163.5
-51.25°	166.0	165.7	165.4	164.9	164.5	163.9	163.4	162.7	162.0	161.3	160.5
-52.5°	162.8	162.5	162.2	161.8	161.3	160.8	160.3	159.6	159.0	158.3	157.5
-53.75°	159.6	159.3	159.0	158.6	158.2	157.7	157.1	157.0	157.0	157.0	157.0
-55°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-56.25°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-57.5°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-58.75°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	156.9	156.8	156.7
-60°	156.9	156.8	156.8	156.7	156.6	156.5	156.4	156.3	156.2	156.1	156.0
-61.25°	156.1	156.1	156.0	156.0	155.9	155.8	155.7	155.6	155.5	155.4	155.3
-62.5°	155.4	155.3	155.3	155.2	155.2	155.1	155.0	154.9	154.8	154.7	154.6
-63.75°	154.6	154.6	154.6	154.5	154.4	154.3	154.3	154.2	154.1	154.0	154.0
-65°	154.0	154.0	154.1	154.1	154.1	154.1	154.2	154.2	154.2	154.2	154.3
-66.25°	154.3	154.3	154.3	154.3	154.3	154.4	154.4	154.4	154.5	154.5	154.5
-67.5°	154.5	154.5	154.6	154.6	154.6	154.6	154.6	154.7	154.7	154.7	154.8
-68.75°	154.8	154.8	154.8	154.8	154.8	154.9	154.9	154.9	154.9	155.0	155.0
-70°	155.0	155.0	155.0	154.9	154.9	154.9	154.9	154.9	154.8	154.8	154.8
-71.25°	154.7	154.7	154.7	154.7	154.7	154.7	154.6	154.6	154.6	154.6	154.5
-72.5°	154.5	154.5	154.5	154.4	154.4	154.4	154.4	154.4	154.4	154.3	154.3
-73.75°	154.2	154.2	154.2	154.2	154.2	154.2	154.2	154.1	154.1	154.1	154.1
-75°	154.0	154.0	154.0	154.0	153.9	153.9	153.9	153.9	153.9	153.9	153.8
-76.25°	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.7	153.6	153.6	153.6
-77.5°	153.5	153.5	153.5	153.5	153.5	153.4	153.4	153.4	153.4	153.4	153.4



REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	153.2	153.2	153.2	153.2	153.2	153.2	153.2	153.2	153.2	153.1	153.1
-80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-82.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-83.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-85°	153.0	153.0	153.0	153.1	153.1	153.1	153.1	153.1	153.2	153.2	153.2
-86.25°	154.0	154.0	154.0	154.0	154.1	154.1	154.1	154.1	154.1	154.1	154.2
-87.5°	155.0	155.0	155.0	155.0	155.0	155.0	155.1	155.1	155.1	155.1	155.1
-88.75°	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.0	156.1
-90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
88.75°	156.1	156.1	156.1	156.1	156.1	156.1	156.1	156.1	156.1	156.1	156.2
87.5°	155.1	155.1	155.2	155.2	155.2	155.2	155.2	155.2	155.3	155.3	155.3
86.25°	154.2	154.2	154.2	154.3	154.3	154.3	154.3	154.4	154.4	154.4	154.5
85°	153.2	153.3	153.3	153.3	153.4	153.4	153.5	153.5	153.5	153.6	153.6
83.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
82.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
78.75°	153.1	153.1	153.1	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0
77.5°	153.3	153.3	153.3	153.3	153.3	153.2	153.2	153.2	153.2	153.1	153.1
76.25°	153.6	153.6	153.5	153.5	153.5	153.5	153.4	153.4	153.4	153.3	153.3
75°	153.8	153.8	153.8	153.7	153.7	153.7	153.7	153.6	153.6	153.6	153.5
73.75°	154.0	154.0	154.0	154.0	153.9	153.9	153.9	153.8	153.8	153.8	153.7
72.5°	154.3	154.3	154.2	154.2	154.2	154.1	154.1	154.1	154.0	154.0	153.9
71.25°	154.5	154.5	154.5	154.4	154.4	154.4	154.3	154.3	154.2	154.2	154.1
70°	154.7	154.7	154.7	154.6	154.6	154.6	154.5	154.5	154.4	154.4	154.4
68.75°	155.0	154.9	154.9	154.9	154.8	154.8	154.8	154.7	154.7	154.6	154.6
67.5°	154.8	154.8	154.9	154.9	154.9	155.0	155.0	154.9	154.9	154.8	154.8
66.25°	154.6	154.6	154.6	154.7	154.7	154.8	154.8	154.9	154.9	155.0	155.0
65°	154.3	154.4	154.4	154.4	154.5	154.5	154.6	154.7	154.7	154.8	154.8
63.75°	154.1	154.1	154.2	154.2	154.3	154.3	154.4	154.4	154.5	154.6	154.6
62.5°	154.4	154.3	154.2	154.0	154.1	154.1	154.2	154.2	154.3	154.3	154.4
61.25°	155.1	155.0	154.8	154.7	154.5	154.3	154.2	154.0	154.1	154.1	154.2
60°	155.8	155.7	155.5	155.3	155.2	155.0	154.8	154.6	154.4	154.2	154.0
58.75°	156.5	156.3	156.2	156.0	155.8	155.6	155.4	155.2	155.0	154.8	154.6
57.5°	157.0	157.0	156.9	156.7	156.5	156.3	156.1	155.9	155.6	155.4	155.2
56.25°	157.0	157.0	157.0	157.0	157.0	156.9	156.7	156.5	156.3	156.0	155.8
55°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	156.9	156.6	156.4
53.75°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	156.9
52.5°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
51.25°	159.7	158.8	157.9	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
50°	162.6	161.7	160.7	159.7	158.6	157.5	157.0	157.0	157.0	157.0	157.0
48.75°	165.5	164.6	163.6	162.5	161.4	160.3	159.1	157.8	157.0	157.0	157.0
47.5°	168.5	167.5	166.4	165.3	164.2	163.0	161.7	160.4	159.1	157.7	157.0
46.25°	179.5	172.3	169.2	168.1	166.9	165.7	164.4	163.0	161.7	160.2	158.8
45°	199.5	192.1	184.2	176.0	169.6	168.3	167.0	165.6	164.2	162.7	161.2
43.75°	219.5	211.7	203.6	195.0	186.1	176.9	169.6	168.2	166.7	165.2	163.6
42.5°	239.4	231.3	222.8	213.9	204.7	195.1	185.2	174.9	169.2	167.6	166.0
41.25°	259.1	250.7	241.9	232.7	223.2	213.2	202.9	192.2	181.3	170.0	168.3
40°	263.8	262.0	260.2	251.4	241.4	231.1	220.5	209.4	198.1	186.4	174.4
38.75°	267.7	265.8	264.0	262.0	259.6	248.9	237.9	226.5	214.7	202.7	190.3
37.5°	271.5	269.7	267.7	265.6	263.5	261.3	255.1	243.3	231.2	218.7	206.0
36.25°	275.4	273.4	271.4	269.3	267.1	264.8	262.4	259.9	247.4	234.5	221.4
35°	277.9	277.2	275.1	272.9	270.6	268.2	265.8	263.3	260.7	250.1	236.6

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	277.4	277.7	277.9	276.4	274.0	271.6	269.1	266.5	263.8	261.1	251.5
32.5°	277.0	277.3	277.5	277.8	277.5	274.9	272.3	269.7	266.9	264.1	261.2
31.25°	276.6	276.9	277.1	277.4	277.7	278.0	275.5	272.8	269.9	267.1	264.1
30°	276.2	276.5	276.7	277.0	277.3	277.6	277.9	275.8	272.9	269.9	266.9
28.75°	276.8	276.1	276.4	276.7	277.0	277.3	277.6	277.9	275.8	272.8	269.7
27.5°	278.3	277.2	276.1	276.3	276.6	276.9	277.2	277.6	277.9	275.5	272.3
26.25°	279.9	278.7	277.5	276.3	276.3	276.6	276.9	277.3	277.6	278.0	274.9
25°	281.4	280.2	279.0	277.7	276.4	276.3	276.6	277.0	277.3	277.7	277.5
23.75°	282.9	281.7	280.4	279.1	277.7	276.3	276.3	276.7	277.0	277.4	277.8
22.5°	285.1	283.1	281.8	280.4	279.0	277.5	276.1	276.4	276.7	277.1	277.5
21.25°	289.0	285.3	283.1	281.7	280.2	278.7	277.2	276.1	276.5	276.9	277.3
20°	292.8	289.0	285.1	282.9	281.4	279.9	278.3	276.8	276.2	276.6	277.0
18.75°	297.5	292.6	288.5	284.4	282.6	281.0	279.4	277.8	276.1	276.4	276.8
17.5°	303.4	296.7	291.8	287.5	283.7	282.1	280.4	278.8	277.1	276.2	276.6
16.25°	309.0	302.1	295.0	290.6	286.1	283.1	281.4	279.7	278.0	276.3	276.4
15°	314.3	307.2	299.9	293.4	288.8	284.1	282.3	280.6	278.8	277.1	276.2
13.75°	319.4	312.0	304.5	296.9	291.4	286.6	283.2	281.4	279.6	277.8	276.0
12.5°	324.2	316.6	308.8	301.0	293.8	288.9	284.0	282.2	280.4	278.5	276.7
11.25°	328.6	320.8	312.8	304.8	296.7	291.0	286.0	282.9	281.0	279.2	277.3
10°	334.1	324.6	316.5	308.3	300.0	293.0	287.8	283.5	281.6	279.8	277.9
8.75°	341.1	328.1	319.8	311.4	303.0	294.7	289.5	284.3	282.2	280.3	278.3
7.5°	347.2	331.3	322.7	314.1	305.6	297.0	290.9	285.6	282.7	280.7	278.8
6.25°	352.5	336.3	325.2	316.5	307.8	299.1	292.2	286.8	283.1	281.1	279.2
5°	357.0	340.5	327.3	318.5	309.7	300.8	293.2	287.8	283.4	281.4	279.5
3.75°	360.5	343.7	328.9	320.0	311.1	302.2	294.0	288.5	283.7	281.7	279.7
2.5°	363.0	346.1	330.1	321.1	312.2	303.2	294.5	289.1	283.8	281.9	279.9
1.25°	364.5	347.5	330.8	321.8	312.8	303.8	294.9	289.4	284.0	282.0	280.0
0°	365.0	348.0	331.0	322.0	313.0	304.0	295.0	289.5	284.0	282.0	280.0
-1.25°	364.5	347.5	330.8	321.8	312.8	303.8	294.9	289.4	284.0	282.0	280.0
-2.5°	363.0	346.1	330.1	321.1	312.2	303.2	294.5	289.1	283.8	281.9	279.9
-3.75°	360.5	343.7	328.9	320.0	311.1	302.2	294.0	288.5	283.7	281.7	279.7
-5°	357.0	340.5	327.3	318.5	309.7	300.8	293.2	287.8	283.4	281.4	279.5
-6.25°	352.5	336.3	325.2	316.5	307.8	299.1	292.2	286.8	283.1	281.1	279.2
-7.5°	347.2	331.3	322.7	314.1	305.6	297.0	290.9	285.6	282.7	280.7	278.8
-8.75°	341.1	328.1	319.8	311.4	303.0	294.7	289.5	284.3	282.2	280.3	278.3
-10°	334.1	324.6	316.5	308.3	300.0	293.0	287.8	283.5	281.6	279.8	277.9
-11.25°	328.6	320.8	312.8	304.8	296.7	291.0	286.0	282.9	281.0	279.2	277.3
-12.5°	324.2	316.6	308.8	301.0	293.8	288.9	284.0	282.2	280.4	278.5	276.7
-13.75°	319.4	312.0	304.5	296.9	291.4	286.6	283.2	281.4	279.6	277.8	276.0
-15°	314.3	307.2	299.9	293.4	288.8	284.1	282.3	280.6	278.8	277.1	276.2
-16.25°	309.0	302.1	295.0	290.6	286.1	283.1	281.4	279.7	278.0	276.3	276.4
-17.5°	303.4	296.7	291.8	287.5	283.7	282.1	280.4	278.8	277.1	276.2	276.6
-18.75°	297.5	292.6	288.5	284.4	282.6	281.0	279.4	277.8	276.1	276.4	276.8
-20°	292.8	289.0	285.1	282.9	281.4	279.9	278.3	276.8	276.2	276.6	277.0
-21.25°	289.0	285.3	283.1	281.7	280.2	278.7	277.2	276.1	276.5	276.9	277.3

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	285.1	283.1	281.8	280.4	279.0	277.5	276.1	276.4	276.7	277.1	277.5
-23.75°	282.9	281.7	280.4	279.1	277.7	276.3	276.3	276.7	277.0	277.4	277.8
-25°	281.4	280.2	279.0	277.7	276.4	276.3	276.6	277.0	277.3	277.7	277.5
-26.25°	279.9	278.7	277.5	276.3	276.3	276.6	276.9	277.3	277.6	278.0	274.9
-27.5°	278.3	277.2	276.1	276.3	276.6	276.9	277.2	277.6	277.9	275.5	272.3
-28.75°	276.8	276.1	276.4	276.7	277.0	277.3	277.6	277.9	275.8	272.8	269.7
-30°	276.2	276.5	276.7	277.0	277.3	277.6	277.9	275.8	272.9	269.9	266.9
-31.25°	276.6	276.9	277.1	277.4	277.7	278.0	275.5	272.8	269.9	267.1	264.1
-32.5°	277.0	277.3	277.5	277.8	277.5	274.9	272.3	269.7	266.9	264.1	261.2
-33.75°	277.4	277.7	277.9	276.4	274.0	271.6	269.1	266.5	263.8	261.1	251.5
-35°	277.9	277.2	275.1	272.9	270.6	268.2	265.8	263.3	260.7	250.1	236.6
-36.25°	275.4	273.4	271.4	269.3	267.1	264.8	262.4	259.9	247.4	234.5	221.4
-37.5°	271.5	269.7	267.7	265.6	263.5	261.3	255.1	243.3	231.2	218.7	206.0
-38.75°	267.7	265.8	264.0	262.0	259.6	248.9	237.9	226.5	214.7	202.7	190.3
-40°	263.8	262.0	260.2	251.4	241.4	231.1	220.5	209.4	198.1	186.4	174.4
-41.25°	259.1	250.7	241.9	232.7	223.2	213.2	202.9	192.2	181.3	170.0	168.3
-42.5°	239.4	231.3	222.8	213.9	204.7	195.1	185.2	174.9	169.2	167.6	166.0
-43.75°	219.5	211.7	203.6	195.0	186.1	176.9	169.6	168.2	166.7	165.2	163.6
-45°	199.5	192.1	184.2	176.0	169.6	168.3	167.0	165.6	164.2	162.7	161.2
-46.25°	179.5	172.3	169.2	168.1	166.9	165.7	164.4	163.0	161.7	160.2	158.8
-47.5°	168.5	167.5	166.4	165.3	164.2	163.0	161.7	160.4	159.1	157.7	157.0
-48.75°	165.5	164.6	163.6	162.5	161.4	160.3	159.1	157.8	157.0	157.0	157.0
-50°	162.6	161.7	160.7	159.7	158.6	157.5	157.0	157.0	157.0	157.0	157.0
-51.25°	159.7	158.8	157.9	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-52.5°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-53.75°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	156.9
-55°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	156.9	156.6	156.4
-56.25°	157.0	157.0	157.0	157.0	157.0	156.9	156.7	156.5	156.3	156.0	155.8
-57.5°	157.0	157.0	156.9	156.7	156.5	156.3	156.1	155.9	155.6	155.4	155.2
-58.75°	156.5	156.3	156.2	156.0	155.8	155.6	155.4	155.2	155.0	154.8	154.6
-60°	155.8	155.7	155.5	155.3	155.2	155.0	154.8	154.6	154.4	154.2	154.0
-61.25°	155.1	155.0	154.8	154.7	154.5	154.3	154.2	154.0	154.1	154.1	154.2
-62.5°	154.4	154.3	154.2	154.0	154.1	154.1	154.2	154.2	154.3	154.3	154.4
-63.75°	154.1	154.1	154.2	154.2	154.3	154.3	154.4	154.4	154.5	154.6	154.6
-65°	154.3	154.4	154.4	154.4	154.5	154.5	154.6	154.7	154.7	154.8	154.8
-66.25°	154.6	154.6	154.6	154.7	154.7	154.8	154.8	154.9	154.9	155.0	155.0
-67.5°	154.8	154.8	154.9	154.9	154.9	155.0	155.0	154.9	154.9	154.8	154.8
-68.75°	155.0	154.9	154.9	154.9	154.8	154.8	154.8	154.7	154.7	154.6	154.6
-70°	154.7	154.7	154.7	154.6	154.6	154.6	154.5	154.5	154.4	154.4	154.4
-71.25°	154.5	154.5	154.5	154.4	154.4	154.4	154.3	154.3	154.2	154.2	154.1
-72.5°	154.3	154.3	154.2	154.2	154.2	154.1	154.1	154.1	154.0	154.0	153.9
-73.75°	154.0	154.0	154.0	154.0	153.9	153.9	153.9	153.8	153.8	153.8	153.7
-75°	153.8	153.8	153.8	153.7	153.7	153.7	153.7	153.6	153.6	153.6	153.5
-76.25°	153.6	153.6	153.5	153.5	153.5	153.5	153.4	153.4	153.4	153.3	153.3
-77.5°	153.3	153.3	153.3	153.3	153.3	153.2	153.2	153.2	153.2	153.1	153.1

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	153.1	153.1	153.1	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-82.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-83.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-85°	153.2	153.3	153.3	153.3	153.4	153.4	153.5	153.5	153.5	153.6	153.6
-86.25°	154.2	154.2	154.2	154.3	154.3	154.3	154.3	154.4	154.4	154.4	154.5
-87.5°	155.1	155.1	155.2	155.2	155.2	155.2	155.2	155.2	155.3	155.3	155.3
-88.75°	156.1	156.1	156.1	156.1	156.1	156.1	156.1	156.1	156.1	156.1	156.2
-90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
88.75°	156.2	156.2	156.2	156.2	156.2	156.2	156.2	156.3	156.3	156.3	156.3
87.5°	155.3	155.4	155.4	155.4	155.4	155.5	155.5	155.5	155.6	155.6	155.6
86.25°	154.5	154.5	154.6	154.6	154.7	154.7	154.7	154.8	154.8	154.9	154.9
85°	153.7	153.7	153.8	153.8	153.9	153.9	154.0	154.1	154.1	154.2	154.2
83.75°	153.0	153.0	153.0	153.0	153.1	153.2	153.2	153.3	153.4	153.5	153.5
82.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
78.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
77.5°	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
76.25°	153.3	153.2	153.2	153.2	153.1	153.1	153.1	153.0	153.0	153.0	153.0
75°	153.5	153.4	153.4	153.4	153.3	153.3	153.2	153.2	153.2	153.1	153.1
73.75°	153.7	153.7	153.6	153.6	153.5	153.5	153.4	153.4	153.3	153.3	153.2
72.5°	153.9	153.9	153.8	153.8	153.7	153.7	153.6	153.6	153.5	153.5	153.4
71.25°	154.1	154.1	154.0	154.0	153.9	153.9	153.8	153.7	153.7	153.6	153.6
70°	154.3	154.3	154.2	154.1	154.1	154.0	154.0	153.9	153.9	153.8	153.7
68.75°	154.5	154.5	154.4	154.3	154.3	154.2	154.2	154.1	154.0	154.0	153.9
67.5°	154.7	154.7	154.6	154.5	154.5	154.4	154.3	154.3	154.2	154.1	154.1
66.25°	154.9	154.9	154.8	154.7	154.7	154.6	154.5	154.5	154.4	154.3	154.2
65°	154.9	154.9	155.0	154.9	154.8	154.8	154.7	154.6	154.6	154.5	154.4
63.75°	154.7	154.8	154.8	154.9	155.0	155.0	154.9	154.8	154.7	154.6	154.6
62.5°	154.5	154.6	154.6	154.7	154.8	154.9	154.9	155.0	154.9	154.8	154.7
61.25°	154.3	154.4	154.4	154.5	154.6	154.7	154.8	154.8	154.9	155.0	154.9
60°	154.1	154.2	154.2	154.3	154.4	154.5	154.6	154.7	154.8	154.9	155.0
58.75°	154.3	154.1	154.1	154.1	154.2	154.3	154.4	154.5	154.6	154.7	154.8
57.5°	154.9	154.7	154.4	154.1	154.0	154.1	154.2	154.3	154.4	154.5	154.6
56.25°	155.5	155.2	155.0	154.7	154.4	154.1	154.1	154.2	154.3	154.4	154.5
55°	156.1	155.8	155.5	155.2	154.9	154.6	154.3	154.0	154.1	154.2	154.3
53.75°	156.7	156.4	156.1	155.8	155.5	155.2	154.8	154.5	154.2	154.1	154.2
52.5°	157.0	156.9	156.6	156.3	156.0	155.7	155.3	155.0	154.7	154.3	154.0
51.25°	157.0	157.0	157.0	156.9	156.5	156.2	155.8	155.5	155.1	154.8	154.4
50°	157.0	157.0	157.0	157.0	157.0	156.7	156.3	156.0	155.6	155.2	154.8
48.75°	157.0	157.0	157.0	157.0	157.0	157.0	156.8	156.5	156.1	155.7	155.3
47.5°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	156.9	156.5	156.1	155.7
46.25°	157.3	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	156.6	156.1
45°	159.6	158.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	156.6
43.75°	162.0	160.3	158.6	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
42.5°	164.3	162.6	160.9	159.1	157.3	157.0	157.0	157.0	157.0	157.0	157.0
41.25°	166.6	164.8	163.0	161.2	159.3	157.4	157.0	157.0	157.0	157.0	157.0
40°	168.9	167.1	165.2	163.3	161.4	159.4	157.4	157.0	157.0	157.0	157.0
38.75°	177.6	169.2	167.3	165.4	163.4	161.4	159.3	157.3	157.0	157.0	157.0
37.5°	192.9	179.6	169.4	167.4	165.4	163.3	161.2	159.1	157.0	157.0	157.0
36.25°	207.9	194.2	180.2	169.4	167.3	165.2	163.0	160.9	158.6	157.0	157.0
35°	222.7	208.6	194.2	179.6	169.2	167.1	164.8	162.6	160.3	158.0	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	237.3	222.7	207.9	192.9	177.6	168.9	166.6	164.3	162.0	159.6	157.3
32.5°	251.5	236.6	221.4	206.0	190.3	174.4	168.3	166.0	163.6	161.2	158.8
31.25°	261.1	250.1	234.5	218.7	202.7	186.4	170.0	167.6	165.2	162.7	160.2
30°	263.8	260.7	247.4	231.2	214.7	198.1	181.3	169.2	166.7	164.2	161.7
28.75°	266.5	263.3	259.9	243.3	226.5	209.4	192.2	174.9	168.2	165.6	163.0
27.5°	269.1	265.8	262.4	255.1	237.9	220.5	202.9	185.2	169.6	167.0	164.4
26.25°	271.6	268.2	264.8	261.3	248.9	231.1	213.2	195.1	176.9	168.3	165.7
25°	274.0	270.6	267.1	263.5	259.6	241.4	223.2	204.7	186.1	169.6	166.9
23.75°	276.4	272.9	269.3	265.6	262.0	251.4	232.7	213.9	195.0	176.0	168.1
22.5°	277.9	275.1	271.4	267.7	264.0	260.2	241.9	222.8	203.6	184.2	169.2
21.25°	277.7	277.2	273.4	269.7	265.8	262.0	250.7	231.3	211.7	192.1	172.3
20°	277.4	277.9	275.4	271.5	267.7	263.8	259.1	239.4	219.5	199.5	179.5
18.75°	277.2	277.7	277.2	273.3	269.4	265.4	261.4	247.0	226.9	206.6	186.3
17.5°	277.0	277.5	277.9	275.0	271.0	267.0	262.9	254.3	233.8	213.3	192.7
16.25°	276.8	277.3	277.7	276.6	272.5	268.4	264.3	260.2	240.3	219.6	198.7
15°	276.6	277.1	277.5	278.0	274.0	269.8	265.7	261.5	246.4	225.4	204.4
13.75°	276.5	276.9	277.4	277.8	275.3	271.1	266.9	262.7	252.1	230.9	209.6
12.5°	276.3	276.8	277.2	277.7	276.5	272.3	268.0	263.7	257.3	235.8	214.3
11.25°	276.1	276.6	277.1	277.6	277.6	273.3	269.0	264.7	260.4	240.4	218.7
10°	276.0	276.5	277.0	277.4	277.9	274.3	270.0	265.6	261.3	244.4	222.6
8.75°	276.4	276.4	276.9	277.3	277.8	275.2	270.8	266.4	262.0	248.1	226.1
7.5°	276.8	276.3	276.8	277.3	277.7	275.9	271.5	267.1	262.7	251.2	229.1
6.25°	277.2	276.2	276.7	277.2	277.7	276.5	272.1	267.7	263.2	253.9	231.6
5°	277.5	276.1	276.6	277.1	277.6	277.1	272.6	268.1	263.7	256.1	233.7
3.75°	277.7	276.1	276.6	277.1	277.6	277.5	273.0	268.5	264.0	257.8	235.4
2.5°	277.9	276.0	276.5	277.0	277.5	277.8	273.3	268.8	264.3	259.0	236.6
1.25°	278.0	276.0	276.5	277.0	277.5	277.9	273.4	268.9	264.4	259.8	237.3
0°	278.0	276.0	276.5	277.0	277.5	278.0	273.5	269.0	264.5	260.0	237.5
-1.25°	278.0	276.0	276.5	277.0	277.5	277.9	273.4	268.9	264.4	259.8	237.3
-2.5°	277.9	276.0	276.5	277.0	277.5	277.8	273.3	268.8	264.3	259.0	236.6
-3.75°	277.7	276.1	276.6	277.1	277.6	277.5	273.0	268.5	264.0	257.8	235.4
-5°	277.5	276.1	276.6	277.1	277.6	277.1	272.6	268.1	263.7	256.1	233.7
-6.25°	277.2	276.2	276.7	277.2	277.7	276.5	272.1	267.7	263.2	253.9	231.6
-7.5°	276.8	276.3	276.8	277.3	277.7	275.9	271.5	267.1	262.7	251.2	229.1
-8.75°	276.4	276.4	276.9	277.3	277.8	275.2	270.8	266.4	262.0	248.1	226.1
-10°	276.0	276.5	277.0	277.4	277.9	274.3	270.0	265.6	261.3	244.4	222.6
-11.25°	276.1	276.6	277.1	277.6	277.6	273.3	269.0	264.7	260.4	240.4	218.7
-12.5°	276.3	276.8	277.2	277.7	276.5	272.3	268.0	263.7	257.3	235.8	214.3
-13.75°	276.5	276.9	277.4	277.8	275.3	271.1	266.9	262.7	252.1	230.9	209.6
-15°	276.6	277.1	277.5	278.0	274.0	269.8	265.7	261.5	246.4	225.4	204.4
-16.25°	276.8	277.3	277.7	276.6	272.5	268.4	264.3	260.2	240.3	219.6	198.7
-17.5°	277.0	277.5	277.9	275.0	271.0	267.0	262.9	254.3	233.8	213.3	192.7
-18.75°	277.2	277.7	277.2	273.3	269.4	265.4	261.4	247.0	226.9	206.6	186.3
-20°	277.4	277.9	275.4	271.5	267.7	263.8	259.1	239.4	219.5	199.5	179.5
-21.25°	277.7	277.2	273.4	269.7	265.8	262.0	250.7	231.3	211.7	192.1	172.3

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	277.9	275.1	271.4	267.7	264.0	260.2	241.9	222.8	203.6	184.2	169.2
-23.75°	276.4	272.9	269.3	265.6	262.0	251.4	232.7	213.9	195.0	176.0	168.1
-25°	274.0	270.6	267.1	263.5	259.6	241.4	223.2	204.7	186.1	169.6	166.9
-26.25°	271.6	268.2	264.8	261.3	248.9	231.1	213.2	195.1	176.9	168.3	165.7
-27.5°	269.1	265.8	262.4	255.1	237.9	220.5	202.9	185.2	169.6	167.0	164.4
-28.75°	266.5	263.3	259.9	243.3	226.5	209.4	192.2	174.9	168.2	165.6	163.0
-30°	263.8	260.7	247.4	231.2	214.7	198.1	181.3	169.2	166.7	164.2	161.7
-31.25°	261.1	250.1	234.5	218.7	202.7	186.4	170.0	167.6	165.2	162.7	160.2
-32.5°	251.5	236.6	221.4	206.0	190.3	174.4	168.3	166.0	163.6	161.2	158.8
-33.75°	237.3	222.7	207.9	192.9	177.6	168.9	166.6	164.3	162.0	159.6	157.3
-35°	222.7	208.6	194.2	179.6	169.2	167.1	164.8	162.6	160.3	158.0	157.0
-36.25°	207.9	194.2	180.2	169.4	167.3	165.2	163.0	160.9	158.6	157.0	157.0
-37.5°	192.9	179.6	169.4	167.4	165.4	163.3	161.2	159.1	157.0	157.0	157.0
-38.75°	177.6	169.2	167.3	165.4	163.4	161.4	159.3	157.3	157.0	157.0	157.0
-40°	168.9	167.1	165.2	163.3	161.4	159.4	157.4	157.0	157.0	157.0	157.0
-41.25°	166.6	164.8	163.0	161.2	159.3	157.4	157.0	157.0	157.0	157.0	157.0
-42.5°	164.3	162.6	160.9	159.1	157.3	157.0	157.0	157.0	157.0	157.0	157.0
-43.75°	162.0	160.3	158.6	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
-45°	159.6	158.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	156.6
-46.25°	157.3	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	156.6	156.1
-47.5°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	156.9	156.5	156.1	155.7
-48.75°	157.0	157.0	157.0	157.0	157.0	157.0	156.8	156.5	156.1	155.7	155.3
-50°	157.0	157.0	157.0	157.0	157.0	156.7	156.3	156.0	155.6	155.2	154.8
-51.25°	157.0	157.0	157.0	156.9	156.5	156.2	155.8	155.5	155.1	154.8	154.4
-52.5°	157.0	156.9	156.6	156.3	156.0	155.7	155.3	155.0	154.7	154.3	154.0
-53.75°	156.7	156.4	156.1	155.8	155.5	155.2	154.8	154.5	154.2	154.1	154.2
-55°	156.1	155.8	155.5	155.2	154.9	154.6	154.3	154.0	154.1	154.2	154.3
-56.25°	155.5	155.2	155.0	154.7	154.4	154.1	154.1	154.2	154.3	154.4	154.5
-57.5°	154.9	154.7	154.4	154.1	154.0	154.1	154.2	154.3	154.4	154.5	154.6
-58.75°	154.3	154.1	154.1	154.1	154.2	154.3	154.4	154.5	154.6	154.7	154.8
-60°	154.1	154.2	154.2	154.3	154.4	154.5	154.6	154.7	154.8	154.9	155.0
-61.25°	154.3	154.4	154.4	154.5	154.6	154.7	154.8	154.8	154.9	155.0	154.9
-62.5°	154.5	154.6	154.6	154.7	154.8	154.9	154.9	155.0	154.9	154.8	154.7
-63.75°	154.7	154.8	154.8	154.9	155.0	155.0	154.9	154.8	154.7	154.6	154.6
-65°	154.9	154.9	155.0	154.9	154.8	154.8	154.7	154.6	154.6	154.5	154.4
-66.25°	154.9	154.9	154.8	154.7	154.7	154.6	154.5	154.5	154.4	154.3	154.2
-67.5°	154.7	154.7	154.6	154.5	154.5	154.4	154.3	154.3	154.2	154.1	154.1
-68.75°	154.5	154.5	154.4	154.3	154.3	154.2	154.2	154.1	154.0	154.0	153.9
-70°	154.3	154.3	154.2	154.1	154.1	154.0	154.0	153.9	153.9	153.8	153.7
-71.25°	154.1	154.1	154.0	154.0	153.9	153.9	153.8	153.7	153.7	153.6	153.6
-72.5°	153.9	153.9	153.8	153.8	153.7	153.7	153.6	153.6	153.5	153.5	153.4
-73.75°	153.7	153.7	153.6	153.6	153.5	153.5	153.4	153.4	153.3	153.3	153.2
-75°	153.5	153.4	153.4	153.4	153.3	153.3	153.2	153.2	153.2	153.1	153.1
-76.25°	153.3	153.2	153.2	153.2	153.1	153.1	153.1	153.0	153.0	153.0	153.0
-77.5°	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0



REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-82.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-83.75°	153.0	153.0	153.0	153.0	153.1	153.2	153.2	153.3	153.4	153.5	153.5
-85°	153.7	153.7	153.8	153.8	153.9	153.9	154.0	154.1	154.1	154.2	154.2
-86.25°	154.5	154.5	154.6	154.6	154.7	154.7	154.7	154.8	154.8	154.9	154.9
-87.5°	155.3	155.4	155.4	155.4	155.4	155.5	155.5	155.5	155.6	155.6	155.6
-88.75°	156.2	156.2	156.2	156.2	156.2	156.2	156.2	156.3	156.3	156.3	156.3
-90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
88.75°	156.3	156.3	156.4	156.4	156.4	156.4	156.4	156.4	156.5	156.5	156.5
87.5°	155.6	155.7	155.7	155.7	155.8	155.8	155.9	155.9	155.9	156.0	156.0
86.25°	155.0	155.0	155.1	155.1	155.2	155.2	155.3	155.3	155.4	155.4	155.5
85°	154.3	154.4	154.4	154.5	154.6	154.6	154.7	154.8	154.9	154.9	155.0
83.75°	153.6	153.7	153.8	153.9	154.0	154.0	154.1	154.2	154.3	154.4	154.5
82.5°	153.0	153.1	153.1	153.3	153.4	153.5	153.6	153.7	153.8	153.9	154.0
81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.2	153.4	153.5
80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
78.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
77.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
76.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
73.75°	153.2	153.1	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
72.5°	153.3	153.3	153.2	153.2	153.1	153.0	153.0	153.0	153.0	153.0	153.0
71.25°	153.5	153.4	153.4	153.3	153.3	153.2	153.1	153.1	153.0	153.0	153.0
70°	153.7	153.6	153.5	153.5	153.4	153.3	153.3	153.2	153.1	153.0	153.0
68.75°	153.8	153.8	153.7	153.6	153.5	153.5	153.4	153.3	153.2	153.2	153.1
67.5°	154.0	153.9	153.8	153.8	153.7	153.6	153.5	153.5	153.4	153.3	153.2
66.25°	154.2	154.1	154.0	153.9	153.8	153.8	153.7	153.6	153.5	153.4	153.3
65°	154.3	154.2	154.2	154.1	154.0	153.9	153.8	153.7	153.6	153.5	153.4
63.75°	154.5	154.4	154.3	154.2	154.1	154.0	153.9	153.8	153.7	153.7	153.6
62.5°	154.6	154.5	154.5	154.4	154.3	154.2	154.1	154.0	153.9	153.8	153.7
61.25°	154.8	154.7	154.6	154.5	154.4	154.3	154.2	154.1	154.0	153.9	153.8
60°	154.9	154.8	154.7	154.6	154.5	154.4	154.3	154.2	154.1	154.0	153.9
58.75°	154.9	155.0	154.9	154.8	154.7	154.6	154.5	154.4	154.2	154.1	154.0
57.5°	154.7	154.9	155.0	154.9	154.8	154.7	154.6	154.5	154.4	154.2	154.1
56.25°	154.6	154.7	154.8	154.9	155.0	154.8	154.7	154.6	154.5	154.4	154.2
55°	154.4	154.6	154.7	154.8	154.9	155.0	154.8	154.7	154.6	154.5	154.3
53.75°	154.3	154.4	154.5	154.7	154.8	154.9	155.0	154.8	154.7	154.6	154.4
52.5°	154.1	154.3	154.4	154.5	154.6	154.8	154.9	155.0	154.8	154.7	154.5
51.25°	154.0	154.1	154.3	154.4	154.5	154.7	154.8	154.9	154.9	154.8	154.6
50°	154.4	154.0	154.1	154.3	154.4	154.5	154.7	154.8	155.0	154.9	154.7
48.75°	154.9	154.5	154.0	154.1	154.3	154.4	154.6	154.7	154.9	155.0	154.8
47.5°	155.3	154.9	154.4	154.0	154.1	154.3	154.4	154.6	154.7	154.9	154.9
46.25°	155.7	155.3	154.8	154.4	154.0	154.2	154.3	154.5	154.6	154.8	155.0
45°	156.1	155.7	155.2	154.8	154.3	154.1	154.2	154.4	154.5	154.7	154.9
43.75°	156.5	156.1	155.6	155.1	154.7	154.2	154.1	154.3	154.4	154.6	154.8
42.5°	156.9	156.5	156.0	155.5	155.0	154.5	154.0	154.2	154.3	154.5	154.7
41.25°	157.0	156.8	156.3	155.8	155.3	154.8	154.3	154.1	154.2	154.4	154.6
40°	157.0	157.0	156.7	156.2	155.7	155.2	154.6	154.1	154.1	154.3	154.5
38.75°	157.0	157.0	157.0	156.5	156.0	155.5	154.9	154.4	154.0	154.2	154.4
37.5°	157.0	157.0	157.0	156.9	156.3	155.8	155.2	154.7	154.1	154.1	154.3
36.25°	157.0	157.0	157.0	157.0	156.6	156.1	155.5	155.0	154.4	154.1	154.2
35°	157.0	157.0	157.0	157.0	156.9	156.4	155.8	155.2	154.7	154.1	154.2

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	157.0	157.0	157.0	157.0	157.0	156.7	156.1	155.5	154.9	154.3	154.1
32.5°	157.0	157.0	157.0	157.0	157.0	156.9	156.4	155.8	155.2	154.6	154.0
31.25°	157.7	157.0	157.0	157.0	157.0	157.0	156.6	156.0	155.4	154.8	154.2
30°	159.1	157.0	157.0	157.0	157.0	157.0	156.9	156.3	155.6	155.0	154.4
28.75°	160.4	157.8	157.0	157.0	157.0	157.0	157.0	156.5	155.9	155.2	154.6
27.5°	161.7	159.1	157.0	157.0	157.0	157.0	157.0	156.7	156.1	155.4	154.8
26.25°	163.0	160.3	157.5	157.0	157.0	157.0	157.0	156.9	156.3	155.6	155.0
25°	164.2	161.4	158.6	157.0	157.0	157.0	157.0	157.0	156.5	155.8	155.2
23.75°	165.3	162.5	159.7	157.0	157.0	157.0	157.0	157.0	156.7	156.0	155.3
22.5°	166.4	163.6	160.7	157.9	157.0	157.0	157.0	157.0	156.9	156.2	155.5
21.25°	167.5	164.6	161.7	158.8	157.0	157.0	157.0	157.0	157.0	156.3	155.7
20°	168.5	165.5	162.6	159.7	157.0	157.0	157.0	157.0	157.0	156.5	155.8
18.75°	169.4	166.5	163.5	160.5	157.5	157.0	157.0	157.0	157.0	156.7	156.0
17.5°	172.1	167.3	164.3	161.3	158.3	157.0	157.0	157.0	157.0	156.8	156.1
16.25°	177.9	168.1	165.1	162.0	159.0	157.0	157.0	157.0	157.0	156.9	156.2
15°	183.2	168.9	165.8	162.7	159.6	157.0	157.0	157.0	157.0	157.0	156.3
13.75°	188.2	169.5	166.5	163.4	160.3	157.1	157.0	157.0	157.0	157.0	156.4
12.5°	192.8	171.3	167.1	163.9	160.8	157.7	157.0	157.0	157.0	157.0	156.5
11.25°	197.0	175.2	167.6	164.5	161.3	158.2	157.0	157.0	157.0	157.0	156.6
10°	200.7	178.8	168.1	164.9	161.8	158.6	157.0	157.0	157.0	157.0	156.7
8.75°	204.1	182.0	168.6	165.4	162.2	159.0	157.0	157.0	157.0	157.0	156.8
7.5°	206.9	184.8	168.9	165.7	162.5	159.3	157.0	157.0	157.0	157.0	156.8
6.25°	209.4	187.1	169.3	166.0	162.8	159.6	157.0	157.0	157.0	157.0	156.9
5°	211.4	189.1	169.5	166.3	163.1	159.8	157.0	157.0	157.0	157.0	156.9
3.75°	213.0	190.6	169.7	166.5	163.3	160.0	157.0	157.0	157.0	157.0	157.0
2.5°	214.1	191.6	169.9	166.6	163.4	160.1	157.0	157.0	157.0	157.0	157.0
1.25°	214.8	192.3	170.0	166.7	163.5	160.2	157.0	157.0	157.0	157.0	157.0
0°	215.0	192.5	170.0	166.8	163.5	160.3	157.0	157.0	157.0	157.0	157.0
-1.25°	214.8	192.3	170.0	166.7	163.5	160.2	157.0	157.0	157.0	157.0	157.0
-2.5°	214.1	191.6	169.9	166.6	163.4	160.1	157.0	157.0	157.0	157.0	157.0
-3.75°	213.0	190.6	169.7	166.5	163.3	160.0	157.0	157.0	157.0	157.0	157.0
-5°	211.4	189.1	169.5	166.3	163.1	159.8	157.0	157.0	157.0	157.0	156.9
-6.25°	209.4	187.1	169.3	166.0	162.8	159.6	157.0	157.0	157.0	157.0	156.9
-7.5°	206.9	184.8	168.9	165.7	162.5	159.3	157.0	157.0	157.0	157.0	156.8
-8.75°	204.1	182.0	168.6	165.4	162.2	159.0	157.0	157.0	157.0	157.0	156.8
-10°	200.7	178.8	168.1	164.9	161.8	158.6	157.0	157.0	157.0	157.0	156.7
-11.25°	197.0	175.2	167.6	164.5	161.3	158.2	157.0	157.0	157.0	157.0	156.6
-12.5°	192.8	171.3	167.1	163.9	160.8	157.7	157.0	157.0	157.0	157.0	156.5
-13.75°	188.2	169.5	166.5	163.4	160.3	157.1	157.0	157.0	157.0	157.0	156.4
-15°	183.2	168.9	165.8	162.7	159.6	157.0	157.0	157.0	157.0	157.0	156.3
-16.25°	177.9	168.1	165.1	162.0	159.0	157.0	157.0	157.0	157.0	156.9	156.2
-17.5°	172.1	167.3	164.3	161.3	158.3	157.0	157.0	157.0	157.0	156.8	156.1
-18.75°	169.4	166.5	163.5	160.5	157.5	157.0	157.0	157.0	157.0	156.7	156.0
-20°	168.5	165.5	162.6	159.7	157.0	157.0	157.0	157.0	157.0	156.5	155.8
-21.25°	167.5	164.6	161.7	158.8	157.0	157.0	157.0	157.0	157.0	156.3	155.7

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	166.4	163.6	160.7	157.9	157.0	157.0	157.0	157.0	156.9	156.2	155.5
-23.75°	165.3	162.5	159.7	157.0	157.0	157.0	157.0	157.0	156.7	156.0	155.3
-25°	164.2	161.4	158.6	157.0	157.0	157.0	157.0	157.0	156.5	155.8	155.2
-26.25°	163.0	160.3	157.5	157.0	157.0	157.0	157.0	156.9	156.3	155.6	155.0
-27.5°	161.7	159.1	157.0	157.0	157.0	157.0	157.0	156.7	156.1	155.4	154.8
-28.75°	160.4	157.8	157.0	157.0	157.0	157.0	157.0	156.5	155.9	155.2	154.6
-30°	159.1	157.0	157.0	157.0	157.0	157.0	156.9	156.3	155.6	155.0	154.4
-31.25°	157.7	157.0	157.0	157.0	157.0	157.0	156.6	156.0	155.4	154.8	154.2
-32.5°	157.0	157.0	157.0	157.0	157.0	156.9	156.4	155.8	155.2	154.6	154.0
-33.75°	157.0	157.0	157.0	157.0	157.0	156.7	156.1	155.5	154.9	154.3	154.1
-35°	157.0	157.0	157.0	157.0	156.9	156.4	155.8	155.2	154.7	154.1	154.2
-36.25°	157.0	157.0	157.0	157.0	156.6	156.1	155.5	155.0	154.4	154.1	154.2
-37.5°	157.0	157.0	157.0	156.9	156.3	155.8	155.2	154.7	154.1	154.1	154.3
-38.75°	157.0	157.0	157.0	156.5	156.0	155.5	154.9	154.4	154.0	154.2	154.4
-40°	157.0	157.0	156.7	156.2	155.7	155.2	154.6	154.1	154.1	154.3	154.5
-41.25°	157.0	156.8	156.3	155.8	155.3	154.8	154.3	154.1	154.2	154.4	154.6
-42.5°	156.9	156.5	156.0	155.5	155.0	154.5	154.0	154.2	154.3	154.5	154.7
-43.75°	156.5	156.1	155.6	155.1	154.7	154.2	154.1	154.3	154.4	154.6	154.8
-45°	156.1	155.7	155.2	154.8	154.3	154.1	154.2	154.4	154.5	154.7	154.9
-46.25°	155.7	155.3	154.8	154.4	154.0	154.2	154.3	154.5	154.6	154.8	155.0
-47.5°	155.3	154.9	154.4	154.0	154.1	154.3	154.4	154.6	154.7	154.9	154.9
-48.75°	154.9	154.5	154.0	154.1	154.3	154.4	154.6	154.7	154.9	155.0	154.8
-50°	154.4	154.0	154.1	154.3	154.4	154.5	154.7	154.8	155.0	154.9	154.7
-51.25°	154.0	154.1	154.3	154.4	154.5	154.7	154.8	154.9	154.9	154.8	154.6
-52.5°	154.1	154.3	154.4	154.5	154.6	154.8	154.9	155.0	154.8	154.7	154.5
-53.75°	154.3	154.4	154.5	154.7	154.8	154.9	155.0	154.8	154.7	154.6	154.4
-55°	154.4	154.6	154.7	154.8	154.9	155.0	154.8	154.7	154.6	154.5	154.3
-56.25°	154.6	154.7	154.8	154.9	155.0	154.8	154.7	154.6	154.5	154.4	154.2
-57.5°	154.7	154.9	155.0	154.9	154.8	154.7	154.6	154.5	154.4	154.2	154.1
-58.75°	154.9	155.0	154.9	154.8	154.7	154.6	154.5	154.4	154.2	154.1	154.0
-60°	154.9	154.8	154.7	154.6	154.5	154.4	154.3	154.2	154.1	154.0	153.9
-61.25°	154.8	154.7	154.6	154.5	154.4	154.3	154.2	154.1	154.0	153.9	153.8
-62.5°	154.6	154.5	154.5	154.4	154.3	154.2	154.1	154.0	153.9	153.8	153.7
-63.75°	154.5	154.4	154.3	154.2	154.1	154.0	153.9	153.8	153.7	153.7	153.6
-65°	154.3	154.2	154.2	154.1	154.0	153.9	153.8	153.7	153.6	153.5	153.4
-66.25°	154.2	154.1	154.0	153.9	153.8	153.8	153.7	153.6	153.5	153.4	153.3
-67.5°	154.0	153.9	153.8	153.8	153.7	153.6	153.5	153.5	153.4	153.3	153.2
-68.75°	153.8	153.8	153.7	153.6	153.5	153.5	153.4	153.3	153.2	153.2	153.1
-70°	153.7	153.6	153.5	153.5	153.4	153.3	153.3	153.2	153.1	153.0	153.0
-71.25°	153.5	153.4	153.4	153.3	153.3	153.2	153.1	153.1	153.0	153.0	153.0
-72.5°	153.3	153.3	153.2	153.2	153.1	153.0	153.0	153.0	153.0	153.0	153.0
-73.75°	153.2	153.1	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-76.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-77.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-80°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-81.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.2	153.4	153.5
-82.5°	153.0	153.1	153.1	153.3	153.4	153.5	153.6	153.7	153.8	153.9	154.0
-83.75°	153.6	153.7	153.8	153.9	154.0	154.0	154.1	154.2	154.3	154.4	154.5
-85°	154.3	154.4	154.4	154.5	154.6	154.6	154.7	154.8	154.9	154.9	155.0
-86.25°	155.0	155.0	155.1	155.1	155.2	155.2	155.3	155.3	155.4	155.4	155.5
-87.5°	155.6	155.7	155.7	155.7	155.8	155.8	155.9	155.9	155.9	156.0	156.0
-88.75°	156.3	156.3	156.4	156.4	156.4	156.4	156.4	156.4	156.5	156.5	156.5
-90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
88.75°	156.5	156.5	156.6	156.6	156.6	156.6	156.6	156.7	156.7	156.7	156.7
87.5°	156.0	156.1	156.1	156.2	156.2	156.2	156.3	156.3	156.4	156.4	156.4
86.25°	155.6	155.6	155.7	155.7	155.8	155.9	155.9	156.0	156.0	156.1	156.2
85°	155.1	155.2	155.2	155.3	155.4	155.5	155.6	155.6	155.7	155.8	155.9
83.75°	154.6	154.7	154.8	154.9	155.0	155.1	155.2	155.3	155.4	155.5	155.6
82.5°	154.1	154.2	154.4	154.5	154.6	154.7	154.8	155.0	155.1	155.2	155.3
81.25°	153.6	153.8	153.9	154.1	154.2	154.3	154.5	154.6	154.8	154.9	155.0
80°	153.2	153.3	153.5	153.6	153.8	154.0	154.1	154.3	154.4	154.6	154.8
78.75°	153.0	153.0	153.0	153.2	153.4	153.6	153.8	153.9	154.1	154.3	154.5
77.5°	153.0	153.0	153.0	153.0	153.0	153.2	153.4	153.6	153.8	154.0	154.2
76.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.3	153.5	153.7	153.9
75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.2	153.4	153.7
73.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.4
72.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1
71.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
70°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
68.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
67.5°	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
66.25°	153.2	153.1	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
65°	153.3	153.3	153.2	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0
63.75°	153.5	153.4	153.3	153.2	153.1	153.0	153.0	153.0	153.0	153.0	153.0
62.5°	153.6	153.5	153.4	153.3	153.1	153.0	153.0	153.0	153.0	153.0	153.0
61.25°	153.7	153.6	153.5	153.3	153.2	153.1	153.0	153.0	153.0	153.0	153.0
60°	153.8	153.7	153.6	153.4	153.3	153.2	153.1	153.0	153.0	153.0	153.0
58.75°	153.9	153.8	153.7	153.5	153.4	153.3	153.2	153.0	153.0	153.0	153.0
57.5°	154.0	153.9	153.7	153.6	153.5	153.4	153.2	153.1	153.0	153.0	153.0
56.25°	154.1	154.0	153.8	153.7	153.6	153.5	153.3	153.2	153.1	153.0	153.0
55°	154.2	154.1	153.9	153.8	153.7	153.5	153.4	153.3	153.1	153.0	153.0
53.75°	154.3	154.2	154.0	153.9	153.8	153.6	153.5	153.3	153.2	153.0	153.0
52.5°	154.4	154.3	154.1	154.0	153.8	153.7	153.5	153.4	153.3	153.1	153.0
51.25°	154.5	154.4	154.2	154.1	153.9	153.8	153.6	153.5	153.3	153.2	153.0
50°	154.6	154.5	154.3	154.2	154.0	153.8	153.7	153.5	153.4	153.2	153.1
48.75°	154.7	154.5	154.4	154.2	154.1	153.9	153.8	153.6	153.4	153.3	153.1
47.5°	154.8	154.6	154.5	154.3	154.2	154.0	153.8	153.7	153.5	153.3	153.2
46.25°	154.9	154.7	154.6	154.4	154.2	154.1	153.9	153.7	153.6	153.4	153.2
45°	155.0	154.8	154.6	154.5	154.3	154.1	154.0	153.8	153.6	153.5	153.3
43.75°	154.9	154.9	154.7	154.6	154.4	154.2	154.0	153.9	153.7	153.5	153.3
42.5°	154.8	155.0	154.8	154.6	154.5	154.3	154.1	153.9	153.7	153.6	153.4
41.25°	154.8	154.9	154.9	154.7	154.5	154.3	154.2	154.0	153.8	153.6	153.4
40°	154.7	154.9	155.0	154.8	154.6	154.4	154.2	154.0	153.9	153.7	153.5
38.75°	154.6	154.8	155.0	154.8	154.7	154.5	154.3	154.1	153.9	153.7	153.5
37.5°	154.5	154.7	154.9	154.9	154.7	154.5	154.3	154.1	154.0	153.8	153.6
36.25°	154.4	154.6	154.8	155.0	154.8	154.6	154.4	154.2	154.0	153.8	153.6
35°	154.4	154.6	154.8	154.9	154.9	154.7	154.5	154.3	154.1	153.9	153.7

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	154.3	154.5	154.7	154.9	154.9	154.7	154.5	154.3	154.1	153.9	153.7
32.5°	154.2	154.4	154.6	154.8	155.0	154.8	154.6	154.4	154.1	153.9	153.7
31.25°	154.1	154.3	154.6	154.8	155.0	154.8	154.6	154.4	154.2	154.0	153.8
30°	154.1	154.3	154.5	154.7	154.9	154.9	154.7	154.4	154.2	154.0	153.8
28.75°	154.0	154.2	154.4	154.7	154.9	154.9	154.7	154.5	154.3	154.1	153.8
27.5°	154.2	154.2	154.4	154.6	154.8	155.0	154.8	154.5	154.3	154.1	153.9
26.25°	154.3	154.1	154.3	154.5	154.8	155.0	154.8	154.6	154.4	154.1	153.9
25°	154.5	154.1	154.3	154.5	154.7	154.9	154.8	154.6	154.4	154.2	153.9
23.75°	154.7	154.0	154.2	154.4	154.7	154.9	154.9	154.6	154.4	154.2	154.0
22.5°	154.8	154.2	154.2	154.4	154.6	154.9	154.9	154.7	154.5	154.2	154.0
21.25°	155.0	154.3	154.1	154.4	154.6	154.8	154.9	154.7	154.5	154.3	154.0
20°	155.1	154.4	154.1	154.3	154.6	154.8	155.0	154.7	154.5	154.3	154.0
18.75°	155.3	154.6	154.0	154.3	154.5	154.8	155.0	154.8	154.5	154.3	154.1
17.5°	155.4	154.7	154.0	154.2	154.5	154.7	155.0	154.8	154.6	154.3	154.1
16.25°	155.5	154.8	154.1	154.2	154.5	154.7	154.9	154.8	154.6	154.4	154.1
15°	155.6	154.9	154.2	154.2	154.4	154.7	154.9	154.9	154.6	154.4	154.1
13.75°	155.7	155.0	154.3	154.2	154.4	154.6	154.9	154.9	154.6	154.4	154.2
12.5°	155.8	155.1	154.3	154.1	154.4	154.6	154.9	154.9	154.7	154.4	154.2
11.25°	155.9	155.2	154.4	154.1	154.3	154.6	154.8	154.9	154.7	154.4	154.2
10°	156.0	155.2	154.5	154.1	154.3	154.6	154.8	154.9	154.7	154.4	154.2
8.75°	156.0	155.3	154.6	154.1	154.3	154.6	154.8	155.0	154.7	154.5	154.2
7.5°	156.1	155.3	154.6	154.0	154.3	154.5	154.8	155.0	154.7	154.5	154.2
6.25°	156.1	155.4	154.6	154.0	154.3	154.5	154.8	155.0	154.7	154.5	154.2
5°	156.2	155.4	154.7	154.0	154.3	154.5	154.8	155.0	154.7	154.5	154.2
3.75°	156.2	155.5	154.7	154.0	154.3	154.5	154.8	155.0	154.7	154.5	154.2
2.5°	156.2	155.5	154.7	154.0	154.3	154.5	154.8	155.0	154.7	154.5	154.2
1.25°	156.2	155.5	154.7	154.0	154.3	154.5	154.8	155.0	154.7	154.5	154.2
0°	156.3	155.5	154.8	154.0	154.3	154.5	154.8	155.0	154.8	154.5	154.3
-1.25°	156.2	155.5	154.7	154.0	154.3	154.5	154.8	155.0	154.7	154.5	154.2
-2.5°	156.2	155.5	154.7	154.0	154.3	154.5	154.8	155.0	154.7	154.5	154.2
-3.75°	156.2	155.5	154.7	154.0	154.3	154.5	154.8	155.0	154.7	154.5	154.2
-5°	156.2	155.4	154.7	154.0	154.3	154.5	154.8	155.0	154.7	154.5	154.2
-6.25°	156.1	155.4	154.6	154.0	154.3	154.5	154.8	155.0	154.7	154.5	154.2
-7.5°	156.1	155.3	154.6	154.0	154.3	154.5	154.8	155.0	154.7	154.5	154.2
-8.75°	156.0	155.3	154.6	154.1	154.3	154.6	154.8	155.0	154.7	154.5	154.2
-10°	156.0	155.2	154.5	154.1	154.3	154.6	154.8	154.9	154.7	154.4	154.2
-11.25°	155.9	155.2	154.4	154.1	154.3	154.6	154.8	154.9	154.7	154.4	154.2
-12.5°	155.8	155.1	154.3	154.1	154.4	154.6	154.9	154.9	154.7	154.4	154.2
-13.75°	155.7	155.0	154.3	154.2	154.4	154.6	154.9	154.9	154.6	154.4	154.2
-15°	155.6	154.9	154.2	154.2	154.4	154.7	154.9	154.9	154.6	154.4	154.1
-16.25°	155.5	154.8	154.1	154.2	154.5	154.7	154.9	154.8	154.6	154.4	154.1
-17.5°	155.4	154.7	154.0	154.2	154.5	154.7	155.0	154.8	154.6	154.3	154.1
-18.75°	155.3	154.6	154.0	154.3	154.5	154.8	155.0	154.8	154.5	154.3	154.1
-20°	155.1	154.4	154.1	154.3	154.6	154.8	155.0	154.7	154.5	154.3	154.0
-21.25°	155.0	154.3	154.1	154.4	154.6	154.8	154.9	154.7	154.5	154.3	154.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	154.8	154.2	154.2	154.4	154.6	154.9	154.9	154.7	154.5	154.2	154.0
-23.75°	154.7	154.0	154.2	154.4	154.7	154.9	154.9	154.6	154.4	154.2	154.0
-25°	154.5	154.1	154.3	154.5	154.7	154.9	154.8	154.6	154.4	154.2	153.9
-26.25°	154.3	154.1	154.3	154.5	154.8	155.0	154.8	154.6	154.4	154.1	153.9
-27.5°	154.2	154.2	154.4	154.6	154.8	155.0	154.8	154.5	154.3	154.1	153.9
-28.75°	154.0	154.2	154.4	154.7	154.9	154.9	154.7	154.5	154.3	154.1	153.8
-30°	154.1	154.3	154.5	154.7	154.9	154.9	154.7	154.4	154.2	154.0	153.8
-31.25°	154.1	154.3	154.6	154.8	155.0	154.8	154.6	154.4	154.2	154.0	153.8
-32.5°	154.2	154.4	154.6	154.8	155.0	154.8	154.6	154.4	154.1	153.9	153.7
-33.75°	154.3	154.5	154.7	154.9	154.9	154.7	154.5	154.3	154.1	153.9	153.7
-35°	154.4	154.6	154.8	154.9	154.9	154.7	154.5	154.3	154.1	153.9	153.7
-36.25°	154.4	154.6	154.8	155.0	154.8	154.6	154.4	154.2	154.0	153.8	153.6
-37.5°	154.5	154.7	154.9	154.9	154.7	154.5	154.3	154.1	154.0	153.8	153.6
-38.75°	154.6	154.8	155.0	154.8	154.7	154.5	154.3	154.1	153.9	153.7	153.5
-40°	154.7	154.9	155.0	154.8	154.6	154.4	154.2	154.0	153.9	153.7	153.5
-41.25°	154.8	154.9	154.9	154.7	154.5	154.3	154.2	154.0	153.8	153.6	153.4
-42.5°	154.8	155.0	154.8	154.6	154.5	154.3	154.1	153.9	153.7	153.6	153.4
-43.75°	154.9	154.9	154.7	154.6	154.4	154.2	154.0	153.9	153.7	153.5	153.3
-45°	155.0	154.8	154.6	154.5	154.3	154.1	154.0	153.8	153.6	153.5	153.3
-46.25°	154.9	154.7	154.6	154.4	154.2	154.1	153.9	153.7	153.6	153.4	153.2
-47.5°	154.8	154.6	154.5	154.3	154.2	154.0	153.8	153.7	153.5	153.3	153.2
-48.75°	154.7	154.5	154.4	154.2	154.1	153.9	153.8	153.6	153.4	153.3	153.1
-50°	154.6	154.5	154.3	154.2	154.0	153.8	153.7	153.5	153.4	153.2	153.1
-51.25°	154.5	154.4	154.2	154.1	153.9	153.8	153.6	153.5	153.3	153.2	153.0
-52.5°	154.4	154.3	154.1	154.0	153.8	153.7	153.5	153.4	153.3	153.1	153.0
-53.75°	154.3	154.2	154.0	153.9	153.8	153.6	153.5	153.3	153.2	153.0	153.0
-55°	154.2	154.1	153.9	153.8	153.7	153.5	153.4	153.3	153.1	153.0	153.0
-56.25°	154.1	154.0	153.8	153.7	153.6	153.5	153.3	153.2	153.1	153.0	153.0
-57.5°	154.0	153.9	153.7	153.6	153.5	153.4	153.2	153.1	153.0	153.0	153.0
-58.75°	153.9	153.8	153.7	153.5	153.4	153.3	153.2	153.0	153.0	153.0	153.0
-60°	153.8	153.7	153.6	153.4	153.3	153.2	153.1	153.0	153.0	153.0	153.0
-61.25°	153.7	153.6	153.5	153.3	153.2	153.1	153.0	153.0	153.0	153.0	153.0
-62.5°	153.6	153.5	153.4	153.3	153.1	153.0	153.0	153.0	153.0	153.0	153.0
-63.75°	153.5	153.4	153.3	153.2	153.1	153.0	153.0	153.0	153.0	153.0	153.0
-65°	153.3	153.3	153.2	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-66.25°	153.2	153.1	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-67.5°	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-68.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-70°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-71.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0
-72.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1
-73.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.4
-75°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.2	153.4	153.7
-76.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.3	153.5	153.7	153.9
-77.5°	153.0	153.0	153.0	153.0	153.0	153.2	153.4	153.6	153.8	154.0	154.2

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	153.0	153.0	153.0	153.2	153.4	153.6	153.8	153.9	154.1	154.3	154.5
-80°	153.2	153.3	153.5	153.6	153.8	154.0	154.1	154.3	154.4	154.6	154.8
-81.25°	153.6	153.8	153.9	154.1	154.2	154.3	154.5	154.6	154.8	154.9	155.0
-82.5°	154.1	154.2	154.4	154.5	154.6	154.7	154.8	155.0	155.1	155.2	155.3
-83.75°	154.6	154.7	154.8	154.9	155.0	155.1	155.2	155.3	155.4	155.5	155.6
-85°	155.1	155.2	155.2	155.3	155.4	155.5	155.6	155.6	155.7	155.8	155.9
-86.25°	155.6	155.6	155.7	155.7	155.8	155.9	155.9	156.0	156.0	156.1	156.2
-87.5°	156.0	156.1	156.1	156.2	156.2	156.2	156.3	156.3	156.4	156.4	156.4
-88.75°	156.5	156.5	156.6	156.6	156.6	156.6	156.6	156.7	156.7	156.7	156.7
-90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0
88.75°	156.7	156.8	156.8	156.8	156.8	156.8	156.9	156.9	156.9	156.9	157.0
87.5°	156.5	156.5	156.6	156.6	156.7	156.7	156.7	156.8	156.8	156.9	156.9
86.25°	156.2	156.3	156.4	156.4	156.5	156.5	156.6	156.7	156.7	156.8	156.9
85°	156.0	156.1	156.1	156.2	156.3	156.4	156.5	156.6	156.7	156.7	156.8
83.75°	155.7	155.8	155.9	156.0	156.1	156.2	156.3	156.5	156.6	156.7	156.8
82.5°	155.5	155.6	155.7	155.8	156.0	156.1	156.2	156.3	156.5	156.6	156.7
81.25°	155.2	155.3	155.5	155.6	155.8	155.9	156.1	156.2	156.4	156.5	156.7
80°	154.9	155.1	155.3	155.4	155.6	155.8	156.0	156.1	156.3	156.5	156.7
78.75°	154.7	154.9	155.1	155.3	155.4	155.6	155.8	156.0	156.2	156.4	156.6
77.5°	154.4	154.6	154.9	155.1	155.3	155.5	155.7	155.9	156.1	156.4	156.6
76.25°	154.2	154.4	154.6	154.9	155.1	155.3	155.6	155.8	156.1	156.3	156.5
75°	153.9	154.2	154.4	154.7	154.9	155.2	155.5	155.7	156.0	156.2	156.5
73.75°	153.7	153.9	154.2	154.5	154.8	155.0	155.3	155.6	155.9	156.2	156.4
72.5°	153.4	153.7	154.0	154.3	154.6	154.9	155.2	155.5	155.8	156.1	156.4
71.25°	153.2	153.5	153.8	154.1	154.4	154.8	155.1	155.4	155.7	156.0	156.4
70°	153.0	153.3	153.6	153.9	154.3	154.6	155.0	155.3	155.6	156.0	156.3
68.75°	153.0	153.0	153.4	153.8	154.1	154.5	154.8	155.2	155.6	155.9	156.3
67.5°	153.0	153.0	153.2	153.6	154.0	154.3	154.7	155.1	155.5	155.9	156.2
66.25°	153.0	153.0	153.0	153.4	153.8	154.2	154.6	155.0	155.4	155.8	156.2
65°	153.0	153.0	153.0	153.2	153.6	154.1	154.5	154.9	155.3	155.7	156.2
63.75°	153.0	153.0	153.0	153.0	153.5	153.9	154.4	154.8	155.2	155.7	156.1
62.5°	153.0	153.0	153.0	153.0	153.3	153.8	154.2	154.7	155.2	155.6	156.1
61.25°	153.0	153.0	153.0	153.0	153.2	153.6	154.1	154.6	155.1	155.6	156.0
60°	153.0	153.0	153.0	153.0	153.0	153.5	154.0	154.5	155.0	155.5	156.0
58.75°	153.0	153.0	153.0	153.0	153.0	153.4	153.9	154.4	154.9	155.4	156.0
57.5°	153.0	153.0	153.0	153.0	153.0	153.2	153.8	154.3	154.9	155.4	155.9
56.25°	153.0	153.0	153.0	153.0	153.0	153.1	153.7	154.2	154.8	155.3	155.9
55°	153.0	153.0	153.0	153.0	153.0	153.0	153.6	154.1	154.7	155.3	155.9
53.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.5	154.0	154.6	155.2	155.8
52.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.4	154.0	154.6	155.2	155.8
51.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.3	153.9	154.5	155.1	155.7
50°	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.8	154.4	155.1	155.7
48.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.7	154.4	155.0	155.7
47.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.6	154.3	155.0	155.6
46.25°	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.5	154.2	154.9	155.6
45°	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.5	154.2	154.9	155.6
43.75°	153.2	153.0	153.0	153.0	153.0	153.0	153.0	153.4	154.1	154.8	155.6
42.5°	153.2	153.0	153.0	153.0	153.0	153.0	153.0	153.3	154.1	154.8	155.5
41.25°	153.2	153.1	153.0	153.0	153.0	153.0	153.0	153.2	154.0	154.7	155.5
40°	153.3	153.1	153.0	153.0	153.0	153.0	153.0	153.2	153.9	154.7	155.5
38.75°	153.3	153.1	153.0	153.0	153.0	153.0	153.0	153.1	153.9	154.7	155.4
37.5°	153.4	153.2	153.0	153.0	153.0	153.0	153.0	153.0	153.8	154.6	155.4
36.25°	153.4	153.2	153.0	153.0	153.0	153.0	153.0	153.0	153.8	154.6	155.4
35°	153.4	153.2	153.0	153.0	153.0	153.0	153.0	153.0	153.7	154.5	155.4

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	153.5	153.3	153.1	153.0	153.0	153.0	153.0	153.0	153.7	154.5	155.3
32.5°	153.5	153.3	153.1	153.0	153.0	153.0	153.0	153.0	153.6	154.5	155.3
31.25°	153.6	153.3	153.1	153.0	153.0	153.0	153.0	153.0	153.6	154.4	155.3
30°	153.6	153.4	153.2	153.0	153.0	153.0	153.0	153.0	153.5	154.4	155.3
28.75°	153.6	153.4	153.2	153.0	153.0	153.0	153.0	153.0	153.5	154.4	155.2
27.5°	153.7	153.4	153.2	153.0	153.0	153.0	153.0	153.0	153.5	154.3	155.2
26.25°	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	153.4	154.3	155.2
25°	153.7	153.5	153.3	153.0	153.0	153.0	153.0	153.0	153.4	154.3	155.2
23.75°	153.7	153.5	153.3	153.1	153.0	153.0	153.0	153.0	153.3	154.3	155.2
22.5°	153.8	153.5	153.3	153.1	153.0	153.0	153.0	153.0	153.3	154.2	155.2
21.25°	153.8	153.6	153.3	153.1	153.0	153.0	153.0	153.0	153.3	154.2	155.1
20°	153.8	153.6	153.3	153.1	153.0	153.0	153.0	153.0	153.2	154.2	155.1
18.75°	153.8	153.6	153.4	153.1	153.0	153.0	153.0	153.0	153.2	154.2	155.1
17.5°	153.9	153.6	153.4	153.1	153.0	153.0	153.0	153.0	153.2	154.1	155.1
16.25°	153.9	153.6	153.4	153.2	153.0	153.0	153.0	153.0	153.2	154.1	155.1
15°	153.9	153.7	153.4	153.2	153.0	153.0	153.0	153.0	153.1	154.1	155.1
13.75°	153.9	153.7	153.4	153.2	153.0	153.0	153.0	153.0	153.1	154.1	155.1
12.5°	153.9	153.7	153.4	153.2	153.0	153.0	153.0	153.0	153.1	154.1	155.0
11.25°	153.9	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.1	154.1	155.0
10°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.1	154.0	155.0
8.75°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	154.0	155.0
7.5°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	154.0	155.0
6.25°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	154.0	155.0
5°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	154.0	155.0
3.75°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	154.0	155.0
2.5°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	154.0	155.0
1.25°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	154.0	155.0
0°	154.0	153.8	153.5	153.3	153.0	153.0	153.0	153.0	153.0	154.0	155.0
-1.25°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	154.0	155.0
-2.5°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	154.0	155.0
-3.75°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	154.0	155.0
-5°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	154.0	155.0
-6.25°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	154.0	155.0
-7.5°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	154.0	155.0
-8.75°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	154.0	155.0
-10°	154.0	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.1	154.0	155.0
-11.25°	153.9	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.1	154.1	155.0
-12.5°	153.9	153.7	153.4	153.2	153.0	153.0	153.0	153.0	153.1	154.1	155.0
-13.75°	153.9	153.7	153.4	153.2	153.0	153.0	153.0	153.0	153.1	154.1	155.1
-15°	153.9	153.7	153.4	153.2	153.0	153.0	153.0	153.0	153.1	154.1	155.1
-16.25°	153.9	153.6	153.4	153.2	153.0	153.0	153.0	153.0	153.2	154.1	155.1
-17.5°	153.9	153.6	153.4	153.1	153.0	153.0	153.0	153.0	153.2	154.1	155.1
-18.75°	153.8	153.6	153.4	153.1	153.0	153.0	153.0	153.0	153.2	154.2	155.1
-20°	153.8	153.6	153.3	153.1	153.0	153.0	153.0	153.0	153.2	154.2	155.1
-21.25°	153.8	153.6	153.3	153.1	153.0	153.0	153.0	153.0	153.3	154.2	155.1

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	153.8	153.5	153.3	153.1	153.0	153.0	153.0	153.0	153.3	154.2	155.2
-23.75°	153.7	153.5	153.3	153.1	153.0	153.0	153.0	153.0	153.3	154.3	155.2
-25°	153.7	153.5	153.3	153.0	153.0	153.0	153.0	153.0	153.4	154.3	155.2
-26.25°	153.7	153.5	153.2	153.0	153.0	153.0	153.0	153.0	153.4	154.3	155.2
-27.5°	153.7	153.4	153.2	153.0	153.0	153.0	153.0	153.0	153.5	154.3	155.2
-28.75°	153.6	153.4	153.2	153.0	153.0	153.0	153.0	153.0	153.5	154.4	155.2
-30°	153.6	153.4	153.2	153.0	153.0	153.0	153.0	153.0	153.5	154.4	155.3
-31.25°	153.6	153.3	153.1	153.0	153.0	153.0	153.0	153.0	153.6	154.4	155.3
-32.5°	153.5	153.3	153.1	153.0	153.0	153.0	153.0	153.0	153.6	154.5	155.3
-33.75°	153.5	153.3	153.1	153.0	153.0	153.0	153.0	153.0	153.7	154.5	155.3
-35°	153.4	153.2	153.0	153.0	153.0	153.0	153.0	153.0	153.7	154.5	155.4
-36.25°	153.4	153.2	153.0	153.0	153.0	153.0	153.0	153.0	153.8	154.6	155.4
-37.5°	153.4	153.2	153.0	153.0	153.0	153.0	153.0	153.0	153.8	154.6	155.4
-38.75°	153.3	153.1	153.0	153.0	153.0	153.0	153.0	153.1	153.9	154.7	155.4
-40°	153.3	153.1	153.0	153.0	153.0	153.0	153.0	153.2	153.9	154.7	155.5
-41.25°	153.2	153.1	153.0	153.0	153.0	153.0	153.0	153.2	154.0	154.7	155.5
-42.5°	153.2	153.0	153.0	153.0	153.0	153.0	153.0	153.3	154.1	154.8	155.5
-43.75°	153.2	153.0	153.0	153.0	153.0	153.0	153.0	153.4	154.1	154.8	155.6
-45°	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.5	154.2	154.9	155.6
-46.25°	153.1	153.0	153.0	153.0	153.0	153.0	153.0	153.5	154.2	154.9	155.6
-47.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.0	153.6	154.3	155.0	155.6
-48.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.7	154.4	155.0	155.7
-50°	153.0	153.0	153.0	153.0	153.0	153.0	153.1	153.8	154.4	155.1	155.7
-51.25°	153.0	153.0	153.0	153.0	153.0	153.0	153.3	153.9	154.5	155.1	155.7
-52.5°	153.0	153.0	153.0	153.0	153.0	153.0	153.4	154.0	154.6	155.2	155.8
-53.75°	153.0	153.0	153.0	153.0	153.0	153.0	153.5	154.0	154.6	155.2	155.8
-55°	153.0	153.0	153.0	153.0	153.0	153.0	153.6	154.1	154.7	155.3	155.9
-56.25°	153.0	153.0	153.0	153.0	153.0	153.1	153.7	154.2	154.8	155.3	155.9
-57.5°	153.0	153.0	153.0	153.0	153.0	153.2	153.8	154.3	154.9	155.4	155.9
-58.75°	153.0	153.0	153.0	153.0	153.0	153.4	153.9	154.4	154.9	155.4	156.0
-60°	153.0	153.0	153.0	153.0	153.0	153.5	154.0	154.5	155.0	155.5	156.0
-61.25°	153.0	153.0	153.0	153.0	153.2	153.6	154.1	154.6	155.1	155.6	156.0
-62.5°	153.0	153.0	153.0	153.0	153.3	153.8	154.2	154.7	155.2	155.6	156.1
-63.75°	153.0	153.0	153.0	153.0	153.5	153.9	154.4	154.8	155.2	155.7	156.1
-65°	153.0	153.0	153.0	153.2	153.6	154.1	154.5	154.9	155.3	155.7	156.2
-66.25°	153.0	153.0	153.0	153.4	153.8	154.2	154.6	155.0	155.4	155.8	156.2
-67.5°	153.0	153.0	153.2	153.6	154.0	154.3	154.7	155.1	155.5	155.9	156.2
-68.75°	153.0	153.0	153.4	153.8	154.1	154.5	154.8	155.2	155.6	155.9	156.3
-70°	153.0	153.3	153.6	153.9	154.3	154.6	155.0	155.3	155.6	156.0	156.3
-71.25°	153.2	153.5	153.8	154.1	154.4	154.8	155.1	155.4	155.7	156.0	156.4
-72.5°	153.4	153.7	154.0	154.3	154.6	154.9	155.2	155.5	155.8	156.1	156.4
-73.75°	153.7	153.9	154.2	154.5	154.8	155.0	155.3	155.6	155.9	156.2	156.4
-75°	153.9	154.2	154.4	154.7	154.9	155.2	155.5	155.7	156.0	156.2	156.5
-76.25°	154.2	154.4	154.6	154.9	155.1	155.3	155.6	155.8	156.1	156.3	156.5
-77.5°	154.4	154.6	154.9	155.1	155.3	155.5	155.7	155.9	156.1	156.4	156.6

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	154.7	154.9	155.1	155.3	155.4	155.6	155.8	156.0	156.2	156.4	156.6
-80°	154.9	155.1	155.3	155.4	155.6	155.8	156.0	156.1	156.3	156.5	156.7
-81.25°	155.2	155.3	155.5	155.6	155.8	155.9	156.1	156.2	156.4	156.5	156.7
-82.5°	155.5	155.6	155.7	155.8	156.0	156.1	156.2	156.3	156.5	156.6	156.7
-83.75°	155.7	155.8	155.9	156.0	156.1	156.2	156.3	156.5	156.6	156.7	156.8
-85°	156.0	156.1	156.1	156.2	156.3	156.4	156.5	156.6	156.7	156.7	156.8
-86.25°	156.2	156.3	156.4	156.4	156.5	156.5	156.6	156.7	156.7	156.8	156.9
-87.5°	156.5	156.5	156.6	156.6	156.7	156.7	156.7	156.8	156.8	156.9	156.9
-88.75°	156.7	156.8	156.8	156.8	156.8	156.8	156.9	156.9	156.9	156.9	157.0
-90°	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	157.0	157.0
88.75°	157.0	157.0
87.5°	157.0	157.0
86.25°	156.9	157.0
85°	156.9	157.0
83.75°	156.9	157.0
82.5°	156.9	157.0
81.25°	156.8	157.0
80°	156.8	157.0
78.75°	156.8	157.0
77.5°	156.8	157.0
76.25°	156.8	157.0
75°	156.7	157.0
73.75°	156.7	157.0
72.5°	156.7	157.0
71.25°	156.7	157.0
70°	156.7	157.0
68.75°	156.6	157.0
67.5°	156.6	157.0
66.25°	156.6	157.0
65°	156.6	157.0
63.75°	156.6	157.0
62.5°	156.5	157.0
61.25°	156.5	157.0
60°	156.5	157.0
58.75°	156.5	157.0
57.5°	156.5	157.0
56.25°	156.4	157.0
55°	156.4	157.0
53.75°	156.4	157.0
52.5°	156.4	157.0
51.25°	156.4	157.0
50°	156.4	157.0
48.75°	156.3	157.0
47.5°	156.3	157.0
46.25°	156.3	157.0
45°	156.3	157.0
43.75°	156.3	157.0
42.5°	156.3	157.0
41.25°	156.2	157.0
40°	156.2	157.0
38.75°	156.2	157.0
37.5°	156.2	157.0
36.25°	156.2	157.0
35°	156.2	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	156.2	157.0
32.5°	156.2	157.0
31.25°	156.1	157.0
30°	156.1	157.0
28.75°	156.1	157.0
27.5°	156.1	157.0
26.25°	156.1	157.0
25°	156.1	157.0
23.75°	156.1	157.0
22.5°	156.1	157.0
21.25°	156.1	157.0
20°	156.1	157.0
18.75°	156.1	157.0
17.5°	156.0	157.0
16.25°	156.0	157.0
15°	156.0	157.0
13.75°	156.0	157.0
12.5°	156.0	157.0
11.25°	156.0	157.0
10°	156.0	157.0
8.75°	156.0	157.0
7.5°	156.0	157.0
6.25°	156.0	157.0
5°	156.0	157.0
3.75°	156.0	157.0
2.5°	156.0	157.0
1.25°	156.0	157.0
0°	156.0	157.0
-1.25°	156.0	157.0
-2.5°	156.0	157.0
-3.75°	156.0	157.0
-5°	156.0	157.0
-6.25°	156.0	157.0
-7.5°	156.0	157.0
-8.75°	156.0	157.0
-10°	156.0	157.0
-11.25°	156.0	157.0
-12.5°	156.0	157.0
-13.75°	156.0	157.0
-15°	156.0	157.0
-16.25°	156.0	157.0
-17.5°	156.0	157.0
-18.75°	156.1	157.0
-20°	156.1	157.0
-21.25°	156.1	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	156.1	157.0
-23.75°	156.1	157.0
-25°	156.1	157.0
-26.25°	156.1	157.0
-27.5°	156.1	157.0
-28.75°	156.1	157.0
-30°	156.1	157.0
-31.25°	156.1	157.0
-32.5°	156.2	157.0
-33.75°	156.2	157.0
-35°	156.2	157.0
-36.25°	156.2	157.0
-37.5°	156.2	157.0
-38.75°	156.2	157.0
-40°	156.2	157.0
-41.25°	156.2	157.0
-42.5°	156.3	157.0
-43.75°	156.3	157.0
-45°	156.3	157.0
-46.25°	156.3	157.0
-47.5°	156.3	157.0
-48.75°	156.3	157.0
-50°	156.4	157.0
-51.25°	156.4	157.0
-52.5°	156.4	157.0
-53.75°	156.4	157.0
-55°	156.4	157.0
-56.25°	156.4	157.0
-57.5°	156.5	157.0
-58.75°	156.5	157.0
-60°	156.5	157.0
-61.25°	156.5	157.0
-62.5°	156.5	157.0
-63.75°	156.6	157.0
-65°	156.6	157.0
-66.25°	156.6	157.0
-67.5°	156.6	157.0
-68.75°	156.6	157.0
-70°	156.7	157.0
-71.25°	156.7	157.0
-72.5°	156.7	157.0
-73.75°	156.7	157.0
-75°	156.7	157.0
-76.25°	156.8	157.0
-77.5°	156.8	157.0

REPORT NUMBER: (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 922-50MR16-12-NSP

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	156.8	157.0
-80°	156.8	157.0
-81.25°	156.8	157.0
-82.5°	156.9	157.0
-83.75°	156.9	157.0
-85°	156.9	157.0
-86.25°	156.9	157.0
-87.5°	157.0	157.0
-88.75°	157.0	157.0
-90°	157.0	157.0

(END OF REPORT)