Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590636

Luminaire Tested: 14CGTX-30-B35-HCD

Issue Date: 9/4/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590636
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2505-442-1)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/4/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	14CGTX-30-B35-HCD
Description:	1X4 3000 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 3500K CCT WITH FROSTED SMOOTH LENS
Light Source:	3500K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	2979.6 lumens
Efficiency:	N/A
Efficacy:	102.4 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 1' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	29.1
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590636
CATALOG NUMBER: 14CGTX-30-B35-HCD

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590636
CATALOG NUMBER: 14CGTX-30-B35-HCD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	87	89	87	85	83
2	98	90	83	77	95	88	81	76	84	79	74	81	76	72	78	74	71	68
3	89	78	70	63	87	77	69	63	74	67	62	71	65	61	68	64	59	57
4	82	69	60	53	79	68	60	53	65	58	52	63	57	52	61	55	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	46	40	67	55	46	40	53	45	39	51	44	39	49	43	39	37
7	64	50	41	35	62	49	41	35	48	40	35	46	40	34	45	39	34	32
8	60	46	37	31	58	45	37	31	44	36	31	43	36	31	41	35	31	29
9	56	42	34	28	54	41	33	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	25	51	38	31	25	37	30	25	36	30	25	35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2683	2683	2683
5°	2690	2682	2677
10°	2674	2682	2688
15°	2687	2677	2684
20°	2670	2675	2677
25°	2659	2654	2664
30°	2667	2653	2650
35°	2641	2648	2628
40°	2629	2614	2624
45°	2615	2603	2603
50°	2591	2579	2565
55°	2552	2544	2539
60°	2521	2506	2500
65°	2464	2450	2440
70°	2392	2375	2375
75°	2325	2292	2292
80°	2221	2179	2196
85°	2062	1995	2044

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2615 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590636
CATALOG NUMBER: 14CGTX-30-B35-HCD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.5	3.2
10°-20°	271.4	9.1
20°-30°	413.5	13.9
30°-40°	502.4	16.9
40°-50°	527.0	17.7
50°-60°	484.3	16.3
60°-70°	380.5	12.8
70°-80°	233.0	7.8
80°-90°	73.1	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	779.4	26.2
0°-40°	1281.8	43.0
0°-60°	2293.0	77.0
0°-90°	2979.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2979.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	997	997	997	997	997	
5°	996	992	993	995	991	94
15°	965	961	961	961	964	271
25°	896	899	894	895	897	414
35°	804	804	806	800	800	504
45°	687	683	684	679	684	530
55°	544	543	542	539	541	488
65°	387	389	385	380	383	383
75°	224	223	220	217	220	236
85°	67	66	65	62	66	75
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590636
CATALOG NUMBER: 14CGTX-30-B35-HCD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*997.1*	*997.1*	*997.1*	*997.1*	*997.1*
2.5°	*996.6*	997.1	996.0	995.5	996.6
5°	*996.0*	992.2	992.8	995.0	991.2
7.5°	*989.0*	987.9	991.2	991.2	987.9
10°	*978.7*	982.5	981.4	978.7	983.6
12.5°	*970.5*	972.2	973.8	973.8	974.9
15°	*964.6*	960.8	960.8	961.3	963.5
17.5°	*947.7*	947.7	947.2	947.7	950.5
20°	*932.5*	934.7	934.2	932.5	934.7
22.5°	*915.2*	917.9	917.9	916.3	913.0
25°	*895.6*	898.9	894.0	895.1	897.3
27.5°	*879.9*	874.5	878.8	873.9	876.6
30°	*858.2*	854.4	853.8	848.4	852.7
32.5°	*831.6*	833.2	828.9	825.1	829.9
35°	*803.9*	803.9	806.1	800.1	800.1
37.5°	*778.9*	778.9	776.2	771.3	772.4
40°	*748.5*	748.5	744.2	741.5	746.9
42.5°	*721.9*	717.6	717.6	710.5	712.7
45°	*687.2*	683.4	683.9	679.0	683.9
47.5°	*653.5*	653.5	650.3	645.4	647.6
50°	*618.8*	617.2	616.1	610.7	612.8
52.5°	*584.6*	580.3	581.3	573.2	577.0
55°	*543.9*	543.3	542.3	539.0	541.2
57.5°	*507.5*	505.9	504.8	500.5	503.7
60°	*468.4*	467.4	465.7	461.9	464.6
62.5°	*428.3*	428.8	426.1	420.7	424.5
65°	*387.0*	389.2	384.8	380.5	383.2
67.5°	*345.2*	345.8	343.6	339.8	343.1
70°	*304.0*	305.1	301.8	298.0	301.8
72.5°	*264.3*	264.3	261.1	257.8	260.5
75°	*223.6*	223.1	220.4	216.6	220.4
77.5°	*183.5*	182.4	179.7	176.4	180.8
80°	*143.3*	142.2	140.6	136.8	141.7
82.5°	*104.8*	103.7	103.1	99.3	103.1
85°	*66.8*	65.7	64.6	62.4	66.2
87.5°	*30.9*	30.9	30.9	30.4	33.7
90°	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590636
CATALOG NUMBER: 14CGTX-30-B35-HCD

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.47	17.13	15.83	17.45	17.76	15.39	17.06	15.76	17.38	17.69
	3H	17.41	18.92	17.79	19.25	19.61	17.33	18.84	17.71	19.17	19.53
	4H	18.19	19.61	18.58	19.96	20.33	18.09	19.52	18.49	19.87	20.24
	6H	18.80	20.13	19.21	20.49	20.88	18.70	20.03	19.11	20.39	20.78
	8H	19.02	20.29	19.44	20.68	21.07	18.92	20.19	19.34	20.57	20.97
	12H	19.18	20.39	19.61	20.78	21.20	19.08	20.29	19.51	20.67	21.10
4H	2H	16.13	17.56	16.53	17.91	18.28	16.08	17.51	16.48	17.85	18.23
	3H	18.31	19.51	18.72	19.91	20.31	18.23	19.44	18.64	19.83	20.23
	4H	19.23	20.32	19.66	20.73	21.16	19.13	20.22	19.56	20.63	21.07
	6H	19.98	20.94	20.44	21.38	21.83	19.87	20.83	20.33	21.27	21.72
	8H	20.26	21.16	20.72	21.60	22.06	20.14	21.04	20.60	21.48	21.95
	12H	20.47	21.28	20.95	21.76	22.22	20.36	21.16	20.84	21.64	22.11
8H	4H	19.58	20.48	20.04	20.92	21.38	19.50	20.39	19.96	20.83	21.30
	6H	20.48	21.23	20.97	21.71	22.19	20.38	21.12	20.87	21.61	22.08
	8H	20.85	21.52	21.35	22.02	22.51	20.73	21.40	21.24	21.91	22.39
	12H	21.15	21.75	21.66	22.23	22.79	21.03	21.62	21.53	22.11	22.67
12H	4H	19.63	20.44	20.11	20.91	21.38	19.55	20.36	20.03	20.83	21.30
	6H	20.56	21.23	21.06	21.73	22.22	20.46	21.13	20.97	21.64	22.12
	8H	20.99	21.58	21.49	22.07	22.63	20.88	21.47	21.38	21.96	22.52

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2507-484-6-R2

Test Date: 08/13/2025

Luminaire Tested: 24CGTX-55HE-B35-HCD

Data in this report applies to families of products including 24CGTX-55HE-B35-HCD

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2507-484-6-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	09/08/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-55HE-B35-HCD**
Description:	*THIS IS A REVISION OF REPORT SP1-2504-484-6 TO UPDATE THE CATALOG INFORMATION* 2X4 5500 Lumen CGTX with MDER board at 3500K

Spectral Parameters

CCT (K):	3471
CIE u':	0.2417
CIE v':	0.4970
Duv:	-0.0112
CIE x:	0.3956
CIE y:	0.3615
CIE z:	0.2429
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	587
Purity:	27.18426
Rf:	90.9
Rg:	99.4

CRI (Ra):	90.5
R1:	93.4
R2:	90.2
R3:	90.1
R4:	96.6
R5:	92.2
R6:	83.3
R7:	88.1
R8:	90.3
R9:	87.9
R10:	81.6
R11:	95.9
R12:	74.5
R13:	91.7
R14:	96.1
R15:	94.9



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP1-2507-484-6-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2507-484-6-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3471K
CIE x = 0.3956
CIE y = 0.3615
Duv = -0.0112

Point lies outside the range

REPORT NUMBER: SP1-2507-484-6-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	169	NR	620	287	NR	750	6	NR	880	0	NR
365	0	NR	495	163	NR	625	292	NR	755	5	NR	885	0	NR
370	0	NR	500	164	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	168	NR	635	615	NR	765	4	NR	895	0	NR
380	0	NR	510	173	NR	640	186	NR	770	3	NR	900	0	NR
385	0	NR	515	178	NR	645	183	NR	775	3	NR	905	0	NR
390	0	NR	520	181	NR	650	156	NR	780	2	NR	910	0	NR
395	2	NR	525	184	NR	655	131	NR	785	2	NR	915	0	NR
400	2	NR	530	187	NR	660	111	NR	790	2	NR	920	0	NR
405	3	NR	535	193	NR	665	93	NR	795	2	NR	925	0	NR
410	5	NR	540	198	NR	670	86	NR	800	1	NR	930	0	NR
415	7	NR	545	203	NR	675	70	NR	805	1	NR	935	0	NR
420	14	NR	550	211	NR	680	60	NR	810	1	NR	940	0	NR
425	25	NR	555	220	NR	685	51	NR	815	1	NR	945	0	NR
430	43	NR	560	229	NR	690	44	NR	820	1	NR	950	0	NR
435	72	NR	565	237	NR	695	37	NR	825	1	NR	955	0	NR
440	121	NR	570	246	NR	700	32	NR	830	1	NR	960	0	NR
445	209	NR	575	255	NR	705	27	NR	835	1	NR	965	0	NR
450	275	NR	580	263	NR	710	23	NR	840	0	NR	970	0	NR
455	209	NR	585	270	NR	715	20	NR	845	0	NR	975	0	NR
460	166	NR	590	275	NR	720	17	NR	850	0	NR	980	0	NR
465	195	NR	595	277	NR	725	14	NR	855	0	NR	985	0	NR
470	239	NR	600	279	NR	730	12	NR	860	0	NR	990	0	NR
475	251	NR	605	281	NR	735	10	NR	865	0	NR	995	0	NR
480	217	NR	610	308	NR	740	9	NR	870	0	NR	1000	0	NR
485	182	NR	615	325	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2507-484-6-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	169	NR	620	287	NR	750	6	NR	880	0	NR
365	0	NR	495	163	NR	625	292	NR	755	5	NR	885	0	NR
370	0	NR	500	164	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	168	NR	635	615	NR	765	4	NR	895	0	NR
380	0	NR	510	173	NR	640	186	NR	770	3	NR	900	0	NR
385	0	NR	515	178	NR	645	183	NR	775	3	NR	905	0	NR
390	0	NR	520	181	NR	650	156	NR	780	2	NR	910	0	NR
395	2	NR	525	184	NR	655	131	NR	785	2	NR	915	0	NR
400	2	NR	530	187	NR	660	111	NR	790	2	NR	920	0	NR
405	3	NR	535	193	NR	665	93	NR	795	2	NR	925	0	NR
410	5	NR	540	198	NR	670	86	NR	800	1	NR	930	0	NR
415	7	NR	545	203	NR	675	70	NR	805	1	NR	935	0	NR
420	14	NR	550	211	NR	680	60	NR	810	1	NR	940	0	NR
425	25	NR	555	220	NR	685	51	NR	815	1	NR	945	0	NR
430	43	NR	560	229	NR	690	44	NR	820	1	NR	950	0	NR
435	72	NR	565	237	NR	695	37	NR	825	1	NR	955	0	NR
440	121	NR	570	246	NR	700	32	NR	830	1	NR	960	0	NR
445	209	NR	575	255	NR	705	27	NR	835	1	NR	965	0	NR
450	275	NR	580	263	NR	710	23	NR	840	0	NR	970	0	NR
455	209	NR	585	270	NR	715	20	NR	845	0	NR	975	0	NR
460	166	NR	590	275	NR	720	17	NR	850	0	NR	980	0	NR
465	195	NR	595	277	NR	725	14	NR	855	0	NR	985	0	NR
470	239	NR	600	279	NR	730	12	NR	860	0	NR	990	0	NR
475	251	NR	605	281	NR	735	10	NR	865	0	NR	995	0	NR
480	217	NR	610	308	NR	740	9	NR	870	0	NR	1000	0	NR
485	182	NR	615	325	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2507-484-6-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.93**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	169	NR	620	287	NR	750	6	NR	880	0	NR
365	0	NR	495	163	NR	625	292	NR	755	5	NR	885	0	NR
370	0	NR	500	164	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	168	NR	635	615	NR	765	4	NR	895	0	NR
380	0	NR	510	173	NR	640	186	NR	770	3	NR	900	0	NR
385	0	NR	515	178	NR	645	183	NR	775	3	NR	905	0	NR
390	0	NR	520	181	NR	650	156	NR	780	2	NR	910	0	NR
395	2	NR	525	184	NR	655	131	NR	785	2	NR	915	0	NR
400	2	NR	530	187	NR	660	111	NR	790	2	NR	920	0	NR
405	3	NR	535	193	NR	665	93	NR	795	2	NR	925	0	NR
410	5	NR	540	198	NR	670	86	NR	800	1	NR	930	0	NR
415	7	NR	545	203	NR	675	70	NR	805	1	NR	935	0	NR
420	14	NR	550	211	NR	680	60	NR	810	1	NR	940	0	NR
425	25	NR	555	220	NR	685	51	NR	815	1	NR	945	0	NR
430	43	NR	560	229	NR	690	44	NR	820	1	NR	950	0	NR
435	72	NR	565	237	NR	695	37	NR	825	1	NR	955	0	NR
440	121	NR	570	246	NR	700	32	NR	830	1	NR	960	0	NR
445	209	NR	575	255	NR	705	27	NR	835	1	NR	965	0	NR
450	275	NR	580	263	NR	710	23	NR	840	0	NR	970	0	NR
455	209	NR	585	270	NR	715	20	NR	845	0	NR	975	0	NR
460	166	NR	590	275	NR	720	17	NR	850	0	NR	980	0	NR
465	195	NR	595	277	NR	725	14	NR	855	0	NR	985	0	NR
470	239	NR	600	279	NR	730	12	NR	860	0	NR	990	0	NR
475	251	NR	605	281	NR	735	10	NR	865	0	NR	995	0	NR
480	217	NR	610	308	NR	740	9	NR	870	0	NR	1000	0	NR
485	182	NR	615	325	NR	745	7	NR	875	0	NR			


REPORT NUMBER: SP1-2507-484-6-R2

TM-30-18


Summary


R_f = 90.9
R_g = 99.4
CIE R_a = 90.5
R_9 = 87.9


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2507-484-6-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 96	CES51 = 93	CES76 = 91
CES02 = 63	CES27 = 88	CES52 = 96	CES77 = 80
CES03 = 32	CES28 = 96	CES53 = 92	CES78 = 90
CES04 = 70	CES29 = 92	CES54 = 88	CES79 = 83
CES05 = 50	CES30 = 86	CES55 = 87	CES80 = 85
CES06 = 51	CES31 = 92	CES56 = 89	CES81 = 66
CES07 = 43	CES32 = 97	CES57 = 88	CES82 = 94
CES08 = 42	CES33 = 92	CES58 = 88	CES83 = 90
CES09 = 29	CES34 = 95	CES59 = 95	CES84 = 97
CES10 = 76	CES35 = 97	CES60 = 91	CES85 = 78
CES11 = 58	CES36 = 81	CES61 = 92	CES86 = 78
CES12 = 65	CES37 = 97	CES62 = 83	CES87 = 93
CES13 = 44	CES38 = 82	CES63 = 95	CES88 = 93
CES14 = 74	CES39 = 97	CES64 = 90	CES89 = 86
CES15 = 72	CES40 = 96	CES65 = 93	CES90 = 91
CES16 = 48	CES41 = 93	CES66 = 91	CES91 = 76
CES17 = 49	CES42 = 95	CES67 = 91	CES92 = 80
CES18 = 57	CES43 = 93	CES68 = 92	CES93 = 88
CES19 = 71	CES44 = 99	CES69 = 92	CES94 = 79
CES20 = 67	CES45 = 96	CES70 = 92	CES95 = 88
CES21 = 86	CES46 = 96	CES71 = 88	CES96 = 96
CES22 = 78	CES47 = 86	CES72 = 95	CES97 = 94
CES23 = 91	CES48 = 86	CES73 = 89	CES98 = 92
CES24 = 90	CES49 = 97	CES74 = 87	CES99 = 91
CES25 = 71	CES50 = 94	CES75 = 89	





REPORT NUMBER: SP1-2507-484-6-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2507-484-6-R2

TM-30-18

Measure Comparisons





(END OF REPORT)