Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590638

Luminaire Tested: 14CGTX-30-B45-HCD

Issue Date: 9/4/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590638
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2510-581-28)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/4/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	14CGTX-30-B45-HCD
Description:	1X4 3000 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 4500K CCT WITH FROSTED SMOOTH LENS
Light Source:	4500K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	2964.9 lumens
Efficiency:	N/A
Efficacy:	101.9 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 1' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	29.1
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590638
CATALOG NUMBER: 14CGTX-30-B45-HCD

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590638
CATALOG NUMBER: 14CGTX-30-B45-HCD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	68
3	89	79	70	63	87	77	69	63	74	67	62	71	65	61	69	64	60	57
4	82	69	60	54	79	68	60	53	66	58	52	63	57	52	61	55	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	39	51	44	39	50	43	39	37
7	64	50	41	35	62	50	41	35	48	40	35	47	40	35	45	39	34	32
8	60	46	37	31	58	45	37	31	44	36	31	43	36	31	41	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	25	37	30	25	36	30	25	35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2683	2683	2683
5°	2692	2682	2669
10°	2692	2683	2683
15°	2693	2684	2684
20°	2668	2677	2672
25°	2690	2653	2666
30°	2656	2643	2650
35°	2628	2625	2632
40°	2629	2609	2612
45°	2609	2586	2590
50°	2584	2575	2550
55°	2552	2529	2516
60°	2518	2486	2469
65°	2447	2430	2399
70°	2396	2357	2327
75°	2297	2257	2206
80°	2179	2137	2095
85°	1995	1961	1877

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2609 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590638
CATALOG NUMBER: 14CGTX-30-B45-HCD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.4	3.2
10°-20°	271.4	9.2
20°-30°	413.0	13.9
30°-40°	501.5	16.9
40°-50°	525.5	17.7
50°-60°	481.8	16.2
60°-70°	376.8	12.7
70°-80°	229.3	7.7
80°-90°	71.2	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	778.8	26.3
0°-40°	1280.3	43.2
0°-60°	2287.6	77.2
0°-90°	2964.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2964.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	997	997	997	997	997	
5°	997	995	993	993	988	95
15°	967	959	964	961	964	272
25°	906	895	894	894	898	415
35°	800	804	799	801	801	502
45°	686	681	680	680	681	528
55°	544	538	539	535	536	485
65°	384	384	382	378	377	380
75°	221	219	217	215	212	233
85°	65	65	64	61	61	72
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590638
CATALOG NUMBER: 14CGTX-30-B45-HCD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*997.1*	997.1	997.1	997.1	997.1
2.5°	*998.2*	*995.5*	*995.0*	*991.2*	*997.7*
5°	*996.6*	995.0	992.8	992.8	987.9
7.5°	*994.4*	990.1	986.3	987.4	990.1
10°	*985.2*	981.4	981.9	976.5	981.9
12.5°	*976.0*	973.3	970.0	972.7	974.3
15°	*966.7*	959.1	963.5	960.8	963.5
17.5°	*947.2*	948.8	948.3	945.0	948.3
20°	*931.5*	935.8	934.7	931.5	933.1
22.5°	*920.6*	914.6	914.1	914.6	916.3
25°	*906.0*	894.6	893.5	894.0	897.8
27.5°	*878.3*	875.0	873.4	872.8	876.6
30°	*854.9*	850.6	850.6	850.0	852.8
32.5°	*830.5*	828.3	827.8	828.3	828.3
35°	*800.1*	804.4	799.0	800.6	801.2
37.5°	*775.1*	776.8	774.0	771.9	773.0
40°	*748.5*	744.7	742.6	742.6	743.7
42.5°	*714.3*	717.6	712.2	715.4	712.2
45°	*685.6*	680.7	679.6	680.1	680.7
47.5°	*650.3*	647.6	645.9	649.7	641.1
50°	*617.2*	614.5	615.0	612.8	609.0
52.5°	*578.1*	576.5	579.7	575.9	573.8
55°	*543.9*	538.5	539.0	535.2	536.3
57.5°	*504.8*	503.2	499.4	499.4	498.3
60°	*467.9*	461.9	461.9	459.8	458.7
62.5°	*422.9*	422.3	425.0	420.7	416.9
65°	*384.3*	383.8	381.6	378.3	376.7
67.5°	*343.6*	340.9	339.8	336.0	338.2
70°	*304.5*	300.7	299.6	295.3	295.8
72.5°	*262.7*	259.5	258.4	253.5	253.0
75°	*220.9*	219.3	217.1	215.0	212.2
77.5°	*179.1*	178.6	179.1	173.2	173.7
80°	*140.6*	140.0	137.9	134.6	135.2
82.5°	*101.0*	101.0	99.9	98.2	96.6
85°	*64.6*	64.6	63.5	60.8	60.8
87.5°	*29.3*	29.9	30.9	30.9	30.4
90°	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590638
CATALOG NUMBER: 14CGTX-30-B45-HCD

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.45	17.11	15.81	17.43	17.74	15.39	17.05	15.75	17.37	17.68
	3H	17.38	18.89	17.76	19.22	19.58	17.29	18.80	17.67	19.13	19.49
	4H	18.15	19.57	18.55	19.92	20.30	18.03	19.46	18.43	19.80	20.18
	6H	18.75	20.07	19.16	20.44	20.83	18.61	19.93	19.02	20.30	20.69
	8H	18.96	20.22	19.38	20.61	21.01	18.81	20.08	19.24	20.46	20.86
	12H	19.11	20.32	19.54	20.70	21.13	18.95	20.16	19.38	20.55	20.97
4H	2H	16.11	17.54	16.51	17.88	18.26	16.07	17.49	16.46	17.84	18.21
	3H	18.27	19.47	18.68	19.87	20.27	18.20	19.39	18.60	19.79	20.19
	4H	19.18	20.27	19.61	20.68	21.11	19.07	20.16	19.50	20.57	21.01
	6H	19.92	20.87	20.37	21.31	21.77	19.79	20.74	20.24	21.18	21.63
	8H	20.19	21.08	20.65	21.52	21.99	20.04	20.94	20.50	21.38	21.84
	12H	20.39	21.20	20.87	21.67	22.14	20.24	21.04	20.72	21.52	21.98
8H	4H	19.53	20.43	19.99	20.87	21.33	19.44	20.33	19.90	20.77	21.24
	6H	20.42	21.16	20.91	21.65	22.12	20.29	21.04	20.78	21.52	22.00
	8H	20.77	21.44	21.28	21.94	22.43	20.63	21.30	21.14	21.81	22.29
	12H	21.07	21.66	21.57	22.15	22.71	20.91	21.50	21.42	21.99	22.55
12H	4H	19.58	20.38	20.06	20.86	21.33	19.49	20.29	19.97	20.77	21.24
	6H	20.49	21.16	21.00	21.67	22.15	20.37	21.04	20.88	21.55	22.03
	8H	20.91	21.50	21.41	21.99	22.55	20.78	21.37	21.28	21.86	22.42

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-581-4-R2

Test Date: 01/21/2026

Luminaire Tested: 24CGTX-55-B45-HCD

Data in this report applies to families of products including 24CGTX-55HE

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-581-4-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-55-B45-HCD**
Description:	*THIS IS A REVISION OF REPORT SP1-2510-581-4-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 CGTX 5500 lumen with BioUp Boards with fixed CCT 4500K - Control Volatge at 3V

Spectral Parameters

CCT (K):	4541
CIE u':	0.2259
CIE v':	0.4759
Duv:	-0.0141
CIE x:	0.3541
CIE y:	0.3316
CIE z:	0.3143
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	622
Purity:	5.72732
Rf:	87.2
Rg:	96.7

CRI (Ra):	86.3
R1:	91.4
R2:	86.5
R3:	84.4
R4:	88.4
R5:	89.6
R6:	80.7
R7:	83.3
R8:	86.2
R9:	86.2
R10:	74.5
R11:	89.9
R12:	69.8
R13:	89.5
R14:	92.9
R15:	92.2



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.1

REPORT NUMBER: SP1-2510-581-4-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2510-581-4-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4541K
CIE x = 0.3541
CIE y = 0.3316
Duv = -0.0141

Point lies outside the range

REPORT NUMBER: SP1-2510-581-4-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	341	NR	620	392	NR	750	9	NR	880	0	NR
365	0	NR	495	298	NR	625	387	NR	755	7	NR	885	0	NR
370	0	NR	500	275	NR	630	1000	NR	760	6	NR	890	0	NR
375	1	NR	505	267	NR	635	584	NR	765	5	NR	895	0	NR
380	2	NR	510	272	NR	640	256	NR	770	5	NR	900	0	NR
385	2	NR	515	276	NR	645	254	NR	775	4	NR	905	0	NR
390	3	NR	520	281	NR	650	210	NR	780	3	NR	910	0	NR
395	5	NR	525	284	NR	655	179	NR	785	3	NR	915	0	NR
400	6	NR	530	289	NR	660	152	NR	790	2	NR	920	0	NR
405	8	NR	535	296	NR	665	130	NR	795	2	NR	925	0	NR
410	10	NR	540	301	NR	670	117	NR	800	2	NR	930	0	NR
415	16	NR	545	312	NR	675	97	NR	805	2	NR	935	0	NR
420	28	NR	550	323	NR	680	83	NR	810	1	NR	940	0	NR
425	51	NR	555	335	NR	685	71	NR	815	1	NR	945	0	NR
430	89	NR	560	352	NR	690	61	NR	820	1	NR	950	0	NR
435	153	NR	565	368	NR	695	52	NR	825	1	NR	955	0	NR
440	254	NR	570	384	NR	700	44	NR	830	1	NR	960	0	NR
445	443	NR	575	398	NR	705	38	NR	835	1	NR	965	0	NR
450	556	NR	580	410	NR	710	32	NR	840	1	NR	970	0	NR
455	426	NR	585	419	NR	715	27	NR	845	1	NR	975	0	NR
460	355	NR	590	424	NR	720	23	NR	850	0	NR	980	0	NR
465	444	NR	595	424	NR	725	19	NR	855	0	NR	985	0	NR
470	579	NR	600	422	NR	730	17	NR	860	0	NR	990	0	NR
475	615	NR	605	418	NR	735	14	NR	865	0	NR	995	0	NR
480	510	NR	610	433	NR	740	12	NR	870	0	NR	1000	0	NR
485	398	NR	615	428	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-4-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 2.17**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	341	NR	620	392	NR	750	9	NR	880	0	NR
365	0	NR	495	298	NR	625	387	NR	755	7	NR	885	0	NR
370	0	NR	500	275	NR	630	1000	NR	760	6	NR	890	0	NR
375	1	NR	505	267	NR	635	584	NR	765	5	NR	895	0	NR
380	2	NR	510	272	NR	640	256	NR	770	5	NR	900	0	NR
385	2	NR	515	276	NR	645	254	NR	775	4	NR	905	0	NR
390	3	NR	520	281	NR	650	210	NR	780	3	NR	910	0	NR
395	5	NR	525	284	NR	655	179	NR	785	3	NR	915	0	NR
400	6	NR	530	289	NR	660	152	NR	790	2	NR	920	0	NR
405	8	NR	535	296	NR	665	130	NR	795	2	NR	925	0	NR
410	10	NR	540	301	NR	670	117	NR	800	2	NR	930	0	NR
415	16	NR	545	312	NR	675	97	NR	805	2	NR	935	0	NR
420	28	NR	550	323	NR	680	83	NR	810	1	NR	940	0	NR
425	51	NR	555	335	NR	685	71	NR	815	1	NR	945	0	NR
430	89	NR	560	352	NR	690	61	NR	820	1	NR	950	0	NR
435	153	NR	565	368	NR	695	52	NR	825	1	NR	955	0	NR
440	254	NR	570	384	NR	700	44	NR	830	1	NR	960	0	NR
445	443	NR	575	398	NR	705	38	NR	835	1	NR	965	0	NR
450	556	NR	580	410	NR	710	32	NR	840	1	NR	970	0	NR
455	426	NR	585	419	NR	715	27	NR	845	1	NR	975	0	NR
460	355	NR	590	424	NR	720	23	NR	850	0	NR	980	0	NR
465	444	NR	595	424	NR	725	19	NR	855	0	NR	985	0	NR
470	579	NR	600	422	NR	730	17	NR	860	0	NR	990	0	NR
475	615	NR	605	418	NR	735	14	NR	865	0	NR	995	0	NR
480	510	NR	610	433	NR	740	12	NR	870	0	NR	1000	0	NR
485	398	NR	615	428	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-4-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 5.01**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	341	NR	620	392	NR	750	9	NR	880	0	NR
365	0	NR	495	298	NR	625	387	NR	755	7	NR	885	0	NR
370	0	NR	500	275	NR	630	1000	NR	760	6	NR	890	0	NR
375	1	NR	505	267	NR	635	584	NR	765	5	NR	895	0	NR
380	2	NR	510	272	NR	640	256	NR	770	5	NR	900	0	NR
385	2	NR	515	276	NR	645	254	NR	775	4	NR	905	0	NR
390	3	NR	520	281	NR	650	210	NR	780	3	NR	910	0	NR
395	5	NR	525	284	NR	655	179	NR	785	3	NR	915	0	NR
400	6	NR	530	289	NR	660	152	NR	790	2	NR	920	0	NR
405	8	NR	535	296	NR	665	130	NR	795	2	NR	925	0	NR
410	10	NR	540	301	NR	670	117	NR	800	2	NR	930	0	NR
415	16	NR	545	312	NR	675	97	NR	805	2	NR	935	0	NR
420	28	NR	550	323	NR	680	83	NR	810	1	NR	940	0	NR
425	51	NR	555	335	NR	685	71	NR	815	1	NR	945	0	NR
430	89	NR	560	352	NR	690	61	NR	820	1	NR	950	0	NR
435	153	NR	565	368	NR	695	52	NR	825	1	NR	955	0	NR
440	254	NR	570	384	NR	700	44	NR	830	1	NR	960	0	NR
445	443	NR	575	398	NR	705	38	NR	835	1	NR	965	0	NR
450	556	NR	580	410	NR	710	32	NR	840	1	NR	970	0	NR
455	426	NR	585	419	NR	715	27	NR	845	1	NR	975	0	NR
460	355	NR	590	424	NR	720	23	NR	850	0	NR	980	0	NR
465	444	NR	595	424	NR	725	19	NR	855	0	NR	985	0	NR
470	579	NR	600	422	NR	730	17	NR	860	0	NR	990	0	NR
475	615	NR	605	418	NR	735	14	NR	865	0	NR	995	0	NR
480	510	NR	610	433	NR	740	12	NR	870	0	NR	1000	0	NR
485	398	NR	615	428	NR	745	10	NR	875	0	NR			


REPORT NUMBER: SP1-2510-581-4-R2

TM-30-18


Summary


R_f = 87.2
R_g = 96.7
CIE R_a = 86.3
R_9 = 86.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-581-4-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 93	CES51 = 87	CES76 = 87
CES02 = 62	CES27 = 85	CES52 = 89	CES77 = 80
CES03 = 31	CES28 = 94	CES53 = 82	CES78 = 87
CES04 = 69	CES29 = 85	CES54 = 85	CES79 = 83
CES05 = 49	CES30 = 80	CES55 = 82	CES80 = 83
CES06 = 50	CES31 = 86	CES56 = 80	CES81 = 66
CES07 = 42	CES32 = 94	CES57 = 78	CES82 = 93
CES08 = 41	CES33 = 86	CES58 = 78	CES83 = 88
CES09 = 29	CES34 = 92	CES59 = 91	CES84 = 96
CES10 = 75	CES35 = 95	CES60 = 88	CES85 = 78
CES11 = 57	CES36 = 77	CES61 = 87	CES86 = 74
CES12 = 63	CES37 = 95	CES62 = 79	CES87 = 90
CES13 = 43	CES38 = 75	CES63 = 92	CES88 = 90
CES14 = 74	CES39 = 93	CES64 = 82	CES89 = 84
CES15 = 71	CES40 = 89	CES65 = 89	CES90 = 87
CES16 = 47	CES41 = 90	CES66 = 84	CES91 = 72
CES17 = 49	CES42 = 88	CES67 = 84	CES92 = 77
CES18 = 56	CES43 = 86	CES68 = 87	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 78
CES20 = 66	CES45 = 89	CES70 = 89	CES95 = 86
CES21 = 85	CES46 = 89	CES71 = 85	CES96 = 94
CES22 = 78	CES47 = 84	CES72 = 94	CES97 = 85
CES23 = 91	CES48 = 79	CES73 = 87	CES98 = 85
CES24 = 90	CES49 = 90	CES74 = 88	CES99 = 87
CES25 = 71	CES50 = 87	CES75 = 86	





REPORT NUMBER: SP1-2510-581-4-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-581-4-R2

TM-30-18

Measure Comparisons





(END OF REPORT)