Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590640

Luminaire Tested: 14CGTX-42-B35-HCD

Issue Date: 9/4/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590640
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2505-442-1)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/4/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	14CGTX-42-B35-HCD
Description:	1X4 4200 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 3500K CCT WITH FROSTED SMOOTH LENS
Light Source:	3500K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3970.4 lumens
Efficiency:	N/A
Efficacy:	96.6 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 1' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	41.1
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590640
CATALOG NUMBER: 14CGTX-42-B35-HCD

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590640
CATALOG NUMBER: 14CGTX-42-B35-HCD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	87	89	87	85	83
2	98	90	83	77	95	88	81	76	84	79	74	81	76	72	78	74	71	68
3	89	78	70	63	87	77	69	63	74	67	62	71	65	61	68	64	59	57
4	82	69	60	53	79	68	60	53	65	58	52	63	57	52	61	55	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	46	40	67	55	46	40	53	45	39	51	44	39	49	43	39	37
7	64	50	41	35	62	49	41	35	48	40	35	46	40	34	45	39	34	32
8	60	46	37	31	58	45	37	31	44	36	31	43	36	31	41	35	31	29
9	56	42	34	28	54	41	33	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	25	51	38	31	25	37	30	25	36	30	25	35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3576	3576	3576
5°	3585	3573	3568
10°	3563	3573	3581
15°	3581	3567	3577
20°	3558	3565	3567
25°	3544	3537	3550
30°	3553	3535	3531
35°	3519	3529	3503
40°	3504	3484	3496
45°	3485	3468	3468
50°	3452	3437	3419
55°	3400	3390	3383
60°	3359	3340	3333
65°	3284	3265	3252
70°	3187	3164	3164
75°	3098	3054	3054
80°	2960	2903	2926
85°	2748	2658	2723

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3485 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590640
CATALOG NUMBER: 14CGTX-42-B35-HCD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.9	3.2
10°-20°	361.7	9.1
20°-30°	550.9	13.9
30°-40°	669.4	16.9
40°-50°	702.2	17.7
50°-60°	645.4	16.3
60°-70°	507.0	12.8
70°-80°	310.5	7.8
80°-90°	97.4	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1038.5	26.2
0°-40°	1708.0	43.0
0°-60°	3055.5	77.0
0°-90°	3970.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3970.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1327	1322	1323	1326	1321	126
15°	1285	1280	1280	1281	1284	362
25°	1194	1198	1191	1193	1196	552
35°	1071	1071	1074	1066	1066	672
45°	916	911	911	905	911	707
55°	725	724	723	718	721	650
65°	516	519	513	507	511	510
75°	298	297	294	289	294	315
85°	89	88	86	83	88	99
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590640
CATALOG NUMBER: 14CGTX-42-B35-HCD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*1328.7*	*1328.7*	*1328.7*	*1328.7*	*1328.7*
2.5°	*1328.0*	1328.7	1327.3	1326.6	1328.0
5°	*1327.3*	1322.2	1322.9	1325.8	1320.8
7.5°	*1317.9*	1316.4	1320.8	1320.8	1316.4
10°	*1304.1*	1309.2	1307.7	1304.1	1310.6
12.5°	*1293.3*	1295.4	1297.6	1297.6	1299.1
15°	*1285.3*	1280.3	1280.3	1281.0	1283.9
17.5°	*1262.9*	1262.9	1262.2	1262.9	1266.5
20°	*1242.6*	1245.5	1244.8	1242.6	1245.5
22.5°	*1219.5*	1223.1	1223.1	1220.9	1216.6
25°	*1193.5*	1197.8	1191.3	1192.7	1195.6
27.5°	*1172.5*	1165.3	1171.0	1164.5	1168.1
30°	*1143.6*	1138.5	1137.8	1130.5	1136.3
32.5°	*1108.1*	1110.3	1104.5	1099.4	1105.9
35°	*1071.2*	1071.2	1074.1	1066.2	1066.2
37.5°	*1037.9*	1037.9	1034.3	1027.8	1029.3
40°	*997.4*	997.4	991.7	988.0	995.3
42.5°	*962.0*	956.2	956.2	946.8	949.7
45°	*915.7*	910.6	911.4	904.9	911.4
47.5°	*870.9*	870.9	866.5	860.0	862.9
50°	*824.6*	822.4	821.0	813.7	816.6
52.5°	*779.0*	773.2	774.7	763.8	768.9
55°	*724.8*	724.0	722.6	718.2	721.1
57.5°	*676.3*	674.1	672.7	666.9	671.2
60°	*624.2*	622.8	620.6	615.5	619.2
62.5°	*570.7*	571.4	567.8	560.6	565.6
65°	*515.7*	518.6	512.8	507.0	510.7
67.5°	*460.0*	460.7	457.9	452.8	457.1
70°	*405.1*	406.5	402.2	397.1	402.2
72.5°	*352.3*	352.3	347.9	343.6	347.2
75°	*298.0*	297.3	293.7	288.6	293.7
77.5°	*244.5*	243.0	239.4	235.1	240.9
80°	*191.0*	189.5	187.3	182.3	188.8
82.5°	*139.6*	138.2	137.4	132.4	137.4
85°	*89.0*	87.5	86.1	83.2	88.2
87.5°	*41.2*	41.2	41.2	40.5	44.8
90°	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590640
CATALOG NUMBER: 14CGTX-42-B35-HCD

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.46	18.13	16.83	18.44	18.76	16.39	18.06	16.76	18.37	18.69
	3H	18.41	19.92	18.78	20.24	20.60	18.33	19.84	18.70	20.16	20.52
	4H	19.18	20.61	19.58	20.96	21.33	19.09	20.52	19.49	20.86	21.24
	6H	19.80	21.12	20.21	21.49	21.88	19.70	21.02	20.11	21.39	21.78
	8H	20.02	21.28	20.44	21.67	22.07	19.92	21.18	20.34	21.57	21.97
	12H	20.18	21.39	20.61	21.77	22.20	20.08	21.29	20.50	21.67	22.10
4H	2H	17.13	18.56	17.53	18.91	19.28	17.08	18.50	17.47	18.85	19.22
	3H	19.31	20.51	19.72	20.90	21.30	19.23	20.43	19.64	20.83	21.23
	4H	20.22	21.31	20.65	21.73	22.16	20.13	21.22	20.56	21.63	22.06
	6H	20.98	21.94	21.43	22.38	22.83	20.87	21.83	21.32	22.27	22.72
	8H	21.26	22.15	21.72	22.59	23.06	21.14	22.04	21.60	22.48	22.94
	12H	21.47	22.28	21.95	22.75	23.22	21.35	22.16	21.83	22.64	23.10
8H	4H	20.58	21.47	21.04	21.92	22.38	20.50	21.39	20.95	21.83	22.30
	6H	21.48	22.23	21.97	22.71	23.19	21.37	22.12	21.87	22.61	23.08
	8H	21.84	22.51	22.35	23.02	23.50	21.73	22.40	22.24	22.90	23.39
	12H	22.15	22.74	22.65	23.23	23.79	22.03	22.62	22.53	23.11	23.67
12H	4H	20.63	21.43	21.10	21.91	22.37	20.55	21.35	21.03	21.83	22.30
	6H	21.55	22.23	22.06	22.73	23.22	21.46	22.13	21.96	22.63	23.12
	8H	21.99	22.58	22.49	23.07	23.63	21.88	22.47	22.38	22.96	23.52

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2507-484-6-R2

Test Date: 08/13/2025

Luminaire Tested: 24CGTX-55HE-B35-HCD

Data in this report applies to families of products including 24CGTX-55HE-B35-HCD

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2507-484-6-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	09/08/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-55HE-B35-HCD**
Description:	*THIS IS A REVISION OF REPORT SP1-2504-484-6 TO UPDATE THE CATALOG INFORMATION* 2X4 5500 Lumen CGTX with MDER board at 3500K

Spectral Parameters

CCT (K):	3471
CIE u':	0.2417
CIE v':	0.4970
Duv:	-0.0112
CIE x:	0.3956
CIE y:	0.3615
CIE z:	0.2429
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	587
Purity:	27.18426
Rf:	90.9
Rg:	99.4

CRI (Ra):	90.5
R1:	93.4
R2:	90.2
R3:	90.1
R4:	96.6
R5:	92.2
R6:	83.3
R7:	88.1
R8:	90.3
R9:	87.9
R10:	81.6
R11:	95.9
R12:	74.5
R13:	91.7
R14:	96.1
R15:	94.9



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP1-2507-484-6-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2507-484-6-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3471K
CIE x = 0.3956
CIE y = 0.3615
Duv = -0.0112

Point lies outside the range

REPORT NUMBER: SP1-2507-484-6-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	169	NR	620	287	NR	750	6	NR	880	0	NR
365	0	NR	495	163	NR	625	292	NR	755	5	NR	885	0	NR
370	0	NR	500	164	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	168	NR	635	615	NR	765	4	NR	895	0	NR
380	0	NR	510	173	NR	640	186	NR	770	3	NR	900	0	NR
385	0	NR	515	178	NR	645	183	NR	775	3	NR	905	0	NR
390	0	NR	520	181	NR	650	156	NR	780	2	NR	910	0	NR
395	2	NR	525	184	NR	655	131	NR	785	2	NR	915	0	NR
400	2	NR	530	187	NR	660	111	NR	790	2	NR	920	0	NR
405	3	NR	535	193	NR	665	93	NR	795	2	NR	925	0	NR
410	5	NR	540	198	NR	670	86	NR	800	1	NR	930	0	NR
415	7	NR	545	203	NR	675	70	NR	805	1	NR	935	0	NR
420	14	NR	550	211	NR	680	60	NR	810	1	NR	940	0	NR
425	25	NR	555	220	NR	685	51	NR	815	1	NR	945	0	NR
430	43	NR	560	229	NR	690	44	NR	820	1	NR	950	0	NR
435	72	NR	565	237	NR	695	37	NR	825	1	NR	955	0	NR
440	121	NR	570	246	NR	700	32	NR	830	1	NR	960	0	NR
445	209	NR	575	255	NR	705	27	NR	835	1	NR	965	0	NR
450	275	NR	580	263	NR	710	23	NR	840	0	NR	970	0	NR
455	209	NR	585	270	NR	715	20	NR	845	0	NR	975	0	NR
460	166	NR	590	275	NR	720	17	NR	850	0	NR	980	0	NR
465	195	NR	595	277	NR	725	14	NR	855	0	NR	985	0	NR
470	239	NR	600	279	NR	730	12	NR	860	0	NR	990	0	NR
475	251	NR	605	281	NR	735	10	NR	865	0	NR	995	0	NR
480	217	NR	610	308	NR	740	9	NR	870	0	NR	1000	0	NR
485	182	NR	615	325	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2507-484-6-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.8**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	169	NR	620	287	NR	750	6	NR	880	0	NR
365	0	NR	495	163	NR	625	292	NR	755	5	NR	885	0	NR
370	0	NR	500	164	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	168	NR	635	615	NR	765	4	NR	895	0	NR
380	0	NR	510	173	NR	640	186	NR	770	3	NR	900	0	NR
385	0	NR	515	178	NR	645	183	NR	775	3	NR	905	0	NR
390	0	NR	520	181	NR	650	156	NR	780	2	NR	910	0	NR
395	2	NR	525	184	NR	655	131	NR	785	2	NR	915	0	NR
400	2	NR	530	187	NR	660	111	NR	790	2	NR	920	0	NR
405	3	NR	535	193	NR	665	93	NR	795	2	NR	925	0	NR
410	5	NR	540	198	NR	670	86	NR	800	1	NR	930	0	NR
415	7	NR	545	203	NR	675	70	NR	805	1	NR	935	0	NR
420	14	NR	550	211	NR	680	60	NR	810	1	NR	940	0	NR
425	25	NR	555	220	NR	685	51	NR	815	1	NR	945	0	NR
430	43	NR	560	229	NR	690	44	NR	820	1	NR	950	0	NR
435	72	NR	565	237	NR	695	37	NR	825	1	NR	955	0	NR
440	121	NR	570	246	NR	700	32	NR	830	1	NR	960	0	NR
445	209	NR	575	255	NR	705	27	NR	835	1	NR	965	0	NR
450	275	NR	580	263	NR	710	23	NR	840	0	NR	970	0	NR
455	209	NR	585	270	NR	715	20	NR	845	0	NR	975	0	NR
460	166	NR	590	275	NR	720	17	NR	850	0	NR	980	0	NR
465	195	NR	595	277	NR	725	14	NR	855	0	NR	985	0	NR
470	239	NR	600	279	NR	730	12	NR	860	0	NR	990	0	NR
475	251	NR	605	281	NR	735	10	NR	865	0	NR	995	0	NR
480	217	NR	610	308	NR	740	9	NR	870	0	NR	1000	0	NR
485	182	NR	615	325	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2507-484-6-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.93**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	169	NR	620	287	NR	750	6	NR	880	0	NR
365	0	NR	495	163	NR	625	292	NR	755	5	NR	885	0	NR
370	0	NR	500	164	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	168	NR	635	615	NR	765	4	NR	895	0	NR
380	0	NR	510	173	NR	640	186	NR	770	3	NR	900	0	NR
385	0	NR	515	178	NR	645	183	NR	775	3	NR	905	0	NR
390	0	NR	520	181	NR	650	156	NR	780	2	NR	910	0	NR
395	2	NR	525	184	NR	655	131	NR	785	2	NR	915	0	NR
400	2	NR	530	187	NR	660	111	NR	790	2	NR	920	0	NR
405	3	NR	535	193	NR	665	93	NR	795	2	NR	925	0	NR
410	5	NR	540	198	NR	670	86	NR	800	1	NR	930	0	NR
415	7	NR	545	203	NR	675	70	NR	805	1	NR	935	0	NR
420	14	NR	550	211	NR	680	60	NR	810	1	NR	940	0	NR
425	25	NR	555	220	NR	685	51	NR	815	1	NR	945	0	NR
430	43	NR	560	229	NR	690	44	NR	820	1	NR	950	0	NR
435	72	NR	565	237	NR	695	37	NR	825	1	NR	955	0	NR
440	121	NR	570	246	NR	700	32	NR	830	1	NR	960	0	NR
445	209	NR	575	255	NR	705	27	NR	835	1	NR	965	0	NR
450	275	NR	580	263	NR	710	23	NR	840	0	NR	970	0	NR
455	209	NR	585	270	NR	715	20	NR	845	0	NR	975	0	NR
460	166	NR	590	275	NR	720	17	NR	850	0	NR	980	0	NR
465	195	NR	595	277	NR	725	14	NR	855	0	NR	985	0	NR
470	239	NR	600	279	NR	730	12	NR	860	0	NR	990	0	NR
475	251	NR	605	281	NR	735	10	NR	865	0	NR	995	0	NR
480	217	NR	610	308	NR	740	9	NR	870	0	NR	1000	0	NR
485	182	NR	615	325	NR	745	7	NR	875	0	NR			


REPORT NUMBER: SP1-2507-484-6-R2

TM-30-18


Summary


R_f = 90.9
R_g = 99.4
CIE R_a = 90.5
R_9 = 87.9


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2507-484-6-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 96	CES51 = 93	CES76 = 91
CES02 = 63	CES27 = 88	CES52 = 96	CES77 = 80
CES03 = 32	CES28 = 96	CES53 = 92	CES78 = 90
CES04 = 70	CES29 = 92	CES54 = 88	CES79 = 83
CES05 = 50	CES30 = 86	CES55 = 87	CES80 = 85
CES06 = 51	CES31 = 92	CES56 = 89	CES81 = 66
CES07 = 43	CES32 = 97	CES57 = 88	CES82 = 94
CES08 = 42	CES33 = 92	CES58 = 88	CES83 = 90
CES09 = 29	CES34 = 95	CES59 = 95	CES84 = 97
CES10 = 76	CES35 = 97	CES60 = 91	CES85 = 78
CES11 = 58	CES36 = 81	CES61 = 92	CES86 = 78
CES12 = 65	CES37 = 97	CES62 = 83	CES87 = 93
CES13 = 44	CES38 = 82	CES63 = 95	CES88 = 93
CES14 = 74	CES39 = 97	CES64 = 90	CES89 = 86
CES15 = 72	CES40 = 96	CES65 = 93	CES90 = 91
CES16 = 48	CES41 = 93	CES66 = 91	CES91 = 76
CES17 = 49	CES42 = 95	CES67 = 91	CES92 = 80
CES18 = 57	CES43 = 93	CES68 = 92	CES93 = 88
CES19 = 71	CES44 = 99	CES69 = 92	CES94 = 79
CES20 = 67	CES45 = 96	CES70 = 92	CES95 = 88
CES21 = 86	CES46 = 96	CES71 = 88	CES96 = 96
CES22 = 78	CES47 = 86	CES72 = 95	CES97 = 94
CES23 = 91	CES48 = 86	CES73 = 89	CES98 = 92
CES24 = 90	CES49 = 97	CES74 = 87	CES99 = 91
CES25 = 71	CES50 = 94	CES75 = 89	





REPORT NUMBER: SP1-2507-484-6-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2507-484-6-R2

TM-30-18

Measure Comparisons





(END OF REPORT)