

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED3010-12-BK**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-4)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED3010-12-BK
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD BLACK
Light Source: (1) SORAA 3000K 95 CRI 10°NSP LED
SM16-07-10D-930-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp:	N/A	NEMA Type:	2H x 2V
Luminaire Lumens:	263.3 lumens	Max Intensity:	4912.1 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	32.9 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	12.3°H x 12.3°V	Field Angle (10%):	19.2°H x 19.2°V
Beam Lumens:	132.4 lumens	Field Lumens:	196.2 lumens
Beam Efficiency:	50.3%	Field Efficiency:	74.5%

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

Iso-Candela Plot




REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

Lumen Table

90																
80	0.0	0.0		0.0		0.0		0.0		0.0		0.0		0.0		0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
60		0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.1	0.1	0.0	0.0	0.0	
40		0.0	0.0	0.1	0.1	0.2	0.3	0.4	0.4	0.3	0.2	0.1	0.1	0.0		
30	0.0	0.0	0.0	0.1	0.2	0.3	0.5	0.8	0.8	0.5	0.3	0.2	0.1	0.0	0.0	
20		0.0	0.0	0.1	0.3	0.5	1.3	3.5	3.5	1.3	0.5	0.3	0.1	0.0		
10	0.0	0.0	0.0	0.1	0.3	0.7	3.4	51.7	51.7	3.4	0.7	0.3	0.1	0.0	0.0	
0		0.0	0.0	0.1	0.3	0.7	3.4	51.7	51.7	3.4	0.7	0.3	0.1	0.0		
-10	0.0	0.0	0.0	0.1	0.3	0.5	1.3	3.5	3.5	1.3	0.5	0.3	0.1	0.0	0.0	
-20		0.0	0.0	0.1	0.2	0.3	0.5	0.8	0.8	0.5	0.3	0.2	0.1	0.0		
-30	0.0	0.0	0.0	0.1	0.1	0.2	0.3	0.4	0.4	0.3	0.2	0.1	0.1	0.0	0.0	
-40		0.0	0.0	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.1	0.1	0.0	0.0		
-50	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-70																
-80	0.0	0.0		0.0		0.0		0.0		0.0		0.0		0.0		
-90																


REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

Luminous Intensity Polar Plot



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

Luminous Intensity Plot



Beam:
H Angle: 12.3°
V Angle: 12.3°
Lumens: 132.4
Efficiency: 50.3%

Field:
H Angle: 19.2°
V Angle: 19.2°
Lumens: 196.2
Efficiency: 74.5%

Spill:
Lumens: 67.2
Efficiency: 25.5%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 0-Deg

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

FIELD
BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	1
45°	0	0	0	0	0	0	0	0	0	0	1
43.75°	0	0	0	0	0	0	0	0	0	1	1
42.5°	0	0	0	0	0	0	0	0	1	1	1
41.25°	0	0	0	0	0	0	0	1	1	1	1
40°	0	0	0	0	0	0	0	1	1	1	1
38.75°	0	0	0	0	0	0	1	1	1	1	1
37.5°	0	0	0	0	0	0	1	1	1	1	1
36.25°	0	0	0	0	0	1	1	1	1	1	1
35°	0	0	0	0	0	1	1	1	1	1	2

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	0	0	0	0	1	1	1	1	1	1	2
32.5°	0	0	0	0	1	1	1	1	1	2	2
31.25°	0	0	0	0	1	1	1	1	1	2	2
30°	0	0	0	1	1	1	1	1	2	2	2
28.75°	0	0	0	1	1	1	1	1	2	2	2
27.5°	0	0	0	1	1	1	1	1	2	2	3
26.25°	0	0	1	1	1	1	1	2	2	2	3
25°	0	0	1	1	1	1	1	2	2	3	3
23.75°	0	0	1	1	1	1	2	2	2	3	3
22.5°	0	0	1	1	1	1	2	2	2	3	3
21.25°	0	1	1	1	1	1	2	2	3	3	3
20°	0	1	1	1	1	1	2	2	3	3	3
18.75°	0	1	1	1	1	2	2	2	3	3	3
17.5°	0	1	1	1	1	2	2	2	3	3	3
16.25°	0	1	1	1	1	2	2	3	3	3	3
15°	1	1	1	1	1	2	2	3	3	3	3
13.75°	1	1	1	1	1	2	2	3	3	3	3
12.5°	1	1	1	1	1	2	2	3	3	3	4
11.25°	1	1	1	1	2	2	2	3	3	3	4
10°	1	1	1	1	2	2	2	3	3	3	4
8.75°	1	1	1	1	2	2	3	3	3	3	4
7.5°	1	1	1	1	2	2	3	3	3	3	4
6.25°	1	1	1	1	2	2	3	3	3	3	4
5°	1	1	1	1	2	2	3	3	3	3	4
3.75°	1	1	1	1	2	2	3	3	3	3	4
2.5°	1	1	1	1	2	2	3	3	3	4	4
1.25°	1	1	1	1	2	2	3	3	3	4	4
0°	1	1	1	1	2	2	3	3	3	4	4
-1.25°	1	1	1	1	2	2	3	3	3	4	4
-2.5°	1	1	1	1	2	2	3	3	3	4	4
-3.75°	1	1	1	1	2	2	3	3	3	3	4
-5°	1	1	1	1	2	2	3	3	3	3	4
-6.25°	1	1	1	1	2	2	3	3	3	3	4
-7.5°	1	1	1	1	2	2	3	3	3	3	4
-8.75°	1	1	1	1	2	2	3	3	3	3	4
-10°	1	1	1	1	2	2	2	3	3	3	4
-11.25°	1	1	1	1	2	2	2	3	3	3	4
-12.5°	1	1	1	1	1	2	2	3	3	3	4
-13.75°	1	1	1	1	1	2	2	3	3	3	3
-15°	1	1	1	1	1	2	2	3	3	3	3
-16.25°	0	1	1	1	1	2	2	3	3	3	3
-17.5°	0	1	1	1	1	2	2	2	3	3	3
-18.75°	0	1	1	1	1	2	2	2	3	3	3
-20°	0	1	1	1	1	1	2	2	3	3	3
-21.25°	0	1	1	1	1	1	2	2	3	3	3

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	0	0	1	1	1	1	2	2	2	3	3
-23.75°	0	0	1	1	1	1	2	2	2	3	3
-25°	0	0	1	1	1	1	1	2	2	3	3
-26.25°	0	0	1	1	1	1	1	2	2	2	3
-27.5°	0	0	0	1	1	1	1	1	2	2	3
-28.75°	0	0	0	1	1	1	1	1	2	2	2
-30°	0	0	0	1	1	1	1	1	2	2	2
-31.25°	0	0	0	0	1	1	1	1	1	2	2
-32.5°	0	0	0	0	1	1	1	1	1	2	2
-33.75°	0	0	0	0	1	1	1	1	1	1	2
-35°	0	0	0	0	0	1	1	1	1	1	2
-36.25°	0	0	0	0	0	1	1	1	1	1	1
-37.5°	0	0	0	0	0	0	1	1	1	1	1
-38.75°	0	0	0	0	0	0	1	1	1	1	1
-40°	0	0	0	0	0	0	0	1	1	1	1
-41.25°	0	0	0	0	0	0	0	1	1	1	1
-42.5°	0	0	0	0	0	0	0	0	1	1	1
-43.75°	0	0	0	0	0	0	0	0	0	1	1
-45°	0	0	0	0	0	0	0	0	0	0	1
-46.25°	0	0	0	0	0	0	0	0	0	0	1
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	1
55°	0	0	0	0	0	0	0	0	1	1	1
53.75°	0	0	0	0	0	0	1	1	1	1	1
52.5°	0	0	0	0	0	1	1	1	1	1	1
51.25°	0	0	0	0	1	1	1	1	1	1	1
50°	0	0	1	1	1	1	1	1	1	1	1
48.75°	0	1	1	1	1	1	1	1	1	1	2
47.5°	1	1	1	1	1	1	1	1	2	2	2
46.25°	1	1	1	1	1	1	1	2	2	2	2
45°	1	1	1	1	1	1	2	2	2	2	3
43.75°	1	1	1	1	1	2	2	2	2	3	3
42.5°	1	1	1	1	2	2	2	2	3	3	3
41.25°	1	1	1	2	2	2	2	3	3	3	3
40°	1	1	2	2	2	2	3	3	3	3	3
38.75°	1	2	2	2	2	3	3	3	3	3	4
37.5°	1	2	2	2	3	3	3	3	3	4	4
36.25°	2	2	2	3	3	3	3	3	4	4	5
35°	2	2	3	3	3	3	3	4	4	5	5

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	2	2	3	3	3	3	4	4	5	5	5
32.5°	2	3	3	3	3	3	4	4	5	5	5
31.25°	2	3	3	3	3	4	4	5	5	5	6
30°	3	3	3	3	4	4	5	5	5	6	6
28.75°	3	3	3	3	4	4	5	5	6	6	6
27.5°	3	3	3	4	4	5	5	5	6	6	7
26.25°	3	3	3	4	5	5	5	6	6	6	7
25°	3	3	4	4	5	5	5	6	6	7	8
23.75°	3	3	4	5	5	5	6	6	7	7	8
22.5°	3	3	4	5	5	5	6	6	7	8	8
21.25°	3	4	4	5	5	6	6	7	7	8	9
20°	3	4	5	5	5	6	6	7	8	9	9
18.75°	3	4	5	5	6	6	6	7	8	9	10
17.5°	4	4	5	5	6	6	7	8	8	9	10
16.25°	4	5	5	5	6	6	7	8	9	10	10
15°	4	5	5	6	6	6	7	8	9	10	10
13.75°	4	5	5	6	6	7	8	8	9	10	10
12.5°	4	5	5	6	6	7	8	9	10	10	10
11.25°	5	5	5	6	6	7	8	9	10	10	11
10°	5	5	5	6	6	7	8	9	10	10	11
8.75°	5	5	6	6	7	7	8	9	10	10	11
7.5°	5	5	6	6	7	8	8	9	10	10	11
6.25°	5	5	6	6	7	8	9	10	10	10	11
5°	5	5	6	6	7	8	9	10	10	11	11
3.75°	5	5	6	6	7	8	9	10	10	11	11
2.5°	5	5	6	6	7	8	9	10	10	11	11
1.25°	5	5	6	6	7	8	9	10	10	11	11
0°	5	5	6	6	7	8	9	10	10	11	12
-1.25°	5	5	6	6	7	8	9	10	10	11	11
-2.5°	5	5	6	6	7	8	9	10	10	11	11
-3.75°	5	5	6	6	7	8	9	10	10	11	11
-5°	5	5	6	6	7	8	9	10	10	11	11
-6.25°	5	5	6	6	7	8	9	10	10	10	11
-7.5°	5	5	6	6	7	8	8	9	10	10	11
-8.75°	5	5	6	6	7	7	8	9	10	10	11
-10°	5	5	5	6	6	7	8	9	10	10	11
-11.25°	5	5	5	6	6	7	8	9	10	10	11
-12.5°	4	5	5	6	6	7	8	9	10	10	10
-13.75°	4	5	5	6	6	7	8	8	9	10	10
-15°	4	5	5	6	6	6	7	8	9	10	10
-16.25°	4	5	5	5	6	6	7	8	9	10	10
-17.5°	4	4	5	5	6	6	7	8	8	9	10
-18.75°	3	4	5	5	6	6	6	7	8	9	10
-20°	3	4	5	5	5	6	6	7	8	9	9
-21.25°	3	4	4	5	5	6	6	7	7	8	9

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	3	3	4	5	5	5	6	6	7	8	8
-23.75°	3	3	4	5	5	5	6	6	7	7	8
-25°	3	3	4	4	5	5	5	6	6	7	8
-26.25°	3	3	3	4	5	5	5	6	6	6	7
-27.5°	3	3	3	4	4	5	5	5	6	6	7
-28.75°	3	3	3	3	4	4	5	5	6	6	6
-30°	3	3	3	3	4	4	5	5	5	6	6
-31.25°	2	3	3	3	3	4	4	5	5	5	6
-32.5°	2	3	3	3	3	3	4	4	5	5	5
-33.75°	2	2	3	3	3	3	4	4	5	5	5
-35°	2	2	3	3	3	3	3	4	4	5	5
-36.25°	2	2	2	3	3	3	3	3	4	4	5
-37.5°	1	2	2	2	3	3	3	3	3	4	4
-38.75°	1	2	2	2	2	3	3	3	3	3	4
-40°	1	1	2	2	2	2	3	3	3	3	3
-41.25°	1	1	1	2	2	2	2	3	3	3	3
-42.5°	1	1	1	1	2	2	2	2	3	3	3
-43.75°	1	1	1	1	1	2	2	2	2	3	3
-45°	1	1	1	1	1	1	2	2	2	2	3
-46.25°	1	1	1	1	1	1	1	2	2	2	2
-47.5°	1	1	1	1	1	1	1	1	2	2	2
-48.75°	0	1	1	1	1	1	1	1	1	1	2
-50°	0	0	1	1	1	1	1	1	1	1	1
-51.25°	0	0	0	0	1	1	1	1	1	1	1
-52.5°	0	0	0	0	0	1	1	1	1	1	1
-53.75°	0	0	0	0	0	0	1	1	1	1	1
-55°	0	0	0	0	0	0	0	0	1	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	1	1	1	1
58.75°	0	0	0	0	1	1	1	1	1	1	1
57.5°	0	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	2	2
53.75°	1	1	1	1	1	1	1	2	2	2	2
52.5°	1	1	1	1	2	2	2	2	2	2	2
51.25°	1	1	2	2	2	2	2	2	3	3	3
50°	2	2	2	2	2	2	3	3	3	3	3
48.75°	2	2	2	2	3	3	3	3	3	3	3
47.5°	2	2	3	3	3	3	3	3	3	3	3
46.25°	3	3	3	3	3	3	3	3	4	4	4
45°	3	3	3	3	3	3	4	4	4	5	5
43.75°	3	3	3	3	4	4	4	5	5	5	5
42.5°	3	3	3	4	4	4	5	5	5	5	5
41.25°	3	4	4	4	5	5	5	5	5	6	6
40°	4	4	4	5	5	5	5	6	6	6	6
38.75°	4	5	5	5	5	6	6	6	6	7	7
37.5°	5	5	5	5	6	6	6	6	7	7	8
36.25°	5	5	5	6	6	6	7	7	8	8	8
35°	5	5	6	6	6	7	7	8	8	9	9

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	5	6	6	6	7	7	8	9	9	9	10
32.5°	6	6	6	7	8	8	9	9	10	10	10
31.25°	6	6	7	8	8	9	9	10	10	10	10
30°	6	7	8	8	9	9	10	10	10	11	11
28.75°	7	7	8	9	9	10	10	10	11	11	12
27.5°	7	8	9	9	10	10	10	11	11	12	12
26.25°	8	9	9	10	10	10	11	11	12	12	13
25°	8	9	10	10	10	11	11	12	12	13	13
23.75°	9	9	10	10	11	11	12	12	13	13	14
22.5°	9	10	10	10	11	12	12	13	13	14	14
21.25°	10	10	10	11	12	12	13	13	13	14	15
20°	10	10	11	11	12	13	13	13	14	15	16
18.75°	10	10	11	12	12	13	13	14	15	16	17
17.5°	10	11	11	12	13	13	14	15	16	17	18
16.25°	10	11	12	12	13	13	14	15	17	18	19
15°	11	11	12	13	13	14	15	16	18	19	21
13.75°	11	12	12	13	13	14	15	17	18	20	22
12.5°	11	12	13	13	14	15	16	18	19	21	23
11.25°	11	12	13	13	14	15	17	18	20	22	24
10°	12	12	13	13	14	16	17	19	21	23	25
8.75°	12	12	13	13	15	16	18	19	21	24	27
7.5°	12	13	13	14	15	17	18	20	22	24	28
6.25°	12	13	13	14	15	17	19	20	23	25	29
5°	12	13	13	14	16	17	19	21	23	26	30
3.75°	12	13	13	14	16	17	19	21	23	27	30
2.5°	12	13	13	15	16	18	19	22	24	27	31
1.25°	12	13	13	15	16	18	19	22	24	27	31
0°	12	13	13	15	16	18	20	22	24	27	31
-1.25°	12	13	13	15	16	18	19	22	24	27	31
-2.5°	12	13	13	15	16	18	19	22	24	27	31
-3.75°	12	13	13	14	16	17	19	21	23	27	30
-5°	12	13	13	14	16	17	19	21	23	26	30
-6.25°	12	13	13	14	15	17	19	20	23	25	29
-7.5°	12	13	13	14	15	17	18	20	22	24	28
-8.75°	12	12	13	13	15	16	18	19	21	24	27
-10°	12	12	13	13	14	16	17	19	21	23	25
-11.25°	11	12	13	13	14	15	17	18	20	22	24
-12.5°	11	12	13	13	14	15	16	18	19	21	23
-13.75°	11	12	12	13	13	14	15	17	18	20	22
-15°	11	11	12	13	13	14	15	16	18	19	21
-16.25°	10	11	12	12	13	13	14	15	17	18	19
-17.5°	10	11	11	12	13	13	14	15	16	17	18
-18.75°	10	10	11	12	12	13	13	14	15	16	17
-20°	10	10	11	11	12	13	13	13	14	15	16
-21.25°	10	10	10	11	12	12	13	13	13	14	15

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	9	10	10	10	11	12	12	13	13	14	14
-23.75°	9	9	10	10	11	11	12	12	13	13	14
-25°	8	9	10	10	10	11	11	12	12	13	13
-26.25°	8	9	9	10	10	10	11	11	12	12	13
-27.5°	7	8	9	9	10	10	10	11	11	12	12
-28.75°	7	7	8	9	9	10	10	10	11	11	12
-30°	6	7	8	8	9	9	10	10	10	11	11
-31.25°	6	6	7	8	8	9	9	10	10	10	10
-32.5°	6	6	6	7	8	8	9	9	10	10	10
-33.75°	5	6	6	6	7	7	8	9	9	9	10
-35°	5	5	6	6	6	7	7	8	8	9	9
-36.25°	5	5	5	6	6	6	7	7	8	8	8
-37.5°	5	5	5	5	6	6	6	6	7	7	8
-38.75°	4	5	5	5	5	6	6	6	6	7	7
-40°	4	4	4	5	5	5	5	6	6	6	6
-41.25°	3	4	4	4	5	5	5	5	5	6	6
-42.5°	3	3	3	4	4	4	5	5	5	5	5
-43.75°	3	3	3	3	4	4	4	5	5	5	5
-45°	3	3	3	3	3	3	4	4	4	5	5
-46.25°	3	3	3	3	3	3	3	3	4	4	4
-47.5°	2	2	3	3	3	3	3	3	3	3	3
-48.75°	2	2	2	2	3	3	3	3	3	3	3
-50°	2	2	2	2	2	2	3	3	3	3	3
-51.25°	1	1	2	2	2	2	2	2	3	3	3
-52.5°	1	1	1	1	2	2	2	2	2	2	2
-53.75°	1	1	1	1	1	1	1	2	2	2	2
-55°	1	1	1	1	1	1	1	1	1	2	2
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	0	1	1	1	1	1	1	1	1	1	1
-58.75°	0	0	0	0	1	1	1	1	1	1	1
-60°	0	0	0	0	0	0	0	1	1	1	1
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	2	2	2
56.25°	1	1	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	3
53.75°	2	2	2	2	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	4	4	4	4
48.75°	3	3	3	4	4	4	4	4	5	5	5
47.5°	4	4	4	4	5	5	5	5	5	5	5
46.25°	4	5	5	5	5	5	5	5	5	5	6
45°	5	5	5	5	5	6	6	6	6	6	6
43.75°	5	5	6	6	6	6	6	6	6	6	7
42.5°	6	6	6	6	6	6	7	7	7	7	7
41.25°	6	6	6	7	7	7	8	8	8	8	8
40°	7	7	7	8	8	8	8	9	9	9	9
38.75°	7	8	8	8	9	9	9	10	10	10	10
37.5°	8	9	9	9	10	10	10	10	10	10	10
36.25°	9	9	10	10	10	10	10	10	11	11	11
35°	10	10	10	10	10	11	11	11	11	12	12

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	10	10	10	11	11	11	12	12	12	12	12
32.5°	10	11	11	11	12	12	12	13	13	13	13
31.25°	11	11	12	12	12	13	13	13	13	13	13
30°	12	12	12	13	13	13	13	14	14	14	15
28.75°	12	13	13	13	13	14	14	15	15	16	16
27.5°	13	13	13	14	14	15	15	16	17	17	18
26.25°	13	13	14	15	15	16	17	18	18	19	19
25°	13	14	15	16	17	18	18	19	20	21	21
23.75°	14	15	16	17	18	19	20	21	22	23	24
22.5°	15	16	17	18	19	21	22	23	24	25	27
21.25°	16	18	19	20	21	22	24	25	27	28	30
20°	18	19	20	22	23	24	26	28	30	33	36
18.75°	19	20	22	23	25	27	29	32	36	40	44
17.5°	20	22	23	25	28	30	34	38	43	47	54
16.25°	21	23	25	28	30	35	40	45	52	59	67
15°	22	24	27	30	35	41	46	55	63	72	80
13.75°	24	26	29	34	40	46	55	65	75	84	93
12.5°	25	28	32	38	45	55	65	76	87	97	107
11.25°	27	30	36	43	52	63	75	87	99	110	132
10°	28	33	40	47	59	72	84	97	110	135	158
8.75°	30	36	44	54	67	80	93	107	132	158	191
7.5°	31	39	47	60	73	87	102	122	152	181	258
6.25°	34	42	51	65	79	94	109	139	169	237	319
5°	36	44	55	69	84	99	121	153	195	285	372
3.75°	37	46	58	73	88	104	131	164	231	324	494
2.5°	39	47	61	75	91	107	138	172	257	353	594
1.25°	39	48	62	77	93	109	143	177	273	371	693
0°	39	48	63	77	94	110	145	179	278	378	733
-1.25°	39	48	62	77	93	109	143	177	273	371	693
-2.5°	39	47	61	75	91	107	138	172	257	353	594
-3.75°	37	46	58	73	88	104	131	164	231	324	494
-5°	36	44	55	69	84	99	121	153	195	285	372
-6.25°	34	42	51	65	79	94	109	139	169	237	319
-7.5°	31	39	47	60	73	87	102	122	152	181	258
-8.75°	30	36	44	54	67	80	93	107	132	158	191
-10°	28	33	40	47	59	72	84	97	110	135	158
-11.25°	27	30	36	43	52	63	75	87	99	110	132
-12.5°	25	28	32	38	45	55	65	76	87	97	107
-13.75°	24	26	29	34	40	46	55	65	75	84	93
-15°	22	24	27	30	35	41	46	55	63	72	80
-16.25°	21	23	25	28	30	35	40	45	52	59	67
-17.5°	20	22	23	25	28	30	34	38	43	47	54
-18.75°	19	20	22	23	25	27	29	32	36	40	44
-20°	18	19	20	22	23	24	26	28	30	33	36
-21.25°	16	18	19	20	21	22	24	25	27	28	30

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	15	16	17	18	19	21	22	23	24	25	27
-23.75°	14	15	16	17	18	19	20	21	22	23	24
-25°	13	14	15	16	17	18	18	19	20	21	21
-26.25°	13	13	14	15	15	16	17	18	18	19	19
-27.5°	13	13	13	14	14	15	15	16	17	17	18
-28.75°	12	13	13	13	13	14	14	15	15	16	16
-30°	12	12	12	13	13	13	13	14	14	14	15
-31.25°	11	11	12	12	12	13	13	13	13	13	13
-32.5°	10	11	11	11	12	12	12	13	13	13	13
-33.75°	10	10	10	11	11	11	12	12	12	12	12
-35°	10	10	10	10	10	11	11	11	11	12	12
-36.25°	9	9	10	10	10	10	10	10	11	11	11
-37.5°	8	9	9	9	10	10	10	10	10	10	10
-38.75°	7	8	8	8	9	9	9	10	10	10	10
-40°	7	7	7	8	8	8	8	9	9	9	9
-41.25°	6	6	6	7	7	7	8	8	8	8	8
-42.5°	6	6	6	6	6	6	7	7	7	7	7
-43.75°	5	5	6	6	6	6	6	6	6	6	7
-45°	5	5	5	5	5	6	6	6	6	6	6
-46.25°	4	5	5	5	5	5	5	5	5	5	6
-47.5°	4	4	4	4	5	5	5	5	5	5	5
-48.75°	3	3	3	4	4	4	4	4	5	5	5
-50°	3	3	3	3	3	3	3	4	4	4	4
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	2	2	2	2	3	3	3	3	3	3	3
-55°	2	2	2	2	2	2	2	2	2	2	3
-56.25°	1	1	2	2	2	2	2	2	2	2	2
-57.5°	1	1	1	1	1	1	1	1	2	2	2
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	0	0	0	0	0	1	1	1	1	1	1
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	4	4	4	4	4	3	3
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	5	5	5	5	5	5	5	5	5	5	5
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	6	6	6	6	6	6	6	6	6	6	6
45°	6	6	6	6	6	6	6	6	6	6	6
43.75°	7	7	7	7	7	7	7	7	7	7	7
42.5°	8	8	8	8	8	8	8	8	8	8	8
41.25°	8	9	9	9	9	9	9	9	9	9	9
40°	9	10	10	10	10	10	10	10	10	10	10
38.75°	10	10	10	10	10	10	10	10	10	10	10
37.5°	10	10	11	11	11	11	11	11	11	11	11
36.25°	11	11	11	11	11	11	12	11	11	11	11
35°	12	12	12	12	12	12	12	12	12	12	12

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	13	13	13	13	13	13	13	13	13	13	13
32.5°	13	13	13	13	13	13	13	13	13	13	13
31.25°	14	14	14	14	15	15	15	15	15	14	14
30°	15	15	16	16	16	16	16	16	16	16	16
28.75°	17	17	17	17	18	18	18	18	18	17	17
27.5°	18	19	19	19	19	19	20	19	19	19	19
26.25°	20	20	21	21	22	22	22	22	22	21	21
25°	22	23	23	23	24	24	24	24	24	23	23
23.75°	24	25	26	27	27	27	27	27	27	27	26
22.5°	28	29	30	30	31	31	31	31	31	30	30
21.25°	31	34	36	37	39	39	39	39	39	37	36
20°	39	42	44	46	47	48	48	48	47	46	44
18.75°	47	51	55	58	61	62	63	62	61	58	55
17.5°	60	65	69	73	75	77	77	77	75	73	69
16.25°	73	79	84	88	91	93	94	93	91	88	84
15°	87	94	99	104	107	109	110	109	107	104	99
13.75°	102	109	121	131	138	143	145	143	138	131	121
12.5°	122	139	153	164	172	177	179	177	172	164	153
11.25°	152	169	195	231	257	273	278	273	257	231	195
10°	181	237	285	324	353	371	378	371	353	324	285
8.75°	258	319	372	494	594	693	733	693	594	494	372
7.5°	331	437	616	904	1148	1359	1431	1359	1148	904	616
6.25°	437	696	1081	1582	1997	2279	2377	2279	1997	1582	1081
5°	616	1081	1736	2379	2883	3208	3323	3208	2883	2379	1736
3.75°	904	1582	2379	3097	3625	3956	4051	3956	3625	3097	2379
2.5°	1148	1997	2883	3625	4151	4459	4543	4459	4151	3625	2883
1.25°	1359	2279	3208	3956	4459	4722	4803	4722	4459	3956	3208
0°	1431	2377	3323	4051	4543	4803	4912	4803	4543	4051	3323
-1.25°	1359	2279	3208	3956	4459	4722	4803	4722	4459	3956	3208
-2.5°	1148	1997	2883	3625	4151	4459	4543	4459	4151	3625	2883
-3.75°	904	1582	2379	3097	3625	3956	4051	3956	3625	3097	2379
-5°	616	1081	1736	2379	2883	3208	3323	3208	2883	2379	1736
-6.25°	437	696	1081	1582	1997	2279	2377	2279	1997	1582	1081
-7.5°	331	437	616	904	1148	1359	1431	1359	1148	904	616
-8.75°	258	319	372	494	594	693	733	693	594	494	372
-10°	181	237	285	324	353	371	378	371	353	324	285
-11.25°	152	169	195	231	257	273	278	273	257	231	195
-12.5°	122	139	153	164	172	177	179	177	172	164	153
-13.75°	102	109	121	131	138	143	145	143	138	131	121
-15°	87	94	99	104	107	109	110	109	107	104	99
-16.25°	73	79	84	88	91	93	94	93	91	88	84
-17.5°	60	65	69	73	75	77	77	77	75	73	69
-18.75°	47	51	55	58	61	62	63	62	61	58	55
-20°	39	42	44	46	47	48	48	48	47	46	44
-21.25°	31	34	36	37	39	39	39	39	39	37	36

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	28	29	30	30	31	31	31	31	31	30	30
-23.75°	24	25	26	27	27	27	27	27	27	27	26
-25°	22	23	23	23	24	24	24	24	24	23	23
-26.25°	20	20	21	21	22	22	22	22	22	21	21
-27.5°	18	19	19	19	19	19	20	19	19	19	19
-28.75°	17	17	17	17	18	18	18	18	18	17	17
-30°	15	15	16	16	16	16	16	16	16	16	16
-31.25°	14	14	14	14	15	15	15	15	15	14	14
-32.5°	13	13	13	13	13	13	13	13	13	13	13
-33.75°	13	13	13	13	13	13	13	13	13	13	13
-35°	12	12	12	12	12	12	12	12	12	12	12
-36.25°	11	11	11	11	11	11	12	11	11	11	11
-37.5°	10	10	11	11	11	11	11	11	11	11	11
-38.75°	10	10	10	10	10	10	10	10	10	10	10
-40°	9	10	10	10	10	10	10	10	10	10	10
-41.25°	8	9	9	9	9	9	9	9	9	9	9
-42.5°	8	8	8	8	8	8	8	8	8	8	8
-43.75°	7	7	7	7	7	7	7	7	7	7	7
-45°	6	6	6	6	6	6	6	6	6	6	6
-46.25°	6	6	6	6	6	6	6	6	6	6	6
-47.5°	5	5	5	5	5	5	5	5	5	5	5
-48.75°	5	5	5	5	5	5	5	5	5	5	5
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	3	3	3	3	4	4	4	4	4	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	1	1	1	1	1	1	1	1	0	0	0
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	2	2	2	2	1	1	1	1	1	1
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	2	2	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	3	3	3	2	2
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	4	4	4	4	4	4	3	3	3	3	3
48.75°	5	5	5	5	5	4	4	4	4	4	3
47.5°	5	5	5	5	5	5	5	5	5	4	4
46.25°	6	6	6	5	5	5	5	5	5	5	5
45°	6	6	6	6	6	6	6	6	5	5	5
43.75°	7	7	7	6	6	6	6	6	6	6	6
42.5°	8	8	7	7	7	7	7	6	6	6	6
41.25°	9	8	8	8	8	8	8	7	7	7	6
40°	10	9	9	9	9	9	8	8	8	8	7
38.75°	10	10	10	10	10	10	9	9	9	8	8
37.5°	10	10	10	10	10	10	10	10	10	9	9
36.25°	11	11	11	11	11	10	10	10	10	10	10
35°	12	12	12	12	11	11	11	11	10	10	10

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	13	13	12	12	12	12	12	11	11	11	10
32.5°	13	13	13	13	13	13	12	12	12	11	11
31.25°	14	14	13	13	13	13	13	13	12	12	12
30°	15	15	15	14	14	14	13	13	13	13	12
28.75°	17	17	16	16	15	15	14	14	13	13	13
27.5°	19	18	18	17	17	16	15	15	14	14	13
26.25°	20	20	19	19	18	18	17	16	15	15	14
25°	23	22	21	21	20	19	18	18	17	16	15
23.75°	25	24	24	23	22	21	20	19	18	17	16
22.5°	29	28	27	25	24	23	22	21	19	18	17
21.25°	34	31	30	28	27	25	24	22	21	20	19
20°	42	39	36	33	30	28	26	24	23	22	20
18.75°	51	47	44	40	36	32	29	27	25	23	22
17.5°	65	60	54	47	43	38	34	30	28	25	23
16.25°	79	73	67	59	52	45	40	35	30	28	25
15°	94	87	80	72	63	55	46	41	35	30	27
13.75°	109	102	93	84	75	65	55	46	40	34	29
12.5°	139	122	107	97	87	76	65	55	45	38	32
11.25°	169	152	132	110	99	87	75	63	52	43	36
10°	237	181	158	135	110	97	84	72	59	47	40
8.75°	319	258	191	158	132	107	93	80	67	54	44
7.5°	437	331	258	181	152	122	102	87	73	60	47
6.25°	696	437	319	237	169	139	109	94	79	65	51
5°	1081	616	372	285	195	153	121	99	84	69	55
3.75°	1582	904	494	324	231	164	131	104	88	73	58
2.5°	1997	1148	594	353	257	172	138	107	91	75	61
1.25°	2279	1359	693	371	273	177	143	109	93	77	62
0°	2377	1431	733	378	278	179	145	110	94	77	63
-1.25°	2279	1359	693	371	273	177	143	109	93	77	62
-2.5°	1997	1148	594	353	257	172	138	107	91	75	61
-3.75°	1582	904	494	324	231	164	131	104	88	73	58
-5°	1081	616	372	285	195	153	121	99	84	69	55
-6.25°	696	437	319	237	169	139	109	94	79	65	51
-7.5°	437	331	258	181	152	122	102	87	73	60	47
-8.75°	319	258	191	158	132	107	93	80	67	54	44
-10°	237	181	158	135	110	97	84	72	59	47	40
-11.25°	169	152	132	110	99	87	75	63	52	43	36
-12.5°	139	122	107	97	87	76	65	55	45	38	32
-13.75°	109	102	93	84	75	65	55	46	40	34	29
-15°	94	87	80	72	63	55	46	41	35	30	27
-16.25°	79	73	67	59	52	45	40	35	30	28	25
-17.5°	65	60	54	47	43	38	34	30	28	25	23
-18.75°	51	47	44	40	36	32	29	27	25	23	22
-20°	42	39	36	33	30	28	26	24	23	22	20
-21.25°	34	31	30	28	27	25	24	22	21	20	19

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	29	28	27	25	24	23	22	21	19	18	17
-23.75°	25	24	24	23	22	21	20	19	18	17	16
-25°	23	22	21	21	20	19	18	18	17	16	15
-26.25°	20	20	19	19	18	18	17	16	15	15	14
-27.5°	19	18	18	17	17	16	15	15	14	14	13
-28.75°	17	17	16	16	15	15	14	14	13	13	13
-30°	15	15	15	14	14	14	13	13	13	13	12
-31.25°	14	14	13	13	13	13	13	13	12	12	12
-32.5°	13	13	13	13	13	13	12	12	12	11	11
-33.75°	13	13	12	12	12	12	12	11	11	11	10
-35°	12	12	12	12	11	11	11	11	10	10	10
-36.25°	11	11	11	11	11	10	10	10	10	10	10
-37.5°	10	10	10	10	10	10	10	10	10	9	9
-38.75°	10	10	10	10	10	10	9	9	9	8	8
-40°	10	9	9	9	9	9	8	8	8	8	7
-41.25°	9	8	8	8	8	8	8	7	7	7	6
-42.5°	8	8	7	7	7	7	7	6	6	6	6
-43.75°	7	7	7	6	6	6	6	6	6	6	6
-45°	6	6	6	6	6	6	6	6	5	5	5
-46.25°	6	6	6	5	5	5	5	5	5	5	5
-47.5°	5	5	5	5	5	5	5	5	5	4	4
-48.75°	5	5	5	5	5	4	4	4	4	4	3
-50°	4	4	4	4	4	4	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	2	2
-55°	3	3	3	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	1	1	0	0	0	0	0	0	0	0	0
60°	1	1	1	1	1	1	0	0	0	0	0
58.75°	1	1	1	1	1	1	1	1	1	0	0
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	2	2	2	2	1	1	1	1	1	1	1
53.75°	2	2	2	2	2	2	1	1	1	1	1
52.5°	3	3	2	2	2	2	2	2	2	1	1
51.25°	3	3	3	3	3	2	2	2	2	2	2
50°	3	3	3	3	3	3	3	2	2	2	2
48.75°	3	3	3	3	3	3	3	3	3	2	2
47.5°	4	4	3	3	3	3	3	3	3	3	3
46.25°	5	4	4	4	4	3	3	3	3	3	3
45°	5	5	5	5	4	4	4	3	3	3	3
43.75°	5	5	5	5	5	5	4	4	4	3	3
42.5°	6	6	5	5	5	5	5	4	4	4	3
41.25°	6	6	6	6	5	5	5	5	5	4	4
40°	7	7	6	6	6	6	5	5	5	5	4
38.75°	8	7	7	7	6	6	6	6	5	5	5
37.5°	9	8	8	7	7	6	6	6	6	5	5
36.25°	9	9	8	8	8	7	7	6	6	6	5
35°	10	10	9	9	8	8	7	7	6	6	6

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	10	10	10	9	9	9	8	7	7	6	6
32.5°	11	10	10	10	10	9	9	8	8	7	6
31.25°	11	11	10	10	10	10	9	9	8	8	7
30°	12	12	11	11	10	10	10	9	9	8	8
28.75°	13	12	12	11	11	10	10	10	9	9	8
27.5°	13	13	12	12	11	11	10	10	10	9	9
26.25°	13	13	13	12	12	11	11	10	10	10	9
25°	14	13	13	13	12	12	11	11	10	10	10
23.75°	15	14	14	13	13	12	12	11	11	10	10
22.5°	16	15	14	14	13	13	12	12	11	10	10
21.25°	18	16	15	14	13	13	13	12	12	11	10
20°	19	18	16	15	14	13	13	13	12	11	11
18.75°	20	19	17	16	15	14	13	13	12	12	11
17.5°	22	20	18	17	16	15	14	13	13	12	11
16.25°	23	21	19	18	17	15	14	13	13	12	12
15°	24	22	21	19	18	16	15	14	13	13	12
13.75°	26	24	22	20	18	17	15	14	13	13	12
12.5°	28	25	23	21	19	18	16	15	14	13	13
11.25°	30	27	24	22	20	18	17	15	14	13	13
10°	33	28	25	23	21	19	17	16	14	13	13
8.75°	36	30	27	24	21	19	18	16	15	13	13
7.5°	39	31	28	24	22	20	18	17	15	14	13
6.25°	42	34	29	25	23	20	19	17	15	14	13
5°	44	36	30	26	23	21	19	17	16	14	13
3.75°	46	37	30	27	23	21	19	17	16	14	13
2.5°	47	39	31	27	24	22	19	18	16	15	13
1.25°	48	39	31	27	24	22	19	18	16	15	13
0°	48	39	31	27	24	22	20	18	16	15	13
-1.25°	48	39	31	27	24	22	19	18	16	15	13
-2.5°	47	39	31	27	24	22	19	18	16	15	13
-3.75°	46	37	30	27	23	21	19	17	16	14	13
-5°	44	36	30	26	23	21	19	17	16	14	13
-6.25°	42	34	29	25	23	20	19	17	15	14	13
-7.5°	39	31	28	24	22	20	18	17	15	14	13
-8.75°	36	30	27	24	21	19	18	16	15	13	13
-10°	33	28	25	23	21	19	17	16	14	13	13
-11.25°	30	27	24	22	20	18	17	15	14	13	13
-12.5°	28	25	23	21	19	18	16	15	14	13	13
-13.75°	26	24	22	20	18	17	15	14	13	13	12
-15°	24	22	21	19	18	16	15	14	13	13	12
-16.25°	23	21	19	18	17	15	14	13	13	12	12
-17.5°	22	20	18	17	16	15	14	13	13	12	11
-18.75°	20	19	17	16	15	14	13	13	12	12	11
-20°	19	18	16	15	14	13	13	13	12	11	11
-21.25°	18	16	15	14	13	13	13	12	12	11	10

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	16	15	14	14	13	13	12	12	11	10	10
-23.75°	15	14	14	13	13	12	12	11	11	10	10
-25°	14	13	13	13	12	12	11	11	10	10	10
-26.25°	13	13	13	12	12	11	11	10	10	10	9
-27.5°	13	13	12	12	11	11	10	10	10	9	9
-28.75°	13	12	12	11	11	10	10	10	9	9	8
-30°	12	12	11	11	10	10	10	9	9	8	8
-31.25°	11	11	10	10	10	10	9	9	8	8	7
-32.5°	11	10	10	10	10	9	9	8	8	7	6
-33.75°	10	10	10	9	9	9	8	7	7	6	6
-35°	10	10	9	9	8	8	7	7	6	6	6
-36.25°	9	9	8	8	8	7	7	6	6	6	5
-37.5°	9	8	8	7	7	6	6	6	6	5	5
-38.75°	8	7	7	7	6	6	6	6	5	5	5
-40°	7	7	6	6	6	6	5	5	5	5	4
-41.25°	6	6	6	6	5	5	5	5	5	4	4
-42.5°	6	6	5	5	5	5	5	4	4	4	3
-43.75°	5	5	5	5	5	5	4	4	4	3	3
-45°	5	5	5	5	4	4	4	3	3	3	3
-46.25°	5	4	4	4	4	3	3	3	3	3	3
-47.5°	4	4	3	3	3	3	3	3	3	3	3
-48.75°	3	3	3	3	3	3	3	3	3	2	2
-50°	3	3	3	3	3	3	3	2	2	2	2
-51.25°	3	3	3	3	3	2	2	2	2	2	2
-52.5°	3	3	2	2	2	2	2	2	2	1	1
-53.75°	2	2	2	2	2	2	1	1	1	1	1
-55°	2	2	2	2	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	0	0
-60°	1	1	1	1	1	1	0	0	0	0	0
-61.25°	1	1	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	1	0	0	0	0	0	0	0	0	0	0
56.25°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	1	1	0	0	0	0	0	0
53.75°	1	1	1	1	1	1	1	0	0	0	0
52.5°	1	1	1	1	1	1	1	1	0	0	0
51.25°	1	1	1	1	1	1	1	1	1	0	0
50°	2	2	1	1	1	1	1	1	1	1	1
48.75°	2	2	2	1	1	1	1	1	1	1	1
47.5°	2	2	2	2	2	1	1	1	1	1	1
46.25°	3	3	2	2	2	2	1	1	1	1	1
45°	3	3	3	2	2	2	2	1	1	1	1
43.75°	3	3	3	3	2	2	2	2	1	1	1
42.5°	3	3	3	3	3	2	2	2	2	1	1
41.25°	4	3	3	3	3	3	2	2	2	2	1
40°	4	4	3	3	3	3	3	2	2	2	2
38.75°	5	4	4	3	3	3	3	3	2	2	2
37.5°	5	5	4	4	3	3	3	3	3	2	2
36.25°	5	5	5	4	4	3	3	3	3	3	2
35°	5	5	5	5	4	4	3	3	3	3	3

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	6	5	5	5	5	4	4	3	3	3	3
32.5°	6	6	5	5	5	4	4	3	3	3	3
31.25°	6	6	6	5	5	5	4	4	3	3	3
30°	7	6	6	6	5	5	5	4	4	3	3
28.75°	7	7	6	6	6	5	5	4	4	3	3
27.5°	8	7	7	6	6	5	5	5	4	4	3
26.25°	9	8	7	6	6	6	5	5	5	4	3
25°	9	8	8	7	6	6	5	5	5	4	4
23.75°	9	9	8	7	7	6	6	5	5	5	4
22.5°	10	9	8	8	7	6	6	5	5	5	4
21.25°	10	10	9	8	7	7	6	6	5	5	4
20°	10	10	9	9	8	7	6	6	5	5	5
18.75°	10	10	10	9	8	7	6	6	6	5	5
17.5°	11	10	10	9	8	8	7	6	6	5	5
16.25°	11	10	10	10	9	8	7	6	6	5	5
15°	11	11	10	10	9	8	7	6	6	6	5
13.75°	12	11	10	10	9	8	8	7	6	6	5
12.5°	12	11	10	10	10	9	8	7	6	6	5
11.25°	12	11	11	10	10	9	8	7	6	6	5
10°	12	12	11	10	10	9	8	7	6	6	5
8.75°	12	12	11	10	10	9	8	7	7	6	6
7.5°	13	12	11	10	10	9	8	8	7	6	6
6.25°	13	12	11	10	10	10	9	8	7	6	6
5°	13	12	11	11	10	10	9	8	7	6	6
3.75°	13	12	11	11	10	10	9	8	7	6	6
2.5°	13	12	11	11	10	10	9	8	7	6	6
1.25°	13	12	11	11	10	10	9	8	7	6	6
0°	13	12	12	11	10	10	9	8	7	6	6
-1.25°	13	12	11	11	10	10	9	8	7	6	6
-2.5°	13	12	11	11	10	10	9	8	7	6	6
-3.75°	13	12	11	11	10	10	9	8	7	6	6
-5°	13	12	11	11	10	10	9	8	7	6	6
-6.25°	13	12	11	10	10	10	9	8	7	6	6
-7.5°	13	12	11	10	10	9	8	8	7	6	6
-8.75°	12	12	11	10	10	9	8	7	7	6	6
-10°	12	12	11	10	10	9	8	7	6	6	5
-11.25°	12	11	11	10	10	9	8	7	6	6	5
-12.5°	12	11	10	10	10	9	8	7	6	6	5
-13.75°	12	11	10	10	9	8	8	7	6	6	5
-15°	11	11	10	10	9	8	7	6	6	6	5
-16.25°	11	10	10	10	9	8	7	6	6	5	5
-17.5°	11	10	10	9	8	8	7	6	6	5	5
-18.75°	10	10	10	9	8	7	6	6	6	5	5
-20°	10	10	9	9	8	7	6	6	5	5	5
-21.25°	10	10	9	8	7	7	6	6	5	5	4

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	10	9	8	8	7	6	6	5	5	5	4
-23.75°	9	9	8	7	7	6	6	5	5	5	4
-25°	9	8	8	7	6	6	5	5	5	4	4
-26.25°	9	8	7	6	6	6	5	5	5	4	3
-27.5°	8	7	7	6	6	5	5	5	4	4	3
-28.75°	7	7	6	6	6	5	5	4	4	3	3
-30°	7	6	6	6	5	5	5	4	4	3	3
-31.25°	6	6	6	5	5	5	4	4	3	3	3
-32.5°	6	6	5	5	5	4	4	3	3	3	3
-33.75°	6	5	5	5	5	4	4	3	3	3	3
-35°	5	5	5	5	4	4	3	3	3	3	3
-36.25°	5	5	5	4	4	3	3	3	3	3	2
-37.5°	5	5	4	4	3	3	3	3	3	2	2
-38.75°	5	4	4	3	3	3	3	3	2	2	2
-40°	4	4	3	3	3	3	3	2	2	2	2
-41.25°	4	3	3	3	3	3	2	2	2	2	1
-42.5°	3	3	3	3	3	2	2	2	2	1	1
-43.75°	3	3	3	3	2	2	2	2	1	1	1
-45°	3	3	3	2	2	2	2	1	1	1	1
-46.25°	3	3	2	2	2	2	1	1	1	1	1
-47.5°	2	2	2	2	2	1	1	1	1	1	1
-48.75°	2	2	2	1	1	1	1	1	1	1	1
-50°	2	2	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	0	0
-52.5°	1	1	1	1	1	1	1	1	0	0	0
-53.75°	1	1	1	1	1	1	1	0	0	0	0
-55°	1	1	1	1	1	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	1	0	0	0	0	0	0	0	0	0	0
47.5°	1	1	0	0	0	0	0	0	0	0	0
46.25°	1	1	1	0	0	0	0	0	0	0	0
45°	1	1	1	0	0	0	0	0	0	0	0
43.75°	1	1	1	1	0	0	0	0	0	0	0
42.5°	1	1	1	1	1	0	0	0	0	0	0
41.25°	1	1	1	1	1	1	0	0	0	0	0
40°	1	1	1	1	1	1	0	0	0	0	0
38.75°	2	1	1	1	1	1	1	0	0	0	0
37.5°	2	1	1	1	1	1	1	0	0	0	0
36.25°	2	2	1	1	1	1	1	1	0	0	0
35°	2	2	2	1	1	1	1	1	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	2	2	2	1	1	1	1	1	1	0	0
32.5°	3	2	2	2	1	1	1	1	1	0	0
31.25°	3	2	2	2	1	1	1	1	1	0	0
30°	3	3	2	2	2	1	1	1	1	1	0
28.75°	3	3	2	2	2	1	1	1	1	1	0
27.5°	3	3	3	2	2	1	1	1	1	1	0
26.25°	3	3	3	2	2	2	1	1	1	1	1
25°	3	3	3	3	2	2	1	1	1	1	1
23.75°	3	3	3	3	2	2	2	1	1	1	1
22.5°	3	3	3	3	2	2	2	1	1	1	1
21.25°	4	3	3	3	3	2	2	1	1	1	1
20°	4	3	3	3	3	2	2	1	1	1	1
18.75°	4	3	3	3	3	2	2	2	1	1	1
17.5°	4	4	3	3	3	2	2	2	1	1	1
16.25°	5	4	3	3	3	3	2	2	1	1	1
15°	5	4	3	3	3	3	2	2	1	1	1
13.75°	5	4	3	3	3	3	2	2	1	1	1
12.5°	5	4	4	3	3	3	2	2	1	1	1
11.25°	5	5	4	3	3	3	2	2	2	1	1
10°	5	5	4	3	3	3	2	2	2	1	1
8.75°	5	5	4	3	3	3	3	2	2	1	1
7.5°	5	5	4	3	3	3	3	2	2	1	1
6.25°	5	5	4	3	3	3	3	2	2	1	1
5°	5	5	4	3	3	3	3	2	2	1	1
3.75°	5	5	4	3	3	3	3	2	2	1	1
2.5°	5	5	4	4	3	3	3	2	2	1	1
1.25°	5	5	4	4	3	3	3	2	2	1	1
0°	5	5	4	4	3	3	3	2	2	1	1
-1.25°	5	5	4	4	3	3	3	2	2	1	1
-2.5°	5	5	4	4	3	3	3	2	2	1	1
-3.75°	5	5	4	3	3	3	3	2	2	1	1
-5°	5	5	4	3	3	3	3	2	2	1	1
-6.25°	5	5	4	3	3	3	3	2	2	1	1
-7.5°	5	5	4	3	3	3	3	2	2	1	1
-8.75°	5	5	4	3	3	3	3	2	2	1	1
-10°	5	5	4	3	3	3	2	2	2	1	1
-11.25°	5	5	4	3	3	3	2	2	2	1	1
-12.5°	5	4	4	3	3	3	2	2	1	1	1
-13.75°	5	4	3	3	3	3	2	2	1	1	1
-15°	5	4	3	3	3	3	2	2	1	1	1
-16.25°	5	4	3	3	3	3	2	2	1	1	1
-17.5°	4	4	3	3	3	2	2	2	1	1	1
-18.75°	4	3	3	3	3	2	2	2	1	1	1
-20°	4	3	3	3	3	2	2	1	1	1	1
-21.25°	4	3	3	3	3	2	2	1	1	1	1

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	3	3	3	3	2	2	2	1	1	1	1
-23.75°	3	3	3	3	2	2	2	1	1	1	1
-25°	3	3	3	3	2	2	1	1	1	1	1
-26.25°	3	3	3	2	2	2	1	1	1	1	1
-27.5°	3	3	3	2	2	1	1	1	1	1	0
-28.75°	3	3	2	2	2	1	1	1	1	1	0
-30°	3	3	2	2	2	1	1	1	1	1	0
-31.25°	3	2	2	2	1	1	1	1	1	0	0
-32.5°	3	2	2	2	1	1	1	1	1	0	0
-33.75°	2	2	2	1	1	1	1	1	1	0	0
-35°	2	2	2	1	1	1	1	1	0	0	0
-36.25°	2	2	1	1	1	1	1	1	0	0	0
-37.5°	2	1	1	1	1	1	1	0	0	0	0
-38.75°	2	1	1	1	1	1	1	0	0	0	0
-40°	1	1	1	1	1	1	0	0	0	0	0
-41.25°	1	1	1	1	1	1	0	0	0	0	0
-42.5°	1	1	1	1	1	0	0	0	0	0	0
-43.75°	1	1	1	1	0	0	0	0	0	0	0
-45°	1	1	1	0	0	0	0	0	0	0	0
-46.25°	1	1	1	0	0	0	0	0	0	0	0
-47.5°	1	1	0	0	0	0	0	0	0	0	0
-48.75°	1	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	1	0	0	0	0	0	0	0	0	0	0
20°	1	0	0	0	0	0	0	0	0	0	0
18.75°	1	0	0	0	0	0	0	0	0	0	0
17.5°	1	0	0	0	0	0	0	0	0	0	0
16.25°	1	0	0	0	0	0	0	0	0	0	0
15°	1	1	0	0	0	0	0	0	0	0	0
13.75°	1	1	0	0	0	0	0	0	0	0	0
12.5°	1	1	0	0	0	0	0	0	0	0	0
11.25°	1	1	0	0	0	0	0	0	0	0	0
10°	1	1	0	0	0	0	0	0	0	0	0
8.75°	1	1	0	0	0	0	0	0	0	0	0
7.5°	1	1	0	0	0	0	0	0	0	0	0
6.25°	1	1	0	0	0	0	0	0	0	0	0
5°	1	1	0	0	0	0	0	0	0	0	0
3.75°	1	1	0	0	0	0	0	0	0	0	0
2.5°	1	1	0	0	0	0	0	0	0	0	0
1.25°	1	1	0	0	0	0	0	0	0	0	0
0°	1	1	0	0	0	0	0	0	0	0	0
-1.25°	1	1	0	0	0	0	0	0	0	0	0
-2.5°	1	1	0	0	0	0	0	0	0	0	0
-3.75°	1	1	0	0	0	0	0	0	0	0	0
-5°	1	1	0	0	0	0	0	0	0	0	0
-6.25°	1	1	0	0	0	0	0	0	0	0	0
-7.5°	1	1	0	0	0	0	0	0	0	0	0
-8.75°	1	1	0	0	0	0	0	0	0	0	0
-10°	1	1	0	0	0	0	0	0	0	0	0
-11.25°	1	1	0	0	0	0	0	0	0	0	0
-12.5°	1	1	0	0	0	0	0	0	0	0	0
-13.75°	1	1	0	0	0	0	0	0	0	0	0
-15°	1	1	0	0	0	0	0	0	0	0	0
-16.25°	1	0	0	0	0	0	0	0	0	0	0
-17.5°	1	0	0	0	0	0	0	0	0	0	0
-18.75°	1	0	0	0	0	0	0	0	0	0	0
-20°	1	0	0	0	0	0	0	0	0	0	0
-21.25°	1	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-BK

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)