Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590650

Luminaire Tested: 22CGTX-25-B45-HCD

Issue Date: 9/4/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590650
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2510-581-28)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/4/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	22CGTX-25-B45-HCD
Description:	2X2 2500 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 4500K CCT WITH FROSTED SMOOTH LENS
Light Source:	4500K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	2706.9 lumens
Efficiency:	N/A
Efficacy:	111.4 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 2' x L: 2' x H: 0')
CIE Type:	Direct
Input Watts (W):	24.3
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590650
CATALOG NUMBER: 22CGTX-25-B45-HCD

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590650
CATALOG NUMBER: 22CGTX-25-B45-HCD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	68
3	89	79	70	63	87	77	69	63	74	67	62	71	65	61	69	64	60	57
4	82	69	60	54	79	68	60	53	66	58	52	63	57	52	61	55	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	39	51	44	39	50	43	39	37
7	64	50	41	35	62	50	41	35	48	40	35	47	40	35	45	39	34	32
8	60	46	37	31	58	45	37	31	44	36	31	43	36	31	41	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	25	37	30	25	36	30	25	35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2450	2450	2450
5°	2458	2448	2436
10°	2458	2450	2450
15°	2459	2450	2450
20°	2435	2444	2440
25°	2456	2422	2434
30°	2425	2413	2419
35°	2400	2396	2403
40°	2401	2381	2385
45°	2382	2361	2365
50°	2359	2351	2328
55°	2330	2309	2297
60°	2299	2270	2254
65°	2234	2218	2190
70°	2187	2153	2125
75°	2097	2061	2015
80°	1990	1951	1912
85°	1822	1791	1714

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2382 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590650
CATALOG NUMBER: 22CGTX-25-B45-HCD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	3.2
10°-20°	247.8	9.2
20°-30°	377.0	13.9
30°-40°	457.8	16.9
40°-50°	479.8	17.7
50°-60°	439.9	16.2
60°-70°	344.0	12.7
70°-80°	209.3	7.7
80°-90°	65.0	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	711.0	26.3
0°-40°	1168.9	43.2
0°-60°	2088.5	77.2
0°-90°	2706.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2706.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	910	910	910	910	910	
5°	910	908	906	906	902	87
15°	883	876	880	877	880	248
25°	827	817	816	816	820	379
35°	730	734	730	731	732	459
45°	626	621	620	621	621	482
55°	497	492	492	489	490	443
65°	351	350	348	345	344	347
75°	202	200	198	196	194	213
85°	59	59	58	56	56	66
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590650
CATALOG NUMBER: 22CGTX-25-B45-HCD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*910.4*	910.4	910.4	910.4	910.4
2.5°	*911.4*	*908.9*	*908.4*	*904.9*	*910.9*
5°	*909.9*	908.4	906.4	906.4	901.9
7.5°	*907.9*	903.9	900.5	901.4	903.9
10°	*899.5*	896.0	896.5	891.5	896.5
12.5°	*891.0*	888.6	885.6	888.1	889.5
15°	*882.6*	875.7	879.6	877.2	879.6
17.5°	*864.8*	866.3	865.8	862.8	865.8
20°	*850.4*	854.4	853.4	850.4	851.9
22.5°	*840.5*	835.0	834.5	835.0	836.5
25°	*827.1*	816.7	815.7	816.2	819.7
27.5°	*801.8*	798.9	797.4	796.9	800.3
30°	*780.5*	776.6	776.6	776.1	778.5
32.5°	*758.2*	756.2	755.7	756.2	756.2
35°	*730.5*	734.4	729.5	731.0	731.5
37.5°	*707.7*	709.2	706.7	704.7	705.7
40°	*683.4*	679.9	677.9	677.9	678.9
42.5°	*652.2*	655.1	650.2	653.2	650.2
45°	*625.9*	621.4	620.5	621.0	621.4
47.5°	*593.7*	591.2	589.7	593.2	585.3
50°	*563.5*	561.0	561.5	559.5	556.0
52.5°	*527.8*	526.3	529.3	525.8	523.8
55°	*496.6*	491.6	492.1	488.6	489.6
57.5°	*460.9*	459.4	455.9	455.9	454.9
60°	*427.2*	421.7	421.7	419.7	418.8
62.5°	*386.0*	385.6	388.0	384.1	380.6
65°	*350.9*	350.4	348.4	345.4	343.9
67.5°	*313.7*	311.2	310.2	306.8	308.7
70°	*278.0*	274.5	273.6	269.6	270.1
72.5°	*239.9*	236.9	235.9	231.4	230.9
75°	*201.7*	200.2	198.2	196.2	193.8
77.5°	*163.5*	163.0	163.5	158.1	158.6
80°	*128.4*	127.9	125.9	122.9	123.4
82.5°	*92.2*	92.2	91.2	89.7	88.2
85°	*59.0*	59.0	58.0	55.5	55.5
87.5°	*26.8*	27.3	28.2	28.2	27.8
90°	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590650
CATALOG NUMBER: 22CGTX-25-B45-HCD

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.13	16.79	15.50	17.11	17.42	15.07	16.73	15.44	17.05	17.36
	3H	17.07	18.58	17.44	18.90	19.26	16.98	18.49	17.35	18.81	19.17
	4H	17.83	19.26	18.23	19.60	19.98	17.71	19.14	18.11	19.49	19.86
	6H	18.43	19.76	18.84	20.12	20.51	18.29	19.62	18.71	19.98	20.37
	8H	18.64	19.91	19.07	20.30	20.69	18.50	19.76	18.92	20.15	20.55
	12H	18.80	20.01	19.22	20.39	20.82	18.64	19.85	19.07	20.23	20.66
4H	2H	15.80	17.22	16.19	17.57	17.94	15.75	17.17	16.15	17.52	17.90
	3H	17.96	19.16	18.37	19.55	19.95	17.88	19.08	18.29	19.47	19.87
	4H	18.86	19.95	19.29	20.36	20.80	18.76	19.84	19.19	20.26	20.69
	6H	19.61	20.56	20.06	21.00	21.45	19.47	20.42	19.92	20.86	21.32
	8H	19.87	20.77	20.33	21.21	21.67	19.73	20.62	20.19	21.06	21.53
	12H	20.08	20.88	20.56	21.36	21.82	19.92	20.72	20.40	21.20	21.67
8H	4H	19.22	20.11	19.68	20.55	21.02	19.12	20.02	19.58	20.46	20.92
	6H	20.10	20.84	20.59	21.33	21.81	19.98	20.72	20.47	21.21	21.68
	8H	20.45	21.12	20.96	21.63	22.11	20.32	20.99	20.82	21.49	21.98
	12H	20.75	21.34	21.25	21.83	22.39	20.59	21.19	21.10	21.68	22.24
12H	4H	19.26	20.07	19.74	20.54	21.01	19.17	19.98	19.65	20.45	20.92
	6H	20.17	20.84	20.68	21.35	21.83	20.06	20.73	20.56	21.23	21.72
	8H	20.59	21.19	21.10	21.68	22.23	20.46	21.06	20.97	21.55	22.10

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-581-4-R2

Test Date: 01/21/2026

Luminaire Tested: 24CGTX-55-B45-HCD

Data in this report applies to families of products including 24CGTX-55HE

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-581-4-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-55-B45-HCD**
Description:	*THIS IS A REVISION OF REPORT SP1-2510-581-4-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 CGTX 5500 lumen with BioUp Boards with fixed CCT 4500K - Control Volatge at 3V

Spectral Parameters

CCT (K):	4541
CIE u':	0.2259
CIE v':	0.4759
Duv:	-0.0141
CIE x:	0.3541
CIE y:	0.3316
CIE z:	0.3143
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	622
Purity:	5.72732
Rf:	87.2
Rg:	96.7

CRI (Ra):	86.3
R1:	91.4
R2:	86.5
R3:	84.4
R4:	88.4
R5:	89.6
R6:	80.7
R7:	83.3
R8:	86.2
R9:	86.2
R10:	74.5
R11:	89.9
R12:	69.8
R13:	89.5
R14:	92.9
R15:	92.2



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.1

REPORT NUMBER: SP1-2510-581-4-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2510-581-4-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4541K
CIE x = 0.3541
CIE y = 0.3316
Duv = -0.0141

Point lies outside the range

REPORT NUMBER: SP1-2510-581-4-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	341	NR	620	392	NR	750	9	NR	880	0	NR
365	0	NR	495	298	NR	625	387	NR	755	7	NR	885	0	NR
370	0	NR	500	275	NR	630	1000	NR	760	6	NR	890	0	NR
375	1	NR	505	267	NR	635	584	NR	765	5	NR	895	0	NR
380	2	NR	510	272	NR	640	256	NR	770	5	NR	900	0	NR
385	2	NR	515	276	NR	645	254	NR	775	4	NR	905	0	NR
390	3	NR	520	281	NR	650	210	NR	780	3	NR	910	0	NR
395	5	NR	525	284	NR	655	179	NR	785	3	NR	915	0	NR
400	6	NR	530	289	NR	660	152	NR	790	2	NR	920	0	NR
405	8	NR	535	296	NR	665	130	NR	795	2	NR	925	0	NR
410	10	NR	540	301	NR	670	117	NR	800	2	NR	930	0	NR
415	16	NR	545	312	NR	675	97	NR	805	2	NR	935	0	NR
420	28	NR	550	323	NR	680	83	NR	810	1	NR	940	0	NR
425	51	NR	555	335	NR	685	71	NR	815	1	NR	945	0	NR
430	89	NR	560	352	NR	690	61	NR	820	1	NR	950	0	NR
435	153	NR	565	368	NR	695	52	NR	825	1	NR	955	0	NR
440	254	NR	570	384	NR	700	44	NR	830	1	NR	960	0	NR
445	443	NR	575	398	NR	705	38	NR	835	1	NR	965	0	NR
450	556	NR	580	410	NR	710	32	NR	840	1	NR	970	0	NR
455	426	NR	585	419	NR	715	27	NR	845	1	NR	975	0	NR
460	355	NR	590	424	NR	720	23	NR	850	0	NR	980	0	NR
465	444	NR	595	424	NR	725	19	NR	855	0	NR	985	0	NR
470	579	NR	600	422	NR	730	17	NR	860	0	NR	990	0	NR
475	615	NR	605	418	NR	735	14	NR	865	0	NR	995	0	NR
480	510	NR	610	433	NR	740	12	NR	870	0	NR	1000	0	NR
485	398	NR	615	428	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-4-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 2.17**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	341	NR	620	392	NR	750	9	NR	880	0	NR
365	0	NR	495	298	NR	625	387	NR	755	7	NR	885	0	NR
370	0	NR	500	275	NR	630	1000	NR	760	6	NR	890	0	NR
375	1	NR	505	267	NR	635	584	NR	765	5	NR	895	0	NR
380	2	NR	510	272	NR	640	256	NR	770	5	NR	900	0	NR
385	2	NR	515	276	NR	645	254	NR	775	4	NR	905	0	NR
390	3	NR	520	281	NR	650	210	NR	780	3	NR	910	0	NR
395	5	NR	525	284	NR	655	179	NR	785	3	NR	915	0	NR
400	6	NR	530	289	NR	660	152	NR	790	2	NR	920	0	NR
405	8	NR	535	296	NR	665	130	NR	795	2	NR	925	0	NR
410	10	NR	540	301	NR	670	117	NR	800	2	NR	930	0	NR
415	16	NR	545	312	NR	675	97	NR	805	2	NR	935	0	NR
420	28	NR	550	323	NR	680	83	NR	810	1	NR	940	0	NR
425	51	NR	555	335	NR	685	71	NR	815	1	NR	945	0	NR
430	89	NR	560	352	NR	690	61	NR	820	1	NR	950	0	NR
435	153	NR	565	368	NR	695	52	NR	825	1	NR	955	0	NR
440	254	NR	570	384	NR	700	44	NR	830	1	NR	960	0	NR
445	443	NR	575	398	NR	705	38	NR	835	1	NR	965	0	NR
450	556	NR	580	410	NR	710	32	NR	840	1	NR	970	0	NR
455	426	NR	585	419	NR	715	27	NR	845	1	NR	975	0	NR
460	355	NR	590	424	NR	720	23	NR	850	0	NR	980	0	NR
465	444	NR	595	424	NR	725	19	NR	855	0	NR	985	0	NR
470	579	NR	600	422	NR	730	17	NR	860	0	NR	990	0	NR
475	615	NR	605	418	NR	735	14	NR	865	0	NR	995	0	NR
480	510	NR	610	433	NR	740	12	NR	870	0	NR	1000	0	NR
485	398	NR	615	428	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-4-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 5.01**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	341	NR	620	392	NR	750	9	NR	880	0	NR
365	0	NR	495	298	NR	625	387	NR	755	7	NR	885	0	NR
370	0	NR	500	275	NR	630	1000	NR	760	6	NR	890	0	NR
375	1	NR	505	267	NR	635	584	NR	765	5	NR	895	0	NR
380	2	NR	510	272	NR	640	256	NR	770	5	NR	900	0	NR
385	2	NR	515	276	NR	645	254	NR	775	4	NR	905	0	NR
390	3	NR	520	281	NR	650	210	NR	780	3	NR	910	0	NR
395	5	NR	525	284	NR	655	179	NR	785	3	NR	915	0	NR
400	6	NR	530	289	NR	660	152	NR	790	2	NR	920	0	NR
405	8	NR	535	296	NR	665	130	NR	795	2	NR	925	0	NR
410	10	NR	540	301	NR	670	117	NR	800	2	NR	930	0	NR
415	16	NR	545	312	NR	675	97	NR	805	2	NR	935	0	NR
420	28	NR	550	323	NR	680	83	NR	810	1	NR	940	0	NR
425	51	NR	555	335	NR	685	71	NR	815	1	NR	945	0	NR
430	89	NR	560	352	NR	690	61	NR	820	1	NR	950	0	NR
435	153	NR	565	368	NR	695	52	NR	825	1	NR	955	0	NR
440	254	NR	570	384	NR	700	44	NR	830	1	NR	960	0	NR
445	443	NR	575	398	NR	705	38	NR	835	1	NR	965	0	NR
450	556	NR	580	410	NR	710	32	NR	840	1	NR	970	0	NR
455	426	NR	585	419	NR	715	27	NR	845	1	NR	975	0	NR
460	355	NR	590	424	NR	720	23	NR	850	0	NR	980	0	NR
465	444	NR	595	424	NR	725	19	NR	855	0	NR	985	0	NR
470	579	NR	600	422	NR	730	17	NR	860	0	NR	990	0	NR
475	615	NR	605	418	NR	735	14	NR	865	0	NR	995	0	NR
480	510	NR	610	433	NR	740	12	NR	870	0	NR	1000	0	NR
485	398	NR	615	428	NR	745	10	NR	875	0	NR			


REPORT NUMBER: SP1-2510-581-4-R2

TM-30-18


Summary


R_f = 87.2
R_g = 96.7
CIE R_a = 86.3
R_9 = 86.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-581-4-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 93	CES51 = 87	CES76 = 87
CES02 = 62	CES27 = 85	CES52 = 89	CES77 = 80
CES03 = 31	CES28 = 94	CES53 = 82	CES78 = 87
CES04 = 69	CES29 = 85	CES54 = 85	CES79 = 83
CES05 = 49	CES30 = 80	CES55 = 82	CES80 = 83
CES06 = 50	CES31 = 86	CES56 = 80	CES81 = 66
CES07 = 42	CES32 = 94	CES57 = 78	CES82 = 93
CES08 = 41	CES33 = 86	CES58 = 78	CES83 = 88
CES09 = 29	CES34 = 92	CES59 = 91	CES84 = 96
CES10 = 75	CES35 = 95	CES60 = 88	CES85 = 78
CES11 = 57	CES36 = 77	CES61 = 87	CES86 = 74
CES12 = 63	CES37 = 95	CES62 = 79	CES87 = 90
CES13 = 43	CES38 = 75	CES63 = 92	CES88 = 90
CES14 = 74	CES39 = 93	CES64 = 82	CES89 = 84
CES15 = 71	CES40 = 89	CES65 = 89	CES90 = 87
CES16 = 47	CES41 = 90	CES66 = 84	CES91 = 72
CES17 = 49	CES42 = 88	CES67 = 84	CES92 = 77
CES18 = 56	CES43 = 86	CES68 = 87	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 78
CES20 = 66	CES45 = 89	CES70 = 89	CES95 = 86
CES21 = 85	CES46 = 89	CES71 = 85	CES96 = 94
CES22 = 78	CES47 = 84	CES72 = 94	CES97 = 85
CES23 = 91	CES48 = 79	CES73 = 87	CES98 = 85
CES24 = 90	CES49 = 90	CES74 = 88	CES99 = 87
CES25 = 71	CES50 = 87	CES75 = 86	





REPORT NUMBER: SP1-2510-581-4-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-581-4-R2

TM-30-18

Measure Comparisons





(END OF REPORT)