

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED3010-12-CS-DIFF**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-36)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED3010-12-CS-DIFF
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD SILVER, DIFFUSED LENS
Light Source: (1) SORAA 3000K 95 CRI 10° NSP LED
SM16-07-10D-930-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004


Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	206.2 lumens	Max Intensity:	824.4 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	27.5 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	22.6°H x 22.6°V	Field Angle (10%):	47.7°H x 47.7°V
Beam Lumens:	70.7 lumens	Field Lumens:	149.4 lumens
Beam Efficiency:	34.3%	Field Efficiency:	72.5%
Input Watts (W):	7.5		
Input Voltage (V):	NR		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF


Iso-Candela Plot



REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)


CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

Lumen Table



REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF


Luminous Intensity Polar Plot





REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

Luminous Intensity Plot



Beam:
H Angle: 22.6°
V Angle: 22.6°
Lumens: 70.7
Efficiency: 34.3%

Field:
H Angle: 47.7°
V Angle: 47.7°
Lumens: 149.4
Efficiency: 72.5%

Spill:
Lumens: 56.8
Efficiency: 27.5%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 0-Deg

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

FIELD
BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	1
22.5°	0	0	0	0	0	0	0	0	0	0	1
21.25°	0	0	0	0	0	0	0	0	0	0	1
20°	0	0	0	0	0	0	0	0	0	0	1
18.75°	0	0	0	0	0	0	0	0	0	0	1
17.5°	0	0	0	0	0	0	0	0	0	0	1
16.25°	0	0	0	0	0	0	0	0	0	0	1
15°	0	0	0	0	0	0	0	0	0	0	1
13.75°	0	0	0	0	0	0	0	0	0	0	1
12.5°	0	0	0	0	0	0	0	0	0	0	1
11.25°	0	0	0	0	0	0	0	0	0	0	1
10°	0	0	0	0	0	0	0	0	0	0	1
8.75°	0	0	0	0	0	0	0	0	0	0	1
7.5°	0	0	0	0	0	0	0	0	0	0	1
6.25°	0	0	0	0	0	0	0	0	0	0	1
5°	0	0	0	0	0	0	0	0	0	0	1
3.75°	0	0	0	0	0	0	0	0	0	0	1
2.5°	0	0	0	0	0	0	0	0	0	0	1
1.25°	0	0	0	0	0	0	0	0	0	0	1
0°	0	0	0	0	0	0	0	0	0	0	1
-1.25°	0	0	0	0	0	0	0	0	0	0	1
-2.5°	0	0	0	0	0	0	0	0	0	0	1
-3.75°	0	0	0	0	0	0	0	0	0	0	1
-5°	0	0	0	0	0	0	0	0	0	0	1
-6.25°	0	0	0	0	0	0	0	0	0	0	1
-7.5°	0	0	0	0	0	0	0	0	0	0	1
-8.75°	0	0	0	0	0	0	0	0	0	0	1
-10°	0	0	0	0	0	0	0	0	0	0	1
-11.25°	0	0	0	0	0	0	0	0	0	0	1
-12.5°	0	0	0	0	0	0	0	0	0	0	1
-13.75°	0	0	0	0	0	0	0	0	0	0	1
-15°	0	0	0	0	0	0	0	0	0	0	1
-16.25°	0	0	0	0	0	0	0	0	0	0	1
-17.5°	0	0	0	0	0	0	0	0	0	0	1
-18.75°	0	0	0	0	0	0	0	0	0	0	1
-20°	0	0	0	0	0	0	0	0	0	0	1
-21.25°	0	0	0	0	0	0	0	0	0	0	1

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	1
-23.75°	0	0	0	0	0	0	0	0	0	0	1
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	1
61.25°	0	0	0	0	0	0	0	0	0	1	1
60°	0	0	0	0	0	0	0	0	1	1	1
58.75°	0	0	0	0	0	0	0	1	1	1	1
57.5°	0	0	0	0	0	0	0	1	1	1	1
56.25°	0	0	0	0	0	0	1	1	1	1	1
55°	0	0	0	0	0	0	1	1	1	1	1
53.75°	0	0	0	0	0	1	1	1	1	1	1
52.5°	0	0	0	0	0	1	1	1	1	1	1
51.25°	0	0	0	0	1	1	1	1	1	1	1
50°	0	0	0	0	1	1	1	1	1	1	1
48.75°	0	0	0	1	1	1	1	1	1	1	1
47.5°	0	0	0	1	1	1	1	1	1	1	1
46.25°	0	0	0	1	1	1	1	1	1	1	1
45°	0	0	1	1	1	1	1	1	1	1	1
43.75°	0	0	1	1	1	1	1	1	1	1	1
42.5°	0	0	1	1	1	1	1	1	1	1	1
41.25°	0	0	1	1	1	1	1	1	1	1	1
40°	0	1	1	1	1	1	1	1	1	1	1
38.75°	0	1	1	1	1	1	1	1	1	1	1
37.5°	0	1	1	1	1	1	1	1	1	1	1
36.25°	0	1	1	1	1	1	1	1	1	1	1
35°	0	1	1	1	1	1	1	1	1	1	1

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	1	1	1	1	1	1	1
32.5°	1	1	1	1	1	1	1	1	1	1	2
31.25°	1	1	1	1	1	1	1	1	1	1	2
30°	1	1	1	1	1	1	1	1	1	1	2
28.75°	1	1	1	1	1	1	1	1	1	2	2
27.5°	1	1	1	1	1	1	1	1	1	2	2
26.25°	1	1	1	1	1	1	1	1	1	2	2
25°	1	1	1	1	1	1	1	1	1	2	2
23.75°	1	1	1	1	1	1	1	1	1	2	2
22.5°	1	1	1	1	1	1	1	1	2	2	2
21.25°	1	1	1	1	1	1	1	1	2	2	2
20°	1	1	1	1	1	1	1	1	2	2	2
18.75°	1	1	1	1	1	1	1	1	2	2	2
17.5°	1	1	1	1	1	1	1	1	2	2	2
16.25°	1	1	1	1	1	1	1	1	2	2	2
15°	1	1	1	1	1	1	1	2	2	2	2
13.75°	1	1	1	1	1	1	1	2	2	2	2
12.5°	1	1	1	1	1	1	1	2	2	2	2
11.25°	1	1	1	1	1	1	1	2	2	2	2
10°	1	1	1	1	1	1	1	2	2	2	2
8.75°	1	1	1	1	1	1	1	2	2	2	2
7.5°	1	1	1	1	1	1	1	2	2	2	2
6.25°	1	1	1	1	1	1	1	2	2	2	2
5°	1	1	1	1	1	1	1	2	2	2	2
3.75°	1	1	1	1	1	1	1	2	2	2	2
2.5°	1	1	1	1	1	1	1	2	2	2	2
1.25°	1	1	1	1	1	1	1	2	2	2	2
0°	1	1	1	1	1	1	1	2	2	2	2
-1.25°	1	1	1	1	1	1	1	2	2	2	2
-2.5°	1	1	1	1	1	1	1	2	2	2	2
-3.75°	1	1	1	1	1	1	1	2	2	2	2
-5°	1	1	1	1	1	1	1	2	2	2	2
-6.25°	1	1	1	1	1	1	1	2	2	2	2
-7.5°	1	1	1	1	1	1	1	2	2	2	2
-8.75°	1	1	1	1	1	1	1	2	2	2	2
-10°	1	1	1	1	1	1	1	2	2	2	2
-11.25°	1	1	1	1	1	1	1	2	2	2	2
-12.5°	1	1	1	1	1	1	1	2	2	2	2
-13.75°	1	1	1	1	1	1	1	2	2	2	2
-15°	1	1	1	1	1	1	1	2	2	2	2
-16.25°	1	1	1	1	1	1	1	1	2	2	2
-17.5°	1	1	1	1	1	1	1	1	2	2	2
-18.75°	1	1	1	1	1	1	1	1	2	2	2
-20°	1	1	1	1	1	1	1	1	2	2	2
-21.25°	1	1	1	1	1	1	1	1	2	2	2

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	1	1	1	1	1	1	2	2	2
-23.75°	1	1	1	1	1	1	1	1	1	2	2
-25°	1	1	1	1	1	1	1	1	1	2	2
-26.25°	1	1	1	1	1	1	1	1	1	2	2
-27.5°	1	1	1	1	1	1	1	1	1	2	2
-28.75°	1	1	1	1	1	1	1	1	1	2	2
-30°	1	1	1	1	1	1	1	1	1	1	2
-31.25°	1	1	1	1	1	1	1	1	1	1	2
-32.5°	1	1	1	1	1	1	1	1	1	1	2
-33.75°	1	1	1	1	1	1	1	1	1	1	1
-35°	0	1	1	1	1	1	1	1	1	1	1
-36.25°	0	1	1	1	1	1	1	1	1	1	1
-37.5°	0	1	1	1	1	1	1	1	1	1	1
-38.75°	0	1	1	1	1	1	1	1	1	1	1
-40°	0	1	1	1	1	1	1	1	1	1	1
-41.25°	0	0	1	1	1	1	1	1	1	1	1
-42.5°	0	0	1	1	1	1	1	1	1	1	1
-43.75°	0	0	1	1	1	1	1	1	1	1	1
-45°	0	0	1	1	1	1	1	1	1	1	1
-46.25°	0	0	0	1	1	1	1	1	1	1	1
-47.5°	0	0	0	1	1	1	1	1	1	1	1
-48.75°	0	0	0	1	1	1	1	1	1	1	1
-50°	0	0	0	0	1	1	1	1	1	1	1
-51.25°	0	0	0	0	1	1	1	1	1	1	1
-52.5°	0	0	0	0	0	1	1	1	1	1	1
-53.75°	0	0	0	0	0	1	1	1	1	1	1
-55°	0	0	0	0	0	0	1	1	1	1	1
-56.25°	0	0	0	0	0	0	1	1	1	1	1
-57.5°	0	0	0	0	0	0	0	1	1	1	1
-58.75°	0	0	0	0	0	0	0	1	1	1	1
-60°	0	0	0	0	0	0	0	0	1	1	1
-61.25°	0	0	0	0	0	0	0	0	0	1	1
-62.5°	0	0	0	0	0	0	0	0	0	0	1
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	1	1
70°	0	0	0	0	0	0	0	1	1	1	1
68.75°	0	0	0	0	0	1	1	1	1	1	1
67.5°	0	0	0	1	1	1	1	1	1	1	1
66.25°	0	0	1	1	1	1	1	1	1	1	1
65°	0	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	2	2
52.5°	1	1	1	1	1	1	1	1	2	2	2
51.25°	1	1	1	1	1	1	1	2	2	2	2
50°	1	1	1	1	1	1	1	2	2	2	2
48.75°	1	1	1	1	1	1	2	2	2	2	2
47.5°	1	1	1	1	1	2	2	2	2	2	2
46.25°	1	1	1	1	2	2	2	2	2	2	2
45°	1	1	1	1	2	2	2	2	2	2	3
43.75°	1	1	1	2	2	2	2	2	2	2	3
42.5°	1	1	1	2	2	2	2	2	2	3	3
41.25°	1	1	2	2	2	2	2	2	3	3	3
40°	1	1	2	2	2	2	2	2	3	3	3
38.75°	1	2	2	2	2	2	2	3	3	3	4
37.5°	1	2	2	2	2	2	3	3	3	3	4
36.25°	2	2	2	2	2	2	3	3	3	4	4
35°	2	2	2	2	2	3	3	3	3	4	5

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	2	2	2	2	2	3	3	3	4	4	5
32.5°	2	2	2	2	3	3	3	3	4	5	6
31.25°	2	2	2	2	3	3	3	4	4	5	6
30°	2	2	2	2	3	3	3	4	5	6	6
28.75°	2	2	2	3	3	3	4	4	5	6	7
27.5°	2	2	2	3	3	3	4	5	5	6	7
26.25°	2	2	2	3	3	3	4	5	6	6	7
25°	2	2	3	3	3	4	4	5	6	7	8
23.75°	2	2	3	3	3	4	5	5	6	7	8
22.5°	2	2	3	3	3	4	5	6	7	7	8
21.25°	2	2	3	3	4	4	5	6	7	8	8
20°	2	2	3	3	4	5	5	6	7	8	9
18.75°	2	3	3	3	4	5	6	6	7	8	9
17.5°	2	3	3	3	4	5	6	7	7	8	9
16.25°	2	3	3	3	4	5	6	7	8	8	9
15°	2	3	3	4	4	5	6	7	8	9	9
13.75°	2	3	3	4	5	5	6	7	8	9	10
12.5°	2	3	3	4	5	6	6	7	8	9	10
11.25°	2	3	3	4	5	6	7	7	8	9	10
10°	3	3	3	4	5	6	7	8	8	9	10
8.75°	3	3	3	4	5	6	7	8	9	9	10
7.5°	3	3	3	4	5	6	7	8	9	9	10
6.25°	3	3	3	4	5	6	7	8	9	10	10
5°	3	3	3	4	5	6	7	8	9	10	10
3.75°	3	3	3	4	5	6	7	8	9	10	11
2.5°	3	3	3	4	5	6	7	8	9	10	11
1.25°	3	3	3	4	5	6	7	8	9	10	11
0°	3	3	4	4	5	6	7	8	9	10	11
-1.25°	3	3	3	4	5	6	7	8	9	10	11
-2.5°	3	3	3	4	5	6	7	8	9	10	11
-3.75°	3	3	3	4	5	6	7	8	9	10	11
-5°	3	3	3	4	5	6	7	8	9	10	10
-6.25°	3	3	3	4	5	6	7	8	9	10	10
-7.5°	3	3	3	4	5	6	7	8	9	9	10
-8.75°	3	3	3	4	5	6	7	8	9	9	10
-10°	3	3	3	4	5	6	7	8	8	9	10
-11.25°	2	3	3	4	5	6	7	7	8	9	10
-12.5°	2	3	3	4	5	6	6	7	8	9	10
-13.75°	2	3	3	4	5	5	6	7	8	9	10
-15°	2	3	3	4	4	5	6	7	8	9	9
-16.25°	2	3	3	3	4	5	6	7	8	8	9
-17.5°	2	3	3	3	4	5	6	7	7	8	9
-18.75°	2	3	3	3	4	5	6	6	7	8	9
-20°	2	2	3	3	4	5	5	6	7	8	9
-21.25°	2	2	3	3	4	4	5	6	7	8	8

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	2	3	3	3	4	5	6	7	7	8
-23.75°	2	2	3	3	3	4	5	5	6	7	8
-25°	2	2	3	3	3	4	4	5	6	7	8
-26.25°	2	2	2	3	3	3	4	5	6	6	7
-27.5°	2	2	2	3	3	3	4	5	5	6	7
-28.75°	2	2	2	3	3	3	4	4	5	6	7
-30°	2	2	2	2	3	3	3	4	5	6	6
-31.25°	2	2	2	2	3	3	3	4	4	5	6
-32.5°	2	2	2	2	3	3	3	3	4	5	6
-33.75°	2	2	2	2	2	3	3	3	4	4	5
-35°	2	2	2	2	2	3	3	3	3	4	5
-36.25°	2	2	2	2	2	2	3	3	3	4	4
-37.5°	1	2	2	2	2	2	3	3	3	3	4
-38.75°	1	2	2	2	2	2	2	3	3	3	4
-40°	1	1	2	2	2	2	2	2	3	3	3
-41.25°	1	1	2	2	2	2	2	2	3	3	3
-42.5°	1	1	1	2	2	2	2	2	2	3	3
-43.75°	1	1	1	2	2	2	2	2	2	2	3
-45°	1	1	1	1	2	2	2	2	2	2	3
-46.25°	1	1	1	1	2	2	2	2	2	2	2
-47.5°	1	1	1	1	1	2	2	2	2	2	2
-48.75°	1	1	1	1	1	1	2	2	2	2	2
-50°	1	1	1	1	1	1	1	2	2	2	2
-51.25°	1	1	1	1	1	1	1	2	2	2	2
-52.5°	1	1	1	1	1	1	1	1	2	2	2
-53.75°	1	1	1	1	1	1	1	1	1	2	2
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	0	1	1	1	1	1	1	1	1	1	1
-66.25°	0	0	1	1	1	1	1	1	1	1	1
-67.5°	0	0	0	1	1	1	1	1	1	1	1
-68.75°	0	0	0	0	0	1	1	1	1	1	1
-70°	0	0	0	0	0	0	0	1	1	1	1
-71.25°	0	0	0	0	0	0	0	0	0	1	1
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	1	1	1	1
73.75°	0	0	0	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	2
61.25°	1	1	1	1	1	1	1	1	2	2	2
60°	1	1	1	1	1	1	2	2	2	2	2
58.75°	1	1	1	1	2	2	2	2	2	2	2
57.5°	1	1	2	2	2	2	2	2	2	2	2
56.25°	1	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	3	3
53.75°	2	2	2	2	2	2	2	2	3	3	3
52.5°	2	2	2	2	2	2	3	3	3	3	3
51.25°	2	2	2	2	2	3	3	3	3	3	4
50°	2	2	2	3	3	3	3	3	4	4	4
48.75°	2	2	3	3	3	3	3	4	4	5	5
47.5°	2	3	3	3	3	3	4	4	5	5	6
46.25°	3	3	3	3	3	4	4	5	5	6	6
45°	3	3	3	4	4	5	5	6	6	6	7
43.75°	3	3	3	4	5	5	6	6	7	7	8
42.5°	3	3	4	5	5	6	6	7	7	8	8
41.25°	3	4	4	5	6	6	7	7	8	8	9
40°	4	4	5	6	6	7	7	8	8	9	9
38.75°	4	5	5	6	7	7	8	8	9	9	10
37.5°	5	5	6	6	7	8	8	9	9	10	10
36.25°	5	6	6	7	8	8	9	9	10	10	11
35°	5	6	7	7	8	9	9	10	10	11	12

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	6	7	7	8	8	9	10	10	11	12	13
32.5°	6	7	8	8	9	10	10	11	12	13	14
31.25°	7	7	8	9	9	10	11	12	13	13	14
30°	7	8	8	9	10	10	11	12	13	14	15
28.75°	7	8	9	9	10	11	12	13	14	14	15
27.5°	8	8	9	10	10	12	13	14	14	15	16
26.25°	8	9	9	10	11	12	13	14	15	15	16
25°	8	9	10	11	12	13	14	14	15	16	17
23.75°	9	9	10	11	12	13	14	15	16	17	18
22.5°	9	10	10	11	13	14	14	15	16	17	18
21.25°	9	10	11	12	13	14	15	16	17	18	19
20°	9	10	11	12	13	14	15	16	17	18	20
18.75°	10	10	12	13	14	15	16	17	18	19	20
17.5°	10	11	12	13	14	15	16	17	18	20	21
16.25°	10	11	12	13	14	15	16	18	19	20	21
15°	10	11	13	14	15	16	17	18	19	20	22
13.75°	10	12	13	14	15	16	17	18	20	21	23
12.5°	11	12	13	14	15	16	17	19	20	21	23
11.25°	11	12	13	14	15	16	18	19	20	22	24
10°	11	12	14	14	15	17	18	19	21	22	24
8.75°	11	13	14	15	16	17	18	20	21	23	25
7.5°	11	13	14	15	16	17	18	20	21	23	25
6.25°	12	13	14	15	16	17	19	20	22	23	25
5°	12	13	14	15	16	17	19	20	22	24	26
3.75°	12	13	14	15	16	18	19	20	22	24	26
2.5°	12	13	14	15	16	18	19	20	22	24	26
1.25°	12	13	14	15	16	18	19	20	22	24	26
0°	12	13	14	15	16	18	19	20	22	24	26
-1.25°	12	13	14	15	16	18	19	20	22	24	26
-2.5°	12	13	14	15	16	18	19	20	22	24	26
-3.75°	12	13	14	15	16	18	19	20	22	24	26
-5°	12	13	14	15	16	17	19	20	22	24	26
-6.25°	12	13	14	15	16	17	19	20	22	23	25
-7.5°	11	13	14	15	16	17	18	20	21	23	25
-8.75°	11	13	14	15	16	17	18	20	21	23	25
-10°	11	12	14	14	15	17	18	19	21	22	24
-11.25°	11	12	13	14	15	16	18	19	20	22	24
-12.5°	11	12	13	14	15	16	17	19	20	21	23
-13.75°	10	12	13	14	15	16	17	18	20	21	23
-15°	10	11	13	14	15	16	17	18	19	20	22
-16.25°	10	11	12	13	14	15	16	18	19	20	21
-17.5°	10	11	12	13	14	15	16	17	18	20	21
-18.75°	10	10	12	13	14	15	16	17	18	19	20
-20°	9	10	11	12	13	14	15	16	17	18	20
-21.25°	9	10	11	12	13	14	15	16	17	18	19

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	9	10	10	11	13	14	14	15	16	17	18
-23.75°	9	9	10	11	12	13	14	15	16	17	18
-25°	8	9	10	11	12	13	14	14	15	16	17
-26.25°	8	9	9	10	11	12	13	14	15	15	16
-27.5°	8	8	9	10	10	12	13	14	14	15	16
-28.75°	7	8	9	9	10	11	12	13	14	14	15
-30°	7	8	8	9	10	10	11	12	13	14	15
-31.25°	7	7	8	9	9	10	11	12	13	13	14
-32.5°	6	7	8	8	9	10	10	11	12	13	14
-33.75°	6	7	7	8	8	9	10	10	11	12	13
-35°	5	6	7	7	8	9	9	10	10	11	12
-36.25°	5	6	6	7	8	8	9	9	10	10	11
-37.5°	5	5	6	6	7	8	8	9	9	10	10
-38.75°	4	5	5	6	7	7	8	8	9	9	10
-40°	4	4	5	6	6	7	7	8	8	9	9
-41.25°	3	4	4	5	6	6	7	7	8	8	9
-42.5°	3	3	4	5	5	6	6	7	7	8	8
-43.75°	3	3	3	4	5	5	6	6	7	7	8
-45°	3	3	3	4	4	5	5	6	6	6	7
-46.25°	3	3	3	3	3	4	4	5	5	6	6
-47.5°	2	3	3	3	3	3	4	4	5	5	6
-48.75°	2	2	3	3	3	3	3	4	4	5	5
-50°	2	2	2	3	3	3	3	3	4	4	4
-51.25°	2	2	2	2	2	3	3	3	3	3	4
-52.5°	2	2	2	2	2	2	3	3	3	3	3
-53.75°	2	2	2	2	2	2	2	2	3	3	3
-55°	2	2	2	2	2	2	2	2	2	3	3
-56.25°	1	2	2	2	2	2	2	2	2	2	2
-57.5°	1	1	2	2	2	2	2	2	2	2	2
-58.75°	1	1	1	1	2	2	2	2	2	2	2
-60°	1	1	1	1	1	1	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	2	2	2
-62.5°	1	1	1	1	1	1	1	1	1	1	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	1	1	1	1	1	1	1	1
-75°	0	0	0	0	0	0	0	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	1	1
76.25°	0	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	2
65°	1	1	1	1	1	2	2	2	2	2	2
63.75°	1	1	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	3	3	3
58.75°	2	2	2	2	2	3	3	3	3	3	3
57.5°	2	2	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	4	4	4
55°	3	3	3	3	3	4	4	4	4	5	5
53.75°	3	3	3	4	4	4	5	5	5	5	6
52.5°	3	4	4	4	5	5	5	6	6	6	7
51.25°	4	4	5	5	6	6	6	6	7	7	7
50°	5	5	6	6	6	7	7	7	8	8	8
48.75°	5	6	6	7	7	7	8	8	8	9	9
47.5°	6	7	7	7	8	8	8	9	9	9	10
46.25°	7	7	8	8	8	9	9	9	10	10	10
45°	7	8	8	9	9	9	10	10	11	11	11
43.75°	8	8	9	9	10	10	10	11	12	12	13
42.5°	9	9	10	10	10	11	12	12	13	13	14
41.25°	9	10	10	11	11	12	13	13	14	14	14
40°	10	10	11	12	12	13	14	14	14	15	15
38.75°	10	11	12	13	13	14	14	15	15	16	16
37.5°	11	12	13	13	14	14	15	15	16	17	17
36.25°	12	13	14	14	15	15	16	16	17	18	18
35°	13	14	14	15	15	16	17	17	18	19	20

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	14	14	15	15	16	17	18	18	19	20	21
32.5°	14	15	15	16	17	18	19	19	20	21	22
31.25°	15	15	16	17	18	19	20	20	22	22	23
30°	15	16	17	18	19	20	21	22	23	24	25
28.75°	16	17	18	19	20	21	22	23	24	25	27
27.5°	17	18	19	20	21	22	23	24	26	27	28
26.25°	17	18	19	20	22	23	24	26	27	29	30
25°	18	19	20	22	23	24	26	27	29	31	32
23.75°	19	20	21	22	24	25	27	29	31	32	35
22.5°	20	21	22	23	25	27	28	30	32	35	38
21.25°	20	22	23	24	26	28	30	32	34	37	41
20°	21	22	24	26	27	29	31	34	37	40	44
18.75°	22	23	25	27	29	31	33	36	39	43	47
17.5°	22	24	26	28	30	32	35	38	42	46	50
16.25°	23	25	27	29	31	33	37	41	45	49	53
15°	24	26	28	30	32	35	39	43	47	52	58
13.75°	24	26	28	31	33	37	41	45	50	55	63
12.5°	25	27	29	32	35	39	43	47	52	59	67
11.25°	26	28	30	33	36	40	45	49	55	63	71
10°	26	28	31	33	37	42	46	51	58	66	76
8.75°	27	29	32	34	39	43	48	53	61	69	80
7.5°	27	30	32	35	40	44	49	55	64	72	84
6.25°	28	30	33	36	41	45	50	57	66	76	88
5°	28	30	33	37	41	46	51	59	68	78	91
3.75°	28	31	33	37	42	47	52	60	69	81	93
2.5°	28	31	34	38	42	47	53	61	70	82	94
1.25°	28	31	34	38	43	48	53	62	71	83	95
0°	28	31	34	38	43	48	53	62	71	83	96
-1.25°	28	31	34	38	43	48	53	62	71	83	95
-2.5°	28	31	34	38	42	47	53	61	70	82	94
-3.75°	28	31	33	37	42	47	52	60	69	81	93
-5°	28	30	33	37	41	46	51	59	68	78	91
-6.25°	28	30	33	36	41	45	50	57	66	76	88
-7.5°	27	30	32	35	40	44	49	55	64	72	84
-8.75°	27	29	32	34	39	43	48	53	61	69	80
-10°	26	28	31	33	37	42	46	51	58	66	76
-11.25°	26	28	30	33	36	40	45	49	55	63	71
-12.5°	25	27	29	32	35	39	43	47	52	59	67
-13.75°	24	26	28	31	33	37	41	45	50	55	63
-15°	24	26	28	30	32	35	39	43	47	52	58
-16.25°	23	25	27	29	31	33	37	41	45	49	53
-17.5°	22	24	26	28	30	32	35	38	42	46	50
-18.75°	22	23	25	27	29	31	33	36	39	43	47
-20°	21	22	24	26	27	29	31	34	37	40	44
-21.25°	20	22	23	24	26	28	30	32	34	37	41

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	20	21	22	23	25	27	28	30	32	35	38
-23.75°	19	20	21	22	24	25	27	29	31	32	35
-25°	18	19	20	22	23	24	26	27	29	31	32
-26.25°	17	18	19	20	22	23	24	26	27	29	30
-27.5°	17	18	19	20	21	22	23	24	26	27	28
-28.75°	16	17	18	19	20	21	22	23	24	25	27
-30°	15	16	17	18	19	20	21	22	23	24	25
-31.25°	15	15	16	17	18	19	20	20	22	22	23
-32.5°	14	15	15	16	17	18	19	19	20	21	22
-33.75°	14	14	15	15	16	17	18	18	19	20	21
-35°	13	14	14	15	15	16	17	17	18	19	20
-36.25°	12	13	14	14	15	15	16	16	17	18	18
-37.5°	11	12	13	13	14	14	15	15	16	17	17
-38.75°	10	11	12	13	13	14	14	15	15	16	16
-40°	10	10	11	12	12	13	14	14	14	15	15
-41.25°	9	10	10	11	11	12	13	13	14	14	14
-42.5°	9	9	10	10	10	11	12	12	13	13	14
-43.75°	8	8	9	9	10	10	10	11	12	12	13
-45°	7	8	8	9	9	9	10	10	11	11	11
-46.25°	7	7	8	8	8	9	9	9	10	10	10
-47.5°	6	7	7	7	8	8	8	9	9	9	10
-48.75°	5	6	6	7	7	7	8	8	8	9	9
-50°	5	5	6	6	6	7	7	7	8	8	8
-51.25°	4	4	5	5	6	6	6	6	7	7	7
-52.5°	3	4	4	4	5	5	5	6	6	6	7
-53.75°	3	3	3	4	4	4	5	5	5	5	6
-55°	3	3	3	3	3	4	4	4	4	5	5
-56.25°	3	3	3	3	3	3	3	3	4	4	4
-57.5°	2	2	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	3	3	3	3	3	3
-60°	2	2	2	2	2	2	2	2	3	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	1	2	2	2	2	2	2	2	2	2
-65°	1	1	1	1	1	2	2	2	2	2	2
-66.25°	1	1	1	1	1	1	1	1	1	1	2
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	0	0	0	0	0	1	1

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	3	3
61.25°	2	2	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	3	3	3	4	4	4	4	4	4
57.5°	4	4	4	4	4	4	5	5	5	5	5
56.25°	4	5	5	5	5	5	5	6	6	6	6
55°	5	5	6	6	6	6	6	6	7	7	7
53.75°	6	6	6	7	7	7	7	7	7	8	8
52.5°	7	7	7	7	8	8	8	8	8	8	9
51.25°	8	8	8	8	8	9	9	9	9	9	9
50°	8	9	9	9	9	9	10	10	10	10	10
48.75°	9	9	10	10	10	10	10	11	11	11	11
47.5°	10	10	10	11	11	11	12	12	12	12	13
46.25°	11	11	12	12	12	13	13	13	13	14	14
45°	12	12	13	13	13	14	14	14	14	14	15
43.75°	13	13	14	14	14	15	15	15	15	15	16
42.5°	14	14	15	15	15	16	16	16	16	17	17
41.25°	15	15	16	16	16	17	17	17	18	18	18
40°	16	16	17	17	18	18	18	19	19	19	20
38.75°	17	17	18	18	19	19	20	20	20	21	21
37.5°	18	18	19	20	20	20	21	21	22	22	23
36.25°	19	20	20	21	21	22	23	23	24	24	25
35°	20	21	22	22	23	24	24	25	26	26	27

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	22	22	23	24	25	26	26	27	28	28	29
32.5°	23	24	25	26	27	28	28	29	30	31	32
31.25°	24	26	27	28	29	30	31	32	33	33	34
30°	26	27	29	30	31	32	33	35	36	37	39
28.75°	28	29	31	32	33	35	37	39	40	42	43
27.5°	30	31	33	35	37	39	41	43	45	46	48
26.25°	32	34	36	38	41	43	45	47	49	51	53
25°	34	37	39	42	45	47	50	52	55	58	61
23.75°	37	40	43	46	49	52	55	59	63	66	69
22.5°	41	44	47	50	53	58	63	67	71	76	80
21.25°	44	47	51	55	60	65	70	76	82	87	92
20°	47	51	56	61	67	73	80	86	92	99	107
18.75°	51	56	62	68	75	82	90	97	107	116	124
17.5°	55	61	68	75	84	92	101	112	122	132	144
16.25°	60	67	75	84	92	104	116	127	140	154	167
15°	65	73	82	92	104	117	129	145	161	176	192
13.75°	70	80	90	101	116	129	147	165	182	203	224
12.5°	76	86	97	112	127	145	165	184	209	233	255
11.25°	82	92	107	122	140	161	182	209	236	261	292
10°	87	99	116	132	154	176	203	233	261	296	329
8.75°	92	107	124	144	167	192	224	255	292	329	365
7.5°	96	114	131	154	179	209	243	279	320	359	403
6.25°	102	119	139	164	190	225	259	302	345	391	437
5°	106	124	146	172	202	238	276	321	367	418	468
3.75°	110	128	152	178	211	248	291	337	387	440	494
2.5°	112	131	156	183	218	255	301	349	402	457	514
1.25°	114	132	159	185	222	260	308	356	411	467	527
0°	114	133	160	186	224	262	310	358	414	471	531
-1.25°	114	132	159	185	222	260	308	356	411	467	527
-2.5°	112	131	156	183	218	255	301	349	402	457	514
-3.75°	110	128	152	178	211	248	291	337	387	440	494
-5°	106	124	146	172	202	238	276	321	367	418	468
-6.25°	102	119	139	164	190	225	259	302	345	391	437
-7.5°	96	114	131	154	179	209	243	279	320	359	403
-8.75°	92	107	124	144	167	192	224	255	292	329	365
-10°	87	99	116	132	154	176	203	233	261	296	329
-11.25°	82	92	107	122	140	161	182	209	236	261	292
-12.5°	76	86	97	112	127	145	165	184	209	233	255
-13.75°	70	80	90	101	116	129	147	165	182	203	224
-15°	65	73	82	92	104	117	129	145	161	176	192
-16.25°	60	67	75	84	92	104	116	127	140	154	167
-17.5°	55	61	68	75	84	92	101	112	122	132	144
-18.75°	51	56	62	68	75	82	90	97	107	116	124
-20°	47	51	56	61	67	73	80	86	92	99	107
-21.25°	44	47	51	55	60	65	70	76	82	87	92

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	41	44	47	50	53	58	63	67	71	76	80
-23.75°	37	40	43	46	49	52	55	59	63	66	69
-25°	34	37	39	42	45	47	50	52	55	58	61
-26.25°	32	34	36	38	41	43	45	47	49	51	53
-27.5°	30	31	33	35	37	39	41	43	45	46	48
-28.75°	28	29	31	32	33	35	37	39	40	42	43
-30°	26	27	29	30	31	32	33	35	36	37	39
-31.25°	24	26	27	28	29	30	31	32	33	33	34
-32.5°	23	24	25	26	27	28	28	29	30	31	32
-33.75°	22	22	23	24	25	26	26	27	28	28	29
-35°	20	21	22	22	23	24	24	25	26	26	27
-36.25°	19	20	20	21	21	22	23	23	24	24	25
-37.5°	18	18	19	20	20	20	21	21	22	22	23
-38.75°	17	17	18	18	19	19	20	20	20	21	21
-40°	16	16	17	17	18	18	18	19	19	19	20
-41.25°	15	15	16	16	16	17	17	17	18	18	18
-42.5°	14	14	15	15	15	16	16	16	16	17	17
-43.75°	13	13	14	14	14	15	15	15	15	15	16
-45°	12	12	13	13	13	14	14	14	14	14	15
-46.25°	11	11	12	12	12	13	13	13	13	14	14
-47.5°	10	10	10	11	11	11	12	12	12	12	13
-48.75°	9	9	10	10	10	10	10	11	11	11	11
-50°	8	9	9	9	9	9	10	10	10	10	10
-51.25°	8	8	8	8	8	9	9	9	9	9	9
-52.5°	7	7	7	7	8	8	8	8	8	8	9
-53.75°	6	6	6	7	7	7	7	7	7	8	8
-55°	5	5	6	6	6	6	6	6	7	7	7
-56.25°	4	5	5	5	5	5	5	6	6	6	6
-57.5°	4	4	4	4	4	4	5	5	5	5	5
-58.75°	3	3	3	3	3	4	4	4	4	4	4
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	2	2	3	3	3	3	3	3	3	3	3
-62.5°	2	2	2	2	2	2	2	2	2	3	3
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	1	1	1	1	1	2	2	2	2	2	2
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	3	3	3	3	3	3	3	3	3	3	3
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	3	4	3	3	3	3
58.75°	4	4	4	4	4	4	4	4	4	4	4
57.5°	5	5	5	5	5	5	5	5	5	5	5
56.25°	6	6	6	6	6	6	6	6	6	6	6
55°	7	7	7	7	7	7	7	7	7	7	7
53.75°	8	8	8	8	8	8	8	8	8	8	8
52.5°	9	9	9	9	9	9	9	9	9	9	9
51.25°	9	10	10	10	10	10	10	10	10	10	10
50°	10	10	10	11	11	11	11	11	11	11	10
48.75°	11	12	12	12	12	12	12	12	12	12	12
47.5°	13	13	13	13	13	13	13	13	13	13	13
46.25°	14	14	14	14	14	14	14	14	14	14	14
45°	15	15	15	15	15	15	15	15	15	15	15
43.75°	16	16	16	16	16	16	16	16	16	16	16
42.5°	17	17	17	18	18	18	18	18	18	18	17
41.25°	18	19	19	19	19	19	19	19	19	19	19
40°	20	20	20	20	20	20	20	20	20	20	20
38.75°	21	22	22	22	22	22	22	22	22	22	22
37.5°	23	23	24	24	24	24	24	24	24	24	24
36.25°	25	25	26	26	26	26	26	26	26	26	26
35°	27	28	28	28	28	28	28	28	28	28	28

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	30	30	30	31	31	31	31	31	31	31	30
32.5°	32	33	33	33	34	34	34	34	34	33	33
31.25°	35	36	37	37	38	38	38	38	38	37	37
30°	40	41	41	42	42	43	43	43	42	42	41
28.75°	44	45	46	47	47	48	48	48	47	47	46
27.5°	49	50	51	52	53	53	53	53	53	52	51
26.25°	55	57	59	60	61	62	62	62	61	60	59
25°	64	66	68	69	70	71	71	71	70	69	68
23.75°	72	76	78	81	82	83	83	83	82	81	78
22.5°	84	88	91	93	94	95	96	95	94	93	91
21.25°	96	102	106	110	112	114	114	114	112	110	106
20°	114	119	124	128	131	132	133	132	131	128	124
18.75°	131	139	146	152	156	159	160	159	156	152	146
17.5°	154	164	172	178	183	185	186	185	183	178	172
16.25°	179	190	202	211	218	222	224	222	218	211	202
15°	209	225	238	248	255	260	262	260	255	248	238
13.75°	243	259	276	291	301	308	310	308	301	291	276
12.5°	279	302	321	337	349	356	358	356	349	337	321
11.25°	320	345	367	387	402	411	414	411	402	387	367
10°	359	391	418	440	457	467	471	467	457	440	418
8.75°	403	437	468	494	514	527	531	527	514	494	468
7.5°	444	483	518	549	573	588	593	588	573	549	518
6.25°	483	527	568	603	629	646	652	646	629	603	568
5°	518	568	614	652	680	698	704	698	680	652	614
3.75°	549	603	652	692	722	743	749	743	722	692	652
2.5°	573	629	680	722	756	777	785	777	756	722	680
1.25°	588	646	698	743	777	802	812	802	777	743	698
0°	593	652	704	749	785	812	824	812	785	749	704
-1.25°	588	646	698	743	777	802	812	802	777	743	698
-2.5°	573	629	680	722	756	777	785	777	756	722	680
-3.75°	549	603	652	692	722	743	749	743	722	692	652
-5°	518	568	614	652	680	698	704	698	680	652	614
-6.25°	483	527	568	603	629	646	652	646	629	603	568
-7.5°	444	483	518	549	573	588	593	588	573	549	518
-8.75°	403	437	468	494	514	527	531	527	514	494	468
-10°	359	391	418	440	457	467	471	467	457	440	418
-11.25°	320	345	367	387	402	411	414	411	402	387	367
-12.5°	279	302	321	337	349	356	358	356	349	337	321
-13.75°	243	259	276	291	301	308	310	308	301	291	276
-15°	209	225	238	248	255	260	262	260	255	248	238
-16.25°	179	190	202	211	218	222	224	222	218	211	202
-17.5°	154	164	172	178	183	185	186	185	183	178	172
-18.75°	131	139	146	152	156	159	160	159	156	152	146
-20°	114	119	124	128	131	132	133	132	131	128	124
-21.25°	96	102	106	110	112	114	114	114	112	110	106

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	84	88	91	93	94	95	96	95	94	93	91
-23.75°	72	76	78	81	82	83	83	83	82	81	78
-25°	64	66	68	69	70	71	71	71	70	69	68
-26.25°	55	57	59	60	61	62	62	62	61	60	59
-27.5°	49	50	51	52	53	53	53	53	53	52	51
-28.75°	44	45	46	47	47	48	48	48	47	47	46
-30°	40	41	41	42	42	43	43	43	42	42	41
-31.25°	35	36	37	37	38	38	38	38	38	37	37
-32.5°	32	33	33	33	34	34	34	34	34	33	33
-33.75°	30	30	30	31	31	31	31	31	31	31	30
-35°	27	28	28	28	28	28	28	28	28	28	28
-36.25°	25	25	26	26	26	26	26	26	26	26	26
-37.5°	23	23	24	24	24	24	24	24	24	24	24
-38.75°	21	22	22	22	22	22	22	22	22	22	22
-40°	20	20	20	20	20	20	20	20	20	20	20
-41.25°	18	19	19	19	19	19	19	19	19	19	19
-42.5°	17	17	17	18	18	18	18	18	18	18	17
-43.75°	16	16	16	16	16	16	16	16	16	16	16
-45°	15	15	15	15	15	15	15	15	15	15	15
-46.25°	14	14	14	14	14	14	14	14	14	14	14
-47.5°	13	13	13	13	13	13	13	13	13	13	13
-48.75°	11	12	12	12	12	12	12	12	12	12	12
-50°	10	10	10	11	11	11	11	11	11	11	10
-51.25°	9	10	10	10	10	10	10	10	10	10	10
-52.5°	9	9	9	9	9	9	9	9	9	9	9
-53.75°	8	8	8	8	8	8	8	8	8	8	8
-55°	7	7	7	7	7	7	7	7	7	7	7
-56.25°	6	6	6	6	6	6	6	6	6	6	6
-57.5°	5	5	5	5	5	5	5	5	5	5	5
-58.75°	4	4	4	4	4	4	4	4	4	4	4
-60°	3	3	3	3	3	3	4	3	3	3	3
-61.25°	3	3	3	3	3	3	3	3	3	3	3
-62.5°	3	3	3	3	3	3	3	3	3	3	3
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	2	2	2	2	2	2	2	2	1	1	1
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	3	3	3	3	2	2	2	2	2	2	2
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	4	4	4	4	4	4	4	4	3	3	3
57.5°	5	5	5	5	5	5	5	4	4	4	4
56.25°	6	6	6	6	6	6	5	5	5	5	5
55°	7	7	7	7	7	6	6	6	6	6	6
53.75°	8	8	8	8	7	7	7	7	7	7	6
52.5°	9	9	9	8	8	8	8	8	8	7	7
51.25°	10	9	9	9	9	9	9	9	8	8	8
50°	10	10	10	10	10	10	10	9	9	9	9
48.75°	12	11	11	11	11	11	10	10	10	10	10
47.5°	13	13	13	12	12	12	12	11	11	11	10
46.25°	14	14	14	14	13	13	13	13	12	12	12
45°	15	15	15	14	14	14	14	14	13	13	13
43.75°	16	16	16	15	15	15	15	15	14	14	14
42.5°	17	17	17	17	16	16	16	16	15	15	15
41.25°	19	18	18	18	18	17	17	17	16	16	16
40°	20	20	20	19	19	19	18	18	18	17	17
38.75°	22	21	21	21	20	20	20	19	19	18	18
37.5°	23	23	23	22	22	21	21	20	20	20	19
36.25°	25	25	25	24	24	23	23	22	21	21	20
35°	28	27	27	26	26	25	24	24	23	22	22

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	30	30	29	28	28	27	26	26	25	24	23
32.5°	33	32	32	31	30	29	28	28	27	26	25
31.25°	36	35	34	33	33	32	31	30	29	28	27
30°	41	40	39	37	36	35	33	32	31	30	29
28.75°	45	44	43	42	40	39	37	35	33	32	31
27.5°	50	49	48	46	45	43	41	39	37	35	33
26.25°	57	55	53	51	49	47	45	43	41	38	36
25°	66	64	61	58	55	52	50	47	45	42	39
23.75°	76	72	69	66	63	59	55	52	49	46	43
22.5°	88	84	80	76	71	67	63	58	53	50	47
21.25°	102	96	92	87	82	76	70	65	60	55	51
20°	119	114	107	99	92	86	80	73	67	61	56
18.75°	139	131	124	116	107	97	90	82	75	68	62
17.5°	164	154	144	132	122	112	101	92	84	75	68
16.25°	190	179	167	154	140	127	116	104	92	84	75
15°	225	209	192	176	161	145	129	117	104	92	82
13.75°	259	243	224	203	182	165	147	129	116	101	90
12.5°	302	279	255	233	209	184	165	145	127	112	97
11.25°	345	320	292	261	236	209	182	161	140	122	107
10°	391	359	329	296	261	233	203	176	154	132	116
8.75°	437	403	365	329	292	255	224	192	167	144	124
7.5°	483	444	403	359	320	279	243	209	179	154	131
6.25°	527	483	437	391	345	302	259	225	190	164	139
5°	568	518	468	418	367	321	276	238	202	172	146
3.75°	603	549	494	440	387	337	291	248	211	178	152
2.5°	629	573	514	457	402	349	301	255	218	183	156
1.25°	646	588	527	467	411	356	308	260	222	185	159
0°	652	593	531	471	414	358	310	262	224	186	160
-1.25°	646	588	527	467	411	356	308	260	222	185	159
-2.5°	629	573	514	457	402	349	301	255	218	183	156
-3.75°	603	549	494	440	387	337	291	248	211	178	152
-5°	568	518	468	418	367	321	276	238	202	172	146
-6.25°	527	483	437	391	345	302	259	225	190	164	139
-7.5°	483	444	403	359	320	279	243	209	179	154	131
-8.75°	437	403	365	329	292	255	224	192	167	144	124
-10°	391	359	329	296	261	233	203	176	154	132	116
-11.25°	345	320	292	261	236	209	182	161	140	122	107
-12.5°	302	279	255	233	209	184	165	145	127	112	97
-13.75°	259	243	224	203	182	165	147	129	116	101	90
-15°	225	209	192	176	161	145	129	117	104	92	82
-16.25°	190	179	167	154	140	127	116	104	92	84	75
-17.5°	164	154	144	132	122	112	101	92	84	75	68
-18.75°	139	131	124	116	107	97	90	82	75	68	62
-20°	119	114	107	99	92	86	80	73	67	61	56
-21.25°	102	96	92	87	82	76	70	65	60	55	51

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	88	84	80	76	71	67	63	58	53	50	47
-23.75°	76	72	69	66	63	59	55	52	49	46	43
-25°	66	64	61	58	55	52	50	47	45	42	39
-26.25°	57	55	53	51	49	47	45	43	41	38	36
-27.5°	50	49	48	46	45	43	41	39	37	35	33
-28.75°	45	44	43	42	40	39	37	35	33	32	31
-30°	41	40	39	37	36	35	33	32	31	30	29
-31.25°	36	35	34	33	33	32	31	30	29	28	27
-32.5°	33	32	32	31	30	29	28	28	27	26	25
-33.75°	30	30	29	28	28	27	26	26	25	24	23
-35°	28	27	27	26	26	25	24	24	23	22	22
-36.25°	25	25	25	24	24	23	23	22	21	21	20
-37.5°	23	23	23	22	22	21	21	20	20	20	19
-38.75°	22	21	21	21	20	20	20	19	19	18	18
-40°	20	20	20	19	19	19	18	18	18	17	17
-41.25°	19	18	18	18	18	17	17	17	16	16	16
-42.5°	17	17	17	17	16	16	16	16	15	15	15
-43.75°	16	16	16	15	15	15	15	15	14	14	14
-45°	15	15	15	14	14	14	14	14	13	13	13
-46.25°	14	14	14	14	13	13	13	13	12	12	12
-47.5°	13	13	13	12	12	12	12	11	11	11	10
-48.75°	12	11	11	11	11	11	10	10	10	10	10
-50°	10	10	10	10	10	10	10	9	9	9	9
-51.25°	10	9	9	9	9	9	9	9	8	8	8
-52.5°	9	9	9	8	8	8	8	8	8	7	7
-53.75°	8	8	8	8	7	7	7	7	7	7	6
-55°	7	7	7	7	7	6	6	6	6	6	6
-56.25°	6	6	6	6	6	6	5	5	5	5	5
-57.5°	5	5	5	5	5	5	5	4	4	4	4
-58.75°	4	4	4	4	4	4	4	4	3	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	3	3	3	3	3	3	3	3	3	3	3
-62.5°	3	3	3	3	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	0	0	0	0	0	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	2	2	2	1	1	1	1	1	1	1	1
65°	2	2	2	2	2	2	2	2	1	1	1
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	3	3	3	3	3	2	2	2	2	2	2
58.75°	3	3	3	3	3	3	3	3	2	2	2
57.5°	4	4	3	3	3	3	3	3	3	3	3
56.25°	5	4	4	4	4	3	3	3	3	3	3
55°	5	5	5	5	4	4	4	4	3	3	3
53.75°	6	6	6	5	5	5	5	4	4	4	3
52.5°	7	7	7	6	6	6	5	5	5	4	4
51.25°	8	8	7	7	7	6	6	6	6	5	5
50°	9	8	8	8	8	7	7	7	6	6	6
48.75°	9	9	9	9	8	8	8	7	7	7	6
47.5°	10	10	10	9	9	9	8	8	8	7	7
46.25°	11	11	10	10	10	9	9	9	8	8	8
45°	12	12	11	11	11	10	10	9	9	9	8
43.75°	13	13	13	12	12	11	10	10	10	9	9
42.5°	14	14	14	13	13	12	12	11	10	10	10
41.25°	15	15	14	14	14	13	13	12	11	11	10
40°	16	16	15	15	14	14	14	13	12	12	11
38.75°	17	17	16	16	15	15	14	14	13	13	12
37.5°	18	18	17	17	16	15	15	14	14	13	13
36.25°	20	19	18	18	17	16	16	15	15	14	14
35°	21	20	20	19	18	17	17	16	15	15	14

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	22	22	21	20	19	18	18	17	16	15	15
32.5°	24	23	22	21	20	19	19	18	17	16	15
31.25°	26	24	23	22	22	20	20	19	18	17	16
30°	27	26	25	24	23	22	21	20	19	18	17
28.75°	29	28	27	25	24	23	22	21	20	19	18
27.5°	31	30	28	27	26	24	23	22	21	20	19
26.25°	34	32	30	29	27	26	24	23	22	20	19
25°	37	34	32	31	29	27	26	24	23	22	20
23.75°	40	37	35	32	31	29	27	25	24	22	21
22.5°	44	41	38	35	32	30	28	27	25	23	22
21.25°	47	44	41	37	34	32	30	28	26	24	23
20°	51	47	44	40	37	34	31	29	27	26	24
18.75°	56	51	47	43	39	36	33	31	29	27	25
17.5°	61	55	50	46	42	38	35	32	30	28	26
16.25°	67	60	53	49	45	41	37	33	31	29	27
15°	73	65	58	52	47	43	39	35	32	30	28
13.75°	80	70	63	55	50	45	41	37	33	31	28
12.5°	86	76	67	59	52	47	43	39	35	32	29
11.25°	92	82	71	63	55	49	45	40	36	33	30
10°	99	87	76	66	58	51	46	42	37	33	31
8.75°	107	92	80	69	61	53	48	43	39	34	32
7.5°	114	96	84	72	64	55	49	44	40	35	32
6.25°	119	102	88	76	66	57	50	45	41	36	33
5°	124	106	91	78	68	59	51	46	41	37	33
3.75°	128	110	93	81	69	60	52	47	42	37	33
2.5°	131	112	94	82	70	61	53	47	42	38	34
1.25°	132	114	95	83	71	62	53	48	43	38	34
0°	133	114	96	83	71	62	53	48	43	38	34
-1.25°	132	114	95	83	71	62	53	48	43	38	34
-2.5°	131	112	94	82	70	61	53	47	42	38	34
-3.75°	128	110	93	81	69	60	52	47	42	37	33
-5°	124	106	91	78	68	59	51	46	41	37	33
-6.25°	119	102	88	76	66	57	50	45	41	36	33
-7.5°	114	96	84	72	64	55	49	44	40	35	32
-8.75°	107	92	80	69	61	53	48	43	39	34	32
-10°	99	87	76	66	58	51	46	42	37	33	31
-11.25°	92	82	71	63	55	49	45	40	36	33	30
-12.5°	86	76	67	59	52	47	43	39	35	32	29
-13.75°	80	70	63	55	50	45	41	37	33	31	28
-15°	73	65	58	52	47	43	39	35	32	30	28
-16.25°	67	60	53	49	45	41	37	33	31	29	27
-17.5°	61	55	50	46	42	38	35	32	30	28	26
-18.75°	56	51	47	43	39	36	33	31	29	27	25
-20°	51	47	44	40	37	34	31	29	27	26	24
-21.25°	47	44	41	37	34	32	30	28	26	24	23

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	44	41	38	35	32	30	28	27	25	23	22
-23.75°	40	37	35	32	31	29	27	25	24	22	21
-25°	37	34	32	31	29	27	26	24	23	22	20
-26.25°	34	32	30	29	27	26	24	23	22	20	19
-27.5°	31	30	28	27	26	24	23	22	21	20	19
-28.75°	29	28	27	25	24	23	22	21	20	19	18
-30°	27	26	25	24	23	22	21	20	19	18	17
-31.25°	26	24	23	22	22	20	20	19	18	17	16
-32.5°	24	23	22	21	20	19	19	18	17	16	15
-33.75°	22	22	21	20	19	18	18	17	16	15	15
-35°	21	20	20	19	18	17	17	16	15	15	14
-36.25°	20	19	18	18	17	16	16	15	15	14	14
-37.5°	18	18	17	17	16	15	15	14	14	13	13
-38.75°	17	17	16	16	15	15	14	14	13	13	12
-40°	16	16	15	15	14	14	14	13	12	12	11
-41.25°	15	15	14	14	14	13	13	12	11	11	10
-42.5°	14	14	14	13	13	12	12	11	10	10	10
-43.75°	13	13	13	12	12	11	10	10	10	9	9
-45°	12	12	11	11	11	10	10	9	9	9	8
-46.25°	11	11	10	10	10	9	9	9	8	8	8
-47.5°	10	10	10	9	9	9	8	8	8	7	7
-48.75°	9	9	9	9	8	8	8	7	7	7	6
-50°	9	8	8	8	8	7	7	7	6	6	6
-51.25°	8	8	7	7	7	6	6	6	6	5	5
-52.5°	7	7	7	6	6	6	5	5	5	4	4
-53.75°	6	6	6	5	5	5	5	4	4	4	3
-55°	5	5	5	5	4	4	4	4	3	3	3
-56.25°	5	4	4	4	4	3	3	3	3	3	3
-57.5°	4	4	3	3	3	3	3	3	3	3	3
-58.75°	3	3	3	3	3	3	3	3	2	2	2
-60°	3	3	3	3	3	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	1	1	1
-66.25°	2	2	2	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	0	0	0	0	0	0	0



REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	0	0	0	0	0
73.75°	1	1	1	1	1	1	1	1	1	1	0
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	1	1	1	1	1	1	1	1
61.25°	2	2	2	2	2	1	1	1	1	1	1
60°	2	2	2	2	2	2	2	1	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	1	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	3	3	2	2	2	2	2	2	2	2	2
55°	3	3	3	3	2	2	2	2	2	2	2
53.75°	3	3	3	3	3	2	2	2	2	2	2
52.5°	4	3	3	3	3	3	3	2	2	2	2
51.25°	4	4	4	3	3	3	3	3	2	2	2
50°	5	5	4	4	4	3	3	3	3	3	2
48.75°	6	5	5	5	4	4	3	3	3	3	3
47.5°	7	6	6	5	5	4	4	3	3	3	3
46.25°	7	7	6	6	5	5	4	4	3	3	3
45°	8	7	7	6	6	6	5	5	4	4	3
43.75°	8	8	8	7	7	6	6	5	5	4	3
42.5°	9	9	8	8	7	7	6	6	5	5	4
41.25°	10	9	9	8	8	7	7	6	6	5	4
40°	10	10	9	9	8	8	7	7	6	6	5
38.75°	11	10	10	9	9	8	8	7	7	6	5
37.5°	12	11	10	10	9	9	8	8	7	6	6
36.25°	13	12	11	10	10	9	9	8	8	7	6
35°	14	13	12	11	10	10	9	9	8	7	7

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	14	14	13	12	11	10	10	9	8	8	7
32.5°	15	14	14	13	12	11	10	10	9	8	8
31.25°	15	15	14	13	13	12	11	10	9	9	8
30°	16	15	15	14	13	12	11	10	10	9	8
28.75°	17	16	15	14	14	13	12	11	10	9	9
27.5°	18	17	16	15	14	14	13	12	10	10	9
26.25°	18	17	16	15	15	14	13	12	11	10	9
25°	19	18	17	16	15	14	14	13	12	11	10
23.75°	20	19	18	17	16	15	14	13	12	11	10
22.5°	21	20	18	17	16	15	14	14	13	11	10
21.25°	22	20	19	18	17	16	15	14	13	12	11
20°	22	21	20	18	17	16	15	14	13	12	11
18.75°	23	22	20	19	18	17	16	15	14	13	12
17.5°	24	22	21	20	18	17	16	15	14	13	12
16.25°	25	23	21	20	19	18	16	15	14	13	12
15°	26	24	22	20	19	18	17	16	15	14	13
13.75°	26	24	23	21	20	18	17	16	15	14	13
12.5°	27	25	23	21	20	19	17	16	15	14	13
11.25°	28	26	24	22	20	19	18	16	15	14	13
10°	28	26	24	22	21	19	18	17	15	14	14
8.75°	29	27	25	23	21	20	18	17	16	15	14
7.5°	30	27	25	23	21	20	18	17	16	15	14
6.25°	30	28	25	23	22	20	19	17	16	15	14
5°	30	28	26	24	22	20	19	17	16	15	14
3.75°	31	28	26	24	22	20	19	18	16	15	14
2.5°	31	28	26	24	22	20	19	18	16	15	14
1.25°	31	28	26	24	22	20	19	18	16	15	14
0°	31	28	26	24	22	20	19	18	16	15	14
-1.25°	31	28	26	24	22	20	19	18	16	15	14
-2.5°	31	28	26	24	22	20	19	18	16	15	14
-3.75°	31	28	26	24	22	20	19	18	16	15	14
-5°	30	28	26	24	22	20	19	17	16	15	14
-6.25°	30	28	25	23	22	20	19	17	16	15	14
-7.5°	30	27	25	23	21	20	18	17	16	15	14
-8.75°	29	27	25	23	21	20	18	17	16	15	14
-10°	28	26	24	22	21	19	18	17	15	14	14
-11.25°	28	26	24	22	20	19	18	16	15	14	13
-12.5°	27	25	23	21	20	19	17	16	15	14	13
-13.75°	26	24	23	21	20	18	17	16	15	14	13
-15°	26	24	22	20	19	18	17	16	15	14	13
-16.25°	25	23	21	20	19	18	16	15	14	13	12
-17.5°	24	22	21	20	18	17	16	15	14	13	12
-18.75°	23	22	20	19	18	17	16	15	14	13	12
-20°	22	21	20	18	17	16	15	14	13	12	11
-21.25°	22	20	19	18	17	16	15	14	13	12	11

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	21	20	18	17	16	15	14	14	13	11	10
-23.75°	20	19	18	17	16	15	14	13	12	11	10
-25°	19	18	17	16	15	14	14	13	12	11	10
-26.25°	18	17	16	15	15	14	13	12	11	10	9
-27.5°	18	17	16	15	14	14	13	12	10	10	9
-28.75°	17	16	15	14	14	13	12	11	10	9	9
-30°	16	15	15	14	13	12	11	10	10	9	8
-31.25°	15	15	14	13	13	12	11	10	9	9	8
-32.5°	15	14	14	13	12	11	10	10	9	8	8
-33.75°	14	14	13	12	11	10	10	9	8	8	7
-35°	14	13	12	11	10	10	9	9	8	7	7
-36.25°	13	12	11	10	10	9	9	8	8	7	6
-37.5°	12	11	10	10	9	9	8	8	7	6	6
-38.75°	11	10	10	9	9	8	8	7	7	6	5
-40°	10	10	9	9	8	8	7	7	6	6	5
-41.25°	10	9	9	8	8	7	7	6	6	5	4
-42.5°	9	9	8	8	7	7	6	6	5	5	4
-43.75°	8	8	8	7	7	6	6	5	5	4	3
-45°	8	7	7	6	6	6	5	5	4	4	3
-46.25°	7	7	6	6	5	5	4	4	3	3	3
-47.5°	7	6	6	5	5	4	4	3	3	3	3
-48.75°	6	5	5	5	4	4	3	3	3	3	3
-50°	5	5	4	4	4	3	3	3	3	3	2
-51.25°	4	4	4	3	3	3	3	3	2	2	2
-52.5°	4	3	3	3	3	3	3	2	2	2	2
-53.75°	3	3	3	3	3	2	2	2	2	2	2
-55°	3	3	3	3	2	2	2	2	2	2	2
-56.25°	3	3	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	1	1
-60°	2	2	2	2	2	2	2	1	1	1	1
-61.25°	2	2	2	2	2	1	1	1	1	1	1
-62.5°	2	2	2	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	0
-75°	1	1	1	1	1	1	0	0	0	0	0
-76.25°	1	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	0	0	0	0	0	0	0	0	0
71.25°	1	1	1	1	0	0	0	0	0	0	0
70°	1	1	1	1	1	1	0	0	0	0	0
68.75°	1	1	1	1	1	1	1	1	0	0	0
67.5°	1	1	1	1	1	1	1	1	1	1	0
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	2	1	1	1	1	1	1	1	1	1	1
55°	2	2	1	1	1	1	1	1	1	1	1
53.75°	2	2	2	2	1	1	1	1	1	1	1
52.5°	2	2	2	2	2	1	1	1	1	1	1
51.25°	2	2	2	2	2	2	1	1	1	1	1
50°	2	2	2	2	2	2	1	1	1	1	1
48.75°	2	2	2	2	2	2	2	1	1	1	1
47.5°	3	2	2	2	2	2	2	2	1	1	1
46.25°	3	3	2	2	2	2	2	2	2	1	1
45°	3	3	3	2	2	2	2	2	2	1	1
43.75°	3	3	3	2	2	2	2	2	2	2	1
42.5°	3	3	3	3	2	2	2	2	2	2	1
41.25°	4	3	3	3	3	2	2	2	2	2	2
40°	4	4	3	3	3	2	2	2	2	2	2
38.75°	5	4	4	3	3	3	2	2	2	2	2
37.5°	5	5	4	3	3	3	3	2	2	2	2
36.25°	6	5	4	4	3	3	3	2	2	2	2
35°	6	5	5	4	3	3	3	3	2	2	2

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	7	6	5	4	4	3	3	3	2	2	2
32.5°	7	6	6	5	4	3	3	3	3	2	2
31.25°	7	7	6	5	4	4	3	3	3	2	2
30°	8	7	6	6	5	4	3	3	3	2	2
28.75°	8	7	7	6	5	4	4	3	3	3	2
27.5°	8	8	7	6	5	5	4	3	3	3	2
26.25°	9	8	7	6	6	5	4	3	3	3	2
25°	9	8	8	7	6	5	4	4	3	3	3
23.75°	9	9	8	7	6	5	5	4	3	3	3
22.5°	10	9	8	7	7	6	5	4	3	3	3
21.25°	10	9	8	8	7	6	5	4	4	3	3
20°	10	9	9	8	7	6	5	5	4	3	3
18.75°	10	10	9	8	7	6	6	5	4	3	3
17.5°	11	10	9	8	7	7	6	5	4	3	3
16.25°	11	10	9	8	8	7	6	5	4	3	3
15°	11	10	9	9	8	7	6	5	4	4	3
13.75°	12	10	10	9	8	7	6	5	5	4	3
12.5°	12	11	10	9	8	7	6	6	5	4	3
11.25°	12	11	10	9	8	7	7	6	5	4	3
10°	12	11	10	9	8	8	7	6	5	4	3
8.75°	13	11	10	9	9	8	7	6	5	4	3
7.5°	13	11	10	9	9	8	7	6	5	4	3
6.25°	13	12	10	10	9	8	7	6	5	4	3
5°	13	12	10	10	9	8	7	6	5	4	3
3.75°	13	12	11	10	9	8	7	6	5	4	3
2.5°	13	12	11	10	9	8	7	6	5	4	3
1.25°	13	12	11	10	9	8	7	6	5	4	3
0°	13	12	11	10	9	8	7	6	5	4	4
-1.25°	13	12	11	10	9	8	7	6	5	4	3
-2.5°	13	12	11	10	9	8	7	6	5	4	3
-3.75°	13	12	11	10	9	8	7	6	5	4	3
-5°	13	12	10	10	9	8	7	6	5	4	3
-6.25°	13	12	10	10	9	8	7	6	5	4	3
-7.5°	13	11	10	9	9	8	7	6	5	4	3
-8.75°	13	11	10	9	9	8	7	6	5	4	3
-10°	12	11	10	9	8	8	7	6	5	4	3
-11.25°	12	11	10	9	8	7	7	6	5	4	3
-12.5°	12	11	10	9	8	7	6	6	5	4	3
-13.75°	12	10	10	9	8	7	6	5	5	4	3
-15°	11	10	9	9	8	7	6	5	4	4	3
-16.25°	11	10	9	8	8	7	6	5	4	3	3
-17.5°	11	10	9	8	7	7	6	5	4	3	3
-18.75°	10	10	9	8	7	6	6	5	4	3	3
-20°	10	9	9	8	7	6	5	5	4	3	3
-21.25°	10	9	8	8	7	6	5	4	4	3	3

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	10	9	8	7	7	6	5	4	3	3	3
-23.75°	9	9	8	7	6	5	5	4	3	3	3
-25°	9	8	8	7	6	5	4	4	3	3	3
-26.25°	9	8	7	6	6	5	4	3	3	3	2
-27.5°	8	8	7	6	5	5	4	3	3	3	2
-28.75°	8	7	7	6	5	4	4	3	3	3	2
-30°	8	7	6	6	5	4	3	3	3	2	2
-31.25°	7	7	6	5	4	4	3	3	3	2	2
-32.5°	7	6	6	5	4	3	3	3	3	2	2
-33.75°	7	6	5	4	4	3	3	3	2	2	2
-35°	6	5	5	4	3	3	3	3	2	2	2
-36.25°	6	5	4	4	3	3	3	2	2	2	2
-37.5°	5	5	4	3	3	3	3	2	2	2	2
-38.75°	5	4	4	3	3	3	2	2	2	2	2
-40°	4	4	3	3	3	2	2	2	2	2	2
-41.25°	4	3	3	3	3	2	2	2	2	2	2
-42.5°	3	3	3	3	2	2	2	2	2	2	1
-43.75°	3	3	3	2	2	2	2	2	2	2	1
-45°	3	3	3	2	2	2	2	2	2	1	1
-46.25°	3	3	2	2	2	2	2	2	2	1	1
-47.5°	3	2	2	2	2	2	2	2	1	1	1
-48.75°	2	2	2	2	2	2	2	1	1	1	1
-50°	2	2	2	2	2	2	1	1	1	1	1
-51.25°	2	2	2	2	2	2	1	1	1	1	1
-52.5°	2	2	2	2	2	1	1	1	1	1	1
-53.75°	2	2	2	2	1	1	1	1	1	1	1
-55°	2	2	1	1	1	1	1	1	1	1	1
-56.25°	2	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	0
-68.75°	1	1	1	1	1	1	1	1	0	0	0
-70°	1	1	1	1	1	1	0	0	0	0	0
-71.25°	1	1	1	1	0	0	0	0	0	0	0
-72.5°	1	1	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	1	0	0	0	0	0	0	0	0	0	0
63.75°	1	1	0	0	0	0	0	0	0	0	0
62.5°	1	1	1	0	0	0	0	0	0	0	0
61.25°	1	1	1	1	0	0	0	0	0	0	0
60°	1	1	1	1	1	0	0	0	0	0	0
58.75°	1	1	1	1	1	1	0	0	0	0	0
57.5°	1	1	1	1	1	1	0	0	0	0	0
56.25°	1	1	1	1	1	1	1	0	0	0	0
55°	1	1	1	1	1	1	1	0	0	0	0
53.75°	1	1	1	1	1	1	1	1	0	0	0
52.5°	1	1	1	1	1	1	1	1	0	0	0
51.25°	1	1	1	1	1	1	1	1	1	0	0
50°	1	1	1	1	1	1	1	1	1	0	0
48.75°	1	1	1	1	1	1	1	1	1	1	0
47.5°	1	1	1	1	1	1	1	1	1	1	0
46.25°	1	1	1	1	1	1	1	1	1	1	0
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	1
40°	1	1	1	1	1	1	1	1	1	1	1
38.75°	2	1	1	1	1	1	1	1	1	1	1
37.5°	2	1	1	1	1	1	1	1	1	1	1
36.25°	2	2	1	1	1	1	1	1	1	1	1
35°	2	2	1	1	1	1	1	1	1	1	1

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	2	2	1	1	1	1	1	1	1	1	1
32.5°	2	2	2	1	1	1	1	1	1	1	1
31.25°	2	2	2	1	1	1	1	1	1	1	1
30°	2	2	2	1	1	1	1	1	1	1	1
28.75°	2	2	2	2	1	1	1	1	1	1	1
27.5°	2	2	2	2	1	1	1	1	1	1	1
26.25°	2	2	2	2	1	1	1	1	1	1	1
25°	2	2	2	2	1	1	1	1	1	1	1
23.75°	2	2	2	2	1	1	1	1	1	1	1
22.5°	2	2	2	2	2	1	1	1	1	1	1
21.25°	2	2	2	2	2	1	1	1	1	1	1
20°	2	2	2	2	2	1	1	1	1	1	1
18.75°	3	2	2	2	2	1	1	1	1	1	1
17.5°	3	2	2	2	2	1	1	1	1	1	1
16.25°	3	2	2	2	2	1	1	1	1	1	1
15°	3	2	2	2	2	2	1	1	1	1	1
13.75°	3	2	2	2	2	2	1	1	1	1	1
12.5°	3	2	2	2	2	2	1	1	1	1	1
11.25°	3	2	2	2	2	2	1	1	1	1	1
10°	3	3	2	2	2	2	1	1	1	1	1
8.75°	3	3	2	2	2	2	1	1	1	1	1
7.5°	3	3	2	2	2	2	1	1	1	1	1
6.25°	3	3	2	2	2	2	1	1	1	1	1
5°	3	3	2	2	2	2	1	1	1	1	1
3.75°	3	3	2	2	2	2	1	1	1	1	1
2.5°	3	3	2	2	2	2	1	1	1	1	1
1.25°	3	3	2	2	2	2	1	1	1	1	1
0°	3	3	2	2	2	2	1	1	1	1	1
-1.25°	3	3	2	2	2	2	1	1	1	1	1
-2.5°	3	3	2	2	2	2	1	1	1	1	1
-3.75°	3	3	2	2	2	2	1	1	1	1	1
-5°	3	3	2	2	2	2	1	1	1	1	1
-6.25°	3	3	2	2	2	2	1	1	1	1	1
-7.5°	3	3	2	2	2	2	1	1	1	1	1
-8.75°	3	3	2	2	2	2	1	1	1	1	1
-10°	3	3	2	2	2	2	1	1	1	1	1
-11.25°	3	2	2	2	2	2	1	1	1	1	1
-12.5°	3	2	2	2	2	2	1	1	1	1	1
-13.75°	3	2	2	2	2	2	1	1	1	1	1
-15°	3	2	2	2	2	2	1	1	1	1	1
-16.25°	3	2	2	2	2	1	1	1	1	1	1
-17.5°	3	2	2	2	2	1	1	1	1	1	1
-18.75°	3	2	2	2	2	1	1	1	1	1	1
-20°	2	2	2	2	2	1	1	1	1	1	1
-21.25°	2	2	2	2	2	1	1	1	1	1	1

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	2	2	2	2	1	1	1	1	1	1
-23.75°	2	2	2	2	1	1	1	1	1	1	1
-25°	2	2	2	2	1	1	1	1	1	1	1
-26.25°	2	2	2	2	1	1	1	1	1	1	1
-27.5°	2	2	2	2	1	1	1	1	1	1	1
-28.75°	2	2	2	2	1	1	1	1	1	1	1
-30°	2	2	2	1	1	1	1	1	1	1	1
-31.25°	2	2	2	1	1	1	1	1	1	1	1
-32.5°	2	2	2	1	1	1	1	1	1	1	1
-33.75°	2	2	1	1	1	1	1	1	1	1	1
-35°	2	2	1	1	1	1	1	1	1	1	1
-36.25°	2	2	1	1	1	1	1	1	1	1	1
-37.5°	2	1	1	1	1	1	1	1	1	1	1
-38.75°	2	1	1	1	1	1	1	1	1	1	1
-40°	1	1	1	1	1	1	1	1	1	1	1
-41.25°	1	1	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	0
-47.5°	1	1	1	1	1	1	1	1	1	1	0
-48.75°	1	1	1	1	1	1	1	1	1	1	0
-50°	1	1	1	1	1	1	1	1	1	0	0
-51.25°	1	1	1	1	1	1	1	1	1	0	0
-52.5°	1	1	1	1	1	1	1	1	0	0	0
-53.75°	1	1	1	1	1	1	1	1	0	0	0
-55°	1	1	1	1	1	1	1	0	0	0	0
-56.25°	1	1	1	1	1	1	1	0	0	0	0
-57.5°	1	1	1	1	1	1	0	0	0	0	0
-58.75°	1	1	1	1	1	1	0	0	0	0	0
-60°	1	1	1	1	1	0	0	0	0	0	0
-61.25°	1	1	1	1	0	0	0	0	0	0	0
-62.5°	1	1	1	0	0	0	0	0	0	0	0
-63.75°	1	1	0	0	0	0	0	0	0	0	0
-65°	1	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	1	0	0	0	0	0	0	0	0	0	0
38.75°	1	0	0	0	0	0	0	0	0	0	0
37.5°	1	0	0	0	0	0	0	0	0	0	0
36.25°	1	0	0	0	0	0	0	0	0	0	0
35°	1	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	0	0	0	0	0	0	0	0	0
32.5°	1	1	0	0	0	0	0	0	0	0	0
31.25°	1	1	0	0	0	0	0	0	0	0	0
30°	1	1	0	0	0	0	0	0	0	0	0
28.75°	1	1	0	0	0	0	0	0	0	0	0
27.5°	1	1	0	0	0	0	0	0	0	0	0
26.25°	1	1	0	0	0	0	0	0	0	0	0
25°	1	1	0	0	0	0	0	0	0	0	0
23.75°	1	1	1	0	0	0	0	0	0	0	0
22.5°	1	1	1	0	0	0	0	0	0	0	0
21.25°	1	1	1	0	0	0	0	0	0	0	0
20°	1	1	1	0	0	0	0	0	0	0	0
18.75°	1	1	1	0	0	0	0	0	0	0	0
17.5°	1	1	1	0	0	0	0	0	0	0	0
16.25°	1	1	1	0	0	0	0	0	0	0	0
15°	1	1	1	0	0	0	0	0	0	0	0
13.75°	1	1	1	0	0	0	0	0	0	0	0
12.5°	1	1	1	0	0	0	0	0	0	0	0
11.25°	1	1	1	0	0	0	0	0	0	0	0
10°	1	1	1	0	0	0	0	0	0	0	0
8.75°	1	1	1	0	0	0	0	0	0	0	0
7.5°	1	1	1	0	0	0	0	0	0	0	0
6.25°	1	1	1	0	0	0	0	0	0	0	0
5°	1	1	1	0	0	0	0	0	0	0	0
3.75°	1	1	1	0	0	0	0	0	0	0	0
2.5°	1	1	1	0	0	0	0	0	0	0	0
1.25°	1	1	1	0	0	0	0	0	0	0	0
0°	1	1	1	0	0	0	0	0	0	0	0
-1.25°	1	1	1	0	0	0	0	0	0	0	0
-2.5°	1	1	1	0	0	0	0	0	0	0	0
-3.75°	1	1	1	0	0	0	0	0	0	0	0
-5°	1	1	1	0	0	0	0	0	0	0	0
-6.25°	1	1	1	0	0	0	0	0	0	0	0
-7.5°	1	1	1	0	0	0	0	0	0	0	0
-8.75°	1	1	1	0	0	0	0	0	0	0	0
-10°	1	1	1	0	0	0	0	0	0	0	0
-11.25°	1	1	1	0	0	0	0	0	0	0	0
-12.5°	1	1	1	0	0	0	0	0	0	0	0
-13.75°	1	1	1	0	0	0	0	0	0	0	0
-15°	1	1	1	0	0	0	0	0	0	0	0
-16.25°	1	1	1	0	0	0	0	0	0	0	0
-17.5°	1	1	1	0	0	0	0	0	0	0	0
-18.75°	1	1	1	0	0	0	0	0	0	0	0
-20°	1	1	1	0	0	0	0	0	0	0	0
-21.25°	1	1	1	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	0	0	0	0	0	0	0	0
-23.75°	1	1	1	0	0	0	0	0	0	0	0
-25°	1	1	0	0	0	0	0	0	0	0	0
-26.25°	1	1	0	0	0	0	0	0	0	0	0
-27.5°	1	1	0	0	0	0	0	0	0	0	0
-28.75°	1	1	0	0	0	0	0	0	0	0	0
-30°	1	1	0	0	0	0	0	0	0	0	0
-31.25°	1	1	0	0	0	0	0	0	0	0	0
-32.5°	1	1	0	0	0	0	0	0	0	0	0
-33.75°	1	1	0	0	0	0	0	0	0	0	0
-35°	1	0	0	0	0	0	0	0	0	0	0
-36.25°	1	0	0	0	0	0	0	0	0	0	0
-37.5°	1	0	0	0	0	0	0	0	0	0	0
-38.75°	1	0	0	0	0	0	0	0	0	0	0
-40°	1	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0

REPORT NUMBER: P246969 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)