Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590669

Luminaire Tested: 24CGTX-30-B40-HCD

Issue Date: 9/4/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590669
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2510-581-27)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/4/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-30-B40-HCD
Description:	2X4 3000 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 4000K CCT WITH FROSTED SMOOTH LENS
Light Source:	4000K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	2997.7 lumens
Efficiency:	N/A
Efficacy:	116.6 lumens/watt
Spacing Criteria (0/90/45):	1.28 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 2' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	25.7
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590669
CATALOG NUMBER: 24CGTX-30-B40-HCD

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590669
CATALOG NUMBER: 24CGTX-30-B40-HCD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	68
3	89	79	70	63	87	77	69	63	74	67	62	71	65	61	69	64	60	57
4	82	69	60	54	79	68	60	53	66	58	52	63	57	52	61	55	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	39	51	44	39	50	43	39	37
7	64	50	42	35	62	50	41	35	48	40	35	47	40	35	45	39	34	32
8	60	46	37	31	58	45	37	31	44	36	31	43	36	31	41	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	25	37	30	25	36	30	25	36	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1355	1355	1355
5°	1364	1355	1354
10°	1359	1354	1359
15°	1360	1353	1354
20°	1357	1351	1351
25°	1354	1348	1347
30°	1346	1335	1340
35°	1335	1330	1332
40°	1325	1321	1326
45°	1324	1310	1304
50°	1297	1296	1290
55°	1293	1277	1271
60°	1269	1252	1243
65°	1239	1229	1218
70°	1204	1191	1170
75°	1150	1138	1121
80°	1099	1078	1056
85°	997	973	956

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1324 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590669
CATALOG NUMBER: 24CGTX-30-B40-HCD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.6	3.2
10°-20°	274.7	9.2
20°-30°	418.0	13.9
30°-40°	506.9	16.9
40°-50°	531.2	17.7
50°-60°	486.6	16.2
60°-70°	381.0	12.7
70°-80°	231.8	7.7
80°-90°	72.0	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	788.2	26.3
0°-40°	1295.1	43.2
0°-60°	2312.9	77.2
0°-90°	2997.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2997.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1007	1007	1007	1007	1007	
5°	1010	1007	1003	1003	1002	96
15°	976	974	971	973	972	276
25°	912	906	908	907	907	420
35°	813	810	810	809	811	510
45°	696	688	689	688	685	534
55°	551	546	544	543	542	491
65°	389	386	386	382	383	385
75°	221	221	219	216	216	236
85°	65	65	63	62	62	73
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590669
CATALOG NUMBER: 24CGTX-30-B40-HCD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*1007.3*	1007.3	1007.3	1007.3	1007.3
2.5°	*1012.2*	*1009.5*	*1006.2*	*1004.6*	*1007.3*
5°	*1010.0*	1006.8	1002.9	1002.9	1002.4
7.5°	*1002.4*	1002.9	1000.7	998.0	999.1
10°	*994.7*	994.7	991.4	992.0	994.7
12.5°	*989.8*	984.9	983.8	982.7	987.1
15°	*976.1*	973.9	971.2	972.8	971.7
17.5°	*964.1*	960.2	957.5	957.5	965.2
20°	*947.6*	943.3	943.8	941.1	943.8
22.5°	*927.9*	926.3	926.3	925.7	931.2
25°	*912.1*	906.0	907.7	906.6	907.1
27.5°	*890.2*	885.8	883.0	883.0	886.9
30°	*866.1*	862.2	859.5	858.9	862.2
32.5°	*843.6*	835.4	837.1	836.5	838.7
35°	*813.0*	810.2	809.7	809.1	810.8
37.5°	*787.8*	782.3	780.7	780.1	779.0
40°	*754.4*	753.3	752.2	750.0	754.9
42.5°	*726.5*	722.1	720.4	721.0	720.4
45°	*695.8*	688.1	688.7	688.1	685.4
47.5°	*656.9*	654.8	656.9	652.6	652.0
50°	*619.7*	619.7	619.2	616.4	616.4
52.5°	*588.0*	583.0	583.0	579.7	580.8
55°	*551.3*	546.4	544.2	543.1	542.0
57.5°	*508.6*	506.4	505.3	503.7	503.1
60°	*471.4*	468.6	465.3	464.2	462.0
62.5°	*429.2*	428.1	426.5	424.8	421.5
65°	*389.2*	386.5	386.0	381.6	382.7
67.5°	*349.3*	346.5	344.3	342.2	339.4
70°	*306.0*	303.8	302.7	299.5	297.3
72.5°	*265.5*	263.3	261.1	257.3	255.1
75°	*221.2*	220.6	219.0	216.2	215.7
77.5°	*182.8*	181.2	179.6	177.4	175.2
80°	*141.8*	141.2	139.1	138.0	136.3
82.5°	*104.0*	102.4	100.2	99.1	98.0
85°	*64.6*	65.1	63.0	62.4	61.9
87.5°	*30.1*	30.1	31.2	31.8	30.1
90°	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590669
CATALOG NUMBER: 24CGTX-30-B40-HCD

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.05	14.71	13.41	15.03	15.34	13.00	14.67	13.37	14.98	15.29
	3H	15.00	16.51	15.38	16.84	17.20	14.91	16.42	15.29	16.75	17.11
	4H	15.77	17.19	16.16	17.54	17.91	15.65	17.08	16.05	17.43	17.80
	6H	16.37	17.69	16.78	18.06	18.45	16.24	17.56	16.65	17.92	18.31
	8H	16.59	17.85	17.01	18.24	18.64	16.44	17.70	16.86	18.09	18.49
	12H	16.74	17.95	17.17	18.33	18.76	16.58	17.79	17.01	18.18	18.60
4H	2H	13.72	15.14	14.12	15.49	15.87	13.68	15.11	14.08	15.45	15.83
	3H	15.90	17.10	16.31	17.49	17.89	15.82	17.02	16.23	17.42	17.81
	4H	16.80	17.88	17.23	18.30	18.73	16.70	17.78	17.13	18.20	18.63
	6H	17.55	18.50	18.00	18.94	19.39	17.42	18.37	17.87	18.81	19.27
	8H	17.82	18.71	18.28	19.15	19.62	17.68	18.57	18.14	19.01	19.48
	12H	18.02	18.83	18.50	19.30	19.77	17.87	18.68	18.35	19.15	19.62
8H	4H	17.15	18.04	17.61	18.48	18.95	17.06	17.96	17.52	18.40	18.86
	6H	18.04	18.78	18.53	19.27	19.74	17.93	18.67	18.42	19.16	19.63
	8H	18.40	19.07	18.90	19.57	20.06	18.27	18.94	18.77	19.44	19.93
	12H	18.69	19.29	19.20	19.78	20.33	18.55	19.14	19.05	19.63	20.19
12H	4H	17.20	18.00	17.68	18.48	18.94	17.11	17.92	17.59	18.39	18.86
	6H	18.11	18.78	18.62	19.29	19.77	18.01	18.68	18.51	19.18	19.67
	8H	18.54	19.13	19.04	19.62	20.18	18.41	19.01	18.92	19.49	20.05

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-581-3-R2

Test Date: 01/21/2026

Luminaire Tested: 24CGTX-55-B40-HCD

Data in this report applies to families of products including 24CGTX-55HE

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-581-3-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-55-B40-HCD**
Description:	*THIS IS A REVISION OF REPORT SP1-2510-581-3-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 CGTX 5500 lumen with BioUp Boards with fixed CCT 4000K - Control Volatge at 4V

Spectral Parameters

CCT (K):	4150
CIE u':	0.2306
CIE v':	0.4822
Duv:	-0.0137
CIE x:	0.3662
CIE y:	0.3403
CIE z:	0.2935
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	595
Purity:	11.98102
Rf:	88
Rg:	97.3

CRI (Ra):	87.7
R1:	92.1
R2:	87.5
R3:	86.1
R4:	91.4
R5:	90.5
R6:	81.3
R7:	84.9
R8:	87.7
R9:	87.2
R10:	76.5
R11:	92.8
R12:	70.9
R13:	90.1
R14:	93.9
R15:	92.9



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.1

REPORT NUMBER: SP1-2510-581-3-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2510-581-3-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4150K
CIE x = 0.3662
CIE y = 0.3403
Duv = -0.0137

Point lies outside the range

REPORT NUMBER: SP1-2510-581-3-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	271	NR	620	350	NR	750	8	NR	880	0	NR
365	0	NR	495	243	NR	625	351	NR	755	7	NR	885	0	NR
370	0	NR	500	230	NR	630	1000	NR	760	6	NR	890	0	NR
375	1	NR	505	228	NR	635	567	NR	765	5	NR	895	0	NR
380	1	NR	510	233	NR	640	228	NR	770	4	NR	900	0	NR
385	2	NR	515	236	NR	645	230	NR	775	3	NR	905	0	NR
390	3	NR	520	241	NR	650	189	NR	780	3	NR	910	0	NR
395	4	NR	525	244	NR	655	160	NR	785	3	NR	915	0	NR
400	5	NR	530	248	NR	660	136	NR	790	2	NR	920	0	NR
405	6	NR	535	255	NR	665	115	NR	795	2	NR	925	0	NR
410	8	NR	540	260	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	269	NR	675	86	NR	805	1	NR	935	0	NR
420	23	NR	550	278	NR	680	74	NR	810	1	NR	940	0	NR
425	41	NR	555	289	NR	685	63	NR	815	1	NR	945	0	NR
430	71	NR	560	303	NR	690	54	NR	820	1	NR	950	0	NR
435	122	NR	565	316	NR	695	46	NR	825	1	NR	955	0	NR
440	203	NR	570	329	NR	700	39	NR	830	1	NR	960	0	NR
445	351	NR	575	341	NR	705	33	NR	835	1	NR	965	0	NR
450	441	NR	580	351	NR	710	28	NR	840	1	NR	970	0	NR
455	336	NR	585	360	NR	715	24	NR	845	1	NR	975	0	NR
460	280	NR	590	365	NR	720	20	NR	850	0	NR	980	0	NR
465	345	NR	595	365	NR	725	17	NR	855	0	NR	985	0	NR
470	444	NR	600	365	NR	730	15	NR	860	0	NR	990	0	NR
475	467	NR	605	364	NR	735	12	NR	865	0	NR	995	0	NR
480	390	NR	610	384	NR	740	11	NR	870	0	NR	1000	0	NR
485	310	NR	615	383	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-3-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 2.05**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	271	NR	620	350	NR	750	8	NR	880	0	NR
365	0	NR	495	243	NR	625	351	NR	755	7	NR	885	0	NR
370	0	NR	500	230	NR	630	1000	NR	760	6	NR	890	0	NR
375	1	NR	505	228	NR	635	567	NR	765	5	NR	895	0	NR
380	1	NR	510	233	NR	640	228	NR	770	4	NR	900	0	NR
385	2	NR	515	236	NR	645	230	NR	775	3	NR	905	0	NR
390	3	NR	520	241	NR	650	189	NR	780	3	NR	910	0	NR
395	4	NR	525	244	NR	655	160	NR	785	3	NR	915	0	NR
400	5	NR	530	248	NR	660	136	NR	790	2	NR	920	0	NR
405	6	NR	535	255	NR	665	115	NR	795	2	NR	925	0	NR
410	8	NR	540	260	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	269	NR	675	86	NR	805	1	NR	935	0	NR
420	23	NR	550	278	NR	680	74	NR	810	1	NR	940	0	NR
425	41	NR	555	289	NR	685	63	NR	815	1	NR	945	0	NR
430	71	NR	560	303	NR	690	54	NR	820	1	NR	950	0	NR
435	122	NR	565	316	NR	695	46	NR	825	1	NR	955	0	NR
440	203	NR	570	329	NR	700	39	NR	830	1	NR	960	0	NR
445	351	NR	575	341	NR	705	33	NR	835	1	NR	965	0	NR
450	441	NR	580	351	NR	710	28	NR	840	1	NR	970	0	NR
455	336	NR	585	360	NR	715	24	NR	845	1	NR	975	0	NR
460	280	NR	590	365	NR	720	20	NR	850	0	NR	980	0	NR
465	345	NR	595	365	NR	725	17	NR	855	0	NR	985	0	NR
470	444	NR	600	365	NR	730	15	NR	860	0	NR	990	0	NR
475	467	NR	605	364	NR	735	12	NR	865	0	NR	995	0	NR
480	390	NR	610	384	NR	740	11	NR	870	0	NR	1000	0	NR
485	310	NR	615	383	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-3-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 4.67**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	271	NR	620	350	NR	750	8	NR	880	0	NR
365	0	NR	495	243	NR	625	351	NR	755	7	NR	885	0	NR
370	0	NR	500	230	NR	630	1000	NR	760	6	NR	890	0	NR
375	1	NR	505	228	NR	635	567	NR	765	5	NR	895	0	NR
380	1	NR	510	233	NR	640	228	NR	770	4	NR	900	0	NR
385	2	NR	515	236	NR	645	230	NR	775	3	NR	905	0	NR
390	3	NR	520	241	NR	650	189	NR	780	3	NR	910	0	NR
395	4	NR	525	244	NR	655	160	NR	785	3	NR	915	0	NR
400	5	NR	530	248	NR	660	136	NR	790	2	NR	920	0	NR
405	6	NR	535	255	NR	665	115	NR	795	2	NR	925	0	NR
410	8	NR	540	260	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	269	NR	675	86	NR	805	1	NR	935	0	NR
420	23	NR	550	278	NR	680	74	NR	810	1	NR	940	0	NR
425	41	NR	555	289	NR	685	63	NR	815	1	NR	945	0	NR
430	71	NR	560	303	NR	690	54	NR	820	1	NR	950	0	NR
435	122	NR	565	316	NR	695	46	NR	825	1	NR	955	0	NR
440	203	NR	570	329	NR	700	39	NR	830	1	NR	960	0	NR
445	351	NR	575	341	NR	705	33	NR	835	1	NR	965	0	NR
450	441	NR	580	351	NR	710	28	NR	840	1	NR	970	0	NR
455	336	NR	585	360	NR	715	24	NR	845	1	NR	975	0	NR
460	280	NR	590	365	NR	720	20	NR	850	0	NR	980	0	NR
465	345	NR	595	365	NR	725	17	NR	855	0	NR	985	0	NR
470	444	NR	600	365	NR	730	15	NR	860	0	NR	990	0	NR
475	467	NR	605	364	NR	735	12	NR	865	0	NR	995	0	NR
480	390	NR	610	384	NR	740	11	NR	870	0	NR	1000	0	NR
485	310	NR	615	383	NR	745	9	NR	875	0	NR			


REPORT NUMBER: SP1-2510-581-3-R2

TM-30-18


Summary


R_f = 88
R_g = 97.3
CIE R_a = 87.7
R_9 = 87.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-581-3-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 93	CES51 = 88	CES76 = 88
CES02 = 62	CES27 = 85	CES52 = 91	CES77 = 80
CES03 = 31	CES28 = 95	CES53 = 85	CES78 = 88
CES04 = 70	CES29 = 86	CES54 = 85	CES79 = 83
CES05 = 49	CES30 = 80	CES55 = 83	CES80 = 83
CES06 = 51	CES31 = 87	CES56 = 83	CES81 = 66
CES07 = 42	CES32 = 95	CES57 = 80	CES82 = 93
CES08 = 41	CES33 = 87	CES58 = 81	CES83 = 88
CES09 = 29	CES34 = 93	CES59 = 92	CES84 = 96
CES10 = 75	CES35 = 95	CES60 = 89	CES85 = 77
CES11 = 58	CES36 = 77	CES61 = 88	CES86 = 76
CES12 = 64	CES37 = 95	CES62 = 79	CES87 = 91
CES13 = 43	CES38 = 76	CES63 = 92	CES88 = 90
CES14 = 74	CES39 = 94	CES64 = 84	CES89 = 85
CES15 = 71	CES40 = 91	CES65 = 90	CES90 = 87
CES16 = 47	CES41 = 90	CES66 = 86	CES91 = 72
CES17 = 49	CES42 = 90	CES67 = 86	CES92 = 78
CES18 = 56	CES43 = 88	CES68 = 88	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 89	CES94 = 79
CES20 = 66	CES45 = 91	CES70 = 90	CES95 = 86
CES21 = 85	CES46 = 91	CES71 = 85	CES96 = 95
CES22 = 78	CES47 = 84	CES72 = 94	CES97 = 88
CES23 = 91	CES48 = 80	CES73 = 87	CES98 = 87
CES24 = 90	CES49 = 91	CES74 = 88	CES99 = 88
CES25 = 71	CES50 = 89	CES75 = 87	





REPORT NUMBER: SP1-2510-581-3-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-581-3-R2

TM-30-18

Measure Comparisons





(END OF REPORT)