

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED3036-12-CS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-9)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED3036-12-CS
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD SILVER
Light Source: (1) SORAA 3000K 90 CRI LED
SM16-07-36D-930-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	329.3 lumens	Max Intensity:	957.4 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	43.3 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		

Beam Angle (50%):	35.1°H x 35.1°V	Field Angle (10%):	52.2°H x 52.2°V
Beam Lumens:	211.7 lumens	Field Lumens:	299.8 lumens
Beam Efficiency:	64.3%	Field Efficiency:	91.0%

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3036-12-CS

Iso-Candela Plot




REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3036-12-CS

Lumen Table

90																	
80	0.0	0.0		0.0		0.0		0.0		0.0		0.0		0.0		0.0	
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
60		0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	
40		0.0	0.0	0.1	0.1	0.2	0.3	0.4	0.4	0.3	0.2	0.1	0.1	0.0	0.0		
30	0.0	0.0	0.0	0.1	0.2	0.4	1.7	3.9	3.9	1.7	0.4	0.2	0.1	0.0	0.0	0.0	
20		0.0	0.1	0.1	0.3	1.6	8.5	16.6	16.6	8.5	1.6	0.3	0.1	0.1	0.0		
10	0.0	0.0	0.1	0.1	0.4	3.6	16.2	26.4	26.4	16.2	3.6	0.4	0.1	0.1	0.0	0.0	
0		0.0	0.1	0.1	0.4	3.6	16.2	26.4	26.4	16.2	3.6	0.4	0.1	0.1	0.0		
-10	0.0	0.0	0.1	0.1	0.3	1.6	8.5	16.6	16.6	8.5	1.6	0.3	0.1	0.1	0.0	0.0	
-20		0.0	0.0	0.1	0.2	0.4	1.7	3.9	3.9	1.7	0.4	0.2	0.1	0.0	0.0		
-30	0.0	0.0	0.0	0.1	0.1	0.2	0.3	0.4	0.4	0.3	0.2	0.1	0.1	0.0	0.0	0.0	
-40		0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0		
-50	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-70																	
-80	0.0	0.0		0.0		0.0		0.0		0.0		0.0		0.0		0.0	
-90																	

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3036-12-CS


Luminous Intensity Polar Plot



REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

Luminous Intensity Plot



Beam:

H Angle: 35.1°
V Angle: 35.1°
Lumens: 211.7
Efficiency: 64.3%

Field:

H Angle: 52.2°
V Angle: 52.2°
Lumens: 299.8
Efficiency: 91.0%

Spill:

Lumens: 29.5
Efficiency: 9.0%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 0-Deg

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

FIELD
BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	1
55°	0	0	0	0	0	0	0	0	0	1	1
53.75°	0	0	0	0	0	0	0	0	0	1	1
52.5°	0	0	0	0	0	0	0	0	1	1	1
51.25°	0	0	0	0	0	0	0	0	1	1	1
50°	0	0	0	0	0	0	0	1	1	1	1
48.75°	0	0	0	0	0	0	0	1	1	1	1
47.5°	0	0	0	0	0	0	1	1	1	1	1
46.25°	0	0	0	0	0	0	1	1	1	1	1
45°	0	0	0	0	0	1	1	1	1	1	1
43.75°	0	0	0	0	0	1	1	1	1	1	1
42.5°	0	0	0	0	0	1	1	1	1	1	1
41.25°	0	0	0	0	1	1	1	1	1	1	1
40°	0	0	0	0	1	1	1	1	1	1	1
38.75°	0	0	0	0	1	1	1	1	1	1	1
37.5°	0	0	0	0	1	1	1	1	1	1	1
36.25°	0	0	0	1	1	1	1	1	1	1	1
35°	0	0	0	1	1	1	1	1	1	1	1

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	1	1	1	1	1	1	1	1
32.5°	0	0	0	1	1	1	1	1	1	1	1
31.25°	0	0	0	1	1	1	1	1	1	1	1
30°	0	0	1	1	1	1	1	1	1	1	1
28.75°	0	0	1	1	1	1	1	1	1	1	1
27.5°	0	0	1	1	1	1	1	1	1	1	1
26.25°	0	0	1	1	1	1	1	1	1	1	1
25°	0	0	1	1	1	1	1	1	1	1	1
23.75°	0	0	1	1	1	1	1	1	1	1	1
22.5°	0	0	1	1	1	1	1	1	1	1	1
21.25°	0	1	1	1	1	1	1	1	1	1	1
20°	0	1	1	1	1	1	1	1	1	1	1
18.75°	0	1	1	1	1	1	1	1	1	1	1
17.5°	0	1	1	1	1	1	1	1	1	1	1
16.25°	0	1	1	1	1	1	1	1	1	1	1
15°	0	1	1	1	1	1	1	1	1	1	1
13.75°	0	1	1	1	1	1	1	1	1	1	1
12.5°	0	1	1	1	1	1	1	1	1	1	1
11.25°	0	1	1	1	1	1	1	1	1	1	1
10°	0	1	1	1	1	1	1	1	1	1	1
8.75°	0	1	1	1	1	1	1	1	1	1	1
7.5°	0	1	1	1	1	1	1	1	1	1	1
6.25°	0	1	1	1	1	1	1	1	1	1	1
5°	0	1	1	1	1	1	1	1	1	1	1
3.75°	0	1	1	1	1	1	1	1	1	1	1
2.5°	0	1	1	1	1	1	1	1	1	1	1
1.25°	0	1	1	1	1	1	1	1	1	1	1
0°	0	1	1	1	1	1	1	1	1	1	1
-1.25°	0	1	1	1	1	1	1	1	1	1	1
-2.5°	0	1	1	1	1	1	1	1	1	1	1
-3.75°	0	1	1	1	1	1	1	1	1	1	1
-5°	0	1	1	1	1	1	1	1	1	1	1
-6.25°	0	1	1	1	1	1	1	1	1	1	1
-7.5°	0	1	1	1	1	1	1	1	1	1	1
-8.75°	0	1	1	1	1	1	1	1	1	1	1
-10°	0	1	1	1	1	1	1	1	1	1	1
-11.25°	0	1	1	1	1	1	1	1	1	1	1
-12.5°	0	1	1	1	1	1	1	1	1	1	1
-13.75°	0	1	1	1	1	1	1	1	1	1	1
-15°	0	1	1	1	1	1	1	1	1	1	1
-16.25°	0	1	1	1	1	1	1	1	1	1	1
-17.5°	0	1	1	1	1	1	1	1	1	1	1
-18.75°	0	1	1	1	1	1	1	1	1	1	1
-20°	0	1	1	1	1	1	1	1	1	1	1
-21.25°	0	1	1	1	1	1	1	1	1	1	1

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	1	1	1	1	1	1	1	1	1
-23.75°	0	0	1	1	1	1	1	1	1	1	1
-25°	0	0	1	1	1	1	1	1	1	1	1
-26.25°	0	0	1	1	1	1	1	1	1	1	1
-27.5°	0	0	1	1	1	1	1	1	1	1	1
-28.75°	0	0	1	1	1	1	1	1	1	1	1
-30°	0	0	1	1	1	1	1	1	1	1	1
-31.25°	0	0	0	1	1	1	1	1	1	1	1
-32.5°	0	0	0	1	1	1	1	1	1	1	1
-33.75°	0	0	0	1	1	1	1	1	1	1	1
-35°	0	0	0	1	1	1	1	1	1	1	1
-36.25°	0	0	0	1	1	1	1	1	1	1	1
-37.5°	0	0	0	0	1	1	1	1	1	1	1
-38.75°	0	0	0	0	1	1	1	1	1	1	1
-40°	0	0	0	0	1	1	1	1	1	1	1
-41.25°	0	0	0	0	1	1	1	1	1	1	1
-42.5°	0	0	0	0	0	1	1	1	1	1	1
-43.75°	0	0	0	0	0	1	1	1	1	1	1
-45°	0	0	0	0	0	1	1	1	1	1	1
-46.25°	0	0	0	0	0	0	1	1	1	1	1
-47.5°	0	0	0	0	0	0	1	1	1	1	1
-48.75°	0	0	0	0	0	0	0	1	1	1	1
-50°	0	0	0	0	0	0	0	1	1	1	1
-51.25°	0	0	0	0	0	0	0	0	1	1	1
-52.5°	0	0	0	0	0	0	0	0	1	1	1
-53.75°	0	0	0	0	0	0	0	0	0	1	1
-55°	0	0	0	0	0	0	0	0	0	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	1
66.25°	0	0	0	0	0	0	0	0	1	1	1
65°	0	0	0	0	0	0	1	1	1	1	1
63.75°	0	0	0	0	0	1	1	1	1	1	1
62.5°	0	0	0	0	1	1	1	1	1	1	1
61.25°	0	0	1	1	1	1	1	1	1	1	1
60°	0	1	1	1	1	1	1	1	1	1	1
58.75°	0	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	2
43.75°	1	1	1	1	1	1	1	1	1	2	2
42.5°	1	1	1	1	1	1	1	1	2	2	2
41.25°	1	1	1	1	1	1	1	1	2	2	2
40°	1	1	1	1	1	1	1	2	2	2	2
38.75°	1	1	1	1	1	1	1	2	2	2	2
37.5°	1	1	1	1	1	1	2	2	2	2	2
36.25°	1	1	1	1	1	1	2	2	2	2	2
35°	1	1	1	1	1	2	2	2	2	2	2

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	1	1	1	2	2	2	2	2	3
32.5°	1	1	1	1	2	2	2	2	2	2	3
31.25°	1	1	1	1	2	2	2	2	2	3	3
30°	1	1	1	2	2	2	2	2	2	3	3
28.75°	1	1	1	2	2	2	2	2	3	3	3
27.5°	1	1	1	2	2	2	2	2	3	3	3
26.25°	1	1	1	2	2	2	2	3	3	3	4
25°	1	1	2	2	2	2	2	3	3	3	4
23.75°	1	1	2	2	2	2	2	3	3	3	4
22.5°	1	1	2	2	2	2	3	3	3	4	4
21.25°	1	1	2	2	2	2	3	3	3	4	4
20°	1	2	2	2	2	2	3	3	3	4	4
18.75°	1	2	2	2	2	2	3	3	4	4	4
17.5°	1	2	2	2	2	3	3	3	4	4	4
16.25°	1	2	2	2	2	3	3	3	4	4	4
15°	1	2	2	2	2	3	3	3	4	4	4
13.75°	1	2	2	2	2	3	3	4	4	4	4
12.5°	2	2	2	2	2	3	3	4	4	4	4
11.25°	2	2	2	2	2	3	3	4	4	4	4
10°	2	2	2	2	3	3	3	4	4	4	4
8.75°	2	2	2	2	3	3	3	4	4	4	4
7.5°	2	2	2	2	3	3	3	4	4	4	4
6.25°	2	2	2	2	3	3	3	4	4	4	4
5°	2	2	2	2	3	3	3	4	4	4	4
3.75°	2	2	2	2	3	3	3	4	4	4	4
2.5°	2	2	2	2	3	3	3	4	4	4	4
1.25°	2	2	2	2	3	3	3	4	4	4	4
0°	2	2	2	2	3	3	4	4	4	4	4
-1.25°	2	2	2	2	3	3	3	4	4	4	4
-2.5°	2	2	2	2	3	3	3	4	4	4	4
-3.75°	2	2	2	2	3	3	3	4	4	4	4
-5°	2	2	2	2	3	3	3	4	4	4	4
-6.25°	2	2	2	2	3	3	3	4	4	4	4
-7.5°	2	2	2	2	3	3	3	4	4	4	4
-8.75°	2	2	2	2	3	3	3	4	4	4	4
-10°	2	2	2	2	3	3	3	4	4	4	4
-11.25°	2	2	2	2	2	3	3	4	4	4	4
-12.5°	2	2	2	2	2	3	3	4	4	4	4
-13.75°	1	2	2	2	2	3	3	4	4	4	4
-15°	1	2	2	2	2	3	3	3	4	4	4
-16.25°	1	2	2	2	2	3	3	3	4	4	4
-17.5°	1	2	2	2	2	3	3	3	4	4	4
-18.75°	1	2	2	2	2	2	3	3	4	4	4
-20°	1	2	2	2	2	2	3	3	3	4	4
-21.25°	1	1	2	2	2	2	3	3	3	4	4

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	1	1	2	2	2	2	3	3	3	4	4
-23.75°	1	1	2	2	2	2	2	3	3	3	4
-25°	1	1	2	2	2	2	2	3	3	3	4
-26.25°	1	1	1	2	2	2	2	3	3	3	4
-27.5°	1	1	1	2	2	2	2	2	3	3	3
-28.75°	1	1	1	2	2	2	2	2	3	3	3
-30°	1	1	1	2	2	2	2	2	2	3	3
-31.25°	1	1	1	1	2	2	2	2	2	3	3
-32.5°	1	1	1	1	2	2	2	2	2	2	3
-33.75°	1	1	1	1	1	2	2	2	2	2	3
-35°	1	1	1	1	1	2	2	2	2	2	2
-36.25°	1	1	1	1	1	1	2	2	2	2	2
-37.5°	1	1	1	1	1	1	2	2	2	2	2
-38.75°	1	1	1	1	1	1	1	2	2	2	2
-40°	1	1	1	1	1	1	1	2	2	2	2
-41.25°	1	1	1	1	1	1	1	1	2	2	2
-42.5°	1	1	1	1	1	1	1	1	2	2	2
-43.75°	1	1	1	1	1	1	1	1	1	2	2
-45°	1	1	1	1	1	1	1	1	1	1	2
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	0	1	1	1	1	1	1	1	1	1	1
-60°	0	1	1	1	1	1	1	1	1	1	1
-61.25°	0	0	1	1	1	1	1	1	1	1	1
-62.5°	0	0	0	0	1	1	1	1	1	1	1
-63.75°	0	0	0	0	0	1	1	1	1	1	1
-65°	0	0	0	0	0	0	1	1	1	1	1
-66.25°	0	0	0	0	0	0	0	0	1	1	1
-67.5°	0	0	0	0	0	0	0	0	0	0	1
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	1
71.25°	0	0	0	0	0	0	1	1	1	1	1
70°	0	0	0	1	1	1	1	1	1	1	1
68.75°	0	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	2	2
53.75°	1	1	1	1	1	1	1	2	2	2	2
52.5°	1	1	1	1	1	2	2	2	2	2	2
51.25°	1	1	1	1	2	2	2	2	2	2	2
50°	1	1	1	2	2	2	2	2	2	2	2
48.75°	1	1	2	2	2	2	2	2	2	2	3
47.5°	1	2	2	2	2	2	2	2	2	3	3
46.25°	2	2	2	2	2	2	2	3	3	3	3
45°	2	2	2	2	2	2	3	3	3	3	3
43.75°	2	2	2	2	2	3	3	3	3	3	4
42.5°	2	2	2	2	3	3	3	3	4	4	4
41.25°	2	2	2	3	3	3	3	4	4	4	4
40°	2	2	3	3	3	3	4	4	4	4	4
38.75°	2	2	3	3	3	4	4	4	4	4	4
37.5°	2	3	3	3	3	4	4	4	4	4	4
36.25°	3	3	3	3	4	4	4	4	4	4	4
35°	3	3	3	4	4	4	4	4	4	4	4

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	3	3	4	4	4	4	4	4	4	4	4
32.5°	3	3	4	4	4	4	4	4	4	4	4
31.25°	3	4	4	4	4	4	4	4	4	4	4
30°	3	4	4	4	4	4	4	4	4	4	4
28.75°	4	4	4	4	4	4	4	4	4	4	4
27.5°	4	4	4	4	4	4	4	4	4	4	5
26.25°	4	4	4	4	4	4	4	4	4	5	5
25°	4	4	4	4	4	4	4	4	4	5	5
23.75°	4	4	4	4	4	4	4	4	5	5	5
22.5°	4	4	4	4	4	4	4	4	5	5	6
21.25°	4	4	4	4	4	4	4	5	5	5	6
20°	4	4	4	4	4	4	4	5	5	6	7
18.75°	4	4	4	4	4	4	5	5	5	6	7
17.5°	4	4	4	4	4	4	5	5	6	7	7
16.25°	4	4	4	4	4	4	5	5	6	7	8
15°	4	4	4	4	4	5	5	5	6	7	8
13.75°	4	4	4	4	4	5	5	6	7	8	9
12.5°	4	4	4	4	4	5	5	6	7	8	9
11.25°	4	4	4	4	4	5	5	6	7	8	10
10°	4	4	4	4	5	5	5	6	7	9	10
8.75°	4	4	4	4	5	5	6	7	8	9	10
7.5°	4	4	4	4	5	5	6	7	8	9	11
6.25°	4	4	4	4	5	5	6	7	8	9	11
5°	4	4	4	4	5	5	6	7	8	9	11
3.75°	4	4	4	4	5	5	6	7	8	10	11
2.5°	4	4	4	4	5	5	6	7	8	10	11
1.25°	4	4	4	4	5	5	6	7	8	10	12
0°	4	4	4	4	5	5	6	7	8	10	12
-1.25°	4	4	4	4	5	5	6	7	8	10	12
-2.5°	4	4	4	4	5	5	6	7	8	10	11
-3.75°	4	4	4	4	5	5	6	7	8	10	11
-5°	4	4	4	4	5	5	6	7	8	9	11
-6.25°	4	4	4	4	5	5	6	7	8	9	11
-7.5°	4	4	4	4	5	5	6	7	8	9	11
-8.75°	4	4	4	4	5	5	6	7	8	9	10
-10°	4	4	4	4	5	5	5	6	7	9	10
-11.25°	4	4	4	4	4	5	5	6	7	8	10
-12.5°	4	4	4	4	4	5	5	6	7	8	9
-13.75°	4	4	4	4	4	5	5	6	7	8	9
-15°	4	4	4	4	4	5	5	5	6	7	8
-16.25°	4	4	4	4	4	4	5	5	6	7	8
-17.5°	4	4	4	4	4	4	5	5	6	7	7
-18.75°	4	4	4	4	4	4	5	5	5	6	7
-20°	4	4	4	4	4	4	4	5	5	6	7
-21.25°	4	4	4	4	4	4	4	5	5	5	6

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	4	4	4	4	4	4	4	4	5	5	6
-23.75°	4	4	4	4	4	4	4	4	5	5	5
-25°	4	4	4	4	4	4	4	4	4	5	5
-26.25°	4	4	4	4	4	4	4	4	4	5	5
-27.5°	4	4	4	4	4	4	4	4	4	4	5
-28.75°	4	4	4	4	4	4	4	4	4	4	4
-30°	3	4	4	4	4	4	4	4	4	4	4
-31.25°	3	4	4	4	4	4	4	4	4	4	4
-32.5°	3	3	4	4	4	4	4	4	4	4	4
-33.75°	3	3	4	4	4	4	4	4	4	4	4
-35°	3	3	3	4	4	4	4	4	4	4	4
-36.25°	3	3	3	3	4	4	4	4	4	4	4
-37.5°	2	3	3	3	3	4	4	4	4	4	4
-38.75°	2	2	3	3	3	4	4	4	4	4	4
-40°	2	2	3	3	3	3	4	4	4	4	4
-41.25°	2	2	2	3	3	3	3	4	4	4	4
-42.5°	2	2	2	2	3	3	3	3	4	4	4
-43.75°	2	2	2	2	2	3	3	3	3	3	4
-45°	2	2	2	2	2	2	3	3	3	3	3
-46.25°	2	2	2	2	2	2	2	3	3	3	3
-47.5°	1	2	2	2	2	2	2	2	2	3	3
-48.75°	1	1	2	2	2	2	2	2	2	2	3
-50°	1	1	1	2	2	2	2	2	2	2	2
-51.25°	1	1	1	1	2	2	2	2	2	2	2
-52.5°	1	1	1	1	1	2	2	2	2	2	2
-53.75°	1	1	1	1	1	1	1	2	2	2	2
-55°	1	1	1	1	1	1	1	1	1	2	2
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	0	1	1	1	1	1	1	1	1	1	1
-70°	0	0	0	1	1	1	1	1	1	1	1
-71.25°	0	0	0	0	0	0	1	1	1	1	1
-72.5°	0	0	0	0	0	0	0	0	0	0	1
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	2	2	2
58.75°	1	1	1	1	2	2	2	2	2	2	2
57.5°	1	1	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	3
53.75°	2	2	2	2	2	2	2	3	3	3	3
52.5°	2	2	2	2	2	3	3	3	3	3	3
51.25°	2	2	2	3	3	3	3	3	3	3	4
50°	2	3	3	3	3	3	3	4	4	4	4
48.75°	3	3	3	3	3	4	4	4	4	4	4
47.5°	3	3	3	4	4	4	4	4	4	4	4
46.25°	3	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	4	4	4	4	4	4
42.5°	4	4	4	4	4	4	4	4	4	4	4
41.25°	4	4	4	4	4	4	4	4	4	4	4
40°	4	4	4	4	4	4	4	4	4	4	4
38.75°	4	4	4	4	4	4	4	4	4	5	5
37.5°	4	4	4	4	4	4	4	5	5	5	5
36.25°	4	4	4	4	4	4	5	5	5	5	6
35°	4	4	4	4	4	5	5	5	6	6	7

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	4	4	4	5	5	5	5	6	6	7	7
32.5°	4	4	5	5	5	5	6	6	7	8	8
31.25°	4	5	5	5	5	6	7	7	8	9	9
30°	4	5	5	5	6	7	7	8	9	10	11
28.75°	5	5	5	6	7	7	8	9	10	11	12
27.5°	5	5	6	7	7	8	9	10	11	12	13
26.25°	5	6	6	7	8	9	10	11	12	14	16
25°	6	6	7	8	9	10	11	12	14	16	19
23.75°	6	7	8	9	10	11	12	14	16	19	22
22.5°	7	7	8	9	11	12	13	16	19	22	26
21.25°	7	8	9	10	12	13	15	18	21	26	30
20°	7	9	10	11	13	15	17	20	25	29	35
18.75°	8	9	10	12	14	16	19	24	28	34	43
17.5°	9	10	11	13	15	18	22	27	32	41	53
16.25°	9	10	12	14	17	20	25	30	37	49	65
15°	10	11	13	15	18	22	28	33	44	58	78
13.75°	10	12	13	17	20	25	30	39	52	69	92
12.5°	11	12	15	18	22	27	33	44	60	81	110
11.25°	11	13	16	19	24	29	37	51	69	93	127
10°	12	13	17	20	25	31	41	56	78	107	143
8.75°	12	14	17	21	27	33	46	63	88	121	157
7.5°	12	15	18	23	29	36	50	70	96	133	171
6.25°	13	15	19	24	30	39	54	75	105	143	183
5°	13	16	19	25	31	41	57	81	113	151	193
3.75°	13	16	20	26	32	43	61	85	120	158	202
2.5°	13	17	20	26	32	45	63	88	124	163	209
1.25°	13	17	20	26	33	46	64	90	127	166	213
0°	13	17	20	27	33	46	65	91	128	167	215
-1.25°	13	17	20	26	33	46	64	90	127	166	213
-2.5°	13	17	20	26	32	45	63	88	124	163	209
-3.75°	13	16	20	26	32	43	61	85	120	158	202
-5°	13	16	19	25	31	41	57	81	113	151	193
-6.25°	13	15	19	24	30	39	54	75	105	143	183
-7.5°	12	15	18	23	29	36	50	70	96	133	171
-8.75°	12	14	17	21	27	33	46	63	88	121	157
-10°	12	13	17	20	25	31	41	56	78	107	143
-11.25°	11	13	16	19	24	29	37	51	69	93	127
-12.5°	11	12	15	18	22	27	33	44	60	81	110
-13.75°	10	12	13	17	20	25	30	39	52	69	92
-15°	10	11	13	15	18	22	28	33	44	58	78
-16.25°	9	10	12	14	17	20	25	30	37	49	65
-17.5°	9	10	11	13	15	18	22	27	32	41	53
-18.75°	8	9	10	12	14	16	19	24	28	34	43
-20°	7	9	10	11	13	15	17	20	25	29	35
-21.25°	7	8	9	10	12	13	15	18	21	26	30

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	7	7	8	9	11	12	13	16	19	22	26
-23.75°	6	7	8	9	10	11	12	14	16	19	22
-25°	6	6	7	8	9	10	11	12	14	16	19
-26.25°	5	6	6	7	8	9	10	11	12	14	16
-27.5°	5	5	6	7	7	8	9	10	11	12	13
-28.75°	5	5	5	6	7	7	8	9	10	11	12
-30°	4	5	5	5	6	7	7	8	9	10	11
-31.25°	4	5	5	5	5	6	7	7	8	9	9
-32.5°	4	4	5	5	5	5	6	6	7	8	8
-33.75°	4	4	4	5	5	5	5	6	6	7	7
-35°	4	4	4	4	4	5	5	5	6	6	7
-36.25°	4	4	4	4	4	4	5	5	5	5	6
-37.5°	4	4	4	4	4	4	4	5	5	5	5
-38.75°	4	4	4	4	4	4	4	4	4	5	5
-40°	4	4	4	4	4	4	4	4	4	4	4
-41.25°	4	4	4	4	4	4	4	4	4	4	4
-42.5°	4	4	4	4	4	4	4	4	4	4	4
-43.75°	4	4	4	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	3	4	4	4	4	4	4	4	4	4	4
-47.5°	3	3	3	4	4	4	4	4	4	4	4
-48.75°	3	3	3	3	3	4	4	4	4	4	4
-50°	2	3	3	3	3	3	3	4	4	4	4
-51.25°	2	2	2	3	3	3	3	3	3	3	4
-52.5°	2	2	2	2	2	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	2	3	3	3	3
-55°	2	2	2	2	2	2	2	2	2	2	3
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	1	1	2	2	2	2	2	2	2	2	2
-58.75°	1	1	1	1	2	2	2	2	2	2	2
-60°	1	1	1	1	1	1	1	1	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	0	1	1	1	1	1	1	1
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	2	2	2	2
61.25°	1	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	3	3
56.25°	2	2	2	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	4	4	4	4	4
52.5°	3	3	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	4	4	4	4	5	5
42.5°	4	4	4	4	4	5	5	5	5	5	5
41.25°	4	4	5	5	5	5	5	5	5	5	6
40°	5	5	5	5	5	5	6	6	6	6	7
38.75°	5	5	5	6	6	6	7	7	7	7	8
37.5°	5	6	6	7	7	7	8	8	8	9	9
36.25°	6	7	7	7	8	8	9	9	10	10	10
35°	7	7	8	9	9	10	10	11	11	12	12

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	8	9	9	10	10	11	12	12	13	13	14
32.5°	9	10	10	11	12	13	13	15	16	17	17
31.25°	10	11	12	13	14	15	17	18	19	20	21
30°	12	13	14	15	17	18	20	22	24	25	27
28.75°	13	15	16	18	20	22	25	27	29	31	33
27.5°	15	17	19	22	25	28	30	33	37	41	46
26.25°	18	20	24	27	30	33	39	44	51	56	63
25°	21	25	28	32	37	44	52	60	69	78	88
23.75°	26	29	34	41	49	58	69	81	93	107	121
22.5°	30	35	43	53	65	78	92	110	127	143	157
21.25°	36	44	55	69	85	103	123	143	161	180	197
20°	44	56	71	89	110	133	155	178	200	224	247
18.75°	55	71	90	114	140	164	190	218	247	276	304
17.5°	69	89	114	142	169	198	231	265	299	334	366
16.25°	85	110	140	169	201	237	276	316	356	394	430
15°	103	133	164	198	237	279	325	370	414	455	493
13.75°	123	155	190	231	276	325	375	424	471	514	552
12.5°	143	178	218	265	316	370	424	476	525	568	604
11.25°	161	200	247	299	356	414	471	525	572	614	649
10°	180	224	276	334	394	455	514	568	614	654	691
8.75°	197	247	304	366	430	493	552	604	649	691	729
7.5°	216	269	330	395	461	526	584	634	681	724	763
6.25°	231	288	353	421	489	554	610	661	708	752	792
5°	245	306	373	443	512	576	631	683	731	775	817
3.75°	257	320	388	460	530	592	648	700	749	794	836
2.5°	265	330	400	472	542	604	660	713	762	808	850
1.25°	270	336	407	480	550	612	667	720	770	816	858
0°	272	338	409	482	552	614	670	723	772	819	861
-1.25°	270	336	407	480	550	612	667	720	770	816	858
-2.5°	265	330	400	472	542	604	660	713	762	808	850
-3.75°	257	320	388	460	530	592	648	700	749	794	836
-5°	245	306	373	443	512	576	631	683	731	775	817
-6.25°	231	288	353	421	489	554	610	661	708	752	792
-7.5°	216	269	330	395	461	526	584	634	681	724	763
-8.75°	197	247	304	366	430	493	552	604	649	691	729
-10°	180	224	276	334	394	455	514	568	614	654	691
-11.25°	161	200	247	299	356	414	471	525	572	614	649
-12.5°	143	178	218	265	316	370	424	476	525	568	604
-13.75°	123	155	190	231	276	325	375	424	471	514	552
-15°	103	133	164	198	237	279	325	370	414	455	493
-16.25°	85	110	140	169	201	237	276	316	356	394	430
-17.5°	69	89	114	142	169	198	231	265	299	334	366
-18.75°	55	71	90	114	140	164	190	218	247	276	304
-20°	44	56	71	89	110	133	155	178	200	224	247
-21.25°	36	44	55	69	85	103	123	143	161	180	197

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	30	35	43	53	65	78	92	110	127	143	157
-23.75°	26	29	34	41	49	58	69	81	93	107	121
-25°	21	25	28	32	37	44	52	60	69	78	88
-26.25°	18	20	24	27	30	33	39	44	51	56	63
-27.5°	15	17	19	22	25	28	30	33	37	41	46
-28.75°	13	15	16	18	20	22	25	27	29	31	33
-30°	12	13	14	15	17	18	20	22	24	25	27
-31.25°	10	11	12	13	14	15	17	18	19	20	21
-32.5°	9	10	10	11	12	13	13	15	16	17	17
-33.75°	8	9	9	10	10	11	12	12	13	13	14
-35°	7	7	8	9	9	10	10	11	11	12	12
-36.25°	6	7	7	7	8	8	9	9	10	10	10
-37.5°	5	6	6	7	7	7	8	8	8	9	9
-38.75°	5	5	5	6	6	6	7	7	7	7	8
-40°	5	5	5	5	5	5	6	6	6	6	7
-41.25°	4	4	5	5	5	5	5	5	5	5	6
-42.5°	4	4	4	4	4	5	5	5	5	5	5
-43.75°	4	4	4	4	4	4	4	4	4	5	5
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	3	3	4	4	4	4	4	4	4	4	4
-53.75°	3	3	3	3	3	3	4	4	4	4	4
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	2	2	3	3	3	3	3	3	3	3
-57.5°	2	2	2	2	2	2	2	2	2	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	2	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	1	1	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	4	3	3	3	3
53.75°	4	4	4	4	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	5	5	5	5	5	5	5	5	5	5	5
42.5°	5	5	5	5	5	5	5	5	5	5	5
41.25°	6	6	6	6	6	6	6	6	6	6	6
40°	7	7	7	7	7	7	7	7	7	7	7
38.75°	8	8	8	8	8	8	8	8	8	8	8
37.5°	9	9	9	10	10	10	10	10	10	10	9
36.25°	11	11	11	11	11	12	12	12	11	11	11
35°	12	13	13	13	13	13	13	13	13	13	13

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	15	15	16	16	17	17	17	17	17	16	16
32.5°	18	19	19	20	20	20	20	20	20	20	19
31.25°	23	24	25	26	26	26	27	26	26	26	25
30°	29	30	31	32	32	33	33	33	32	32	31
28.75°	36	39	41	43	45	46	46	46	45	43	41
27.5°	50	54	57	61	63	64	65	64	63	61	57
26.25°	70	75	81	85	88	90	91	90	88	85	81
25°	96	105	113	120	124	127	128	127	124	120	113
23.75°	133	143	151	158	163	166	167	166	163	158	151
22.5°	171	183	193	202	209	213	215	213	209	202	193
21.25°	216	231	245	257	265	270	272	270	265	257	245
20°	269	288	306	320	330	336	338	336	330	320	306
18.75°	330	353	373	388	400	407	409	407	400	388	373
17.5°	395	421	443	460	472	480	482	480	472	460	443
16.25°	461	489	512	530	542	550	552	550	542	530	512
15°	526	554	576	592	604	612	614	612	604	592	576
13.75°	584	610	631	648	660	667	670	667	660	648	631
12.5°	634	661	683	700	713	720	723	720	713	700	683
11.25°	681	708	731	749	762	770	772	770	762	749	731
10°	724	752	775	794	808	816	819	816	808	794	775
8.75°	763	792	817	836	850	858	861	858	850	836	817
7.5°	797	828	853	872	885	893	895	893	885	872	853
6.25°	828	859	883	901	912	918	920	918	912	901	883
5°	853	883	906	920	929	934	935	934	929	920	906
3.75°	872	901	920	932	939	942	943	942	939	932	920
2.5°	885	912	929	939	944	946	947	946	944	939	929
1.25°	893	918	934	942	946	950	953	950	946	942	934
0°	895	920	935	943	947	953	957	953	947	943	935
-1.25°	893	918	934	942	946	950	953	950	946	942	934
-2.5°	885	912	929	939	944	946	947	946	944	939	929
-3.75°	872	901	920	932	939	942	943	942	939	932	920
-5°	853	883	906	920	929	934	935	934	929	920	906
-6.25°	828	859	883	901	912	918	920	918	912	901	883
-7.5°	797	828	853	872	885	893	895	893	885	872	853
-8.75°	763	792	817	836	850	858	861	858	850	836	817
-10°	724	752	775	794	808	816	819	816	808	794	775
-11.25°	681	708	731	749	762	770	772	770	762	749	731
-12.5°	634	661	683	700	713	720	723	720	713	700	683
-13.75°	584	610	631	648	660	667	670	667	660	648	631
-15°	526	554	576	592	604	612	614	612	604	592	576
-16.25°	461	489	512	530	542	550	552	550	542	530	512
-17.5°	395	421	443	460	472	480	482	480	472	460	443
-18.75°	330	353	373	388	400	407	409	407	400	388	373
-20°	269	288	306	320	330	336	338	336	330	320	306
-21.25°	216	231	245	257	265	270	272	270	265	257	245

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	171	183	193	202	209	213	215	213	209	202	193
-23.75°	133	143	151	158	163	166	167	166	163	158	151
-25°	96	105	113	120	124	127	128	127	124	120	113
-26.25°	70	75	81	85	88	90	91	90	88	85	81
-27.5°	50	54	57	61	63	64	65	64	63	61	57
-28.75°	36	39	41	43	45	46	46	46	45	43	41
-30°	29	30	31	32	32	33	33	33	32	32	31
-31.25°	23	24	25	26	26	26	27	26	26	26	25
-32.5°	18	19	19	20	20	20	20	20	20	20	19
-33.75°	15	15	16	16	17	17	17	17	17	16	16
-35°	12	13	13	13	13	13	13	13	13	13	13
-36.25°	11	11	11	11	11	12	12	12	11	11	11
-37.5°	9	9	9	10	10	10	10	10	10	10	9
-38.75°	8	8	8	8	8	8	8	8	8	8	8
-40°	7	7	7	7	7	7	7	7	7	7	7
-41.25°	6	6	6	6	6	6	6	6	6	6	6
-42.5°	5	5	5	5	5	5	5	5	5	5	5
-43.75°	5	5	5	5	5	5	5	5	5	5	5
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	4	4	4	4
-55°	3	3	3	3	3	3	4	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	1	1	1	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	2	2	2	2	2	2	2
56.25°	3	3	3	3	3	3	3	3	3	3	2
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	4	4	4	4	4	4	4	3	3	3	3
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	5	5	5	5	4	4	4	4	4	4	4
42.5°	5	5	5	5	5	5	5	5	4	4	4
41.25°	6	6	6	5	5	5	5	5	5	5	5
40°	7	7	7	6	6	6	6	5	5	5	5
38.75°	8	8	8	7	7	7	7	6	6	6	5
37.5°	9	9	9	9	8	8	8	7	7	7	6
36.25°	11	11	10	10	10	9	9	8	8	7	7
35°	13	12	12	12	11	11	10	10	9	9	8

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	15	15	14	13	13	12	12	11	10	10	9
32.5°	19	18	17	17	16	15	13	13	12	11	10
31.25°	24	23	21	20	19	18	17	15	14	13	12
30°	30	29	27	25	24	22	20	18	17	15	14
28.75°	39	36	33	31	29	27	25	22	20	18	16
27.5°	54	50	46	41	37	33	30	28	25	22	19
26.25°	75	70	63	56	51	44	39	33	30	27	24
25°	105	96	88	78	69	60	52	44	37	32	28
23.75°	143	133	121	107	93	81	69	58	49	41	34
22.5°	183	171	157	143	127	110	92	78	65	53	43
21.25°	231	216	197	180	161	143	123	103	85	69	55
20°	288	269	247	224	200	178	155	133	110	89	71
18.75°	353	330	304	276	247	218	190	164	140	114	90
17.5°	421	395	366	334	299	265	231	198	169	142	114
16.25°	489	461	430	394	356	316	276	237	201	169	140
15°	554	526	493	455	414	370	325	279	237	198	164
13.75°	610	584	552	514	471	424	375	325	276	231	190
12.5°	661	634	604	568	525	476	424	370	316	265	218
11.25°	708	681	649	614	572	525	471	414	356	299	247
10°	752	724	691	654	614	568	514	455	394	334	276
8.75°	792	763	729	691	649	604	552	493	430	366	304
7.5°	828	797	763	724	681	634	584	526	461	395	330
6.25°	859	828	792	752	708	661	610	554	489	421	353
5°	883	853	817	775	731	683	631	576	512	443	373
3.75°	901	872	836	794	749	700	648	592	530	460	388
2.5°	912	885	850	808	762	713	660	604	542	472	400
1.25°	918	893	858	816	770	720	667	612	550	480	407
0°	920	895	861	819	772	723	670	614	552	482	409
-1.25°	918	893	858	816	770	720	667	612	550	480	407
-2.5°	912	885	850	808	762	713	660	604	542	472	400
-3.75°	901	872	836	794	749	700	648	592	530	460	388
-5°	883	853	817	775	731	683	631	576	512	443	373
-6.25°	859	828	792	752	708	661	610	554	489	421	353
-7.5°	828	797	763	724	681	634	584	526	461	395	330
-8.75°	792	763	729	691	649	604	552	493	430	366	304
-10°	752	724	691	654	614	568	514	455	394	334	276
-11.25°	708	681	649	614	572	525	471	414	356	299	247
-12.5°	661	634	604	568	525	476	424	370	316	265	218
-13.75°	610	584	552	514	471	424	375	325	276	231	190
-15°	554	526	493	455	414	370	325	279	237	198	164
-16.25°	489	461	430	394	356	316	276	237	201	169	140
-17.5°	421	395	366	334	299	265	231	198	169	142	114
-18.75°	353	330	304	276	247	218	190	164	140	114	90
-20°	288	269	247	224	200	178	155	133	110	89	71
-21.25°	231	216	197	180	161	143	123	103	85	69	55

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	183	171	157	143	127	110	92	78	65	53	43
-23.75°	143	133	121	107	93	81	69	58	49	41	34
-25°	105	96	88	78	69	60	52	44	37	32	28
-26.25°	75	70	63	56	51	44	39	33	30	27	24
-27.5°	54	50	46	41	37	33	30	28	25	22	19
-28.75°	39	36	33	31	29	27	25	22	20	18	16
-30°	30	29	27	25	24	22	20	18	17	15	14
-31.25°	24	23	21	20	19	18	17	15	14	13	12
-32.5°	19	18	17	17	16	15	13	13	12	11	10
-33.75°	15	15	14	13	13	12	12	11	10	10	9
-35°	13	12	12	12	11	11	10	10	9	9	8
-36.25°	11	11	10	10	10	9	9	8	8	7	7
-37.5°	9	9	9	9	8	8	8	7	7	7	6
-38.75°	8	8	8	7	7	7	7	6	6	6	5
-40°	7	7	7	6	6	6	6	5	5	5	5
-41.25°	6	6	6	5	5	5	5	5	5	5	5
-42.5°	5	5	5	5	5	5	5	5	4	4	4
-43.75°	5	5	5	5	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	2
-57.5°	3	3	3	3	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	1	1	0	0	0	0	0	0	0	0	0
73.75°	1	1	1	1	1	1	1	1	1	0	0
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	1	1	1	1	1	1	1	1	1	1
60°	2	2	2	2	2	1	1	1	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	1	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	2	2	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	2	2	2	2	2
52.5°	3	3	3	3	3	3	3	3	2	2	2
51.25°	4	4	4	3	3	3	3	3	3	3	2
50°	4	4	4	4	4	4	3	3	3	3	3
48.75°	4	4	4	4	4	4	4	4	3	3	3
47.5°	4	4	4	4	4	4	4	4	4	4	3
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	4	4	4	4	4	4
42.5°	4	4	4	4	4	4	4	4	4	4	4
41.25°	4	4	4	4	4	4	4	4	4	4	4
40°	5	5	4	4	4	4	4	4	4	4	4
38.75°	5	5	5	5	4	4	4	4	4	4	4
37.5°	6	5	5	5	5	5	4	4	4	4	4
36.25°	7	6	6	5	5	5	5	4	4	4	4
35°	7	7	7	6	6	5	5	5	4	4	4

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	9	8	7	7	6	6	5	5	5	5	4
32.5°	10	9	8	8	7	6	6	5	5	5	5
31.25°	11	10	9	9	8	7	7	6	5	5	5
30°	13	12	11	10	9	8	7	7	6	5	5
28.75°	15	13	12	11	10	9	8	7	7	6	5
27.5°	17	15	13	12	11	10	9	8	7	7	6
26.25°	20	18	16	14	12	11	10	9	8	7	6
25°	25	21	19	16	14	12	11	10	9	8	7
23.75°	29	26	22	19	16	14	12	11	10	9	8
22.5°	35	30	26	22	19	16	13	12	11	9	8
21.25°	44	36	30	26	21	18	15	13	12	10	9
20°	56	44	35	29	25	20	17	15	13	11	10
18.75°	71	55	43	34	28	24	19	16	14	12	10
17.5°	89	69	53	41	32	27	22	18	15	13	11
16.25°	110	85	65	49	37	30	25	20	17	14	12
15°	133	103	78	58	44	33	28	22	18	15	13
13.75°	155	123	92	69	52	39	30	25	20	17	13
12.5°	178	143	110	81	60	44	33	27	22	18	15
11.25°	200	161	127	93	69	51	37	29	24	19	16
10°	224	180	143	107	78	56	41	31	25	20	17
8.75°	247	197	157	121	88	63	46	33	27	21	17
7.5°	269	216	171	133	96	70	50	36	29	23	18
6.25°	288	231	183	143	105	75	54	39	30	24	19
5°	306	245	193	151	113	81	57	41	31	25	19
3.75°	320	257	202	158	120	85	61	43	32	26	20
2.5°	330	265	209	163	124	88	63	45	32	26	20
1.25°	336	270	213	166	127	90	64	46	33	26	20
0°	338	272	215	167	128	91	65	46	33	27	20
-1.25°	336	270	213	166	127	90	64	46	33	26	20
-2.5°	330	265	209	163	124	88	63	45	32	26	20
-3.75°	320	257	202	158	120	85	61	43	32	26	20
-5°	306	245	193	151	113	81	57	41	31	25	19
-6.25°	288	231	183	143	105	75	54	39	30	24	19
-7.5°	269	216	171	133	96	70	50	36	29	23	18
-8.75°	247	197	157	121	88	63	46	33	27	21	17
-10°	224	180	143	107	78	56	41	31	25	20	17
-11.25°	200	161	127	93	69	51	37	29	24	19	16
-12.5°	178	143	110	81	60	44	33	27	22	18	15
-13.75°	155	123	92	69	52	39	30	25	20	17	13
-15°	133	103	78	58	44	33	28	22	18	15	13
-16.25°	110	85	65	49	37	30	25	20	17	14	12
-17.5°	89	69	53	41	32	27	22	18	15	13	11
-18.75°	71	55	43	34	28	24	19	16	14	12	10
-20°	56	44	35	29	25	20	17	15	13	11	10
-21.25°	44	36	30	26	21	18	15	13	12	10	9

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	35	30	26	22	19	16	13	12	11	9	8
-23.75°	29	26	22	19	16	14	12	11	10	9	8
-25°	25	21	19	16	14	12	11	10	9	8	7
-26.25°	20	18	16	14	12	11	10	9	8	7	6
-27.5°	17	15	13	12	11	10	9	8	7	7	6
-28.75°	15	13	12	11	10	9	8	7	7	6	5
-30°	13	12	11	10	9	8	7	7	6	5	5
-31.25°	11	10	9	9	8	7	7	6	5	5	5
-32.5°	10	9	8	8	7	6	6	5	5	5	5
-33.75°	9	8	7	7	6	6	5	5	5	5	4
-35°	7	7	7	6	6	5	5	5	4	4	4
-36.25°	7	6	6	5	5	5	5	4	4	4	4
-37.5°	6	5	5	5	5	5	4	4	4	4	4
-38.75°	5	5	5	5	4	4	4	4	4	4	4
-40°	5	5	4	4	4	4	4	4	4	4	4
-41.25°	4	4	4	4	4	4	4	4	4	4	4
-42.5°	4	4	4	4	4	4	4	4	4	4	4
-43.75°	4	4	4	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	3
-48.75°	4	4	4	4	4	4	4	4	3	3	3
-50°	4	4	4	4	4	4	3	3	3	3	3
-51.25°	4	4	4	3	3	3	3	3	3	3	2
-52.5°	3	3	3	3	3	3	3	3	2	2	2
-53.75°	3	3	3	3	3	3	2	2	2	2	2
-55°	3	3	3	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	1	1
-60°	2	2	2	2	2	1	1	1	1	1	1
-61.25°	2	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	0	0
-75°	1	1	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	1	0	0	0	0	0	0	0	0
71.25°	1	1	1	1	1	1	1	0	0	0	0
70°	1	1	1	1	1	1	1	1	1	1	0
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	1	1	1	1	1	1	1	1	1
55°	2	2	2	2	1	1	1	1	1	1	1
53.75°	2	2	2	2	2	2	1	1	1	1	1
52.5°	2	2	2	2	2	2	2	2	1	1	1
51.25°	2	2	2	2	2	2	2	2	2	1	1
50°	3	2	2	2	2	2	2	2	2	2	1
48.75°	3	3	3	2	2	2	2	2	2	2	2
47.5°	3	3	3	3	2	2	2	2	2	2	2
46.25°	4	3	3	3	3	3	2	2	2	2	2
45°	4	4	3	3	3	3	3	2	2	2	2
43.75°	4	4	4	3	3	3	3	3	2	2	2
42.5°	4	4	4	4	4	3	3	3	3	2	2
41.25°	4	4	4	4	4	4	3	3	3	3	2
40°	4	4	4	4	4	4	4	3	3	3	3
38.75°	4	4	4	4	4	4	4	4	3	3	3
37.5°	4	4	4	4	4	4	4	4	3	3	3
36.25°	4	4	4	4	4	4	4	4	4	3	3
35°	4	4	4	4	4	4	4	4	4	4	3

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	4	4	4	4	4	4	4	4	4	4	4
32.5°	4	4	4	4	4	4	4	4	4	4	4
31.25°	5	4	4	4	4	4	4	4	4	4	4
30°	5	4	4	4	4	4	4	4	4	4	4
28.75°	5	5	4	4	4	4	4	4	4	4	4
27.5°	5	5	5	4	4	4	4	4	4	4	4
26.25°	6	5	5	5	4	4	4	4	4	4	4
25°	6	6	5	5	4	4	4	4	4	4	4
23.75°	7	6	5	5	5	4	4	4	4	4	4
22.5°	7	7	6	5	5	4	4	4	4	4	4
21.25°	8	7	6	5	5	5	4	4	4	4	4
20°	9	7	7	6	5	5	4	4	4	4	4
18.75°	9	8	7	6	5	5	5	4	4	4	4
17.5°	10	9	7	7	6	5	5	4	4	4	4
16.25°	10	9	8	7	6	5	5	4	4	4	4
15°	11	10	8	7	6	5	5	5	4	4	4
13.75°	12	10	9	8	7	6	5	5	4	4	4
12.5°	12	11	9	8	7	6	5	5	4	4	4
11.25°	13	11	10	8	7	6	5	5	4	4	4
10°	13	12	10	9	7	6	5	5	5	4	4
8.75°	14	12	10	9	8	7	6	5	5	4	4
7.5°	15	12	11	9	8	7	6	5	5	4	4
6.25°	15	13	11	9	8	7	6	5	5	4	4
5°	16	13	11	9	8	7	6	5	5	4	4
3.75°	16	13	11	10	8	7	6	5	5	4	4
2.5°	17	13	11	10	8	7	6	5	5	4	4
1.25°	17	13	12	10	8	7	6	5	5	4	4
0°	17	13	12	10	8	7	6	5	5	4	4
-1.25°	17	13	12	10	8	7	6	5	5	4	4
-2.5°	17	13	11	10	8	7	6	5	5	4	4
-3.75°	16	13	11	10	8	7	6	5	5	4	4
-5°	16	13	11	9	8	7	6	5	5	4	4
-6.25°	15	13	11	9	8	7	6	5	5	4	4
-7.5°	15	12	11	9	8	7	6	5	5	4	4
-8.75°	14	12	10	9	8	7	6	5	5	4	4
-10°	13	12	10	9	7	6	5	5	5	4	4
-11.25°	13	11	10	8	7	6	5	5	4	4	4
-12.5°	12	11	9	8	7	6	5	5	4	4	4
-13.75°	12	10	9	8	7	6	5	5	4	4	4
-15°	11	10	8	7	6	5	5	5	4	4	4
-16.25°	10	9	8	7	6	5	5	4	4	4	4
-17.5°	10	9	7	7	6	5	5	4	4	4	4
-18.75°	9	8	7	6	5	5	5	4	4	4	4
-20°	9	7	7	6	5	5	4	4	4	4	4
-21.25°	8	7	6	5	5	5	4	4	4	4	4

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	7	7	6	5	5	4	4	4	4	4	4
-23.75°	7	6	5	5	5	4	4	4	4	4	4
-25°	6	6	5	5	4	4	4	4	4	4	4
-26.25°	6	5	5	5	4	4	4	4	4	4	4
-27.5°	5	5	5	4	4	4	4	4	4	4	4
-28.75°	5	5	4	4	4	4	4	4	4	4	4
-30°	5	4	4	4	4	4	4	4	4	4	4
-31.25°	5	4	4	4	4	4	4	4	4	4	4
-32.5°	4	4	4	4	4	4	4	4	4	4	4
-33.75°	4	4	4	4	4	4	4	4	4	4	4
-35°	4	4	4	4	4	4	4	4	4	4	3
-36.25°	4	4	4	4	4	4	4	4	4	3	3
-37.5°	4	4	4	4	4	4	4	4	3	3	3
-38.75°	4	4	4	4	4	4	4	4	3	3	3
-40°	4	4	4	4	4	4	4	3	3	3	3
-41.25°	4	4	4	4	4	4	3	3	3	3	2
-42.5°	4	4	4	4	4	3	3	3	3	2	2
-43.75°	4	4	4	3	3	3	3	3	2	2	2
-45°	4	4	3	3	3	3	3	2	2	2	2
-46.25°	4	3	3	3	3	3	2	2	2	2	2
-47.5°	3	3	3	3	2	2	2	2	2	2	2
-48.75°	3	3	3	2	2	2	2	2	2	2	2
-50°	3	2	2	2	2	2	2	2	2	2	1
-51.25°	2	2	2	2	2	2	2	2	2	1	1
-52.5°	2	2	2	2	2	2	2	2	1	1	1
-53.75°	2	2	2	2	2	2	1	1	1	1	1
-55°	2	2	2	2	1	1	1	1	1	1	1
-56.25°	2	2	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	0
-71.25°	1	1	1	1	1	1	1	0	0	0	0
-72.5°	1	1	1	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	1	0	0	0	0	0	0	0	0	0	0
67.5°	1	1	1	0	0	0	0	0	0	0	0
66.25°	1	1	1	1	1	0	0	0	0	0	0
65°	1	1	1	1	1	1	1	0	0	0	0
63.75°	1	1	1	1	1	1	1	1	0	0	0
62.5°	1	1	1	1	1	1	1	1	1	0	0
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	2	1	1	1	1	1	1	1	1	1	1
46.25°	2	2	1	1	1	1	1	1	1	1	1
45°	2	2	2	1	1	1	1	1	1	1	1
43.75°	2	2	2	2	1	1	1	1	1	1	1
42.5°	2	2	2	2	2	1	1	1	1	1	1
41.25°	2	2	2	2	2	1	1	1	1	1	1
40°	2	2	2	2	2	2	1	1	1	1	1
38.75°	2	2	2	2	2	2	1	1	1	1	1
37.5°	3	2	2	2	2	2	2	1	1	1	1
36.25°	3	3	2	2	2	2	2	1	1	1	1
35°	3	3	2	2	2	2	2	2	1	1	1

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	3	3	3	2	2	2	2	2	1	1	1
32.5°	3	3	3	2	2	2	2	2	2	1	1
31.25°	4	3	3	3	2	2	2	2	2	1	1
30°	4	3	3	3	2	2	2	2	2	2	1
28.75°	4	4	3	3	3	2	2	2	2	2	1
27.5°	4	4	3	3	3	2	2	2	2	2	1
26.25°	4	4	4	3	3	3	2	2	2	2	1
25°	4	4	4	3	3	3	2	2	2	2	2
23.75°	4	4	4	3	3	3	2	2	2	2	2
22.5°	4	4	4	4	3	3	3	2	2	2	2
21.25°	4	4	4	4	3	3	3	2	2	2	2
20°	4	4	4	4	3	3	3	2	2	2	2
18.75°	4	4	4	4	4	3	3	2	2	2	2
17.5°	4	4	4	4	4	3	3	3	2	2	2
16.25°	4	4	4	4	4	3	3	3	2	2	2
15°	4	4	4	4	4	3	3	3	2	2	2
13.75°	4	4	4	4	4	4	3	3	2	2	2
12.5°	4	4	4	4	4	4	3	3	2	2	2
11.25°	4	4	4	4	4	4	3	3	2	2	2
10°	4	4	4	4	4	4	3	3	3	2	2
8.75°	4	4	4	4	4	4	3	3	3	2	2
7.5°	4	4	4	4	4	4	3	3	3	2	2
6.25°	4	4	4	4	4	4	3	3	3	2	2
5°	4	4	4	4	4	4	3	3	3	2	2
3.75°	4	4	4	4	4	4	3	3	3	2	2
2.5°	4	4	4	4	4	4	3	3	3	2	2
1.25°	4	4	4	4	4	4	3	3	3	2	2
0°	4	4	4	4	4	4	4	3	3	2	2
-1.25°	4	4	4	4	4	4	3	3	3	2	2
-2.5°	4	4	4	4	4	4	3	3	3	2	2
-3.75°	4	4	4	4	4	4	3	3	3	2	2
-5°	4	4	4	4	4	4	3	3	3	2	2
-6.25°	4	4	4	4	4	4	3	3	3	2	2
-7.5°	4	4	4	4	4	4	3	3	3	2	2
-8.75°	4	4	4	4	4	4	3	3	3	2	2
-10°	4	4	4	4	4	4	3	3	3	2	2
-11.25°	4	4	4	4	4	4	3	3	2	2	2
-12.5°	4	4	4	4	4	4	3	3	2	2	2
-13.75°	4	4	4	4	4	4	3	3	2	2	2
-15°	4	4	4	4	4	3	3	3	2	2	2
-16.25°	4	4	4	4	4	3	3	3	2	2	2
-17.5°	4	4	4	4	4	3	3	3	2	2	2
-18.75°	4	4	4	4	4	3	3	2	2	2	2
-20°	4	4	4	4	3	3	3	2	2	2	2
-21.25°	4	4	4	4	3	3	3	2	2	2	2

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	4	4	4	4	3	3	3	2	2	2	2
-23.75°	4	4	4	3	3	3	2	2	2	2	2
-25°	4	4	4	3	3	3	2	2	2	2	2
-26.25°	4	4	4	3	3	3	2	2	2	2	1
-27.5°	4	4	3	3	3	2	2	2	2	2	1
-28.75°	4	4	3	3	3	2	2	2	2	2	1
-30°	4	3	3	3	2	2	2	2	2	2	1
-31.25°	4	3	3	3	2	2	2	2	2	1	1
-32.5°	3	3	3	2	2	2	2	2	2	1	1
-33.75°	3	3	3	2	2	2	2	2	1	1	1
-35°	3	3	2	2	2	2	2	2	1	1	1
-36.25°	3	3	2	2	2	2	2	1	1	1	1
-37.5°	3	2	2	2	2	2	2	1	1	1	1
-38.75°	2	2	2	2	2	2	1	1	1	1	1
-40°	2	2	2	2	2	2	1	1	1	1	1
-41.25°	2	2	2	2	2	1	1	1	1	1	1
-42.5°	2	2	2	2	2	1	1	1	1	1	1
-43.75°	2	2	2	2	1	1	1	1	1	1	1
-45°	2	2	2	1	1	1	1	1	1	1	1
-46.25°	2	2	1	1	1	1	1	1	1	1	1
-47.5°	2	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	0	0
-63.75°	1	1	1	1	1	1	1	1	0	0	0
-65°	1	1	1	1	1	1	1	0	0	0	0
-66.25°	1	1	1	1	1	0	0	0	0	0	0
-67.5°	1	1	1	0	0	0	0	0	0	0	0
-68.75°	1	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	1	0	0	0	0	0	0	0	0	0	0
58.75°	1	0	0	0	0	0	0	0	0	0	0
57.5°	1	1	0	0	0	0	0	0	0	0	0
56.25°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	1	0	0	0	0	0	0	0
53.75°	1	1	1	1	0	0	0	0	0	0	0
52.5°	1	1	1	1	1	0	0	0	0	0	0
51.25°	1	1	1	1	1	0	0	0	0	0	0
50°	1	1	1	1	1	1	0	0	0	0	0
48.75°	1	1	1	1	1	1	0	0	0	0	0
47.5°	1	1	1	1	1	1	1	0	0	0	0
46.25°	1	1	1	1	1	1	1	0	0	0	0
45°	1	1	1	1	1	1	1	1	0	0	0
43.75°	1	1	1	1	1	1	1	1	0	0	0
42.5°	1	1	1	1	1	1	1	1	0	0	0
41.25°	1	1	1	1	1	1	1	1	1	0	0
40°	1	1	1	1	1	1	1	1	1	0	0
38.75°	1	1	1	1	1	1	1	1	1	0	0
37.5°	1	1	1	1	1	1	1	1	1	0	0
36.25°	1	1	1	1	1	1	1	1	1	1	0
35°	1	1	1	1	1	1	1	1	1	1	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	1	1	1	1	1	1	1	0
32.5°	1	1	1	1	1	1	1	1	1	1	0
31.25°	1	1	1	1	1	1	1	1	1	1	0
30°	1	1	1	1	1	1	1	1	1	1	1
28.75°	1	1	1	1	1	1	1	1	1	1	1
27.5°	1	1	1	1	1	1	1	1	1	1	1
26.25°	1	1	1	1	1	1	1	1	1	1	1
25°	1	1	1	1	1	1	1	1	1	1	1
23.75°	1	1	1	1	1	1	1	1	1	1	1
22.5°	1	1	1	1	1	1	1	1	1	1	1
21.25°	1	1	1	1	1	1	1	1	1	1	1
20°	2	1	1	1	1	1	1	1	1	1	1
18.75°	2	1	1	1	1	1	1	1	1	1	1
17.5°	2	1	1	1	1	1	1	1	1	1	1
16.25°	2	1	1	1	1	1	1	1	1	1	1
15°	2	1	1	1	1	1	1	1	1	1	1
13.75°	2	1	1	1	1	1	1	1	1	1	1
12.5°	2	2	1	1	1	1	1	1	1	1	1
11.25°	2	2	1	1	1	1	1	1	1	1	1
10°	2	2	1	1	1	1	1	1	1	1	1
8.75°	2	2	1	1	1	1	1	1	1	1	1
7.5°	2	2	1	1	1	1	1	1	1	1	1
6.25°	2	2	1	1	1	1	1	1	1	1	1
5°	2	2	1	1	1	1	1	1	1	1	1
3.75°	2	2	1	1	1	1	1	1	1	1	1
2.5°	2	2	1	1	1	1	1	1	1	1	1
1.25°	2	2	1	1	1	1	1	1	1	1	1
0°	2	2	1	1	1	1	1	1	1	1	1
-1.25°	2	2	1	1	1	1	1	1	1	1	1
-2.5°	2	2	1	1	1	1	1	1	1	1	1
-3.75°	2	2	1	1	1	1	1	1	1	1	1
-5°	2	2	1	1	1	1	1	1	1	1	1
-6.25°	2	2	1	1	1	1	1	1	1	1	1
-7.5°	2	2	1	1	1	1	1	1	1	1	1
-8.75°	2	2	1	1	1	1	1	1	1	1	1
-10°	2	2	1	1	1	1	1	1	1	1	1
-11.25°	2	2	1	1	1	1	1	1	1	1	1
-12.5°	2	2	1	1	1	1	1	1	1	1	1
-13.75°	2	1	1	1	1	1	1	1	1	1	1
-15°	2	1	1	1	1	1	1	1	1	1	1
-16.25°	2	1	1	1	1	1	1	1	1	1	1
-17.5°	2	1	1	1	1	1	1	1	1	1	1
-18.75°	2	1	1	1	1	1	1	1	1	1	1
-20°	2	1	1	1	1	1	1	1	1	1	1
-21.25°	1	1	1	1	1	1	1	1	1	1	1

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	1	1	1	1	1	1	1	1	1	1	1
-23.75°	1	1	1	1	1	1	1	1	1	1	1
-25°	1	1	1	1	1	1	1	1	1	1	1
-26.25°	1	1	1	1	1	1	1	1	1	1	1
-27.5°	1	1	1	1	1	1	1	1	1	1	1
-28.75°	1	1	1	1	1	1	1	1	1	1	1
-30°	1	1	1	1	1	1	1	1	1	1	1
-31.25°	1	1	1	1	1	1	1	1	1	1	0
-32.5°	1	1	1	1	1	1	1	1	1	1	0
-33.75°	1	1	1	1	1	1	1	1	1	1	0
-35°	1	1	1	1	1	1	1	1	1	1	0
-36.25°	1	1	1	1	1	1	1	1	1	1	0
-37.5°	1	1	1	1	1	1	1	1	1	0	0
-38.75°	1	1	1	1	1	1	1	1	1	0	0
-40°	1	1	1	1	1	1	1	1	1	0	0
-41.25°	1	1	1	1	1	1	1	1	1	0	0
-42.5°	1	1	1	1	1	1	1	1	0	0	0
-43.75°	1	1	1	1	1	1	1	1	0	0	0
-45°	1	1	1	1	1	1	1	1	0	0	0
-46.25°	1	1	1	1	1	1	1	0	0	0	0
-47.5°	1	1	1	1	1	1	1	0	0	0	0
-48.75°	1	1	1	1	1	1	0	0	0	0	0
-50°	1	1	1	1	1	1	0	0	0	0	0
-51.25°	1	1	1	1	1	0	0	0	0	0	0
-52.5°	1	1	1	1	1	0	0	0	0	0	0
-53.75°	1	1	1	1	0	0	0	0	0	0	0
-55°	1	1	1	1	0	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	1	0	0	0	0	0	0	0	0	0
-58.75°	1	0	0	0	0	0	0	0	0	0	0
-60°	1	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	1	0	0	0	0	0	0	0	0	0	0
20°	1	0	0	0	0	0	0	0	0	0	0
18.75°	1	0	0	0	0	0	0	0	0	0	0
17.5°	1	0	0	0	0	0	0	0	0	0	0
16.25°	1	0	0	0	0	0	0	0	0	0	0
15°	1	0	0	0	0	0	0	0	0	0	0
13.75°	1	0	0	0	0	0	0	0	0	0	0
12.5°	1	0	0	0	0	0	0	0	0	0	0
11.25°	1	0	0	0	0	0	0	0	0	0	0
10°	1	0	0	0	0	0	0	0	0	0	0
8.75°	1	0	0	0	0	0	0	0	0	0	0
7.5°	1	0	0	0	0	0	0	0	0	0	0
6.25°	1	0	0	0	0	0	0	0	0	0	0
5°	1	0	0	0	0	0	0	0	0	0	0
3.75°	1	0	0	0	0	0	0	0	0	0	0
2.5°	1	0	0	0	0	0	0	0	0	0	0
1.25°	1	0	0	0	0	0	0	0	0	0	0
0°	1	0	0	0	0	0	0	0	0	0	0
-1.25°	1	0	0	0	0	0	0	0	0	0	0
-2.5°	1	0	0	0	0	0	0	0	0	0	0
-3.75°	1	0	0	0	0	0	0	0	0	0	0
-5°	1	0	0	0	0	0	0	0	0	0	0
-6.25°	1	0	0	0	0	0	0	0	0	0	0
-7.5°	1	0	0	0	0	0	0	0	0	0	0
-8.75°	1	0	0	0	0	0	0	0	0	0	0
-10°	1	0	0	0	0	0	0	0	0	0	0
-11.25°	1	0	0	0	0	0	0	0	0	0	0
-12.5°	1	0	0	0	0	0	0	0	0	0	0
-13.75°	1	0	0	0	0	0	0	0	0	0	0
-15°	1	0	0	0	0	0	0	0	0	0	0
-16.25°	1	0	0	0	0	0	0	0	0	0	0
-17.5°	1	0	0	0	0	0	0	0	0	0	0
-18.75°	1	0	0	0	0	0	0	0	0	0	0
-20°	1	0	0	0	0	0	0	0	0	0	0
-21.25°	1	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0

REPORT NUMBER: P246988 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3036-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)