

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED4010-12-BK**

Test Date: 04/06/18

Test Information

Test Method: LM-79-08
Report Number: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-4)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/06/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4010-12-BK
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD BLACK
Light Source: (1) SORAA 4000K 95 CRI 10°NSP LED
SM16-07-10D-940-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004


Summary

Lumens per Lamp:	N/A	NEMA Type:	2H x 2V
Luminaire Lumens:	297 lumens	Max Intensity:	5541 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	37.1 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	12.3°H x 12.3°V	Field Angle (10%):	19.2°H x 19.2°V
Beam Lumens:	149.3 lumens	Field Lumens:	221.3 lumens
Beam Efficiency:	50.3%	Field Efficiency:	74.5%
Input Watts (W):	8		
Input Voltage (V):	12.0		
Input Current (Ain):	0.709		
Voltage Rise (V):	NR		
Power Factor:	0.9469		
Total Harmonic Distortion (THDi):	27.5		
Frequency (hertz):	60		
Stabilization Time:	0.5 HR		
Operation Time:	9 HR		
Ambient Temperature (°C):	24.9		
Test Distance:	25 FT		



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

Iso-Candela Plot




REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

Lumen Table

90																		
80	0.0	0.0		0.0		0.0		0.0		0.0		0.0		0.0		0.0		0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
60		0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0			
50	0.0	0.0	0.0	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.1	0.1	0.0	0.0	0.0	0.0		
40		0.0	0.0	0.1	0.1	0.3	0.4	0.4	0.4	0.4	0.3	0.1	0.1	0.0	0.0			
30	0.0	0.0	0.0	0.1	0.2	0.4	0.6	0.8	0.8	0.6	0.4	0.2	0.1	0.0	0.0	0.0		
20		0.0	0.0	0.1	0.3	0.6	1.5	3.9	3.9	1.5	0.6	0.3	0.1	0.0	0.0			
10	0.0	0.0	0.0	0.2	0.3	0.8	3.8	58.3	58.3	3.8	0.8	0.3	0.2	0.0	0.0	0.0		
0		0.0	0.0	0.2	0.3	0.8	3.8	58.3	58.3	3.8	0.8	0.3	0.2	0.0	0.0			
-10	0.0	0.0	0.0	0.1	0.3	0.6	1.5	3.9	3.9	1.5	0.6	0.3	0.1	0.0	0.0	0.0		
-20		0.0	0.0	0.1	0.2	0.4	0.6	0.8	0.8	0.6	0.4	0.2	0.1	0.0	0.0			
-30	0.0	0.0	0.0	0.1	0.1	0.3	0.4	0.4	0.4	0.4	0.3	0.1	0.1	0.0	0.0	0.0		
-40		0.0	0.0	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.1	0.1	0.0	0.0	0.0			
-50	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0		
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0			
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0			
-90	0.0	0.0		0.0		0.0		0.0		0.0		0.0		0.0		0.0		
	Horizontal Angle (degrees)																	


REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

Luminous Intensity Polar Plot



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

Luminous Intensity Plot



Beam:
H Angle: 12.3°
V Angle: 12.3°
Lumens: 149.3
Efficiency: 50.3%

Field:
H Angle: 19.2°
V Angle: 19.2°
Lumens: 221.3
Efficiency: 74.5%

Spill:
Lumens: 75.7
Efficiency: 25.5%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

FIELD
BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	1
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	1
45°	0	0	0	0	0	0	0	0	0	1	1
43.75°	0	0	0	0	0	0	0	0	0	1	1
42.5°	0	0	0	0	0	0	0	0	1	1	1
41.25°	0	0	0	0	0	0	0	1	1	1	1
40°	0	0	0	0	0	0	0	1	1	1	1
38.75°	0	0	0	0	0	0	1	1	1	1	1
37.5°	0	0	0	0	0	0	1	1	1	1	1
36.25°	0	0	0	0	0	1	1	1	1	1	1
35°	0	0	0	0	0	1	1	1	1	1	2

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	0	0	0	0	1	1	1	1	1	2	2
32.5°	0	0	0	0	1	1	1	1	1	2	2
31.25°	0	0	0	1	1	1	1	1	2	2	2
30°	0	0	0	1	1	1	1	1	2	2	3
28.75°	0	0	0	1	1	1	1	1	2	2	3
27.5°	0	0	1	1	1	1	1	2	2	2	3
26.25°	0	0	1	1	1	1	1	2	2	3	3
25°	0	0	1	1	1	1	2	2	2	3	3
23.75°	0	0	1	1	1	1	2	2	3	3	3
22.5°	0	1	1	1	1	1	2	2	3	3	3
21.25°	0	1	1	1	1	1	2	2	3	3	3
20°	0	1	1	1	1	2	2	3	3	3	3
18.75°	0	1	1	1	1	2	2	3	3	3	3
17.5°	0	1	1	1	1	2	2	3	3	3	3
16.25°	1	1	1	1	1	2	2	3	3	3	3
15°	1	1	1	1	2	2	2	3	3	3	4
13.75°	1	1	1	1	2	2	3	3	3	3	4
12.5°	1	1	1	1	2	2	3	3	3	3	4
11.25°	1	1	1	1	2	2	3	3	3	3	4
10°	1	1	1	1	2	2	3	3	3	3	4
8.75°	1	1	1	1	2	2	3	3	3	4	5
7.5°	1	1	1	1	2	2	3	3	3	4	5
6.25°	1	1	1	1	2	2	3	3	3	4	5
5°	1	1	1	1	2	2	3	3	3	4	5
3.75°	1	1	1	1	2	2	3	3	3	4	5
2.5°	1	1	1	1	2	2	3	3	3	4	5
1.25°	1	1	1	1	2	2	3	3	3	4	5
0°	1	1	1	2	2	3	3	3	3	4	5
-1.25°	1	1	1	1	2	2	3	3	3	4	5
-2.5°	1	1	1	1	2	2	3	3	3	4	5
-3.75°	1	1	1	1	2	2	3	3	3	4	5
-5°	1	1	1	1	2	2	3	3	3	4	5
-6.25°	1	1	1	1	2	2	3	3	3	4	5
-7.5°	1	1	1	1	2	2	3	3	3	4	5
-8.75°	1	1	1	1	2	2	3	3	3	4	5
-10°	1	1	1	1	2	2	3	3	3	3	4
-11.25°	1	1	1	1	2	2	3	3	3	3	4
-12.5°	1	1	1	1	2	2	3	3	3	3	4
-13.75°	1	1	1	1	2	2	3	3	3	3	4
-15°	1	1	1	1	2	2	2	3	3	3	4
-16.25°	1	1	1	1	1	2	2	3	3	3	3
-17.5°	0	1	1	1	1	2	2	3	3	3	3
-18.75°	0	1	1	1	1	2	2	3	3	3	3
-20°	0	1	1	1	1	2	2	3	3	3	3
-21.25°	0	1	1	1	1	1	2	2	3	3	3

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	0	1	1	1	1	1	2	2	3	3	3
-23.75°	0	0	1	1	1	1	2	2	3	3	3
-25°	0	0	1	1	1	1	2	2	2	3	3
-26.25°	0	0	1	1	1	1	1	2	2	3	3
-27.5°	0	0	1	1	1	1	1	2	2	2	3
-28.75°	0	0	0	1	1	1	1	1	2	2	3
-30°	0	0	0	1	1	1	1	1	2	2	3
-31.25°	0	0	0	1	1	1	1	1	2	2	2
-32.5°	0	0	0	0	1	1	1	1	1	2	2
-33.75°	0	0	0	0	1	1	1	1	1	2	2
-35°	0	0	0	0	0	1	1	1	1	1	2
-36.25°	0	0	0	0	0	1	1	1	1	1	1
-37.5°	0	0	0	0	0	0	1	1	1	1	1
-38.75°	0	0	0	0	0	0	1	1	1	1	1
-40°	0	0	0	0	0	0	0	1	1	1	1
-41.25°	0	0	0	0	0	0	0	1	1	1	1
-42.5°	0	0	0	0	0	0	0	0	1	1	1
-43.75°	0	0	0	0	0	0	0	0	0	1	1
-45°	0	0	0	0	0	0	0	0	0	1	1
-46.25°	0	0	0	0	0	0	0	0	0	0	1
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	1
55°	0	0	0	0	0	0	0	0	1	1	1
53.75°	0	0	0	0	0	0	1	1	1	1	1
52.5°	0	0	0	0	0	1	1	1	1	1	1
51.25°	0	0	0	1	1	1	1	1	1	1	1
50°	0	0	1	1	1	1	1	1	1	1	1
48.75°	0	1	1	1	1	1	1	1	1	2	2
47.5°	1	1	1	1	1	1	1	1	2	2	2
46.25°	1	1	1	1	1	1	2	2	2	2	3
45°	1	1	1	1	1	2	2	2	2	3	3
43.75°	1	1	1	1	2	2	2	2	3	3	3
42.5°	1	1	1	2	2	2	2	3	3	3	3
41.25°	1	1	2	2	2	2	3	3	3	3	3
40°	1	1	2	2	2	3	3	3	3	3	4
38.75°	1	2	2	2	3	3	3	3	3	4	4
37.5°	2	2	2	3	3	3	3	3	4	4	5
36.25°	2	2	3	3	3	3	3	4	4	5	5
35°	2	2	3	3	3	3	3	4	5	5	6

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	2	3	3	3	3	3	4	5	5	6	6
32.5°	3	3	3	3	3	4	4	5	5	6	6
31.25°	3	3	3	3	4	4	5	5	6	6	6
30°	3	3	3	3	4	5	5	6	6	6	7
28.75°	3	3	3	4	4	5	5	6	6	7	7
27.5°	3	3	3	4	5	5	6	6	7	7	8
26.25°	3	3	4	4	5	6	6	6	7	7	8
25°	3	3	4	5	5	6	6	7	7	8	9
23.75°	3	4	4	5	6	6	6	7	7	8	9
22.5°	3	4	5	5	6	6	7	7	8	9	10
21.25°	3	4	5	5	6	6	7	7	8	9	10
20°	4	5	5	6	6	7	7	8	9	10	10
18.75°	4	5	5	6	6	7	7	8	9	10	11
17.5°	4	5	6	6	6	7	8	9	9	10	11
16.25°	4	5	6	6	7	7	8	9	10	11	11
15°	5	5	6	6	7	7	8	9	10	11	11
13.75°	5	5	6	6	7	8	9	9	10	11	12
12.5°	5	6	6	6	7	8	9	10	11	11	12
11.25°	5	6	6	7	7	8	9	10	11	11	12
10°	5	6	6	7	7	8	9	10	11	12	12
8.75°	5	6	6	7	7	8	9	10	11	12	12
7.5°	5	6	6	7	8	9	10	11	11	12	12
6.25°	5	6	6	7	8	9	10	11	11	12	13
5°	5	6	6	7	8	9	10	11	11	12	13
3.75°	5	6	6	7	8	9	10	11	11	12	13
2.5°	5	6	6	7	8	9	10	11	11	12	13
1.25°	5	6	6	7	8	9	10	11	11	12	13
0°	6	6	7	7	8	9	10	11	12	12	13
-1.25°	5	6	6	7	8	9	10	11	11	12	13
-2.5°	5	6	6	7	8	9	10	11	11	12	13
-3.75°	5	6	6	7	8	9	10	11	11	12	13
-5°	5	6	6	7	8	9	10	11	11	12	13
-6.25°	5	6	6	7	8	9	10	11	11	12	13
-7.5°	5	6	6	7	8	9	10	11	11	12	12
-8.75°	5	6	6	7	7	8	9	10	11	12	12
-10°	5	6	6	7	7	8	9	10	11	12	12
-11.25°	5	6	6	7	7	8	9	10	11	11	12
-12.5°	5	6	6	6	7	8	9	10	11	11	12
-13.75°	5	5	6	6	7	8	9	9	10	11	12
-15°	5	5	6	6	7	7	8	9	10	11	11
-16.25°	4	5	6	6	7	7	8	9	10	11	11
-17.5°	4	5	6	6	6	7	8	9	9	10	11
-18.75°	4	5	5	6	6	7	7	8	9	10	11
-20°	4	5	5	6	6	7	7	8	9	10	10
-21.25°	3	4	5	5	6	6	7	7	8	9	10

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	3	4	5	5	6	6	7	7	8	9	10
-23.75°	3	4	4	5	6	6	6	7	7	8	9
-25°	3	3	4	5	5	6	6	7	7	8	9
-26.25°	3	3	4	4	5	6	6	6	7	7	8
-27.5°	3	3	3	4	5	5	6	6	7	7	8
-28.75°	3	3	3	4	4	5	5	6	6	7	7
-30°	3	3	3	3	4	5	5	6	6	6	7
-31.25°	3	3	3	3	4	4	5	5	6	6	6
-32.5°	3	3	3	3	3	4	4	5	5	6	6
-33.75°	2	3	3	3	3	3	4	5	5	6	6
-35°	2	2	3	3	3	3	3	4	5	5	6
-36.25°	2	2	3	3	3	3	3	4	4	5	5
-37.5°	2	2	2	3	3	3	3	3	4	4	5
-38.75°	1	2	2	2	3	3	3	3	3	4	4
-40°	1	1	2	2	2	3	3	3	3	3	4
-41.25°	1	1	2	2	2	2	3	3	3	3	3
-42.5°	1	1	1	2	2	2	2	3	3	3	3
-43.75°	1	1	1	1	2	2	2	2	3	3	3
-45°	1	1	1	1	1	2	2	2	2	3	3
-46.25°	1	1	1	1	1	1	2	2	2	2	3
-47.5°	1	1	1	1	1	1	1	1	2	2	2
-48.75°	0	1	1	1	1	1	1	1	1	2	2
-50°	0	0	1	1	1	1	1	1	1	1	1
-51.25°	0	0	0	1	1	1	1	1	1	1	1
-52.5°	0	0	0	0	0	1	1	1	1	1	1
-53.75°	0	0	0	0	0	0	1	1	1	1	1
-55°	0	0	0	0	0	0	0	0	1	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	1
60°	0	0	0	0	0	0	1	1	1	1	1
58.75°	0	0	0	1	1	1	1	1	1	1	1
57.5°	0	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	2	2	2
53.75°	1	1	1	1	1	1	2	2	2	2	2
52.5°	1	1	1	2	2	2	2	2	2	3	3
51.25°	1	2	2	2	2	2	2	3	3	3	3
50°	2	2	2	2	3	3	3	3	3	3	3
48.75°	2	2	3	3	3	3	3	3	3	3	3
47.5°	2	3	3	3	3	3	3	3	3	4	4
46.25°	3	3	3	3	3	3	3	4	4	4	5
45°	3	3	3	3	3	4	4	4	5	5	5
43.75°	3	3	3	4	4	4	5	5	5	6	6
42.5°	3	3	4	4	5	5	5	6	6	6	6
41.25°	3	4	4	5	5	5	6	6	6	6	7
40°	4	5	5	5	6	6	6	6	7	7	7
38.75°	5	5	5	6	6	6	7	7	7	7	8
37.5°	5	6	6	6	6	7	7	7	8	8	9
36.25°	6	6	6	6	7	7	8	8	9	9	10
35°	6	6	6	7	7	8	8	9	9	10	10

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	6	6	7	7	8	8	9	10	10	11	11
32.5°	6	7	7	8	9	9	10	10	11	11	11
31.25°	7	7	8	9	9	10	10	11	11	12	12
30°	7	8	9	9	10	11	11	11	12	12	13
28.75°	8	8	9	10	11	11	11	12	12	13	13
27.5°	8	9	10	10	11	11	12	12	13	13	14
26.25°	9	10	10	11	11	12	12	13	13	14	14
25°	9	10	11	11	12	12	13	13	14	14	15
23.75°	10	11	11	12	12	13	13	14	14	15	15
22.5°	10	11	11	12	13	13	14	14	15	15	16
21.25°	11	11	12	12	13	14	14	15	15	16	17
20°	11	12	12	13	14	14	15	15	16	17	18
18.75°	11	12	12	13	14	14	15	16	17	18	20
17.5°	12	12	13	14	14	15	15	17	18	19	21
16.25°	12	12	13	14	14	15	16	17	19	20	22
15°	12	13	14	14	15	15	17	18	20	21	23
13.75°	12	13	14	14	15	16	17	19	21	23	25
12.5°	12	13	14	15	15	17	18	20	22	24	26
11.25°	13	14	14	15	16	17	19	21	22	25	27
10°	13	14	14	15	16	18	19	21	23	26	29
8.75°	13	14	15	15	17	18	20	22	24	27	30
7.5°	13	14	15	16	17	19	21	23	25	28	31
6.25°	14	14	15	16	17	19	21	23	26	29	32
5°	14	14	15	16	18	19	21	24	26	29	33
3.75°	14	14	15	16	18	20	22	24	26	30	34
2.5°	14	14	15	16	18	20	22	24	27	31	35
1.25°	14	14	15	16	18	20	22	24	27	31	35
0°	14	15	15	17	18	20	22	25	27	31	35
-1.25°	14	14	15	16	18	20	22	24	27	31	35
-2.5°	14	14	15	16	18	20	22	24	27	31	35
-3.75°	14	14	15	16	18	20	22	24	26	30	34
-5°	14	14	15	16	18	19	21	24	26	29	33
-6.25°	14	14	15	16	17	19	21	23	26	29	32
-7.5°	13	14	15	16	17	19	21	23	25	28	31
-8.75°	13	14	15	15	17	18	20	22	24	27	30
-10°	13	14	14	15	16	18	19	21	23	26	29
-11.25°	13	14	14	15	16	17	19	21	22	25	27
-12.5°	12	13	14	15	15	17	18	20	22	24	26
-13.75°	12	13	14	14	15	16	17	19	21	23	25
-15°	12	13	14	14	15	15	17	18	20	21	23
-16.25°	12	12	13	14	14	15	16	17	19	20	22
-17.5°	12	12	13	14	14	15	15	17	18	19	21
-18.75°	11	12	12	13	14	14	15	16	17	18	20
-20°	11	12	12	13	14	14	15	15	16	17	18
-21.25°	11	11	12	12	13	14	14	15	15	16	17

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	10	11	11	12	13	13	14	14	15	15	16
-23.75°	10	11	11	12	12	13	13	14	14	15	15
-25°	9	10	11	11	12	12	13	13	14	14	15
-26.25°	9	10	10	11	11	12	12	13	13	14	14
-27.5°	8	9	10	10	11	11	12	12	13	13	14
-28.75°	8	8	9	10	11	11	11	12	12	13	13
-30°	7	8	9	9	10	11	11	11	12	12	13
-31.25°	7	7	8	9	9	10	10	11	11	12	12
-32.5°	6	7	7	8	9	9	10	10	11	11	11
-33.75°	6	6	7	7	8	8	9	10	10	11	11
-35°	6	6	6	7	7	8	8	9	9	10	10
-36.25°	6	6	6	6	7	7	8	8	9	9	10
-37.5°	5	6	6	6	6	7	7	7	8	8	9
-38.75°	5	5	5	6	6	6	7	7	7	7	8
-40°	4	5	5	5	6	6	6	6	7	7	7
-41.25°	3	4	4	5	5	5	6	6	6	6	7
-42.5°	3	3	4	4	5	5	5	6	6	6	6
-43.75°	3	3	3	4	4	4	5	5	5	6	6
-45°	3	3	3	3	3	4	4	4	5	5	5
-46.25°	3	3	3	3	3	3	3	4	4	4	5
-47.5°	2	3	3	3	3	3	3	3	3	4	4
-48.75°	2	2	3	3	3	3	3	3	3	3	3
-50°	2	2	2	2	3	3	3	3	3	3	3
-51.25°	1	2	2	2	2	2	2	3	3	3	3
-52.5°	1	1	1	2	2	2	2	2	2	3	3
-53.75°	1	1	1	1	1	1	2	2	2	2	2
-55°	1	1	1	1	1	1	1	1	2	2	2
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	0	1	1	1	1	1	1	1	1	1	1
-58.75°	0	0	0	1	1	1	1	1	1	1	1
-60°	0	0	0	0	0	0	1	1	1	1	1
-61.25°	0	0	0	0	0	0	0	0	0	0	1
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	2	2	2	2	2	2
56.25°	1	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	3	3	3	3	3
53.75°	2	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	4
50°	3	3	3	3	3	4	4	4	4	4	5
48.75°	3	4	4	4	4	5	5	5	5	5	5
47.5°	4	5	5	5	5	5	5	6	6	6	6
46.25°	5	5	5	6	6	6	6	6	6	6	6
45°	5	6	6	6	6	6	6	6	7	7	7
43.75°	6	6	6	6	7	7	7	7	7	7	7
42.5°	6	7	7	7	7	7	8	8	8	8	8
41.25°	7	7	7	8	8	8	9	9	9	9	9
40°	7	8	8	9	9	9	9	10	10	10	10
38.75°	8	9	9	9	10	10	10	11	11	11	11
37.5°	9	10	10	10	11	11	11	11	11	12	12
36.25°	10	10	11	11	11	11	12	12	12	12	12
35°	11	11	11	12	12	12	12	12	13	13	13

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	11	12	12	12	12	13	13	13	14	14	14
32.5°	12	12	12	13	13	14	14	14	14	14	15
31.25°	12	13	13	14	14	14	14	15	15	15	15
30°	13	14	14	14	14	15	15	15	16	16	17
28.75°	14	14	14	15	15	15	16	17	17	18	18
27.5°	14	15	15	15	16	17	17	18	19	19	20
26.25°	15	15	16	17	17	18	19	20	21	21	22
25°	15	16	17	18	19	20	21	22	22	23	24
23.75°	16	17	18	19	20	21	23	24	25	26	27
22.5°	17	18	20	21	22	23	25	26	27	29	30
21.25°	18	20	21	22	24	25	27	29	30	32	34
20°	20	21	23	24	26	28	30	32	34	37	41
18.75°	21	23	24	26	28	31	33	36	41	45	49
17.5°	22	24	26	28	31	34	38	43	49	53	61
16.25°	24	26	28	31	34	39	45	51	58	67	75
15°	25	28	31	34	39	46	52	61	72	81	90
13.75°	27	30	33	38	45	52	63	74	84	95	105
12.5°	29	32	36	43	51	61	74	86	98	110	121
11.25°	30	34	41	49	58	72	84	98	111	124	148
10°	32	37	45	53	67	81	95	110	124	152	178
8.75°	34	41	49	61	75	90	105	121	148	178	215
7.5°	35	44	53	67	82	98	115	138	171	204	291
6.25°	38	47	58	73	89	106	123	157	191	267	360
5°	40	50	62	78	95	112	136	172	220	321	420
3.75°	42	51	66	82	99	117	148	185	260	366	558
2.5°	43	53	68	85	103	121	156	194	290	399	671
1.25°	44	54	70	86	105	123	161	200	308	419	781
0°	45	54	71	87	106	124	163	202	314	426	827
-1.25°	44	54	70	86	105	123	161	200	308	419	781
-2.5°	43	53	68	85	103	121	156	194	290	399	671
-3.75°	42	51	66	82	99	117	148	185	260	366	558
-5°	40	50	62	78	95	112	136	172	220	321	420
-6.25°	38	47	58	73	89	106	123	157	191	267	360
-7.5°	35	44	53	67	82	98	115	138	171	204	291
-8.75°	34	41	49	61	75	90	105	121	148	178	215
-10°	32	37	45	53	67	81	95	110	124	152	178
-11.25°	30	34	41	49	58	72	84	98	111	124	148
-12.5°	29	32	36	43	51	61	74	86	98	110	121
-13.75°	27	30	33	38	45	52	63	74	84	95	105
-15°	25	28	31	34	39	46	52	61	72	81	90
-16.25°	24	26	28	31	34	39	45	51	58	67	75
-17.5°	22	24	26	28	31	34	38	43	49	53	61
-18.75°	21	23	24	26	28	31	33	36	41	45	49
-20°	20	21	23	24	26	28	30	32	34	37	41
-21.25°	18	20	21	22	24	25	27	29	30	32	34

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	17	18	20	21	22	23	25	26	27	29	30
-23.75°	16	17	18	19	20	21	23	24	25	26	27
-25°	15	16	17	18	19	20	21	22	22	23	24
-26.25°	15	15	16	17	17	18	19	20	21	21	22
-27.5°	14	15	15	15	16	17	17	18	19	19	20
-28.75°	14	14	14	15	15	15	16	17	17	18	18
-30°	13	14	14	14	14	15	15	15	16	16	17
-31.25°	12	13	13	14	14	14	14	15	15	15	15
-32.5°	12	12	12	13	13	14	14	14	14	14	15
-33.75°	11	12	12	12	12	13	13	13	14	14	14
-35°	11	11	11	12	12	12	12	12	13	13	13
-36.25°	10	10	11	11	11	11	12	12	12	12	12
-37.5°	9	10	10	10	11	11	11	11	11	12	12
-38.75°	8	9	9	9	10	10	10	11	11	11	11
-40°	7	8	8	9	9	9	9	10	10	10	10
-41.25°	7	7	7	8	8	8	9	9	9	9	9
-42.5°	6	7	7	7	7	7	8	8	8	8	8
-43.75°	6	6	6	6	7	7	7	7	7	7	7
-45°	5	6	6	6	6	6	6	6	7	7	7
-46.25°	5	5	5	6	6	6	6	6	6	6	6
-47.5°	4	5	5	5	5	5	5	6	6	6	6
-48.75°	3	4	4	4	4	5	5	5	5	5	5
-50°	3	3	3	3	3	4	4	4	4	4	5
-51.25°	3	3	3	3	3	3	3	3	3	3	4
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	2	3	3	3	3	3	3	3	3	3	3
-55°	2	2	2	2	2	2	3	3	3	3	3
-56.25°	1	2	2	2	2	2	2	2	2	2	2
-57.5°	1	1	1	1	1	2	2	2	2	2	2
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	0	0	0	0	1	1	1	1	1	1	1
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	1	0	0	0	0
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	2	1	1	1	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	3	2	2	2	2
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	5	5	5	5	5	5	5	5	5	5	5
48.75°	5	5	5	5	5	5	6	5	5	5	5
47.5°	6	6	6	6	6	6	6	6	6	6	6
46.25°	6	6	6	6	6	6	7	6	6	6	6
45°	7	7	7	7	7	7	7	7	7	7	7
43.75°	8	8	8	8	8	8	8	8	8	8	8
42.5°	9	9	9	9	9	9	9	9	9	9	9
41.25°	10	10	10	10	10	10	10	10	10	10	10
40°	11	11	11	11	11	11	11	11	11	11	11
38.75°	11	11	11	11	11	11	12	11	11	11	11
37.5°	12	12	12	12	12	12	12	12	12	12	12
36.25°	12	13	13	13	13	13	13	13	13	13	13
35°	13	14	14	14	14	14	14	14	14	14	14

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	14	14	14	14	14	14	15	14	14	14	14
32.5°	15	15	15	15	15	15	15	15	15	15	15
31.25°	16	16	16	16	16	16	17	16	16	16	16
30°	17	17	18	18	18	18	18	18	18	18	18
28.75°	19	19	19	20	20	20	20	20	20	20	19
27.5°	21	21	21	22	22	22	22	22	22	22	21
26.25°	23	23	24	24	24	24	25	24	24	24	24
25°	25	26	26	26	27	27	27	27	27	26	26
23.75°	28	29	29	30	31	31	31	31	31	30	29
22.5°	31	32	33	34	35	35	35	35	35	34	33
21.25°	35	38	40	42	43	44	45	44	43	42	40
20°	44	47	50	51	53	54	54	54	53	51	50
18.75°	53	58	62	66	68	70	71	70	68	66	62
17.5°	67	73	78	82	85	86	87	86	85	82	78
16.25°	82	89	95	99	103	105	106	105	103	99	95
15°	98	106	112	117	121	123	124	123	121	117	112
13.75°	115	123	136	148	156	161	163	161	156	148	136
12.5°	138	157	172	185	194	200	202	200	194	185	172
11.25°	171	191	220	260	290	308	314	308	290	260	220
10°	204	267	321	366	399	419	426	419	399	366	321
8.75°	291	360	420	558	671	781	827	781	671	558	420
7.5°	373	493	695	1020	1295	1533	1615	1533	1295	1020	695
6.25°	493	786	1220	1785	2253	2571	2682	2571	2253	1785	1220
5°	695	1220	1958	2684	3252	3619	3748	3619	3252	2684	1958
3.75°	1020	1785	2684	3494	4089	4463	4570	4463	4089	3494	2684
2.5°	1295	2253	3252	4089	4683	5030	5125	5030	4683	4089	3252
1.25°	1533	2571	3619	4463	5030	5327	5418	5327	5030	4463	3619
0°	1615	2682	3748	4570	5125	5418	5541	5418	5125	4570	3748
-1.25°	1533	2571	3619	4463	5030	5327	5418	5327	5030	4463	3619
-2.5°	1295	2253	3252	4089	4683	5030	5125	5030	4683	4089	3252
-3.75°	1020	1785	2684	3494	4089	4463	4570	4463	4089	3494	2684
-5°	695	1220	1958	2684	3252	3619	3748	3619	3252	2684	1958
-6.25°	493	786	1220	1785	2253	2571	2682	2571	2253	1785	1220
-7.5°	373	493	695	1020	1295	1533	1615	1533	1295	1020	695
-8.75°	291	360	420	558	671	781	827	781	671	558	420
-10°	204	267	321	366	399	419	426	419	399	366	321
-11.25°	171	191	220	260	290	308	314	308	290	260	220
-12.5°	138	157	172	185	194	200	202	200	194	185	172
-13.75°	115	123	136	148	156	161	163	161	156	148	136
-15°	98	106	112	117	121	123	124	123	121	117	112
-16.25°	82	89	95	99	103	105	106	105	103	99	95
-17.5°	67	73	78	82	85	86	87	86	85	82	78
-18.75°	53	58	62	66	68	70	71	70	68	66	62
-20°	44	47	50	51	53	54	54	54	53	51	50
-21.25°	35	38	40	42	43	44	45	44	43	42	40

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	31	32	33	34	35	35	35	35	35	34	33
-23.75°	28	29	29	30	31	31	31	31	31	30	29
-25°	25	26	26	26	27	27	27	27	27	26	26
-26.25°	23	23	24	24	24	24	25	24	24	24	24
-27.5°	21	21	21	22	22	22	22	22	22	22	21
-28.75°	19	19	19	20	20	20	20	20	20	20	19
-30°	17	17	18	18	18	18	18	18	18	18	18
-31.25°	16	16	16	16	16	16	17	16	16	16	16
-32.5°	15	15	15	15	15	15	15	15	15	15	15
-33.75°	14	14	14	14	14	14	15	14	14	14	14
-35°	13	14	14	14	14	14	14	14	14	14	14
-36.25°	12	13	13	13	13	13	13	13	13	13	13
-37.5°	12	12	12	12	12	12	12	12	12	12	12
-38.75°	11	11	11	11	11	11	12	11	11	11	11
-40°	11	11	11	11	11	11	11	11	11	11	11
-41.25°	10	10	10	10	10	10	10	10	10	10	10
-42.5°	9	9	9	9	9	9	9	9	9	9	9
-43.75°	8	8	8	8	8	8	8	8	8	8	8
-45°	7	7	7	7	7	7	7	7	7	7	7
-46.25°	6	6	6	6	6	6	7	6	6	6	6
-47.5°	6	6	6	6	6	6	6	6	6	6	6
-48.75°	5	5	5	5	5	5	6	5	5	5	5
-50°	5	5	5	5	5	5	5	5	5	5	5
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	2	2	2	2	2	3	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	1	1	1	1	1	1	2	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	0	0	0	0	0	0	1	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	1	1	1	1	1	1	1	1	1	0	0
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	2	2	2	2	2	2	2	1	1	1
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	3	3	3	3	2	2	2	2
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	4	4	4	3	3	3	3	3	3	3	3
50°	5	5	5	4	4	4	4	4	3	3	3
48.75°	5	5	5	5	5	5	5	5	4	4	4
47.5°	6	6	6	6	6	6	5	5	5	5	5
46.25°	6	6	6	6	6	6	6	6	6	6	5
45°	7	7	7	7	7	6	6	6	6	6	6
43.75°	8	8	7	7	7	7	7	7	7	6	6
42.5°	9	9	8	8	8	8	8	7	7	7	7
41.25°	10	10	9	9	9	9	9	8	8	8	7
40°	11	11	10	10	10	10	9	9	9	9	8
38.75°	11	11	11	11	11	11	10	10	10	9	9
37.5°	12	12	12	12	11	11	11	11	11	10	10
36.25°	13	12	12	12	12	12	12	11	11	11	11
35°	14	13	13	13	13	12	12	12	12	12	11

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	14	14	14	14	14	13	13	13	12	12	12
32.5°	15	15	15	14	14	14	14	14	13	13	12
31.25°	16	16	15	15	15	15	14	14	14	14	13
30°	17	17	17	16	16	15	15	15	14	14	14
28.75°	19	19	18	18	17	17	16	15	15	15	14
27.5°	21	21	20	19	19	18	17	17	16	15	15
26.25°	23	23	22	21	21	20	19	18	17	17	16
25°	26	25	24	23	22	22	21	20	19	18	17
23.75°	29	28	27	26	25	24	23	21	20	19	18
22.5°	32	31	30	29	27	26	25	23	22	21	20
21.25°	38	35	34	32	30	29	27	25	24	22	21
20°	47	44	41	37	34	32	30	28	26	24	23
18.75°	58	53	49	45	41	36	33	31	28	26	24
17.5°	73	67	61	53	49	43	38	34	31	28	26
16.25°	89	82	75	67	58	51	45	39	34	31	28
15°	106	98	90	81	72	61	52	46	39	34	31
13.75°	123	115	105	95	84	74	63	52	45	38	33
12.5°	157	138	121	110	98	86	74	61	51	43	36
11.25°	191	171	148	124	111	98	84	72	58	49	41
10°	267	204	178	152	124	110	95	81	67	53	45
8.75°	360	291	215	178	148	121	105	90	75	61	49
7.5°	493	373	291	204	171	138	115	98	82	67	53
6.25°	786	493	360	267	191	157	123	106	89	73	58
5°	1220	695	420	321	220	172	136	112	95	78	62
3.75°	1785	1020	558	366	260	185	148	117	99	82	66
2.5°	2253	1295	671	399	290	194	156	121	103	85	68
1.25°	2571	1533	781	419	308	200	161	123	105	86	70
0°	2682	1615	827	426	314	202	163	124	106	87	71
-1.25°	2571	1533	781	419	308	200	161	123	105	86	70
-2.5°	2253	1295	671	399	290	194	156	121	103	85	68
-3.75°	1785	1020	558	366	260	185	148	117	99	82	66
-5°	1220	695	420	321	220	172	136	112	95	78	62
-6.25°	786	493	360	267	191	157	123	106	89	73	58
-7.5°	493	373	291	204	171	138	115	98	82	67	53
-8.75°	360	291	215	178	148	121	105	90	75	61	49
-10°	267	204	178	152	124	110	95	81	67	53	45
-11.25°	191	171	148	124	111	98	84	72	58	49	41
-12.5°	157	138	121	110	98	86	74	61	51	43	36
-13.75°	123	115	105	95	84	74	63	52	45	38	33
-15°	106	98	90	81	72	61	52	46	39	34	31
-16.25°	89	82	75	67	58	51	45	39	34	31	28
-17.5°	73	67	61	53	49	43	38	34	31	28	26
-18.75°	58	53	49	45	41	36	33	31	28	26	24
-20°	47	44	41	37	34	32	30	28	26	24	23
-21.25°	38	35	34	32	30	29	27	25	24	22	21

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	32	31	30	29	27	26	25	23	22	21	20
-23.75°	29	28	27	26	25	24	23	21	20	19	18
-25°	26	25	24	23	22	22	21	20	19	18	17
-26.25°	23	23	22	21	21	20	19	18	17	17	16
-27.5°	21	21	20	19	19	18	17	17	16	15	15
-28.75°	19	19	18	18	17	17	16	15	15	15	14
-30°	17	17	17	16	16	15	15	15	14	14	14
-31.25°	16	16	15	15	15	15	14	14	14	14	13
-32.5°	15	15	15	14	14	14	14	14	13	13	12
-33.75°	14	14	14	14	14	13	13	13	12	12	12
-35°	14	13	13	13	13	12	12	12	12	12	11
-36.25°	13	12	12	12	12	12	12	11	11	11	11
-37.5°	12	12	12	12	11	11	11	11	11	10	10
-38.75°	11	11	11	11	11	11	10	10	10	9	9
-40°	11	11	10	10	10	10	9	9	9	9	8
-41.25°	10	10	9	9	9	9	9	8	8	8	7
-42.5°	9	9	8	8	8	8	8	7	7	7	7
-43.75°	8	8	7	7	7	7	7	7	7	6	6
-45°	7	7	7	7	7	6	6	6	6	6	6
-46.25°	6	6	6	6	6	6	6	6	6	6	5
-47.5°	6	6	6	6	6	6	5	5	5	5	5
-48.75°	5	5	5	5	5	5	5	5	4	4	4
-50°	5	5	5	4	4	4	4	4	3	3	3
-51.25°	4	4	4	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	1	1	1	0	0	0	0	0	0	0	0
60°	1	1	1	1	1	1	1	0	0	0	0
58.75°	1	1	1	1	1	1	1	1	1	1	0
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	2	1	1	1	1	1	1	1	1	1	1
55°	2	2	2	2	2	1	1	1	1	1	1
53.75°	3	2	2	2	2	2	2	1	1	1	1
52.5°	3	3	3	3	2	2	2	2	2	2	1
51.25°	3	3	3	3	3	3	2	2	2	2	2
50°	3	3	3	3	3	3	3	3	3	2	2
48.75°	4	3	3	3	3	3	3	3	3	3	3
47.5°	5	4	4	4	3	3	3	3	3	3	3
46.25°	5	5	5	4	4	4	3	3	3	3	3
45°	6	5	5	5	5	4	4	4	3	3	3
43.75°	6	6	6	6	5	5	5	4	4	4	3
42.5°	7	6	6	6	6	6	5	5	5	4	4
41.25°	7	7	7	6	6	6	6	5	5	5	4
40°	8	7	7	7	7	6	6	6	6	5	5
38.75°	9	8	8	7	7	7	7	6	6	6	5
37.5°	10	9	9	8	8	7	7	7	6	6	6
36.25°	10	10	10	9	9	8	8	7	7	6	6
35°	11	11	10	10	9	9	8	8	7	7	6

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	12	11	11	11	10	10	9	8	8	7	7
32.5°	12	12	11	11	11	10	10	9	9	8	7
31.25°	13	12	12	12	11	11	10	10	9	9	8
30°	14	13	13	12	12	11	11	11	10	9	9
28.75°	14	14	13	13	12	12	11	11	11	10	9
27.5°	15	14	14	13	13	12	12	11	11	10	10
26.25°	15	15	14	14	13	13	12	12	11	11	10
25°	16	15	15	14	14	13	13	12	12	11	11
23.75°	17	16	15	15	14	14	13	13	12	12	11
22.5°	18	17	16	15	15	14	14	13	13	12	11
21.25°	20	18	17	16	15	15	14	14	13	12	12
20°	21	20	18	17	16	15	15	14	14	13	12
18.75°	23	21	20	18	17	16	15	14	14	13	12
17.5°	24	22	21	19	18	17	15	15	14	14	13
16.25°	26	24	22	20	19	17	16	15	14	14	13
15°	28	25	23	21	20	18	17	15	15	14	14
13.75°	30	27	25	23	21	19	17	16	15	14	14
12.5°	32	29	26	24	22	20	18	17	15	15	14
11.25°	34	30	27	25	22	21	19	17	16	15	14
10°	37	32	29	26	23	21	19	18	16	15	14
8.75°	41	34	30	27	24	22	20	18	17	15	15
7.5°	44	35	31	28	25	23	21	19	17	16	15
6.25°	47	38	32	29	26	23	21	19	17	16	15
5°	50	40	33	29	26	24	21	19	18	16	15
3.75°	51	42	34	30	26	24	22	20	18	16	15
2.5°	53	43	35	31	27	24	22	20	18	16	15
1.25°	54	44	35	31	27	24	22	20	18	16	15
0°	54	45	35	31	27	25	22	20	18	17	15
-1.25°	54	44	35	31	27	24	22	20	18	16	15
-2.5°	53	43	35	31	27	24	22	20	18	16	15
-3.75°	51	42	34	30	26	24	22	20	18	16	15
-5°	50	40	33	29	26	24	21	19	18	16	15
-6.25°	47	38	32	29	26	23	21	19	17	16	15
-7.5°	44	35	31	28	25	23	21	19	17	16	15
-8.75°	41	34	30	27	24	22	20	18	17	15	15
-10°	37	32	29	26	23	21	19	18	16	15	14
-11.25°	34	30	27	25	22	21	19	17	16	15	14
-12.5°	32	29	26	24	22	20	18	17	15	15	14
-13.75°	30	27	25	23	21	19	17	16	15	14	14
-15°	28	25	23	21	20	18	17	15	15	14	14
-16.25°	26	24	22	20	19	17	16	15	14	14	13
-17.5°	24	22	21	19	18	17	15	15	14	14	13
-18.75°	23	21	20	18	17	16	15	14	14	13	12
-20°	21	20	18	17	16	15	15	14	14	13	12
-21.25°	20	18	17	16	15	15	14	14	13	12	12

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	18	17	16	15	15	14	14	13	13	12	11
-23.75°	17	16	15	15	14	14	13	13	12	12	11
-25°	16	15	15	14	14	13	13	12	12	11	11
-26.25°	15	15	14	14	13	13	12	12	11	11	10
-27.5°	15	14	14	13	13	12	12	11	11	10	10
-28.75°	14	14	13	13	12	12	11	11	11	10	9
-30°	14	13	13	12	12	11	11	11	10	9	9
-31.25°	13	12	12	12	11	11	10	10	9	9	8
-32.5°	12	12	11	11	11	10	10	9	9	8	7
-33.75°	12	11	11	11	10	10	9	8	8	7	7
-35°	11	11	10	10	9	9	8	8	7	7	6
-36.25°	10	10	10	9	9	8	8	7	7	6	6
-37.5°	10	9	9	8	8	7	7	7	6	6	6
-38.75°	9	8	8	7	7	7	7	6	6	6	5
-40°	8	7	7	7	7	6	6	6	6	5	5
-41.25°	7	7	7	6	6	6	6	5	5	5	4
-42.5°	7	6	6	6	6	6	5	5	5	4	4
-43.75°	6	6	6	6	5	5	5	4	4	4	3
-45°	6	5	5	5	5	4	4	4	3	3	3
-46.25°	5	5	5	4	4	4	3	3	3	3	3
-47.5°	5	4	4	4	3	3	3	3	3	3	3
-48.75°	4	3	3	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	2	2
-51.25°	3	3	3	3	3	3	2	2	2	2	2
-52.5°	3	3	3	3	2	2	2	2	2	2	1
-53.75°	3	2	2	2	2	2	2	1	1	1	1
-55°	2	2	2	2	2	1	1	1	1	1	1
-56.25°	2	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	0
-60°	1	1	1	1	1	1	1	0	0	0	0
-61.25°	1	1	1	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	1	0	0	0	0	0	0	0	0	0	0
56.25°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	1	1	0	0	0	0	0	0
53.75°	1	1	1	1	1	1	1	0	0	0	0
52.5°	1	1	1	1	1	1	1	1	0	0	0
51.25°	2	1	1	1	1	1	1	1	1	1	0
50°	2	2	1	1	1	1	1	1	1	1	1
48.75°	2	2	2	2	1	1	1	1	1	1	1
47.5°	3	2	2	2	2	1	1	1	1	1	1
46.25°	3	3	3	2	2	2	2	1	1	1	1
45°	3	3	3	3	2	2	2	2	1	1	1
43.75°	3	3	3	3	3	2	2	2	2	1	1
42.5°	3	3	3	3	3	3	2	2	2	2	1
41.25°	4	3	3	3	3	3	3	2	2	2	2
40°	5	4	4	3	3	3	3	3	2	2	2
38.75°	5	5	4	4	3	3	3	3	3	2	2
37.5°	6	5	5	4	4	3	3	3	3	3	2
36.25°	6	6	5	5	4	4	3	3	3	3	3
35°	6	6	6	5	5	4	3	3	3	3	3

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	6	6	6	6	5	5	4	3	3	3	3
32.5°	7	6	6	6	5	5	4	4	3	3	3
31.25°	7	7	6	6	6	5	5	4	4	3	3
30°	8	7	7	6	6	6	5	5	4	3	3
28.75°	8	8	7	7	6	6	5	5	4	4	3
27.5°	9	8	8	7	7	6	6	5	5	4	3
26.25°	10	9	8	7	7	6	6	6	5	4	4
25°	10	9	9	8	7	7	6	6	5	5	4
23.75°	11	10	9	8	7	7	6	6	6	5	4
22.5°	11	10	10	9	8	7	7	6	6	5	5
21.25°	11	11	10	9	8	7	7	6	6	5	5
20°	12	11	10	10	9	8	7	7	6	6	5
18.75°	12	11	11	10	9	8	7	7	6	6	5
17.5°	12	12	11	10	9	9	8	7	6	6	6
16.25°	12	12	11	11	10	9	8	7	7	6	6
15°	13	12	11	11	10	9	8	7	7	6	6
13.75°	13	12	12	11	10	9	9	8	7	6	6
12.5°	13	12	12	11	11	10	9	8	7	6	6
11.25°	14	13	12	11	11	10	9	8	7	7	6
10°	14	13	12	12	11	10	9	8	7	7	6
8.75°	14	13	12	12	11	10	9	8	7	7	6
7.5°	14	13	12	12	11	11	10	9	8	7	6
6.25°	14	14	13	12	11	11	10	9	8	7	6
5°	14	14	13	12	11	11	10	9	8	7	6
3.75°	14	14	13	12	11	11	10	9	8	7	6
2.5°	14	14	13	12	11	11	10	9	8	7	6
1.25°	14	14	13	12	11	11	10	9	8	7	6
0°	15	14	13	12	12	11	10	9	8	7	7
-1.25°	14	14	13	12	11	11	10	9	8	7	6
-2.5°	14	14	13	12	11	11	10	9	8	7	6
-3.75°	14	14	13	12	11	11	10	9	8	7	6
-5°	14	14	13	12	11	11	10	9	8	7	6
-6.25°	14	14	13	12	11	11	10	9	8	7	6
-7.5°	14	13	12	12	11	11	10	9	8	7	6
-8.75°	14	13	12	12	11	10	9	8	7	7	6
-10°	14	13	12	12	11	10	9	8	7	7	6
-11.25°	14	13	12	11	11	10	9	8	7	7	6
-12.5°	13	12	12	11	11	10	9	8	7	6	6
-13.75°	13	12	12	11	10	9	9	8	7	6	6
-15°	13	12	11	11	10	9	8	7	7	6	6
-16.25°	12	12	11	11	10	9	8	7	7	6	6
-17.5°	12	12	11	10	9	9	8	7	6	6	6
-18.75°	12	11	11	10	9	8	7	7	6	6	5
-20°	12	11	10	10	9	8	7	7	6	6	5
-21.25°	11	11	10	9	8	7	7	6	6	5	5

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	11	10	10	9	8	7	7	6	6	5	5
-23.75°	11	10	9	8	7	7	6	6	6	5	4
-25°	10	9	9	8	7	7	6	6	5	5	4
-26.25°	10	9	8	7	7	6	6	6	5	4	4
-27.5°	9	8	8	7	7	6	6	5	5	4	3
-28.75°	8	8	7	7	6	6	5	5	4	4	3
-30°	8	7	7	6	6	6	5	5	4	3	3
-31.25°	7	7	6	6	6	5	5	4	4	3	3
-32.5°	7	6	6	6	5	5	4	4	3	3	3
-33.75°	6	6	6	6	5	5	4	3	3	3	3
-35°	6	6	6	5	5	4	3	3	3	3	3
-36.25°	6	6	5	5	4	4	3	3	3	3	3
-37.5°	6	5	5	4	4	3	3	3	3	3	2
-38.75°	5	5	4	4	3	3	3	3	3	2	2
-40°	5	4	4	3	3	3	3	3	2	2	2
-41.25°	4	3	3	3	3	3	3	2	2	2	2
-42.5°	3	3	3	3	3	3	2	2	2	2	1
-43.75°	3	3	3	3	3	2	2	2	2	1	1
-45°	3	3	3	3	2	2	2	2	1	1	1
-46.25°	3	3	3	2	2	2	2	1	1	1	1
-47.5°	3	2	2	2	2	1	1	1	1	1	1
-48.75°	2	2	2	2	1	1	1	1	1	1	1
-50°	2	2	1	1	1	1	1	1	1	1	1
-51.25°	2	1	1	1	1	1	1	1	1	1	0
-52.5°	1	1	1	1	1	1	1	1	0	0	0
-53.75°	1	1	1	1	1	1	1	0	0	0	0
-55°	1	1	1	1	1	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	1	0	0	0	0	0	0	0	0	0	0
47.5°	1	1	0	0	0	0	0	0	0	0	0
46.25°	1	1	1	0	0	0	0	0	0	0	0
45°	1	1	1	1	0	0	0	0	0	0	0
43.75°	1	1	1	1	0	0	0	0	0	0	0
42.5°	1	1	1	1	1	0	0	0	0	0	0
41.25°	1	1	1	1	1	1	0	0	0	0	0
40°	1	1	1	1	1	1	0	0	0	0	0
38.75°	2	1	1	1	1	1	1	0	0	0	0
37.5°	2	2	1	1	1	1	1	0	0	0	0
36.25°	2	2	1	1	1	1	1	1	0	0	0
35°	2	2	2	1	1	1	1	1	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	3	2	2	2	1	1	1	1	1	0	0
32.5°	3	3	2	2	1	1	1	1	1	0	0
31.25°	3	3	2	2	2	1	1	1	1	1	0
30°	3	3	3	2	2	1	1	1	1	1	0
28.75°	3	3	3	2	2	1	1	1	1	1	0
27.5°	3	3	3	2	2	2	1	1	1	1	1
26.25°	3	3	3	3	2	2	1	1	1	1	1
25°	3	3	3	3	2	2	2	1	1	1	1
23.75°	4	3	3	3	3	2	2	1	1	1	1
22.5°	4	3	3	3	3	2	2	1	1	1	1
21.25°	4	3	3	3	3	2	2	1	1	1	1
20°	5	4	3	3	3	3	2	2	1	1	1
18.75°	5	4	3	3	3	3	2	2	1	1	1
17.5°	5	4	3	3	3	3	2	2	1	1	1
16.25°	5	4	3	3	3	3	2	2	1	1	1
15°	5	5	4	3	3	3	2	2	2	1	1
13.75°	5	5	4	3	3	3	3	2	2	1	1
12.5°	6	5	4	3	3	3	3	2	2	1	1
11.25°	6	5	4	3	3	3	3	2	2	1	1
10°	6	5	4	3	3	3	3	2	2	1	1
8.75°	6	5	5	4	3	3	3	2	2	1	1
7.5°	6	5	5	4	3	3	3	2	2	1	1
6.25°	6	5	5	4	3	3	3	2	2	1	1
5°	6	5	5	4	3	3	3	2	2	1	1
3.75°	6	5	5	4	3	3	3	2	2	1	1
2.5°	6	5	5	4	3	3	3	2	2	1	1
1.25°	6	5	5	4	3	3	3	2	2	1	1
0°	6	6	5	4	3	3	3	3	2	2	1
-1.25°	6	5	5	4	3	3	3	2	2	1	1
-2.5°	6	5	5	4	3	3	3	2	2	1	1
-3.75°	6	5	5	4	3	3	3	2	2	1	1
-5°	6	5	5	4	3	3	3	2	2	1	1
-6.25°	6	5	5	4	3	3	3	2	2	1	1
-7.5°	6	5	5	4	3	3	3	2	2	1	1
-8.75°	6	5	5	4	3	3	3	2	2	1	1
-10°	6	5	4	3	3	3	3	2	2	1	1
-11.25°	6	5	4	3	3	3	3	2	2	1	1
-12.5°	6	5	4	3	3	3	3	2	2	1	1
-13.75°	5	5	4	3	3	3	3	2	2	1	1
-15°	5	5	4	3	3	3	2	2	2	1	1
-16.25°	5	4	3	3	3	3	2	2	1	1	1
-17.5°	5	4	3	3	3	3	2	2	1	1	1
-18.75°	5	4	3	3	3	3	2	2	1	1	1
-20°	5	4	3	3	3	3	2	2	1	1	1
-21.25°	4	3	3	3	3	2	2	1	1	1	1

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	4	3	3	3	3	2	2	1	1	1	1
-23.75°	4	3	3	3	3	2	2	1	1	1	1
-25°	3	3	3	3	2	2	2	1	1	1	1
-26.25°	3	3	3	3	2	2	1	1	1	1	1
-27.5°	3	3	3	2	2	2	1	1	1	1	1
-28.75°	3	3	3	2	2	1	1	1	1	1	0
-30°	3	3	3	2	2	1	1	1	1	1	0
-31.25°	3	3	2	2	2	1	1	1	1	1	0
-32.5°	3	3	2	2	1	1	1	1	1	0	0
-33.75°	3	2	2	2	1	1	1	1	1	0	0
-35°	2	2	2	1	1	1	1	1	0	0	0
-36.25°	2	2	1	1	1	1	1	1	0	0	0
-37.5°	2	2	1	1	1	1	1	0	0	0	0
-38.75°	2	1	1	1	1	1	1	0	0	0	0
-40°	1	1	1	1	1	1	0	0	0	0	0
-41.25°	1	1	1	1	1	1	0	0	0	0	0
-42.5°	1	1	1	1	1	0	0	0	0	0	0
-43.75°	1	1	1	1	0	0	0	0	0	0	0
-45°	1	1	1	1	0	0	0	0	0	0	0
-46.25°	1	1	1	0	0	0	0	0	0	0	0
-47.5°	1	1	0	0	0	0	0	0	0	0	0
-48.75°	1	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	1	0	0	0	0	0	0	0	0	0	0
21.25°	1	0	0	0	0	0	0	0	0	0	0
20°	1	0	0	0	0	0	0	0	0	0	0
18.75°	1	0	0	0	0	0	0	0	0	0	0
17.5°	1	0	0	0	0	0	0	0	0	0	0
16.25°	1	1	0	0	0	0	0	0	0	0	0
15°	1	1	0	0	0	0	0	0	0	0	0
13.75°	1	1	0	0	0	0	0	0	0	0	0
12.5°	1	1	0	0	0	0	0	0	0	0	0
11.25°	1	1	0	0	0	0	0	0	0	0	0
10°	1	1	0	0	0	0	0	0	0	0	0
8.75°	1	1	0	0	0	0	0	0	0	0	0
7.5°	1	1	0	0	0	0	0	0	0	0	0
6.25°	1	1	0	0	0	0	0	0	0	0	0
5°	1	1	0	0	0	0	0	0	0	0	0
3.75°	1	1	0	0	0	0	0	0	0	0	0
2.5°	1	1	0	0	0	0	0	0	0	0	0
1.25°	1	1	0	0	0	0	0	0	0	0	0
0°	1	1	1	0	0	0	0	0	0	0	0
-1.25°	1	1	0	0	0	0	0	0	0	0	0
-2.5°	1	1	0	0	0	0	0	0	0	0	0
-3.75°	1	1	0	0	0	0	0	0	0	0	0
-5°	1	1	0	0	0	0	0	0	0	0	0
-6.25°	1	1	0	0	0	0	0	0	0	0	0
-7.5°	1	1	0	0	0	0	0	0	0	0	0
-8.75°	1	1	0	0	0	0	0	0	0	0	0
-10°	1	1	0	0	0	0	0	0	0	0	0
-11.25°	1	1	0	0	0	0	0	0	0	0	0
-12.5°	1	1	0	0	0	0	0	0	0	0	0
-13.75°	1	1	0	0	0	0	0	0	0	0	0
-15°	1	1	0	0	0	0	0	0	0	0	0
-16.25°	1	1	0	0	0	0	0	0	0	0	0
-17.5°	1	0	0	0	0	0	0	0	0	0	0
-18.75°	1	0	0	0	0	0	0	0	0	0	0
-20°	1	0	0	0	0	0	0	0	0	0	0
-21.25°	1	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	1	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0

REPORT NUMBER: G2-1802-569-4 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)