Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590689

Luminaire Tested: 24CGTX-65-B40-HCD2

Issue Date: 9/4/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590689
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2510-581-27)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/4/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-65-B40-HCD2
Description:	2X4 6500 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 4000K CCT WITH FROSTED SMOOTH LENS
Light Source:	4000K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	6116.2 lumens
Efficiency:	N/A
Efficacy:	109.2 lumens/watt
Spacing Criteria (0/90/45):	1.28 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 2' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	56
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590689
CATALOG NUMBER: 24CGTX-65-B40-HCD2

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590689
CATALOG NUMBER: 24CGTX-65-B40-HCD2

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	68
3	89	79	70	63	87	77	69	63	74	67	62	71	65	61	69	64	60	57
4	82	69	60	54	79	68	60	53	66	58	52	63	57	52	61	55	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	39	51	44	39	50	43	39	37
7	64	50	42	35	62	50	41	35	48	40	35	47	40	35	45	39	34	32
8	60	46	37	31	58	45	37	31	44	36	31	43	36	31	41	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	25	37	30	25	36	30	25	36	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2765	2765	2765
5°	2783	2764	2762
10°	2773	2764	2773
15°	2774	2760	2762
20°	2768	2757	2757
25°	2763	2749	2748
30°	2745	2724	2733
35°	2724	2713	2717
40°	2703	2696	2705
45°	2701	2674	2661
50°	2647	2644	2633
55°	2639	2605	2594
60°	2588	2555	2537
65°	2528	2507	2486
70°	2456	2430	2386
75°	2346	2323	2288
80°	2242	2198	2155
85°	2035	1984	1948

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2701 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590689
CATALOG NUMBER: 24CGTX-65-B40-HCD2

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.0	3.2
10°-20°	560.4	9.2
20°-30°	852.8	13.9
30°-40°	1034.2	16.9
40°-50°	1083.7	17.7
50°-60°	992.7	16.2
60°-70°	777.4	12.7
70°-80°	473.0	7.7
80°-90°	146.9	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1608.2	26.3
0°-40°	2642.5	43.2
0°-60°	4718.9	77.2
0°-90°	6116.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6116.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2055	2055	2055	2055	2055	
5°	2061	2054	2046	2046	2045	196
15°	1992	1987	1982	1985	1983	563
25°	1861	1849	1852	1850	1851	856
35°	1659	1653	1652	1651	1654	1040
45°	1420	1404	1405	1404	1398	1090
55°	1125	1115	1110	1108	1106	1001
65°	794	789	788	778	781	786
75°	451	450	447	441	440	481
85°	132	133	128	127	126	150
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590689
CATALOG NUMBER: 24CGTX-65-B40-HCD2

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*2055.2*	2055.2	2055.2	2055.2	2055.2
2.5°	*2065.3*	*2059.7*	*2053.0*	*2049.6*	*2055.2*
5°	*2060.8*	2054.1	2046.3	2046.3	2045.2
7.5°	*2045.2*	2046.3	2041.8	2036.2	2038.5
10°	*2029.5*	2029.5	2022.8	2023.9	2029.5
12.5°	*2019.5*	2009.4	2007.2	2004.9	2013.9
15°	*1991.5*	1987.1	1981.5	1984.8	1982.6
17.5°	*1967.0*	1959.1	1953.6	1953.6	1969.2
20°	*1933.5*	1924.5	1925.6	1920.1	1925.6
22.5°	*1893.2*	1889.9	1889.9	1888.8	1899.9
25°	*1860.9*	1848.6	1851.9	1849.7	1850.8
27.5°	*1816.2*	1807.2	1801.7	1801.7	1809.5
30°	*1767.0*	1759.2	1753.6	1752.5	1759.2
32.5°	*1721.2*	1704.5	1707.8	1706.7	1711.2
35°	*1658.7*	1653.1	1652.0	1650.9	1654.2
37.5°	*1607.3*	1596.1	1592.8	1591.7	1589.4
40°	*1539.2*	1536.9	1534.7	1530.2	1540.3
42.5°	*1482.2*	1473.3	1469.9	1471.0	1469.9
45°	*1419.7*	1404.0	1405.1	1404.0	1398.4
47.5°	*1340.4*	1335.9	1340.4	1331.4	1330.3
50°	*1264.4*	1264.4	1263.3	1257.7	1257.7
52.5°	*1199.6*	1189.6	1189.6	1182.9	1185.1
55°	*1124.8*	1114.7	1110.3	1108.0	1105.8
57.5°	*1037.7*	1033.2	1031.0	1027.6	1026.5
60°	*961.7*	956.1	949.4	947.2	942.7
62.5°	*875.7*	873.5	870.1	866.8	860.1
65°	*794.2*	788.6	787.5	778.5	780.8
67.5°	*712.6*	707.0	702.6	698.1	692.5
70°	*624.4*	619.9	617.7	611.0	606.5
72.5°	*541.7*	537.3	532.8	525.0	520.5
75°	*451.3*	450.1	446.8	441.2	440.1
77.5°	*373.1*	369.7	366.4	361.9	357.4
80°	*289.3*	288.2	283.7	281.5	278.1
82.5°	*212.2*	208.9	204.4	202.2	199.9
85°	*131.8*	132.9	128.5	127.3	126.2
87.5°	*61.4*	61.4	63.7	64.8	61.4
90°	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590689
CATALOG NUMBER: 24CGTX-65-B40-HCD2

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.53	17.19	15.89	17.50	17.82	15.48	17.14	15.84	17.46	17.77
	3H	17.48	18.99	17.86	19.32	19.68	17.39	18.90	17.77	19.22	19.58
	4H	18.24	19.67	18.64	20.01	20.39	18.13	19.56	18.53	19.90	20.28
	6H	18.85	20.17	19.26	20.54	20.93	18.71	20.04	19.13	20.40	20.79
	8H	19.07	20.33	19.49	20.72	21.12	18.92	20.18	19.34	20.57	20.97
	12H	19.22	20.43	19.65	20.81	21.24	19.06	20.27	19.49	20.65	21.08
4H	2H	16.20	17.62	16.60	17.97	18.34	16.16	17.58	16.56	17.93	18.31
	3H	18.38	19.57	18.78	19.97	20.37	18.30	19.50	18.71	19.89	20.29
	4H	19.27	20.36	19.70	20.77	21.21	19.17	20.26	19.60	20.67	21.11
	6H	20.02	20.98	20.48	21.42	21.87	19.90	20.85	20.35	21.29	21.74
	8H	20.30	21.19	20.75	21.63	22.09	20.15	21.05	20.61	21.49	21.95
	12H	20.50	21.31	20.98	21.78	22.25	20.35	21.15	20.83	21.63	22.10
8H	4H	19.63	20.52	20.09	20.96	21.43	19.54	20.43	20.00	20.87	21.34
	6H	20.52	21.26	21.01	21.75	22.22	20.40	21.15	20.90	21.64	22.11
	8H	20.87	21.54	21.38	22.05	22.53	20.74	21.41	21.25	21.92	22.40
	12H	21.17	21.76	21.68	22.25	22.81	21.03	21.62	21.53	22.11	22.67
12H	4H	19.67	20.48	20.15	20.95	21.42	19.59	20.40	20.07	20.87	21.34
	6H	20.59	21.26	21.10	21.77	22.25	20.48	21.15	20.99	21.66	22.14
	8H	21.01	21.61	21.52	22.10	22.66	20.89	21.48	21.39	21.97	22.53

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-581-3-R2

Test Date: 01/21/2026

Luminaire Tested: 24CGTX-55-B40-HCD

Data in this report applies to families of products including 24CGTX-55HE

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-581-3-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-55-B40-HCD**
Description:	*THIS IS A REVISION OF REPORT SP1-2510-581-3-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 CGTX 5500 lumen with BioUp Boards with fixed CCT 4000K - Control Volatge at 4V

Spectral Parameters

CCT (K):	4150
CIE u':	0.2306
CIE v':	0.4822
Duv:	-0.0137
CIE x:	0.3662
CIE y:	0.3403
CIE z:	0.2935
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	595
Purity:	11.98102
Rf:	88
Rg:	97.3

CRI (Ra):	87.7
R1:	92.1
R2:	87.5
R3:	86.1
R4:	91.4
R5:	90.5
R6:	81.3
R7:	84.9
R8:	87.7
R9:	87.2
R10:	76.5
R11:	92.8
R12:	70.9
R13:	90.1
R14:	93.9
R15:	92.9



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.1

REPORT NUMBER: SP1-2510-581-3-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2510-581-3-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4150K
CIE x = 0.3662
CIE y = 0.3403
Duv = -0.0137

Point lies outside the range

REPORT NUMBER: SP1-2510-581-3-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	271	NR	620	350	NR	750	8	NR	880	0	NR
365	0	NR	495	243	NR	625	351	NR	755	7	NR	885	0	NR
370	0	NR	500	230	NR	630	1000	NR	760	6	NR	890	0	NR
375	1	NR	505	228	NR	635	567	NR	765	5	NR	895	0	NR
380	1	NR	510	233	NR	640	228	NR	770	4	NR	900	0	NR
385	2	NR	515	236	NR	645	230	NR	775	3	NR	905	0	NR
390	3	NR	520	241	NR	650	189	NR	780	3	NR	910	0	NR
395	4	NR	525	244	NR	655	160	NR	785	3	NR	915	0	NR
400	5	NR	530	248	NR	660	136	NR	790	2	NR	920	0	NR
405	6	NR	535	255	NR	665	115	NR	795	2	NR	925	0	NR
410	8	NR	540	260	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	269	NR	675	86	NR	805	1	NR	935	0	NR
420	23	NR	550	278	NR	680	74	NR	810	1	NR	940	0	NR
425	41	NR	555	289	NR	685	63	NR	815	1	NR	945	0	NR
430	71	NR	560	303	NR	690	54	NR	820	1	NR	950	0	NR
435	122	NR	565	316	NR	695	46	NR	825	1	NR	955	0	NR
440	203	NR	570	329	NR	700	39	NR	830	1	NR	960	0	NR
445	351	NR	575	341	NR	705	33	NR	835	1	NR	965	0	NR
450	441	NR	580	351	NR	710	28	NR	840	1	NR	970	0	NR
455	336	NR	585	360	NR	715	24	NR	845	1	NR	975	0	NR
460	280	NR	590	365	NR	720	20	NR	850	0	NR	980	0	NR
465	345	NR	595	365	NR	725	17	NR	855	0	NR	985	0	NR
470	444	NR	600	365	NR	730	15	NR	860	0	NR	990	0	NR
475	467	NR	605	364	NR	735	12	NR	865	0	NR	995	0	NR
480	390	NR	610	384	NR	740	11	NR	870	0	NR	1000	0	NR
485	310	NR	615	383	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-3-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 2.05**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	271	NR	620	350	NR	750	8	NR	880	0	NR
365	0	NR	495	243	NR	625	351	NR	755	7	NR	885	0	NR
370	0	NR	500	230	NR	630	1000	NR	760	6	NR	890	0	NR
375	1	NR	505	228	NR	635	567	NR	765	5	NR	895	0	NR
380	1	NR	510	233	NR	640	228	NR	770	4	NR	900	0	NR
385	2	NR	515	236	NR	645	230	NR	775	3	NR	905	0	NR
390	3	NR	520	241	NR	650	189	NR	780	3	NR	910	0	NR
395	4	NR	525	244	NR	655	160	NR	785	3	NR	915	0	NR
400	5	NR	530	248	NR	660	136	NR	790	2	NR	920	0	NR
405	6	NR	535	255	NR	665	115	NR	795	2	NR	925	0	NR
410	8	NR	540	260	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	269	NR	675	86	NR	805	1	NR	935	0	NR
420	23	NR	550	278	NR	680	74	NR	810	1	NR	940	0	NR
425	41	NR	555	289	NR	685	63	NR	815	1	NR	945	0	NR
430	71	NR	560	303	NR	690	54	NR	820	1	NR	950	0	NR
435	122	NR	565	316	NR	695	46	NR	825	1	NR	955	0	NR
440	203	NR	570	329	NR	700	39	NR	830	1	NR	960	0	NR
445	351	NR	575	341	NR	705	33	NR	835	1	NR	965	0	NR
450	441	NR	580	351	NR	710	28	NR	840	1	NR	970	0	NR
455	336	NR	585	360	NR	715	24	NR	845	1	NR	975	0	NR
460	280	NR	590	365	NR	720	20	NR	850	0	NR	980	0	NR
465	345	NR	595	365	NR	725	17	NR	855	0	NR	985	0	NR
470	444	NR	600	365	NR	730	15	NR	860	0	NR	990	0	NR
475	467	NR	605	364	NR	735	12	NR	865	0	NR	995	0	NR
480	390	NR	610	384	NR	740	11	NR	870	0	NR	1000	0	NR
485	310	NR	615	383	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-3-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 4.67**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	271	NR	620	350	NR	750	8	NR	880	0	NR
365	0	NR	495	243	NR	625	351	NR	755	7	NR	885	0	NR
370	0	NR	500	230	NR	630	1000	NR	760	6	NR	890	0	NR
375	1	NR	505	228	NR	635	567	NR	765	5	NR	895	0	NR
380	1	NR	510	233	NR	640	228	NR	770	4	NR	900	0	NR
385	2	NR	515	236	NR	645	230	NR	775	3	NR	905	0	NR
390	3	NR	520	241	NR	650	189	NR	780	3	NR	910	0	NR
395	4	NR	525	244	NR	655	160	NR	785	3	NR	915	0	NR
400	5	NR	530	248	NR	660	136	NR	790	2	NR	920	0	NR
405	6	NR	535	255	NR	665	115	NR	795	2	NR	925	0	NR
410	8	NR	540	260	NR	670	104	NR	800	2	NR	930	0	NR
415	13	NR	545	269	NR	675	86	NR	805	1	NR	935	0	NR
420	23	NR	550	278	NR	680	74	NR	810	1	NR	940	0	NR
425	41	NR	555	289	NR	685	63	NR	815	1	NR	945	0	NR
430	71	NR	560	303	NR	690	54	NR	820	1	NR	950	0	NR
435	122	NR	565	316	NR	695	46	NR	825	1	NR	955	0	NR
440	203	NR	570	329	NR	700	39	NR	830	1	NR	960	0	NR
445	351	NR	575	341	NR	705	33	NR	835	1	NR	965	0	NR
450	441	NR	580	351	NR	710	28	NR	840	1	NR	970	0	NR
455	336	NR	585	360	NR	715	24	NR	845	1	NR	975	0	NR
460	280	NR	590	365	NR	720	20	NR	850	0	NR	980	0	NR
465	345	NR	595	365	NR	725	17	NR	855	0	NR	985	0	NR
470	444	NR	600	365	NR	730	15	NR	860	0	NR	990	0	NR
475	467	NR	605	364	NR	735	12	NR	865	0	NR	995	0	NR
480	390	NR	610	384	NR	740	11	NR	870	0	NR	1000	0	NR
485	310	NR	615	383	NR	745	9	NR	875	0	NR			


REPORT NUMBER: SP1-2510-581-3-R2

TM-30-18


Summary


R_f = 88
R_g = 97.3
CIE R_a = 87.7
R_9 = 87.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-581-3-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 93	CES51 = 88	CES76 = 88
CES02 = 62	CES27 = 85	CES52 = 91	CES77 = 80
CES03 = 31	CES28 = 95	CES53 = 85	CES78 = 88
CES04 = 70	CES29 = 86	CES54 = 85	CES79 = 83
CES05 = 49	CES30 = 80	CES55 = 83	CES80 = 83
CES06 = 51	CES31 = 87	CES56 = 83	CES81 = 66
CES07 = 42	CES32 = 95	CES57 = 80	CES82 = 93
CES08 = 41	CES33 = 87	CES58 = 81	CES83 = 88
CES09 = 29	CES34 = 93	CES59 = 92	CES84 = 96
CES10 = 75	CES35 = 95	CES60 = 89	CES85 = 77
CES11 = 58	CES36 = 77	CES61 = 88	CES86 = 76
CES12 = 64	CES37 = 95	CES62 = 79	CES87 = 91
CES13 = 43	CES38 = 76	CES63 = 92	CES88 = 90
CES14 = 74	CES39 = 94	CES64 = 84	CES89 = 85
CES15 = 71	CES40 = 91	CES65 = 90	CES90 = 87
CES16 = 47	CES41 = 90	CES66 = 86	CES91 = 72
CES17 = 49	CES42 = 90	CES67 = 86	CES92 = 78
CES18 = 56	CES43 = 88	CES68 = 88	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 89	CES94 = 79
CES20 = 66	CES45 = 91	CES70 = 90	CES95 = 86
CES21 = 85	CES46 = 91	CES71 = 85	CES96 = 95
CES22 = 78	CES47 = 84	CES72 = 94	CES97 = 88
CES23 = 91	CES48 = 80	CES73 = 87	CES98 = 87
CES24 = 90	CES49 = 91	CES74 = 88	CES99 = 88
CES25 = 71	CES50 = 89	CES75 = 87	





REPORT NUMBER: SP1-2510-581-3-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-581-3-R2

TM-30-18

Measure Comparisons





(END OF REPORT)