Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1559234

Luminaire Tested: 14CGTX-30-B2750-W2D-3500K

Issue Date: 8/30/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1559234
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2510-581-15)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	8/30/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	14CGTX-30-B2750-W2D-3500K
Description:	1X4 3000 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 3500K CCT WITH FROSTED SMOOTH l
Light Source:	3500K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3096.7 lumens
Efficiency:	N/A
Efficacy:	102.2 lumens/watt
Spacing Criteria (0/90/45):	1.26 / 1.26 / 1.38
Luminous Opening:	Rectangular (W 1' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	30.3
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559234
CATALOG NUMBER: 14CGTX-30-B2750-W2D-3500K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559234
CATALOG NUMBER: 14CGTX-30-B2750-W2D-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	77	73	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	45	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	35	33
8	60	46	38	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	39	31	26	38	30	26	37	30	25	36	30	25	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2837	2837	2837
5°	2837	2831	2845
10°	2837	2831	2845
15°	2830	2825	2836
20°	2817	2814	2823
25°	2804	2801	2810
30°	2784	2784	2784
35°	2761	2757	2757
40°	2747	2736	2729
45°	2711	2707	2695
50°	2682	2673	2657
55°	2655	2637	2608
60°	2606	2579	2552
65°	2550	2506	2479
70°	2469	2429	2382
75°	2381	2319	2266
80°	2283	2205	2095
85°	2056	1933	1837

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
Vertical Angle: 45°
Luminance: 2715 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559234
CATALOG NUMBER: 14CGTX-30-B2750-W2D-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	3.2
10°-20°	286.7	9.3
20°-30°	435.2	14.1
30°-40°	526.1	17.0
40°-50°	548.8	17.7
50°-60°	501.7	16.2
60°-70°	390.4	12.6
70°-80°	236.6	7.6
80°-90°	71.1	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	821.9	26.5
0°-40°	1348.0	43.5
0°-60°	2398.5	77.5
0°-90°	3096.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3096.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1054	1054	1054	1054	1054	
5°	1050	1051	1048	1052	1053	100
15°	1016	1015	1014	1018	1018	287
25°	944	944	943	945	946	435
35°	840	842	839	840	839	527
45°	712	713	711	710	708	551
55°	566	566	562	559	556	505
65°	400	400	394	389	389	396
75°	229	228	223	219	218	243
85°	67	64	63	60	60	75
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559234
CATALOG NUMBER: 14CGTX-30-B2750-W2D-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1054.3	1054.3	1054.3	1054.3	*1054.3*
2.5°	*1054.3*	*1054.3*	*1051.3*	*1055.3*	*1056.3*
5°	1050.3	1051.3	1048.2	1052.3	*1053.3*
7.5°	1045.2	1045.2	1044.2	1047.2	*1048.2*
10°	1038.2	1038.2	1036.1	1040.2	*1041.2*
12.5°	1028.1	1028.1	1026.1	1030.1	*1031.1*
15°	1016.0	1015.0	1013.9	1018.0	*1018.0*
17.5°	1000.8	1000.8	999.8	1002.8	*1003.9*
20°	983.7	983.7	982.7	985.7	*985.7*
22.5°	964.5	965.5	964.5	966.5	*967.5*
25°	944.3	944.3	943.3	945.3	*946.3*
27.5°	921.1	921.1	920.1	922.1	*923.1*
30°	895.9	895.9	895.9	895.9	*895.9*
32.5°	870.7	870.7	868.7	868.7	*868.7*
35°	840.4	842.4	839.4	840.4	*839.4*
37.5°	812.2	813.2	811.2	810.1	*810.1*
40°	781.9	780.9	778.9	778.9	*776.9*
42.5°	748.6	747.6	746.6	744.6	*743.6*
45°	712.3	713.3	711.3	710.3	*708.2*
47.5°	680.0	678.0	675.0	672.9	*672.9*
50°	640.7	642.7	638.6	636.6	*634.6*
52.5°	604.3	603.3	602.3	598.3	*595.3*
55°	566.0	566.0	562.0	558.9	*555.9*
57.5°	524.6	525.6	520.6	516.6	*515.5*
60°	484.3	483.3	479.2	476.2	*474.2*
62.5°	442.9	440.9	437.9	432.8	*430.8*
65°	400.5	399.5	393.5	389.4	*389.4*
67.5°	358.2	357.2	352.1	348.1	*344.0*
70°	313.8	312.8	308.7	304.7	*302.7*
72.5°	273.4	271.4	267.4	261.3	*260.3*
75°	229.0	228.0	223.0	218.9	*217.9*
77.5°	186.6	186.6	182.6	178.6	*176.6*
80°	147.3	144.3	142.3	136.2	*135.2*
82.5°	104.9	103.9	101.9	98.9	*95.8*
85°	66.6	63.6	62.6	60.5	*59.5*
87.5°	29.3	29.3	26.2	26.2	*24.2*
90°	0.0	0.0	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1559234
CATALOG NUMBER: 14CGTX-30-B2750-W2D-3500K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.60	17.26	15.96	17.57	17.89	15.48	17.14	15.84	17.45	17.77
	3H	17.53	19.03	17.90	19.36	19.72	17.36	18.87	17.74	19.19	19.55
	4H	18.29	19.71	18.69	20.06	20.43	18.09	19.51	18.49	19.86	20.23
	6H	18.89	20.21	19.30	20.57	20.96	18.65	19.97	19.07	20.34	20.73
	8H	19.10	20.36	19.52	20.75	21.15	18.84	20.10	19.27	20.49	20.89
	12H	19.25	20.45	19.68	20.84	21.26	18.97	20.18	19.40	20.56	20.99
4H	2H	16.25	17.66	16.64	18.01	18.39	16.15	17.57	16.55	17.92	18.29
	3H	18.41	19.60	18.82	20.00	20.40	18.26	19.46	18.67	19.85	20.25
	4H	19.31	20.39	19.74	20.80	21.24	19.13	20.21	19.56	20.62	21.06
	6H	20.05	21.00	20.51	21.44	21.89	19.83	20.77	20.28	21.21	21.67
	8H	20.32	21.21	20.78	21.65	22.11	20.07	20.96	20.53	21.40	21.86
	12H	20.52	21.32	21.00	21.79	22.26	20.25	21.05	20.72	21.52	21.99
8H	4H	19.65	20.54	20.11	20.98	21.45	19.50	20.38	19.95	20.83	21.29
	6H	20.54	21.28	21.03	21.76	22.24	20.33	21.07	20.82	21.56	22.03
	8H	20.88	21.55	21.39	22.06	22.54	20.65	21.32	21.16	21.82	22.31
	12H	21.17	21.76	21.67	22.25	22.81	20.91	21.50	21.42	21.99	22.55
12H	4H	19.70	20.50	20.18	20.97	21.44	19.55	20.35	20.02	20.82	21.29
	6H	20.61	21.27	21.11	21.78	22.26	20.41	21.08	20.92	21.58	22.07
	8H	21.02	21.61	21.52	22.10	22.66	20.80	21.39	21.30	21.88	22.43

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-581-8-R2

Test Date: 02/03/2026

Luminaire Tested: 24CGTX-45-B2750-W2D-3500K

Data in this report applies to families of products including 24CGTX-45-UNV


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-581-8-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-45-B2750-W2D-3500K**
Description:	*THIS IS A REVISION OF REPORT SP1-2510-581-8-R2 TO UPDATE THE CATALOG INFORMATION*2X4 CGTX 4500 lumen with BioUp Boards - 3500K

Spectral Parameters

CCT (K):	3407	CRI (Ra):	90.6		
CIE u':	0.2428	R1:	93.7	R9:	86.5
CIE v':	0.4992	R2:	90.5	R10:	82.1
Duv:	-0.0104	R3:	90.2	R11:	96.0
CIE x:	0.3996	R4:	96.7	R12:	75.0
CIE y:	0.3651	R5:	92.5	R13:	92.1
CIE z:	0.2353	R6:	83.5	R14:	96.1
Peak Wavelength (nm):	630	R7:	88.1	R15:	95.7
Dominant Wavelength (nm):	587	R8:	89.8		
Purity:	29.46494				
Rf:	90.9				
Rg:	99.5				




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2510-581-8-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3407K
CIE x = 0.3996
CIE y = 0.3651
Duv = -0.0104

Point lies outside the range

REPORT NUMBER: SP1-2510-581-8-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	165	NR	620	285	NR	750	6	NR	880	0	NR
365	0	NR	495	161	NR	625	293	NR	755	5	NR	885	0	NR
370	0	NR	500	162	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	166	NR	635	530	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	184	NR	770	3	NR	900	0	NR
385	1	NR	515	175	NR	645	198	NR	775	3	NR	905	0	NR
390	1	NR	520	178	NR	650	156	NR	780	2	NR	910	0	NR
395	2	NR	525	182	NR	655	131	NR	785	2	NR	915	0	NR
400	3	NR	530	185	NR	660	110	NR	790	2	NR	920	0	NR
405	3	NR	535	189	NR	665	93	NR	795	2	NR	925	0	NR
410	5	NR	540	194	NR	670	85	NR	800	1	NR	930	0	NR
415	8	NR	545	201	NR	675	70	NR	805	1	NR	935	0	NR
420	13	NR	550	209	NR	680	60	NR	810	1	NR	940	0	NR
425	23	NR	555	216	NR	685	51	NR	815	1	NR	945	0	NR
430	40	NR	560	225	NR	690	44	NR	820	1	NR	950	0	NR
435	68	NR	565	234	NR	695	37	NR	825	1	NR	955	0	NR
440	114	NR	570	243	NR	700	32	NR	830	1	NR	960	0	NR
445	200	NR	575	251	NR	705	27	NR	835	1	NR	965	0	NR
450	260	NR	580	259	NR	710	23	NR	840	0	NR	970	0	NR
455	194	NR	585	266	NR	715	19	NR	845	0	NR	975	0	NR
460	155	NR	590	271	NR	720	17	NR	850	0	NR	980	0	NR
465	182	NR	595	273	NR	725	14	NR	855	0	NR	985	0	NR
470	226	NR	600	276	NR	730	12	NR	860	0	NR	990	0	NR
475	241	NR	605	279	NR	735	10	NR	865	0	NR	995	0	NR
480	211	NR	610	307	NR	740	9	NR	870	0	NR	1000	0	NR
485	177	NR	615	311	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-8-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.78**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	165	NR	620	285	NR	750	6	NR	880	0	NR
365	0	NR	495	161	NR	625	293	NR	755	5	NR	885	0	NR
370	0	NR	500	162	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	166	NR	635	530	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	184	NR	770	3	NR	900	0	NR
385	1	NR	515	175	NR	645	198	NR	775	3	NR	905	0	NR
390	1	NR	520	178	NR	650	156	NR	780	2	NR	910	0	NR
395	2	NR	525	182	NR	655	131	NR	785	2	NR	915	0	NR
400	3	NR	530	185	NR	660	110	NR	790	2	NR	920	0	NR
405	3	NR	535	189	NR	665	93	NR	795	2	NR	925	0	NR
410	5	NR	540	194	NR	670	85	NR	800	1	NR	930	0	NR
415	8	NR	545	201	NR	675	70	NR	805	1	NR	935	0	NR
420	13	NR	550	209	NR	680	60	NR	810	1	NR	940	0	NR
425	23	NR	555	216	NR	685	51	NR	815	1	NR	945	0	NR
430	40	NR	560	225	NR	690	44	NR	820	1	NR	950	0	NR
435	68	NR	565	234	NR	695	37	NR	825	1	NR	955	0	NR
440	114	NR	570	243	NR	700	32	NR	830	1	NR	960	0	NR
445	200	NR	575	251	NR	705	27	NR	835	1	NR	965	0	NR
450	260	NR	580	259	NR	710	23	NR	840	0	NR	970	0	NR
455	194	NR	585	266	NR	715	19	NR	845	0	NR	975	0	NR
460	155	NR	590	271	NR	720	17	NR	850	0	NR	980	0	NR
465	182	NR	595	273	NR	725	14	NR	855	0	NR	985	0	NR
470	226	NR	600	276	NR	730	12	NR	860	0	NR	990	0	NR
475	241	NR	605	279	NR	735	10	NR	865	0	NR	995	0	NR
480	211	NR	610	307	NR	740	9	NR	870	0	NR	1000	0	NR
485	177	NR	615	311	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-8-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.85**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	165	NR	620	285	NR	750	6	NR	880	0	NR
365	0	NR	495	161	NR	625	293	NR	755	5	NR	885	0	NR
370	0	NR	500	162	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	166	NR	635	530	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	184	NR	770	3	NR	900	0	NR
385	1	NR	515	175	NR	645	198	NR	775	3	NR	905	0	NR
390	1	NR	520	178	NR	650	156	NR	780	2	NR	910	0	NR
395	2	NR	525	182	NR	655	131	NR	785	2	NR	915	0	NR
400	3	NR	530	185	NR	660	110	NR	790	2	NR	920	0	NR
405	3	NR	535	189	NR	665	93	NR	795	2	NR	925	0	NR
410	5	NR	540	194	NR	670	85	NR	800	1	NR	930	0	NR
415	8	NR	545	201	NR	675	70	NR	805	1	NR	935	0	NR
420	13	NR	550	209	NR	680	60	NR	810	1	NR	940	0	NR
425	23	NR	555	216	NR	685	51	NR	815	1	NR	945	0	NR
430	40	NR	560	225	NR	690	44	NR	820	1	NR	950	0	NR
435	68	NR	565	234	NR	695	37	NR	825	1	NR	955	0	NR
440	114	NR	570	243	NR	700	32	NR	830	1	NR	960	0	NR
445	200	NR	575	251	NR	705	27	NR	835	1	NR	965	0	NR
450	260	NR	580	259	NR	710	23	NR	840	0	NR	970	0	NR
455	194	NR	585	266	NR	715	19	NR	845	0	NR	975	0	NR
460	155	NR	590	271	NR	720	17	NR	850	0	NR	980	0	NR
465	182	NR	595	273	NR	725	14	NR	855	0	NR	985	0	NR
470	226	NR	600	276	NR	730	12	NR	860	0	NR	990	0	NR
475	241	NR	605	279	NR	735	10	NR	865	0	NR	995	0	NR
480	211	NR	610	307	NR	740	9	NR	870	0	NR	1000	0	NR
485	177	NR	615	311	NR	745	7	NR	875	0	NR			


REPORT NUMBER: SP1-2510-581-8-R2

TM-30-18


Summary


R_f = 90.9
R_g = 99.5
CIE R_a = 90.6
R_9 = 86.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-581-8-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 95	CES51 = 93	CES76 = 90
CES02 = 63	CES27 = 88	CES52 = 97	CES77 = 79
CES03 = 32	CES28 = 96	CES53 = 92	CES78 = 90
CES04 = 70	CES29 = 92	CES54 = 89	CES79 = 82
CES05 = 50	CES30 = 87	CES55 = 87	CES80 = 85
CES06 = 51	CES31 = 92	CES56 = 89	CES81 = 65
CES07 = 43	CES32 = 97	CES57 = 88	CES82 = 94
CES08 = 42	CES33 = 92	CES58 = 88	CES83 = 89
CES09 = 29	CES34 = 95	CES59 = 95	CES84 = 97
CES10 = 76	CES35 = 96	CES60 = 91	CES85 = 78
CES11 = 58	CES36 = 81	CES61 = 92	CES86 = 77
CES12 = 65	CES37 = 97	CES62 = 83	CES87 = 93
CES13 = 44	CES38 = 82	CES63 = 95	CES88 = 93
CES14 = 74	CES39 = 98	CES64 = 91	CES89 = 86
CES15 = 72	CES40 = 96	CES65 = 93	CES90 = 91
CES16 = 48	CES41 = 93	CES66 = 91	CES91 = 76
CES17 = 49	CES42 = 95	CES67 = 91	CES92 = 80
CES18 = 57	CES43 = 93	CES68 = 92	CES93 = 88
CES19 = 71	CES44 = 99	CES69 = 93	CES94 = 79
CES20 = 67	CES45 = 96	CES70 = 92	CES95 = 88
CES21 = 86	CES46 = 96	CES71 = 88	CES96 = 96
CES22 = 78	CES47 = 86	CES72 = 95	CES97 = 94
CES23 = 91	CES48 = 86	CES73 = 90	CES98 = 92
CES24 = 90	CES49 = 97	CES74 = 87	CES99 = 91
CES25 = 71	CES50 = 94	CES75 = 89	





REPORT NUMBER: SP1-2510-581-8-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-581-8-R2

TM-30-18

Measure Comparisons





(END OF REPORT)