Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1559250

Luminaire Tested: 22CGTX-25-B2750-W2D-2700K

Issue Date: 8/30/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1559250
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	8/30/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	22CGTX-25-B2750-W2D-2700K
Description:	2X2 2500 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 2700K CCT WITH FROSTED SMOOTH L
Light Source:	2700K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	2797.4 lumens
Efficiency:	N/A
Efficacy:	111.0 lumens/watt
Spacing Criteria (0/90/45):	1.26 / 1.26 / 1.38
Luminous Opening:	Rectangular (W 1.81' x L: 1.81' x H: 0')
CIE Type:	Direct
Input Watts (W):	25.2
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559250
CATALOG NUMBER: 22CGTX-25-B2750-W2D-2700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559250
CATALOG NUMBER: 22CGTX-25-B2750-W2D-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	44	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	34	32
8	60	46	37	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	25	37	30	25	36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3116	3116	3116
5°	3121	3115	3121
10°	3121	3111	3121
15°	3107	3104	3111
20°	3093	3089	3100
25°	3080	3077	3084
30°	3053	3053	3065
35°	3036	3032	3040
40°	3011	3007	3015
45°	2970	2970	2984
50°	2941	2941	2956
55°	2885	2896	2902
60°	2831	2837	2851
65°	2760	2768	2783
70°	2654	2673	2692
75°	2545	2557	2595
80°	2396	2434	2453
85°	2105	2143	2256

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
Vertical Angle: 45°
Luminance: 2984 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559250
CATALOG NUMBER: 22CGTX-25-B2750-W2D-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.1	3.2
10°-20°	258.5	9.2
20°-30°	392.2	14.0
30°-40°	474.5	17.0
40°-50°	495.9	17.7
50°-60°	453.6	16.2
60°-70°	353.3	12.6
70°-80°	214.4	7.7
80°-90°	64.9	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	740.8	26.5
0°-40°	1215.3	43.4
0°-60°	2164.8	77.4
0°-90°	2797.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2797.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	951	951	951	951	951	
5°	949	948	947	948	949	90
15°	916	915	915	916	917	259
25°	852	851	851	851	853	392
35°	759	758	758	759	760	474
45°	641	643	641	643	644	495
55°	505	506	507	509	508	453
65°	356	356	357	359	359	352
75°	201	201	202	204	205	213
85°	56	56	57	58	60	64
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559250
CATALOG NUMBER: 22CGTX-25-B2750-W2D-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	951	951	951	951	951
2.5°	951	950	950	951	951
5°	949	948	947	948	949
7.5°	944	943	942	943	944
10°	938	936	935	937	938
12.5°	928	927	926	927	928
15°	916	915	915	916	917
17.5°	903	902	902	903	904
20°	887	887	886	888	889
22.5°	870	869	869	870	872
25°	852	851	851	851	853
27.5°	830	829	829	831	832
30°	807	808	807	808	810
32.5°	783	784	783	785	785
35°	759	758	758	759	760
37.5°	731	731	730	732	732
40°	704	703	703	704	705
42.5°	674	673	673	675	675
45°	641	643	641	643	644
47.5°	610	610	611	613	613
50°	577	577	577	578	580
52.5°	542	543	543	545	544
55°	505	506	507	509	508
57.5°	472	471	471	472	473
60°	432	433	433	434	435
62.5°	395	394	396	398	397
65°	356	356	357	359	359
67.5°	317	316	318	320	320
70°	277	277	279	282	281
72.5°	240	239	241	243	244
75°	201	201	202	204	205
77.5°	163	163	165	167	168
80°	127	126	129	130	130
82.5°	90	91	92	93	93
85°	56	56	57	58	60
87.5°	24	24	26	26	27
90°	0	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1559250
CATALOG NUMBER: 22CGTX-25-B2750-W2D-2700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.88	17.54	16.24	17.85	18.16	15.89	17.55	16.26	17.87	18.18
	3H	17.76	19.27	18.14	19.59	19.95	17.81	19.32	18.19	19.64	20.00
	4H	18.51	19.93	18.90	20.27	20.65	18.57	19.99	18.97	20.34	20.71
	6H	19.08	20.40	19.49	20.76	21.15	19.17	20.49	19.58	20.85	21.24
	8H	19.28	20.54	19.70	20.93	21.33	19.37	20.63	19.80	21.02	21.42
	12H	19.41	20.62	19.84	21.00	21.43	19.52	20.73	19.95	21.11	21.54
4H	2H	16.54	17.96	16.94	18.31	18.68	16.55	17.97	16.95	18.32	18.69
	3H	18.66	19.85	19.06	20.25	20.65	18.70	19.90	19.11	20.29	20.69
	4H	19.53	20.62	19.96	21.03	21.46	19.60	20.68	20.03	21.09	21.53
	6H	20.25	21.20	20.70	21.64	22.09	20.34	21.29	20.79	21.73	22.18
	8H	20.50	21.39	20.96	21.83	22.29	20.60	21.49	21.05	21.93	22.39
	12H	20.68	21.49	21.16	21.96	22.43	20.80	21.60	21.27	22.07	22.54
8H	4H	19.89	20.78	20.35	21.22	21.69	19.95	20.84	20.41	21.28	21.74
	6H	20.74	21.48	21.23	21.97	22.45	20.83	21.57	21.32	22.05	22.53
	8H	21.08	21.74	21.58	22.25	22.73	21.17	21.84	21.68	22.34	22.83
	12H	21.35	21.94	21.85	22.43	22.98	21.46	22.05	21.96	22.54	23.09
12H	4H	19.94	20.74	20.42	21.22	21.69	19.99	20.79	20.47	21.27	21.74
	6H	20.82	21.49	21.33	21.99	22.48	20.90	21.57	21.41	22.07	22.56
	8H	21.22	21.81	21.72	22.30	22.86	21.31	21.90	21.81	22.39	22.95

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2505-441-28-R2

Test Date: 07/10/2025

Luminaire Tested: 24CGTX-45-B2750-W2D-2700K

Data in this report applies to families of products including 24CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2505-441-28-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-45-B2750-W2D-2700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2504-441-28-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 4500 LUMEN CGTX. Using WaveLinx PRO F1 sensor.

Spectral Parameters

CCT (K):	2694	CRI (Ra):	95.4		
CIE u':	0.2630	R1:	96.8	R9:	80.8
CIE v':	0.5264	R2:	98.3	R10:	98.3
Duv:	-0.0008	R3:	97.9	R11:	89.1
CIE x:	0.4590	R4:	94.6	R12:	93.4
CIE y:	0.4084	R5:	96.4	R13:	96.9
CIE z:	0.1326	R6:	92.3	R14:	97.1
Peak Wavelength (nm):	630	R7:	94.8	R15:	98.2
Dominant Wavelength (nm):	584	R8:	92.1		
Purity:	60.36523				
Rf:	93.8				
Rg:	102				




Test Conditions

Stabilization Time:	24M
Operation Time:	1H 24M
Sphere Temperature (°C):	24.0


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2505-441-28-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2694K
CIE x = 0.4590
CIE y = 0.4084
Duv = -0.0008

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2505-441-28-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	228	NR	750	5	NR	880	0	NR
365	0	NR	495	86	NR	625	239	NR	755	4	NR	885	0	NR
370	0	NR	500	100	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	111	NR	635	614	NR	765	3	NR	895	0	NR
380	0	NR	510	118	NR	640	147	NR	770	3	NR	900	0	NR
385	0	NR	515	122	NR	645	148	NR	775	2	NR	905	0	NR
390	0	NR	520	126	NR	650	127	NR	780	2	NR	910	0	NR
395	0	NR	525	128	NR	655	105	NR	785	2	NR	915	0	NR
400	1	NR	530	130	NR	660	88	NR	790	1	NR	920	0	NR
405	1	NR	535	134	NR	665	73	NR	795	1	NR	925	0	NR
410	2	NR	540	139	NR	670	70	NR	800	1	NR	930	0	NR
415	3	NR	545	143	NR	675	55	NR	805	1	NR	935	0	NR
420	6	NR	550	148	NR	680	47	NR	810	1	NR	940	0	NR
425	10	NR	555	154	NR	685	41	NR	815	1	NR	945	0	NR
430	18	NR	560	159	NR	690	35	NR	820	1	NR	950	0	NR
435	28	NR	565	164	NR	695	30	NR	825	1	NR	955	0	NR
440	44	NR	570	169	NR	700	25	NR	830	0	NR	960	0	NR
445	75	NR	575	175	NR	705	22	NR	835	0	NR	965	0	NR
450	107	NR	580	179	NR	710	18	NR	840	0	NR	970	0	NR
455	82	NR	585	186	NR	715	16	NR	845	0	NR	975	0	NR
460	58	NR	590	190	NR	720	13	NR	850	0	NR	980	0	NR
465	53	NR	595	192	NR	725	11	NR	855	0	NR	985	0	NR
470	45	NR	600	198	NR	730	10	NR	860	0	NR	990	0	NR
475	41	NR	605	203	NR	735	8	NR	865	0	NR	995	0	NR
480	46	NR	610	237	NR	740	7	NR	870	0	NR	1000	0	NR
485	57	NR	615	264	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-28-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.34**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	228	NR	750	5	NR	880	0	NR
365	0	NR	495	86	NR	625	239	NR	755	4	NR	885	0	NR
370	0	NR	500	100	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	111	NR	635	614	NR	765	3	NR	895	0	NR
380	0	NR	510	118	NR	640	147	NR	770	3	NR	900	0	NR
385	0	NR	515	122	NR	645	148	NR	775	2	NR	905	0	NR
390	0	NR	520	126	NR	650	127	NR	780	2	NR	910	0	NR
395	0	NR	525	128	NR	655	105	NR	785	2	NR	915	0	NR
400	1	NR	530	130	NR	660	88	NR	790	1	NR	920	0	NR
405	1	NR	535	134	NR	665	73	NR	795	1	NR	925	0	NR
410	2	NR	540	139	NR	670	70	NR	800	1	NR	930	0	NR
415	3	NR	545	143	NR	675	55	NR	805	1	NR	935	0	NR
420	6	NR	550	148	NR	680	47	NR	810	1	NR	940	0	NR
425	10	NR	555	154	NR	685	41	NR	815	1	NR	945	0	NR
430	18	NR	560	159	NR	690	35	NR	820	1	NR	950	0	NR
435	28	NR	565	164	NR	695	30	NR	825	1	NR	955	0	NR
440	44	NR	570	169	NR	700	25	NR	830	0	NR	960	0	NR
445	75	NR	575	175	NR	705	22	NR	835	0	NR	965	0	NR
450	107	NR	580	179	NR	710	18	NR	840	0	NR	970	0	NR
455	82	NR	585	186	NR	715	16	NR	845	0	NR	975	0	NR
460	58	NR	590	190	NR	720	13	NR	850	0	NR	980	0	NR
465	53	NR	595	192	NR	725	11	NR	855	0	NR	985	0	NR
470	45	NR	600	198	NR	730	10	NR	860	0	NR	990	0	NR
475	41	NR	605	203	NR	735	8	NR	865	0	NR	995	0	NR
480	46	NR	610	237	NR	740	7	NR	870	0	NR	1000	0	NR
485	57	NR	615	264	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-28-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.58**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	228	NR	750	5	NR	880	0	NR
365	0	NR	495	86	NR	625	239	NR	755	4	NR	885	0	NR
370	0	NR	500	100	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	111	NR	635	614	NR	765	3	NR	895	0	NR
380	0	NR	510	118	NR	640	147	NR	770	3	NR	900	0	NR
385	0	NR	515	122	NR	645	148	NR	775	2	NR	905	0	NR
390	0	NR	520	126	NR	650	127	NR	780	2	NR	910	0	NR
395	0	NR	525	128	NR	655	105	NR	785	2	NR	915	0	NR
400	1	NR	530	130	NR	660	88	NR	790	1	NR	920	0	NR
405	1	NR	535	134	NR	665	73	NR	795	1	NR	925	0	NR
410	2	NR	540	139	NR	670	70	NR	800	1	NR	930	0	NR
415	3	NR	545	143	NR	675	55	NR	805	1	NR	935	0	NR
420	6	NR	550	148	NR	680	47	NR	810	1	NR	940	0	NR
425	10	NR	555	154	NR	685	41	NR	815	1	NR	945	0	NR
430	18	NR	560	159	NR	690	35	NR	820	1	NR	950	0	NR
435	28	NR	565	164	NR	695	30	NR	825	1	NR	955	0	NR
440	44	NR	570	169	NR	700	25	NR	830	0	NR	960	0	NR
445	75	NR	575	175	NR	705	22	NR	835	0	NR	965	0	NR
450	107	NR	580	179	NR	710	18	NR	840	0	NR	970	0	NR
455	82	NR	585	186	NR	715	16	NR	845	0	NR	975	0	NR
460	58	NR	590	190	NR	720	13	NR	850	0	NR	980	0	NR
465	53	NR	595	192	NR	725	11	NR	855	0	NR	985	0	NR
470	45	NR	600	198	NR	730	10	NR	860	0	NR	990	0	NR
475	41	NR	605	203	NR	735	8	NR	865	0	NR	995	0	NR
480	46	NR	610	237	NR	740	7	NR	870	0	NR	1000	0	NR
485	57	NR	615	264	NR	745	6	NR	875	0	NR			


REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18


Summary


R_f = 93.8
R_g = 102
CIE R_a = 95.4
R_9 = 80.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 99	CES51 = 93	CES76 = 96
CES02 = 64	CES27 = 95	CES52 = 93	CES77 = 79
CES03 = 32	CES28 = 100	CES53 = 93	CES78 = 92
CES04 = 70	CES29 = 97	CES54 = 96	CES79 = 84
CES05 = 52	CES30 = 100	CES55 = 96	CES80 = 89
CES06 = 51	CES31 = 98	CES56 = 95	CES81 = 65
CES07 = 45	CES32 = 90	CES57 = 95	CES82 = 95
CES08 = 43	CES33 = 96	CES58 = 94	CES83 = 91
CES09 = 29	CES34 = 99	CES59 = 97	CES84 = 98
CES10 = 77	CES35 = 99	CES60 = 96	CES85 = 80
CES11 = 59	CES36 = 90	CES61 = 96	CES86 = 78
CES12 = 66	CES37 = 96	CES62 = 92	CES87 = 95
CES13 = 45	CES38 = 96	CES63 = 97	CES88 = 99
CES14 = 74	CES39 = 97	CES64 = 95	CES89 = 85
CES15 = 72	CES40 = 95	CES65 = 98	CES90 = 98
CES16 = 49	CES41 = 94	CES66 = 96	CES91 = 86
CES17 = 50	CES42 = 93	CES67 = 96	CES92 = 83
CES18 = 57	CES43 = 95	CES68 = 97	CES93 = 90
CES19 = 72	CES44 = 99	CES69 = 97	CES94 = 77
CES20 = 68	CES45 = 95	CES70 = 97	CES95 = 90
CES21 = 87	CES46 = 96	CES71 = 96	CES96 = 96
CES22 = 79	CES47 = 82	CES72 = 98	CES97 = 93
CES23 = 92	CES48 = 99	CES73 = 94	CES98 = 97
CES24 = 91	CES49 = 94	CES74 = 86	CES99 = 96
CES25 = 72	CES50 = 94	CES75 = 96	





REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18

Measure Comparisons





(END OF REPORT)