

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information


Test Method: LM-79-08
Report Number: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29474)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS,
FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 2700K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	617.4 lumens	Max Intensity:	1801.1 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	63.0 lumens/watt		
Luminous Opening:	Circular (Dia: 0.25' x H: 0')		
Beam Angle (50%):	35.6°H x 35.6°V	Field Angle (10%):	52.1°H x 52.1°V
Beam Lumens:	411.6 lumens	Field Lumens:	579.4 lumens
Beam Efficiency:	66.7%	Field Efficiency:	93.9%
Input Watts (W):	9.8		
Input Voltage (V):	120		
Input Current (A _{in}):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

Iso-Candela Plot






REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	
40		0.0	0.0	0.1	0.1	0.2	0.4	0.6	0.6	0.4	0.2	0.1	0.1	0.0	0.0		
30	0.0	0.0	0.0	0.1	0.1	0.6	3.0	7.8	7.8	3.0	0.6	0.1	0.1	0.0	0.0	0.0	
20		0.0	0.0	0.1	0.3	2.8	17.3	31.9	31.9	17.3	2.8	0.3	0.1	0.0	0.0		
10	0.0	0.0	0.0	0.1	0.5	7.2	31.0	49.3	49.3	31.0	7.2	0.5	0.1	0.0	0.0	0.0	
0		0.0	0.0	0.1	0.5	7.2	31.0	49.3	49.3	31.0	7.2	0.5	0.1	0.0	0.0		
-10	0.0	0.0	0.0	0.1	0.3	2.8	17.3	31.9	31.9	17.3	2.8	0.3	0.1	0.0	0.0	0.0	
-20		0.0	0.0	0.1	0.1	0.6	3.0	7.8	7.8	3.0	0.6	0.1	0.1	0.0	0.0		
-30	0.0	0.0	0.0	0.1	0.1	0.2	0.4	0.6	0.6	0.4	0.2	0.1	0.1	0.0	0.0	0.0	
-40		0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0		
-50	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0		
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0			
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0			
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	


REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

Luminous Intensity Polar Plot



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

Luminous Intensity Plot



Beam:
 H Angle: 35.6°
 V Angle: 35.6°
 Lumens: 411.6
 Efficiency: 66.7%

Field:
 H Angle: 52.1°
 V Angle: 52.1°
 Lumens: 579.4
 Efficiency: 93.9%

Spill:
 Lumens: 37.9
 Efficiency: 6.1%

— Vertical Distribution through 0-Deg
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	1
35°	0	0	0	0	0	0	0	0	0	0	1



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	0	0	0	0	0	0	0	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
31.25°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	0	1	1
28.75°	0	0	0	0	0	0	0	0	1	1	1
27.5°	0	0	0	0	0	0	0	0	1	1	1
26.25°	0	0	0	0	0	0	0	0	1	1	1
25°	0	0	0	0	0	0	0	0	1	1	1
23.75°	0	0	0	0	0	0	0	0	1	1	1
22.5°	0	0	0	0	0	0	0	1	1	1	1
21.25°	0	0	0	0	0	0	0	1	1	1	1
20°	0	0	0	0	0	0	0	1	1	1	1
18.75°	0	0	0	0	0	0	0	1	1	1	1
17.5°	0	0	0	0	0	0	0	1	1	1	1
16.25°	0	0	0	0	0	0	0	1	1	1	1
15°	0	0	0	0	0	0	0	1	1	1	1
13.75°	0	0	0	0	0	0	0	1	1	1	1
12.5°	0	0	0	0	0	0	1	1	1	1	1
11.25°	0	0	0	0	0	0	1	1	1	1	1
10°	0	0	0	0	0	0	1	1	1	1	1
8.75°	0	0	0	0	0	0	1	1	1	1	1
7.5°	0	0	0	0	0	0	1	1	1	1	1
6.25°	0	0	0	0	0	0	1	1	1	1	1
5°	0	0	0	0	0	0	1	1	1	1	1
3.75°	0	0	0	0	0	0	1	1	1	1	1
2.5°	0	0	0	0	0	0	1	1	1	1	1
1.25°	0	0	0	0	0	0	1	1	1	1	1
0°	0	0	0	0	0	0	1	1	1	1	1
-1.25°	0	0	0	0	0	0	1	1	1	1	1
-2.5°	0	0	0	0	0	0	1	1	1	1	1
-3.75°	0	0	0	0	0	0	1	1	1	1	1
-5°	0	0	0	0	0	0	1	1	1	1	1
-6.25°	0	0	0	0	0	0	1	1	1	1	1
-7.5°	0	0	0	0	0	0	1	1	1	1	1
-8.75°	0	0	0	0	0	0	1	1	1	1	1
-10°	0	0	0	0	0	0	1	1	1	1	1
-11.25°	0	0	0	0	0	0	1	1	1	1	1
-12.5°	0	0	0	0	0	0	1	1	1	1	1
-13.75°	0	0	0	0	0	0	0	1	1	1	1
-15°	0	0	0	0	0	0	0	1	1	1	1
-16.25°	0	0	0	0	0	0	0	1	1	1	1
-17.5°	0	0	0	0	0	0	0	1	1	1	1
-18.75°	0	0	0	0	0	0	0	1	1	1	1
-20°	0	0	0	0	0	0	0	1	1	1	1
-21.25°	0	0	0	0	0	0	0	1	1	1	1



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	0	0	0	0	0	1	1	1	1
-23.75°	0	0	0	0	0	0	0	0	1	1	1
-25°	0	0	0	0	0	0	0	0	1	1	1
-26.25°	0	0	0	0	0	0	0	0	1	1	1
-27.5°	0	0	0	0	0	0	0	0	1	1	1
-28.75°	0	0	0	0	0	0	0	0	1	1	1
-30°	0	0	0	0	0	0	0	0	0	1	1
-31.25°	0	0	0	0	0	0	0	0	0	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-33.75°	0	0	0	0	0	0	0	0	0	0	1
-35°	0	0	0	0	0	0	0	0	0	0	1
-36.25°	0	0	0	0	0	0	0	0	0	0	1
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	1
55°	0	0	0	0	0	0	0	0	0	1	1
53.75°	0	0	0	0	0	0	0	0	1	1	1
52.5°	0	0	0	0	0	0	0	1	1	1	1
51.25°	0	0	0	0	0	0	1	1	1	1	1
50°	0	0	0	0	0	1	1	1	1	1	1
48.75°	0	0	0	0	1	1	1	1	1	1	1
47.5°	0	0	0	0	1	1	1	1	1	1	1
46.25°	0	0	0	1	1	1	1	1	1	1	1
45°	0	0	1	1	1	1	1	1	1	1	1
43.75°	0	0	1	1	1	1	1	1	1	1	1
42.5°	0	1	1	1	1	1	1	1	1	1	1
41.25°	0	1	1	1	1	1	1	1	1	1	1
40°	1	1	1	1	1	1	1	1	1	1	1
38.75°	1	1	1	1	1	1	1	1	1	1	2
37.5°	1	1	1	1	1	1	1	1	1	1	2
36.25°	1	1	1	1	1	1	1	1	1	2	2
35°	1	1	1	1	1	1	1	1	1	2	2



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	1	1	1	1	1	1	2	2	2
32.5°	1	1	1	1	1	1	1	1	2	2	2
31.25°	1	1	1	1	1	1	1	2	2	2	2
30°	1	1	1	1	1	1	1	2	2	2	2
28.75°	1	1	1	1	1	1	2	2	2	2	2
27.5°	1	1	1	1	1	1	2	2	2	2	2
26.25°	1	1	1	1	1	1	2	2	2	2	2
25°	1	1	1	1	1	2	2	2	2	2	2
23.75°	1	1	1	1	1	2	2	2	2	2	2
22.5°	1	1	1	1	1	2	2	2	2	2	3
21.25°	1	1	1	1	2	2	2	2	2	2	3
20°	1	1	1	1	2	2	2	2	2	2	3
18.75°	1	1	1	1	2	2	2	2	2	3	3
17.5°	1	1	1	1	2	2	2	2	2	3	3
16.25°	1	1	1	1	2	2	2	2	2	3	3
15°	1	1	1	2	2	2	2	2	2	3	3
13.75°	1	1	1	2	2	2	2	2	3	3	3
12.5°	1	1	1	2	2	2	2	2	3	3	3
11.25°	1	1	1	2	2	2	2	2	3	3	3
10°	1	1	1	2	2	2	2	2	3	3	3
8.75°	1	1	1	2	2	2	2	2	3	3	3
7.5°	1	1	1	2	2	2	2	2	3	3	3
6.25°	1	1	1	2	2	2	2	2	3	3	3
5°	1	1	1	2	2	2	2	2	3	3	3
3.75°	1	1	1	2	2	2	2	2	3	3	3
2.5°	1	1	1	2	2	2	2	2	3	3	3
1.25°	1	1	1	2	2	2	2	2	3	3	3
0°	1	1	2	2	2	2	2	3	3	3	3
-1.25°	1	1	1	2	2	2	2	2	3	3	3
-2.5°	1	1	1	2	2	2	2	2	3	3	3
-3.75°	1	1	1	2	2	2	2	2	3	3	3
-5°	1	1	1	2	2	2	2	2	3	3	3
-6.25°	1	1	1	2	2	2	2	2	3	3	3
-7.5°	1	1	1	2	2	2	2	2	3	3	3
-8.75°	1	1	1	2	2	2	2	2	3	3	3
-10°	1	1	1	2	2	2	2	2	3	3	3
-11.25°	1	1	1	2	2	2	2	2	3	3	3
-12.5°	1	1	1	2	2	2	2	2	3	3	3
-13.75°	1	1	1	2	2	2	2	2	3	3	3
-15°	1	1	1	2	2	2	2	2	2	3	3
-16.25°	1	1	1	1	2	2	2	2	2	3	3
-17.5°	1	1	1	1	2	2	2	2	2	3	3
-18.75°	1	1	1	1	2	2	2	2	2	3	3
-20°	1	1	1	1	2	2	2	2	2	2	3
-21.25°	1	1	1	1	2	2	2	2	2	2	3



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	1	1	1	1	1	2	2	2	2	2	3
-23.75°	1	1	1	1	1	2	2	2	2	2	2
-25°	1	1	1	1	1	2	2	2	2	2	2
-26.25°	1	1	1	1	1	1	2	2	2	2	2
-27.5°	1	1	1	1	1	1	2	2	2	2	2
-28.75°	1	1	1	1	1	1	2	2	2	2	2
-30°	1	1	1	1	1	1	1	2	2	2	2
-31.25°	1	1	1	1	1	1	1	2	2	2	2
-32.5°	1	1	1	1	1	1	1	1	2	2	2
-33.75°	1	1	1	1	1	1	1	1	2	2	2
-35°	1	1	1	1	1	1	1	1	1	2	2
-36.25°	1	1	1	1	1	1	1	1	1	2	2
-37.5°	1	1	1	1	1	1	1	1	1	1	2
-38.75°	1	1	1	1	1	1	1	1	1	1	2
-40°	1	1	1	1	1	1	1	1	1	1	1
-41.25°	0	1	1	1	1	1	1	1	1	1	1
-42.5°	0	1	1	1	1	1	1	1	1	1	1
-43.75°	0	0	1	1	1	1	1	1	1	1	1
-45°	0	0	1	1	1	1	1	1	1	1	1
-46.25°	0	0	0	1	1	1	1	1	1	1	1
-47.5°	0	0	0	0	1	1	1	1	1	1	1
-48.75°	0	0	0	0	1	1	1	1	1	1	1
-50°	0	0	0	0	0	1	1	1	1	1	1
-51.25°	0	0	0	0	0	0	1	1	1	1	1
-52.5°	0	0	0	0	0	0	0	1	1	1	1
-53.75°	0	0	0	0	0	0	0	0	1	1	1
-55°	0	0	0	0	0	0	0	0	0	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	1
62.5°	0	0	0	0	0	0	0	1	1	1	1
61.25°	0	0	0	0	0	1	1	1	1	1	1
60°	0	0	0	1	1	1	1	1	1	1	1
58.75°	0	0	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	2
50°	1	1	1	1	1	1	1	1	2	2	2
48.75°	1	1	1	1	1	1	1	2	2	2	2
47.5°	1	1	1	1	1	1	2	2	2	2	2
46.25°	1	1	1	1	1	2	2	2	2	2	2
45°	1	1	1	2	2	2	2	2	2	2	2
43.75°	1	1	1	2	2	2	2	2	2	2	2
42.5°	1	1	2	2	2	2	2	2	2	2	3
41.25°	1	2	2	2	2	2	2	2	2	3	3
40°	2	2	2	2	2	2	2	2	3	3	3
38.75°	2	2	2	2	2	2	2	3	3	3	3
37.5°	2	2	2	2	2	2	3	3	3	3	3
36.25°	2	2	2	2	2	3	3	3	3	3	3
35°	2	2	2	2	3	3	3	3	3	3	3



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	2	2	2	2	3	3	3	3	3	3	3
32.5°	2	2	2	3	3	3	3	3	3	3	3
31.25°	2	2	2	3	3	3	3	3	3	3	4
30°	2	2	3	3	3	3	3	3	3	4	4
28.75°	2	3	3	3	3	3	3	3	4	4	4
27.5°	2	3	3	3	3	3	3	3	4	4	4
26.25°	3	3	3	3	3	3	3	4	4	4	4
25°	3	3	3	3	3	3	3	4	4	4	4
23.75°	3	3	3	3	3	3	4	4	4	4	5
22.5°	3	3	3	3	3	3	4	4	4	4	5
21.25°	3	3	3	3	3	4	4	4	4	5	5
20°	3	3	3	3	3	4	4	4	4	5	6
18.75°	3	3	3	3	4	4	4	4	5	5	6
17.5°	3	3	3	3	4	4	4	4	5	6	7
16.25°	3	3	3	3	4	4	4	5	5	6	7
15°	3	3	3	3	4	4	4	5	5	6	8
13.75°	3	3	3	4	4	4	4	5	6	7	8
12.5°	3	3	3	4	4	4	5	5	6	7	9
11.25°	3	3	3	4	4	4	5	5	6	8	10
10°	3	3	3	4	4	4	5	5	6	8	10
8.75°	3	3	3	4	4	4	5	6	7	9	11
7.5°	3	3	4	4	4	4	5	6	7	9	12
6.25°	3	3	4	4	4	4	5	6	7	9	12
5°	3	3	4	4	4	5	5	6	8	9	13
3.75°	3	3	4	4	4	5	5	6	8	10	13
2.5°	3	3	4	4	4	5	5	6	8	10	14
1.25°	3	3	4	4	4	5	5	6	8	10	14
0°	3	3	4	4	4	5	5	6	8	10	14
-1.25°	3	3	4	4	4	5	5	6	8	10	14
-2.5°	3	3	4	4	4	5	5	6	8	10	14
-3.75°	3	3	4	4	4	5	5	6	8	10	13
-5°	3	3	4	4	4	5	5	6	8	9	13
-6.25°	3	3	4	4	4	4	5	6	7	9	12
-7.5°	3	3	4	4	4	4	5	6	7	9	12
-8.75°	3	3	3	4	4	4	5	6	7	9	11
-10°	3	3	3	4	4	4	5	5	6	8	10
-11.25°	3	3	3	4	4	4	5	5	6	8	10
-12.5°	3	3	3	4	4	4	5	5	6	7	9
-13.75°	3	3	3	4	4	4	4	5	6	7	8
-15°	3	3	3	3	4	4	4	5	5	6	8
-16.25°	3	3	3	3	4	4	4	5	5	6	7
-17.5°	3	3	3	3	4	4	4	4	5	6	7
-18.75°	3	3	3	3	4	4	4	4	5	5	6
-20°	3	3	3	3	3	4	4	4	4	5	6
-21.25°	3	3	3	3	3	4	4	4	4	5	5



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	3	3	3	3	3	3	4	4	4	4	5
-23.75°	3	3	3	3	3	3	4	4	4	4	5
-25°	3	3	3	3	3	3	3	4	4	4	4
-26.25°	3	3	3	3	3	3	3	4	4	4	4
-27.5°	2	3	3	3	3	3	3	3	4	4	4
-28.75°	2	3	3	3	3	3	3	3	4	4	4
-30°	2	2	3	3	3	3	3	3	3	4	4
-31.25°	2	2	2	3	3	3	3	3	3	3	4
-32.5°	2	2	2	3	3	3	3	3	3	3	3
-33.75°	2	2	2	2	3	3	3	3	3	3	3
-35°	2	2	2	2	3	3	3	3	3	3	3
-36.25°	2	2	2	2	2	3	3	3	3	3	3
-37.5°	2	2	2	2	2	2	3	3	3	3	3
-38.75°	2	2	2	2	2	2	2	3	3	3	3
-40°	2	2	2	2	2	2	2	2	3	3	3
-41.25°	1	2	2	2	2	2	2	2	2	3	3
-42.5°	1	1	2	2	2	2	2	2	2	2	3
-43.75°	1	1	1	2	2	2	2	2	2	2	2
-45°	1	1	1	2	2	2	2	2	2	2	2
-46.25°	1	1	1	1	1	2	2	2	2	2	2
-47.5°	1	1	1	1	1	1	2	2	2	2	2
-48.75°	1	1	1	1	1	1	1	2	2	2	2
-50°	1	1	1	1	1	1	1	1	2	2	2
-51.25°	1	1	1	1	1	1	1	1	1	1	2
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	0	0	1	1	1	1	1	1	1	1	1
-60°	0	0	0	1	1	1	1	1	1	1	1
-61.25°	0	0	0	0	0	1	1	1	1	1	1
-62.5°	0	0	0	0	0	0	0	1	1	1	1
-63.75°	0	0	0	0	0	0	0	0	0	0	1
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	1
66.25°	0	0	0	0	0	1	1	1	1	1	1
65°	0	0	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	2	2	2
55°	1	1	1	1	1	2	2	2	2	2	2
53.75°	1	1	1	2	2	2	2	2	2	2	2
52.5°	1	2	2	2	2	2	2	2	2	2	2
51.25°	2	2	2	2	2	2	2	2	2	2	2
50°	2	2	2	2	2	2	2	2	2	2	3
48.75°	2	2	2	2	2	2	2	3	3	3	3
47.5°	2	2	2	2	2	3	3	3	3	3	3
46.25°	2	2	2	2	3	3	3	3	3	3	3
45°	2	2	3	3	3	3	3	3	3	3	3
43.75°	3	3	3	3	3	3	3	3	3	3	3
42.5°	3	3	3	3	3	3	3	3	3	3	3
41.25°	3	3	3	3	3	3	3	3	3	4	4
40°	3	3	3	3	3	3	3	4	4	4	4
38.75°	3	3	3	3	3	4	4	4	4	4	4
37.5°	3	3	3	3	4	4	4	4	4	4	4
36.25°	3	3	3	4	4	4	4	4	4	5	5
35°	3	3	4	4	4	4	4	5	5	5	6



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	3	4	4	4	4	4	5	5	5	6	6
32.5°	4	4	4	4	4	5	5	6	6	7	8
31.25°	4	4	4	4	5	5	6	6	7	8	9
30°	4	4	4	5	5	6	6	8	9	10	12
28.75°	4	4	5	5	6	6	8	9	10	13	15
27.5°	4	5	5	6	6	8	9	11	13	16	18
26.25°	5	5	6	6	8	9	11	13	16	19	24
25°	5	5	6	7	9	10	13	16	19	24	29
23.75°	5	6	7	8	10	13	16	19	24	29	35
22.5°	6	6	8	9	12	15	18	24	29	35	41
21.25°	6	7	9	11	14	17	22	28	34	40	46
20°	7	8	10	13	16	21	27	33	39	46	53
18.75°	7	9	11	15	18	25	31	37	44	51	60
17.5°	8	10	13	17	22	28	35	42	49	58	76
16.25°	9	11	15	19	25	32	39	46	55	70	101
15°	10	13	16	22	29	36	43	50	62	87	132
13.75°	11	14	18	25	32	39	47	56	74	112	169
12.5°	12	15	20	27	35	42	50	62	90	141	209
11.25°	13	17	23	30	37	45	55	72	111	171	249
10°	14	18	25	32	40	48	59	82	133	204	290
8.75°	15	19	27	34	42	51	65	98	157	235	327
7.5°	16	21	28	36	44	54	72	113	178	263	363
6.25°	16	22	30	38	46	56	78	126	199	290	395
5°	17	23	31	39	48	58	84	140	217	312	421
3.75°	17	24	32	40	49	60	92	151	232	330	442
2.5°	18	25	32	41	49	63	97	159	242	344	458
1.25°	18	25	33	41	50	65	100	163	248	352	467
0°	18	25	33	42	50	65	101	165	250	355	471
-1.25°	18	25	33	41	50	65	100	163	248	352	467
-2.5°	18	25	32	41	49	63	97	159	242	344	458
-3.75°	17	24	32	40	49	60	92	151	232	330	442
-5°	17	23	31	39	48	58	84	140	217	312	421
-6.25°	16	22	30	38	46	56	78	126	199	290	395
-7.5°	16	21	28	36	44	54	72	113	178	263	363
-8.75°	15	19	27	34	42	51	65	98	157	235	327
-10°	14	18	25	32	40	48	59	82	133	204	290
-11.25°	13	17	23	30	37	45	55	72	111	171	249
-12.5°	12	15	20	27	35	42	50	62	90	141	209
-13.75°	11	14	18	25	32	39	47	56	74	112	169
-15°	10	13	16	22	29	36	43	50	62	87	132
-16.25°	9	11	15	19	25	32	39	46	55	70	101
-17.5°	8	10	13	17	22	28	35	42	49	58	76
-18.75°	7	9	11	15	18	25	31	37	44	51	60
-20°	7	8	10	13	16	21	27	33	39	46	53
-21.25°	6	7	9	11	14	17	22	28	34	40	46



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	6	6	8	9	12	15	18	24	29	35	41
-23.75°	5	6	7	8	10	13	16	19	24	29	35
-25°	5	5	6	7	9	10	13	16	19	24	29
-26.25°	5	5	6	6	8	9	11	13	16	19	24
-27.5°	4	5	5	6	6	8	9	11	13	16	18
-28.75°	4	4	5	5	6	6	8	9	10	13	15
-30°	4	4	4	5	5	6	6	8	9	10	12
-31.25°	4	4	4	4	5	5	6	6	7	8	9
-32.5°	4	4	4	4	4	5	5	6	6	7	8
-33.75°	3	4	4	4	4	4	5	5	5	6	6
-35°	3	3	4	4	4	4	4	5	5	5	6
-36.25°	3	3	3	4	4	4	4	4	4	5	5
-37.5°	3	3	3	3	4	4	4	4	4	4	4
-38.75°	3	3	3	3	3	4	4	4	4	4	4
-40°	3	3	3	3	3	3	3	4	4	4	4
-41.25°	3	3	3	3	3	3	3	3	3	4	4
-42.5°	3	3	3	3	3	3	3	3	3	3	3
-43.75°	3	3	3	3	3	3	3	3	3	3	3
-45°	2	2	3	3	3	3	3	3	3	3	3
-46.25°	2	2	2	2	3	3	3	3	3	3	3
-47.5°	2	2	2	2	2	3	3	3	3	3	3
-48.75°	2	2	2	2	2	2	2	3	3	3	3
-50°	2	2	2	2	2	2	2	2	2	2	3
-51.25°	2	2	2	2	2	2	2	2	2	2	2
-52.5°	1	2	2	2	2	2	2	2	2	2	2
-53.75°	1	1	1	2	2	2	2	2	2	2	2
-55°	1	1	1	1	1	2	2	2	2	2	2
-56.25°	1	1	1	1	1	1	1	1	2	2	2
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	0	0	1	1	1	1	1	1	1	1	1
-66.25°	0	0	0	0	0	1	1	1	1	1	1
-67.5°	0	0	0	0	0	0	0	0	0	0	1
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	2
53.75°	2	2	2	2	2	2	2	2	2	2	2
52.5°	2	2	2	2	2	2	3	3	3	3	3
51.25°	2	2	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	3
47.5°	3	3	3	3	3	3	3	3	3	3	3
46.25°	3	3	3	3	3	3	3	3	3	3	3
45°	3	3	3	3	3	3	4	4	4	4	4
43.75°	3	3	4	4	4	4	4	4	4	4	4
42.5°	4	4	4	4	4	4	4	4	4	4	4
41.25°	4	4	4	4	4	4	4	5	5	5	5
40°	4	4	4	4	5	5	5	5	5	5	6
38.75°	4	4	5	5	5	5	6	6	6	6	7
37.5°	5	5	5	6	6	6	7	7	8	8	9
36.25°	5	6	6	7	7	8	8	9	10	10	11
35°	6	7	7	8	9	10	11	12	13	14	15



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	7	8	9	10	11	13	14	15	17	18	19
32.5°	9	10	11	13	15	16	18	20	23	25	27
31.25°	11	13	15	17	19	22	25	27	30	32	34
30°	14	16	18	22	25	29	32	35	37	40	42
28.75°	17	21	25	28	32	36	39	42	45	48	51
27.5°	22	27	31	35	39	43	47	50	55	59	65
26.25°	28	33	37	42	46	50	56	62	72	82	98
25°	34	39	44	49	55	62	74	90	111	133	157
23.75°	40	46	51	58	70	87	112	141	171	204	235
22.5°	46	53	60	76	101	132	169	209	249	290	327
21.25°	53	63	80	111	150	193	241	291	339	388	432
20°	63	81	116	160	211	266	323	382	439	493	541
18.75°	80	116	164	220	282	347	413	479	541	597	645
17.5°	111	160	220	287	359	433	507	575	638	694	745
16.25°	150	211	282	359	440	520	596	665	730	790	847
15°	193	266	347	433	520	604	679	752	822	888	947
13.75°	241	323	413	507	596	679	759	838	912	981	1048
12.5°	291	382	479	575	665	752	838	920	999	1076	1140
11.25°	339	439	541	638	730	822	912	999	1084	1158	1226
10°	388	493	597	694	790	888	981	1076	1158	1236	1303
8.75°	432	541	645	745	847	947	1048	1140	1226	1303	1371
7.5°	473	583	688	792	898	1001	1104	1198	1285	1361	1430
6.25°	508	619	725	833	941	1050	1152	1249	1335	1411	1482
5°	537	648	756	868	977	1090	1192	1288	1374	1453	1525
3.75°	559	671	781	895	1008	1120	1224	1320	1406	1486	1558
2.5°	575	687	799	915	1030	1142	1247	1342	1429	1510	1583
1.25°	585	697	811	926	1043	1155	1260	1355	1443	1525	1598
0°	589	700	815	930	1048	1159	1265	1360	1448	1530	1602
-1.25°	585	697	811	926	1043	1155	1260	1355	1443	1525	1598
-2.5°	575	687	799	915	1030	1142	1247	1342	1429	1510	1583
-3.75°	559	671	781	895	1008	1120	1224	1320	1406	1486	1558
-5°	537	648	756	868	977	1090	1192	1288	1374	1453	1525
-6.25°	508	619	725	833	941	1050	1152	1249	1335	1411	1482
-7.5°	473	583	688	792	898	1001	1104	1198	1285	1361	1430
-8.75°	432	541	645	745	847	947	1048	1140	1226	1303	1371
-10°	388	493	597	694	790	888	981	1076	1158	1236	1303
-11.25°	339	439	541	638	730	822	912	999	1084	1158	1226
-12.5°	291	382	479	575	665	752	838	920	999	1076	1140
-13.75°	241	323	413	507	596	679	759	838	912	981	1048
-15°	193	266	347	433	520	604	679	752	822	888	947
-16.25°	150	211	282	359	440	520	596	665	730	790	847
-17.5°	111	160	220	287	359	433	507	575	638	694	745
-18.75°	80	116	164	220	282	347	413	479	541	597	645
-20°	63	81	116	160	211	266	323	382	439	493	541
-21.25°	53	63	80	111	150	193	241	291	339	388	432



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	46	53	60	76	101	132	169	209	249	290	327
-23.75°	40	46	51	58	70	87	112	141	171	204	235
-25°	34	39	44	49	55	62	74	90	111	133	157
-26.25°	28	33	37	42	46	50	56	62	72	82	98
-27.5°	22	27	31	35	39	43	47	50	55	59	65
-28.75°	17	21	25	28	32	36	39	42	45	48	51
-30°	14	16	18	22	25	29	32	35	37	40	42
-31.25°	11	13	15	17	19	22	25	27	30	32	34
-32.5°	9	10	11	13	15	16	18	20	23	25	27
-33.75°	7	8	9	10	11	13	14	15	17	18	19
-35°	6	7	7	8	9	10	11	12	13	14	15
-36.25°	5	6	6	7	7	8	8	9	10	10	11
-37.5°	5	5	5	6	6	6	7	7	8	8	9
-38.75°	4	4	5	5	5	5	6	6	6	6	7
-40°	4	4	4	4	5	5	5	5	5	5	6
-41.25°	4	4	4	4	4	4	4	5	5	5	5
-42.5°	4	4	4	4	4	4	4	4	4	4	4
-43.75°	3	3	4	4	4	4	4	4	4	4	4
-45°	3	3	3	3	3	3	4	4	4	4	4
-46.25°	3	3	3	3	3	3	3	3	3	3	3
-47.5°	3	3	3	3	3	3	3	3	3	3	3
-48.75°	3	3	3	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	2	2	3	3	3	3	3	3	3	3	3
-52.5°	2	2	2	2	2	2	3	3	3	3	3
-53.75°	2	2	2	2	2	2	2	2	2	2	2
-55°	2	2	2	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	1	1	1	1	1	2	2	2	2	2	2
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	0	0	0	0	0	0	0	1	1	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	2	1	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	2
53.75°	2	2	2	2	2	2	3	2	2	2	2
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	3
47.5°	3	3	3	3	3	3	3	3	3	3	3
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	4	4	4	4	4	4
42.5°	4	4	5	5	5	5	5	5	5	5	5
41.25°	5	5	5	5	5	5	5	5	5	5	5
40°	6	6	6	6	6	6	6	6	6	6	6
38.75°	7	7	8	8	8	8	8	8	8	8	8
37.5°	9	9	9	10	10	10	10	10	10	10	9
36.25°	12	12	13	13	14	14	14	14	14	13	13
35°	16	16	17	17	18	18	18	18	18	17	17



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	21	22	23	24	25	25	25	25	25	24	23
32.5°	28	30	31	32	32	33	33	33	32	32	31
31.25°	36	38	39	40	41	41	42	41	41	40	39
30°	44	46	48	49	49	50	50	50	49	49	48
28.75°	54	56	58	60	63	65	65	65	63	60	58
27.5°	72	78	84	92	97	100	101	100	97	92	84
26.25°	113	126	140	151	159	163	165	163	159	151	140
25°	178	199	217	232	242	248	250	248	242	232	217
23.75°	263	290	312	330	344	352	355	352	344	330	312
22.5°	363	395	421	442	458	467	471	467	458	442	421
21.25°	473	508	537	559	575	585	589	585	575	559	537
20°	583	619	648	671	687	697	700	697	687	671	648
18.75°	688	725	756	781	799	811	815	811	799	781	756
17.5°	792	833	868	895	915	926	930	926	915	895	868
16.25°	898	941	977	1008	1030	1043	1048	1043	1030	1008	977
15°	1001	1050	1090	1120	1142	1155	1159	1155	1142	1120	1090
13.75°	1104	1152	1192	1224	1247	1260	1265	1260	1247	1224	1192
12.5°	1198	1249	1288	1320	1342	1355	1360	1355	1342	1320	1288
11.25°	1285	1335	1374	1406	1429	1443	1448	1443	1429	1406	1374
10°	1361	1411	1453	1486	1510	1525	1530	1525	1510	1486	1453
8.75°	1430	1482	1525	1558	1583	1598	1602	1598	1583	1558	1525
7.5°	1491	1544	1588	1622	1647	1661	1666	1661	1647	1622	1588
6.25°	1544	1598	1643	1676	1700	1713	1718	1713	1700	1676	1643
5°	1588	1643	1687	1718	1739	1751	1756	1751	1739	1718	1687
3.75°	1622	1676	1718	1747	1766	1777	1779	1777	1766	1747	1718
2.5°	1647	1700	1739	1766	1781	1787	1789	1787	1781	1766	1739
1.25°	1661	1713	1751	1777	1787	1793	1795	1793	1787	1777	1751
0°	1666	1718	1756	1779	1789	1795	1801	1795	1789	1779	1756
-1.25°	1661	1713	1751	1777	1787	1793	1795	1793	1787	1777	1751
-2.5°	1647	1700	1739	1766	1781	1787	1789	1787	1781	1766	1739
-3.75°	1622	1676	1718	1747	1766	1777	1779	1777	1766	1747	1718
-5°	1588	1643	1687	1718	1739	1751	1756	1751	1739	1718	1687
-6.25°	1544	1598	1643	1676	1700	1713	1718	1713	1700	1676	1643
-7.5°	1491	1544	1588	1622	1647	1661	1666	1661	1647	1622	1588
-8.75°	1430	1482	1525	1558	1583	1598	1602	1598	1583	1558	1525
-10°	1361	1411	1453	1486	1510	1525	1530	1525	1510	1486	1453
-11.25°	1285	1335	1374	1406	1429	1443	1448	1443	1429	1406	1374
-12.5°	1198	1249	1288	1320	1342	1355	1360	1355	1342	1320	1288
-13.75°	1104	1152	1192	1224	1247	1260	1265	1260	1247	1224	1192
-15°	1001	1050	1090	1120	1142	1155	1159	1155	1142	1120	1090
-16.25°	898	941	977	1008	1030	1043	1048	1043	1030	1008	977
-17.5°	792	833	868	895	915	926	930	926	915	895	868
-18.75°	688	725	756	781	799	811	815	811	799	781	756
-20°	583	619	648	671	687	697	700	697	687	671	648
-21.25°	473	508	537	559	575	585	589	585	575	559	537



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	363	395	421	442	458	467	471	467	458	442	421
-23.75°	263	290	312	330	344	352	355	352	344	330	312
-25°	178	199	217	232	242	248	250	248	242	232	217
-26.25°	113	126	140	151	159	163	165	163	159	151	140
-27.5°	72	78	84	92	97	100	101	100	97	92	84
-28.75°	54	56	58	60	63	65	65	65	63	60	58
-30°	44	46	48	49	49	50	50	50	49	49	48
-31.25°	36	38	39	40	41	41	42	41	41	40	39
-32.5°	28	30	31	32	32	33	33	33	32	32	31
-33.75°	21	22	23	24	25	25	25	25	25	24	23
-35°	16	16	17	17	18	18	18	18	18	17	17
-36.25°	12	12	13	13	14	14	14	14	14	13	13
-37.5°	9	9	9	10	10	10	10	10	10	10	9
-38.75°	7	7	8	8	8	8	8	8	8	8	8
-40°	6	6	6	6	6	6	6	6	6	6	6
-41.25°	5	5	5	5	5	5	5	5	5	5	5
-42.5°	4	4	5	5	5	5	5	5	5	5	5
-43.75°	4	4	4	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	3	3	3	3	3	3	3	3	3	3	3
-48.75°	3	3	3	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	3	2	2	2	2
-55°	2	2	2	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	1	1	1	1	1	1	2	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	1	1	0	0	0	0	0
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	2	2	2	2	2	2	2	2	1	1	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	2
53.75°	2	2	2	2	2	2	2	2	2	2	2
52.5°	3	3	3	3	3	3	3	2	2	2	2
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	3
47.5°	3	3	3	3	3	3	3	3	3	3	3
46.25°	4	4	3	3	3	3	3	3	3	3	3
45°	4	4	4	4	4	4	4	3	3	3	3
43.75°	4	4	4	4	4	4	4	4	4	4	4
42.5°	4	4	4	4	4	4	4	4	4	4	4
41.25°	5	5	5	5	5	5	4	4	4	4	4
40°	6	6	6	5	5	5	5	5	5	4	4
38.75°	7	7	7	6	6	6	6	5	5	5	5
37.5°	9	9	9	8	8	7	7	6	6	6	5
36.25°	12	12	11	10	10	9	8	8	7	7	6
35°	16	16	15	14	13	12	11	10	9	8	7



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	22	21	19	18	17	15	14	13	11	10	9
32.5°	30	28	27	25	23	20	18	16	15	13	11
31.25°	38	36	34	32	30	27	25	22	19	17	15
30°	46	44	42	40	37	35	32	29	25	22	18
28.75°	56	54	51	48	45	42	39	36	32	28	25
27.5°	78	72	65	59	55	50	47	43	39	35	31
26.25°	126	113	98	82	72	62	56	50	46	42	37
25°	199	178	157	133	111	90	74	62	55	49	44
23.75°	290	263	235	204	171	141	112	87	70	58	51
22.5°	395	363	327	290	249	209	169	132	101	76	60
21.25°	508	473	432	388	339	291	241	193	150	111	80
20°	619	583	541	493	439	382	323	266	211	160	116
18.75°	725	688	645	597	541	479	413	347	282	220	164
17.5°	833	792	745	694	638	575	507	433	359	287	220
16.25°	941	898	847	790	730	665	596	520	440	359	282
15°	1050	1001	947	888	822	752	679	604	520	433	347
13.75°	1152	1104	1048	981	912	838	759	679	596	507	413
12.5°	1249	1198	1140	1076	999	920	838	752	665	575	479
11.25°	1335	1285	1226	1158	1084	999	912	822	730	638	541
10°	1411	1361	1303	1236	1158	1076	981	888	790	694	597
8.75°	1482	1430	1371	1303	1226	1140	1048	947	847	745	645
7.5°	1544	1491	1430	1361	1285	1198	1104	1001	898	792	688
6.25°	1598	1544	1482	1411	1335	1249	1152	1050	941	833	725
5°	1643	1588	1525	1453	1374	1288	1192	1090	977	868	756
3.75°	1676	1622	1558	1486	1406	1320	1224	1120	1008	895	781
2.5°	1700	1647	1583	1510	1429	1342	1247	1142	1030	915	799
1.25°	1713	1661	1598	1525	1443	1355	1260	1155	1043	926	811
0°	1718	1666	1602	1530	1448	1360	1265	1159	1048	930	815
-1.25°	1713	1661	1598	1525	1443	1355	1260	1155	1043	926	811
-2.5°	1700	1647	1583	1510	1429	1342	1247	1142	1030	915	799
-3.75°	1676	1622	1558	1486	1406	1320	1224	1120	1008	895	781
-5°	1643	1588	1525	1453	1374	1288	1192	1090	977	868	756
-6.25°	1598	1544	1482	1411	1335	1249	1152	1050	941	833	725
-7.5°	1544	1491	1430	1361	1285	1198	1104	1001	898	792	688
-8.75°	1482	1430	1371	1303	1226	1140	1048	947	847	745	645
-10°	1411	1361	1303	1236	1158	1076	981	888	790	694	597
-11.25°	1335	1285	1226	1158	1084	999	912	822	730	638	541
-12.5°	1249	1198	1140	1076	999	920	838	752	665	575	479
-13.75°	1152	1104	1048	981	912	838	759	679	596	507	413
-15°	1050	1001	947	888	822	752	679	604	520	433	347
-16.25°	941	898	847	790	730	665	596	520	440	359	282
-17.5°	833	792	745	694	638	575	507	433	359	287	220
-18.75°	725	688	645	597	541	479	413	347	282	220	164
-20°	619	583	541	493	439	382	323	266	211	160	116
-21.25°	508	473	432	388	339	291	241	193	150	111	80



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	395	363	327	290	249	209	169	132	101	76	60
-23.75°	290	263	235	204	171	141	112	87	70	58	51
-25°	199	178	157	133	111	90	74	62	55	49	44
-26.25°	126	113	98	82	72	62	56	50	46	42	37
-27.5°	78	72	65	59	55	50	47	43	39	35	31
-28.75°	56	54	51	48	45	42	39	36	32	28	25
-30°	46	44	42	40	37	35	32	29	25	22	18
-31.25°	38	36	34	32	30	27	25	22	19	17	15
-32.5°	30	28	27	25	23	20	18	16	15	13	11
-33.75°	22	21	19	18	17	15	14	13	11	10	9
-35°	16	16	15	14	13	12	11	10	9	8	7
-36.25°	12	12	11	10	10	9	8	8	7	7	6
-37.5°	9	9	9	8	8	7	7	6	6	6	5
-38.75°	7	7	7	6	6	6	6	5	5	5	5
-40°	6	6	6	5	5	5	5	5	5	4	4
-41.25°	5	5	5	5	5	5	4	4	4	4	4
-42.5°	4	4	4	4	4	4	4	4	4	4	4
-43.75°	4	4	4	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	3	3	3	3
-46.25°	4	4	3	3	3	3	3	3	3	3	3
-47.5°	3	3	3	3	3	3	3	3	3	3	3
-48.75°	3	3	3	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	2	2	2	2
-53.75°	2	2	2	2	2	2	2	2	2	2	2
-55°	2	2	2	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	1	1	1	0	0	0	0	0	0	0	0
66.25°	1	1	1	1	1	1	1	1	0	0	0
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	2	1	1	1	1	1	1	1	1	1
56.25°	2	2	2	2	2	1	1	1	1	1	1
55°	2	2	2	2	2	2	2	2	1	1	1
53.75°	2	2	2	2	2	2	2	2	2	2	1
52.5°	2	2	2	2	2	2	2	2	2	2	2
51.25°	2	2	2	2	2	2	2	2	2	2	2
50°	3	3	3	2	2	2	2	2	2	2	2
48.75°	3	3	3	3	3	3	2	2	2	2	2
47.5°	3	3	3	3	3	3	3	3	2	2	2
46.25°	3	3	3	3	3	3	3	3	3	2	2
45°	3	3	3	3	3	3	3	3	3	3	3
43.75°	3	3	3	3	3	3	3	3	3	3	3
42.5°	4	4	3	3	3	3	3	3	3	3	3
41.25°	4	4	4	4	3	3	3	3	3	3	3
40°	4	4	4	4	4	4	3	3	3	3	3
38.75°	4	4	4	4	4	4	4	4	3	3	3
37.5°	5	5	4	4	4	4	4	4	4	3	3
36.25°	6	5	5	5	4	4	4	4	4	4	3
35°	7	6	6	5	5	5	4	4	4	4	4



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	8	7	6	6	5	5	5	4	4	4	4
32.5°	10	9	8	7	6	6	5	5	4	4	4
31.25°	13	11	9	8	7	6	6	5	5	4	4
30°	16	14	12	10	9	8	6	6	5	5	4
28.75°	21	17	15	13	10	9	8	6	6	5	5
27.5°	27	22	18	16	13	11	9	8	6	6	5
26.25°	33	28	24	19	16	13	11	9	8	6	6
25°	39	34	29	24	19	16	13	10	9	7	6
23.75°	46	40	35	29	24	19	16	13	10	8	7
22.5°	53	46	41	35	29	24	18	15	12	9	8
21.25°	63	53	46	40	34	28	22	17	14	11	9
20°	81	63	53	46	39	33	27	21	16	13	10
18.75°	116	80	60	51	44	37	31	25	18	15	11
17.5°	160	111	76	58	49	42	35	28	22	17	13
16.25°	211	150	101	70	55	46	39	32	25	19	15
15°	266	193	132	87	62	50	43	36	29	22	16
13.75°	323	241	169	112	74	56	47	39	32	25	18
12.5°	382	291	209	141	90	62	50	42	35	27	20
11.25°	439	339	249	171	111	72	55	45	37	30	23
10°	493	388	290	204	133	82	59	48	40	32	25
8.75°	541	432	327	235	157	98	65	51	42	34	27
7.5°	583	473	363	263	178	113	72	54	44	36	28
6.25°	619	508	395	290	199	126	78	56	46	38	30
5°	648	537	421	312	217	140	84	58	48	39	31
3.75°	671	559	442	330	232	151	92	60	49	40	32
2.5°	687	575	458	344	242	159	97	63	49	41	32
1.25°	697	585	467	352	248	163	100	65	50	41	33
0°	700	589	471	355	250	165	101	65	50	42	33
-1.25°	697	585	467	352	248	163	100	65	50	41	33
-2.5°	687	575	458	344	242	159	97	63	49	41	32
-3.75°	671	559	442	330	232	151	92	60	49	40	32
-5°	648	537	421	312	217	140	84	58	48	39	31
-6.25°	619	508	395	290	199	126	78	56	46	38	30
-7.5°	583	473	363	263	178	113	72	54	44	36	28
-8.75°	541	432	327	235	157	98	65	51	42	34	27
-10°	493	388	290	204	133	82	59	48	40	32	25
-11.25°	439	339	249	171	111	72	55	45	37	30	23
-12.5°	382	291	209	141	90	62	50	42	35	27	20
-13.75°	323	241	169	112	74	56	47	39	32	25	18
-15°	266	193	132	87	62	50	43	36	29	22	16
-16.25°	211	150	101	70	55	46	39	32	25	19	15
-17.5°	160	111	76	58	49	42	35	28	22	17	13
-18.75°	116	80	60	51	44	37	31	25	18	15	11
-20°	81	63	53	46	39	33	27	21	16	13	10
-21.25°	63	53	46	40	34	28	22	17	14	11	9



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	53	46	41	35	29	24	18	15	12	9	8
-23.75°	46	40	35	29	24	19	16	13	10	8	7
-25°	39	34	29	24	19	16	13	10	9	7	6
-26.25°	33	28	24	19	16	13	11	9	8	6	6
-27.5°	27	22	18	16	13	11	9	8	6	6	5
-28.75°	21	17	15	13	10	9	8	6	6	5	5
-30°	16	14	12	10	9	8	6	6	5	5	4
-31.25°	13	11	9	8	7	6	6	5	5	4	4
-32.5°	10	9	8	7	6	6	5	5	4	4	4
-33.75°	8	7	6	6	5	5	5	4	4	4	4
-35°	7	6	6	5	5	5	4	4	4	4	4
-36.25°	6	5	5	5	4	4	4	4	4	4	3
-37.5°	5	5	4	4	4	4	4	4	4	3	3
-38.75°	4	4	4	4	4	4	4	4	3	3	3
-40°	4	4	4	4	4	4	3	3	3	3	3
-41.25°	4	4	4	4	3	3	3	3	3	3	3
-42.5°	4	4	3	3	3	3	3	3	3	3	3
-43.75°	3	3	3	3	3	3	3	3	3	3	3
-45°	3	3	3	3	3	3	3	3	3	3	3
-46.25°	3	3	3	3	3	3	3	3	3	2	2
-47.5°	3	3	3	3	3	3	3	3	2	2	2
-48.75°	3	3	3	3	3	3	2	2	2	2	2
-50°	3	3	3	2	2	2	2	2	2	2	2
-51.25°	2	2	2	2	2	2	2	2	2	2	2
-52.5°	2	2	2	2	2	2	2	2	2	2	2
-53.75°	2	2	2	2	2	2	2	2	2	2	1
-55°	2	2	2	2	2	2	2	2	1	1	1
-56.25°	2	2	2	2	2	1	1	1	1	1	1
-57.5°	2	2	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	0	0	0
-67.5°	1	1	1	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	1	1	1	0	0	0	0	0	0	0	0
62.5°	1	1	1	1	1	1	0	0	0	0	0
61.25°	1	1	1	1	1	1	1	1	0	0	0
60°	1	1	1	1	1	1	1	1	1	1	0
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	2	1	1	1	1	1	1	1	1	1	1
51.25°	2	2	2	1	1	1	1	1	1	1	1
50°	2	2	2	2	2	1	1	1	1	1	1
48.75°	2	2	2	2	2	2	1	1	1	1	1
47.5°	2	2	2	2	2	2	2	1	1	1	1
46.25°	2	2	2	2	2	2	2	2	1	1	1
45°	2	2	2	2	2	2	2	2	2	2	1
43.75°	3	3	2	2	2	2	2	2	2	2	1
42.5°	3	3	3	2	2	2	2	2	2	2	2
41.25°	3	3	3	3	2	2	2	2	2	2	2
40°	3	3	3	3	3	2	2	2	2	2	2
38.75°	3	3	3	3	3	3	2	2	2	2	2
37.5°	3	3	3	3	3	3	3	2	2	2	2
36.25°	3	3	3	3	3	3	3	3	2	2	2
35°	3	3	3	3	3	3	3	3	3	2	2



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	4	3	3	3	3	3	3	3	3	2	2
32.5°	4	4	3	3	3	3	3	3	3	3	2
31.25°	4	4	4	3	3	3	3	3	3	3	2
30°	4	4	4	4	3	3	3	3	3	3	3
28.75°	4	4	4	4	4	3	3	3	3	3	3
27.5°	5	4	4	4	4	3	3	3	3	3	3
26.25°	5	5	4	4	4	4	3	3	3	3	3
25°	5	5	4	4	4	4	3	3	3	3	3
23.75°	6	5	5	4	4	4	4	3	3	3	3
22.5°	6	6	5	4	4	4	4	3	3	3	3
21.25°	7	6	5	5	4	4	4	4	3	3	3
20°	8	7	6	5	4	4	4	4	3	3	3
18.75°	9	7	6	5	5	4	4	4	4	3	3
17.5°	10	8	7	6	5	4	4	4	4	3	3
16.25°	11	9	7	6	5	5	4	4	4	3	3
15°	13	10	8	6	5	5	4	4	4	3	3
13.75°	14	11	8	7	6	5	4	4	4	4	3
12.5°	15	12	9	7	6	5	5	4	4	4	3
11.25°	17	13	10	8	6	5	5	4	4	4	3
10°	18	14	10	8	6	5	5	4	4	4	3
8.75°	19	15	11	9	7	6	5	4	4	4	3
7.5°	21	16	12	9	7	6	5	4	4	4	4
6.25°	22	16	12	9	7	6	5	4	4	4	4
5°	23	17	13	9	8	6	5	5	4	4	4
3.75°	24	17	13	10	8	6	5	5	4	4	4
2.5°	25	18	14	10	8	6	5	5	4	4	4
1.25°	25	18	14	10	8	6	5	5	4	4	4
0°	25	18	14	10	8	6	5	5	4	4	4
-1.25°	25	18	14	10	8	6	5	5	4	4	4
-2.5°	25	18	14	10	8	6	5	5	4	4	4
-3.75°	24	17	13	10	8	6	5	5	4	4	4
-5°	23	17	13	9	8	6	5	5	4	4	4
-6.25°	22	16	12	9	7	6	5	4	4	4	4
-7.5°	21	16	12	9	7	6	5	4	4	4	4
-8.75°	19	15	11	9	7	6	5	4	4	4	3
-10°	18	14	10	8	6	5	5	4	4	4	3
-11.25°	17	13	10	8	6	5	5	4	4	4	3
-12.5°	15	12	9	7	6	5	5	4	4	4	3
-13.75°	14	11	8	7	6	5	4	4	4	4	3
-15°	13	10	8	6	5	5	4	4	4	3	3
-16.25°	11	9	7	6	5	5	4	4	4	3	3
-17.5°	10	8	7	6	5	4	4	4	4	3	3
-18.75°	9	7	6	5	5	4	4	4	4	3	3
-20°	8	7	6	5	4	4	4	4	3	3	3
-21.25°	7	6	5	5	4	4	4	4	3	3	3



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	6	6	5	4	4	4	4	3	3	3	3
-23.75°	6	5	5	4	4	4	4	3	3	3	3
-25°	5	5	4	4	4	4	3	3	3	3	3
-26.25°	5	5	4	4	4	4	3	3	3	3	3
-27.5°	5	4	4	4	4	3	3	3	3	3	3
-28.75°	4	4	4	4	4	3	3	3	3	3	3
-30°	4	4	4	4	3	3	3	3	3	3	3
-31.25°	4	4	4	3	3	3	3	3	3	3	2
-32.5°	4	4	3	3	3	3	3	3	3	3	2
-33.75°	4	3	3	3	3	3	3	3	3	2	2
-35°	3	3	3	3	3	3	3	3	3	2	2
-36.25°	3	3	3	3	3	3	3	3	2	2	2
-37.5°	3	3	3	3	3	3	3	2	2	2	2
-38.75°	3	3	3	3	3	3	2	2	2	2	2
-40°	3	3	3	3	3	2	2	2	2	2	2
-41.25°	3	3	3	3	2	2	2	2	2	2	2
-42.5°	3	3	3	2	2	2	2	2	2	2	2
-43.75°	3	3	2	2	2	2	2	2	2	2	1
-45°	2	2	2	2	2	2	2	2	2	2	1
-46.25°	2	2	2	2	2	2	2	2	1	1	1
-47.5°	2	2	2	2	2	2	2	1	1	1	1
-48.75°	2	2	2	2	2	2	1	1	1	1	1
-50°	2	2	2	2	2	1	1	1	1	1	1
-51.25°	2	2	2	1	1	1	1	1	1	1	1
-52.5°	2	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	0
-61.25°	1	1	1	1	1	1	1	1	0	0	0
-62.5°	1	1	1	1	1	1	0	0	0	0	0
-63.75°	1	1	1	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	1	1	0	0	0	0	0	0	0	0	0
56.25°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	1	0	0	0	0	0	0	0
53.75°	1	1	1	1	1	0	0	0	0	0	0
52.5°	1	1	1	1	1	1	0	0	0	0	0
51.25°	1	1	1	1	1	1	1	0	0	0	0
50°	1	1	1	1	1	1	1	1	0	0	0
48.75°	1	1	1	1	1	1	1	1	1	0	0
47.5°	1	1	1	1	1	1	1	1	1	0	0
46.25°	1	1	1	1	1	1	1	1	1	1	0
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	2	1	1	1	1	1	1	1	1	1	1
40°	2	2	1	1	1	1	1	1	1	1	1
38.75°	2	2	2	1	1	1	1	1	1	1	1
37.5°	2	2	2	1	1	1	1	1	1	1	1
36.25°	2	2	2	2	1	1	1	1	1	1	1
35°	2	2	2	2	1	1	1	1	1	1	1



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	2	2	2	2	2	1	1	1	1	1	1
32.5°	2	2	2	2	2	1	1	1	1	1	1
31.25°	2	2	2	2	2	2	1	1	1	1	1
30°	2	2	2	2	2	2	1	1	1	1	1
28.75°	3	2	2	2	2	2	2	1	1	1	1
27.5°	3	2	2	2	2	2	2	1	1	1	1
26.25°	3	3	2	2	2	2	2	1	1	1	1
25°	3	3	2	2	2	2	2	2	1	1	1
23.75°	3	3	2	2	2	2	2	2	1	1	1
22.5°	3	3	3	2	2	2	2	2	1	1	1
21.25°	3	3	3	2	2	2	2	2	2	1	1
20°	3	3	3	2	2	2	2	2	2	1	1
18.75°	3	3	3	3	2	2	2	2	2	1	1
17.5°	3	3	3	3	2	2	2	2	2	1	1
16.25°	3	3	3	3	2	2	2	2	2	1	1
15°	3	3	3	3	2	2	2	2	2	2	1
13.75°	3	3	3	3	3	2	2	2	2	2	1
12.5°	3	3	3	3	3	2	2	2	2	2	1
11.25°	3	3	3	3	3	2	2	2	2	2	1
10°	3	3	3	3	3	2	2	2	2	2	1
8.75°	3	3	3	3	3	2	2	2	2	2	1
7.5°	3	3	3	3	3	2	2	2	2	2	1
6.25°	3	3	3	3	3	2	2	2	2	2	1
5°	3	3	3	3	3	2	2	2	2	2	1
3.75°	3	3	3	3	3	2	2	2	2	2	1
2.5°	3	3	3	3	3	2	2	2	2	2	1
1.25°	3	3	3	3	3	2	2	2	2	2	1
0°	3	3	3	3	3	3	2	2	2	2	2
-1.25°	3	3	3	3	3	2	2	2	2	2	1
-2.5°	3	3	3	3	3	2	2	2	2	2	1
-3.75°	3	3	3	3	3	2	2	2	2	2	1
-5°	3	3	3	3	3	2	2	2	2	2	1
-6.25°	3	3	3	3	3	2	2	2	2	2	1
-7.5°	3	3	3	3	3	2	2	2	2	2	1
-8.75°	3	3	3	3	3	2	2	2	2	2	1
-10°	3	3	3	3	3	2	2	2	2	2	1
-11.25°	3	3	3	3	3	2	2	2	2	2	1
-12.5°	3	3	3	3	3	2	2	2	2	2	1
-13.75°	3	3	3	3	3	2	2	2	2	2	1
-15°	3	3	3	3	2	2	2	2	2	2	1
-16.25°	3	3	3	3	2	2	2	2	2	1	1
-17.5°	3	3	3	3	2	2	2	2	2	1	1
-18.75°	3	3	3	3	2	2	2	2	2	1	1
-20°	3	3	3	2	2	2	2	2	2	1	1
-21.25°	3	3	3	2	2	2	2	2	2	1	1



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	3	3	3	2	2	2	2	2	1	1	1
-23.75°	3	3	2	2	2	2	2	2	1	1	1
-25°	3	3	2	2	2	2	2	2	1	1	1
-26.25°	3	3	2	2	2	2	2	1	1	1	1
-27.5°	3	2	2	2	2	2	2	1	1	1	1
-28.75°	3	2	2	2	2	2	2	1	1	1	1
-30°	2	2	2	2	2	2	1	1	1	1	1
-31.25°	2	2	2	2	2	2	1	1	1	1	1
-32.5°	2	2	2	2	2	1	1	1	1	1	1
-33.75°	2	2	2	2	2	1	1	1	1	1	1
-35°	2	2	2	2	1	1	1	1	1	1	1
-36.25°	2	2	2	2	1	1	1	1	1	1	1
-37.5°	2	2	2	1	1	1	1	1	1	1	1
-38.75°	2	2	2	1	1	1	1	1	1	1	1
-40°	2	2	1	1	1	1	1	1	1	1	1
-41.25°	2	1	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	0
-47.5°	1	1	1	1	1	1	1	1	1	0	0
-48.75°	1	1	1	1	1	1	1	1	1	0	0
-50°	1	1	1	1	1	1	1	1	0	0	0
-51.25°	1	1	1	1	1	1	1	0	0	0	0
-52.5°	1	1	1	1	1	1	0	0	0	0	0
-53.75°	1	1	1	1	1	0	0	0	0	0	0
-55°	1	1	1	1	0	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	1	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	1	0	0	0	0	0	0	0	0	0	0
41.25°	1	0	0	0	0	0	0	0	0	0	0
40°	1	1	0	0	0	0	0	0	0	0	0
38.75°	1	1	0	0	0	0	0	0	0	0	0
37.5°	1	1	0	0	0	0	0	0	0	0	0
36.25°	1	1	1	0	0	0	0	0	0	0	0
35°	1	1	1	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	0	0	0	0	0	0	0	0
32.5°	1	1	1	1	0	0	0	0	0	0	0
31.25°	1	1	1	1	0	0	0	0	0	0	0
30°	1	1	1	1	0	0	0	0	0	0	0
28.75°	1	1	1	1	1	0	0	0	0	0	0
27.5°	1	1	1	1	1	0	0	0	0	0	0
26.25°	1	1	1	1	1	0	0	0	0	0	0
25°	1	1	1	1	1	0	0	0	0	0	0
23.75°	1	1	1	1	1	0	0	0	0	0	0
22.5°	1	1	1	1	1	1	0	0	0	0	0
21.25°	1	1	1	1	1	1	0	0	0	0	0
20°	1	1	1	1	1	1	0	0	0	0	0
18.75°	1	1	1	1	1	1	0	0	0	0	0
17.5°	1	1	1	1	1	1	0	0	0	0	0
16.25°	1	1	1	1	1	1	0	0	0	0	0
15°	1	1	1	1	1	1	0	0	0	0	0
13.75°	1	1	1	1	1	1	0	0	0	0	0
12.5°	1	1	1	1	1	1	1	0	0	0	0
11.25°	1	1	1	1	1	1	1	0	0	0	0
10°	1	1	1	1	1	1	1	0	0	0	0
8.75°	1	1	1	1	1	1	1	0	0	0	0
7.5°	1	1	1	1	1	1	1	0	0	0	0
6.25°	1	1	1	1	1	1	1	0	0	0	0
5°	1	1	1	1	1	1	1	0	0	0	0
3.75°	1	1	1	1	1	1	1	0	0	0	0
2.5°	1	1	1	1	1	1	1	0	0	0	0
1.25°	1	1	1	1	1	1	1	0	0	0	0
0°	1	1	1	1	1	1	1	0	0	0	0
-1.25°	1	1	1	1	1	1	1	0	0	0	0
-2.5°	1	1	1	1	1	1	1	0	0	0	0
-3.75°	1	1	1	1	1	1	1	0	0	0	0
-5°	1	1	1	1	1	1	1	0	0	0	0
-6.25°	1	1	1	1	1	1	1	0	0	0	0
-7.5°	1	1	1	1	1	1	1	0	0	0	0
-8.75°	1	1	1	1	1	1	1	0	0	0	0
-10°	1	1	1	1	1	1	1	0	0	0	0
-11.25°	1	1	1	1	1	1	1	0	0	0	0
-12.5°	1	1	1	1	1	1	1	0	0	0	0
-13.75°	1	1	1	1	1	1	0	0	0	0	0
-15°	1	1	1	1	1	1	0	0	0	0	0
-16.25°	1	1	1	1	1	1	0	0	0	0	0
-17.5°	1	1	1	1	1	1	0	0	0	0	0
-18.75°	1	1	1	1	1	1	0	0	0	0	0
-20°	1	1	1	1	1	1	0	0	0	0	0
-21.25°	1	1	1	1	1	1	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	1	1	1	1	1	1	0	0	0	0	0
-23.75°	1	1	1	1	1	0	0	0	0	0	0
-25°	1	1	1	1	1	0	0	0	0	0	0
-26.25°	1	1	1	1	1	0	0	0	0	0	0
-27.5°	1	1	1	1	1	0	0	0	0	0	0
-28.75°	1	1	1	1	1	0	0	0	0	0	0
-30°	1	1	1	1	0	0	0	0	0	0	0
-31.25°	1	1	1	1	0	0	0	0	0	0	0
-32.5°	1	1	1	1	0	0	0	0	0	0	0
-33.75°	1	1	1	0	0	0	0	0	0	0	0
-35°	1	1	1	0	0	0	0	0	0	0	0
-36.25°	1	1	1	0	0	0	0	0	0	0	0
-37.5°	1	1	0	0	0	0	0	0	0	0	0
-38.75°	1	1	0	0	0	0	0	0	0	0	0
-40°	1	1	0	0	0	0	0	0	0	0	0
-41.25°	1	0	0	0	0	0	0	0	0	0	0
-42.5°	1	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: P220540 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED2797-F-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)