Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1559304

Luminaire Tested: 24CGTX-55-B2750-W2D2-2700K

Issue Date: 9/2/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1559304
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/2/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-55-B2750-W2D2-2700K
Description:	2X4 5500 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 2700K CCT WITH FROSTED SMOOTH L
Light Source:	2700K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	5556.6 lumens
Efficiency:	N/A
Efficacy:	106.7 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.26 / 1.38
Luminous Opening:	Rectangular (W 1.88' x L: 3.83' x H: 0')
CIE Type:	Direct
Input Watts (W):	52.1
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559304
CATALOG NUMBER: 24CGTX-55-B2750-W2D2-2700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559304
CATALOG NUMBER: 24CGTX-55-B2750-W2D2-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	94	97	94	91	93	90	88	89	87	85	83
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69
3	90	79	70	64	87	77	69	63	74	68	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	45	39	50	44	39	37
7	64	51	42	36	63	50	41	35	48	41	35	47	40	35	45	39	35	33
8	60	46	38	32	58	45	37	32	44	37	31	43	36	31	42	36	31	29
9	56	42	34	28	54	42	34	28	41	33	28	40	33	28	38	32	28	26
10	52	39	31	26	51	39	31	26	38	30	26	37	30	25	36	30	25	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2838	2838	2838
5°	2849	2837	2841
10°	2845	2835	2839
15°	2839	2828	2834
20°	2827	2819	2822
25°	2817	2804	2806
30°	2798	2786	2788
35°	2777	2766	2766
40°	2753	2739	2741
45°	2722	2713	2711
50°	2691	2672	2665
55°	2650	2629	2619
60°	2603	2573	2546
65°	2534	2502	2473
70°	2448	2417	2364
75°	2326	2297	2257
80°	2199	2147	2087
85°	1907	1890	1821

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2722 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559304
CATALOG NUMBER: 24CGTX-55-B2750-W2D2-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.5	3.2
10°-20°	515.3	9.3
20°-30°	782.9	14.1
30°-40°	946.7	17.0
40°-50°	988.1	17.8
50°-60°	901.2	16.2
60°-70°	699.2	12.6
70°-80°	419.8	7.6
80°-90°	123.9	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1477.7	26.6
0°-40°	2424.4	43.6
0°-60°	4313.7	77.6
0°-90°	5556.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5556.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1895	1895	1895	1895	1895	
5°	1895	1889	1887	1885	1890	180
15°	1831	1826	1824	1823	1828	517
25°	1705	1700	1697	1696	1698	785
35°	1519	1514	1513	1510	1513	950
45°	1285	1283	1281	1277	1280	993
55°	1015	1014	1007	1004	1003	907
65°	715	714	706	702	698	708
75°	402	403	397	393	390	426
85°	111	111	110	106	106	126
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559304
CATALOG NUMBER: 24CGTX-55-B2750-W2D2-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*1895*	1895	1895	1895	1895
2.5°	*1900*	*1895*	*1892*	*1891*	*1895*
5°	*1895*	1889	1887	1885	1890
7.5°	*1885*	1879	1877	1876	1880
10°	*1871*	1866	1864	1863	1867
12.5°	*1852*	1848	1847	1846	1849
15°	*1831*	1826	1824	1823	1828
17.5°	*1805*	1800	1798	1798	1801
20°	*1774*	1770	1769	1768	1771
22.5°	*1743*	1738	1736	1735	1738
25°	*1705*	1700	1697	1696	1698
27.5°	*1661*	1658	1656	1655	1657
30°	*1618*	1615	1611	1610	1612
32.5°	*1569*	1566	1563	1560	1564
35°	*1519*	1514	1513	1510	1513
37.5°	*1465*	1462	1457	1456	1461
40°	*1408*	1405	1401	1399	1402
42.5°	*1351*	1347	1342	1340	1339
45°	*1285*	1283	1281	1277	1280
47.5°	*1225*	1220	1214	1216	1215
50°	*1155*	1151	1147	1146	1144
52.5°	*1088*	1085	1082	1077	1074
55°	*1015*	1014	1007	1004	1003
57.5°	*942*	940	937	930	926
60°	*869*	864	859	855	850
62.5°	*792*	789	783	779	776
65°	*715*	714	706	702	698
67.5°	*639*	638	627	623	621
70°	*559*	559	552	544	540
72.5°	*479*	479	475	469	467
75°	*402*	403	397	393	390
77.5°	*326*	325	321	316	315
80°	*255*	253	249	244	242
82.5°	*182*	182	180	173	170
85°	*111*	111	110	106	106
87.5°	*44*	44	44	47	43
90°	*0*	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1559304
CATALOG NUMBER: 24CGTX-55-B2750-W2D2-2700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.58	17.24	15.94	17.55	17.86	15.49	17.15	15.86	17.47	17.78
	3H	17.50	19.00	17.87	19.33	19.69	17.37	18.87	17.74	19.19	19.55
	4H	18.24	19.65	18.64	20.00	20.38	18.09	19.51	18.49	19.86	20.23
	6H	18.81	20.13	19.22	20.49	20.88	18.65	19.96	19.06	20.33	20.72
	8H	19.01	20.27	19.43	20.66	21.05	18.83	20.09	19.26	20.48	20.88
	12H	19.15	20.35	19.57	20.73	21.16	18.96	20.16	19.39	20.54	20.97
4H	2H	16.23	17.64	16.63	17.99	18.37	16.16	17.58	16.56	17.93	18.30
	3H	18.38	19.57	18.78	19.96	20.36	18.26	19.45	18.67	19.85	20.25
	4H	19.25	20.33	19.69	20.75	21.18	19.13	20.21	19.56	20.62	21.05
	6H	19.97	20.91	20.42	21.35	21.81	19.81	20.76	20.27	21.20	21.65
	8H	20.22	21.11	20.68	21.55	22.01	20.05	20.94	20.51	21.38	21.84
	12H	20.41	21.21	20.89	21.68	22.15	20.22	21.02	20.70	21.50	21.96
8H	4H	19.59	20.48	20.05	20.92	21.39	19.48	20.37	19.94	20.81	21.27
	6H	20.44	21.18	20.94	21.67	22.14	20.30	21.04	20.80	21.53	22.00
	8H	20.78	21.45	21.29	21.95	22.44	20.62	21.28	21.13	21.79	22.27
	12H	21.05	21.64	21.56	22.13	22.69	20.87	21.46	21.38	21.95	22.51
12H	4H	19.64	20.43	20.11	20.91	21.38	19.53	20.33	20.01	20.80	21.27
	6H	20.51	21.18	21.02	21.68	22.17	20.38	21.04	20.89	21.55	22.03
	8H	20.91	21.50	21.42	21.99	22.55	20.76	21.35	21.26	21.84	22.39

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2505-441-28-R2

Test Date: 07/10/2025

Luminaire Tested: 24CGTX-45-B2750-W2D-2700K

Data in this report applies to families of products including 24CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2505-441-28-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-45-B2750-W2D-2700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2504-441-28-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 4500 LUMEN CGTX. Using WaveLinx PRO F1 sensor.

Spectral Parameters

CCT (K):	2694	CRI (Ra):	95.4		
CIE u':	0.2630	R1:	96.8	R9:	80.8
CIE v':	0.5264	R2:	98.3	R10:	98.3
Duv:	-0.0008	R3:	97.9	R11:	89.1
CIE x:	0.4590	R4:	94.6	R12:	93.4
CIE y:	0.4084	R5:	96.4	R13:	96.9
CIE z:	0.1326	R6:	92.3	R14:	97.1
Peak Wavelength (nm):	630	R7:	94.8	R15:	98.2
Dominant Wavelength (nm):	584	R8:	92.1		
Purity:	60.36523				
Rf:	93.8				
Rg:	102				




Test Conditions

Stabilization Time:	24M
Operation Time:	1H 24M
Sphere Temperature (°C):	24.0


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2505-441-28-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2694K
CIE x = 0.4590
CIE y = 0.4084
Duv = -0.0008

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2505-441-28-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	228	NR	750	5	NR	880	0	NR
365	0	NR	495	86	NR	625	239	NR	755	4	NR	885	0	NR
370	0	NR	500	100	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	111	NR	635	614	NR	765	3	NR	895	0	NR
380	0	NR	510	118	NR	640	147	NR	770	3	NR	900	0	NR
385	0	NR	515	122	NR	645	148	NR	775	2	NR	905	0	NR
390	0	NR	520	126	NR	650	127	NR	780	2	NR	910	0	NR
395	0	NR	525	128	NR	655	105	NR	785	2	NR	915	0	NR
400	1	NR	530	130	NR	660	88	NR	790	1	NR	920	0	NR
405	1	NR	535	134	NR	665	73	NR	795	1	NR	925	0	NR
410	2	NR	540	139	NR	670	70	NR	800	1	NR	930	0	NR
415	3	NR	545	143	NR	675	55	NR	805	1	NR	935	0	NR
420	6	NR	550	148	NR	680	47	NR	810	1	NR	940	0	NR
425	10	NR	555	154	NR	685	41	NR	815	1	NR	945	0	NR
430	18	NR	560	159	NR	690	35	NR	820	1	NR	950	0	NR
435	28	NR	565	164	NR	695	30	NR	825	1	NR	955	0	NR
440	44	NR	570	169	NR	700	25	NR	830	0	NR	960	0	NR
445	75	NR	575	175	NR	705	22	NR	835	0	NR	965	0	NR
450	107	NR	580	179	NR	710	18	NR	840	0	NR	970	0	NR
455	82	NR	585	186	NR	715	16	NR	845	0	NR	975	0	NR
460	58	NR	590	190	NR	720	13	NR	850	0	NR	980	0	NR
465	53	NR	595	192	NR	725	11	NR	855	0	NR	985	0	NR
470	45	NR	600	198	NR	730	10	NR	860	0	NR	990	0	NR
475	41	NR	605	203	NR	735	8	NR	865	0	NR	995	0	NR
480	46	NR	610	237	NR	740	7	NR	870	0	NR	1000	0	NR
485	57	NR	615	264	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-28-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.34**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	228	NR	750	5	NR	880	0	NR
365	0	NR	495	86	NR	625	239	NR	755	4	NR	885	0	NR
370	0	NR	500	100	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	111	NR	635	614	NR	765	3	NR	895	0	NR
380	0	NR	510	118	NR	640	147	NR	770	3	NR	900	0	NR
385	0	NR	515	122	NR	645	148	NR	775	2	NR	905	0	NR
390	0	NR	520	126	NR	650	127	NR	780	2	NR	910	0	NR
395	0	NR	525	128	NR	655	105	NR	785	2	NR	915	0	NR
400	1	NR	530	130	NR	660	88	NR	790	1	NR	920	0	NR
405	1	NR	535	134	NR	665	73	NR	795	1	NR	925	0	NR
410	2	NR	540	139	NR	670	70	NR	800	1	NR	930	0	NR
415	3	NR	545	143	NR	675	55	NR	805	1	NR	935	0	NR
420	6	NR	550	148	NR	680	47	NR	810	1	NR	940	0	NR
425	10	NR	555	154	NR	685	41	NR	815	1	NR	945	0	NR
430	18	NR	560	159	NR	690	35	NR	820	1	NR	950	0	NR
435	28	NR	565	164	NR	695	30	NR	825	1	NR	955	0	NR
440	44	NR	570	169	NR	700	25	NR	830	0	NR	960	0	NR
445	75	NR	575	175	NR	705	22	NR	835	0	NR	965	0	NR
450	107	NR	580	179	NR	710	18	NR	840	0	NR	970	0	NR
455	82	NR	585	186	NR	715	16	NR	845	0	NR	975	0	NR
460	58	NR	590	190	NR	720	13	NR	850	0	NR	980	0	NR
465	53	NR	595	192	NR	725	11	NR	855	0	NR	985	0	NR
470	45	NR	600	198	NR	730	10	NR	860	0	NR	990	0	NR
475	41	NR	605	203	NR	735	8	NR	865	0	NR	995	0	NR
480	46	NR	610	237	NR	740	7	NR	870	0	NR	1000	0	NR
485	57	NR	615	264	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-28-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.58**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	228	NR	750	5	NR	880	0	NR
365	0	NR	495	86	NR	625	239	NR	755	4	NR	885	0	NR
370	0	NR	500	100	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	111	NR	635	614	NR	765	3	NR	895	0	NR
380	0	NR	510	118	NR	640	147	NR	770	3	NR	900	0	NR
385	0	NR	515	122	NR	645	148	NR	775	2	NR	905	0	NR
390	0	NR	520	126	NR	650	127	NR	780	2	NR	910	0	NR
395	0	NR	525	128	NR	655	105	NR	785	2	NR	915	0	NR
400	1	NR	530	130	NR	660	88	NR	790	1	NR	920	0	NR
405	1	NR	535	134	NR	665	73	NR	795	1	NR	925	0	NR
410	2	NR	540	139	NR	670	70	NR	800	1	NR	930	0	NR
415	3	NR	545	143	NR	675	55	NR	805	1	NR	935	0	NR
420	6	NR	550	148	NR	680	47	NR	810	1	NR	940	0	NR
425	10	NR	555	154	NR	685	41	NR	815	1	NR	945	0	NR
430	18	NR	560	159	NR	690	35	NR	820	1	NR	950	0	NR
435	28	NR	565	164	NR	695	30	NR	825	1	NR	955	0	NR
440	44	NR	570	169	NR	700	25	NR	830	0	NR	960	0	NR
445	75	NR	575	175	NR	705	22	NR	835	0	NR	965	0	NR
450	107	NR	580	179	NR	710	18	NR	840	0	NR	970	0	NR
455	82	NR	585	186	NR	715	16	NR	845	0	NR	975	0	NR
460	58	NR	590	190	NR	720	13	NR	850	0	NR	980	0	NR
465	53	NR	595	192	NR	725	11	NR	855	0	NR	985	0	NR
470	45	NR	600	198	NR	730	10	NR	860	0	NR	990	0	NR
475	41	NR	605	203	NR	735	8	NR	865	0	NR	995	0	NR
480	46	NR	610	237	NR	740	7	NR	870	0	NR	1000	0	NR
485	57	NR	615	264	NR	745	6	NR	875	0	NR			


REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18


Summary


R_f = 93.8
R_g = 102
CIE R_a = 95.4
R_9 = 80.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 99	CES51 = 93	CES76 = 96
CES02 = 64	CES27 = 95	CES52 = 93	CES77 = 79
CES03 = 32	CES28 = 100	CES53 = 93	CES78 = 92
CES04 = 70	CES29 = 97	CES54 = 96	CES79 = 84
CES05 = 52	CES30 = 100	CES55 = 96	CES80 = 89
CES06 = 51	CES31 = 98	CES56 = 95	CES81 = 65
CES07 = 45	CES32 = 90	CES57 = 95	CES82 = 95
CES08 = 43	CES33 = 96	CES58 = 94	CES83 = 91
CES09 = 29	CES34 = 99	CES59 = 97	CES84 = 98
CES10 = 77	CES35 = 99	CES60 = 96	CES85 = 80
CES11 = 59	CES36 = 90	CES61 = 96	CES86 = 78
CES12 = 66	CES37 = 96	CES62 = 92	CES87 = 95
CES13 = 45	CES38 = 96	CES63 = 97	CES88 = 99
CES14 = 74	CES39 = 97	CES64 = 95	CES89 = 85
CES15 = 72	CES40 = 95	CES65 = 98	CES90 = 98
CES16 = 49	CES41 = 94	CES66 = 96	CES91 = 86
CES17 = 50	CES42 = 93	CES67 = 96	CES92 = 83
CES18 = 57	CES43 = 95	CES68 = 97	CES93 = 90
CES19 = 72	CES44 = 99	CES69 = 97	CES94 = 77
CES20 = 68	CES45 = 95	CES70 = 97	CES95 = 90
CES21 = 87	CES46 = 96	CES71 = 96	CES96 = 96
CES22 = 79	CES47 = 82	CES72 = 98	CES97 = 93
CES23 = 92	CES48 = 99	CES73 = 94	CES98 = 97
CES24 = 91	CES49 = 94	CES74 = 86	CES99 = 96
CES25 = 72	CES50 = 94	CES75 = 96	





REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18

Measure Comparisons





(END OF REPORT)