

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information


Test Method: LM-79-08
Report Number: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29472)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, RECESSED LENS, SPOT
OPTIC, BLACK HOUSING.
Light Source: (1) 3500K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp:	N/A	NEMA Type:	3H x 3V
Luminaire Lumens:	658.1 lumens	Max Intensity:	5650.1 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	67.2 lumens/watt		
Luminous Opening:	Circular (Dia: 0.25' x H: 0')		
Beam Angle (50%):	15.7°H x 15.7°V	Field Angle (10%):	35°H x 35°V
Beam Lumens:	234.6 lumens	Field Lumens:	504.2 lumens
Beam Efficiency:	35.7%	Field Efficiency:	76.6%
Input Watts (W):	9.8		
Input Voltage (V):	120		
Input Current (A _{in}):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

Iso-Candela Plot






REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	
40		0.0	0.0	0.1	0.1	0.1	0.2	0.3	0.3	0.2	0.1	0.1	0.1	0.0	0.0		
30	0.0	0.0	0.0	0.1	0.1	0.3	2.0	5.8	5.8	2.0	0.3	0.1	0.1	0.0	0.0	0.0	
20		0.0	0.0	0.1	0.2	1.9	11.9	22.5	22.5	11.9	1.9	0.2	0.1	0.0	0.0		
10	0.0	0.0	0.0	0.1	0.3	5.3	21.9	89.9	89.9	21.9	5.3	0.3	0.1	0.0	0.0	0.0	
0		0.0	0.0	0.1	0.3	5.3	21.9	89.9	89.9	21.9	5.3	0.3	0.1	0.0	0.0		
-10	0.0	0.0	0.0	0.1	0.2	1.9	11.9	22.5	22.5	11.9	1.9	0.2	0.1	0.0	0.0	0.0	
-20		0.0	0.0	0.1	0.1	0.3	2.0	5.8	5.8	2.0	0.3	0.1	0.1	0.0	0.0		
-30	0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.3	0.3	0.2	0.1	0.1	0.1	0.0	0.0	0.0	
-40		0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0		
-50	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0			
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	


REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

Luminous Intensity Polar Plot



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

Luminous Intensity Plot



Beam:
 H Angle: 15.7°
 V Angle: 15.7°
 Lumens: 234.6
 Efficiency: 35.7%

Field:
 H Angle: 35°
 V Angle: 35°
 Lumens: 504.2
 Efficiency: 76.6%

Spill:
 Lumens: 154
 Efficiency: 23.4%

— Vertical Distribution through 0-Deg
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	1
36.25°	0	0	0	0	0	0	0	0	0	0	1
35°	0	0	0	0	0	0	0	0	0	0	1



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	0	0	0	0	0	0	1	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
31.25°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	0	1	1
28.75°	0	0	0	0	0	0	0	0	1	1	1
27.5°	0	0	0	0	0	0	0	0	1	1	1
26.25°	0	0	0	0	0	0	0	0	1	1	1
25°	0	0	0	0	0	0	0	0	1	1	1
23.75°	0	0	0	0	0	0	0	1	1	1	1
22.5°	0	0	0	0	0	0	0	1	1	1	1
21.25°	0	0	0	0	0	0	0	1	1	1	1
20°	0	0	0	0	0	0	0	1	1	1	1
18.75°	0	0	0	0	0	0	0	1	1	1	1
17.5°	0	0	0	0	0	0	0	1	1	1	1
16.25°	0	0	0	0	0	0	0	1	1	1	1
15°	0	0	0	0	0	0	0	1	1	1	1
13.75°	0	0	0	0	0	0	1	1	1	1	1
12.5°	0	0	0	0	0	0	1	1	1	1	1
11.25°	0	0	0	0	0	0	1	1	1	1	1
10°	0	0	0	0	0	0	1	1	1	1	1
8.75°	0	0	0	0	0	0	1	1	1	1	1
7.5°	0	0	0	0	0	0	1	1	1	1	1
6.25°	0	0	0	0	0	0	1	1	1	1	1
5°	0	0	0	0	0	0	1	1	1	1	1
3.75°	0	0	0	0	0	0	1	1	1	1	1
2.5°	0	0	0	0	0	0	1	1	1	1	1
1.25°	0	0	0	0	0	0	1	1	1	1	1
0°	0	0	0	0	0	0	1	1	1	1	2
-1.25°	0	0	0	0	0	0	1	1	1	1	1
-2.5°	0	0	0	0	0	0	1	1	1	1	1
-3.75°	0	0	0	0	0	0	1	1	1	1	1
-5°	0	0	0	0	0	0	1	1	1	1	1
-6.25°	0	0	0	0	0	0	1	1	1	1	1
-7.5°	0	0	0	0	0	0	1	1	1	1	1
-8.75°	0	0	0	0	0	0	1	1	1	1	1
-10°	0	0	0	0	0	0	1	1	1	1	1
-11.25°	0	0	0	0	0	0	1	1	1	1	1
-12.5°	0	0	0	0	0	0	1	1	1	1	1
-13.75°	0	0	0	0	0	0	1	1	1	1	1
-15°	0	0	0	0	0	0	0	1	1	1	1
-16.25°	0	0	0	0	0	0	0	1	1	1	1
-17.5°	0	0	0	0	0	0	0	1	1	1	1
-18.75°	0	0	0	0	0	0	0	1	1	1	1
-20°	0	0	0	0	0	0	0	1	1	1	1
-21.25°	0	0	0	0	0	0	0	1	1	1	1



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	0	0	0	0	0	1	1	1	1
-23.75°	0	0	0	0	0	0	0	1	1	1	1
-25°	0	0	0	0	0	0	0	0	1	1	1
-26.25°	0	0	0	0	0	0	0	0	1	1	1
-27.5°	0	0	0	0	0	0	0	0	1	1	1
-28.75°	0	0	0	0	0	0	0	0	1	1	1
-30°	0	0	0	0	0	0	0	0	0	1	1
-31.25°	0	0	0	0	0	0	0	0	0	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-33.75°	0	0	0	0	0	0	0	0	0	1	1
-35°	0	0	0	0	0	0	0	0	0	0	1
-36.25°	0	0	0	0	0	0	0	0	0	0	1
-37.5°	0	0	0	0	0	0	0	0	0	0	1
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	1
55°	0	0	0	0	0	0	0	0	1	1	1
53.75°	0	0	0	0	0	0	0	1	1	1	1
52.5°	0	0	0	0	0	0	1	1	1	1	1
51.25°	0	0	0	0	0	1	1	1	1	1	1
50°	0	0	0	0	1	1	1	1	1	1	1
48.75°	0	0	0	1	1	1	1	1	1	1	1
47.5°	0	0	1	1	1	1	1	1	1	1	1
46.25°	0	0	1	1	1	1	1	1	1	2	2
45°	0	0	1	1	1	1	1	1	2	2	2
43.75°	0	0	1	1	1	1	1	1	2	2	2
42.5°	0	1	1	1	1	1	1	2	2	2	2
41.25°	0	1	1	1	1	1	2	2	2	2	2
40°	1	1	1	1	1	1	2	2	2	2	2
38.75°	1	1	1	1	1	2	2	2	2	2	2
37.5°	1	1	1	1	1	2	2	2	2	2	2
36.25°	1	1	1	1	2	2	2	2	2	2	2
35°	1	1	1	1	2	2	2	2	2	2	2



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	1	1	2	2	2	2	2	2	3
32.5°	1	1	1	1	2	2	2	2	2	2	3
31.25°	1	1	1	2	2	2	2	2	2	3	3
30°	1	1	1	2	2	2	2	2	2	3	3
28.75°	1	1	1	2	2	2	2	2	3	3	3
27.5°	1	1	2	2	2	2	2	2	3	3	3
26.25°	1	1	2	2	2	2	2	3	3	3	3
25°	1	1	2	2	2	2	2	3	3	3	3
23.75°	1	1	2	2	2	2	2	3	3	3	3
22.5°	1	2	2	2	2	2	3	3	3	3	3
21.25°	1	2	2	2	2	2	3	3	3	3	3
20°	1	2	2	2	2	2	3	3	3	3	3
18.75°	1	2	2	2	2	2	3	3	3	3	3
17.5°	1	2	2	2	2	3	3	3	3	3	3
16.25°	2	2	2	2	2	3	3	3	3	3	3
15°	2	2	2	2	2	3	3	3	3	3	3
13.75°	2	2	2	2	2	3	3	3	3	3	3
12.5°	2	2	2	2	2	3	3	3	3	3	3
11.25°	2	2	2	2	2	3	3	3	3	3	3
10°	2	2	2	2	3	3	3	3	3	3	3
8.75°	2	2	2	2	3	3	3	3	3	3	3
7.5°	2	2	2	2	3	3	3	3	3	3	3
6.25°	2	2	2	2	3	3	3	3	3	3	3
5°	2	2	2	2	3	3	3	3	3	3	3
3.75°	2	2	2	2	3	3	3	3	3	3	3
2.5°	2	2	2	2	3	3	3	3	3	3	3
1.25°	2	2	2	2	3	3	3	3	3	3	3
0°	2	2	2	2	3	3	3	3	3	3	4
-1.25°	2	2	2	2	3	3	3	3	3	3	3
-2.5°	2	2	2	2	3	3	3	3	3	3	3
-3.75°	2	2	2	2	3	3	3	3	3	3	3
-5°	2	2	2	2	3	3	3	3	3	3	3
-6.25°	2	2	2	2	3	3	3	3	3	3	3
-7.5°	2	2	2	2	3	3	3	3	3	3	3
-8.75°	2	2	2	2	3	3	3	3	3	3	3
-10°	2	2	2	2	3	3	3	3	3	3	3
-11.25°	2	2	2	2	2	3	3	3	3	3	3
-12.5°	2	2	2	2	2	3	3	3	3	3	3
-13.75°	2	2	2	2	2	3	3	3	3	3	3
-15°	2	2	2	2	2	3	3	3	3	3	3
-16.25°	2	2	2	2	2	3	3	3	3	3	3
-17.5°	1	2	2	2	2	3	3	3	3	3	3
-18.75°	1	2	2	2	2	2	3	3	3	3	3
-20°	1	2	2	2	2	2	3	3	3	3	3
-21.25°	1	2	2	2	2	2	3	3	3	3	3



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	1	2	2	2	2	2	3	3	3	3	3
-23.75°	1	1	2	2	2	2	2	3	3	3	3
-25°	1	1	2	2	2	2	2	3	3	3	3
-26.25°	1	1	2	2	2	2	2	3	3	3	3
-27.5°	1	1	2	2	2	2	2	2	3	3	3
-28.75°	1	1	1	2	2	2	2	2	3	3	3
-30°	1	1	1	2	2	2	2	2	2	3	3
-31.25°	1	1	1	2	2	2	2	2	2	3	3
-32.5°	1	1	1	1	2	2	2	2	2	2	3
-33.75°	1	1	1	1	2	2	2	2	2	2	3
-35°	1	1	1	1	1	2	2	2	2	2	2
-36.25°	1	1	1	1	1	2	2	2	2	2	2
-37.5°	1	1	1	1	1	1	2	2	2	2	2
-38.75°	1	1	1	1	1	1	2	2	2	2	2
-40°	1	1	1	1	1	1	1	2	2	2	2
-41.25°	0	1	1	1	1	1	1	2	2	2	2
-42.5°	0	1	1	1	1	1	1	1	2	2	2
-43.75°	0	0	1	1	1	1	1	1	1	2	2
-45°	0	0	1	1	1	1	1	1	1	2	2
-46.25°	0	0	0	1	1	1	1	1	1	1	2
-47.5°	0	0	0	1	1	1	1	1	1	1	1
-48.75°	0	0	0	0	1	1	1	1	1	1	1
-50°	0	0	0	0	0	1	1	1	1	1	1
-51.25°	0	0	0	0	0	0	1	1	1	1	1
-52.5°	0	0	0	0	0	0	0	1	1	1	1
-53.75°	0	0	0	0	0	0	0	0	1	1	1
-55°	0	0	0	0	0	0	0	0	0	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	1	1
62.5°	0	0	0	0	0	0	0	1	1	1	1
61.25°	0	0	0	0	0	1	1	1	1	1	1
60°	0	0	0	1	1	1	1	1	1	1	1
58.75°	0	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	2
55°	1	1	1	1	1	1	1	1	2	2	2
53.75°	1	1	1	1	1	1	2	2	2	2	2
52.5°	1	1	1	1	1	2	2	2	2	2	2
51.25°	1	1	1	2	2	2	2	2	2	2	2
50°	1	1	2	2	2	2	2	2	2	2	2
48.75°	1	2	2	2	2	2	2	2	2	2	3
47.5°	2	2	2	2	2	2	2	2	2	3	3
46.25°	2	2	2	2	2	2	2	3	3	3	3
45°	2	2	2	2	2	2	3	3	3	3	3
43.75°	2	2	2	2	2	3	3	3	3	3	3
42.5°	2	2	2	2	3	3	3	3	3	3	3
41.25°	2	2	2	3	3	3	3	3	3	3	3
40°	2	2	3	3	3	3	3	3	3	3	3
38.75°	2	2	3	3	3	3	3	3	3	3	3
37.5°	2	3	3	3	3	3	3	3	3	3	3
36.25°	3	3	3	3	3	3	3	3	3	3	4
35°	3	3	3	3	3	3	3	3	3	4	4



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	3	3	3	3	3	3	3	3	4	4	4
32.5°	3	3	3	3	3	3	3	4	4	4	4
31.25°	3	3	3	3	3	3	3	4	4	4	4
30°	3	3	3	3	3	3	4	4	4	4	4
28.75°	3	3	3	3	3	4	4	4	4	4	4
27.5°	3	3	3	3	3	4	4	4	4	4	5
26.25°	3	3	3	3	4	4	4	4	4	4	5
25°	3	3	3	3	4	4	4	4	4	5	5
23.75°	3	3	3	4	4	4	4	4	4	5	5
22.5°	3	3	3	4	4	4	4	4	5	5	5
21.25°	3	3	4	4	4	4	4	5	5	5	6
20°	3	3	4	4	4	4	4	5	5	5	6
18.75°	3	3	4	4	4	4	4	5	5	6	6
17.5°	3	4	4	4	4	4	5	5	5	6	6
16.25°	3	4	4	4	4	4	5	5	6	6	6
15°	3	4	4	4	4	4	5	5	6	6	6
13.75°	3	4	4	4	4	5	5	5	6	6	7
12.5°	4	4	4	4	4	5	5	6	6	6	7
11.25°	4	4	4	4	4	5	5	6	6	6	7
10°	4	4	4	4	4	5	5	6	6	7	7
8.75°	4	4	4	4	5	5	5	6	6	7	7
7.5°	4	4	4	4	5	5	5	6	6	7	7
6.25°	4	4	4	4	5	5	6	6	6	7	8
5°	4	4	4	4	5	5	6	6	6	7	8
3.75°	4	4	4	4	5	5	6	6	6	7	8
2.5°	4	4	4	4	5	5	6	6	6	7	8
1.25°	4	4	4	4	5	5	6	6	6	7	8
0°	4	4	4	4	5	5	6	6	7	7	8
-1.25°	4	4	4	4	5	5	6	6	6	7	8
-2.5°	4	4	4	4	5	5	6	6	6	7	8
-3.75°	4	4	4	4	5	5	6	6	6	7	8
-5°	4	4	4	4	5	5	6	6	6	7	8
-6.25°	4	4	4	4	5	5	6	6	6	7	8
-7.5°	4	4	4	4	5	5	5	6	6	7	7
-8.75°	4	4	4	4	5	5	5	6	6	7	7
-10°	4	4	4	4	4	5	5	6	6	7	7
-11.25°	4	4	4	4	4	5	5	6	6	6	7
-12.5°	4	4	4	4	4	5	5	6	6	6	7
-13.75°	3	4	4	4	4	5	5	5	6	6	7
-15°	3	4	4	4	4	4	5	5	6	6	6
-16.25°	3	4	4	4	4	4	5	5	6	6	6
-17.5°	3	4	4	4	4	4	5	5	5	6	6
-18.75°	3	3	4	4	4	4	4	5	5	6	6
-20°	3	3	4	4	4	4	4	5	5	5	6
-21.25°	3	3	4	4	4	4	4	5	5	5	6



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	3	3	3	4	4	4	4	4	5	5	5
-23.75°	3	3	3	4	4	4	4	4	4	5	5
-25°	3	3	3	3	4	4	4	4	4	5	5
-26.25°	3	3	3	3	4	4	4	4	4	4	5
-27.5°	3	3	3	3	3	4	4	4	4	4	5
-28.75°	3	3	3	3	3	4	4	4	4	4	4
-30°	3	3	3	3	3	3	4	4	4	4	4
-31.25°	3	3	3	3	3	3	3	4	4	4	4
-32.5°	3	3	3	3	3	3	3	4	4	4	4
-33.75°	3	3	3	3	3	3	3	3	4	4	4
-35°	3	3	3	3	3	3	3	3	3	4	4
-36.25°	3	3	3	3	3	3	3	3	3	3	4
-37.5°	2	3	3	3	3	3	3	3	3	3	3
-38.75°	2	2	3	3	3	3	3	3	3	3	3
-40°	2	2	3	3	3	3	3	3	3	3	3
-41.25°	2	2	2	3	3	3	3	3	3	3	3
-42.5°	2	2	2	2	3	3	3	3	3	3	3
-43.75°	2	2	2	2	2	3	3	3	3	3	3
-45°	2	2	2	2	2	2	3	3	3	3	3
-46.25°	2	2	2	2	2	2	2	3	3	3	3
-47.5°	2	2	2	2	2	2	2	2	2	3	3
-48.75°	1	2	2	2	2	2	2	2	2	2	3
-50°	1	1	2	2	2	2	2	2	2	2	2
-51.25°	1	1	1	2	2	2	2	2	2	2	2
-52.5°	1	1	1	1	1	2	2	2	2	2	2
-53.75°	1	1	1	1	1	1	2	2	2	2	2
-55°	1	1	1	1	1	1	1	1	2	2	2
-56.25°	1	1	1	1	1	1	1	1	1	1	2
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	0	1	1	1	1	1	1	1	1	1	1
-60°	0	0	0	1	1	1	1	1	1	1	1
-61.25°	0	0	0	0	0	1	1	1	1	1	1
-62.5°	0	0	0	0	0	0	0	1	1	1	1
-63.75°	0	0	0	0	0	0	0	0	0	1	1
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	1	1
66.25°	0	0	0	0	0	1	1	1	1	1	1
65°	0	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	2
60°	1	1	1	1	1	1	2	2	2	2	2
58.75°	1	1	1	2	2	2	2	2	2	2	2
57.5°	1	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	3
53.75°	2	2	2	2	2	2	2	3	3	3	3
52.5°	2	2	2	2	2	3	3	3	3	3	3
51.25°	2	2	2	3	3	3	3	3	3	3	3
50°	2	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	3
47.5°	3	3	3	3	3	3	3	3	3	3	3
46.25°	3	3	3	3	3	3	3	3	3	3	3
45°	3	3	3	3	3	3	3	3	3	4	4
43.75°	3	3	3	3	3	3	3	4	4	4	4
42.5°	3	3	3	3	3	4	4	4	4	4	4
41.25°	3	3	3	3	4	4	4	4	4	4	4
40°	3	3	4	4	4	4	4	4	4	4	4
38.75°	3	4	4	4	4	4	4	4	4	4	5
37.5°	4	4	4	4	4	4	4	4	5	5	5
36.25°	4	4	4	4	4	4	5	5	5	5	5
35°	4	4	4	4	4	5	5	5	5	6	6



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	4	4	4	4	5	5	5	5	6	6	6
32.5°	4	4	4	5	5	5	6	6	6	6	6
31.25°	4	4	5	5	5	6	6	6	6	7	7
30°	4	5	5	5	6	6	6	6	7	7	7
28.75°	5	5	5	6	6	6	6	7	7	8	8
27.5°	5	5	6	6	6	6	7	7	8	8	9
26.25°	5	5	6	6	6	7	7	8	9	10	12
25°	5	6	6	6	7	7	8	9	10	12	15
23.75°	6	6	6	7	7	8	8	10	12	15	17
22.5°	6	6	6	7	7	8	9	12	15	17	21
21.25°	6	6	7	7	8	9	11	14	17	20	24
20°	6	7	7	8	9	10	13	16	20	23	27
18.75°	6	7	7	8	9	12	15	19	22	26	31
17.5°	7	7	8	9	11	14	17	21	25	30	43
16.25°	7	7	8	10	13	16	20	24	28	38	64
15°	7	8	9	11	14	18	22	26	32	51	92
13.75°	7	8	9	12	16	20	24	29	41	74	128
12.5°	7	8	10	14	17	21	26	33	54	101	163
11.25°	8	9	11	15	19	23	28	40	73	130	197
10°	8	9	13	16	20	25	30	47	93	158	231
8.75°	8	10	13	17	21	26	35	62	116	185	262
7.5°	8	11	14	18	23	28	40	74	136	209	290
6.25°	9	11	15	19	23	29	44	86	154	231	314
5°	9	12	15	20	24	30	49	100	170	250	333
3.75°	9	12	16	20	25	31	56	110	182	264	347
2.5°	9	13	16	21	25	33	60	118	191	275	357
1.25°	9	13	16	21	26	34	63	122	196	281	363
0°	9	13	17	21	26	35	64	124	198	283	365
-1.25°	9	13	16	21	26	34	63	122	196	281	363
-2.5°	9	13	16	21	25	33	60	118	191	275	357
-3.75°	9	12	16	20	25	31	56	110	182	264	347
-5°	9	12	15	20	24	30	49	100	170	250	333
-6.25°	9	11	15	19	23	29	44	86	154	231	314
-7.5°	8	11	14	18	23	28	40	74	136	209	290
-8.75°	8	10	13	17	21	26	35	62	116	185	262
-10°	8	9	13	16	20	25	30	47	93	158	231
-11.25°	8	9	11	15	19	23	28	40	73	130	197
-12.5°	7	8	10	14	17	21	26	33	54	101	163
-13.75°	7	8	9	12	16	20	24	29	41	74	128
-15°	7	8	9	11	14	18	22	26	32	51	92
-16.25°	7	7	8	10	13	16	20	24	28	38	64
-17.5°	7	7	8	9	11	14	17	21	25	30	43
-18.75°	6	7	7	8	9	12	15	19	22	26	31
-20°	6	7	7	8	9	10	13	16	20	23	27
-21.25°	6	6	7	7	8	9	11	14	17	20	24



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	6	6	6	7	7	8	9	12	15	17	21
-23.75°	6	6	6	7	7	8	8	10	12	15	17
-25°	5	6	6	6	7	7	8	9	10	12	15
-26.25°	5	5	6	6	6	7	7	8	9	10	12
-27.5°	5	5	6	6	6	6	7	7	8	8	9
-28.75°	5	5	5	6	6	6	6	7	7	8	8
-30°	4	5	5	5	6	6	6	6	7	7	7
-31.25°	4	4	5	5	5	6	6	6	6	7	7
-32.5°	4	4	4	5	5	5	6	6	6	6	6
-33.75°	4	4	4	4	5	5	5	5	6	6	6
-35°	4	4	4	4	4	5	5	5	5	6	6
-36.25°	4	4	4	4	4	4	5	5	5	5	5
-37.5°	4	4	4	4	4	4	4	4	5	5	5
-38.75°	3	4	4	4	4	4	4	4	4	4	5
-40°	3	3	4	4	4	4	4	4	4	4	4
-41.25°	3	3	3	3	4	4	4	4	4	4	4
-42.5°	3	3	3	3	3	4	4	4	4	4	4
-43.75°	3	3	3	3	3	3	3	4	4	4	4
-45°	3	3	3	3	3	3	3	3	3	4	4
-46.25°	3	3	3	3	3	3	3	3	3	3	3
-47.5°	3	3	3	3	3	3	3	3	3	3	3
-48.75°	3	3	3	3	3	3	3	3	3	3	3
-50°	2	3	3	3	3	3	3	3	3	3	3
-51.25°	2	2	2	3	3	3	3	3	3	3	3
-52.5°	2	2	2	2	2	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	2	3	3	3	3
-55°	2	2	2	2	2	2	2	2	2	2	3
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	1	2	2	2	2	2	2	2	2	2	2
-58.75°	1	1	1	2	2	2	2	2	2	2	2
-60°	1	1	1	1	1	1	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	2
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	0	1	1	1	1	1	1	1	1	1	1
-66.25°	0	0	0	0	0	1	1	1	1	1	1
-67.5°	0	0	0	0	0	0	0	0	0	1	1
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	3	3
56.25°	2	2	2	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	4	4	4	4
47.5°	3	3	3	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	4	4	4	4	4	5
42.5°	4	4	4	4	4	4	5	5	5	5	5
41.25°	4	4	4	5	5	5	5	5	5	5	5
40°	5	5	5	5	5	5	5	6	6	6	6
38.75°	5	5	5	5	6	6	6	6	6	6	6
37.5°	5	5	6	6	6	6	6	6	6	7	7
36.25°	6	6	6	6	6	6	7	7	7	7	7
35°	6	6	6	7	7	7	7	7	8	8	8



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	6	7	7	7	7	8	8	8	9	9	10
32.5°	7	7	7	8	8	9	9	10	11	13	13
31.25°	7	8	8	9	10	11	12	14	15	16	17
30°	8	9	9	11	13	14	16	17	19	20	21
28.75°	9	10	12	14	16	18	20	21	23	25	26
27.5°	11	13	15	17	20	22	24	26	28	30	35
26.25°	14	16	19	21	24	26	29	33	40	47	62
25°	17	20	22	25	28	32	41	54	73	93	116
23.75°	20	23	26	30	38	51	74	101	130	158	185
22.5°	24	27	31	43	64	92	128	163	197	231	262
21.25°	27	33	45	73	109	149	190	232	271	308	341
20°	33	46	77	119	164	211	259	304	345	379	406
18.75°	45	77	122	172	224	277	328	370	406	432	450
17.5°	73	119	172	228	286	341	388	422	448	466	484
16.25°	109	164	224	286	345	396	432	457	479	500	525
15°	149	211	277	341	396	435	461	486	514	543	573
13.75°	190	259	328	388	432	461	489	521	555	591	633
12.5°	232	304	370	422	457	486	521	559	602	652	720
11.25°	271	345	406	448	479	514	555	602	661	739	830
10°	308	379	432	466	500	543	591	652	739	843	958
8.75°	341	406	450	484	525	573	633	720	830	958	1117
7.5°	366	426	464	500	548	604	682	792	925	1093	1310
6.25°	389	442	477	519	570	634	733	861	1022	1241	1531
5°	404	451	488	534	588	667	784	931	1127	1397	1765
3.75°	414	459	497	546	608	699	827	988	1221	1554	2002
2.5°	422	464	504	556	621	722	859	1042	1306	1682	2185
1.25°	427	467	509	562	630	736	882	1077	1359	1762	2309
0°	428	469	510	564	633	740	889	1088	1376	1788	2353
-1.25°	427	467	509	562	630	736	882	1077	1359	1762	2309
-2.5°	422	464	504	556	621	722	859	1042	1306	1682	2185
-3.75°	414	459	497	546	608	699	827	988	1221	1554	2002
-5°	404	451	488	534	588	667	784	931	1127	1397	1765
-6.25°	389	442	477	519	570	634	733	861	1022	1241	1531
-7.5°	366	426	464	500	548	604	682	792	925	1093	1310
-8.75°	341	406	450	484	525	573	633	720	830	958	1117
-10°	308	379	432	466	500	543	591	652	739	843	958
-11.25°	271	345	406	448	479	514	555	602	661	739	830
-12.5°	232	304	370	422	457	486	521	559	602	652	720
-13.75°	190	259	328	388	432	461	489	521	555	591	633
-15°	149	211	277	341	396	435	461	486	514	543	573
-16.25°	109	164	224	286	345	396	432	457	479	500	525
-17.5°	73	119	172	228	286	341	388	422	448	466	484
-18.75°	45	77	122	172	224	277	328	370	406	432	450
-20°	33	46	77	119	164	211	259	304	345	379	406
-21.25°	27	33	45	73	109	149	190	232	271	308	341



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	24	27	31	43	64	92	128	163	197	231	262
-23.75°	20	23	26	30	38	51	74	101	130	158	185
-25°	17	20	22	25	28	32	41	54	73	93	116
-26.25°	14	16	19	21	24	26	29	33	40	47	62
-27.5°	11	13	15	17	20	22	24	26	28	30	35
-28.75°	9	10	12	14	16	18	20	21	23	25	26
-30°	8	9	9	11	13	14	16	17	19	20	21
-31.25°	7	8	8	9	10	11	12	14	15	16	17
-32.5°	7	7	7	8	8	9	9	10	11	13	13
-33.75°	6	7	7	7	7	8	8	8	9	9	10
-35°	6	6	6	7	7	7	7	7	8	8	8
-36.25°	6	6	6	6	6	6	7	7	7	7	7
-37.5°	5	5	6	6	6	6	6	6	6	7	7
-38.75°	5	5	5	5	6	6	6	6	6	6	6
-40°	5	5	5	5	5	5	5	6	6	6	6
-41.25°	4	4	4	5	5	5	5	5	5	5	5
-42.5°	4	4	4	4	4	4	5	5	5	5	5
-43.75°	4	4	4	4	4	4	4	4	4	4	5
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	3	3	3	4	4	4	4	4	4	4	4
-48.75°	3	3	3	3	3	3	3	4	4	4	4
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	2	2	3	3	3	3	3	3	3	3
-57.5°	2	2	2	2	2	2	2	2	2	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	0	0	0	0	0	0	1	1	1	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	2	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	4	3	3	3	3
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	5	5	5	5	5	5	5	5	5	5	5
42.5°	5	5	5	5	5	5	5	5	5	5	5
41.25°	5	6	6	6	6	6	6	6	6	6	6
40°	6	6	6	6	6	6	6	6	6	6	6
38.75°	6	6	6	6	6	6	7	6	6	6	6
37.5°	7	7	7	7	7	7	7	7	7	7	7
36.25°	7	8	8	8	8	8	8	8	8	8	8
35°	8	9	9	9	9	9	9	9	9	9	9



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	11	11	12	12	13	13	13	13	13	12	12
32.5°	14	15	15	16	16	16	17	16	16	16	15
31.25°	18	19	20	20	21	21	21	21	21	20	20
30°	23	23	24	25	25	26	26	26	25	25	24
28.75°	28	29	30	31	33	34	35	34	33	31	30
27.5°	40	44	49	56	60	63	64	63	60	56	49
26.25°	74	86	100	110	118	122	124	122	118	110	100
25°	136	154	170	182	191	196	198	196	191	182	170
23.75°	209	231	250	264	275	281	283	281	275	264	250
22.5°	290	314	333	347	357	363	365	363	357	347	333
21.25°	366	389	404	414	422	427	428	427	422	414	404
20°	426	442	451	459	464	467	469	467	464	459	451
18.75°	464	477	488	497	504	509	510	509	504	497	488
17.5°	500	519	534	546	556	562	564	562	556	546	534
16.25°	548	570	588	608	621	630	633	630	621	608	588
15°	604	634	667	699	722	736	740	736	722	699	667
13.75°	682	733	784	827	859	882	889	882	859	827	784
12.5°	792	861	931	988	1042	1077	1088	1077	1042	988	931
11.25°	925	1022	1127	1221	1306	1359	1376	1359	1306	1221	1127
10°	1093	1241	1397	1554	1682	1762	1788	1762	1682	1554	1397
8.75°	1310	1531	1765	2002	2185	2309	2353	2309	2185	2002	1765
7.5°	1583	1898	2225	2538	2781	2945	3001	2945	2781	2538	2225
6.25°	1898	2313	2729	3119	3418	3607	3673	3607	3418	3119	2729
5°	2225	2729	3238	3674	4014	4234	4312	4234	4014	3674	3238
3.75°	2538	3119	3674	4159	4537	4785	4859	4785	4537	4159	3674
2.5°	2781	3418	4014	4537	4938	5191	5272	5191	4938	4537	4014
1.25°	2945	3607	4234	4785	5191	5448	5536	5448	5191	4785	4234
0°	3001	3673	4312	4859	5272	5536	5650	5536	5272	4859	4312
-1.25°	2945	3607	4234	4785	5191	5448	5536	5448	5191	4785	4234
-2.5°	2781	3418	4014	4537	4938	5191	5272	5191	4938	4537	4014
-3.75°	2538	3119	3674	4159	4537	4785	4859	4785	4537	4159	3674
-5°	2225	2729	3238	3674	4014	4234	4312	4234	4014	3674	3238
-6.25°	1898	2313	2729	3119	3418	3607	3673	3607	3418	3119	2729
-7.5°	1583	1898	2225	2538	2781	2945	3001	2945	2781	2538	2225
-8.75°	1310	1531	1765	2002	2185	2309	2353	2309	2185	2002	1765
-10°	1093	1241	1397	1554	1682	1762	1788	1762	1682	1554	1397
-11.25°	925	1022	1127	1221	1306	1359	1376	1359	1306	1221	1127
-12.5°	792	861	931	988	1042	1077	1088	1077	1042	988	931
-13.75°	682	733	784	827	859	882	889	882	859	827	784
-15°	604	634	667	699	722	736	740	736	722	699	667
-16.25°	548	570	588	608	621	630	633	630	621	608	588
-17.5°	500	519	534	546	556	562	564	562	556	546	534
-18.75°	464	477	488	497	504	509	510	509	504	497	488
-20°	426	442	451	459	464	467	469	467	464	459	451
-21.25°	366	389	404	414	422	427	428	427	422	414	404



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	290	314	333	347	357	363	365	363	357	347	333
-23.75°	209	231	250	264	275	281	283	281	275	264	250
-25°	136	154	170	182	191	196	198	196	191	182	170
-26.25°	74	86	100	110	118	122	124	122	118	110	100
-27.5°	40	44	49	56	60	63	64	63	60	56	49
-28.75°	28	29	30	31	33	34	35	34	33	31	30
-30°	23	23	24	25	25	26	26	26	25	25	24
-31.25°	18	19	20	20	21	21	21	21	21	20	20
-32.5°	14	15	15	16	16	16	17	16	16	16	15
-33.75°	11	11	12	12	13	13	13	13	13	12	12
-35°	8	9	9	9	9	9	9	9	9	9	9
-36.25°	7	8	8	8	8	8	8	8	8	8	8
-37.5°	7	7	7	7	7	7	7	7	7	7	7
-38.75°	6	6	6	6	6	6	7	6	6	6	6
-40°	6	6	6	6	6	6	6	6	6	6	6
-41.25°	5	6	6	6	6	6	6	6	6	6	6
-42.5°	5	5	5	5	5	5	5	5	5	5	5
-43.75°	5	5	5	5	5	5	5	5	5	5	5
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	3	3	3	3	3	3	4	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	2	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	1	1	1	0	0	0	0
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	2	2	2	2	2	2	2
56.25°	3	3	3	3	3	3	3	3	3	3	2
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	4	4	4	4	4	4	3	3	3	3	3
47.5°	4	4	4	4	4	4	4	4	4	4	3
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	5	5	5	4	4	4	4	4	4	4	4
42.5°	5	5	5	5	5	5	5	4	4	4	4
41.25°	6	5	5	5	5	5	5	5	5	5	4
40°	6	6	6	6	6	6	5	5	5	5	5
38.75°	6	6	6	6	6	6	6	6	6	5	5
37.5°	7	7	7	7	6	6	6	6	6	6	6
36.25°	8	7	7	7	7	7	7	6	6	6	6
35°	9	8	8	8	8	7	7	7	7	7	6



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	11	11	10	9	9	8	8	8	7	7	7
32.5°	15	14	13	13	11	10	9	9	8	8	7
31.25°	19	18	17	16	15	14	12	11	10	9	8
30°	23	23	21	20	19	17	16	14	13	11	9
28.75°	29	28	26	25	23	21	20	18	16	14	12
27.5°	44	40	35	30	28	26	24	22	20	17	15
26.25°	86	74	62	47	40	33	29	26	24	21	19
25°	154	136	116	93	73	54	41	32	28	25	22
23.75°	231	209	185	158	130	101	74	51	38	30	26
22.5°	314	290	262	231	197	163	128	92	64	43	31
21.25°	389	366	341	308	271	232	190	149	109	73	45
20°	442	426	406	379	345	304	259	211	164	119	77
18.75°	477	464	450	432	406	370	328	277	224	172	122
17.5°	519	500	484	466	448	422	388	341	286	228	172
16.25°	570	548	525	500	479	457	432	396	345	286	224
15°	634	604	573	543	514	486	461	435	396	341	277
13.75°	733	682	633	591	555	521	489	461	432	388	328
12.5°	861	792	720	652	602	559	521	486	457	422	370
11.25°	1022	925	830	739	661	602	555	514	479	448	406
10°	1241	1093	958	843	739	652	591	543	500	466	432
8.75°	1531	1310	1117	958	830	720	633	573	525	484	450
7.5°	1898	1583	1310	1093	925	792	682	604	548	500	464
6.25°	2313	1898	1531	1241	1022	861	733	634	570	519	477
5°	2729	2225	1765	1397	1127	931	784	667	588	534	488
3.75°	3119	2538	2002	1554	1221	988	827	699	608	546	497
2.5°	3418	2781	2185	1682	1306	1042	859	722	621	556	504
1.25°	3607	2945	2309	1762	1359	1077	882	736	630	562	509
0°	3673	3001	2353	1788	1376	1088	889	740	633	564	510
-1.25°	3607	2945	2309	1762	1359	1077	882	736	630	562	509
-2.5°	3418	2781	2185	1682	1306	1042	859	722	621	556	504
-3.75°	3119	2538	2002	1554	1221	988	827	699	608	546	497
-5°	2729	2225	1765	1397	1127	931	784	667	588	534	488
-6.25°	2313	1898	1531	1241	1022	861	733	634	570	519	477
-7.5°	1898	1583	1310	1093	925	792	682	604	548	500	464
-8.75°	1531	1310	1117	958	830	720	633	573	525	484	450
-10°	1241	1093	958	843	739	652	591	543	500	466	432
-11.25°	1022	925	830	739	661	602	555	514	479	448	406
-12.5°	861	792	720	652	602	559	521	486	457	422	370
-13.75°	733	682	633	591	555	521	489	461	432	388	328
-15°	634	604	573	543	514	486	461	435	396	341	277
-16.25°	570	548	525	500	479	457	432	396	345	286	224
-17.5°	519	500	484	466	448	422	388	341	286	228	172
-18.75°	477	464	450	432	406	370	328	277	224	172	122
-20°	442	426	406	379	345	304	259	211	164	119	77
-21.25°	389	366	341	308	271	232	190	149	109	73	45



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	314	290	262	231	197	163	128	92	64	43	31
-23.75°	231	209	185	158	130	101	74	51	38	30	26
-25°	154	136	116	93	73	54	41	32	28	25	22
-26.25°	86	74	62	47	40	33	29	26	24	21	19
-27.5°	44	40	35	30	28	26	24	22	20	17	15
-28.75°	29	28	26	25	23	21	20	18	16	14	12
-30°	23	23	21	20	19	17	16	14	13	11	9
-31.25°	19	18	17	16	15	14	12	11	10	9	8
-32.5°	15	14	13	13	11	10	9	9	8	8	7
-33.75°	11	11	10	9	9	8	8	8	7	7	7
-35°	9	8	8	8	8	7	7	7	7	7	6
-36.25°	8	7	7	7	7	7	7	6	6	6	6
-37.5°	7	7	7	7	6	6	6	6	6	6	6
-38.75°	6	6	6	6	6	6	6	6	6	5	5
-40°	6	6	6	6	6	6	5	5	5	5	5
-41.25°	6	5	5	5	5	5	5	5	5	5	4
-42.5°	5	5	5	5	5	5	5	4	4	4	4
-43.75°	5	5	5	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	3
-48.75°	4	4	4	4	4	4	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	2
-57.5°	3	3	3	3	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	1	1	1	1	0	0	0	0	0	0	0
66.25°	1	1	1	1	1	1	1	1	0	0	0
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	2	2	1	1	1	1	1	1	1	1
60°	2	2	2	2	2	2	2	1	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	2	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	2	2	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	2	2	2	2	2
52.5°	3	3	3	3	3	3	3	3	2	2	2
51.25°	3	3	3	3	3	3	3	3	3	3	2
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	3
47.5°	3	3	3	3	3	3	3	3	3	3	3
46.25°	4	4	3	3	3	3	3	3	3	3	3
45°	4	4	4	4	3	3	3	3	3	3	3
43.75°	4	4	4	4	4	4	3	3	3	3	3
42.5°	4	4	4	4	4	4	4	4	3	3	3
41.25°	4	4	4	4	4	4	4	4	4	3	3
40°	5	5	4	4	4	4	4	4	4	4	4
38.75°	5	5	5	4	4	4	4	4	4	4	4
37.5°	5	5	5	5	5	4	4	4	4	4	4
36.25°	6	6	5	5	5	5	5	4	4	4	4
35°	6	6	6	6	5	5	5	5	4	4	4



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	7	6	6	6	6	5	5	5	5	4	4
32.5°	7	7	6	6	6	6	6	5	5	5	4
31.25°	8	7	7	7	6	6	6	6	5	5	5
30°	9	8	7	7	7	6	6	6	6	5	5
28.75°	10	9	8	8	7	7	6	6	6	6	5
27.5°	13	11	9	8	8	7	7	6	6	6	6
26.25°	16	14	12	10	9	8	7	7	6	6	6
25°	20	17	15	12	10	9	8	7	7	6	6
23.75°	23	20	17	15	12	10	8	8	7	7	6
22.5°	27	24	21	17	15	12	9	8	7	7	6
21.25°	33	27	24	20	17	14	11	9	8	7	7
20°	46	33	27	23	20	16	13	10	9	8	7
18.75°	77	45	31	26	22	19	15	12	9	8	7
17.5°	119	73	43	30	25	21	17	14	11	9	8
16.25°	164	109	64	38	28	24	20	16	13	10	8
15°	211	149	92	51	32	26	22	18	14	11	9
13.75°	259	190	128	74	41	29	24	20	16	12	9
12.5°	304	232	163	101	54	33	26	21	17	14	10
11.25°	345	271	197	130	73	40	28	23	19	15	11
10°	379	308	231	158	93	47	30	25	20	16	13
8.75°	406	341	262	185	116	62	35	26	21	17	13
7.5°	426	366	290	209	136	74	40	28	23	18	14
6.25°	442	389	314	231	154	86	44	29	23	19	15
5°	451	404	333	250	170	100	49	30	24	20	15
3.75°	459	414	347	264	182	110	56	31	25	20	16
2.5°	464	422	357	275	191	118	60	33	25	21	16
1.25°	467	427	363	281	196	122	63	34	26	21	16
0°	469	428	365	283	198	124	64	35	26	21	17
-1.25°	467	427	363	281	196	122	63	34	26	21	16
-2.5°	464	422	357	275	191	118	60	33	25	21	16
-3.75°	459	414	347	264	182	110	56	31	25	20	16
-5°	451	404	333	250	170	100	49	30	24	20	15
-6.25°	442	389	314	231	154	86	44	29	23	19	15
-7.5°	426	366	290	209	136	74	40	28	23	18	14
-8.75°	406	341	262	185	116	62	35	26	21	17	13
-10°	379	308	231	158	93	47	30	25	20	16	13
-11.25°	345	271	197	130	73	40	28	23	19	15	11
-12.5°	304	232	163	101	54	33	26	21	17	14	10
-13.75°	259	190	128	74	41	29	24	20	16	12	9
-15°	211	149	92	51	32	26	22	18	14	11	9
-16.25°	164	109	64	38	28	24	20	16	13	10	8
-17.5°	119	73	43	30	25	21	17	14	11	9	8
-18.75°	77	45	31	26	22	19	15	12	9	8	7
-20°	46	33	27	23	20	16	13	10	9	8	7
-21.25°	33	27	24	20	17	14	11	9	8	7	7



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	27	24	21	17	15	12	9	8	7	7	6
-23.75°	23	20	17	15	12	10	8	8	7	7	6
-25°	20	17	15	12	10	9	8	7	7	6	6
-26.25°	16	14	12	10	9	8	7	7	6	6	6
-27.5°	13	11	9	8	8	7	7	6	6	6	6
-28.75°	10	9	8	8	7	7	6	6	6	6	5
-30°	9	8	7	7	7	6	6	6	6	5	5
-31.25°	8	7	7	7	6	6	6	6	5	5	5
-32.5°	7	7	6	6	6	6	6	5	5	5	4
-33.75°	7	6	6	6	6	5	5	5	5	4	4
-35°	6	6	6	6	5	5	5	5	4	4	4
-36.25°	6	6	5	5	5	5	5	4	4	4	4
-37.5°	5	5	5	5	5	4	4	4	4	4	4
-38.75°	5	5	5	4	4	4	4	4	4	4	4
-40°	5	5	4	4	4	4	4	4	4	4	4
-41.25°	4	4	4	4	4	4	4	4	4	3	3
-42.5°	4	4	4	4	4	4	4	4	3	3	3
-43.75°	4	4	4	4	4	4	3	3	3	3	3
-45°	4	4	4	4	3	3	3	3	3	3	3
-46.25°	4	4	3	3	3	3	3	3	3	3	3
-47.5°	3	3	3	3	3	3	3	3	3	3	3
-48.75°	3	3	3	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	2
-52.5°	3	3	3	3	3	3	3	3	2	2	2
-53.75°	3	3	3	3	3	3	2	2	2	2	2
-55°	3	3	3	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	1
-60°	2	2	2	2	2	2	2	1	1	1	1
-61.25°	2	2	2	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	0	0	0
-67.5°	1	1	1	1	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	1	0	0	0	0	0	0	0	0	0	0
63.75°	1	1	1	1	0	0	0	0	0	0	0
62.5°	1	1	1	1	1	1	0	0	0	0	0
61.25°	1	1	1	1	1	1	1	1	0	0	0
60°	1	1	1	1	1	1	1	1	1	1	0
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	2	1	1	1	1	1	1	1	1
55°	2	2	2	2	2	1	1	1	1	1	1
53.75°	2	2	2	2	2	2	2	1	1	1	1
52.5°	2	2	2	2	2	2	2	2	1	1	1
51.25°	2	2	2	2	2	2	2	2	2	2	1
50°	3	2	2	2	2	2	2	2	2	2	2
48.75°	3	3	3	2	2	2	2	2	2	2	2
47.5°	3	3	3	3	2	2	2	2	2	2	2
46.25°	3	3	3	3	3	3	2	2	2	2	2
45°	3	3	3	3	3	3	3	2	2	2	2
43.75°	3	3	3	3	3	3	3	3	2	2	2
42.5°	3	3	3	3	3	3	3	3	3	2	2
41.25°	3	3	3	3	3	3	3	3	3	3	2
40°	3	3	3	3	3	3	3	3	3	3	3
38.75°	4	3	3	3	3	3	3	3	3	3	3
37.5°	4	4	3	3	3	3	3	3	3	3	3
36.25°	4	4	4	3	3	3	3	3	3	3	3
35°	4	4	4	4	3	3	3	3	3	3	3



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	4	4	4	4	4	3	3	3	3	3	3
32.5°	4	4	4	4	4	4	3	3	3	3	3
31.25°	4	4	4	4	4	4	3	3	3	3	3
30°	5	4	4	4	4	4	4	3	3	3	3
28.75°	5	5	4	4	4	4	4	4	3	3	3
27.5°	5	5	5	4	4	4	4	4	3	3	3
26.25°	5	5	5	4	4	4	4	4	4	3	3
25°	6	5	5	5	4	4	4	4	4	3	3
23.75°	6	6	5	5	4	4	4	4	4	4	3
22.5°	6	6	5	5	5	4	4	4	4	4	3
21.25°	6	6	6	5	5	5	4	4	4	4	4
20°	7	6	6	5	5	5	4	4	4	4	4
18.75°	7	6	6	6	5	5	4	4	4	4	4
17.5°	7	7	6	6	5	5	5	4	4	4	4
16.25°	7	7	6	6	6	5	5	4	4	4	4
15°	8	7	6	6	6	5	5	4	4	4	4
13.75°	8	7	7	6	6	5	5	5	4	4	4
12.5°	8	7	7	6	6	6	5	5	4	4	4
11.25°	9	8	7	6	6	6	5	5	4	4	4
10°	9	8	7	7	6	6	5	5	4	4	4
8.75°	10	8	7	7	6	6	5	5	5	4	4
7.5°	11	8	7	7	6	6	5	5	5	4	4
6.25°	11	9	8	7	6	6	6	5	5	4	4
5°	12	9	8	7	6	6	6	5	5	4	4
3.75°	12	9	8	7	6	6	6	5	5	4	4
2.5°	13	9	8	7	6	6	6	5	5	4	4
1.25°	13	9	8	7	6	6	6	5	5	4	4
0°	13	9	8	7	6	6	6	5	5	4	4
-1.25°	13	9	8	7	6	6	6	5	5	4	4
-2.5°	13	9	8	7	6	6	6	5	5	4	4
-3.75°	12	9	8	7	6	6	6	5	5	4	4
-5°	12	9	8	7	6	6	6	5	5	4	4
-6.25°	11	9	8	7	6	6	6	5	5	4	4
-7.5°	11	8	7	7	6	6	5	5	5	4	4
-8.75°	10	8	7	7	6	6	5	5	5	4	4
-10°	9	8	7	7	6	6	5	5	4	4	4
-11.25°	9	8	7	6	6	6	5	5	4	4	4
-12.5°	8	7	7	6	6	6	5	5	4	4	4
-13.75°	8	7	7	6	6	5	5	5	4	4	4
-15°	8	7	6	6	6	5	5	4	4	4	4
-16.25°	7	7	6	6	6	5	5	4	4	4	4
-17.5°	7	7	6	6	5	5	5	4	4	4	4
-18.75°	7	6	6	6	5	5	4	4	4	4	4
-20°	7	6	6	5	5	5	4	4	4	4	4
-21.25°	6	6	6	5	5	5	4	4	4	4	4



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	6	6	5	5	5	4	4	4	4	4	3
-23.75°	6	6	5	5	4	4	4	4	4	4	3
-25°	6	5	5	5	4	4	4	4	4	3	3
-26.25°	5	5	5	4	4	4	4	4	4	3	3
-27.5°	5	5	5	4	4	4	4	4	3	3	3
-28.75°	5	5	4	4	4	4	4	4	3	3	3
-30°	5	4	4	4	4	4	4	3	3	3	3
-31.25°	4	4	4	4	4	4	3	3	3	3	3
-32.5°	4	4	4	4	4	4	3	3	3	3	3
-33.75°	4	4	4	4	4	3	3	3	3	3	3
-35°	4	4	4	4	3	3	3	3	3	3	3
-36.25°	4	4	4	3	3	3	3	3	3	3	3
-37.5°	4	4	3	3	3	3	3	3	3	3	3
-38.75°	4	3	3	3	3	3	3	3	3	3	3
-40°	3	3	3	3	3	3	3	3	3	3	3
-41.25°	3	3	3	3	3	3	3	3	3	3	2
-42.5°	3	3	3	3	3	3	3	3	3	2	2
-43.75°	3	3	3	3	3	3	3	3	2	2	2
-45°	3	3	3	3	3	3	3	2	2	2	2
-46.25°	3	3	3	3	3	3	2	2	2	2	2
-47.5°	3	3	3	3	2	2	2	2	2	2	2
-48.75°	3	3	3	2	2	2	2	2	2	2	2
-50°	3	2	2	2	2	2	2	2	2	2	2
-51.25°	2	2	2	2	2	2	2	2	2	2	1
-52.5°	2	2	2	2	2	2	2	2	1	1	1
-53.75°	2	2	2	2	2	2	2	1	1	1	1
-55°	2	2	2	2	2	1	1	1	1	1	1
-56.25°	2	2	2	1	1	1	1	1	1	1	1
-57.5°	2	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	0
-61.25°	1	1	1	1	1	1	1	1	0	0	0
-62.5°	1	1	1	1	1	1	0	0	0	0	0
-63.75°	1	1	1	1	0	0	0	0	0	0	0
-65°	1	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	1	0	0	0	0	0	0	0	0	0	0
57.5°	1	1	0	0	0	0	0	0	0	0	0
56.25°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	1	0	0	0	0	0	0	0
53.75°	1	1	1	1	1	0	0	0	0	0	0
52.5°	1	1	1	1	1	1	0	0	0	0	0
51.25°	1	1	1	1	1	1	1	0	0	0	0
50°	1	1	1	1	1	1	1	1	0	0	0
48.75°	2	1	1	1	1	1	1	1	1	0	0
47.5°	2	2	1	1	1	1	1	1	1	1	0
46.25°	2	2	2	1	1	1	1	1	1	1	0
45°	2	2	2	2	1	1	1	1	1	1	1
43.75°	2	2	2	2	1	1	1	1	1	1	1
42.5°	2	2	2	2	2	1	1	1	1	1	1
41.25°	2	2	2	2	2	2	1	1	1	1	1
40°	2	2	2	2	2	2	1	1	1	1	1
38.75°	2	2	2	2	2	2	2	1	1	1	1
37.5°	3	2	2	2	2	2	2	1	1	1	1
36.25°	3	3	2	2	2	2	2	2	1	1	1
35°	3	3	2	2	2	2	2	2	1	1	1



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	3	3	3	2	2	2	2	2	2	1	1
32.5°	3	3	3	2	2	2	2	2	2	1	1
31.25°	3	3	3	3	2	2	2	2	2	2	1
30°	3	3	3	3	2	2	2	2	2	2	1
28.75°	3	3	3	3	3	2	2	2	2	2	1
27.5°	3	3	3	3	3	2	2	2	2	2	2
26.25°	3	3	3	3	3	3	2	2	2	2	2
25°	3	3	3	3	3	3	2	2	2	2	2
23.75°	3	3	3	3	3	3	2	2	2	2	2
22.5°	3	3	3	3	3	3	3	2	2	2	2
21.25°	3	3	3	3	3	3	3	2	2	2	2
20°	3	3	3	3	3	3	3	2	2	2	2
18.75°	3	3	3	3	3	3	3	2	2	2	2
17.5°	4	3	3	3	3	3	3	3	2	2	2
16.25°	4	3	3	3	3	3	3	3	2	2	2
15°	4	3	3	3	3	3	3	3	2	2	2
13.75°	4	3	3	3	3	3	3	3	2	2	2
12.5°	4	4	3	3	3	3	3	3	2	2	2
11.25°	4	4	3	3	3	3	3	3	2	2	2
10°	4	4	3	3	3	3	3	3	3	2	2
8.75°	4	4	3	3	3	3	3	3	3	2	2
7.5°	4	4	3	3	3	3	3	3	3	2	2
6.25°	4	4	3	3	3	3	3	3	3	2	2
5°	4	4	3	3	3	3	3	3	3	2	2
3.75°	4	4	3	3	3	3	3	3	3	2	2
2.5°	4	4	3	3	3	3	3	3	3	2	2
1.25°	4	4	3	3	3	3	3	3	3	2	2
0°	4	4	4	3	3	3	3	3	3	2	2
-1.25°	4	4	3	3	3	3	3	3	3	2	2
-2.5°	4	4	3	3	3	3	3	3	3	2	2
-3.75°	4	4	3	3	3	3	3	3	3	2	2
-5°	4	4	3	3	3	3	3	3	3	2	2
-6.25°	4	4	3	3	3	3	3	3	3	2	2
-7.5°	4	4	3	3	3	3	3	3	3	2	2
-8.75°	4	4	3	3	3	3	3	3	3	2	2
-10°	4	4	3	3	3	3	3	3	3	2	2
-11.25°	4	4	3	3	3	3	3	3	2	2	2
-12.5°	4	4	3	3	3	3	3	3	2	2	2
-13.75°	4	3	3	3	3	3	3	3	2	2	2
-15°	4	3	3	3	3	3	3	3	2	2	2
-16.25°	4	3	3	3	3	3	3	3	2	2	2
-17.5°	4	3	3	3	3	3	3	3	2	2	2
-18.75°	3	3	3	3	3	3	3	2	2	2	2
-20°	3	3	3	3	3	3	3	2	2	2	2
-21.25°	3	3	3	3	3	3	3	2	2	2	2



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	3	3	3	3	3	3	3	2	2	2	2
-23.75°	3	3	3	3	3	3	2	2	2	2	2
-25°	3	3	3	3	3	3	2	2	2	2	2
-26.25°	3	3	3	3	3	3	2	2	2	2	2
-27.5°	3	3	3	3	3	2	2	2	2	2	2
-28.75°	3	3	3	3	3	2	2	2	2	2	1
-30°	3	3	3	3	2	2	2	2	2	2	1
-31.25°	3	3	3	3	2	2	2	2	2	2	1
-32.5°	3	3	3	2	2	2	2	2	2	1	1
-33.75°	3	3	3	2	2	2	2	2	2	1	1
-35°	3	3	2	2	2	2	2	2	1	1	1
-36.25°	3	3	2	2	2	2	2	2	1	1	1
-37.5°	3	2	2	2	2	2	2	1	1	1	1
-38.75°	2	2	2	2	2	2	2	1	1	1	1
-40°	2	2	2	2	2	2	1	1	1	1	1
-41.25°	2	2	2	2	2	2	1	1	1	1	1
-42.5°	2	2	2	2	2	1	1	1	1	1	1
-43.75°	2	2	2	2	1	1	1	1	1	1	1
-45°	2	2	2	2	1	1	1	1	1	1	1
-46.25°	2	2	2	1	1	1	1	1	1	1	0
-47.5°	2	2	1	1	1	1	1	1	1	1	0
-48.75°	2	1	1	1	1	1	1	1	1	0	0
-50°	1	1	1	1	1	1	1	1	0	0	0
-51.25°	1	1	1	1	1	1	1	0	0	0	0
-52.5°	1	1	1	1	1	1	0	0	0	0	0
-53.75°	1	1	1	1	1	0	0	0	0	0	0
-55°	1	1	1	1	0	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	1	0	0	0	0	0	0	0	0	0
-58.75°	1	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	1	0	0	0	0	0	0	0	0	0	0
41.25°	1	0	0	0	0	0	0	0	0	0	0
40°	1	1	0	0	0	0	0	0	0	0	0
38.75°	1	1	0	0	0	0	0	0	0	0	0
37.5°	1	1	1	0	0	0	0	0	0	0	0
36.25°	1	1	1	0	0	0	0	0	0	0	0
35°	1	1	1	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	1	0	0	0	0	0	0	0
32.5°	1	1	1	1	0	0	0	0	0	0	0
31.25°	1	1	1	1	0	0	0	0	0	0	0
30°	1	1	1	1	0	0	0	0	0	0	0
28.75°	1	1	1	1	1	0	0	0	0	0	0
27.5°	1	1	1	1	1	0	0	0	0	0	0
26.25°	1	1	1	1	1	0	0	0	0	0	0
25°	1	1	1	1	1	0	0	0	0	0	0
23.75°	1	1	1	1	1	1	0	0	0	0	0
22.5°	2	1	1	1	1	1	0	0	0	0	0
21.25°	2	1	1	1	1	1	0	0	0	0	0
20°	2	1	1	1	1	1	0	0	0	0	0
18.75°	2	1	1	1	1	1	0	0	0	0	0
17.5°	2	1	1	1	1	1	0	0	0	0	0
16.25°	2	2	1	1	1	1	0	0	0	0	0
15°	2	2	1	1	1	1	0	0	0	0	0
13.75°	2	2	1	1	1	1	1	0	0	0	0
12.5°	2	2	1	1	1	1	1	0	0	0	0
11.25°	2	2	1	1	1	1	1	0	0	0	0
10°	2	2	1	1	1	1	1	0	0	0	0
8.75°	2	2	1	1	1	1	1	0	0	0	0
7.5°	2	2	1	1	1	1	1	0	0	0	0
6.25°	2	2	1	1	1	1	1	0	0	0	0
5°	2	2	1	1	1	1	1	0	0	0	0
3.75°	2	2	1	1	1	1	1	0	0	0	0
2.5°	2	2	1	1	1	1	1	0	0	0	0
1.25°	2	2	1	1	1	1	1	0	0	0	0
0°	2	2	2	1	1	1	1	0	0	0	0
-1.25°	2	2	1	1	1	1	1	0	0	0	0
-2.5°	2	2	1	1	1	1	1	0	0	0	0
-3.75°	2	2	1	1	1	1	1	0	0	0	0
-5°	2	2	1	1	1	1	1	0	0	0	0
-6.25°	2	2	1	1	1	1	1	0	0	0	0
-7.5°	2	2	1	1	1	1	1	0	0	0	0
-8.75°	2	2	1	1	1	1	1	0	0	0	0
-10°	2	2	1	1	1	1	1	0	0	0	0
-11.25°	2	2	1	1	1	1	1	0	0	0	0
-12.5°	2	2	1	1	1	1	1	0	0	0	0
-13.75°	2	2	1	1	1	1	1	0	0	0	0
-15°	2	2	1	1	1	1	0	0	0	0	0
-16.25°	2	2	1	1	1	1	0	0	0	0	0
-17.5°	2	1	1	1	1	1	0	0	0	0	0
-18.75°	2	1	1	1	1	1	0	0	0	0	0
-20°	2	1	1	1	1	1	0	0	0	0	0
-21.25°	2	1	1	1	1	1	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	1	1	1	1	1	0	0	0	0	0
-23.75°	1	1	1	1	1	1	0	0	0	0	0
-25°	1	1	1	1	1	0	0	0	0	0	0
-26.25°	1	1	1	1	1	0	0	0	0	0	0
-27.5°	1	1	1	1	1	0	0	0	0	0	0
-28.75°	1	1	1	1	1	0	0	0	0	0	0
-30°	1	1	1	1	0	0	0	0	0	0	0
-31.25°	1	1	1	1	0	0	0	0	0	0	0
-32.5°	1	1	1	1	0	0	0	0	0	0	0
-33.75°	1	1	1	1	0	0	0	0	0	0	0
-35°	1	1	1	0	0	0	0	0	0	0	0
-36.25°	1	1	1	0	0	0	0	0	0	0	0
-37.5°	1	1	1	0	0	0	0	0	0	0	0
-38.75°	1	1	0	0	0	0	0	0	0	0	0
-40°	1	1	0	0	0	0	0	0	0	0	0
-41.25°	1	0	0	0	0	0	0	0	0	0	0
-42.5°	1	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: P220508 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-[RW, RI]-LED3597-S-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)