Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1559317

Luminaire Tested: 24CGTX-72-B2750-W2D2-3000K

Issue Date: 9/3/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1559317
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2510-581-45)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/3/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-72-B2750-W2D2-3000K
Description:	2X4 7200 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 3000K CCT WITH FROSTED SMOOTH l
Light Source:	3000K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	7291.7 lumens
Efficiency:	N/A
Efficacy:	106.9 lumens/watt
Spacing Criteria (0/90/45):	1.29 / 1.28 / 1.4
Luminous Opening:	Rectangular (W 2' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	68.2
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559317
CATALOG NUMBER: 24CGTX-72-B2750-W2D2-3000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559317
CATALOG NUMBER: 24CGTX-72-B2750-W2D2-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	97	93	96	93	90	92	90	87	89	87	84	82
2	98	89	82	76	95	87	81	75	84	78	73	80	76	72	77	74	70	68
3	89	78	70	63	86	76	69	62	73	67	61	71	65	60	68	63	59	57
4	81	69	60	53	79	68	59	53	65	58	52	63	56	51	60	55	50	48
5	75	61	52	45	73	60	52	45	58	50	45	56	49	44	54	48	44	41
6	69	55	46	39	67	54	46	39	52	45	39	51	44	39	49	43	38	36
7	64	50	41	35	62	49	41	35	48	40	34	46	39	34	45	39	34	32
8	59	46	37	31	58	45	37	31	44	36	31	42	35	30	41	35	30	28
9	55	42	33	28	54	41	33	28	40	33	28	39	32	27	38	32	27	25
10	52	39	30	25	51	38	30	25	37	30	25	36	29	25	35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3207	3207	3207
5°	3226	3211	3215
10°	3228	3214	3220
15°	3227	3216	3221
20°	3227	3214	3222
25°	3221	3209	3218
30°	3212	3201	3204
35°	3201	3190	3191
40°	3189	3175	3177
45°	3176	3157	3157
50°	3148	3140	3140
55°	3121	3110	3105
60°	3090	3077	3052
65°	3046	3034	3015
70°	3015	2968	2921
75°	2927	2901	2860
80°	2903	2834	2803
85°	2908	2800	2754

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
Vertical Angle: 87.5°
Luminance: 3338 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559317
CATALOG NUMBER: 24CGTX-72-B2750-W2D2-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.4	3.1
10°-20°	652.4	8.9
20°-30°	997.1	13.7
30°-40°	1215.5	16.7
40°-50°	1281.2	17.6
50°-60°	1185.8	16.3
60°-70°	941.1	12.9
70°-80°	589.8	8.1
80°-90°	202.5	2.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1875.9	25.7
0°-40°	3091.4	42.4
0°-60°	5558.4	76.2
0°-90°	7291.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7291.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2384	2384	2384	2384	2384	
5°	2389	2381	2378	2376	2381	227
15°	2317	2311	2309	2307	2313	654
25°	2169	2162	2161	2160	2167	1000
35°	1949	1944	1942	1941	1943	1219
45°	1669	1661	1659	1657	1659	1286
55°	1331	1330	1326	1324	1324	1192
65°	957	954	953	946	947	947
75°	563	563	558	552	550	598
85°	188	184	181	180	178	205
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559317
CATALOG NUMBER: 24CGTX-72-B2750-W2D2-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*2383.7*	2383.7	2383.7	2383.7	2383.7
2.5°	*2392.7*	*2385.7*	*2382.7*	*2380.7*	*2385.7*
5°	*2388.7*	2380.7	2377.7	2375.7	2380.7
7.5°	*2378.7*	2370.7	2368.7	2366.7	2372.7
10°	*2362.7*	2355.7	2352.7	2352.7	2356.7
12.5°	*2342.6*	2335.6	2333.6	2331.6	2337.6
15°	*2316.6*	2310.6	2308.6	2306.6	2312.6
17.5°	*2287.5*	2281.5	2279.5	2278.5	2283.5
20°	*2253.5*	2245.5	2244.5	2245.5	2250.5
22.5°	*2213.4*	2206.4	2205.4	2205.4	2210.4
25°	*2169.3*	2162.3	2161.3	2160.3	2167.3
27.5°	*2121.2*	2114.2	2113.2	2112.2	2115.2
30°	*2067.1*	2061.1	2060.1	2059.1	2062.1
32.5°	*2009.0*	2004.0	2002.0	2000.0	2006.0
35°	*1948.9*	1943.9	1941.9	1940.9	1942.9
37.5°	*1881.7*	1879.7	1876.7	1875.7	1875.7
40°	*1815.6*	1810.6	1807.6	1806.6	1808.6
42.5°	*1740.5*	1739.5	1737.4	1734.4	1736.4
45°	*1669.3*	1661.3	1659.3	1657.3	1659.3
47.5°	*1587.1*	1581.1	1581.1	1578.1	1582.1
50°	*1504.0*	1505.0	1500.0	1497.0	1500.0
52.5°	*1424.8*	1417.8	1413.8	1412.8	1410.8
55°	*1330.6*	1329.6	1325.6	1323.6	1323.6
57.5°	*1244.5*	1239.5	1238.5	1231.4	1233.4
60°	*1148.3*	1144.3	1143.3	1138.3	1134.3
62.5°	*1052.1*	1052.1	1052.1	1042.1	1044.1
65°	*956.9*	953.9	952.9	945.9	946.9
67.5°	*859.7*	860.7	852.7	849.7	848.7
70°	*766.5*	758.5	754.5	750.5	742.5
72.5°	*664.3*	662.3	658.3	650.3	644.3
75°	*563.1*	563.1	558.1	552.1	550.1
77.5°	*467.9*	462.9	463.9	457.9	452.9
80°	*374.7*	368.7	365.7	363.7	361.7
82.5°	*278.6*	277.6	274.5	271.5	269.5
85°	*188.4*	184.4	181.4	180.4	178.4
87.5°	*97.2*	102.2	103.2	107.2	108.2
90°	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1559317
CATALOG NUMBER: 24CGTX-72-B2750-W2D2-3000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.16	17.84	16.53	18.15	18.47	16.12	17.79	16.48	18.11	18.42
	3H	18.17	19.69	18.54	20.01	20.37	18.09	19.61	18.46	19.93	20.29
	4H	18.97	20.41	19.37	20.75	21.13	18.87	20.31	19.27	20.66	21.03
	6H	19.63	20.96	20.04	21.33	21.72	19.52	20.85	19.93	21.21	21.60
	8H	19.88	21.15	20.30	21.54	21.94	19.76	21.03	20.18	21.42	21.82
	12H	20.07	21.30	20.50	21.68	22.11	19.94	21.17	20.37	21.55	21.97
4H	2H	16.85	18.28	17.25	18.63	19.01	16.81	18.25	17.21	18.59	18.97
	3H	19.08	20.29	19.49	20.69	21.09	19.01	20.22	19.42	20.62	21.02
	4H	20.02	21.13	20.46	21.54	21.97	19.94	21.04	20.37	21.45	21.89
	6H	20.83	21.80	21.28	22.24	22.69	20.73	21.69	21.18	22.13	22.59
	8H	21.14	22.05	21.60	22.49	22.95	21.03	21.94	21.49	22.38	22.84
	12H	21.40	22.22	21.88	22.69	23.16	21.28	22.09	21.76	22.57	23.04
8H	4H	20.40	21.31	20.86	21.75	22.21	20.33	21.23	20.79	21.67	22.14
	6H	21.36	22.12	21.85	22.60	23.08	21.27	22.03	21.76	22.51	22.99
	8H	21.77	22.45	22.27	22.95	23.44	21.67	22.35	22.17	22.85	23.34
	12H	22.13	22.73	22.63	23.22	23.78	22.02	22.62	22.52	23.11	23.67
12H	4H	20.46	21.27	20.94	21.75	22.22	20.39	21.20	20.86	21.68	22.14
	6H	21.45	22.13	21.95	22.63	23.12	21.36	22.04	21.87	22.55	23.03
	8H	21.93	22.53	22.43	23.02	23.58	21.83	22.44	22.34	22.93	23.48

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-581-7-R2

Test Date: 02/03/2026

Luminaire Tested: 24CGTX-45-B2750-W2D-3000K

Data in this report applies to families of products including 24CGTX-45-UNV


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-581-7-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-45-B2750-W2D-3000K**
Description:	*THIS IS A REVISION OF REPORT SP1-2510-581-7-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 CGTX 4500 lumen with BioUp Boards - 3000K

Spectral Parameters

CCT (K):	2952	CRI (Ra):	93.5		
CIE u':	0.2542	R1:	95.6	R9:	82.5
CIE v':	0.5145	R2:	94.7	R10:	90.6
Duv:	-0.0056	R3:	96.0	R11:	92.8
CIE x:	0.4322	R4:	97.3	R12:	84.0
CIE y:	0.3888	R5:	94.8	R13:	94.8
CIE z:	0.1790	R6:	87.8	R14:	98.9
Peak Wavelength (nm):	630	R7:	91.5	R15:	98.9
Dominant Wavelength (nm):	585	R8:	90.6		
Purity:	46.40923				
Rf:	93.3				
Rg:	101.3				



Test Conditions


Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.1

REPORT NUMBER: SP1-2510-581-7-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2510-581-7-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2952K
CIE x = 0.4322
CIE y = 0.3888
Duv = -0.0056

Point lies inside the ANSI 3000K 7-step quadrangle

REPORT NUMBER: SP1-2510-581-7-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	104	NR	620	249	NR	750	5	NR	880	0	NR
365	0	NR	495	113	NR	625	262	NR	755	5	NR	885	0	NR
370	0	NR	500	123	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	131	NR	635	519	NR	765	3	NR	895	0	NR
380	0	NR	510	137	NR	640	160	NR	770	3	NR	900	0	NR
385	0	NR	515	141	NR	645	177	NR	775	2	NR	905	0	NR
390	1	NR	520	145	NR	650	138	NR	780	2	NR	910	0	NR
395	1	NR	525	147	NR	655	114	NR	785	2	NR	915	0	NR
400	1	NR	530	151	NR	660	96	NR	790	2	NR	920	0	NR
405	2	NR	535	155	NR	665	80	NR	795	1	NR	925	0	NR
410	3	NR	540	159	NR	670	75	NR	800	1	NR	930	0	NR
415	5	NR	545	165	NR	675	60	NR	805	1	NR	935	0	NR
420	9	NR	550	171	NR	680	52	NR	810	1	NR	940	0	NR
425	15	NR	555	176	NR	685	44	NR	815	1	NR	945	0	NR
430	26	NR	560	184	NR	690	38	NR	820	1	NR	950	0	NR
435	43	NR	565	190	NR	695	32	NR	825	1	NR	955	0	NR
440	70	NR	570	197	NR	700	28	NR	830	1	NR	960	0	NR
445	121	NR	575	203	NR	705	24	NR	835	0	NR	965	0	NR
450	160	NR	580	209	NR	710	20	NR	840	0	NR	970	0	NR
455	120	NR	585	215	NR	715	17	NR	845	0	NR	975	0	NR
460	91	NR	590	220	NR	720	14	NR	850	0	NR	980	0	NR
465	98	NR	595	223	NR	725	12	NR	855	0	NR	985	0	NR
470	108	NR	600	228	NR	730	10	NR	860	0	NR	990	0	NR
475	111	NR	605	233	NR	735	9	NR	865	0	NR	995	0	NR
480	104	NR	610	265	NR	740	8	NR	870	0	NR	1000	0	NR
485	100	NR	615	273	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-7-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.53**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	104	NR	620	249	NR	750	5	NR	880	0	NR
365	0	NR	495	113	NR	625	262	NR	755	5	NR	885	0	NR
370	0	NR	500	123	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	131	NR	635	519	NR	765	3	NR	895	0	NR
380	0	NR	510	137	NR	640	160	NR	770	3	NR	900	0	NR
385	0	NR	515	141	NR	645	177	NR	775	2	NR	905	0	NR
390	1	NR	520	145	NR	650	138	NR	780	2	NR	910	0	NR
395	1	NR	525	147	NR	655	114	NR	785	2	NR	915	0	NR
400	1	NR	530	151	NR	660	96	NR	790	2	NR	920	0	NR
405	2	NR	535	155	NR	665	80	NR	795	1	NR	925	0	NR
410	3	NR	540	159	NR	670	75	NR	800	1	NR	930	0	NR
415	5	NR	545	165	NR	675	60	NR	805	1	NR	935	0	NR
420	9	NR	550	171	NR	680	52	NR	810	1	NR	940	0	NR
425	15	NR	555	176	NR	685	44	NR	815	1	NR	945	0	NR
430	26	NR	560	184	NR	690	38	NR	820	1	NR	950	0	NR
435	43	NR	565	190	NR	695	32	NR	825	1	NR	955	0	NR
440	70	NR	570	197	NR	700	28	NR	830	1	NR	960	0	NR
445	121	NR	575	203	NR	705	24	NR	835	0	NR	965	0	NR
450	160	NR	580	209	NR	710	20	NR	840	0	NR	970	0	NR
455	120	NR	585	215	NR	715	17	NR	845	0	NR	975	0	NR
460	91	NR	590	220	NR	720	14	NR	850	0	NR	980	0	NR
465	98	NR	595	223	NR	725	12	NR	855	0	NR	985	0	NR
470	108	NR	600	228	NR	730	10	NR	860	0	NR	990	0	NR
475	111	NR	605	233	NR	735	9	NR	865	0	NR	995	0	NR
480	104	NR	610	265	NR	740	8	NR	870	0	NR	1000	0	NR
485	100	NR	615	273	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-7-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.12**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	104	NR	620	249	NR	750	5	NR	880	0	NR
365	0	NR	495	113	NR	625	262	NR	755	5	NR	885	0	NR
370	0	NR	500	123	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	131	NR	635	519	NR	765	3	NR	895	0	NR
380	0	NR	510	137	NR	640	160	NR	770	3	NR	900	0	NR
385	0	NR	515	141	NR	645	177	NR	775	2	NR	905	0	NR
390	1	NR	520	145	NR	650	138	NR	780	2	NR	910	0	NR
395	1	NR	525	147	NR	655	114	NR	785	2	NR	915	0	NR
400	1	NR	530	151	NR	660	96	NR	790	2	NR	920	0	NR
405	2	NR	535	155	NR	665	80	NR	795	1	NR	925	0	NR
410	3	NR	540	159	NR	670	75	NR	800	1	NR	930	0	NR
415	5	NR	545	165	NR	675	60	NR	805	1	NR	935	0	NR
420	9	NR	550	171	NR	680	52	NR	810	1	NR	940	0	NR
425	15	NR	555	176	NR	685	44	NR	815	1	NR	945	0	NR
430	26	NR	560	184	NR	690	38	NR	820	1	NR	950	0	NR
435	43	NR	565	190	NR	695	32	NR	825	1	NR	955	0	NR
440	70	NR	570	197	NR	700	28	NR	830	1	NR	960	0	NR
445	121	NR	575	203	NR	705	24	NR	835	0	NR	965	0	NR
450	160	NR	580	209	NR	710	20	NR	840	0	NR	970	0	NR
455	120	NR	585	215	NR	715	17	NR	845	0	NR	975	0	NR
460	91	NR	590	220	NR	720	14	NR	850	0	NR	980	0	NR
465	98	NR	595	223	NR	725	12	NR	855	0	NR	985	0	NR
470	108	NR	600	228	NR	730	10	NR	860	0	NR	990	0	NR
475	111	NR	605	233	NR	735	9	NR	865	0	NR	995	0	NR
480	104	NR	610	265	NR	740	8	NR	870	0	NR	1000	0	NR
485	100	NR	615	273	NR	745	6	NR	875	0	NR			


REPORT NUMBER: SP1-2510-581-7-R2

TM-30-18


Summary


R_f = 93.3
R_g = 101.3
CIE R_a = 93.5
R_9 = 82.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-581-7-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 97	CES51 = 95	CES76 = 94
CES02 = 64	CES27 = 92	CES52 = 96	CES77 = 79
CES03 = 32	CES28 = 98	CES53 = 96	CES78 = 92
CES04 = 70	CES29 = 98	CES54 = 93	CES79 = 83
CES05 = 51	CES30 = 94	CES55 = 93	CES80 = 87
CES06 = 51	CES31 = 98	CES56 = 96	CES81 = 65
CES07 = 44	CES32 = 93	CES57 = 96	CES82 = 94
CES08 = 43	CES33 = 99	CES58 = 95	CES83 = 91
CES09 = 29	CES34 = 97	CES59 = 98	CES84 = 98
CES10 = 76	CES35 = 98	CES60 = 94	CES85 = 78
CES11 = 59	CES36 = 86	CES61 = 95	CES86 = 77
CES12 = 65	CES37 = 98	CES62 = 89	CES87 = 95
CES13 = 44	CES38 = 90	CES63 = 98	CES88 = 97
CES14 = 74	CES39 = 99	CES64 = 96	CES89 = 85
CES15 = 72	CES40 = 98	CES65 = 97	CES90 = 95
CES16 = 48	CES41 = 95	CES66 = 96	CES91 = 82
CES17 = 50	CES42 = 96	CES67 = 96	CES92 = 81
CES18 = 57	CES43 = 94	CES68 = 95	CES93 = 88
CES19 = 72	CES44 = 99	CES69 = 95	CES94 = 77
CES20 = 68	CES45 = 97	CES70 = 95	CES95 = 89
CES21 = 86	CES46 = 99	CES71 = 92	CES96 = 96
CES22 = 79	CES47 = 85	CES72 = 97	CES97 = 97
CES23 = 91	CES48 = 94	CES73 = 92	CES98 = 98
CES24 = 90	CES49 = 97	CES74 = 86	CES99 = 94
CES25 = 71	CES50 = 95	CES75 = 92	





REPORT NUMBER: SP1-2510-581-7-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-581-7-R2

TM-30-18

Measure Comparisons





(END OF REPORT)