Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590723

Luminaire Tested: 22CGTX-20-L92765-W2A-4000K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590723
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G2-2510-566-13)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	22CGTX-20-L92765-W2A-4000K
Description:	2X2 2000 LUMEN CGTX TROFFER WITH VividTune LEDS AT 4000K CCT WITH FROSTED SMOOTH LENS
Light Source:	4000K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	1987.2 lumens
Efficiency:	N/A
Efficacy:	108.0 lumens/watt
Spacing Criteria (0/90/45):	1.25 / 1.26 / 1.38
Luminous Opening:	Rectangular (W 2' x L: 2' x H: 0')
CIE Type:	Direct
Input Watts (W):	18.4
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590723
CATALOG NUMBER: 22CGTX-20-L92765-W2A-4000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590723
CATALOG NUMBER: 22CGTX-20-L92765-W2A-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	45	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	35	33
8	60	46	38	32	58	45	37	32	44	37	31	43	36	31	42	36	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	39	31	26	38	30	26	37	30	25	36	30	25	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1827	1827	1827
5°	1823	1834	1823
10°	1826	1821	1829
15°	1816	1824	1819
20°	1810	1818	1812
25°	1795	1802	1799
30°	1778	1791	1788
35°	1770	1774	1767
40°	1746	1750	1757
45°	1729	1737	1737
50°	1710	1714	1705
55°	1681	1686	1686
60°	1636	1658	1653
65°	1589	1610	1603
70°	1520	1545	1570
75°	1434	1488	1510
80°	1344	1409	1441
85°	1192	1291	1321

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
Vertical Angle: 45°
Luminance: 1737 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590723
CATALOG NUMBER: 22CGTX-20-L92765-W2A-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.3	3.2
10°-20°	184.5	9.3
20°-30°	279.6	14.1
30°-40°	337.6	17.0
40°-50°	352.0	17.7
50°-60°	320.9	16.1
60°-70°	249.7	12.6
70°-80°	151.5	7.6
80°-90°	47.0	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	528.4	26.6
0°-40°	866.1	43.6
0°-60°	1539.0	77.4
0°-90°	1987.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1987.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	679	679	679	679	679	
5°	675	677	679	679	675	64
15°	652	654	655	654	653	184
25°	605	606	607	607	606	279
35°	539	540	540	541	538	336
45°	454	456	456	456	456	351
55°	358	358	359	360	359	320
65°	250	252	253	255	252	246
75°	138	143	143	145	145	147
85°	39	42	42	44	43	44
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590723
CATALOG NUMBER: 22CGTX-20-L92765-W2A-4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*678.9*	*678.9*	*678.9*	*678.9*	*678.9*
2.5°	*677.8*	677.8	677.8	677.8	676.8
5°	*674.7*	676.8	678.9	678.9	674.7
7.5°	*671.6*	673.7	673.7	672.6	673.7
10°	*668.4*	668.4	666.3	666.3	669.5
12.5°	*663.2*	662.2	662.2	662.2	660.1
15°	*651.7*	653.8	654.9	653.8	652.8
17.5°	*641.3*	644.4	645.5	644.4	644.4
20°	*631.9*	635.0	635.0	634.0	632.9
22.5°	*619.3*	620.4	621.4	620.4	622.5
25°	*604.7*	605.8	606.8	606.8	605.8
27.5°	*588.0*	592.2	592.2	593.2	589.1
30°	*572.3*	574.4	576.5	575.5	575.5
32.5°	*555.6*	558.8	558.8	559.8	558.8
35°	*538.9*	540.0	540.0	541.0	537.9
37.5°	*519.1*	520.1	520.1	521.2	518.0
40°	*497.1*	500.3	498.2	501.3	500.3
42.5°	*476.3*	479.4	478.3	481.5	478.3
45°	*454.3*	456.4	456.4	456.4	456.4
47.5°	*432.4*	432.4	434.5	434.5	432.4
50°	*408.4*	409.4	409.4	410.5	407.3
52.5°	*383.3*	384.3	385.4	384.3	383.3
55°	*358.2*	358.2	359.3	360.3	359.3
57.5°	*332.1*	332.1	333.2	334.2	334.2
60°	*303.9*	305.0	308.1	308.1	307.1
62.5°	*275.7*	279.9	279.9	282.0	283.0
65°	*249.6*	251.7	252.8	254.8	251.7
67.5°	*219.3*	222.5	225.6	226.6	226.6
70°	*193.2*	196.4	196.4	199.5	199.5
72.5°	*166.1*	169.2	170.2	172.3	172.3
75°	*137.9*	143.1	143.1	145.2	145.2
77.5°	*111.8*	115.9	115.9	119.1	119.1
80°	*86.7*	90.9	90.9	93.0	93.0
82.5°	*62.7*	65.8	65.8	67.9	66.8
85°	*38.6*	41.8	41.8	43.9	42.8
87.5°	*16.7*	19.8	18.8	19.8	19.8
90°	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590723
CATALOG NUMBER: 22CGTX-20-L92765-W2A-4000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.95	15.61	14.32	15.92	16.24	14.00	15.66	14.36	15.97	16.28
	3H	15.82	17.32	16.19	17.65	18.01	15.92	17.42	16.30	17.75	18.11
	4H	16.55	17.97	16.94	18.31	18.69	16.68	18.10	17.08	18.44	18.82
	6H	17.11	18.43	17.52	18.79	19.18	17.28	18.60	17.69	18.96	19.35
	8H	17.30	18.56	17.73	18.95	19.35	17.49	18.75	17.92	19.14	19.54
	12H	17.44	18.65	17.87	19.03	19.46	17.64	18.85	18.07	19.23	19.66
4H	2H	14.62	16.04	15.02	16.39	16.76	14.66	16.08	15.06	16.42	16.80
	3H	16.72	17.92	17.13	18.31	18.71	16.81	18.00	17.22	18.40	18.80
	4H	17.60	18.68	18.03	19.09	19.53	17.71	18.79	18.14	19.20	19.64
	6H	18.30	19.25	18.75	19.69	20.14	18.45	19.40	18.91	19.84	20.30
	8H	18.55	19.44	19.01	19.88	20.35	18.72	19.61	19.18	20.05	20.52
	12H	18.74	19.54	19.22	20.01	20.48	18.93	19.73	19.41	20.20	20.67
8H	4H	17.96	18.85	18.42	19.29	19.75	18.06	18.94	18.51	19.39	19.85
	6H	18.81	19.55	19.30	20.04	20.51	18.94	19.69	19.44	20.17	20.65
	8H	19.15	19.81	19.65	20.32	20.80	19.30	19.97	19.81	20.47	20.96
	12H	19.42	20.01	19.93	20.50	21.06	19.60	20.19	20.11	20.68	21.24
12H	4H	18.01	18.81	18.49	19.28	19.75	18.10	18.90	18.58	19.38	19.84
	6H	18.89	19.56	19.40	20.06	20.55	19.02	19.69	19.53	20.19	20.68
	8H	19.29	19.88	19.80	20.37	20.93	19.44	20.03	19.95	20.52	21.08

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-566-11-R2

Test Date: 10/14/2025

Luminaire Tested: 22CGTX-50-L92765-W2A-4000K

Data in this report applies to families of products including 22CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-566-11-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/29/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L92765-W2A-4000K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-566-11-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 50000 Lumen CGTX TUNABLE WHITE FROM 2700K TO 6500K -5 V

Spectral Parameters

CCT (K):	4246	CRI (Ra):	96.1		
CIE u':	0.2245	R1:	98.0	R9:	83.1
CIE v':	0.4902	R2:	98.1	R10:	94.7
Duv:	-0.0058	R3:	95.1	R11:	95.0
CIE x:	0.3671	R4:	97.2	R12:	76.2
CIE y:	0.3563	R5:	97.9	R13:	98.7
CIE z:	0.2766	R6:	93.8	R14:	96.3
Peak Wavelength (nm):	630	R7:	95.3	R15:	98.7
Dominant Wavelength (nm):	582	R8:	93.5		
Purity:	17.05535				
Rf:	91.3				
Rg:	101.8				




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2510-566-11-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4246K
CIE x = 0.3671
CIE y = 0.3563
Duv = -0.0058

Point lies outside the range

REPORT NUMBER: SP1-2510-566-11-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	162	NR	620	297	NR	750	7	NR	880	0	NR
365	0	NR	495	185	NR	625	301	NR	755	6	NR	885	0	NR
370	0	NR	500	211	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	232	NR	635	592	NR	765	4	NR	895	0	NR
380	0	NR	510	249	NR	640	190	NR	770	4	NR	900	0	NR
385	1	NR	515	262	NR	645	191	NR	775	3	NR	905	0	NR
390	1	NR	520	270	NR	650	160	NR	780	3	NR	910	0	NR
395	3	NR	525	273	NR	655	134	NR	785	2	NR	915	0	NR
400	4	NR	530	277	NR	660	114	NR	790	2	NR	920	0	NR
405	5	NR	535	280	NR	665	96	NR	795	2	NR	925	0	NR
410	7	NR	540	283	NR	670	88	NR	800	1	NR	930	0	NR
415	12	NR	545	285	NR	675	72	NR	805	1	NR	935	0	NR
420	21	NR	550	288	NR	680	62	NR	810	1	NR	940	0	NR
425	36	NR	555	292	NR	685	53	NR	815	1	NR	945	0	NR
430	64	NR	560	295	NR	690	46	NR	820	1	NR	950	0	NR
435	113	NR	565	298	NR	695	39	NR	825	1	NR	955	0	NR
440	196	NR	570	300	NR	700	33	NR	830	1	NR	960	0	NR
445	327	NR	575	302	NR	705	28	NR	835	1	NR	965	0	NR
450	462	NR	580	304	NR	710	24	NR	840	0	NR	970	0	NR
455	458	NR	585	306	NR	715	21	NR	845	0	NR	975	0	NR
460	327	NR	590	306	NR	720	17	NR	850	0	NR	980	0	NR
465	246	NR	595	302	NR	725	15	NR	855	0	NR	985	0	NR
470	197	NR	600	300	NR	730	13	NR	860	0	NR	990	0	NR
475	155	NR	605	299	NR	735	11	NR	865	0	NR	995	0	NR
480	138	NR	610	324	NR	740	9	NR	870	0	NR	1000	0	NR
485	144	NR	615	337	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-11-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.9**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	162	NR	620	297	NR	750	7	NR	880	0	NR
365	0	NR	495	185	NR	625	301	NR	755	6	NR	885	0	NR
370	0	NR	500	211	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	232	NR	635	592	NR	765	4	NR	895	0	NR
380	0	NR	510	249	NR	640	190	NR	770	4	NR	900	0	NR
385	1	NR	515	262	NR	645	191	NR	775	3	NR	905	0	NR
390	1	NR	520	270	NR	650	160	NR	780	3	NR	910	0	NR
395	3	NR	525	273	NR	655	134	NR	785	2	NR	915	0	NR
400	4	NR	530	277	NR	660	114	NR	790	2	NR	920	0	NR
405	5	NR	535	280	NR	665	96	NR	795	2	NR	925	0	NR
410	7	NR	540	283	NR	670	88	NR	800	1	NR	930	0	NR
415	12	NR	545	285	NR	675	72	NR	805	1	NR	935	0	NR
420	21	NR	550	288	NR	680	62	NR	810	1	NR	940	0	NR
425	36	NR	555	292	NR	685	53	NR	815	1	NR	945	0	NR
430	64	NR	560	295	NR	690	46	NR	820	1	NR	950	0	NR
435	113	NR	565	298	NR	695	39	NR	825	1	NR	955	0	NR
440	196	NR	570	300	NR	700	33	NR	830	1	NR	960	0	NR
445	327	NR	575	302	NR	705	28	NR	835	1	NR	965	0	NR
450	462	NR	580	304	NR	710	24	NR	840	0	NR	970	0	NR
455	458	NR	585	306	NR	715	21	NR	845	0	NR	975	0	NR
460	327	NR	590	306	NR	720	17	NR	850	0	NR	980	0	NR
465	246	NR	595	302	NR	725	15	NR	855	0	NR	985	0	NR
470	197	NR	600	300	NR	730	13	NR	860	0	NR	990	0	NR
475	155	NR	605	299	NR	735	11	NR	865	0	NR	995	0	NR
480	138	NR	610	324	NR	740	9	NR	870	0	NR	1000	0	NR
485	144	NR	615	337	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-11-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 4.06**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	162	NR	620	297	NR	750	7	NR	880	0	NR
365	0	NR	495	185	NR	625	301	NR	755	6	NR	885	0	NR
370	0	NR	500	211	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	232	NR	635	592	NR	765	4	NR	895	0	NR
380	0	NR	510	249	NR	640	190	NR	770	4	NR	900	0	NR
385	1	NR	515	262	NR	645	191	NR	775	3	NR	905	0	NR
390	1	NR	520	270	NR	650	160	NR	780	3	NR	910	0	NR
395	3	NR	525	273	NR	655	134	NR	785	2	NR	915	0	NR
400	4	NR	530	277	NR	660	114	NR	790	2	NR	920	0	NR
405	5	NR	535	280	NR	665	96	NR	795	2	NR	925	0	NR
410	7	NR	540	283	NR	670	88	NR	800	1	NR	930	0	NR
415	12	NR	545	285	NR	675	72	NR	805	1	NR	935	0	NR
420	21	NR	550	288	NR	680	62	NR	810	1	NR	940	0	NR
425	36	NR	555	292	NR	685	53	NR	815	1	NR	945	0	NR
430	64	NR	560	295	NR	690	46	NR	820	1	NR	950	0	NR
435	113	NR	565	298	NR	695	39	NR	825	1	NR	955	0	NR
440	196	NR	570	300	NR	700	33	NR	830	1	NR	960	0	NR
445	327	NR	575	302	NR	705	28	NR	835	1	NR	965	0	NR
450	462	NR	580	304	NR	710	24	NR	840	0	NR	970	0	NR
455	458	NR	585	306	NR	715	21	NR	845	0	NR	975	0	NR
460	327	NR	590	306	NR	720	17	NR	850	0	NR	980	0	NR
465	246	NR	595	302	NR	725	15	NR	855	0	NR	985	0	NR
470	197	NR	600	300	NR	730	13	NR	860	0	NR	990	0	NR
475	155	NR	605	299	NR	735	11	NR	865	0	NR	995	0	NR
480	138	NR	610	324	NR	740	9	NR	870	0	NR	1000	0	NR
485	144	NR	615	337	NR	745	8	NR	875	0	NR			


REPORT NUMBER: SP1-2510-566-11-R2

TM-30-18


Summary


R_f = 91.3
R_g = 101.8
CIE R_a = 96.1
R_9 = 83.1


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-566-11-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 92	CES51 = 98	CES76 = 84
CES02 = 62	CES27 = 92	CES52 = 97	CES77 = 87
CES03 = 31	CES28 = 95	CES53 = 97	CES78 = 81
CES04 = 69	CES29 = 95	CES54 = 93	CES79 = 94
CES05 = 49	CES30 = 93	CES55 = 92	CES80 = 92
CES06 = 50	CES31 = 95	CES56 = 96	CES81 = 83
CES07 = 42	CES32 = 86	CES57 = 95	CES82 = 96
CES08 = 41	CES33 = 98	CES58 = 95	CES83 = 96
CES09 = 29	CES34 = 91	CES59 = 98	CES84 = 93
CES10 = 74	CES35 = 94	CES60 = 92	CES85 = 82
CES11 = 57	CES36 = 80	CES61 = 92	CES86 = 87
CES12 = 63	CES37 = 92	CES62 = 86	CES87 = 91
CES13 = 43	CES38 = 88	CES63 = 93	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 87
CES15 = 71	CES40 = 97	CES65 = 90	CES90 = 97
CES16 = 47	CES41 = 97	CES66 = 88	CES91 = 72
CES17 = 49	CES42 = 89	CES67 = 86	CES92 = 80
CES18 = 56	CES43 = 90	CES68 = 87	CES93 = 88
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 80
CES20 = 66	CES45 = 94	CES70 = 85	CES95 = 84
CES21 = 85	CES46 = 96	CES71 = 79	CES96 = 93
CES22 = 78	CES47 = 93	CES72 = 93	CES97 = 95
CES23 = 91	CES48 = 94	CES73 = 79	CES98 = 97
CES24 = 90	CES49 = 94	CES74 = 91	CES99 = 96
CES25 = 71	CES50 = 98	CES75 = 81	





REPORT NUMBER: SP1-2510-566-11-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-566-11-R2

TM-30-18

Measure Comparisons





(END OF REPORT)