

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29478)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, FLUSH LENS, FLOOD
OPTIC, WHITE HOUSING.
Light Source: (1) 3500K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	1443.5 lumens	Max Intensity:	3880.8 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	71.8 lumens/watt		
Luminous Opening:	Circular (Dia: 0.25' x H: 0')		
Beam Angle (50%):	35.4°H x 35.4°V	Field Angle (10%):	58.1°H x 58.1°V
Beam Lumens:	864.7 lumens	Field Lumens:	1355.2 lumens
Beam Efficiency:	59.9%	Field Efficiency:	93.9%
Input Watts (W):	20.1		
Input Voltage (V):	120		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

Iso-Candela Plot






REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

Lumen Table

90	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	
50	0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.0	0.0
40		0.0	0.0	0.1	0.1	0.4	1.3	2.5	2.5	1.3	0.4	0.1	0.1	0.0	0.0
30	0.0	0.0	0.0	0.1	0.4	2.6	12.4	23.1	23.1	12.4	2.6	0.4	0.1	0.0	0.0
20		0.0	0.1	0.1	1.1	11.8	39.5	68.0	68.0	39.5	11.8	1.1	0.1	0.1	0.0
10	0.0	0.0	0.1	0.2	2.1	21.2	66.1	105.6	105.6	66.1	21.2	2.1	0.2	0.1	0.0
0		0.0	0.1	0.2	2.1	21.2	66.1	105.6	105.6	66.1	21.2	2.1	0.2	0.1	0.0
-10	0.0	0.0	0.1	0.1	1.1	11.8	39.5	68.0	68.0	39.5	11.8	1.1	0.1	0.1	0.0
-20		0.0	0.0	0.1	0.4	2.6	12.4	23.1	23.1	12.4	2.6	0.4	0.1	0.0	0.0
-30	0.0	0.0	0.0	0.1	0.1	0.4	1.3	2.5	2.5	1.3	0.4	0.1	0.1	0.0	0.0
-40		0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.0	0.0
-50	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0
-60		0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	
-70	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	
-80	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	
-90	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	


REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

Luminous Intensity Polar Plot



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

Luminous Intensity Plot



Beam:
 H Angle: 35.4°
 V Angle: 35.4°
 Lumens: 864.7
 Efficiency: 59.9%

Field:
 H Angle: 58.1°
 V Angle: 58.1°
 Lumens: 1355.2
 Efficiency: 93.9%

Spill:
 Lumens: 88.4
 Efficiency: 6.1%

— Vertical Distribution through 0-Deg
 - - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

FIELD
BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	1
56.25°	0	0	0	0	0	0	0	0	0	0	1
55°	0	0	0	0	0	0	0	0	0	0	1
53.75°	0	0	0	0	0	0	0	0	0	1	1
52.5°	0	0	0	0	0	0	0	0	0	1	1
51.25°	0	0	0	0	0	0	0	0	0	1	1
50°	0	0	0	0	0	0	0	0	0	1	1
48.75°	0	0	0	0	0	0	0	0	1	1	1
47.5°	0	0	0	0	0	0	0	0	1	1	1
46.25°	0	0	0	0	0	0	0	0	1	1	1
45°	0	0	0	0	0	0	0	0	1	1	1
43.75°	0	0	0	0	0	0	0	0	1	1	1
42.5°	0	0	0	0	0	0	0	0	1	1	1
41.25°	0	0	0	0	0	0	0	1	1	1	1
40°	0	0	0	0	0	0	0	1	1	1	1
38.75°	0	0	0	0	0	0	0	1	1	1	1
37.5°	0	0	0	0	0	0	0	1	1	1	1
36.25°	0	0	0	0	0	0	0	1	1	1	1
35°	0	0	0	0	0	0	0	1	1	1	1



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	1	1	1	1
32.5°	0	0	0	0	0	0	0	1	1	1	1
31.25°	0	0	0	0	0	0	0	1	1	1	1
30°	0	0	0	0	0	0	0	1	1	1	1
28.75°	0	0	0	0	0	0	1	1	1	1	1
27.5°	0	0	0	0	0	0	1	1	1	1	1
26.25°	0	0	0	0	0	0	1	1	1	1	1
25°	0	0	0	0	0	0	1	1	1	1	1
23.75°	0	0	0	0	0	0	1	1	1	1	1
22.5°	0	0	0	0	0	0	1	1	1	1	1
21.25°	0	0	0	0	0	0	1	1	1	1	1
20°	0	0	0	0	0	0	1	1	1	1	1
18.75°	0	0	0	0	0	0	1	1	1	1	1
17.5°	0	0	0	0	0	0	1	1	1	1	1
16.25°	0	0	0	0	0	0	1	1	1	1	1
15°	0	0	0	0	0	0	1	1	1	1	1
13.75°	0	0	0	0	0	0	1	1	1	1	1
12.5°	0	0	0	0	0	0	1	1	1	1	1
11.25°	0	0	0	0	0	0	1	1	1	1	1
10°	0	0	0	0	0	0	1	1	1	1	1
8.75°	0	0	0	0	0	0	1	1	1	1	1
7.5°	0	0	0	0	0	0	1	1	1	1	1
6.25°	0	0	0	0	0	0	1	1	1	1	1
5°	0	0	0	0	0	0	1	1	1	1	1
3.75°	0	0	0	0	0	0	1	1	1	1	1
2.5°	0	0	0	0	0	0	1	1	1	1	1
1.25°	0	0	0	0	0	0	1	1	1	1	1
0°	0	0	0	0	0	0	1	1	1	1	1
-1.25°	0	0	0	0	0	0	1	1	1	1	1
-2.5°	0	0	0	0	0	0	1	1	1	1	1
-3.75°	0	0	0	0	0	0	1	1	1	1	1
-5°	0	0	0	0	0	0	1	1	1	1	1
-6.25°	0	0	0	0	0	0	1	1	1	1	1
-7.5°	0	0	0	0	0	0	1	1	1	1	1
-8.75°	0	0	0	0	0	0	1	1	1	1	1
-10°	0	0	0	0	0	0	1	1	1	1	1
-11.25°	0	0	0	0	0	0	1	1	1	1	1
-12.5°	0	0	0	0	0	0	1	1	1	1	1
-13.75°	0	0	0	0	0	0	1	1	1	1	1
-15°	0	0	0	0	0	0	1	1	1	1	1
-16.25°	0	0	0	0	0	0	1	1	1	1	1
-17.5°	0	0	0	0	0	0	1	1	1	1	1
-18.75°	0	0	0	0	0	0	1	1	1	1	1
-20°	0	0	0	0	0	0	1	1	1	1	1
-21.25°	0	0	0	0	0	0	1	1	1	1	1



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	1	1	1	1	1
-23.75°	0	0	0	0	0	0	1	1	1	1	1
-25°	0	0	0	0	0	0	1	1	1	1	1
-26.25°	0	0	0	0	0	0	1	1	1	1	1
-27.5°	0	0	0	0	0	0	1	1	1	1	1
-28.75°	0	0	0	0	0	0	1	1	1	1	1
-30°	0	0	0	0	0	0	0	1	1	1	1
-31.25°	0	0	0	0	0	0	0	1	1	1	1
-32.5°	0	0	0	0	0	0	0	1	1	1	1
-33.75°	0	0	0	0	0	0	0	1	1	1	1
-35°	0	0	0	0	0	0	0	1	1	1	1
-36.25°	0	0	0	0	0	0	0	1	1	1	1
-37.5°	0	0	0	0	0	0	0	1	1	1	1
-38.75°	0	0	0	0	0	0	0	1	1	1	1
-40°	0	0	0	0	0	0	0	1	1	1	1
-41.25°	0	0	0	0	0	0	0	1	1	1	1
-42.5°	0	0	0	0	0	0	0	0	1	1	1
-43.75°	0	0	0	0	0	0	0	0	1	1	1
-45°	0	0	0	0	0	0	0	0	1	1	1
-46.25°	0	0	0	0	0	0	0	0	1	1	1
-47.5°	0	0	0	0	0	0	0	0	1	1	1
-48.75°	0	0	0	0	0	0	0	0	1	1	1
-50°	0	0	0	0	0	0	0	0	0	1	1
-51.25°	0	0	0	0	0	0	0	0	0	1	1
-52.5°	0	0	0	0	0	0	0	0	0	1	1
-53.75°	0	0	0	0	0	0	0	0	0	1	1
-55°	0	0	0	0	0	0	0	0	0	0	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	1
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	1
73.75°	0	0	0	0	0	0	0	0	0	1	1
72.5°	0	0	0	0	0	0	0	1	1	1	1
71.25°	0	0	0	0	0	0	1	1	1	1	1
70°	0	0	0	0	0	1	1	1	1	1	1
68.75°	0	0	0	0	1	1	1	1	1	1	1
67.5°	0	0	0	1	1	1	1	1	1	1	1
66.25°	0	0	0	1	1	1	1	1	1	1	1
65°	0	0	1	1	1	1	1	1	1	1	1
63.75°	0	1	1	1	1	1	1	1	1	1	1
62.5°	0	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	2
53.75°	1	1	1	1	1	1	1	1	1	1	2
52.5°	1	1	1	1	1	1	1	1	1	2	2
51.25°	1	1	1	1	1	1	1	1	1	2	2
50°	1	1	1	1	1	1	1	1	2	2	2
48.75°	1	1	1	1	1	1	1	1	2	2	2
47.5°	1	1	1	1	1	1	1	2	2	2	2
46.25°	1	1	1	1	1	1	1	2	2	2	2
45°	1	1	1	1	1	1	2	2	2	2	2
43.75°	1	1	1	1	1	1	2	2	2	2	2
42.5°	1	1	1	1	1	1	2	2	2	2	2
41.25°	1	1	1	1	1	2	2	2	2	2	2
40°	1	1	1	1	1	2	2	2	2	2	2
38.75°	1	1	1	1	1	2	2	2	2	2	2
37.5°	1	1	1	1	2	2	2	2	2	2	2
36.25°	1	1	1	1	2	2	2	2	2	2	2
35°	1	1	1	1	2	2	2	2	2	2	2



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	2	2	2	2	2	2	2
32.5°	1	1	1	2	2	2	2	2	2	2	2
31.25°	1	1	1	2	2	2	2	2	2	2	2
30°	1	1	1	2	2	2	2	2	2	2	2
28.75°	1	1	1	2	2	2	2	2	2	2	2
27.5°	1	1	1	2	2	2	2	2	2	2	2
26.25°	1	1	1	2	2	2	2	2	2	2	2
25°	1	1	2	2	2	2	2	2	2	2	2
23.75°	1	1	2	2	2	2	2	2	2	2	2
22.5°	1	1	2	2	2	2	2	2	2	2	2
21.25°	1	1	2	2	2	2	2	2	2	2	2
20°	1	1	2	2	2	2	2	2	2	2	2
18.75°	1	1	2	2	2	2	2	2	2	2	2
17.5°	1	1	2	2	2	2	2	2	2	2	2
16.25°	1	1	2	2	2	2	2	2	2	2	2
15°	1	1	2	2	2	2	2	2	2	2	2
13.75°	1	1	2	2	2	2	2	2	2	2	2
12.5°	1	1	2	2	2	2	2	2	2	2	2
11.25°	1	2	2	2	2	2	2	2	2	2	2
10°	1	2	2	2	2	2	2	2	2	2	2
8.75°	1	2	2	2	2	2	2	2	2	2	2
7.5°	1	2	2	2	2	2	2	2	2	2	2
6.25°	1	2	2	2	2	2	2	2	2	2	2
5°	1	2	2	2	2	2	2	2	2	2	2
3.75°	1	2	2	2	2	2	2	2	2	2	2
2.5°	1	2	2	2	2	2	2	2	2	2	2
1.25°	1	2	2	2	2	2	2	2	2	2	2
0°	1	2	2	2	2	2	2	2	2	2	2
-1.25°	1	2	2	2	2	2	2	2	2	2	2
-2.5°	1	2	2	2	2	2	2	2	2	2	2
-3.75°	1	2	2	2	2	2	2	2	2	2	2
-5°	1	2	2	2	2	2	2	2	2	2	2
-6.25°	1	2	2	2	2	2	2	2	2	2	2
-7.5°	1	2	2	2	2	2	2	2	2	2	2
-8.75°	1	2	2	2	2	2	2	2	2	2	2
-10°	1	2	2	2	2	2	2	2	2	2	2
-11.25°	1	2	2	2	2	2	2	2	2	2	2
-12.5°	1	1	2	2	2	2	2	2	2	2	2
-13.75°	1	1	2	2	2	2	2	2	2	2	2
-15°	1	1	2	2	2	2	2	2	2	2	2
-16.25°	1	1	2	2	2	2	2	2	2	2	2
-17.5°	1	1	2	2	2	2	2	2	2	2	2
-18.75°	1	1	2	2	2	2	2	2	2	2	2
-20°	1	1	2	2	2	2	2	2	2	2	2
-21.25°	1	1	2	2	2	2	2	2	2	2	2



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	2	2	2	2	2	2	2	2	2
-23.75°	1	1	2	2	2	2	2	2	2	2	2
-25°	1	1	2	2	2	2	2	2	2	2	2
-26.25°	1	1	1	2	2	2	2	2	2	2	2
-27.5°	1	1	1	2	2	2	2	2	2	2	2
-28.75°	1	1	1	2	2	2	2	2	2	2	2
-30°	1	1	1	2	2	2	2	2	2	2	2
-31.25°	1	1	1	2	2	2	2	2	2	2	2
-32.5°	1	1	1	2	2	2	2	2	2	2	2
-33.75°	1	1	1	1	2	2	2	2	2	2	2
-35°	1	1	1	1	2	2	2	2	2	2	2
-36.25°	1	1	1	1	2	2	2	2	2	2	2
-37.5°	1	1	1	1	2	2	2	2	2	2	2
-38.75°	1	1	1	1	1	2	2	2	2	2	2
-40°	1	1	1	1	1	2	2	2	2	2	2
-41.25°	1	1	1	1	1	2	2	2	2	2	2
-42.5°	1	1	1	1	1	1	2	2	2	2	2
-43.75°	1	1	1	1	1	1	2	2	2	2	2
-45°	1	1	1	1	1	1	2	2	2	2	2
-46.25°	1	1	1	1	1	1	1	2	2	2	2
-47.5°	1	1	1	1	1	1	1	2	2	2	2
-48.75°	1	1	1	1	1	1	1	1	2	2	2
-50°	1	1	1	1	1	1	1	1	2	2	2
-51.25°	1	1	1	1	1	1	1	1	1	2	2
-52.5°	1	1	1	1	1	1	1	1	1	2	2
-53.75°	1	1	1	1	1	1	1	1	1	1	2
-55°	1	1	1	1	1	1	1	1	1	1	2
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	0	1	1	1	1	1	1	1	1	1	1
-63.75°	0	1	1	1	1	1	1	1	1	1	1
-65°	0	0	1	1	1	1	1	1	1	1	1
-66.25°	0	0	0	1	1	1	1	1	1	1	1
-67.5°	0	0	0	1	1	1	1	1	1	1	1
-68.75°	0	0	0	0	1	1	1	1	1	1	1
-70°	0	0	0	0	0	1	1	1	1	1	1
-71.25°	0	0	0	0	0	0	1	1	1	1	1
-72.5°	0	0	0	0	0	0	0	1	1	1	1
-73.75°	0	0	0	0	0	0	0	0	0	1	1
-75°	0	0	0	0	0	0	0	0	0	0	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	1	1	1	1
77.5°	0	0	0	0	1	1	1	1	1	1	1
76.25°	0	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	2
65°	1	1	1	1	1	1	1	1	2	2	2
63.75°	1	1	1	1	1	1	2	2	2	2	2
62.5°	1	1	1	1	1	2	2	2	2	2	2
61.25°	1	1	1	1	2	2	2	2	2	2	2
60°	1	1	1	2	2	2	2	2	2	2	2
58.75°	1	1	2	2	2	2	2	2	2	2	2
57.5°	1	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	2
53.75°	2	2	2	2	2	2	2	2	2	2	2
52.5°	2	2	2	2	2	2	2	2	2	2	2
51.25°	2	2	2	2	2	2	2	2	2	2	2
50°	2	2	2	2	2	2	2	2	2	2	2
48.75°	2	2	2	2	2	2	2	2	2	2	2
47.5°	2	2	2	2	2	2	2	2	2	2	2
46.25°	2	2	2	2	2	2	2	2	2	2	2
45°	2	2	2	2	2	2	2	2	2	2	2
43.75°	2	2	2	2	2	2	2	2	2	2	2
42.5°	2	2	2	2	2	2	2	2	2	2	2
41.25°	2	2	2	2	2	2	2	2	2	2	2
40°	2	2	2	2	2	2	2	2	2	2	2
38.75°	2	2	2	2	2	2	2	2	2	2	2
37.5°	2	2	2	2	2	2	2	2	2	2	3
36.25°	2	2	2	2	2	2	2	2	2	3	3
35°	2	2	2	2	2	2	2	2	2	3	3



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	2	2	2	2	2	2	2	2	3	3	3
32.5°	2	2	2	2	2	2	2	2	3	3	3
31.25°	2	2	2	2	2	2	2	3	3	3	3
30°	2	2	2	2	2	2	2	3	3	3	3
28.75°	2	2	2	2	2	2	2	3	3	3	3
27.5°	2	2	2	2	2	2	3	3	3	3	3
26.25°	2	2	2	2	2	2	3	3	3	3	3
25°	2	2	2	2	2	2	3	3	3	3	3
23.75°	2	2	2	2	2	3	3	3	3	3	4
22.5°	2	2	2	2	2	3	3	3	3	3	4
21.25°	2	2	2	2	2	3	3	3	3	3	4
20°	2	2	2	2	3	3	3	3	3	4	4
18.75°	2	2	2	2	3	3	3	3	3	4	4
17.5°	2	2	2	2	3	3	3	3	3	4	4
16.25°	2	2	2	2	3	3	3	3	3	4	4
15°	2	2	2	2	3	3	3	3	4	4	4
13.75°	2	2	2	2	3	3	3	3	4	4	4
12.5°	2	2	2	3	3	3	3	3	4	4	4
11.25°	2	2	2	3	3	3	3	3	4	4	5
10°	2	2	2	3	3	3	3	3	4	4	5
8.75°	2	2	2	3	3	3	3	3	4	4	5
7.5°	2	2	2	3	3	3	3	3	4	4	5
6.25°	2	2	2	3	3	3	3	4	4	4	5
5°	2	2	2	3	3	3	3	4	4	4	5
3.75°	2	2	2	3	3	3	3	4	4	4	5
2.5°	2	2	2	3	3	3	3	4	4	4	5
1.25°	2	2	2	3	3	3	3	4	4	4	5
0°	2	2	2	3	3	3	3	4	4	4	5
-1.25°	2	2	2	3	3	3	3	4	4	4	5
-2.5°	2	2	2	3	3	3	3	4	4	4	5
-3.75°	2	2	2	3	3	3	3	4	4	4	5
-5°	2	2	2	3	3	3	3	4	4	4	5
-6.25°	2	2	2	3	3	3	3	4	4	4	5
-7.5°	2	2	2	3	3	3	3	3	4	4	5
-8.75°	2	2	2	3	3	3	3	3	4	4	5
-10°	2	2	2	3	3	3	3	3	4	4	5
-11.25°	2	2	2	3	3	3	3	3	4	4	5
-12.5°	2	2	2	3	3	3	3	3	4	4	4
-13.75°	2	2	2	2	3	3	3	3	4	4	4
-15°	2	2	2	2	3	3	3	3	4	4	4
-16.25°	2	2	2	2	3	3	3	3	3	4	4
-17.5°	2	2	2	2	3	3	3	3	3	4	4
-18.75°	2	2	2	2	3	3	3	3	3	4	4
-20°	2	2	2	2	3	3	3	3	3	4	4
-21.25°	2	2	2	2	2	3	3	3	3	3	4



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	2	2	2	2	3	3	3	3	3	4
-23.75°	2	2	2	2	2	3	3	3	3	3	4
-25°	2	2	2	2	2	2	3	3	3	3	3
-26.25°	2	2	2	2	2	2	3	3	3	3	3
-27.5°	2	2	2	2	2	2	3	3	3	3	3
-28.75°	2	2	2	2	2	2	2	3	3	3	3
-30°	2	2	2	2	2	2	2	3	3	3	3
-31.25°	2	2	2	2	2	2	2	3	3	3	3
-32.5°	2	2	2	2	2	2	2	2	3	3	3
-33.75°	2	2	2	2	2	2	2	2	3	3	3
-35°	2	2	2	2	2	2	2	2	2	3	3
-36.25°	2	2	2	2	2	2	2	2	2	3	3
-37.5°	2	2	2	2	2	2	2	2	2	2	3
-38.75°	2	2	2	2	2	2	2	2	2	2	2
-40°	2	2	2	2	2	2	2	2	2	2	2
-41.25°	2	2	2	2	2	2	2	2	2	2	2
-42.5°	2	2	2	2	2	2	2	2	2	2	2
-43.75°	2	2	2	2	2	2	2	2	2	2	2
-45°	2	2	2	2	2	2	2	2	2	2	2
-46.25°	2	2	2	2	2	2	2	2	2	2	2
-47.5°	2	2	2	2	2	2	2	2	2	2	2
-48.75°	2	2	2	2	2	2	2	2	2	2	2
-50°	2	2	2	2	2	2	2	2	2	2	2
-51.25°	2	2	2	2	2	2	2	2	2	2	2
-52.5°	2	2	2	2	2	2	2	2	2	2	2
-53.75°	2	2	2	2	2	2	2	2	2	2	2
-55°	2	2	2	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	1	2	2	2	2	2	2	2	2	2	2
-58.75°	1	1	2	2	2	2	2	2	2	2	2
-60°	1	1	1	2	2	2	2	2	2	2	2
-61.25°	1	1	1	1	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	2	2	2	2	2
-65°	1	1	1	1	1	1	1	1	2	2	2
-66.25°	1	1	1	1	1	1	1	1	1	1	2
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	1	1	1	1	1	1	1



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	1	1	1	1
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	1	1	1	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	2	2
70°	1	1	1	1	1	1	2	2	2	2	2
68.75°	1	1	1	2	2	2	2	2	2	2	2
67.5°	1	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	2
53.75°	2	2	2	2	2	2	2	2	2	2	2
52.5°	2	2	2	2	2	2	2	2	2	2	2
51.25°	2	2	2	2	2	2	2	2	2	2	3
50°	2	2	2	2	2	2	2	2	2	3	3
48.75°	2	2	2	2	2	2	2	3	3	3	3
47.5°	2	2	2	2	2	2	3	3	3	3	3
46.25°	2	2	2	2	2	3	3	3	3	3	3
45°	2	2	2	2	3	3	3	3	3	3	3
43.75°	2	2	2	3	3	3	3	3	3	3	3
42.5°	2	2	3	3	3	3	3	3	3	3	4
41.25°	2	3	3	3	3	3	3	3	3	4	4
40°	3	3	3	3	3	3	3	3	4	4	4
38.75°	3	3	3	3	3	3	3	4	4	4	4
37.5°	3	3	3	3	3	3	4	4	4	4	5
36.25°	3	3	3	3	3	4	4	4	4	5	5
35°	3	3	3	3	4	4	4	4	5	5	5



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	3	3	3	4	4	4	4	5	5	5	5
32.5°	3	3	3	4	4	4	5	5	5	5	5
31.25°	3	3	4	4	4	5	5	5	5	5	6
30°	3	3	4	4	4	5	5	5	5	5	6
28.75°	3	4	4	4	5	5	5	5	5	6	6
27.5°	3	4	4	4	5	5	5	5	6	6	7
26.25°	4	4	4	5	5	5	5	5	6	7	7
25°	4	4	4	5	5	5	5	6	6	7	8
23.75°	4	4	5	5	5	5	5	6	7	8	9
22.5°	4	4	5	5	5	5	6	7	7	8	12
21.25°	4	4	5	5	5	5	6	7	8	9	15
20°	4	5	5	5	5	6	6	7	8	12	18
18.75°	4	5	5	5	5	6	7	7	9	15	21
17.5°	4	5	5	5	6	6	7	8	11	17	23
16.25°	5	5	5	5	6	7	7	8	13	20	26
15°	5	5	5	5	6	7	8	9	16	22	29
13.75°	5	5	5	5	6	7	8	11	18	24	31
12.5°	5	5	5	6	6	7	8	13	20	27	34
11.25°	5	5	5	6	7	7	8	15	21	29	36
10°	5	5	5	6	7	7	10	16	23	30	38
8.75°	5	5	5	6	7	8	11	17	24	32	40
7.5°	5	5	5	6	7	8	12	19	26	33	43
6.25°	5	5	5	6	7	8	13	20	27	34	44
5°	5	5	6	6	7	8	14	20	28	35	46
3.75°	5	5	6	6	7	8	14	21	29	36	47
2.5°	5	5	6	6	7	8	15	21	29	37	48
1.25°	5	5	6	6	7	8	15	22	29	37	48
0°	5	5	6	7	7	8	15	22	30	37	49
-1.25°	5	5	6	6	7	8	15	22	29	37	48
-2.5°	5	5	6	6	7	8	15	21	29	37	48
-3.75°	5	5	6	6	7	8	14	21	29	36	47
-5°	5	5	6	6	7	8	14	20	28	35	46
-6.25°	5	5	5	6	7	8	13	20	27	34	44
-7.5°	5	5	5	6	7	8	12	19	26	33	43
-8.75°	5	5	5	6	7	8	11	17	24	32	40
-10°	5	5	5	6	7	7	10	16	23	30	38
-11.25°	5	5	5	6	7	7	8	15	21	29	36
-12.5°	5	5	5	6	6	7	8	13	20	27	34
-13.75°	5	5	5	5	6	7	8	11	18	24	31
-15°	5	5	5	5	6	7	8	9	16	22	29
-16.25°	5	5	5	5	6	7	7	8	13	20	26
-17.5°	4	5	5	5	6	6	7	8	11	17	23
-18.75°	4	5	5	5	5	6	7	7	9	15	21
-20°	4	5	5	5	5	6	6	7	8	12	18
-21.25°	4	4	5	5	5	5	6	7	8	9	15



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	4	4	5	5	5	5	6	7	7	8	12
-23.75°	4	4	5	5	5	5	5	6	7	8	9
-25°	4	4	4	5	5	5	5	6	6	7	8
-26.25°	4	4	4	5	5	5	5	5	6	7	7
-27.5°	3	4	4	4	5	5	5	5	6	6	7
-28.75°	3	4	4	4	5	5	5	5	5	6	6
-30°	3	3	4	4	4	5	5	5	5	5	6
-31.25°	3	3	4	4	4	5	5	5	5	5	6
-32.5°	3	3	3	4	4	4	5	5	5	5	5
-33.75°	3	3	3	4	4	4	4	5	5	5	5
-35°	3	3	3	3	4	4	4	4	5	5	5
-36.25°	3	3	3	3	3	4	4	4	4	5	5
-37.5°	3	3	3	3	3	3	4	4	4	4	5
-38.75°	3	3	3	3	3	3	3	4	4	4	4
-40°	3	3	3	3	3	3	3	3	4	4	4
-41.25°	2	3	3	3	3	3	3	3	3	4	4
-42.5°	2	2	3	3	3	3	3	3	3	3	4
-43.75°	2	2	2	3	3	3	3	3	3	3	3
-45°	2	2	2	2	3	3	3	3	3	3	3
-46.25°	2	2	2	2	2	3	3	3	3	3	3
-47.5°	2	2	2	2	2	2	3	3	3	3	3
-48.75°	2	2	2	2	2	2	2	3	3	3	3
-50°	2	2	2	2	2	2	2	2	2	3	3
-51.25°	2	2	2	2	2	2	2	2	2	2	3
-52.5°	2	2	2	2	2	2	2	2	2	2	2
-53.75°	2	2	2	2	2	2	2	2	2	2	2
-55°	2	2	2	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	1	2	2	2	2	2	2	2	2	2	2
-68.75°	1	1	1	2	2	2	2	2	2	2	2
-70°	1	1	1	1	1	1	2	2	2	2	2
-71.25°	1	1	1	1	1	1	1	1	1	2	2
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	0	0	0	0	0	0	1	1	1	1	1
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	1	1	1	1	1	1
81.25°	1	1	1	1	1	1	1	1	1	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	2	2	2
72.5°	1	1	2	2	2	2	2	2	2	2	2
71.25°	2	2	2	2	2	2	2	2	2	2	2
70°	2	2	2	2	2	2	2	2	2	2	2
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	3	3
55°	2	2	2	2	2	2	3	3	3	3	3
53.75°	2	2	2	3	3	3	3	3	3	3	3
52.5°	2	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	4	4
48.75°	3	3	3	3	3	3	3	4	4	4	4
47.5°	3	3	3	3	3	4	4	4	4	4	4
46.25°	3	3	3	4	4	4	4	4	4	5	5
45°	3	4	4	4	4	4	4	5	5	5	5
43.75°	4	4	4	4	4	5	5	5	5	5	5
42.5°	4	4	4	5	5	5	5	5	5	5	5
41.25°	4	4	5	5	5	5	5	5	5	5	6
40°	4	5	5	5	5	5	5	5	6	6	7
38.75°	5	5	5	5	5	5	6	6	6	7	7
37.5°	5	5	5	5	5	6	6	7	7	8	8
36.25°	5	5	5	6	6	6	7	7	8	9	12
35°	5	5	6	6	7	7	8	8	10	14	17



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	5	6	6	7	7	8	8	12	16	19	23
32.5°	6	6	7	7	8	9	13	17	21	25	29
31.25°	6	7	7	8	10	14	18	22	27	31	35
30°	7	7	8	10	14	19	23	28	32	37	43
28.75°	7	8	9	14	19	23	28	33	38	45	52
27.5°	8	8	13	18	23	28	33	39	46	53	61
26.25°	8	12	17	22	28	33	39	47	54	64	82
25°	10	16	21	27	32	38	46	54	65	84	103
23.75°	14	19	25	31	37	45	53	64	84	104	135
22.5°	17	23	29	35	43	52	61	82	103	135	196
21.25°	21	27	33	40	49	58	78	100	128	192	255
20°	24	30	37	46	55	71	94	116	181	248	318
18.75°	27	34	42	51	62	86	109	163	232	303	393
17.5°	30	37	47	56	76	100	137	210	282	372	468
16.25°	33	41	51	64	89	114	181	255	340	440	542
15°	36	46	56	75	101	144	221	298	400	506	614
13.75°	39	50	60	86	113	181	259	352	459	570	683
12.5°	43	53	70	97	134	215	295	402	515	630	749
11.25°	46	57	79	106	164	246	338	450	567	687	810
10°	49	60	87	114	191	274	378	495	616	740	868
8.75°	51	66	94	130	215	300	415	535	660	789	920
7.5°	54	72	100	150	236	330	448	571	699	831	965
6.25°	55	77	106	167	254	356	476	602	733	868	1004
5°	57	81	110	181	268	377	499	628	762	899	1036
3.75°	58	85	114	192	280	393	518	649	784	923	1065
2.5°	59	87	116	200	288	406	532	664	800	941	1086
1.25°	60	88	118	205	293	413	540	673	810	951	1099
0°	60	89	118	207	295	415	543	676	813	954	1103
-1.25°	60	88	118	205	293	413	540	673	810	951	1099
-2.5°	59	87	116	200	288	406	532	664	800	941	1086
-3.75°	58	85	114	192	280	393	518	649	784	923	1065
-5°	57	81	110	181	268	377	499	628	762	899	1036
-6.25°	55	77	106	167	254	356	476	602	733	868	1004
-7.5°	54	72	100	150	236	330	448	571	699	831	965
-8.75°	51	66	94	130	215	300	415	535	660	789	920
-10°	49	60	87	114	191	274	378	495	616	740	868
-11.25°	46	57	79	106	164	246	338	450	567	687	810
-12.5°	43	53	70	97	134	215	295	402	515	630	749
-13.75°	39	50	60	86	113	181	259	352	459	570	683
-15°	36	46	56	75	101	144	221	298	400	506	614
-16.25°	33	41	51	64	89	114	181	255	340	440	542
-17.5°	30	37	47	56	76	100	137	210	282	372	468
-18.75°	27	34	42	51	62	86	109	163	232	303	393
-20°	24	30	37	46	55	71	94	116	181	248	318
-21.25°	21	27	33	40	49	58	78	100	128	192	255



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	17	23	29	35	43	52	61	82	103	135	196
-23.75°	14	19	25	31	37	45	53	64	84	104	135
-25°	10	16	21	27	32	38	46	54	65	84	103
-26.25°	8	12	17	22	28	33	39	47	54	64	82
-27.5°	8	8	13	18	23	28	33	39	46	53	61
-28.75°	7	8	9	14	19	23	28	33	38	45	52
-30°	7	7	8	10	14	19	23	28	32	37	43
-31.25°	6	7	7	8	10	14	18	22	27	31	35
-32.5°	6	6	7	7	8	9	13	17	21	25	29
-33.75°	5	6	6	7	7	8	8	12	16	19	23
-35°	5	5	6	6	7	7	8	8	10	14	17
-36.25°	5	5	5	6	6	6	7	7	8	9	12
-37.5°	5	5	5	5	5	6	6	7	7	8	8
-38.75°	5	5	5	5	5	5	6	6	6	7	7
-40°	4	5	5	5	5	5	5	5	6	6	7
-41.25°	4	4	5	5	5	5	5	5	5	5	6
-42.5°	4	4	4	5	5	5	5	5	5	5	5
-43.75°	4	4	4	4	4	5	5	5	5	5	5
-45°	3	4	4	4	4	4	4	5	5	5	5
-46.25°	3	3	3	4	4	4	4	4	4	5	5
-47.5°	3	3	3	3	3	4	4	4	4	4	4
-48.75°	3	3	3	3	3	3	3	4	4	4	4
-50°	3	3	3	3	3	3	3	3	3	4	4
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	2	3	3	3	3	3	3	3	3	3	3
-53.75°	2	2	2	3	3	3	3	3	3	3	3
-55°	2	2	2	2	2	2	3	3	3	3	3
-56.25°	2	2	2	2	2	2	2	2	2	3	3
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	2	2	2	2	2	2	2	2	2	2	2
-71.25°	2	2	2	2	2	2	2	2	2	2	2
-72.5°	1	1	2	2	2	2	2	2	2	2	2
-73.75°	1	1	1	1	1	1	1	1	2	2	2
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	1	1	1	1	1	1	1	1	1	1	1
-82.5°	0	0	0	0	0	1	1	1	1	1	1
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	1	1	1	1	1	1	1	1	1	1	1
81.25°	1	1	1	1	1	1	1	1	1	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	2	2	2
73.75°	2	2	2	2	2	2	2	2	2	2	2
72.5°	2	2	2	2	2	2	2	2	2	2	2
71.25°	2	2	2	2	2	2	2	2	2	2	2
70°	2	2	2	2	2	2	2	2	2	2	2
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	3	3	3	3
57.5°	2	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	4	4	4	4	4	4
51.25°	3	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	5	5	5
48.75°	4	4	4	4	5	5	5	5	5	5	5
47.5°	4	5	5	5	5	5	5	5	5	5	5
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	5	5	5	5	5	5	5	6	6	6	6
43.75°	5	5	5	6	6	6	6	6	7	7	7
42.5°	5	6	6	6	7	7	7	7	7	7	8
41.25°	6	6	7	7	7	8	8	8	8	10	11
40°	7	7	7	8	8	9	11	13	15	16	17
38.75°	8	8	9	11	13	16	18	20	21	23	24
37.5°	9	12	15	17	20	22	24	27	29	30	32
36.25°	15	18	21	23	26	29	31	34	36	38	40
35°	21	24	27	30	33	36	39	43	46	49	51



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	27	30	34	37	41	46	50	53	57	60	66
32.5°	33	37	42	47	51	56	60	70	79	87	94
31.25°	40	46	51	56	64	75	86	97	106	114	130
30°	49	55	62	76	89	101	113	134	164	191	215
28.75°	58	71	86	100	114	144	181	215	246	274	300
27.5°	78	94	109	137	181	221	259	295	338	378	415
26.25°	100	116	163	210	255	298	352	402	450	495	535
25°	128	181	232	282	340	400	459	515	567	616	660
23.75°	192	248	303	372	440	506	570	630	687	740	789
22.5°	255	318	393	468	542	614	683	749	810	868	920
21.25°	324	404	486	567	646	724	798	869	935	995	1051
20°	404	492	579	666	751	834	914	988	1060	1133	1205
18.75°	486	579	673	765	856	944	1027	1115	1205	1296	1387
17.5°	567	666	765	864	959	1052	1152	1261	1372	1482	1588
16.25°	646	751	856	959	1061	1172	1296	1426	1556	1681	1799
15°	724	834	944	1052	1172	1308	1453	1602	1746	1883	2015
13.75°	798	914	1027	1152	1296	1453	1617	1779	1937	2089	2227
12.5°	869	988	1115	1261	1426	1602	1779	1956	2127	2285	2427
11.25°	935	1060	1205	1372	1556	1746	1937	2127	2304	2468	2609
10°	995	1133	1296	1482	1681	1883	2089	2285	2468	2628	2775
8.75°	1051	1205	1387	1588	1799	2015	2227	2427	2609	2775	2924
7.5°	1106	1275	1470	1684	1905	2132	2349	2550	2734	2904	3057
6.25°	1154	1336	1546	1770	2001	2233	2454	2655	2844	3015	3173
5°	1198	1393	1611	1842	2082	2317	2538	2742	2932	3109	3269
3.75°	1235	1437	1663	1899	2145	2383	2604	2812	3003	3182	3341
2.5°	1262	1469	1700	1942	2190	2431	2652	2861	3055	3235	3394
1.25°	1278	1489	1723	1968	2218	2460	2681	2890	3086	3268	3425
0°	1283	1495	1731	1977	2227	2469	2690	2900	3097	3279	3435
-1.25°	1278	1489	1723	1968	2218	2460	2681	2890	3086	3268	3425
-2.5°	1262	1469	1700	1942	2190	2431	2652	2861	3055	3235	3394
-3.75°	1235	1437	1663	1899	2145	2383	2604	2812	3003	3182	3341
-5°	1198	1393	1611	1842	2082	2317	2538	2742	2932	3109	3269
-6.25°	1154	1336	1546	1770	2001	2233	2454	2655	2844	3015	3173
-7.5°	1106	1275	1470	1684	1905	2132	2349	2550	2734	2904	3057
-8.75°	1051	1205	1387	1588	1799	2015	2227	2427	2609	2775	2924
-10°	995	1133	1296	1482	1681	1883	2089	2285	2468	2628	2775
-11.25°	935	1060	1205	1372	1556	1746	1937	2127	2304	2468	2609
-12.5°	869	988	1115	1261	1426	1602	1779	1956	2127	2285	2427
-13.75°	798	914	1027	1152	1296	1453	1617	1779	1937	2089	2227
-15°	724	834	944	1052	1172	1308	1453	1602	1746	1883	2015
-16.25°	646	751	856	959	1061	1172	1296	1426	1556	1681	1799
-17.5°	567	666	765	864	959	1052	1152	1261	1372	1482	1588
-18.75°	486	579	673	765	856	944	1027	1115	1205	1296	1387
-20°	404	492	579	666	751	834	914	988	1060	1133	1205
-21.25°	324	404	486	567	646	724	798	869	935	995	1051



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	255	318	393	468	542	614	683	749	810	868	920
-23.75°	192	248	303	372	440	506	570	630	687	740	789
-25°	128	181	232	282	340	400	459	515	567	616	660
-26.25°	100	116	163	210	255	298	352	402	450	495	535
-27.5°	78	94	109	137	181	221	259	295	338	378	415
-28.75°	58	71	86	100	114	144	181	215	246	274	300
-30°	49	55	62	76	89	101	113	134	164	191	215
-31.25°	40	46	51	56	64	75	86	97	106	114	130
-32.5°	33	37	42	47	51	56	60	70	79	87	94
-33.75°	27	30	34	37	41	46	50	53	57	60	66
-35°	21	24	27	30	33	36	39	43	46	49	51
-36.25°	15	18	21	23	26	29	31	34	36	38	40
-37.5°	9	12	15	17	20	22	24	27	29	30	32
-38.75°	8	8	9	11	13	16	18	20	21	23	24
-40°	7	7	7	8	8	9	11	13	15	16	17
-41.25°	6	6	7	7	7	8	8	8	8	10	11
-42.5°	5	6	6	6	7	7	7	7	7	7	8
-43.75°	5	5	5	6	6	6	6	6	7	7	7
-45°	5	5	5	5	5	5	5	6	6	6	6
-46.25°	5	5	5	5	5	5	5	5	5	5	5
-47.5°	4	5	5	5	5	5	5	5	5	5	5
-48.75°	4	4	4	4	5	5	5	5	5	5	5
-50°	4	4	4	4	4	4	4	4	5	5	5
-51.25°	3	4	4	4	4	4	4	4	4	4	4
-52.5°	3	3	3	3	3	4	4	4	4	4	4
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	2	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	3	3	3	3
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	2	2	2	2	2	2	2	2	2	2	2
-71.25°	2	2	2	2	2	2	2	2	2	2	2
-72.5°	2	2	2	2	2	2	2	2	2	2	2
-73.75°	2	2	2	2	2	2	2	2	2	2	2
-75°	1	1	1	1	1	1	1	1	2	2	2
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	1	1	1	1	1	1	1	1	1	1	1
-82.5°	1	1	1	1	1	1	1	1	1	1	1
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	1	1	1	1	1	1	1	1	1	1	1
81.25°	1	1	1	1	1	1	1	1	1	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	2	2	2	2	2	2	2	2	2	2	2
73.75°	2	2	2	2	2	2	2	2	2	2	2
72.5°	2	2	2	2	2	2	2	2	2	2	2
71.25°	2	2	2	2	2	2	2	2	2	2	2
70°	2	2	2	2	2	2	2	2	2	2	2
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	3	3	3	3	3	3	3	3	3	3	3
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	4	4	4	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	5	5	5	5	5	5	5	5	5	5	5
48.75°	5	5	5	5	5	5	5	5	5	5	5
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	5	5	6	6	6	6	6	6	6	6	6
45°	6	6	6	6	6	6	7	6	6	6	6
43.75°	7	7	7	7	7	7	7	7	7	7	7
42.5°	8	8	8	8	8	8	8	8	8	8	8
41.25°	12	13	14	14	15	15	15	15	15	14	14
40°	19	20	20	21	21	22	22	22	21	21	20
38.75°	26	27	28	29	29	29	30	29	29	29	28
37.5°	33	34	35	36	37	37	37	37	37	36	35
36.25°	43	44	46	47	48	48	49	48	48	47	46
35°	54	55	57	58	59	60	60	60	59	58	57



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	72	77	81	85	87	88	89	88	87	85	81
32.5°	100	106	110	114	116	118	118	118	116	114	110
31.25°	150	167	181	192	200	205	207	205	200	192	181
30°	236	254	268	280	288	293	295	293	288	280	268
28.75°	330	356	377	393	406	413	415	413	406	393	377
27.5°	448	476	499	518	532	540	543	540	532	518	499
26.25°	571	602	628	649	664	673	676	673	664	649	628
25°	699	733	762	784	800	810	813	810	800	784	762
23.75°	831	868	899	923	941	951	954	951	941	923	899
22.5°	965	1004	1036	1065	1086	1099	1103	1099	1086	1065	1036
21.25°	1106	1154	1198	1235	1262	1278	1283	1278	1262	1235	1198
20°	1275	1336	1393	1437	1469	1489	1495	1489	1469	1437	1393
18.75°	1470	1546	1611	1663	1700	1723	1731	1723	1700	1663	1611
17.5°	1684	1770	1842	1899	1942	1968	1977	1968	1942	1899	1842
16.25°	1905	2001	2082	2145	2190	2218	2227	2218	2190	2145	2082
15°	2132	2233	2317	2383	2431	2460	2469	2460	2431	2383	2317
13.75°	2349	2454	2538	2604	2652	2681	2690	2681	2652	2604	2538
12.5°	2550	2655	2742	2812	2861	2890	2900	2890	2861	2812	2742
11.25°	2734	2844	2932	3003	3055	3086	3097	3086	3055	3003	2932
10°	2904	3015	3109	3182	3235	3268	3279	3268	3235	3182	3109
8.75°	3057	3173	3269	3341	3394	3425	3435	3425	3394	3341	3269
7.5°	3194	3310	3406	3478	3532	3562	3572	3562	3532	3478	3406
6.25°	3310	3426	3523	3593	3642	3669	3679	3669	3642	3593	3523
5°	3406	3523	3615	3679	3720	3743	3752	3743	3720	3679	3615
3.75°	3478	3593	3679	3735	3771	3793	3799	3793	3771	3735	3679
2.5°	3532	3642	3720	3771	3805	3826	3833	3826	3805	3771	3720
1.25°	3562	3669	3743	3793	3826	3850	3861	3850	3826	3793	3743
0°	3572	3679	3752	3799	3833	3861	3881	3861	3833	3799	3752
-1.25°	3562	3669	3743	3793	3826	3850	3861	3850	3826	3793	3743
-2.5°	3532	3642	3720	3771	3805	3826	3833	3826	3805	3771	3720
-3.75°	3478	3593	3679	3735	3771	3793	3799	3793	3771	3735	3679
-5°	3406	3523	3615	3679	3720	3743	3752	3743	3720	3679	3615
-6.25°	3310	3426	3523	3593	3642	3669	3679	3669	3642	3593	3523
-7.5°	3194	3310	3406	3478	3532	3562	3572	3562	3532	3478	3406
-8.75°	3057	3173	3269	3341	3394	3425	3435	3425	3394	3341	3269
-10°	2904	3015	3109	3182	3235	3268	3279	3268	3235	3182	3109
-11.25°	2734	2844	2932	3003	3055	3086	3097	3086	3055	3003	2932
-12.5°	2550	2655	2742	2812	2861	2890	2900	2890	2861	2812	2742
-13.75°	2349	2454	2538	2604	2652	2681	2690	2681	2652	2604	2538
-15°	2132	2233	2317	2383	2431	2460	2469	2460	2431	2383	2317
-16.25°	1905	2001	2082	2145	2190	2218	2227	2218	2190	2145	2082
-17.5°	1684	1770	1842	1899	1942	1968	1977	1968	1942	1899	1842
-18.75°	1470	1546	1611	1663	1700	1723	1731	1723	1700	1663	1611
-20°	1275	1336	1393	1437	1469	1489	1495	1489	1469	1437	1393
-21.25°	1106	1154	1198	1235	1262	1278	1283	1278	1262	1235	1198



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	965	1004	1036	1065	1086	1099	1103	1099	1086	1065	1036
-23.75°	831	868	899	923	941	951	954	951	941	923	899
-25°	699	733	762	784	800	810	813	810	800	784	762
-26.25°	571	602	628	649	664	673	676	673	664	649	628
-27.5°	448	476	499	518	532	540	543	540	532	518	499
-28.75°	330	356	377	393	406	413	415	413	406	393	377
-30°	236	254	268	280	288	293	295	293	288	280	268
-31.25°	150	167	181	192	200	205	207	205	200	192	181
-32.5°	100	106	110	114	116	118	118	118	116	114	110
-33.75°	72	77	81	85	87	88	89	88	87	85	81
-35°	54	55	57	58	59	60	60	60	59	58	57
-36.25°	43	44	46	47	48	48	49	48	48	47	46
-37.5°	33	34	35	36	37	37	37	37	37	36	35
-38.75°	26	27	28	29	29	29	30	29	29	29	28
-40°	19	20	20	21	21	22	22	22	21	21	20
-41.25°	12	13	14	14	15	15	15	15	15	14	14
-42.5°	8	8	8	8	8	8	8	8	8	8	8
-43.75°	7	7	7	7	7	7	7	7	7	7	7
-45°	6	6	6	6	6	6	7	6	6	6	6
-46.25°	5	5	6	6	6	6	6	6	6	6	6
-47.5°	5	5	5	5	5	5	5	5	5	5	5
-48.75°	5	5	5	5	5	5	5	5	5	5	5
-50°	5	5	5	5	5	5	5	5	5	5	5
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	3	4	4	4	4	4	4	4	4	4	4
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	3
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	2	2	2	2	2	2	2	2	2	2	2
-71.25°	2	2	2	2	2	2	2	2	2	2	2
-72.5°	2	2	2	2	2	2	2	2	2	2	2
-73.75°	2	2	2	2	2	2	2	2	2	2	2
-75°	2	2	2	2	2	2	2	2	2	2	2
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	1	1	1	1	1	1	1	1	1	1	1
-82.5°	1	1	1	1	1	1	1	1	1	1	1
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	1	1	1	1	1	1	1	1	1	1	1
81.25°	1	1	1	1	1	1	1	1	1	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	2	2	2	2	2	1	1	1	1	1	1
73.75°	2	2	2	2	2	2	2	2	2	2	2
72.5°	2	2	2	2	2	2	2	2	2	2	2
71.25°	2	2	2	2	2	2	2	2	2	2	2
70°	2	2	2	2	2	2	2	2	2	2	2
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	3	3	3	3	3	3	2	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	4	3	3	3	3	3	3	3	3	3	3
52.5°	4	4	4	4	4	4	4	4	3	3	3
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	5	5	5	5	5	4	4	4	4	4	4
48.75°	5	5	5	5	5	5	5	5	5	4	4
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	6	6	6	6	6	6	5	5	5	5	5
43.75°	7	7	7	7	7	6	6	6	6	6	5
42.5°	8	8	8	7	7	7	7	7	7	6	6
41.25°	13	12	11	10	8	8	8	8	7	7	7
40°	20	19	17	16	15	13	11	9	8	8	7
38.75°	27	26	24	23	21	20	18	16	13	11	9
37.5°	34	33	32	30	29	27	24	22	20	17	15
36.25°	44	43	40	38	36	34	31	29	26	23	21
35°	55	54	51	49	46	43	39	36	33	30	27



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	77	72	66	60	57	53	50	46	41	37	34
32.5°	106	100	94	87	79	70	60	56	51	47	42
31.25°	167	150	130	114	106	97	86	75	64	56	51
30°	254	236	215	191	164	134	113	101	89	76	62
28.75°	356	330	300	274	246	215	181	144	114	100	86
27.5°	476	448	415	378	338	295	259	221	181	137	109
26.25°	602	571	535	495	450	402	352	298	255	210	163
25°	733	699	660	616	567	515	459	400	340	282	232
23.75°	868	831	789	740	687	630	570	506	440	372	303
22.5°	1004	965	920	868	810	749	683	614	542	468	393
21.25°	1154	1106	1051	995	935	869	798	724	646	567	486
20°	1336	1275	1205	1133	1060	988	914	834	751	666	579
18.75°	1546	1470	1387	1296	1205	1115	1027	944	856	765	673
17.5°	1770	1684	1588	1482	1372	1261	1152	1052	959	864	765
16.25°	2001	1905	1799	1681	1556	1426	1296	1172	1061	959	856
15°	2233	2132	2015	1883	1746	1602	1453	1308	1172	1052	944
13.75°	2454	2349	2227	2089	1937	1779	1617	1453	1296	1152	1027
12.5°	2655	2550	2427	2285	2127	1956	1779	1602	1426	1261	1115
11.25°	2844	2734	2609	2468	2304	2127	1937	1746	1556	1372	1205
10°	3015	2904	2775	2628	2468	2285	2089	1883	1681	1482	1296
8.75°	3173	3057	2924	2775	2609	2427	2227	2015	1799	1588	1387
7.5°	3310	3194	3057	2904	2734	2550	2349	2132	1905	1684	1470
6.25°	3426	3310	3173	3015	2844	2655	2454	2233	2001	1770	1546
5°	3523	3406	3269	3109	2932	2742	2538	2317	2082	1842	1611
3.75°	3593	3478	3341	3182	3003	2812	2604	2383	2145	1899	1663
2.5°	3642	3532	3394	3235	3055	2861	2652	2431	2190	1942	1700
1.25°	3669	3562	3425	3268	3086	2890	2681	2460	2218	1968	1723
0°	3679	3572	3435	3279	3097	2900	2690	2469	2227	1977	1731
-1.25°	3669	3562	3425	3268	3086	2890	2681	2460	2218	1968	1723
-2.5°	3642	3532	3394	3235	3055	2861	2652	2431	2190	1942	1700
-3.75°	3593	3478	3341	3182	3003	2812	2604	2383	2145	1899	1663
-5°	3523	3406	3269	3109	2932	2742	2538	2317	2082	1842	1611
-6.25°	3426	3310	3173	3015	2844	2655	2454	2233	2001	1770	1546
-7.5°	3310	3194	3057	2904	2734	2550	2349	2132	1905	1684	1470
-8.75°	3173	3057	2924	2775	2609	2427	2227	2015	1799	1588	1387
-10°	3015	2904	2775	2628	2468	2285	2089	1883	1681	1482	1296
-11.25°	2844	2734	2609	2468	2304	2127	1937	1746	1556	1372	1205
-12.5°	2655	2550	2427	2285	2127	1956	1779	1602	1426	1261	1115
-13.75°	2454	2349	2227	2089	1937	1779	1617	1453	1296	1152	1027
-15°	2233	2132	2015	1883	1746	1602	1453	1308	1172	1052	944
-16.25°	2001	1905	1799	1681	1556	1426	1296	1172	1061	959	856
-17.5°	1770	1684	1588	1482	1372	1261	1152	1052	959	864	765
-18.75°	1546	1470	1387	1296	1205	1115	1027	944	856	765	673
-20°	1336	1275	1205	1133	1060	988	914	834	751	666	579
-21.25°	1154	1106	1051	995	935	869	798	724	646	567	486



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	1004	965	920	868	810	749	683	614	542	468	393
-23.75°	868	831	789	740	687	630	570	506	440	372	303
-25°	733	699	660	616	567	515	459	400	340	282	232
-26.25°	602	571	535	495	450	402	352	298	255	210	163
-27.5°	476	448	415	378	338	295	259	221	181	137	109
-28.75°	356	330	300	274	246	215	181	144	114	100	86
-30°	254	236	215	191	164	134	113	101	89	76	62
-31.25°	167	150	130	114	106	97	86	75	64	56	51
-32.5°	106	100	94	87	79	70	60	56	51	47	42
-33.75°	77	72	66	60	57	53	50	46	41	37	34
-35°	55	54	51	49	46	43	39	36	33	30	27
-36.25°	44	43	40	38	36	34	31	29	26	23	21
-37.5°	34	33	32	30	29	27	24	22	20	17	15
-38.75°	27	26	24	23	21	20	18	16	13	11	9
-40°	20	19	17	16	15	13	11	9	8	8	7
-41.25°	13	12	11	10	8	8	8	8	7	7	7
-42.5°	8	8	8	7	7	7	7	7	7	6	6
-43.75°	7	7	7	7	7	6	6	6	6	6	5
-45°	6	6	6	6	6	6	5	5	5	5	5
-46.25°	5	5	5	5	5	5	5	5	5	5	5
-47.5°	5	5	5	5	5	5	5	5	5	5	5
-48.75°	5	5	5	5	5	5	5	5	5	4	4
-50°	5	5	5	5	5	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	3	3	3
-53.75°	4	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	3	3	3	3	3	3	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	2	2	2	2	2	2	2	2	2	2	2
-71.25°	2	2	2	2	2	2	2	2	2	2	2
-72.5°	2	2	2	2	2	2	2	2	2	2	2
-73.75°	2	2	2	2	2	2	2	2	2	2	2
-75°	2	2	2	2	2	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	1	1	1	1	1	1	1	1	1	1	1
-82.5°	1	1	1	1	1	1	1	1	1	1	1
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	1	1	1	1	1	1	1	1	0	0	0
81.25°	1	1	1	1	1	1	1	1	1	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	2	2	2	2	2	1	1	1	1	1	1
72.5°	2	2	2	2	2	2	2	2	2	2	2
71.25°	2	2	2	2	2	2	2	2	2	2	2
70°	2	2	2	2	2	2	2	2	2	2	2
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	2	2	2	2	2	2	2	2	2	2
56.25°	3	3	3	3	2	2	2	2	2	2	2
55°	3	3	3	3	3	3	3	2	2	2	2
53.75°	3	3	3	3	3	3	3	3	3	3	2
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	4	3	3	3	3	3	3	3	3	3	3
50°	4	4	4	4	3	3	3	3	3	3	3
48.75°	4	4	4	4	4	4	3	3	3	3	3
47.5°	5	4	4	4	4	4	4	4	3	3	3
46.25°	5	5	5	5	4	4	4	4	4	4	3
45°	5	5	5	5	5	5	4	4	4	4	4
43.75°	5	5	5	5	5	5	5	5	4	4	4
42.5°	6	5	5	5	5	5	5	5	5	5	4
41.25°	6	6	6	5	5	5	5	5	5	5	5
40°	7	7	7	6	6	5	5	5	5	5	5
38.75°	8	8	7	7	6	6	6	5	5	5	5
37.5°	12	9	8	8	7	7	6	6	5	5	5
36.25°	18	15	12	9	8	7	7	6	6	6	5
35°	24	21	17	14	10	8	8	7	7	6	6



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	30	27	23	19	16	12	8	8	7	7	6
32.5°	37	33	29	25	21	17	13	9	8	7	7
31.25°	46	40	35	31	27	22	18	14	10	8	7
30°	55	49	43	37	32	28	23	19	14	10	8
28.75°	71	58	52	45	38	33	28	23	19	14	9
27.5°	94	78	61	53	46	39	33	28	23	18	13
26.25°	116	100	82	64	54	47	39	33	28	22	17
25°	181	128	103	84	65	54	46	38	32	27	21
23.75°	248	192	135	104	84	64	53	45	37	31	25
22.5°	318	255	196	135	103	82	61	52	43	35	29
21.25°	404	324	255	192	128	100	78	58	49	40	33
20°	492	404	318	248	181	116	94	71	55	46	37
18.75°	579	486	393	303	232	163	109	86	62	51	42
17.5°	666	567	468	372	282	210	137	100	76	56	47
16.25°	751	646	542	440	340	255	181	114	89	64	51
15°	834	724	614	506	400	298	221	144	101	75	56
13.75°	914	798	683	570	459	352	259	181	113	86	60
12.5°	988	869	749	630	515	402	295	215	134	97	70
11.25°	1060	935	810	687	567	450	338	246	164	106	79
10°	1133	995	868	740	616	495	378	274	191	114	87
8.75°	1205	1051	920	789	660	535	415	300	215	130	94
7.5°	1275	1106	965	831	699	571	448	330	236	150	100
6.25°	1336	1154	1004	868	733	602	476	356	254	167	106
5°	1393	1198	1036	899	762	628	499	377	268	181	110
3.75°	1437	1235	1065	923	784	649	518	393	280	192	114
2.5°	1469	1262	1086	941	800	664	532	406	288	200	116
1.25°	1489	1278	1099	951	810	673	540	413	293	205	118
0°	1495	1283	1103	954	813	676	543	415	295	207	118
-1.25°	1489	1278	1099	951	810	673	540	413	293	205	118
-2.5°	1469	1262	1086	941	800	664	532	406	288	200	116
-3.75°	1437	1235	1065	923	784	649	518	393	280	192	114
-5°	1393	1198	1036	899	762	628	499	377	268	181	110
-6.25°	1336	1154	1004	868	733	602	476	356	254	167	106
-7.5°	1275	1106	965	831	699	571	448	330	236	150	100
-8.75°	1205	1051	920	789	660	535	415	300	215	130	94
-10°	1133	995	868	740	616	495	378	274	191	114	87
-11.25°	1060	935	810	687	567	450	338	246	164	106	79
-12.5°	988	869	749	630	515	402	295	215	134	97	70
-13.75°	914	798	683	570	459	352	259	181	113	86	60
-15°	834	724	614	506	400	298	221	144	101	75	56
-16.25°	751	646	542	440	340	255	181	114	89	64	51
-17.5°	666	567	468	372	282	210	137	100	76	56	47
-18.75°	579	486	393	303	232	163	109	86	62	51	42
-20°	492	404	318	248	181	116	94	71	55	46	37
-21.25°	404	324	255	192	128	100	78	58	49	40	33



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	318	255	196	135	103	82	61	52	43	35	29
-23.75°	248	192	135	104	84	64	53	45	37	31	25
-25°	181	128	103	84	65	54	46	38	32	27	21
-26.25°	116	100	82	64	54	47	39	33	28	22	17
-27.5°	94	78	61	53	46	39	33	28	23	18	13
-28.75°	71	58	52	45	38	33	28	23	19	14	9
-30°	55	49	43	37	32	28	23	19	14	10	8
-31.25°	46	40	35	31	27	22	18	14	10	8	7
-32.5°	37	33	29	25	21	17	13	9	8	7	7
-33.75°	30	27	23	19	16	12	8	8	7	7	6
-35°	24	21	17	14	10	8	8	7	7	6	6
-36.25°	18	15	12	9	8	7	7	6	6	6	5
-37.5°	12	9	8	8	7	7	6	6	5	5	5
-38.75°	8	8	7	7	6	6	6	5	5	5	5
-40°	7	7	7	6	6	5	5	5	5	5	5
-41.25°	6	6	6	5	5	5	5	5	5	5	5
-42.5°	6	5	5	5	5	5	5	5	5	5	4
-43.75°	5	5	5	5	5	5	5	5	4	4	4
-45°	5	5	5	5	5	5	4	4	4	4	4
-46.25°	5	5	5	5	4	4	4	4	4	4	3
-47.5°	5	4	4	4	4	4	4	4	3	3	3
-48.75°	4	4	4	4	4	4	3	3	3	3	3
-50°	4	4	4	4	3	3	3	3	3	3	3
-51.25°	4	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	2
-55°	3	3	3	3	3	3	3	2	2	2	2
-56.25°	3	3	3	3	2	2	2	2	2	2	2
-57.5°	3	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	2	2	2	2	2	2	2	2	2	2	2
-71.25°	2	2	2	2	2	2	2	2	2	2	2
-72.5°	2	2	2	2	2	2	2	2	2	2	2
-73.75°	2	2	2	2	2	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	1	1	1	1	1	1	1	1	1	1	1
-82.5°	1	1	1	1	1	1	1	1	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	1	1	1	1	1	1	1	0	0	0	0
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	2	2	2	2	1	1	1	1	1	1	1
70°	2	2	2	2	2	2	2	1	1	1	1
68.75°	2	2	2	2	2	2	2	2	2	2	1
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	2
53.75°	2	2	2	2	2	2	2	2	2	2	2
52.5°	3	2	2	2	2	2	2	2	2	2	2
51.25°	3	3	3	2	2	2	2	2	2	2	2
50°	3	3	3	3	2	2	2	2	2	2	2
48.75°	3	3	3	3	3	3	2	2	2	2	2
47.5°	3	3	3	3	3	3	3	2	2	2	2
46.25°	3	3	3	3	3	3	3	3	2	2	2
45°	4	3	3	3	3	3	3	3	3	2	2
43.75°	4	4	3	3	3	3	3	3	3	3	2
42.5°	4	4	4	3	3	3	3	3	3	3	3
41.25°	4	4	4	4	3	3	3	3	3	3	3
40°	5	4	4	4	4	3	3	3	3	3	3
38.75°	5	5	4	4	4	4	3	3	3	3	3
37.5°	5	5	5	4	4	4	4	3	3	3	3
36.25°	5	5	5	5	4	4	4	4	3	3	3
35°	5	5	5	5	5	4	4	4	4	3	3



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	6	5	5	5	5	5	4	4	4	4	3
32.5°	6	6	5	5	5	5	5	4	4	4	3
31.25°	7	6	6	5	5	5	5	5	4	4	4
30°	7	7	6	5	5	5	5	5	4	4	4
28.75°	8	7	6	6	5	5	5	5	5	4	4
27.5°	8	8	7	6	6	5	5	5	5	4	4
26.25°	12	8	7	7	6	5	5	5	5	5	4
25°	16	10	8	7	6	6	5	5	5	5	4
23.75°	19	14	9	8	7	6	5	5	5	5	5
22.5°	23	17	12	8	7	7	6	5	5	5	5
21.25°	27	21	15	9	8	7	6	5	5	5	5
20°	30	24	18	12	8	7	6	6	5	5	5
18.75°	34	27	21	15	9	7	7	6	5	5	5
17.5°	37	30	23	17	11	8	7	6	6	5	5
16.25°	41	33	26	20	13	8	7	7	6	5	5
15°	46	36	29	22	16	9	8	7	6	5	5
13.75°	50	39	31	24	18	11	8	7	6	5	5
12.5°	53	43	34	27	20	13	8	7	6	6	5
11.25°	57	46	36	29	21	15	8	7	7	6	5
10°	60	49	38	30	23	16	10	7	7	6	5
8.75°	66	51	40	32	24	17	11	8	7	6	5
7.5°	72	54	43	33	26	19	12	8	7	6	5
6.25°	77	55	44	34	27	20	13	8	7	6	5
5°	81	57	46	35	28	20	14	8	7	6	6
3.75°	85	58	47	36	29	21	14	8	7	6	6
2.5°	87	59	48	37	29	21	15	8	7	6	6
1.25°	88	60	48	37	29	22	15	8	7	6	6
0°	89	60	49	37	30	22	15	8	7	6	6
-1.25°	88	60	48	37	29	22	15	8	7	6	6
-2.5°	87	59	48	37	29	21	15	8	7	6	6
-3.75°	85	58	47	36	29	21	14	8	7	6	6
-5°	81	57	46	35	28	20	14	8	7	6	6
-6.25°	77	55	44	34	27	20	13	8	7	6	5
-7.5°	72	54	43	33	26	19	12	8	7	6	5
-8.75°	66	51	40	32	24	17	11	8	7	6	5
-10°	60	49	38	30	23	16	10	7	7	6	5
-11.25°	57	46	36	29	21	15	8	7	7	6	5
-12.5°	53	43	34	27	20	13	8	7	6	6	5
-13.75°	50	39	31	24	18	11	8	7	6	5	5
-15°	46	36	29	22	16	9	8	7	6	5	5
-16.25°	41	33	26	20	13	8	7	7	6	5	5
-17.5°	37	30	23	17	11	8	7	6	6	5	5
-18.75°	34	27	21	15	9	7	7	6	5	5	5
-20°	30	24	18	12	8	7	6	6	5	5	5
-21.25°	27	21	15	9	8	7	6	5	5	5	5



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	23	17	12	8	7	7	6	5	5	5	5
-23.75°	19	14	9	8	7	6	5	5	5	5	5
-25°	16	10	8	7	6	6	5	5	5	5	4
-26.25°	12	8	7	7	6	5	5	5	5	5	4
-27.5°	8	8	7	6	6	5	5	5	5	4	4
-28.75°	8	7	6	6	5	5	5	5	5	4	4
-30°	7	7	6	5	5	5	5	5	4	4	4
-31.25°	7	6	6	5	5	5	5	5	4	4	4
-32.5°	6	6	5	5	5	5	5	4	4	4	3
-33.75°	6	5	5	5	5	5	4	4	4	4	3
-35°	5	5	5	5	5	4	4	4	4	3	3
-36.25°	5	5	5	5	4	4	4	4	3	3	3
-37.5°	5	5	5	4	4	4	4	3	3	3	3
-38.75°	5	5	4	4	4	4	3	3	3	3	3
-40°	5	4	4	4	4	3	3	3	3	3	3
-41.25°	4	4	4	4	3	3	3	3	3	3	3
-42.5°	4	4	4	3	3	3	3	3	3	3	3
-43.75°	4	4	3	3	3	3	3	3	3	3	2
-45°	4	3	3	3	3	3	3	3	3	2	2
-46.25°	3	3	3	3	3	3	3	3	2	2	2
-47.5°	3	3	3	3	3	3	3	2	2	2	2
-48.75°	3	3	3	3	3	3	2	2	2	2	2
-50°	3	3	3	3	2	2	2	2	2	2	2
-51.25°	3	3	3	2	2	2	2	2	2	2	2
-52.5°	3	2	2	2	2	2	2	2	2	2	2
-53.75°	2	2	2	2	2	2	2	2	2	2	2
-55°	2	2	2	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	1
-70°	2	2	2	2	2	2	2	1	1	1	1
-71.25°	2	2	2	2	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	1	1	1	1	1	1	1	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	1	1	0	0	0	0	0	0	0	0	0
78.75°	1	1	1	1	1	1	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	2	1	1	1	1	1	1	1	1	1	1
66.25°	2	2	2	1	1	1	1	1	1	1	1
65°	2	2	2	2	2	1	1	1	1	1	1
63.75°	2	2	2	2	2	2	2	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	1	1	1
61.25°	2	2	2	2	2	2	2	2	2	1	1
60°	2	2	2	2	2	2	2	2	2	2	1
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	2
53.75°	2	2	2	2	2	2	2	2	2	2	2
52.5°	2	2	2	2	2	2	2	2	2	2	2
51.25°	2	2	2	2	2	2	2	2	2	2	2
50°	2	2	2	2	2	2	2	2	2	2	2
48.75°	2	2	2	2	2	2	2	2	2	2	2
47.5°	2	2	2	2	2	2	2	2	2	2	2
46.25°	2	2	2	2	2	2	2	2	2	2	2
45°	2	2	2	2	2	2	2	2	2	2	2
43.75°	2	2	2	2	2	2	2	2	2	2	2
42.5°	2	2	2	2	2	2	2	2	2	2	2
41.25°	3	2	2	2	2	2	2	2	2	2	2
40°	3	3	2	2	2	2	2	2	2	2	2
38.75°	3	3	2	2	2	2	2	2	2	2	2
37.5°	3	3	3	2	2	2	2	2	2	2	2
36.25°	3	3	3	3	2	2	2	2	2	2	2
35°	3	3	3	3	2	2	2	2	2	2	2



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	3	3	3	3	3	2	2	2	2	2	2
32.5°	3	3	3	3	3	2	2	2	2	2	2
31.25°	3	3	3	3	3	3	2	2	2	2	2
30°	3	3	3	3	3	3	2	2	2	2	2
28.75°	4	3	3	3	3	3	2	2	2	2	2
27.5°	4	3	3	3	3	3	3	2	2	2	2
26.25°	4	4	3	3	3	3	3	2	2	2	2
25°	4	4	3	3	3	3	3	2	2	2	2
23.75°	4	4	4	3	3	3	3	3	2	2	2
22.5°	4	4	4	3	3	3	3	3	2	2	2
21.25°	4	4	4	3	3	3	3	3	2	2	2
20°	5	4	4	4	3	3	3	3	3	2	2
18.75°	5	4	4	4	3	3	3	3	3	2	2
17.5°	5	4	4	4	3	3	3	3	3	2	2
16.25°	5	5	4	4	3	3	3	3	3	2	2
15°	5	5	4	4	4	3	3	3	3	2	2
13.75°	5	5	4	4	4	3	3	3	3	2	2
12.5°	5	5	4	4	4	3	3	3	3	3	2
11.25°	5	5	5	4	4	3	3	3	3	3	2
10°	5	5	5	4	4	3	3	3	3	3	2
8.75°	5	5	5	4	4	3	3	3	3	3	2
7.5°	5	5	5	4	4	3	3	3	3	3	2
6.25°	5	5	5	4	4	4	3	3	3	3	2
5°	5	5	5	4	4	4	3	3	3	3	2
3.75°	5	5	5	4	4	4	3	3	3	3	2
2.5°	5	5	5	4	4	4	3	3	3	3	2
1.25°	5	5	5	4	4	4	3	3	3	3	2
0°	5	5	5	4	4	4	3	3	3	3	2
-1.25°	5	5	5	4	4	4	3	3	3	3	2
-2.5°	5	5	5	4	4	4	3	3	3	3	2
-3.75°	5	5	5	4	4	4	3	3	3	3	2
-5°	5	5	5	4	4	4	3	3	3	3	2
-6.25°	5	5	5	4	4	4	3	3	3	3	2
-7.5°	5	5	5	4	4	3	3	3	3	3	2
-8.75°	5	5	5	4	4	3	3	3	3	3	2
-10°	5	5	5	4	4	3	3	3	3	3	2
-11.25°	5	5	5	4	4	3	3	3	3	3	2
-12.5°	5	5	4	4	4	3	3	3	3	3	2
-13.75°	5	5	4	4	4	3	3	3	3	2	2
-15°	5	5	4	4	4	3	3	3	3	2	2
-16.25°	5	5	4	4	3	3	3	3	3	2	2
-17.5°	5	4	4	4	3	3	3	3	3	2	2
-18.75°	5	4	4	4	3	3	3	3	3	2	2
-20°	5	4	4	4	3	3	3	3	3	2	2
-21.25°	4	4	4	3	3	3	3	3	2	2	2



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	4	4	4	3	3	3	3	3	2	2	2
-23.75°	4	4	4	3	3	3	3	3	2	2	2
-25°	4	4	3	3	3	3	3	2	2	2	2
-26.25°	4	4	3	3	3	3	3	2	2	2	2
-27.5°	4	3	3	3	3	3	3	2	2	2	2
-28.75°	4	3	3	3	3	3	2	2	2	2	2
-30°	3	3	3	3	3	3	2	2	2	2	2
-31.25°	3	3	3	3	3	3	2	2	2	2	2
-32.5°	3	3	3	3	3	2	2	2	2	2	2
-33.75°	3	3	3	3	3	2	2	2	2	2	2
-35°	3	3	3	3	2	2	2	2	2	2	2
-36.25°	3	3	3	3	2	2	2	2	2	2	2
-37.5°	3	3	3	2	2	2	2	2	2	2	2
-38.75°	3	3	2	2	2	2	2	2	2	2	2
-40°	3	3	2	2	2	2	2	2	2	2	2
-41.25°	3	2	2	2	2	2	2	2	2	2	2
-42.5°	2	2	2	2	2	2	2	2	2	2	2
-43.75°	2	2	2	2	2	2	2	2	2	2	2
-45°	2	2	2	2	2	2	2	2	2	2	2
-46.25°	2	2	2	2	2	2	2	2	2	2	2
-47.5°	2	2	2	2	2	2	2	2	2	2	2
-48.75°	2	2	2	2	2	2	2	2	2	2	2
-50°	2	2	2	2	2	2	2	2	2	2	2
-51.25°	2	2	2	2	2	2	2	2	2	2	2
-52.5°	2	2	2	2	2	2	2	2	2	2	2
-53.75°	2	2	2	2	2	2	2	2	2	2	2
-55°	2	2	2	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	1
-61.25°	2	2	2	2	2	2	2	2	2	1	1
-62.5°	2	2	2	2	2	2	2	2	1	1	1
-63.75°	2	2	2	2	2	2	2	1	1	1	1
-65°	2	2	2	2	2	1	1	1	1	1	1
-66.25°	2	2	2	1	1	1	1	1	1	1	1
-67.5°	2	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	1	1	1	1	1	1	0	0	0	0	0
-80°	1	1	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	0	0	0	0	0	0	0	0
73.75°	1	1	1	1	0	0	0	0	0	0	0
72.5°	1	1	1	1	1	1	0	0	0	0	0
71.25°	1	1	1	1	1	1	1	0	0	0	0
70°	1	1	1	1	1	1	1	1	0	0	0
68.75°	1	1	1	1	1	1	1	1	1	0	0
67.5°	1	1	1	1	1	1	1	1	1	1	0
66.25°	1	1	1	1	1	1	1	1	1	1	0
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	1	1	1	1	1	1	1	1	1
55°	2	2	2	1	1	1	1	1	1	1	1
53.75°	2	2	2	1	1	1	1	1	1	1	1
52.5°	2	2	2	2	1	1	1	1	1	1	1
51.25°	2	2	2	2	1	1	1	1	1	1	1
50°	2	2	2	2	2	1	1	1	1	1	1
48.75°	2	2	2	2	2	1	1	1	1	1	1
47.5°	2	2	2	2	2	2	1	1	1	1	1
46.25°	2	2	2	2	2	2	1	1	1	1	1
45°	2	2	2	2	2	2	2	1	1	1	1
43.75°	2	2	2	2	2	2	2	1	1	1	1
42.5°	2	2	2	2	2	2	2	1	1	1	1
41.25°	2	2	2	2	2	2	2	2	1	1	1
40°	2	2	2	2	2	2	2	2	1	1	1
38.75°	2	2	2	2	2	2	2	2	1	1	1
37.5°	2	2	2	2	2	2	2	2	2	1	1
36.25°	2	2	2	2	2	2	2	2	2	1	1
35°	2	2	2	2	2	2	2	2	2	1	1



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	2	2	2	2	2	2	2	2	2	1	1
32.5°	2	2	2	2	2	2	2	2	2	2	1
31.25°	2	2	2	2	2	2	2	2	2	2	1
30°	2	2	2	2	2	2	2	2	2	2	1
28.75°	2	2	2	2	2	2	2	2	2	2	1
27.5°	2	2	2	2	2	2	2	2	2	2	1
26.25°	2	2	2	2	2	2	2	2	2	2	1
25°	2	2	2	2	2	2	2	2	2	2	2
23.75°	2	2	2	2	2	2	2	2	2	2	2
22.5°	2	2	2	2	2	2	2	2	2	2	2
21.25°	2	2	2	2	2	2	2	2	2	2	2
20°	2	2	2	2	2	2	2	2	2	2	2
18.75°	2	2	2	2	2	2	2	2	2	2	2
17.5°	2	2	2	2	2	2	2	2	2	2	2
16.25°	2	2	2	2	2	2	2	2	2	2	2
15°	2	2	2	2	2	2	2	2	2	2	2
13.75°	2	2	2	2	2	2	2	2	2	2	2
12.5°	2	2	2	2	2	2	2	2	2	2	2
11.25°	2	2	2	2	2	2	2	2	2	2	2
10°	2	2	2	2	2	2	2	2	2	2	2
8.75°	2	2	2	2	2	2	2	2	2	2	2
7.5°	2	2	2	2	2	2	2	2	2	2	2
6.25°	2	2	2	2	2	2	2	2	2	2	2
5°	2	2	2	2	2	2	2	2	2	2	2
3.75°	2	2	2	2	2	2	2	2	2	2	2
2.5°	2	2	2	2	2	2	2	2	2	2	2
1.25°	2	2	2	2	2	2	2	2	2	2	2
0°	2	2	2	2	2	2	2	2	2	2	2
-1.25°	2	2	2	2	2	2	2	2	2	2	2
-2.5°	2	2	2	2	2	2	2	2	2	2	2
-3.75°	2	2	2	2	2	2	2	2	2	2	2
-5°	2	2	2	2	2	2	2	2	2	2	2
-6.25°	2	2	2	2	2	2	2	2	2	2	2
-7.5°	2	2	2	2	2	2	2	2	2	2	2
-8.75°	2	2	2	2	2	2	2	2	2	2	2
-10°	2	2	2	2	2	2	2	2	2	2	2
-11.25°	2	2	2	2	2	2	2	2	2	2	2
-12.5°	2	2	2	2	2	2	2	2	2	2	2
-13.75°	2	2	2	2	2	2	2	2	2	2	2
-15°	2	2	2	2	2	2	2	2	2	2	2
-16.25°	2	2	2	2	2	2	2	2	2	2	2
-17.5°	2	2	2	2	2	2	2	2	2	2	2
-18.75°	2	2	2	2	2	2	2	2	2	2	2
-20°	2	2	2	2	2	2	2	2	2	2	2
-21.25°	2	2	2	2	2	2	2	2	2	2	2



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	2	2	2	2	2	2	2	2	2	2
-23.75°	2	2	2	2	2	2	2	2	2	2	2
-25°	2	2	2	2	2	2	2	2	2	2	2
-26.25°	2	2	2	2	2	2	2	2	2	2	1
-27.5°	2	2	2	2	2	2	2	2	2	2	1
-28.75°	2	2	2	2	2	2	2	2	2	2	1
-30°	2	2	2	2	2	2	2	2	2	2	1
-31.25°	2	2	2	2	2	2	2	2	2	2	1
-32.5°	2	2	2	2	2	2	2	2	2	2	1
-33.75°	2	2	2	2	2	2	2	2	2	1	1
-35°	2	2	2	2	2	2	2	2	2	1	1
-36.25°	2	2	2	2	2	2	2	2	2	1	1
-37.5°	2	2	2	2	2	2	2	2	2	1	1
-38.75°	2	2	2	2	2	2	2	2	1	1	1
-40°	2	2	2	2	2	2	2	2	1	1	1
-41.25°	2	2	2	2	2	2	2	2	1	1	1
-42.5°	2	2	2	2	2	2	2	1	1	1	1
-43.75°	2	2	2	2	2	2	2	1	1	1	1
-45°	2	2	2	2	2	2	2	1	1	1	1
-46.25°	2	2	2	2	2	2	1	1	1	1	1
-47.5°	2	2	2	2	2	2	1	1	1	1	1
-48.75°	2	2	2	2	2	1	1	1	1	1	1
-50°	2	2	2	2	2	1	1	1	1	1	1
-51.25°	2	2	2	2	1	1	1	1	1	1	1
-52.5°	2	2	2	2	1	1	1	1	1	1	1
-53.75°	2	2	2	1	1	1	1	1	1	1	1
-55°	2	2	2	1	1	1	1	1	1	1	1
-56.25°	2	2	1	1	1	1	1	1	1	1	1
-57.5°	2	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	0
-67.5°	1	1	1	1	1	1	1	1	1	1	0
-68.75°	1	1	1	1	1	1	1	1	1	0	0
-70°	1	1	1	1	1	1	1	1	0	0	0
-71.25°	1	1	1	1	1	1	1	0	0	0	0
-72.5°	1	1	1	1	1	1	0	0	0	0	0
-73.75°	1	1	1	1	0	0	0	0	0	0	0
-75°	1	1	1	0	0	0	0	0	0	0	0
-76.25°	1	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	1	0	0	0	0	0	0	0	0	0	0
62.5°	1	0	0	0	0	0	0	0	0	0	0
61.25°	1	1	0	0	0	0	0	0	0	0	0
60°	1	1	0	0	0	0	0	0	0	0	0
58.75°	1	1	0	0	0	0	0	0	0	0	0
57.5°	1	1	1	0	0	0	0	0	0	0	0
56.25°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	0	0	0	0	0	0	0	0
53.75°	1	1	1	1	0	0	0	0	0	0	0
52.5°	1	1	1	1	0	0	0	0	0	0	0
51.25°	1	1	1	1	0	0	0	0	0	0	0
50°	1	1	1	1	0	0	0	0	0	0	0
48.75°	1	1	1	1	1	0	0	0	0	0	0
47.5°	1	1	1	1	1	0	0	0	0	0	0
46.25°	1	1	1	1	1	0	0	0	0	0	0
45°	1	1	1	1	1	0	0	0	0	0	0
43.75°	1	1	1	1	1	0	0	0	0	0	0
42.5°	1	1	1	1	1	0	0	0	0	0	0
41.25°	1	1	1	1	1	1	0	0	0	0	0
40°	1	1	1	1	1	1	0	0	0	0	0
38.75°	1	1	1	1	1	1	0	0	0	0	0
37.5°	1	1	1	1	1	1	0	0	0	0	0
36.25°	1	1	1	1	1	1	0	0	0	0	0
35°	1	1	1	1	1	1	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	1	1	1	1	0	0	0	0	0
32.5°	1	1	1	1	1	1	0	0	0	0	0
31.25°	1	1	1	1	1	1	0	0	0	0	0
30°	1	1	1	1	1	1	0	0	0	0	0
28.75°	1	1	1	1	1	1	1	0	0	0	0
27.5°	1	1	1	1	1	1	1	0	0	0	0
26.25°	1	1	1	1	1	1	1	0	0	0	0
25°	1	1	1	1	1	1	1	0	0	0	0
23.75°	1	1	1	1	1	1	1	0	0	0	0
22.5°	1	1	1	1	1	1	1	0	0	0	0
21.25°	1	1	1	1	1	1	1	0	0	0	0
20°	1	1	1	1	1	1	1	0	0	0	0
18.75°	1	1	1	1	1	1	1	0	0	0	0
17.5°	1	1	1	1	1	1	1	0	0	0	0
16.25°	1	1	1	1	1	1	1	0	0	0	0
15°	1	1	1	1	1	1	1	0	0	0	0
13.75°	1	1	1	1	1	1	1	0	0	0	0
12.5°	1	1	1	1	1	1	1	0	0	0	0
11.25°	2	1	1	1	1	1	1	0	0	0	0
10°	2	1	1	1	1	1	1	0	0	0	0
8.75°	2	1	1	1	1	1	1	0	0	0	0
7.5°	2	1	1	1	1	1	1	0	0	0	0
6.25°	2	1	1	1	1	1	1	0	0	0	0
5°	2	1	1	1	1	1	1	0	0	0	0
3.75°	2	1	1	1	1	1	1	0	0	0	0
2.5°	2	1	1	1	1	1	1	0	0	0	0
1.25°	2	1	1	1	1	1	1	0	0	0	0
0°	2	1	1	1	1	1	1	0	0	0	0
-1.25°	2	1	1	1	1	1	1	0	0	0	0
-2.5°	2	1	1	1	1	1	1	0	0	0	0
-3.75°	2	1	1	1	1	1	1	0	0	0	0
-5°	2	1	1	1	1	1	1	0	0	0	0
-6.25°	2	1	1	1	1	1	1	0	0	0	0
-7.5°	2	1	1	1	1	1	1	0	0	0	0
-8.75°	2	1	1	1	1	1	1	0	0	0	0
-10°	2	1	1	1	1	1	1	0	0	0	0
-11.25°	2	1	1	1	1	1	1	0	0	0	0
-12.5°	1	1	1	1	1	1	1	0	0	0	0
-13.75°	1	1	1	1	1	1	1	0	0	0	0
-15°	1	1	1	1	1	1	1	0	0	0	0
-16.25°	1	1	1	1	1	1	1	0	0	0	0
-17.5°	1	1	1	1	1	1	1	0	0	0	0
-18.75°	1	1	1	1	1	1	1	0	0	0	0
-20°	1	1	1	1	1	1	1	0	0	0	0
-21.25°	1	1	1	1	1	1	1	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	1	1	1	1	0	0	0	0
-23.75°	1	1	1	1	1	1	1	0	0	0	0
-25°	1	1	1	1	1	1	1	0	0	0	0
-26.25°	1	1	1	1	1	1	1	0	0	0	0
-27.5°	1	1	1	1	1	1	1	0	0	0	0
-28.75°	1	1	1	1	1	1	1	0	0	0	0
-30°	1	1	1	1	1	1	0	0	0	0	0
-31.25°	1	1	1	1	1	1	0	0	0	0	0
-32.5°	1	1	1	1	1	1	0	0	0	0	0
-33.75°	1	1	1	1	1	1	0	0	0	0	0
-35°	1	1	1	1	1	1	0	0	0	0	0
-36.25°	1	1	1	1	1	1	0	0	0	0	0
-37.5°	1	1	1	1	1	1	0	0	0	0	0
-38.75°	1	1	1	1	1	1	0	0	0	0	0
-40°	1	1	1	1	1	1	0	0	0	0	0
-41.25°	1	1	1	1	1	1	0	0	0	0	0
-42.5°	1	1	1	1	1	0	0	0	0	0	0
-43.75°	1	1	1	1	1	0	0	0	0	0	0
-45°	1	1	1	1	1	0	0	0	0	0	0
-46.25°	1	1	1	1	1	0	0	0	0	0	0
-47.5°	1	1	1	1	1	0	0	0	0	0	0
-48.75°	1	1	1	1	1	0	0	0	0	0	0
-50°	1	1	1	1	0	0	0	0	0	0	0
-51.25°	1	1	1	1	0	0	0	0	0	0	0
-52.5°	1	1	1	1	0	0	0	0	0	0	0
-53.75°	1	1	1	1	0	0	0	0	0	0	0
-55°	1	1	1	0	0	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	1	1	0	0	0	0	0	0	0	0
-58.75°	1	1	0	0	0	0	0	0	0	0	0
-60°	1	1	0	0	0	0	0	0	0	0	0
-61.25°	1	1	0	0	0	0	0	0	0	0	0
-62.5°	1	0	0	0	0	0	0	0	0	0	0
-63.75°	1	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: P220616 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED3590-F-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)